

# CROSS X STEP



STEP

**2 IN 1  
LADDER**

SERIES FXS1400HD  
**SHELF**

**6-IN CLOSER TO  
WORKING AREA\***

"V" shaped ProTop allows you to lean the ladder on corners, walls, and poles

LOCKING LATCH TO SECURE REAR SECTION

• **RAPTOR BOOT** - PROTECTS FIBERGLASS AND HAS NON-MARRING HEAVY DUTY BONDED TREAD

• **SHOX** - SUPERIOR IMPACT ABSORPTION, PROTECTS FIBERGLASS AND STEP

**ANSI**  
Standard for Ladders

**OSHA**  
SAFETY

"H" BRACING MAKES IT EASY TO OPEN \*8, 10, 12 FT ONLY

\* Patent Pending



MODEL	LADDER SIZE	BOTTOM WIDTH (IN)	APPROX. SPREAD (IN)	APPROX. WEIGHT (LBS)	APPROX. CUBES (FT)	SHEFLADDER		STEPLADDER	
						HIGHEST STANDING LEVEL (IN)	MAX. REACH	HIGHEST STANDING LEVEL (IN)	MAX. REACH
FXS1404HD	4'	20 3/4	24	16	4.0	11"	7' 6"	1' 11"	8' 6"
FXS1406HD	6'	23 3/4	36	23	6.8	2' 10"	9' 5"	3' 9"	10' 4"
FXS1408HD	8'	26 3/4	48	31	10.1	4' 9"	11' 4"	5' 8"	12' 3"
FXS1410HD	10'	29 3/4	60	39	14.0	6' 8"	13' 3"	7' 7"	14' 2"
FXS1412HD	12'	32 3/4	71	48	18.5	8' 6"	15' 1"	9' 6"	16' 1"

LOUISVILLE LADDER FXS1400HD FLYER v1 ©2016 Louisville Ladder, Inc. All rights reserved.

\*Compared to a regular step ladder