Test Gauges

For Gas or Water Service



Gas Test Gauge





Gas Test: 2" Dial

Water Test: 21/2" Dial

Gas Test: 3/4 NPT Female

Water Test: 3/4 NPT Hose Bib

Trerice **Gas** and **Water Test Gauges** are integral tools for passing building inspections. Once the system has been pressurized, any leaks are visible as a pressure drop on the dial of the Gas Test Gauge. The Water Test Gauge has a ³/4 NPT hose bib connection mounted at 12 o'clock for easy viewing and accurately measures in-line water pressure. A maximum register pointer is available on either gauge having a dial range of 60 psi or greater.

Specifications Models

120 Gas Test Gauge122 Water Test Gauge

Dial Sizes Gas Test: 2" (50mm)

Water Test: 2 1/2" (63mm)

Wetted Parts

Bronze tube, brass socket

Connection Gas Test: 3/4 NPT female Water Test: 3/4 female hose-bib connection,

12 o'clock mount

Steel, black painted

Case Steel, black painted

Ring Steel, black painted

Window Acrylic

Pointer Steel, black painted

Adjustable via screw on dial face

Accuracy 3-2-3%, Grade B

Maximum Temperature

150°F (65°C)

Approximate Shipping Weight

2" Gas Test: 0.6 lbs. (0.27 kg) 21/2" Water Test: 0.4 lbs. (0.18 kg)

Gas Test Gauge Part Number *	Water Test Gauge Part Number *	Range
PGT12010	N/A	0 to 15 psi
PGT120190	N/A	0 to 15 psi/kPa
PGT120191	N/A	0 to 30 psi/kPa
PGT120192	N/A	0 to 60 psi/kPa
PGT120193	N/A	0 to 100 psi/kPa
N/A	PWT122194	0 to 160 psi/kPa
N/A	PWT122196	0 to 300 psi/kPa


^{*} Add MAX to any part number for Maximum Registering Pointer. (60 psi and greater only) Example: **PGT120192MAX**

Test Gauges

All dimensions are nominal. Dimensions in [] are in millimeters.

For Gas or Water Service

WATER TEST GAUGE



GAS TEST GAUGE

