Quartz





Quartz[®] Explosionproof valve monitoring

The Quartz is available in explosionproof (QX), nonincendive, intrinsically safe (QN), and general purpose (QG) versions. The robust epoxy-coated anodized aluminum construction, and optional stainless steel version, makes this platform extremely durable and wellsuited for use in corrosive, heavy washdown environments.

Options may be selected to accommodate most applications.

The Quartz series

The StoneL Quartz series is durable, corrosion-resistant, and versatile, making it ideal for most of your process valve monitoring requirements.

Enclosures optimized for environment



QX: Explosionproof, water tight and corrosion-resistant enclosure is approved for use in Div. 1/Zone 1 hazardous areas. Available options include stainless steel and epoxy-coated anodized aluminum.



QN: Nonincendive is approved for Div. 2/Zone 2 hazardous environments with proximity sensors using a clear cover. Intrinsically safe NAMUR sensors or passive switches are available for Div. 1/Zone 0 applications.



QG: General purpose features a clear Lexan® cover with mechanical switches. All enclosures are Type 4, 4x, and 6.

Save space with low profile design

Clearance above the actuator is critical in complex piping systems. Quartz boldly displays valve position and encloses all electrical components in an explosionproof compartment with less than 5" clearance requirement.



Features

1. Enclosures optimized for environment

Available in three enclosure styles suitable for use in various process environment areas.

2. Rapid enclosure access

Screw-on cover allows quick enclosure access, saving you valuable maintenance and set-up time. The cover provides a vaportight seal and allows entry to internal components in less than five seconds.

3. Faster wiring

Pre-wired and labeled terminal strip enables quick, convenient attachment of field wires.

- 4. Wide variety of switching & communication Switching options include dual module sensors and communication, Maxx-Guard proximity switches, and mechanical switches. Continuous signal output is available in a 4-20 mA position transmitter.
- 5. Quick set cams are easy to adjust Touch and tune switch settings allow you to make adjustments in seconds without the use of tools.
- 6. Dual shaft o-ring seals eliminate corrosion Top inner and bottom outer shaft o-rings seal the drive bushing from both external corrosives and internal contaminants that enter the enclosure.



7. Special drive bushing assures long cycle life The oil impregnated bronze bushing maintains smooth op

The oil impregnated bronze bushing maintains smooth operation and eliminates the potential for shaft seizure due to actuator shaft eccentricity.

8. Bold space saving visual indication

Visual indicator offers excellent viewability without sacrificing accessibility or adding to space requirements. Indicators are also available with continuous percentage or three-way indication. (See page 51)

Wide variety of switch/sensor functions

A wide variety of switch/sensor communications and position transmitters may be selected for the Quartz series. Options include 2, 4 or 6 mechanical or proximity switches, position transmitters with or without switches, and the StoneL dual module with two SST or two





Proximity switches

Mechanical switches

Speed installation with LED indication

StoneL's coordinated visual indicator and LEDs give you an extra measure of safety and increased convenience during plant start-up and operation. Green visual indication and green LED means the valve is open and the computer circuit is properly operating. Red

visual indication and red LED means the valve is closed and the computer is properly matched. All systems are functioning properly.



Eliminate seal fittings in Division 1 and 2 areas

FMus ratings certify the Quartz QX series with proximity switches for use without seal fittings in all hazardous areas. By passing special pressure piling tests, the all aluminum enclosure was certified for this elite distinction. Now, a time-consuming procedure can be safely eliminated in Division 1 and Division 2 areas.

Consolidate your components and minimize costs

NAMUR sensors or AS-

Interface, DeviceNet[™]

or Foundation Fieldbus

communication

capabilities.

The Quartz design offers up to three conduit entries with extra wire terminations. By terminating solenoid valves in the switch enclosure, significant savings are realized by eliminating a junction box, wiring, conduit materials, and labor.



Mounting kits Kits may be ordered in 316 stainless steel. Consult StoneL factory for details.

Sealed mounting kit

Mounting to standard actuators is achieved with a bold visual indicator and sealed mounting system. Sealed mounting is exclusive with extended visual indicator option N. Adaptor plate is epoxy-coated anodized aluminum. All fasterners and couplings are stainless steel.



- Direct mount to actuators with VDI/VDE 3845 interface.
- Tolerant to vibration and mechanical stress.
- Prevents contamination and icing in coupling area.
- Available for all VDI/VDE 3845 (NAMUR) mounting configurations and most quarter-turn actuators.



Quarter-turn actuators

Low profile convenient mounting systems are readily available in stainless steel for most standard actuators.



Positioners

Quartz position transmitter and switches may be retrofitted directly to most positioners. 4-20 feedback may be provided on simple pneumatic positioners.



Manual valves

Proper fit and operation is assured with StoneL's custom designs for each manual valve. Hundreds of unique mounting systems have been designed and fabricated for manually operated valves.



Linear operators

Precision ball joint connections attach the Quartz to valve travel stems. Stroke lengths ranging from 20 mm to 150 mm (¾" to 6") may be easily accommodated.



Quartz stainless steel option



For the most challenging environments

The explosion proof Quartz for process valve monitoring is available with a 316 stainless steel enclosure that is extremely durable and well-suited for use in corrosive, heavy washdown and high seas environments. A broad range of switching, position

transmitters and communication options may be selected to accommodate most applications. You can attach the Quartz to quarter-turn actuators, manual operators, linear operators, and positioners using readily available stainless steel mounting systems.

Position transmitter

4-20 mA position transmitter

Position transmitters provide a precise 4-20 mA signal on a twowire DC loop. Control valves and dampers are accurately monitored through their range of travel offering assurance of exact valve position at all times. Several function options are available making it easy to find the correct product that fits your desired application. Choose a position transmitter with a standard potentiometer (5_), a vibration proof, high-performance potentiometer (7_), or the innovative non-contact magnetic resistive (mag res) digital transmitter (T_).

Digital transmitter

The digital transmitter utilizes an innovative non-contact magnetic sensor. The module features easy push button calibration to reduce set-up and commissioning time. With the bold red/green LED indication, the unit is visible from a distance and the calibration diagnostic LED indications confirm set up is valid. The position transmitter module housed with the Quartz platform is fully sealed and potted, providing reliable operation and outstanding vibration tolerance in tough applications.



Position transmitter



Digital transmitter

Position transmitter specifications				
	Standard transmitter (5_)	High performance transmitter (7_)	Digital transmitter (T_)	
Output	2-wire 4-20 mA	2-wire 4-20 mA	2-wire 4-20 mA	
Supply source	10 - 40 VDC	10 - 40 VDC	10 - 40 VDC	
Indication	None None Red/Green LED*			
Span range	35° to 270° 35° to 270° 35° to 320°			
Maximum loading	700 ohms @ 24 VDC 700 ohms @ 24 VDC 683 ohms @ 24 VDC			
Refresh rate	< 1 ms < 5 ms			
Linearity error	+/-0.85° +/-0.35° +/-0.35°		+/-0.35°	
Cycle life	2 million rotations 50 million rotations Unlimited			
Vibration tolerance	Acceptable Outstanding Outstanding			
* Open / Closed LED	position indication and	d calibration status diag	gnostics	
Electrical schematic - 4 - 20 mA readout + +				
Power Supply				

Sensors and communications

Dual module system

The Quartz series is available with the dual module in its various configurations. Two solid state sensors and/or communications and other electronics are sealed in for the ultimate in reliability and convenience. All dual module versions have a five year warranty.



SST switching sensors (35)	
Configuration	(2) SST solid state sensors Wire terminations for one or two solenoids
Operations	Normally open (NO) for Normally closed (NC), consult factory
Maximum current inrush	1.0 amp
Maximum current continuous	0.1 amp
Minimum on current	0.5 mA
Maximum leakage current	0.25 mA (AC) 0.15 mA (DC)
Voltage range	20 - 250 VAC 8 - 250 VDC
Maximum voltage drop	6.5 volts @ 10 mA 7.2 volts @ 100 mA
Wiring diagram (35) SST &	Solenoid Valve Solenoid of Utput 1 2 Solenoid Valve Solenoid of Utput 1 2 Solenoid Valve 1 2 2 Valve Open 2 2 2 Valve Closed 2 2 2 Valve Closed 2 2 2

Sensor specification	s
NAMUR sensor (45)	
Configuration	(2) NAMUR sensors (EN 60947-5-6; I.S.) Wire terminations for one or two solenoids
Operation	Normally closed NAMUR sensors (solid state)
Voltage range	5 - 25 VDC
Current ratings	Target on I<1 mA Target off I>3 mA
Wiring diagram (45)	Solenoid Valve Solenoid {1 2
NAMUR	$ \begin{array}{c c} Solenoid \\ Power \\ \left(\begin{array}{c} 1 \\ 2 \\ \end{array} \right) \\ \left(\begin{array}{c} Valve \\ open \end{array} \right) \\ \left(\begin{array}{c} + \\ - \\ \end{array} \right) \\ \left(\begin{array}{c} Valve \\ closed \end{array} \right) \\ \left\{ \begin{array}{c} + \\ - \\ \end{array} \right\} \\ \left(\begin{array}{c} + \\ - \\ \end{array} \right) \\ \left(\begin{array}{c} + \\ \end{array} \right) \\ \left(\begin{array}{c} $

Valve Communicatio	n Terminal (VCT) specifications
DeviceNet™ (92)	
Configuration	(2) Discrete inputs (open and closed)(2) Power outputs (solenoids)(1) 4-20 mA auxiliary analog input, 10-bit resolution; no additional power source required
Transmission rate	Software selectable 125K, 250K or 500K baud
Messaging	Polling, cyclic and change of state
Outputs	4 watts @ 24 VDC outputs combined
Outputs, voltage	24 VDC (with input voltage ranging from 10 - 24 VDC)
Other features	Predetermined output fail state
Wiring diagram (92) DeviceNet	V+ CAN H SHIELD CAN L V- Ain - Ain - Ain - Ain + Solenoid Valve OUT1 - 24 VDC + Solenoid Valve OUT2 - V - V - V - V - V - V - V - V

Sensors and communications

	tion Terminal (VCT) specifications	
AS-Interface (96)		
Configuration	(2) Discrete sensor inputs(2) Auxiliary discrete inputs(2) Power outputs (solenoids)	
Maximum current	160 mA, both outputs combined	
Auxiliary inputs	24 VDC @ 2 mA (self-powered)	
Output	4 watts @ 24 VDC both outputs combined	
Outputs, voltage	21 - 26 VDC	
Configuration code	ID=F, IO=4; user defined (4DI/2DO)	
AS-i version	3.0	
Devices per network	31	
	AUX IN + AUX IN + AUX IN + AUX IN - AUX IN2 - 3 WIRE RTN OUT2 + OUT2 -	
	Solenoid Valve OUT2 - OUT1 + OUT1 + OUT1 - O	
AS-Interface VCT with ex	OUT1 + Solenoid Valve OUT1 -	
AS-Interface VCT with ext Configuration	OUT1 + Solenoid Valve OUT1 -	
	OUT1 + OUT1 + OUT1 -	
Configuration	ended addressing (97) (2) Discrete sensor inputs (2) Auxiliary discrete inputs (1) Power output (solenoid)	
Configuration Maximum current	ended addressing (97) (2) Discrete sensor inputs (2) Auxiliary discrete inputs (1) Power output (solenoid) 100 mA	
Configuration Maximum current Auxiliary inputs	OUT1 + OUT1 + Solenoid Valve OUT1 +	
Configuration Maximum current Auxiliary inputs Output	OUT1 + OUT1 + Solenoid Valve OUT1 +	
Configuration Maximum current Auxiliary inputs Output Output, voltage	ended addressing (97) (2) Discrete sensor inputs (2) Auxiliary discrete inputs (1) Power output (solenoid) 100 mA 24 VDC @ 2 mA (self-powered) 2 watts @ 24 VDC 21 - 26 VDC	
Configuration Maximum current Auxiliary inputs Output Output, voltage Configuration code	ended addressing (97) (2) Discrete sensor inputs (2) Auxiliary discrete inputs (1) Power output (solenoid) 100 mA 24 VDC @ 2 mA (self-powered) 2 watts @ 24 VDC 21 - 26 VDC ID=A, IO=4; user defined (4DI/1DO)	

Valve Communication Terminal (VCT) specifications			
Foundation Fieldbus VCT, bus powered (93)			
Configuration	(2) Discrete Inputs (2) Power outputs (solenoids) Multiple DI/DO blocks or modified output block		
Outputs	2 mA @ 6.5 VDC ea current limited to 2	ch 2 mA (bus powered)	
Devices per network	Max of 16 devices recommended		
Wiring diagram (93) FOUNDATION	Solenoid Valve	FB + FB - OUT1 + OUT1 - OUT2 + OUT2 - SIM JMPR SIM JMPR	

Sensors and switches

Maxx-Guard proximity switch

Maxx-Guard hermetically-sealed switches are suitable for computer input circuits and general purpose applications. SPDT tungsten contacts are designed for 125 VAC computer inputs and 240 VAC moderate power applications. SPDT rhodium contacts are suitable for both 24 VDC and 120 VAC computer inputs. SPST ruthenium contacts are ideal for either 24 VDC or 125 VAC low power computer inputs.



Electrical ratings	SPST NO; passive (intrinsically safe) 0.10 amp @ 10 - 30 VDC 0.1 volts @ 10 mA
Maximum voltage drop	
5	0.1 volts @ 10 mA
	0.5 volts @ 100 mA
Contact composition	Ruthenium
P switch	
Configuration	SPST NO
Electrical ratings	0.15 amp @ 125 VAC/30 VDC
5	0.1 volts @ 10 mA 0.5 volts @ 100 mA
Contact composition	Ruthenium

Single-Pole Double-Throw (SPDT)		
G switch		
Configuration	SPDT	
Electrical ratings	0.2 amp @ 120 VAC 0.30 amp @ 24 VDC	
Maximum voltage drop	0.1 volts @ 10 mA 0.5 volts @ 100 mA	
Contact composition	Rhodium	
H switch		
Configuration	SPDT	
Electrical ratings	240 volts max; 3 amps max 100 watts max; 2.0 watts min	
Maximum voltage drop	0.1 volts @ 10 mA 0.5 volts @ 100 mA	
Contact composition	Tungsten	
M switch		
Configuration	SPDT; passive (intrinsically safe)	
Electrical ratings	0.10 amp @ 10 - 30 VDC	
Maximum voltage drop	0.1 volts @ 10 mA 0.5 volts @ 100 mA	
Contact composition	Rhodium	
S switch		
Configuration	SPDT (LED)	
Electrical ratings	0.1 amp @ 120 VAC 0.1 amp @ 24 VDC	
Maximum voltage drop	3.5 volts @ 10 mA 6.5 volts @ 100 mA	
Contact composition	Rhodium	
SPDT		
C NO		

Maxx-Guard proximity switch

Specifications		
Temperature range	-40° C to 80° C (-40° F to 176° F)	
Seal	Hermetically-sealed	
Operating life	5 million cycles	
Warranty	Two years	

Sensors and switches

Mechanical switch (SPDT)

Low cost single-pole double-throw mechanical switches with silver contacts are recommended for high power 125 VAC applications. Gold contacts may be used in 24 VDC computer input applications when cycle life does not exceed 100,000 operations.

Mechanical switch (SPDT)		
Silver contacts (_V switch)		
Electrical ratings	10 amp @ 125⁄250 VAC 0.5 amp @ 125 VDC	
Operating life	400,000 cycles	
Not recommended for electrica	l circuits operating at less than 20 mA @ 24 VDC.	
Gold contacts (_W switch)		
Electrical ratings	1 amp @ 125 VAC 0.5 amp @ 30 VDC	
Operating life	100,000 cycles	
C NC	9002 PU (1) V3L-389 IIAJ/3#F253 <u>420</u> .277 vAC L156 L156 V3L-389 VAC L156	

Mechanical switch (DPDT)

Double-pole double-throw mechanical switches enable two electrical circuits to be activated simultaneously. Each switch circuit is electrically isolated from the other. As with standard silver contacts, DPDT switches are designed to operate in high-power applications.

Mechanical switch (DPDT)		
14 switch		
Electrical ratings	4.5 amp @ 125/250 VAC, 24 - 125 VDC	
Operating life	250,000 (VAC), 100,000 (VDC) cycles	
Not recommended for electrical circuits operating at less than 20 mA @ 24 VDC.		
9 NC C • NO 9 NC C • NO	NO 2 NO 3 NO 7 USLA NO 3	

SST switching sensor

Solid state SST proximity sensors are ideal for use in AC and DC computer input circuits.

SST switching sensors		
_X switch		
Operation	NO/NC (cam selectable)	
Maximum inrush current	1.0 amps @ 125 VAC/VDC	
Maximum continuous current	0.1 amps @ 125 VAC/VDC	
Minimum on current	2.0 mA	
Leakage current	Less than 0.50 mA	
Voltage range	24 - 125 VAC 8 - 125 VDC	
Maximum voltage drop	6.5 volts @ 10 mA 7.5 volts @ 100 mA	
Operating life	Unlimited	
Warranty	Five years	

RIE	S					
(E	xplos	ionpro	of dual	modu	ules and V	′CTs
	FUI	отто	NS			
	Sen	sor/sv	vitchin	g moo	dules (pro	oximity type)
	33	SST N	O swite	- hing s	ensor du	al module [old]
	35	SST U	sensor dual module [new]			
	44	NAMI	JR dual	modu	ile <i>[old]</i> (E	N 60947-5-6; I.S.)
	45	NAMU	JR dual	modu	ıle [new] ((EN 60947-5-6; I.S.)
	Valv	ve Con	nmuni	ation	Termina	ils (VCTs)
	92	Devic	eNet™			
	93	Found	dation F	ieldbu	us (bus po	owered; I.S.)
	96	AS-Int	erface			
	97	AS-Int	erface	(with e	extended	addressing)
		EN	CLOSU	IRE		
		Е	Alum	num N	North Am	erican (NEC/CEC)
		R		******	nternatio	
		F	Alum	num E	Brazilian	
		S*	Stainl	ess ste	el North	American (NEC/CEC)
		Т*	Stainl	ess ste	el Interna	ational (IEC)
		M*	Stainl	ess ste	el Brazilia	n
			* Avai	lable v	vith 03 or	06 conduit entry only
			со	NDUI	T ENTRI	ES
			02	(1) 3⁄4	" NPT & (1) 1⁄2" NPT
			03	(1) 3⁄4	" NPT & (2	2) 1⁄2" NPT
			05	(2) M	120	
			06	(3) M	120	
				0	UTPUT	
				S	Short v	visual indicator
				N	Extend	ed visual indicator
					VIS	UAL INDICATOR [see chart on page 51]
					RA	Red closed/green open
					GA	Green closed/red open
					1A	T-1 three way flow path
					2A	T-2 three way flow path
					3A	T-3 three way flow path
					4A	T-4 three way flow path
					5A	T-5 three way flow path
					0A	No indication
					XA	Special
					CA	Continuous
del	num	her ov	ampla			
del	num 35	ber exa E	ample 02	N	RA	- OPTIONAL
•					ĸА	
			LNUN			PARTNERSHIP ID
unt	ing h	nardwa	re requ	ired ar	nd sold	Some models may include 5-digit identification suffix.

Model	select	or							
SERIES			_	_					
QX Explo	osionpro	of proxir	nity swite	hes					
FL	υνςτιο	NS							
	ensors								
28	(2) P+	 (2) P+F special 3-wire NPN sensor; NBB2-V3-E0-V5 (2) PNP solid state 3-wire P+F sensor; NBB2-V3-E2-V5 (2) SPDT Maxx-Guard (low current) 							
2F	= (2) PN								
20	G (2) SPI								
2H	H (2) SPI	DT Maxx-	-Guard (3	amp)				
21	(2) SPS	ST Maxx-Guard (LED)							
2F	2P (2) SPST Maxx-Guard								
		•••••	Guard (L						
		•••••	Guard (lo		······				
		•••••	Guard (3)				
	• (4) SP	•••••	Guard (Ll	ED)					
		•••••	-Guard (L	FD)					
		••••••							
		CLOSUF							
	E				erican (NEC/CEC)				
	F		um Interi um Brazil						
	S*	••••			American (NEC/CEC)				
	T*				tional (IFC)				
	M*	•••••	s steel Br						
		* Availa	ble with	03 or	06 conduit entry only				
		CON	DUITEN	ITRIF					
) 1⁄2" NPT				
			• • • • • • • • • • • • • • • • • • • •) ½" NPT				
			(2) M20		£				
		06	(3) M20						
			OUTP	UT					
			S Sh	nort vi	isual indicator				
			N Ex	tende	ed visual indicator				
				visu	JAL INDICATOR [see chart on page 51]				
				RA	Red closed/green open				
				GA	Green closed/red open				
				1A	T-1 three way flow path				
				2A	T-2 three way flow path				
				3A	T-3 three way flow path				
				4A	T-4 three way flow path				
				5A	T-5 three way flow path				
				0A	No indication				
				XA	Special				
				CA	Continuous				
Model nur	mber exa	mple							
QX 20		02	N	RA	- OPTIONAL				
		LNUME			PARTNERSHIP ID				
Mounting	g hardwa			old	Some models may include				
separately	/.				5-digit identification suffix.				

I ES Evolo	ionn	ofme	anie-'	cuvit-ch-	s and position transmitters						
EXPIO:	sionpro	of meci	nanicai	switche	s and position transmitters						
FU	ΝΟΤΙΟ	NS									
		al swite									
		DT swite									
	 W (2) SPDT switches, gold contact V (4) SPDT switches 										
		•••••		old cont	act						
	•••••	DT swit									
		•••••		•••••							
		r ansmi ard with		itches							
		•••••	•••••	•••••	-Guard (low current)						
	••••	•••••		•••••	nanical switches						
	•••••	•••••		•••••	nanical switches, gold contact						
53	Stand	ard with	n SST (3	3) NO sv	witching sensor dual module						
54	Stand	ard with	n NAMI	JR (44) c	lual module (EN 60947-5-6; I.S.)						
70	High p	perform	ance (l	HP) with	no switches						
	•••••			•••••	d (low current)						
	•••••	•••••		•••••	ng sensor dual module						
	•••••	•••••		•••••	odule (EN 60947-5-6; I.S.)						
	••••	•••••	•••••	•••••	o switches ST (35) NO switching sensor dual module						
	•••••	•••••		•••••	AMUR (45) dual module (EN 60947-5-6; I.S.)						
		•••••									
				•••••	erican (NEC/CEC)						
		Aluminum International (IEC) Aluminum Brazilian Stainless steel North American (NEC/CEC) Stainless steel International (IEC)									
		Stainle									
		* Avail	vailable with 03 or 06 conduit entry only								
		co	TIUDN	ENTRI	ES						
					 1) 1⁄2" NPT						
		03	(1) 3/4"	NPT & (2	2) 1⁄2" NPT						
			(2) M2	•••••	· · · · · · · · · · · · · · · · · · ·						
		06	(3) M2	20							
			ou	TPUT							
			S		risual indicator						
			N	••••	ed visual indicator						
				VISI	JAL INDICATOR [see chart on page 51]						
				RA	Red closed/green open						
				GA							
				1A	T-1 three way flow path						
				2A	T-2 three way flow path						
				3A	T-3 three way flow path						
				4A	T-4 three way flow path						
				5A	T-5 three way flow path						
				0A	No indication						
				XA	Special						
				CA	Continuous						
	bar	mela									
1 num 2V	iber exa E	impie 02	N	RA	- OPTIONAL						
				-114							
		L NUM re requi			PARTNERSHIP ID Some models may include						

lodel selector													
SERI	ES												
QG	Gener	al purp	ose me	chanica	al switch	nes (clear cover)							
	FUI	отто	N										
	Me	chanic	al swite	hes									
	2V	(2) SPDT switches											
	2W	(2) SP[DT swite	ches, go	old conta	act							
	4V	(4) SP[DT swite	ches									
	4W	(4) SP[DT swite	ches, go	old conta	act							
	14	(2) DP	(2) DPDT switches										
		ENCLOSURE											
		С	Gener	al purp	ose, univ	versal							
		CONDUIT ENTRIES											
			02	(1) 3⁄4"	NPT & (1	1) 1⁄2" NPT							
			03	••••	•••••	2) 1⁄2" NPT							
			05	(2) M2	0								
			06	(3) M2	0								
				OU	TPUT								
				S	Short vi	visual indicator							
				N	Extende	ed visual indicator							
					VISU	UAL INDICATOR [see chart on page 51]							
					RA	Red closed/green open							
					GA	Green closed/red open							
					1A	T-1 three way flow path							
					2A	T-2 three way flow path							
					ЗA	T-3 three way flow path							
					4A	T-4 three way flow path							
					5A	T-5 three way flow path							
					0A	No indication							
					XA	Special							
					CA	Continuous							
Mode	num	ber exa	mole										
QG	2V	C	02	Ν	RA	- OPTIONAL							
	I	MODE	LNUM	BER		PARTNERSHIP ID							
Mour separ		hardwa	re requi	red and	d sold	Some models may include 5-digit identification suffix.							

Nod	el <u>s</u> e	elect	or								
SERI	ES										
QN N	Vonin	cendiv	e dual r	module	es and VC	CTs					
	FUI	отто	NS								
	Sen	sor/sv	vitchin	g [proxi	imity type	2]					
	33	SST N	O switc	hing se	ensor du	al module <i>[old]</i>					
35 SST Universal NO switching sensor dual module [new]											
	ls (VCTs)										
	92	92 DeviceNet™									
	93	Found	dation F	ieldbu	s (bus po	owered) [intrinsically safe]					
	96	AS-Int	erface		•••••						
	97	AS-Int	erface	with ex	tended	addressing					
		EN	CLOSU	JRE							
		Cle	ar cove	er							
		С	North	Amerio	can (NEC	/CEC)					
		D	Intern	ational	(IEC)						
			со	NDUIT	ENTRI	ES					
			02	(1) 3⁄4"	NPT & (1) 1⁄2" NPT					
			03	(1) 3⁄4"	NPT & (2	2) 1⁄2" NPT					
			05	(2) M2	20						
			06	(3) M2	20						
				ou	TPUT						
				S	Short v	isual indicator					
				Ν	Extend	ed visual indicator					
					VIS	UAL INDICATOR [see chart on page 51]					
					RA	Red closed/green open					
					GA	Green closed/red open					
					1A	T-1 three way flow path					
					2A	T-2 three way flow path					
					3A	T-3 three way flow path					
					4A	T-4 three way flow path					
					5A	T-5 three way flow path					
					0A XA	No indication Special					
					CA						
/odel	num	ber exa	ample	-	-						
QN	35	С	02	S	RA	- OPTIONAL					
	I	MODE		IBER		PARTNERSHIP ID					
			re requ		d sold	Some models may include 5-digit identification suffix.					

Model selector											
SER	IES										
QN	Nonin	cendiv	e proxii	mity swi	tches						
	FUI	огто	N								
	Sen	sors									
	2F	(2) PN	P solid	state 3-v	wire P+I	^E sensor; NBB2-V3-E2-V5					
	irrent)										
	2H (2) SPDT Maxx-Guard (3 amp) 2L (2) SPST Maxx-Guard (LED)										
	2P										
	25 (2) SPDT Maxx-Guard (LED)										
	4G	(4) SP[DT Max	x-Guard	(low cu	irrent)					
	4H	(4) SP[DT Max	x-Guard	(3 amp)					
	4L	(4) SPS	ST Max	k-Guard	(LED)						
	4P	(4) SPS	ST Max	k-Guard							
	4S	(4) SP[DT Max	x-Guard	(LED)						
	4X	(4) SST	r senso	r (LED)							
		EN	CLOSU	IRE							
			ar cove								
		C		Americ	an (NEC	/CEC)					
			Intern								
				(1) 34" NPT & (1) 1/2" NPT							
				(1) 34" NPT & (2) 1/2" NPT							
				(2) M20	•••••						
			06	(3) M20	0						
				OUT	TPUT						
				S	Short v	isual indicator					
				Ν	Extend	ed visual indicator					
					VISU	JAL INDICATOR [see chart on page 51]					
					RA	Red closed/green open					
					GA	Green closed/red open					
					1A	T-1 three way flow path					
					2A	T-2 three way flow path					
					ЗA	T-3 three way flow path					
					4A	T-4 three way flow path					
					5A	T-5 three way flow path					
					0A	No indication					
					XA	Special					
					CA	Continuous					
		ber exa	Imple								
QN	2G	C	02	Ν	RA	OPTIONAL					
	I	MODE	LNUN	IBER		PARTNERSHIP ID					
	nting h rately.	nardwa	re requ	ired and	l sold	Some models may include 5-digit identification suffix.					

Ν

Model selector											
SERIES											
QN Intrins	sically sa	afe (I.S.)	proxim	nity swite	ches and position transmitters						
FU	ΝΟΤΙΟ	NS									
Ser	nsor/sw	itchin	g modi	ules (pro	oximity type)						
44	NAMU	IR dual	modul	e <i>[old]</i> (E	N 60947-5-6; I.S.)						
45	NAMU	IR dual	modul	e [<i>new</i>] (EN 60947-5-6; I.S.)						
Ser	nsor										
2A	(2) P+F; NJ2-12GK-5N										
2J	(2) SPST (passive)										
2M	(2) SPDT (passive)										
2N	(2) P+I	- NAMI	JR sens	ors; NJ2	-V3-N						
4J	(4) SPS	ST (pass	ive)								
4M	(4) SP[DT (pas	sive)	•••••							
4N	(4) P+I	NAM	JR sens	ors; NJ2	-V3-N						
Pos	sition tr	ansmi	tters								
50	Standa	ard wit	n no sw	/itches							
54	Standa	ard with	ח NAMI	JR (44) c	lual module (EN 60947-5-6; I.S.)						
70	High p	perform	ance (H	HP) with	no switches						
74	High p	perform	ance (H	HP) with	NAMUR (44) dual module (EN 60947-5-6; I.S.)						
	EN	CLOSU	RE								
	Clea	ar cove	er								
	С	North	Americ	an (NEC	/CEC)						
	D	Intern	ational	(IEC)							
	Alu	minun	n cover	[not exp	plosion proof]						
	Е	North	Americ	an (NEC	/CEC)						
	R	Intern	ational	(IEC)							
	F	Brazili	an								
		со	NDUIT	ENTRI	ES						
		02	(1) 3⁄4"	NPT & (1	1) 1⁄2" NPT						
		03	(1) 3⁄4"	NPT & (2	2) ½" NPT						
			(2) M2	20							
		06	(3) M2	20							
			ου	TPUT							
			S	Short v	isual indicator						
			N	Extend	ed visual indicator						
				VISU	JAL INDICATOR [see chart on page 51]						
				RA	Red closed/green open						
				GA	Green closed/red open						
				1A	T-1 three way flow path						
				2A	T-2 three way flow path						
				3A	T-3 three way flow path						
				4A 5A	T-4 three way flow path T-5 three way flow path						
				0A	No indication						
				XA	Special						
				CA	Continuous						
Model num	ıber exa	mple									
QN 45	C	02	Ν	RA	OPTIONAL						
	MODE	LNUM	BER		PARTNERSHIP ID						
Mounting I	hardwai	re requ	red and	d sold	Some models may include						
separately.					5-digit identification suffix.						

Model selector										
SERIES										
QN 1	lonin	cendiv	e proxin	nity sw	itches ar	nd positi	ion transmitters			
	FU	отто	NS							
	Pos	ition t	ransmit	ters						
50 Standard with no switches										
	5G Standard with (2) SPDT Maxx-Guard (low current)									
		Standard with SST (33) NO switching sensor dual module								
			•••••		HP) with	•••••	•••••••••••••••••••••••••••••••••••••••			
			••••••	•••••		•••••	T Maxx-Guard (low current)			
			•••••		t with n	••••••) NO switching sensor dual module			
		•••••	••••••			•••••	NO switching sensor dual module			
		••••	••••••	•••••		••••••	(45) dual module (EN 60947-5-6; I.S.)			
			••••••							
			CLOSU							
		Cle	ar cove		an (NEC					
			Interna			/CLC)				
		U			······					
					ENTRI		~			
					NPT & (1	·····	•••••••••••••••••••••••••••••••••••••••			
				·	NPT & (2	2) /2 NP	1			
				(2) M2 (3) M2						
			00		•••••	•••••				
					TPUT		1			
				S	••••	isual ind	•••••••••••••••••••••••••••••••••••••••			
				N	Extend	ed visua	al indicator			
							DICATOR [see chart on page 51]			
					RA GA	•••••	osed/green open			
					1A		closed/red open ee way flow path			
					2A	•••••	ee way flow path			
					3A		ee way flow path			
					4A		ee way flow path			
					5A		ee way flow path			
					0A	No ind	lication			
					XA	Specia	l			
					CA	Contin	nuous			
		ber exa								
QN	50	C	02	Ν	RA	-	OPTIONAL			
		MODE	L NUM	BER			PARTNERSHIP ID			
	Mounting hardware required and sold Some models may include separately. 5-digit identification suffix.									

Specifications								
Materials of construction								
Housing & cover	Epoxy-coated anodized marine grade aluminum or stainless steel							
Clear cover & indicator	Lexan® polycarbonate							
Elastomer seals	Buna-N; optional EPDM							
Drive shaft	Stainless steel							
Drive bushing	Bronze, oil impregnated							
Fasteners	Stainless steel							
Temperature ratings								
Mechanical components	-40° C to 80° C (-40° F to 176° F)							
Dual modules	-40° C to 80° C (-40° F to 176° F)							
Maxx-Guard & SST	-40° C to 80° C (-40° F to 176° F)							
Warranty								
Mechanical components	Two years							
SST & dual modules	Five years							
Lexan® is a registered trademark of General Electric Corporation.								

Ratings							
Explosionproof (Ex d, Zone 1 or Class I and II, Div. 1)	QX models*						
Nonincendive (Class I and II, Div. 2)	QN models*						
Intrinsically safe (Ex ia, Zone 0 or Class I and II, Div. 1)	Functions 44, 45, 93, _A, _J, _M and _N*						
Enclosure protection							
Type 4, 4X and 6	All models						
Ingress Protection 67	All models						
Approvals*	See <u>StoneL.com/approvals</u>						
* Only models listed on StoneL's off	* Only models listed on StoneL's official website are approved per specific rating.						

Dimensions

Output option "S" - Short visual indicator



Output option "N" - Extended visual indicator



NOTE 1

Cover height varies based on model number. Dual module and 2-switch models use short covers.

- Short cover = 102 mm [4.0"]
- Medium cover = 123.4 mm [4.86"]
- Tall cover = 155.4 mm [6.12"]





Visual indicator designations

DESIGNATION	0°	90°	180°
R	RED CLOSED	GREEN OPEN	
G	GREEN CLOSED	RED OPEN	
1	A C	A B	
2	A B	A B	
3		CLOSED	A B
4	A B	A 🔶 B	A B C
5	A B	A B	A B C
с	0% 50		
x	Specialty configuration	 please consult factory 	