



SPECIFICATIONS

Product Description: **8" (20.3 cm) AIR BAG BLOWER SYSTEM**
 Part Number: **9535-08DC, 9535-08LDC**
 Style: **AXIAL FAN**

GENERAL DESCRIPTION:

8" (20.3 cm) blower system with ducting is built into a heavy duty bag. Zippered ends allow blower use without removing from bag. Combination Axial 8" (20.3 cm) blower, 15' (4.57 m) or 25' (7.62 m) duct and custom storage bag to house the system.



CONSTRUCTION:

- Lightweight, metal 8" (20.3 cm) blower
- Super quiet
- Carry handle with molded-in 2-speed switch
- Steel/powder coated housing and grills
- Unique bag with openings for plug/cord, inlet and outlet
- Durable reinforced polyester bag
- Easy to carry and store
- All-in-one unit for ease of operation
- Duct mounted on the blower and stored inside bag
- Both carrying handle and shoulder strap allows for easy transportation
- 15' (4.75 m) power cord with battery clamps
- Easily accessible inline fuse

MOTOR:

HP: 1/4 HP
 Voltage: 12V DC
 Max RPM: 3800
 Amps: 22A
 Fuse: 30A

FAN:

- Glass Reinforced Polypropylene (PPG), six blade with aluminum hub

DUCTING:

- Single-ply lightweight vinyl/polyester, PVC coated 180° F (82.2° C) temperature resistant
- Non-collapsible retractable design
- Yellow with black wear-strip and integrated nylon attachment strap on one end

DIMENSIONS:

Length	Width	Height	Weight
27" (68.5 cm)	15" (38.1 cm)	12" (30.4 cm)	25.5 lbs. (11.6 kg)

FLOW RATES: (CFM calculated using 15' (4.57 m) of 8" (20.3 cm) ducting)

Free Air CFM (m³/hr)	One 90° Bend CFM (m³/hr)	Two 90° Bends CFM (m³/hr)
668 (1135)	497 (844)	462 (785)

AVAILABLE:

9535-08 8" (20.3 cm) blower system with 15' (4.57 m) ducting
9535-08L 8" (20.3 cm) blower system with 25' (7.62 m) ducting