



SPECIFICATIONS

Product Description: **DUCTING, STATICALLY CONDUCTIVE**

Part Number: **9550-15EX, 9550-25EX**

Style: 12" (30.4cm) RETRACTABLE

GENERAL DESCRIPTION:

This product is lightweight, retractable and designed for maximum air handling capabilities. Dual direction flow with low friction loss while providing a safe positive means of discharging static build-up.

CONSTRUCTION:

- Vinyl and polyester anti-static materials
- Single-Ply
- Neoprene coated
- Temperature resistant up to 250°F (121°C)
- Retractable, non-collapsible design.
- Class 1 hard drawn spring steel wire helix
- Meets ASTM 227 Specs
- Meet flame retardant requirements of UL-94-V0
- Rated to 100,000 OHMS or less per square inch
- Integrated with extended solid grounding wire at each end



AVAILABLE:

Part No	Diameter In. (cm)	Length Ft. (m)	End-Straps
9550-15EX	12" (30.4 cm)	15' (4.57 m)	Dual
9550-25EX	12" (30.4 cm)	25' (7.62 m)	Dual

ACCESSORIES:

Part No.	Ducting Size	Description
9550-01	12" (30.4 cm)	Duct to duct connector with raised lip
9600-36	12" (30.4 cm)	Storage rack for 12" (30.4 cm) ducting up to 25' (7.62 m)
		ducting
9600-45	12" (30.4 cm)	Duct storage bag

1360 Shiloh Church Road Piedmont, SC 29673 864-846-8740 800-622-3530 FAX: 800-362-7231 <u>www.allegrosafety.com</u>

Rev G 10-02-13