



SPECIFICATIONS

Product Description: **DUCTING, STATICALLY CONDUCTIVE, 20" DIAMETER**
 Part Number: **9650-15EX, 9650-25EX**
 Style: **RETRACTABLE**

GENERAL DESCRIPTION:

This product is lightweight, retractable and designed for maximum air handling capabilities. Dual direction flow with low friction loss while providing a safe positive means of discharging static build-up.

CONSTRUCTION:

- Vinyl and polyester anti-static materials
- Single-Ply
- Neoprene coated
- Temp resistant up to -65°F to 250°F (-53°C to 121°C)
- Retractable, Non-collapsible design.
- Class 1 hard drawn spring steel wire helix
- Meets ASTM 227 Specs.
- Meets flame retardant requirements of UL-94-V0
- Rated to 100,000 OHMS or less per square inch
- Integrated with extended solid grounding wire at each end



AVAILABLE:

Part No.	Diameter	Length	End-Straps
9650-15EX	20" (50.8 cm)	15' (4.57 m)	Dual
9650-25EX	20" (50.8 cm)	25' (7.62 m)	Dual

ACCESSORIES:

Part No.	Ducting Size	Description
9650-01	20" (50.8 cm)	Duct to duct connector, with raised lip
9600-45	20" (50.8 cm)	Duct storage bag