



SPECIFICATIONS

Product Description: **DUCTING, STATICALLY CONDUCTIVE, 16”(40.6cm) DIAMETER**
 Part Number: **9600-15EX, 9600-25EX**
 Style: **RETRACTABLE**

GENERAL DESCRIPTION:

This product is lightweight, retractable and designed for maximum air handling capabilities. Dual direction flow with low friction loss while providing a safe positive means of discharging static build-up.



CONSTRUCTION:

- Vinyl and polyester anti-static materials
- Single-Ply
- Neoprene coated
- Temp resistant up to -65°F to 250°F (-53°C to 121°C)
- Retractable, Non-collapsible design.
- Class 1 hard drawn spring steel wire helix
- Meets ASTM 227 Specs.
- Meets flame retardant requirements of UL-94-V0
- Rated to 100,000 OHMS or less per square inch
- Integrated with extended solid grounding wire at each end

AVAILABLE:

Part No.	Diameter In (cm)	Length Ft (m)	End-Straps
9600-15EX	16” (40.6 cm)	15’ (4.57 m)	Dual
9600-25EX	16” (40.6 cm)	25’ (7.62 m)	Dual

ACCESSORIES:

Part No.	Ducting Size In (cm)	Description
9600-01	16” (40.6 cm)	Duct to duct connector, with raised lip
9600-36	16” (40.6 cm)	Storage rack for 16” ducting, up to 25’ (7.62m) ducting
9600-45	16” (40.6 cm)	Duct storage bag
9600-50EX	8” (20.3 cm)	Reducer, statically conductive for 16” (40.6m) blower to 8” (20.3m) ducting