
STERCO S Y S T E M S TEChnical Data Sheet

Stormwater Catch Basins

Applications

Orenco[®]'s Stormwater Catch Basin (SCB) is a cost-effective alternative to concrete or steel catch basins. It is ideal for jurisdictions that require filtration of stormwater before it is released onsite or to a stormwater collection system. It is also well-suited for use in rainwater collection systems. The SCB is designed to screen materials as small as 1/8-inch (3-mm) diameter out of stormwater.



SCB1236-6L Stormwater Catch Basin with level inlet/outlet

General

Orenco's Stormwater Catch Basin (SCB) is based on Orenco's proven Screened Pump Vault* technology and materials. Stormwater flows into the basin vault and is screened through the 1/8-inch (3-mm) filter mesh before flowing out through the basin outlet. The filter has a nominal open area of 50%.


The inlet and outlet couplings on the SCB1236-6L accommodate 6-inch IPS pipe; the inlet and outlet couplings on all other models accommodate 4-inch IPS pipe. All SCBs use durable Orenco fiberglass lids and bases. Additionally, the SCB1236-L and SCB1236-6L come with stainless steel lid screws for enhanced security.

SCBs come with filters that are easy to remove and clean, simplifying maintenance.

Standard Models

SCB0824, SCB0836, SCB1224-L, SCB1236-L, SCB1236-6L

Product Code Diagram




Materials of Construction

Cap and base	Fiberglass		
Cap screws	Stainless steel (SCB1236-L and -6L only)		
Basin	PVC		
Inlet and outlet	Schedule 40 PVC		
Filter ring and base	Polyurethane		
Filter screen Polyethylene, ¼-inch (3-mm) screen mest			
*Orenco's screened pump	vault technology is protected under		

US Patent #4,439,323

Specifications

Dimensions, in. (mm)				
Model	SCB0824	SCB0836	SCB1236-L	SCB1236-6L
A	15½ (394)	15½ (394)	21½ (546)	21½ (546)
В	24 (610)	36 (915)	36 (915)	36 (915)
С	4½ (114)	41⁄2 (114)	4½ (114)	65⁄8 (168)
D	13½ (343)	13½ (343)	13³⁄8 (340)	15 (380)
E	4½ (114)	41⁄2 (114)	4½ (114)	65⁄8 (168)
F	8 (203)	8 (203)	13³⁄8 (340)	15 (380)
G	13 (330)	13 (330)	13 (330)	13 (330)
Flow Rates, gpm (L/sec)				
Model	SCB0824	SCB0836	SCB1236-L	SCB1236-6L
Top of Inlet	130 (8.2)	130 (8.2)	40 (2.5)	115 (7.3)
Top of Inlet + 4 in. (100 mm)	170 (10.7)	170 (10.7)	n/a	n/a
Top of Inlet + 6 in. (150 mm)	n/a	n/a	100 (6.3)	190 (12.0)
Top of Inlet + 12 in. (300 mm)	n/a	n/a	140 (8.8)	n/a



Orenco Systems® Inc. , 814 Airway Ave., Sutherlin, OR 97479 USA • 800-348-9843 • 541-459-4449 • www.orenco.com