

Use this number when searching for this item:

9085200103200

Drill, 13/32 3xD, RT 100 HF, Carbide, nano-Si, Coolant through



>> Item Info

EDP #	9085200103200
Series	8520
Order Code	10.320
Coating	nano-Si
Coolant	Yes
Cutting Direction	RH
Drilling Depth	3xD
Material	Carbide
Point Angle	140
Shank	DIN 6535-HA
Type	High Performance
Tolerance	m7


>> Features

- Special geometry
- Maximum tool life
- High process reliability

>> Suggested Materials

- Tool Steels
- Ti and Ti-alloys
- Special Alloys
- Hardened Steels

>> Technical Specs



		Diameter	Diameter	Diameter	Diameter	Shank dia	OAL	Flute length	Drilling depth	
EDP #	Order Code	d1	d1	d1	d1	d2	l1	l2	tmax	Shank
		(in)	(frac)	Wire/ letter	(mm)	(mm)	(mm)	(mm)	(mm)	
9085200103200	10.320	0.4063	13/32		10.320	12.000	102.00	55.00	39.52	Straight



WARNING:
This product contains Cobalt, a chemical known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

*** **DISCLAIMER:** Data on this PDF is subject to change at any time without notice.