Series JD Direct Drive Mixer, Clamp or Cup Plate Mount 1750 rpm, Grease Lube

This mixer was engineered to meet the need for a large direct drive mixer with a housing that cannot leak oil.

Features

- Square pitch 1.0 ratio marine propellers are used exclusively. Flow coefficients and power consumption characteristics equal those of the best hydrofoil impeller designs.
- 316SS propellers and shafts are standard. Optional coatings such as rubber, PVC or Teflon® also available.
- JD mixers have adjustable angles of entry by indexed ball-and-socket design to achieve different process results.
- Motors are available in TEFC or explosion-proof enclosures (1750 rpm, 56C frame). Air motors also available.
- Vibration-absorbing pad standard.
- All JD mixer shaft bearings are permanently lubricated.
- Variable speed drives also available.
- Cast aluminum housing.
- Fixed cup plate mount optional.

Model Number	Standard Motor Description	A Shaft Length	В	С		D
				Single	Dual	Shaft Diameter
Totally-enc	losed fan-cooled (TEFC)					•
JD-2.0	1/3 HP-1-115/230	36"	21%"	4"	4"	3/4"
JD-2.1	1/3 HP-3-230/460	36"	20%"	4"	4"	3/4"
JD-3.0	1/2 HP-1-115/230	48"	22"	5"	4"	3/4"
JD-3.1	1/2 HP-3-230/460	48"	21%"	5"	4"	3/4"
JD-4.0	3/4 HP-1-115/230	48"	22¼"	5"	4"	3/4"
JD-4.1	3/4 HP-3-230/460	48"	21½"	5"	4"	3/4"
JD-5.1	1 HP-3-230/460	60"	21¾"	6"	5"	1"
JD-6.1	1½ HP-3-230/460	60"	22¼"	6"	5"	1"
JD-7.1	2 HP-3-230/460	60"	23½"	7"	6"	1"
Explosion-p	proof class 1 group D (EP)					
JD-2.2	1/3 HP-1-115/230	36"	24"	4"	4"	3/4"
JD-2.3	1/3 HP-3-230/460	36"	20¾"	4"	4"	3/4"
JD-3.2	1/2 HP-1-115/230	48"	24½"	5"	4"	3/4"
JD-3.3	1/2 HP-3-230/460	48"	23%"	5"	4"	3/4"
JD-4.2	3/4 HP-1-115/230	48"	25"	5"	4"	3/4"
JD-4.3	3/4 HP-3-230/460	48"	23%"	5"	4"	3/4"
JD-5.3	1 HP-3-230/460	60"	24"	6"	5"	1"
JD-6.3	1½ HP-3-230/460	60"	24"	6"	5"	1"
JD-7.3	2 HP-3-230/460	60"	25½"	7"	6"	1"
Air motor						
JD-3.4	1/3 HP to 1/2 HP AIR Air Requirements: 12-20CFM at 20-40PSI	48"	16½"	5"	4"	3/4"
JD-4.4	3/4 HP AIR Air Requirements: 30CFM at 60PSI	48"	17%"	5"	4"	3/4"
JD-5.4	1 HP AIR Air Requirements: 40CFM at 40PSI	60"	18½"	6"	5"	1"
JD-6.4	1½ HP AIR Air Requirements: 55CFM at 60PSI	60"	18½"	6"	5"	1"
JD-7.4	2 HP AIR Air Requirements: 65CFM at 75PSI	60"	18½"	7"	6"	1"







