



MCR
SAFETY

4901

Memphis

Welder

Specification Sheet

PRODUCT DESCRIPTION:

Only the finest top grain leathers our magnesium inert gas (MIG) and tungsten inert gas (TIG) welding gloves. They assure the best in comfort, dexterity and longevity in the industry. Sewn with Kevlar® thread to resist sparks and sharp metals which can unravel most gloves, you will find these gloves a great long-term value. Low heat welding often requires optimal dexterity which affords great attention to detail. The 4901 features all grain premium grade cowhide, 4 1/2" grain leather gauntlet cuff, fleecy lining, and sewn with Dupont™ Kevlar®.

FEATURES:

- Premium grain cowhide
- 4.5" grain leather gauntlet cuff
- Fleecy lining
- Sewn with Dupont(tm) Kevlar®
- MIG/TIG

APPLICATIONS:

Ship building, Construction, Mig/Tig, Welding

TECHNICAL DATA FOR: 4901L

Series	Memphis
Material Group	Leather
Product Type	Welder
Glove Size	Large
Material	Leather
Leather Cut	Grain
Leather Type	Cow
Grade	Premium
Features	Sewn With KEVLAR
Lining	Fleece Palm
Pattern	Gunn
Thumb Style	Wing
Thickness	1.0 - 1.6 mm



MCR
SAFETY

4901


Memphis

Welder

Specification Sheet

Made In

China



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
4901L	Large	12.370	4.75	4.500	33.102 lb.	5.517
4901M	Medium	12.250	4.63	4.500	28.674 lb.	4.779
4901XL	X - Large	13.000	5.250	5	35.340 lb.	5.890

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2019 MCR Safety - All Rights Reserved