

Safety Data Sheet

Printing date 01/03/2018

Revised On 01/03/2018

1 Identification of the substance and manufacturer

Trade name: SAFETY RED
Product code: 0000160671
Manufacturer/Supplier: Seymour of Sycamore
 917 Crosby Avenue
 Sycamore, IL 60178 USA
 phone: 815-895-9101
 www.seymourpaint.com
Emergency telephone number: 1-800-255-3924

Seymour of Sycamore
 3041 Dougall Avenue, Suite 503
 Windsor, ONT N9E 1S3 CANADA
 phone: 800-435-4482
 www.seymourpaint.com

2 Hazard(s) identification

Classification of the substance or mixture

Flam. Aerosol 1 H222 Extremely flammable aerosol.
 Press. Gas H280 Contains gas under pressure; may explode if heated.
 STOT SE 3 H335 May cause respiratory irritation.
 STOT RE 2 H373 May cause damage to organs through prolonged or repeated exposure.

GHS Hazard pictograms



GHS02 GHS04 GHS07 GHS08

Signal word

Danger

Hazard statements

Extremely flammable aerosol.
 Contains gas under pressure; may explode if heated.
 May cause respiratory irritation.
 May cause damage to organs through prolonged or repeated exposure.
 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
 Do not spray on an open flame or other ignition source.
 Pressurized container: Do not pierce or burn, even after use.
 Do not breathe dust/fume/gas/mist/vapors/spray.
 Use only outdoors or in a well-ventilated area.
 IF INHALED: Remove person to fresh air and keep comfortable for breathing.
 Call a poison center/doctor if you feel unwell.
 Store in a well-ventilated place.
 Store locked up.
 Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
 Dispose of contents/container in accordance with local/regional/national/international regulations.

Precautionary statements

3 Composition/information on ingredients

Chemical characterization: Mixtures

Chemical Description:

This product is a mixture of the substances listed below with nonhazardous additions.

Dangerous components:

64742-89-8	VM&P Naphtha	16.16%
74-98-6	propane	15.11%
1317-65-3	Calcium Carbonate	12.79%
106-97-8	n-butane	8.88%
64742-47-8	Mineral Spirits	4.17%

4 First-aid measures

After inhalation: Supply fresh air; consult doctor in case of complaints.
After skin contact: Remove contaminated clothing. Wash exposed area with soap and water.
After eye contact: Rinse opened eye for several minutes under running water. Then consult a doctor.
After swallowing: Rinse out mouth and then drink plenty of water. Rinse mouth with water. Do not induce vomiting.
Most important symptoms and effects: Dizziness
Indication of any immediate medical attention needed: No further relevant information available.

5 Fire-fighting measures

Extinguishing agents: CO₂, extinguishing powder or water spray. Fight larger fires with water spray.
Special hazards: Can form explosive gas-air mixtures.
Protective equipment for firefighters: A respiratory protective device may be necessary.

6 Accidental release measures

Personal precautions, protective equipment and emergency procedures: Wear protective equipment. Keep unprotected persons away. Use respiratory protective device against the effects of fumes/dust/aerosol.
Methods and material for containment and cleaning up: Ensure adequate ventilation.

7 Handling and storage

Precautions for safe handling Use only in well ventilated areas.

(Contd. on page 2)

Safety Data Sheet

Printing date 01/03/2018

Revised On 01/03/2018

Trade name: SAFETY RED

Storage requirements: Keep away from sources of heat and direct sunlight. Do not warehouse in subfreezing conditions. Store locked up. (Contd. of page 1)

8 Exposure controls/personal protection

Components with limit values that require monitoring at the workplace:

74-98-6 propane

PEL (USA) Long-term value: 1800 mg/m³, 1000 ppm
 REL (USA) Long-term value: 1800 mg/m³, 1000 ppm
 TLV (USA) refer to Appendix F in TLVs&BEIs book; D, EX

106-97-8 n-butane

REL (USA) Long-term value: 1900 mg/m³, 800 ppm
 TLV (USA) Short-term value: 2370 mg/m³, 1000 ppm (EX)

Hygienic protection: Keep away from foodstuffs and animal feed. Wash hands after use.
 Wash hands after use.

Breathing equipment: Do not eat or drink while working.
 A respirator is generally not necessary when using this product outdoors or in large open areas. In cases where short and/or long term overexposure exists, a charcoal filter respirator should be worn. If you suspect overexposure conditions exist, please consult an authority on chemical hygiene.

Hand protection: Nitrile gloves.
 The glove material must be impermeable and resistant to the substance.

Eye protection: Tightly sealed goggles

9 Physical and chemical properties

Appearance: Aerosol.
Odor: Aromatic
Odor threshold: Not determined.
pH-value: Not determined.
Melting point/Melting range Undetermined.
Boiling point: -44 °C (-47.2 °F)
Flash point: -19 °C (-2.2 °F)
Flammability (solid, gas): Extremely flammable.
Decomposition temperature: Not determined.
Auto igniting: Product is not self-igniting.
Danger of explosion: In use, may form flammable/explosive vapour-air mixture.
Lower Explosion Limit: 1.7 Vol %
Upper Explosion Limit: 10.9 Vol %
Vapor pressure: Not determined.
Relative Density: Between 0.77 and 0.85 (Water equals 1.00)
Vapor density Not determined.
Evaporation rate Not applicable.
Partition coefficient: n-octanol/water: Not determined.
Solubility: Not determined.
Viscosity: Not determined.
Water: 33.3 %

10 Stability and reactivity

Reactivity: Stable at normal temperatures.
Conditions to avoid: Do not allow can to exceed 120 degrees Fahrenheit. Do not warehouse in subfreezing temperatures.
Chemical stability: Not fully evaluated.
Possibility of hazardous reactions: No dangerous reactions known.
Incompatible materials: No further relevant information available.
Hazardous decomposition: No dangerous decomposition products known.

11 Toxicological information

LD/LC50 values that are relevant for classification:

106-97-8 n-butane

Inhalative LC50/4 h 658 mg/l (rat)

Information on toxicological effects: No data available.
Skin effects: No irritant effect.
Eye effects: No irritating effect.
Sensitization: No sensitizing effects known.

12 Ecological information

Aquatic toxicity: Hazardous for water, do not empty into drains.
Persistence and degradability: The product is degradable after prolonged exposure to natural weathering processes.
Bioaccumulative potential: No further relevant information available.
Mobility in soil: No further relevant information available.

(Contd. on page 3)

Safety Data Sheet

Printing date 01/03/2018

Revised On 01/03/2018

Trade name: SAFETY RED

Other adverse effects: No further relevant information available.

(Contd. of page 2)

13 Disposal considerations

Dispose of in accordance with local, state, and federal regulations. Do not puncture, incinerate, or compact. Partially empty cans must be disposed of responsibly. Do not heat or cut empty containers with electric or gas torches.

Recommendation: Completely empty cans should be recycled.**14 Transport information**

UN-Number	UN1950
DOT	N/A
DOT	UN1950
ADR	Consumer Commodity ORM-D
Transport hazard class(es):	Aerosols, flammable
Class	1950 Aerosols
Marine pollutant:	2.1
Special precautions for user:	No
EMS Number:	Warning: Gases
Packaging Group:	F-D,S-U
UN "Model Regulation":	--
	UN1950, Aerosols, 2.1

15 Regulatory information**SARA Section 355 (extremely hazardous substances):**

None of the ingredients in this product are listed.

SARA Section 313 (Specific toxic chemical listings):

None of the ingredients is listed.

Toxic Substances Control Act (TSCA):

All hazardous ingredients for this product are found on the inventory list of substances.

Consumer Product Safety Commission (CPSC):

This product complies with 16 CFR 1303 and does not contain more than 90 ppm of lead.

California Proposition 65 chemicals known to cause cancer:

100-41-4 ethyl benzene

California Proposition 65 chemicals known to cause birth defects or reproductive harm:

None of the ingredients in this product are listed.

CANADIAN ENVIRONMENTAL PROTECTION ACT:**WHMIS Symbols for Canada:**

All hazardous ingredients for this product appear on the Canadian Domestic Substance List.

A - Compressed gas

**EPA:**

None of the ingredients is listed.

16 Other information

Contact:	Regulatory Affairs
Date of preparation / last revision	01/03/2018 / -