

STAINLESS STEEL BIDIRECTIONAL RESILIENT SEATED KNIFE GATE VALVE

The figure 6800 knife gate valve has an all cast stainless steel body and yoke with investment cast packing follower. It is a general purpose zero-leak bidirectional shutoff valve. Perimeter gate sealing is not pressure dependent, so there is no minimum differential needed for shutoff. Port sizing is similar to schedule 40 pipe, so the valve offers unrestricted flow and minimal pressure drop.

Features

- · Bidirectional Bubble-Tight Shutoff
- Maximum Pressure: 150 PSI CWP (30" is 50 PSI CWP)
- Maximum Temperature: 176°F (80°C)
- Non-Differential Pressure Dependent Shutoff
- · Cast Stainless Steel Body, Yoke, & Packing Gland
- Thrust Needle Bearing
- Combination Chest Liner & Anti-Extrusion Strip (Anti-Extrusion Strip Only on 14" and Larger Valves)
- · Wire Reinforced & Retained Resilient Seat
- · Stainless Steel Position Indication Arrow
- · Stainless Steel Hardware
- · Machined Gland Pocket Area
- · Bonnetless, Outside Screw & Yoke
- · Rising Stem
- · Cast Iron Hand Wheel
- Gear-Operator Standard on 30" Valve
- Available in sizes 3" to 30"
- · Standard design accommodates locking device

Standards

- Face-to-Face: MSS SP-81
- Flange Drilling: ANSI B16.5 (30" to MSS SP-44 Flanges)
- Testing
 - o Shell (Before Assembly): 1.5 Time Max. CWP (No Leak)
 - o Seat: 1.1 Times Max. CWP (No Leak)
- · Material: ASME B16.34


Figure Number Matrix

FNW 6800 Seat Size								
SEAT CODE Buna (Nitrile) = B (SS Wire Reinforced)		10 = 10 12 = 12 14 = 14 16 = 16	18 = 18 20 = 20 24 = 24 30 = 30					

Cv & Weight

Size	Cv	Wt (Lbs)
3	565	44
4	1,040	53
6	2,440	88
8	4,460	139
10	6,250	181
12	9,400	229

Size	Cv	Wt (Lbs)			
14	12,500	364			
16	16,500	397			
18	21,400	463			
20	27,000	573			
24	39,700	617			
30	60,000	882			



FEATURES

Hand wheel is heavy cast iron, with a rounded grip and epoxy coated hand wheel.

Double set screws prevent threaded-on hand wheel from backing off or coming loose.

Stainless steel needle bearings reduce hand wheel rim pull force.

Aluminum-Bronze thrust components for antigalling operation.

Grease fitting for maintaining smooth drive sleeve operation.

Cast stainless steel yoke arms provide optimum flexural rigidity.

Stainless steel position indication arrow is standard

Stem-to-gate clevis is deliberately loose to allow play in gate to minimize binding.

Stainless steel hardware is standard

Horizontal clevis bolts provide flexibility of the gate during travel.

Multiple layers of PTFE impregnated square braid packing provides excellent gland sealing at full valve pressure differential.


Combination PTFE chest liner & anti-extrusion strips (anti-extrusion strips only on 14" and larger valves), enhance packing functionality while centering the gate. They also act as a gate wiper, and support the gate in horizontally mounted valves.

The single piece cast all stainless steel body is rugged and compact. It offers better leak tightness than fabricated or two-piece designs.

The gate is high-quality, ground-finished stainless steel. A generous gate thickness is well supported by the packing.

Port sizing is similar to schedule 40 pipe, so the valve offers unrestricted flow and minimal pressure drop.

Perimeter gate sealing is not pressure dependent, so there is no minimum differential needed for shutoff.




Secured Wire Reinforcement Gate/Seat Interference Fit Perimeter Seat

Seat Seal Configuration


The figure 6800 knife gate valve provides bubble-tight shutoff. When the valve is closed, there is a friction fit along the entire perimeter between the flat edge of the gate and the elastomer seat. This friction fit ensures tight shutoff without the requirement of a minimum line pressure, but is tight enough to maintain shutoff at maximum rated pressures as well. There is no recommended flow direction because the seal is made at the gate's edge, hence bidirectional flow capability.

Seat seal retention is twofold. First, the seat is retained in a channel with a machined retention lip. This lip overhangs both sides of the seat, preventing seat removal from high velocity



flows. Secondly, the seat is reinforced with a heavy stainless steel wire. The ends of the wire are wrapped around gland bolts. The wire adds rigidity to the seat form which also prevents seat movement during high flow or valve opening/closing operation.


Standard Materials



Ref.	Description	Material	Qty		
No.	-	Stainless Steel, ASTM A351	1		
1	Body	Gr. CÉ8M	1		
1A	Seat	Buna (Nitrile) with ASTM A276 Type 304 Wire	1		
2	Gate	Stainless Steel, ASTM A240 Type 316	1		
3	Packing	PTFE Impregnated Syntex Fiber	3 (3"~24") 4 (30")		
	Chest Liner		2 (3"~12")		
5	Anti Extrusion Strip	PTFE	2 (14"~30")		
6	Gland	Stainless Steel, ASTM A351 Gr.CF8	1		
7	Gland Bolt	Stainless Steel 304, ASTM A193 Gr. B8	2~10		
8	Gland Nut	Stainless Steel 304, ASTM A194 Gr. 8	2~10		
9	Yoke Arm	Stainless Steel, ASTM A351 Gr.CF8	2		
10	Yoke Bolt	Stainless Steel 304, ASTM A193 Gr. B8	4		
11	Stem	Stainless Steel, ASTM A276 Type 304	1		
12	Clevis Bolt	Stainless Steel 304, ASTM A193 Gr. B8	2		
13	Clevis Nut	Stainless Steel 304, ASTM A194 Gr. 8	2		
14	Collar	Stainless Steel, ASTM A351 Gr.CF8	1 (3"~24)		
15	Collar Bolt	Stainless Steel 304, ASTM A193 Gr. B8	2 (3"~8") 4 (10"~24")		
16	Collar Nut	Stainless Steel 304, ASTM A194 Gr. 8	2 (3"~8")		
17	Hand Wheel	Cast Iron, ASTM A126 Gr. B	1		
18	Yoke Sleeve	Aluminum Bronze, ASTM B148, UNS C95200	1 (3"~24)		
19	Thrust Needle Bearing	Stainless Steel,	2 (3"~24)		
20	Set Screws	Stainless Steel, 304SS	2 (3"~24)		
21	Position Indicator	Stainless Steel, 304SS	1		
30	Gear-Op	Enclosed Type Model BG03 (not shown)	1 (30" only)		



STAINLESS STEEL BIDIRECTIONAL RESILIENT SEATED KNIFE GATE VALVE



Dimensions (inches)

Size	Α	В	С	D	Е	F	G	Н	J	K	N	S
3	2.00	6.00	5.00	16.34	19.49	9.84	2	5/8"-11	0.39	2	2.95	0.47
4	2.00	7.50	6.22	18.31	21.26	9.84	2	5/8"-11	0.39	6	4.00	0.47
6	2.25	9.50	8.50	22.05	27.36	11.75	2	3/4"-10	0.43	6	6.00	0.57
8	2.75	11.75	10.63	25.59	33.27	15.98	2	3/4"-10	0.43	6	8.00	0.57
10	2.75	14.25	12.76	28.66	39.37	15.98	4	7/8"-9	0.49	8	10.04	0.69
12	3.00	17.00	14.76	33.46	46.46	20.00	4	7/8"-9	0.43	8	11.97	0.69
14	3.00	18.75	16.26	37.60	53.15	20.00	4	1"-8	0.51	8	13.11	0.75
16	3.50	21.25	18.50	41.34	58.27	20.00	6	1"-8	0.63	10	15.00	0.87
18	3.50	22.75	20.98	45.67	63.78	20.00	6	1-1/8"-7	0.59	10	16.93	0.94
20	4.50	25.00	23.03	50.39	70.47	20.00	8	1-1/8"-7	0.75	12	18.82	0.98
24	4.50	29.50	27.24	58.46	83.66	20.00	8	1-1/4"-7	0.91	12	22.64	0.98
30	4.62	36.00	33.75	81.00*	110.00	19.68	10	1-1/4"-7	0.94	18	28.74	1.12

^{*} Dimension "D" for 30" valve is centerline of valve to centerline of gear-operator hand wheel shaft.

DOC: FNW680013 Ver. 8/2014

 $\ensuremath{\text{@}}$ 2014 - FNW. All rights reserved. 22038

The FNW logo is a trademark of Ferguson Enterprises, Inc., PL Sourcing, PO Box 2778, Newport News, VA 23609

The contents of this publication are presented for information purposes only, and while effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, expressed or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available on request. We reserve the right to modify or improve the designs or specifications of our products at any time without notice. Always verify that you have the most recent product specifications or other documentation prior to the installation of these products.