

## Safety Data Sheet

Printing date 02/22/2019

Revised On 02/22/2019

**1 Identification of the substance and manufacturer**

**Trade name:** GLOSS BLACK  
**Product code:** 0000110003  
**Recommended use:** Paint and coating applications.  
**Uses advised against:** Any that differs from the recommended use.  
**Manufacturer/Supplier:** Seymour of Sycamore  
 917 Crosby Avenue  
 Sycamore, IL 60178 USA  
 phone: 815-895-9101  
 www.seymourpaint.com  
**Emergency telephone number:** 1-800-255-3924

Seymour of Sycamore  
 3041 Dougall Avenue, Suite 503  
 Windsor, ONT N9E 1S3 CANADA  
 phone: 800-435-4482  
 www.seymourpaint.com

**2 Hazard(s) identification****Classification of the substance or mixture**

Flam. Aerosol 1 H222 Extremely flammable aerosol.  
 Press. Gas H280 Contains gas under pressure; may explode if heated.  
 Eye Irrit. 2A H319 Causes serious eye irritation.  
 Repr. 1B H360 May damage fertility or the unborn child.  
 STOT SE 3 H336 May cause drowsiness or dizziness.  
 STOT RE 2 H373 May cause damage to organs through prolonged or repeated exposure.

**GHS Hazard pictograms**

GHS02 GHS04 GHS07 GHS08

**Signal word**

Danger

**Hazard statements**

Extremely flammable aerosol.  
 Contains gas under pressure; may explode if heated.  
 Causes serious eye irritation.  
 May damage fertility or the unborn child.  
 May cause drowsiness or dizziness.

**Precautionary statements**

May cause damage to organs through prolonged or repeated exposure.  
 Obtain special instructions before use.  
 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.  
 Do not spray on an open flame or other ignition source.  
 Pressurized container: Do not pierce or burn, even after use.  
 Do not breathe dust/fume/gas/mist/vapors/spray.  
 Wash hands thoroughly after handling.  
 Use only outdoors or in a well-ventilated area.  
 Wear protective gloves/protective clothing/eye protection/face protection.  
 IF INHALED: Remove person to fresh air and keep comfortable for breathing.  
 If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
 Call a poison center/doctor if you feel unwell.  
 If eye irritation persists: Get medical advice/attention.  
 Store in a well-ventilated place.  
 Store locked up.  
 Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.  
 Dispose of contents/container in accordance with local/regional/national/international regulations.

**3 Composition/information on ingredients****Chemical characterization: Mixtures**

**Chemical Description:** This product is a mixture of the substances listed below with nonhazardous additions.

**Dangerous components:**

67-64-1	Acetone	29.98%
74-98-6	propane	22.04%
106-97-8	n-butane	12.94%
64742-89-8	VM&P Naphtha	8.16%
64742-47-8	Mineral Spirits	5.47%
108-88-3	Toluene	4.49%
67-63-0	Isopropyl Alcohol	2.71%

**4 First-aid measures**

**After inhalation:** Supply fresh air; consult doctor in case of complaints.  
**After skin contact:** Remove contaminated clothing. Wash exposed area with soap and water.  
**After eye contact:** Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.  
**After swallowing:** Rinse mouth with water. Do not induce vomiting.  
**Most important symptoms and effects:** Dizziness  
**Indication of any immediate medical attention needed:** No further relevant information available.

**5 Fire-fighting measures**

**Extinguishing agents:** CO2, extinguishing powder or water spray. Fight larger fires with water spray.  
**Special hazards:** Can form explosive gas-air mixtures.

(Contd. on page 2)

## Safety Data Sheet

Printing date 02/22/2019

Revised On 02/22/2019

Trade name: GLOSS BLACK

(Contd. of page 1)

**Protective equipment for firefighters:**

A respiratory protective device may be necessary.

**6 Accidental release measures****Personal precautions, protective equipment and emergency procedures:**

Use respiratory protective device against the effects of fumes/dust/aerosol.

**Methods and material for containment and cleaning up:**

Dispose contaminated material as waste according to section 13.

**7 Handling and storage****Precautions for safe handling  
Storage requirements:**

Use only in well ventilated areas.

Keep away from sources of heat and direct sunlight. Do not warehouse in subfreezing conditions. Store locked up.

**8 Exposure controls/personal protection****Components with limit values that require monitoring at the workplace:****67-64-1 Acetone**PEL (USA) Long-term value: 2400 mg/m<sup>3</sup>, 1000 ppmREL (USA) Long-term value: 590 mg/m<sup>3</sup>, 250 ppmTLV (USA) Short-term value: 1187 mg/m<sup>3</sup>, 500 ppmLong-term value: 594 mg/m<sup>3</sup>, 250 ppm

BEI

**74-98-6 propane**PEL (USA) Long-term value: 1800 mg/m<sup>3</sup>, 1000 ppmREL (USA) Long-term value: 1800 mg/m<sup>3</sup>, 1000 ppm

TLV (USA) refer to Appendix F in TLVs&amp;BEIs book; D, EX

**106-97-8 n-butane**REL (USA) Long-term value: 1900 mg/m<sup>3</sup>, 800 ppmTLV (USA) Short-term value: 2370 mg/m<sup>3</sup>, 1000 ppm  
(EX)**108-88-3 Toluene**PEL (USA) Long-term value: 200 ppm  
Ceiling limit value: 300; 500\* ppm  
\*10-min peak per 8-hr shiftREL (USA) Short-term value: 560 mg/m<sup>3</sup>, 150 ppmLong-term value: 375 mg/m<sup>3</sup>, 100 ppmTLV (USA) Long-term value: 75 mg/m<sup>3</sup>, 20 ppm

BEI

**67-63-0 Isopropyl Alcohol**PEL (USA) Long-term value: 980 mg/m<sup>3</sup>, 400 ppmREL (USA) Short-term value: 1225 mg/m<sup>3</sup>, 500 ppmLong-term value: 980 mg/m<sup>3</sup>, 400 ppmTLV (USA) Short-term value: 984 mg/m<sup>3</sup>, 400 ppmLong-term value: 492 mg/m<sup>3</sup>, 200 ppm

BEI

**Ingredients with biological limit values:****67-64-1 Acetone**

BEI (USA) 50 mg/L

Medium: urine

Time: end of shift

Parameter: Acetone (nonspecific)

**67-63-0 Isopropyl Alcohol**

BEI (USA) 40 mg/L

Medium: urine

Time: end of shift at end of workweek

Parameter: Acetone (background, nonspecific)

**Hygienic protection:**

Immediately remove all soiled and contaminated clothing.

Wash hands after use.

Store protective clothing separately.

Avoid contact with the eyes and skin.

Do not eat or drink while working.

**Breathing equipment:**

A respirator is generally not necessary when using this product outdoors or in large open areas.

In cases where short and/or long term overexposure exists, a charcoal filter respirator should be worn. If you suspect overexposure conditions exist, please consult an authority on chemical hygiene.

**Hand protection:**

Nitrile gloves.

The glove material must be impermeable and resistant to the substance.

**Eye protection:**

Tightly sealed goggles

**9 Physical and chemical properties****Appearance:**

Aerosol.

**Odor:**

Aromatic

(Contd. on page 3)

## Safety Data Sheet

Printing date 02/22/2019

Revised On 02/22/2019

Trade name: GLOSS BLACK

(Contd. of page 2)

<b>Odor threshold:</b>	Not determined.
<b>pH-value:</b>	Not determined.
<b>Melting point/Melting range</b>	Undetermined.
<b>Boiling point:</b>	-44 °C (-47.2 °F)
<b>Flash point:</b>	-19 °C (-2.2 °F)
<b>Flammability (solid, gas):</b>	Extremely flammable.
<b>Decomposition temperature:</b>	Not determined.
<b>Auto igniting:</b>	Product is not self-igniting.
<b>Danger of explosion:</b>	In use, may form flammable/explosive vapour-air mixture.
<b>Lower Explosion Limit:</b>	1.5 Vol %
<b>Upper Explosion Limit:</b>	10.9 Vol %
<b>Vapor pressure:</b>	Not determined.
<b>Relative Density:</b>	Between 0.77 and 0.85 (Water equals 1.00)
<b>Vapor density</b>	Not determined.
<b>Evaporation rate</b>	Not applicable.
<b>Partition coefficient: n-octonal/water:</b>	Not determined.
<b>Solubility:</b>	Not determined.
<b>Viscosity:</b>	Not determined.
<b>VOC content (less exempt solvents):</b>	52.3 %

**10 Stability and reactivity**

<b>Reactivity:</b>	Stable at normal temperatures.
<b>Conditions to avoid:</b>	Do not allow can to exceed 120 degrees Fahrenheit. Do not warehouse in subfreezing temperatures.
<b>Chemical stability:</b>	Not fully evaluated.
<b>Possibility of hazardous reactions:</b>	No dangerous reactions known.
<b>Incompatible materials:</b>	No further relevant information available.
<b>Hazardous decomposition:</b>	No dangerous decomposition products known.

**11 Toxicological information****LD/LC50 values that are relevant for classification:****106-97-8 n-butane**

Inhalative LC50/4 h 658 mg/l (rat)

**67-63-0 Isopropyl Alcohol**

Oral	LD50	4,570 mg/kg (rat)
Dermal	LD50	13,400 mg/kg (rab)
Inhalative	LC50/4 h	30 mg/l (rat)

<b>Information on toxicological effects:</b>	No data available.
<b>Skin effects:</b>	No irritant effect.
<b>Eye effects:</b>	Irritating effect.
<b>Sensitization:</b>	No sensitizing effects known.

**12 Ecological information**

<b>Aquatic toxicity:</b>	Hazardous for water, do not empty into drains.
<b>Persistence and degradability:</b>	The product is degradable after prolonged exposure to natural weathering processes.
<b>Other information:</b>	This product does not contain any chlorofluorocarbons (CFC's), hydrochlorofluorocarbons (HCFC's), perfluorocarbons (PFC's), heavy metals (chromium, lead, cadmium), or chlorinated solvents.
<b>Bioaccumulative potential:</b>	No further relevant information available.
<b>Mobility in soil:</b>	No further relevant information available.
<b>Other adverse effects:</b>	No further relevant information available.

**13 Disposal considerations**

Dispose of in accordance with local, state, and federal regulations. Do not puncture, incinerate, or compact. Partially empty cans must be disposed of responsibly. Do not heat or cut empty containers with electric or gas torches.

**Recommendation:** Completely empty cans should be recycled.

**14 Transport information**

<b>UN-Number</b>	UN1950
<b>DOT</b>	N/A
<b>DOT</b>	Consumer Commodity ORM-D Aerosols, flammable
<b>ADR</b>	1950 Aerosols
<b>Transport hazard class(es):</b>	
<b>Class</b>	2.1
<b>Marine pollutant:</b>	No
<b>Special precautions for user:</b>	Warning: Gases
<b>EMS Number:</b>	F-D,S-U
<b>Packaging Group:</b>	--

(Contd. on page 4)

## Safety Data Sheet

Printing date 02/22/2019

Revised On 02/22/2019

Trade name: GLOSS BLACK

UN "Model Regulation": UN1950, Aerosols, 2.1

(Contd. of page 3)

**15 Regulatory information****SARA Section 355 (extremely hazardous substances):**

None of the ingredients in this product are listed.

**SARA Section 313 (Specific toxic chemical listings):**

108-88-3 Toluene

67-63-0 Isopropyl Alcohol

**Toxic Substances Control Act (TSCA):**

All hazardous ingredients for this product are found on the inventory list of substances.

**Consumer Product Safety****Commission (CPSC):**

This product complies with 16 CFR 1303 and does not contain more than 90 ppm of lead.

**California Proposition 65 chemicals known to cause cancer:**

1333-86-4 Carbon black

100-41-4 ethyl benzene

**California Proposition 65 chemicals known to cause birth defects or reproductive harm:**

108-88-3 Toluene

**CANADIAN ENVIRONMENTAL PROTECTION ACT:**

All hazardous ingredients for this product appear on the Canadian Domestic Substance List.

**EPA:**

67-64-1 Acetone

**16 Other information**

Contact: Regulatory Affairs