Printing date 02/22/2019 Revised On 02/22/2019

1 Identification of the substance and manufacturer

Trade name: FLAT BLACK ENAMEL

0000980010 Product code:

Recommended use: Paint and coating applications.

Uses advised against: Any that differs from the recommended use.

Seymour of Sycamore Manufacturer/Supplier:

917 Crosby Avenue Sycamore, IL 60178 USA phone: 815-895-9101

Seymour of Sycamore 3041 Dougall Avenue, Suite 503 Windsor, ONT N9E 1S3 CANADA phone: 800-435-4482 www.seymourpaint.com www.seymourpaint.com

Emergency telephone number: 1-800-255-3924

2 Hazard(s) identification

Classification of the substance or mixture

Flam. Aerosol 1 H222 Extremely flammable aerosol.

Press. Gas H280 Contains gas under pressure; may explode if heated.

Eye Irrit. 2A H319 Causes serious eye irritation.

Repr. 1B H360 May damage fertility or the unborn child. STOT SE 3 H336 May cause drowsiness or dizziness.

STOT RE 2 H373 May cause damage to organs through prolonged or repeated exposure.

GHS Hazard pictograms

Precautionary statements

GHS02 GHS04 GHS07 GHS08

Signal word Danger

Hazard statements Extremely flammable aerosol.

Contains gas under pressure; may explode if heated.

Causes serious eye irritation.

May damage fertility or the unborn child. May cause drowsiness or dizziness

May cause damage to organs through prolonged or repeated exposure. Obtain special instructions before use.

Cotain special instructions before use.

Keep away from heat/sparks/open flames/hot surfaces. - No smoking.

Do not spray on an open flame or other ignition source.

Pressurized container: Do not pierce or burn, even after use.

Do not breathe dust/fume/gas/mist/vapors/spray.

Wash hands thoroughly after handling.

Use only outdoors or in a well-ventilated area.
Wear protective gloves/protective clothing/eye protection/face protection.
IF INHALED: Remove person to fresh air and keep comfortable for breathing.

If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present

and easy to do. Continue rinsing.

Call a poison center/doctor if you feel unwell. If eye irritation persists: Get medical advice/attention.

Store in a well-ventilated place.

Store locked up.

Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.

Dispose of contents/container in accordance with local/regional/national/international

regulations.

3 Composition/information on ingredients

Chemical characterization: Mixtures

Chemical Description: This product is a mixture of the substances listed below with nonhazardous additions.

Dangerous components:		
	Acetone	23.14%
	propane	18.9%
	Calcium Carbonate	12.29%
	VM&P Naphtha	11.21%
106-97-8		11.1%
	Mineral Spirits	7.88%
108-88-3		3.18%
67-63-0	Isopropyl Alcohol	2.53%

4 First-aid measures

After inhalation: Supply fresh air; consult doctor in case of complaints.

After skin contact: Remove contaminated clothing. Wash exposed area with soap and water.

Rinse opened eye for several minutes under running water. If symptoms persist, consult a After eye contact:

doctor.

Rinse out mouth and then drink plenty of water. After swallowing: Rinse mouth with water. Do not induce vomiting.

Most important symptoms and

effects:

Dizziness

Indication of any immediate medical attention needed:

No further relevant information available.

5 Fire-fighting measures

Extinguishing agents: CO2, extinguishing powder or water spray. Fight larger fires with water spray.

(Contd. on page 2)

(Contd. of page 1)

Printing date 02/22/2019 Revised On 02/22/2019

Trade name: FLAT BLACK ENAMEL

Special hazards: Protective equipment for Can form explosive gas-air mixtures.

A respiratory protective device may be necessary.

6 Accidental release measures

Personal precautions, protective equipment and emergency

procedures:

firefighters:

Wear protective equipment. Keep unprotected persons away. Use respiratory protective device against the effects of fumes/dust/aerosol.

Methods and material for containment and cleaning up:

Ensure adequate ventilation.

Dispose contaminated material as waste according to section 13.

7 Handling and storage

Precautions for safe handling Storage requirements:

Use only in well ventilated areas.

Keep away from sources of heat and direct sunlight. Do not warehouse in subfreezing conditions. Store locked up.

8 Exposure controls/personal protection

Components with limit values that require monitoring at the workplace:

67-64-1 Acetone

PEL (USA) Long-term value: 2400 mg/m³, 1000 ppm REL (USA) Long-term value: 590 mg/m³, 250 ppm TLV (USA) Short-term value: 1187 mg/m³, 500 ppm Long-term value: 594 mg/m³, 250 ppm

74-98-6 propane

PEL (USA) Long-term value: 1800 mg/m³, 1000 ppm REL (USA) Long-term value: 1800 mg/m³, 1000 ppm TLV (USA) refer to Appendix F inTLVs&BEIs book; D, EX

106-97-8 n-butane

REL (USA) Long-term value: 1900 mg/m³, 800 ppm TLV (USA) Short-term value: 2370 mg/m³, 1000 ppm

108-88-3 Toluene

PEL (USA) Long-term value: 200 ppm Ceiling limit value: 300; 500* ppm 10-mĭn peak per 8-hr shift

Short-term value: 560 mg/m³, 150 ppm Long-term value: 375 mg/m³, 100 ppm REL (USA) Long-term value: 75 mg/m³, 20 ppm TLV (USA)

67-63-0 Isopropyl Alcohol

PEL (USA) Long-term value: 980 mg/m³, 400 ppm REL (USA) Short-term value: 1225 mg/m³, 500 ppm Long-term value: 980 mg/m³, 400 ppm

Short-term value: 984 mg/m³, 400 ppm Long-term value: 492 mg/m³, 200 ppm TLV (USA)

Ingredients with biological limit values:

67-64-1 Acetone

BEI (USA) 50 mg/L

Medium: urine Time: end of shift

Parameter: Acetone (nonspecific)

67-63-0 Isopropyl Alcohol

BEI (USA) 40 mg/L

Medium: urine

Time: end of shift at end of workweek

Parameter: Acetone (background, nonspecific)

Keep away from foodstuffs and animal feed. Wash hands after use. Hygienic protection: Immediately remove all soiled and contaminated clothing.

Wash hands after use.

Store protective clothing separately. Avoid contact with the eyes and skin. Do not eat or drink while working.

Breathing equipment: A respirator is generally not necessary when using this product outdoors or in large open areas. In cases where short and/or long term overexposure exists, a charcoal filter respirator should be

worn. If you suspect overexposure conditions exist, please consult an authority on chemical

hygeine.

Hand protection: Nitrile gloves.

The glove material must be impermeable and resistant to the substance.

(Contd. on page 3)

Printing date 02/22/2019 Revised On 02/22/2019

Trade name: FLAT BLACK ENAMEL

(Contd. of page 2) Eye protection: Tightly sealed goggles

9 Physical and chemical properties

Appearance: Aerosol. Odor: Aromatic Odor threshold: Not determined. pH-value: Not determined. Melting point/Melting range Undetermined. **Boiling point:** -44 °C (-47.2 °F) Flash point: -19 °C (-2.2 °F)

Flammability (solid, gas): Extremely flammable. **Decomposition temperature:** Not determined.

Auto igniting: Product is not self-igniting.

Danger of explosion: In use, may form flammable/explosive vapour-air mixture.

Lower Explosion Limit: 1.5 Vol % **Upper Explosion Limit:** 10.9 Vol % Vapor pressure: Not determined.

Relative Density: Between 0.77 and 0.85 (Water equals 1.00)

Vapor density Not determined. **Evaporation rate** Not applicable. Partition coefficient: n-octonal/water: Not determined. Solubility: Not determined. Viscosity: Not determined.

VOC content (less exempt solvents): 52.5 % Water: 0.0 %

10 Stability and reactivity

Reactivity: Stable at normal temperatures.

Do not allow can to exceed 120 degrees Fahrenheit. Do not warehouse in subfreezing Conditions to avoid:

temperatures. Chemical stability:

Not fully evaluated.

Possibility of hazardous reactions: No dangerous reactions known.

Incompatible materials: No further relevant information available. Hazardous decomposition: No dangerous decomposition products known.

11 Toxicological information

LD/LC50 values that are relevant for classification:

106-97-8 n-butane

Inhalative LC50/4 h 658 mg/l (rat)

67-63-0 Isopropyl Alcohol

Oral LD50 4,570 mg/kg (rat) Dermal LD50 13,400 mg/kg (rab) Inhalative LC50/4 h 30 mg/l (rat)

Information on toxicological effects: No data available. Skin effects: No irritant effect. Eve effects: Irritating effect.

Sénsitization: No sensitizing effects known.

12 Ecological information

Aquatic toxicity: Persistence and degradability: Hazardous for water, do not empty into drains.

The product is degradable after prolonged exposure to natural weathering processes.

This product does not contain any chlorofluorocarbons (CFC's), hydrochlorofluorocarbons (HCFC's), perfluorocarbons (PFC's), heavy metals (chromium, lead, cadmium), or chlorinated Other information:

solvents.

Bioaccumulative potential: No further relevant information available. No further relevant information available. Mobility in soil: Other adverse effects: No further relevant information available.

13 Disposal considerations

Dispose of in accordance with local, state, and federal regulations. Do not puncture, incinerate, or compact. Partially empty cans must be disposed of responsibly. Do not heat or cut empty containers with electric or gas torches.

Recommendation: Completely empty cans should be recycled.

14 Transport information

UN-Number UN1950 DOT N/A

Consumer Commodity ORM-D DOT

Aerosols, flammable

ADR 1950 Aerosols (Contd. on page 4)

Ι

(Contd. of page 3)

Printing date 02/22/2019 Revised On 02/22/2019

Trade name: FLAT BLACK ENAMEL

Transport hazard class(es):

2.1 No

Class Marine pollutant:

Special precautions for user: EMS Number: Warning: Gases

F-D,S-Ŭ

Packaging Group: UN "Model Regulation":

UN1950, Aerosols, 2.1

15 Regulatory information

SARA Section 355 (extremely hazardous substances):

None of the ingredients in this product are listed.

SARA Section 313 (Specific toxic chemical listings):

108-88-3 Toluene

67-63-0 Isopropyl Alcohol

Toxic Substances Control Act

All hazardous ingredients for this product are found on the inventory list of substances. (TSCA): Consumer Product Safety

Comission (CPSC): This product complies with 16 CFR 1303 and does not contain more than 90 ppm of lead.

California Proposition 65 chemicals known to cause cancer:

1333-86-4 Carbon black

100-41-4 ethyl benzene

California Proposition 65 chemicals known to cause birth defects or reproductive harm:

108-88-3 Toluene

CANADIAN ENVIRONMENTAL

PROTECTION ACT: All hazardous ingredients for this product appear on the Canadian Domestic Substance List.

EPA:

16 Other information

67-64-1 Acetone

Contact: Regulatory Affairs