

Products Distributed by: BEST MATERIALS ®

Ph: 800-474-7570, 602-272-8

www.BestMaterials.com

Email: Sales@BestMaterials.com



In addition to Josam Company's complete line of quality cast iron and PVC specification drainage products, we are also pleased to offer the following product lines.

Push-Fit Stainless Steel Drainage System

Complete Line of Stainless Steel Drains



- Pipe and fittings manufactured of austenitic grade 316L stainless steel
- A gasketed "Push-Fit" design resulting in cost effective installations
- Pipe and fittings in sizes 1-1 /2" through 8" pipe size
- Specific gasket materials to suit different product applications
- Pressure ratings that are at least 4 times higher than previous generation systems
- Capable of being used in vacuum systems

- 8", 10" and 12" adjustable and non-adjustable round top floor drains
- 6", 8", 10", 12" and 16" adjustable and nonadjustable square top floor drains
- 2" through 8" no-hub outlets for easy connection to existing piping
- 6", 8", 12" and 16" wide trench drains
- Grates for the lightest to heaviest of loads
- 5/16". 3/4" and 3" slot and mini channels
- Ability to customize products to suit individual requirements



Complete Siphonic Roof Drainage System

- A complete system including "Push-Fit" galvanized pipes, fittings and drains
- Josam support in calculating the siphonic size requirements for a balanced system
- Space gained due to horizontal piping without slope below the roof deck
- A higher discharge rate as a result of closed flow circuit allowing smaller pipe sizes
- Less labor cost due to fewer vertical pipes and less pipe penetrations

Pro-Plus Trench Drain System



- SMC/GRP Construction
- Available with and without slope
- 4", 8" and 12" nominal interior widths
- Lightweight 70% lighter than polymer concrete
- 1.5 times stronger than polymer concrete
- Load class A-E

Information and access to pricing and literature on all of these products is available at www.JOSAM.com.

Should you require further details please contact your local Josam representative or Josam directly.

Introduction

This Josam Installation Guide is a dimensional and installation reference guide for use in the field or in the office. It contains details, specifications and roughing dimensions for all Josam Plumbing Drainage Products. All designs, descriptions and dimensions are subject to change without notice.

PRODUCT DESIGNATIONS—Each product is designated by a series number. For drainage products, the last digit in the type number indicates the pipe size. For Hydrants the type number typically indicates wall thickness, for shock absorbers the type number is based on fixture units and for interceptors the type number is based on volume or size. Outlet types are indicated by suffixes to the type number. Please specify –T for threaded, -X for inside caulk, -Y for hub outlet with gasket for 2-4" sizes and –Z for no-hub. Alpha or numeric options are added to the type number and many commonly used options are depicted on separate submittal drawings.

ALPHABETICAL INDEX—The following index will help you to locate specific products when you do not know the product series number.

SUBMITTAL DRAWINGS—This guide is arranged in numerical order by product categories in the numerical ranges shown below. Additional option or installation information is provided at the beginning of the product sections.

		Pages
Closet Carriers	11001-16123	6-44
Fixture Carriers	17000-17735	45-65
Jiffee-Joint Gaskets	19800-19826	66
Roof Drains	21500-29112	67-108
Green Roof Drains	21500-ORDG1 – 21500-Q515	109-112
Combination Drains	21500-Q265 - 30000-M-1-2	113-119
Floor Drains	30000-39960	120-179
Stainless Steel	30000-A-SS-T - 56670-SS	180-185
Sanitary Floor Sinks	49000-49870A	186-210
Cleanouts	55000-58910	211-232
Interceptors	60100H-61800	233-258
Backwater Valves	67100A-67800	259-264
Hydrants	71300-71650	265-274
Shock Absorbers	75000-75000-S	275-276
Trench Drains	76000-76800	277-281
Miscellaneous Products	85220-85903	282-283
Traps & Accessories	88100-88970	284-292
Lite Line	FD-100-A - JG-010S	293-312

FURTHER ASSISTANCE—For additional technical information, please visit our website at www.Josam.com, or contact your local Josam representative or Josam Customer Service at 1-800-36-JOSAM.

A	Cast Stainless Steel 181-185	Refrigerator (See Floor Sinks)
Abbreviations 4	Cleanouts	Roof (See Roof Drains)
Access Covers	Ferrules	Sill Drain
Floor	Plugs	Slaughter House 159, 172, 177 Stainless Steel 181-185
Parking Lot	Stainless Steel	Toilet Rooms 139-149
Wall	w/Cleanouts 140, 173-177	Trench (See Trench Drains)
Acid-Resisting Floor Sinks (See Floor Sinks)	Cleanout Access Covers	Drain Receiver, Roof 67-69
Adapters	Floor	E
Hub 289-290	Wall224-230	Electronic Grease Interceptors 240, 247
No-Hub	Cleanouts, Adjustable 212-221	Grease/Oil Level Detectors 248
Trap Primer	Finished Areas 212, 214-221 Unfinished Areas	Expansion Joints, Roof 105
Adjustable Floor Drains (See Drains)		Extension Collars
Air Gaps 290-291	Closet Fittings (See Closet Carriers)	Fixed, Floor
Air Inlets 291-292	Combination Drains 113-119	Fixed, Roof
Arresters, Water Hammer 276	Composition Deck Drains	LEVELEZE® Roof 71, 79-80, 88
В		
Backwater Valves	Connections	F
Ball Float	Hub Inside Caulk (X)	Finishes & Materials
Comb. Check & Gate 260-261	Gasket, JIFFEE-JOINT (Y) No-Hub Spigot (Z)	Fittings (See Carriers)
Offset	Threaded (T)	Fixed Air Gaps 290-291
Straight-Through Pattern 260-261	D	Fixed Supports (See Carriers)
Swing-Check 260-264		Fixture Carriers (See Carriers)
Terminal	Deck Clamps, Roof Drain	Flashing Sleeves 105-106
Backwater Valve Drains	Deep Seal Trap Drains286	FLO-SEPTOR® Drains 103-104
Bearing Pan (Drain Receiver) 67-69	Dental Sink Interceptors	Floor Access Covers (See Cleanouts)
Butt Weld Outlet 180-185	Distribution Unit	Floor Cleanouts (See Cleanouts)
	Drains Adjustable w/Strainers	Floor Drains (See Drains)
C	Cast Iron 141-154	Floor Sinks Acid-Resisting Cast Iron 188-210
Can Wash Drain (See Drains)	Adjustable, Floor	Stainless Steel
Carriers, Closet	Cast Iron	(See Josam Stainless Steel
Adapter Types	156-158, 161-162, 170, 172 Stainless Steel 181-184	Drainage Products Catalog)
Adjustable Horizontal 20-25	Balcony	Flow Control Roof Drains
Adjustable Vertical 26-37	Blood	(FLO-SET®)
Floor-Mounted Back Outlet	Boiler Room175 Can-Wash	Flow Control Fittings237
Options, Illustrated 10-17	Acid-Resisting	Frames & Grates, Trench 279-281
Prison	Cast Iron	Fresh Air Inlets
Wheelchair	Combination/Cleanouts	Funnels
Wide Chase		Funnel Drains 144-145, 286
Carriers, Cooler Drinking Fountain57-58, 60-61	Drip Drains144-145	G
Carriers, Lavatory	Extended Rim 103-104, 144	Gasket, JIFFEE-JOINT66
Corner Type	Flushing Rim, C.I	Grates & Frames, Trench 279-281
Floor-Mount	Funnel 144-145, 286 Gasoline, Volatile Liquid 174	Grease Interceptors
Concealed Arms 48-49 Exposed Arms 52-54, 63	Gutter, Roof 96-98	Electronic
Hanger Plate	Isolation Deck, Roof	High Volume
Options Illustrated 47	IRMA, Roof 81-82, 89 Key Lock, Floor	Low Boy244-245
Wall Mount	LEVELEZE® Drains	Manual Clean
Concealed Arms 49-52 Exposed Arms 54-55	Floor 156-158	239, 241-242, 244-247 Recessed242, 244
Hanger Plate 61-62	Roof	Semi-Automatic Draw-Off 243-245
Carriers, Sink	NON-CLOG 156-157, 160-162, 164 Overflow	Grease Removal Device (GRD) 240
Floor-Mount	Downspout Scupper 98-103	Green Drains 109-112, 116
Exposed Arms 52-54 w/Hanger Plate	Fountain	Н
Hanger Plate w/Adapter 64	Roof 79-80, 85-86, 103-104 Packing House 159, 172, 177	Hair Interceptors
Hanger Plate w/Fitting 65	Parapet	Hydrants
Options, Illustrated 47	Parking Deck, Roof 93-95	HYDRASAN® I (See Below)
Carriers, Urinal	Pit, Cast Iron	Integral Backflow Preventer 267
Floor-Mount Hanger Plate 57, 60 Wall-Mount Hanger Plate 62-63	Planting Area	Non-Freeze
		. 3.13 2.35

Post	P	Vent Caps, Vandal-Proof 106
Repair Kits	"P" Traps, Cast Iron 286	Vent Stack Sleeves 105-106
Wall	Packing House Drains 159, 172, 177	W
Yard270	Parapet Drains 98-100	Wall Access Covers
HYDRASAN® I	Planting Area Drains108, 178	
Maintenance Instructions 271	Plaster Interceptor	Wall Hydrants (See Hydrants)
Parts Drawing	Plaza Drains	Wall-Hung Fixture Supports
Mild Climate	(See Promenade Roof Drains)	(See Carriers)
Repair Kits	Plugs, Cleanouts	Water Hammer Arresters 276
l , '	Promenade Roof Drains 87-92	Υ
I Installation Drawings	R	Yard Hydrants274
Installation Drawings Backwater Valve	Roof Drains	
Carriers, Closet 6-9	Adjustable 79-80, 88	Abbreviations Used
Bowl to Carrier 16	Balcony	in this Catalog
Blowout8	Controlled Flow (FLO-SET®)107	Adj Adjustable
Siphon Jet	Deck Clamps	ANSI American National
Floor Drains 121, 124-125	Drain Receiver 67-69 Extensions	Standards Institute A.R.E Acid Resisting Enamel
Floor Sinks 186-187	Fixed	ASME Acid Resisting Enamer
Hydrants	LEVELEZE [®] 71, 79-80, 88	of Mechanical Engineers
Interceptors	Flashing Sleeves 105-106	ASPE American Society of
Roof Drains	Gutter	Plumbing Engineers
Interceptors	Indirect Waste 103-104	ASSE American Society
Flow Control Fittings 237	Isolation Deck 108, 116-118	of Sanitary Engineers
Grease (See Grease Interceptors)	Options, Illustrated 66-71	ASTM American Society
In-Line	Overflow 79-80, 85-86, 103-104 Parapet	for Testing & Materials
Oil Sludge	Parking Deck 93-95	Aux Auxiliary
Sand	Promenade Deck 87-92	Br Branch
Solids	Sill	Brz Bronze BWV Backwater Valve
Dental Labs	S	Cap
Food 257-258	Sanitary Floor Sinks (See Floor Sinks)	C.I
Hair	Sediment Interceptors 254-256	CISPI Cast Iron Soil Pipe Institute
Lint	Separators, Oil (See Oil Separators)	CP Chrome Plated
Plaster	Sewer Valves (See Backwater Valves)	Dim Dimension
Isolation Deck Drains 108, 116-118	Shock Absorbers, Arresters 276	DWV Drain, Waste, Vent
lκ	Sill Drains	Ext Extension
Key Lock Drain	Sinks, Floor (See Floor Sinks) SUPER-FLO-SEPTORS®	FtgFitting
	Sink Fixture Supports	Galv
L	(See Carriers, Sink)	G.P.H Gallons Per Hour
Lavatory Fixture Supports (See Carriers, Lavatory)	Solids Interceptors (See Interceptors)	G.P.M
LEVELEZE®	Stack Sleeves 105-106	H.P.T Hose Pipe Thread
Cleanouts 211-216	Stainless Steel Products	ID Inside Diameter
Floor Drains 156-158	Cast Stainless Cleanouts	IRMA Insulated Roof
Roof Drains 79-80, 88	Floor Drains 181-184	Membrane Assembly
	Fabricated Stainless Steel	L.H Left Hand
Low Boy Grease Interceptor 244-245	Grease Recovery Device	NB Nickel Bronze
M	(GRD)247	N.P.S.L. National Pipe Straight Locknut
Materials & Finishes 5	Т	N.P.T National Pipe Taper
N	Traps (See Interceptors)	O.C. On Center OD Outside Diameter
Nozzle, Downspout 101-103	Trap Primers	PDI Plumbing and
NON-CLOG Drains (See Drains)		Drainage Institute
0	Trench Drains	R.H Right Hand
		S.F Satin Finish
Oil Separators Extended Top 249, 251-252	Ulvinal Cumparts (Cas Carrians)	SSStainless Steel
External Storage Tanks 250-252	Urinal Supports (See Carriers)	SV Service Weight
Gravity Draw-Off 249-252	V	SW Service Weight
High-Volume 250-252	Valves (See Backwater Valves)	XH Extra Heavy

MATERIALS & FINISHES

Materials

BRONZE:

JOSAM bronze is a semi-red brass, generally used with a satin finish and is also an excellent base for chromium plating. All JOSAM chromium plated bronze is cast with this alloy and results in a lasting bright appearance which is stain resistant and maintenance free. Use of bronze instead of cast iron may reduce load classification.

CAST IRON:

JOSAM gray iron is produced to ASTM Standards and has a 25,000 p.s.i. minimum tensile strength. The use of quality materials and the most modern production methods results in sound, dependable metal with good corrosion resistance.

DUCTILE IRON:

A nodular graphite iron with the strength of steel is supplied for gratings, which must carry the heaviest loads.

NIKALOY:

This nickel bronze alloy is used when a high strength harder bronze material is needed for chemical resistance and a long-lasting, easily-maintained bright finish. Use of Nikaloy instead of cast iron may reduce load classification.

ACID-RESISTING COATINGS:

Floor Sinks are provided with an acid-resisting porcelain enameled or highgloss baked epoxy sanitary acid-resisting white coating that has an excellent appearance and is easy to clean. The acid-resisting coating provided on other cast iron and steel products is a two-part epoxy coating.

STAINLESS STEEL:

Stainless steel is commonly used in the dairy, food processing, chemical, pharmaceutical and institutional industries. Available in type 304 and 316L stainless steel.

PLATING AND SPECIAL COATINGS:

JOSAM bronze is often chromium plated for ease of maintenance and resistance to chlorine. All JOSAM cast iron is dip coated with a quality paint and, when required, special chemical-resistant coatings are furnished for harsh environments. Galvanized coatings are supplied by a new zinc-rich polymeric coating. This finish conforms to Mil. Spec. MIL-P21035 and is preferred to hot dipped coatings.

Finishes

ROUGH:

This designation applies to Nikaloy and bronze items, which are supplied in an "as cast" condition. All of the features of Nikaloy and bronze are present.

PAINTED:

JOSAM's protective coating is a water-reducible air-dry enamel paint.

SATIN:


Low luster finish applied to Nikaloy and bronze products makes them compatible with the present architectural trends calling for exposed hardware to be inconspicuous in appearance. This satin finish has been selected by JOSAM to be standard on all Nikaloy and bronze finished parts.

INSTALLATION OF OFF-THE-FLOOR FIXTURES

Many factors, including cost, material, labor required, space, handling and others must be thoroughly evaluated when planning an installation. With on-the-floor water closets, slabs must be penetrated and sleeved at each fixture to accommodate waste piping which, in many instances, has to be suspended below the slab.


Such suspended piping requires concealment in multi-story installations, thereby necessitating drop or furred ceilings in the rooms below. The fitting and assembly of waste piping in such installations, as a rule, must be accomplished on the spot with the aid of scaffolding and extra mechanics, which contributes to high construction costs and affects not only the mechanical contractor but the structural, floor, wall and ceiling mechanics as well.

Conversely, with off-the-floor fixtures, there is no slab penetration in toilet room areas. The support and piping systems are concealed behind the walls. Such systems are ideally suited to the modern modular plumbing concept as they are readily fabricated either on site or in the contractor's shop at significant savings over conventional piece-by-piece assembly. A well planned and executed off-the-floor fixture installation today will provide lasting benefits appreciated by future building occupants and owners.



Horizontal Fitting & Carrier Selection

DIAGRAM TO DETERMINE LEFT- OR RIGHT-HAND CLOSET FITTINGS




TYPICAL INSTALLATION SHOWN

- 1. If flow in waste line is **from the right of the stack**, the closet fitting should be a **right-hand fitting**.
- 2. If flow in waste line is **from the left of the stack**, the closet fitting should be a **left-hand fitting**.

Extension Length Determination

This is a side view. The enlarged inset shows the depth of the gasket within the groove of the fixture and the extension with proper pressure on the gasket.

When the closet is installed on the carrier, the front end of the extension must be located properly in order to compress the gasket enough so that the gasket's adhesive coated surfaces are in contact with the china and the face of the extension. This will help ensure a tight seal.




For closets which have a groove with a rectangular cross-section, use this formula: C = A + B - 1/2''

Where: A = Distance from Closet to Wall B = Depth of Groove in Closet C = Distance Extension Extends from Wall

For closets which have a groove with a V-shaped cross-section:


Use the above formula, but an additional 1/8" (or more) may be added to C.


SIPHON JET



This type, because of its quiet, efficient, sanitary flushing action, is usually specified in most commercial, institutional and hotel applications. Water is introduced into the bowl through the rim and up leg of trap through jets placed there to fill the trapway thus creating siphonic action to quickly evacuate the bowl. The large water surface in the bowl insures sanitation.

BLOWOUT







This type is particularly suited to heavy use applications such as public facilities in stadiums and terminals. The flushing action produced by the jet of water in the outlet passage is strong for rapid evacuation of the bowl. Fouling problems are minimal. However, because of the powerful flushing action, this type of closet is noisy to operate.


ONE CARRIER FOR SIPHON JET OR BLOWOUT

CHASE-SAVER® is shipped pre-assembled for siphon jet closets and is quickly inverted for use with blowout closets.






SPECIFICATION: JOSAM 12000-PF Series coated cast iron CHASE-SAVER® II Closet Carrier with adjustable connection, adjustable pylon feet, ABS extension with integral test cap, chrome plated trim, coated accessories and JIFFEE-SEAL Neoprene fixture gasket, for use with blowout or siphon jet water closets.



SPECIFICATION: JOSAM 12000-OR Series coated cast iron CHASE-SAVER® II Closet Carrier with adjustable connection, adjustable pylon feet, ABS extension with integral test cap, chrome plated trim, coated accessories and JIFFEE-SEAL Neoprene fixture gasket, for use with blowout or siphon jet water closets.



SPECIFICATION: JOSAM –32 coated cast iron Wide Chase Closet Carrier with adjustable closet connection, adjustable pylon feet, ABS extension with integral test cap, chrome plated trim, coated accessories and JIFFEE-SEAL Neoprene fixture gasket, for use with blowout or siphon jet water closets.


-32 NIPPLE SELECTION

-32 OPTION RECOMMENDED LENGTH NIPPLES (BY OTHERS)

A* Minimum Chase	Length Nipple to Use
9-1/4	2-7/8
10-1/4	4
11-1/4	5
12-1/4	6
13-1/4	7
14-1/4	8
15-1/4	9
16-1/4	10
17-1/4	11
18-1/4	12

Recommended Pipe: 4" Galvanized Steel

NIPPLE LENGTH DRAWING




To provide proper fixture support, the carrier should be set directly behind or within the wall. To accomplish this in wide pipe chases with DWV piping either centered or offset, it is necessary to separate carrier and drainage fitting as required with nipples that are longer than 2-7/8." The minimum dimension (A*) was determined using a 2-7/8" length nipple. Nipples ranging in length from 2-7/8" to 12" in 1 inch increments are identified on this page for specification when such construction conditions are encountered.

12000 Minimum Dimensions SINGLE **BACK-TO-BACK**


12000-32 Minimum Dimensions * MAY VARY + 1/4 * MAY VARY ±1/4"

ADJUSTABLE EXTENSIONS AVAILABLE FOR -32 OPTION							
Wall Thickness	Length of Extension	Length of Threaded Rod	ABS Extension Part No.				
1" through 5-1/2"	7"	9-1/2"	07095A				
5-1/2" through 10-1/2"	12"	14-1/2"	07095E				




(-AUX) OPTION, 2" AUXILIARY INLET

The 2" auxiliary inlet is for applications with back-to-back bathrooms where the ladies room has a water closet carrier and the mens room has a urinal carrier. (Available on 12674 and 12684 Series.)



(-VP) OPTION, VANDAL-PROOF TRIM


The JOSAM Vandal-Proof trim is designed to prevent tampering and possible damage to the fixture caused by vandalism. The Vandal-Proof trim can be used in place of the regular JOSAM cap nuts. Trim is installed using a hex key. After installation is complete, chrome plated expansion plugs which match the nuts, snap into place minimizing the chances of vandalism.



(-1) OPTION, TRU-SET POSITIONING FRAME (Siphon Jet Closets Only)


Made of high impact polystyrene, the TRU-SET Positioning Frame offers many advantages to the plumbing contractor. The positioning frame is mounted on the carrier studs at the time the carrier is being installed, thus it acts as a guide and template, eliminating problems caused by normal dimensional variations when the wall is being erected. Studs and adjustable extension are set to the frame, eliminating further adjustment when the fixture is being hung. Chances of bowl breakage are minimized since bowl is held the correct distance from finished wall.


NOTE: Sold only with JOSAM closet carriers.



(-6) OPTION, SUPPLY PIPE SUPPORT

Support assembly attaches to an upper carrier mounting stud and securely holds water supply pipe running to the flush valve. This hanger prevents movement of water piping during and after construction, protecting piping as well as the flush valve. When ordering, specify type of pipe to be supported.









ILLUSTRATION A

ILLUSTRATION B


(-24) OPTION, FOR FLOOR-MOUNTED BACK-OUTLET CHINA CLOSETS

This option adapts adjustable as well as other types of fittings for securing floor-mounted back-outlet China closets. Any adjustable fitting is adapted as shown in Illustration A. Other types of fittings are provided with bosses to attach the closet securing studs at the correct dimensions for this type of closet. See Illustration B.



(-35) OPTION, CLOSET CARRIER FOR WHEELCHAIR HIGH ROUGH


This optional carrier can be used with all adjustable fittings. When used with blowout closets over 12 1/2", **specify –M1358**.



-PAF OPTION, PRE-FAB ADJUSTABLE FEET


These optional feet can be used with 12000-OR, 12000-CR or 12000-PF faceplates. Feet are designed to be attached to angle iron or unistrut for pre-fab construction.

12000-OR WRENCH



Use 12000-OR wrench to apply forward pressure as you thread extension into 12000-OR faceplace.

BOWL TO CARRIER INSTALLATION



FH Hardware Part #: 565985T Mounting Stud and Back-up Nut not included in FH Hardware Kit.


To set bowl using finished hardware group "FH," put a hex nut, back-up washer, and a bowl stabilizer on each mounting stud.

Adjust with front of back-up nut and washer at finished wall line.


If the back-up nut and washer are moved to clear irregularities in the finished wall, the extension MUST be adjusted an equal amount.

Place fixture gasket in toilet outlet and hang closet. Assemble fiber washers and JOSAM cap nuts to two studs on the center line of the closet outlet and one other stud below and tighten with a wrench.

Assemble fiber washer and JOSAM cap nut to remaining stud, hand tighten and take 1/2 turn with a wrench




Installation of back-to-back 12000-PF Series Adjustable Carrier showing minimum extension.




Installation of 12000-PF Series Adjustable Carrier in a standard 12" wide pipe chase showing minimum extension.

Installations 90° Double Waste Fitting 15964 &15984 Series

Installations of 15964 and 15984 Series double vertical 90° no-hub fittings where a closet and lavatory are installed in each room with one stack serving two rooms.








15984 SERIES DOUBLE WASTE VERTICAL FITTING SHOWN INSTALLED IN A TYPICAL ROOM BOTTOM DISCHARGE TOILET FACILITY LAYOUT

JOSAM SERIES 11001 COATED CAST IRON UNIVERSAL PIPE GRIP CLOSET CARRIER WITH 4" PIPE ADAPTER, ADJUSTABLE FEET AND FINISH HARDWARE AND TRIM TO SUPPORT SIPHON JET OR BLOWOUT WALL-HUNG WATER CLOSET. WASTE PIPING AND FITTING SUPPLIED BY OTHERS.

CLOSET CARRIER

WITH PIPE ADAPTER

11001 SERIES



MICHIGAN CITY, INDIANA


SPECIFICATION:

JOSAM SERIES 11007 AND 11008 COATED CAST IRON UNIVERSAL PIPE GRIP CLOSET CARRIER WITH 3" OR 4" COPPER PIPE ADAPTER, ADJUSTABLE FEET AND FINISH HARDWARE AND TRIM TO SUPPORT SIPHON JET OR BLOWOUT WALL-HUNG WATER CLOSET. WASTE PIPING AND FITTING SUPPLIED BY OTHERS.

CLOSET CARRIER

WITH COPPER PIPE ADAPTER

SERIES 11007 & 11008



IMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

DIMENSIONS ARE SUBJECT TO MANUFACTURERS


TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA

SPECIFICATION: JOSAM 12674-XSD AND 12684-XSD SERIES COATED CAST IRON HORIZONTAL 4" NO-HUB FITTING WITH 2" NO-HUB VENT AND ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP. PYLON FEET, ANCHOR FOOT, ANGLE SUPPORT, THREADED ROD. PLATED HARDWARE AND NEOPRENE FIXTURE GASKET.

BARIATRIC CARRIER (LEFT HAND SHOWN)

12674-XSD 12684-XSD SERIES




MICHIGAN CITY, INDIANA

SPECIFICATION: JOSAM 12674 SERIES COATED CAST IRON SINGLE HORIZONTAL 4" NO-HUB LEFT-HAND OFFSET FITTING WITH 2" NO-HUB VENT AND ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND

NEOPRENE FIXTURE GASKET.

CLOSET CARRIER LEFT HAND

12674 **SERIES**



-PF	PYLON FOOT, STD		-6	SUPPLY PIPE SUPPORT (SPECIFY TYPE OF PIPE)	
-OR	O-RING CARRIER		-10	ABS EXTENSION THROUGH 10-1/2" WALL	
-SD	SPECIAL-DUTY 500 LB CARRIER		-24	FLOOR MOUNTED BACK OUTLET CHINA BOWL	
-HS	HUB & SPIGOT		-30	CAST IRON ADJ. EXTENSION W/ CONNECTOR	
-AUX	O AUXILIARY INLET (2" NO-HUB)		-30-2	CAST IRON ADJ. EXTENSION W/ CONNECTOR & TEST CAP	
-HUB AUX	O AUXILIARY INLET (2" HUB)		-32	CARRIER FOR WIDE CHASE INSTALLATIONS	
-VP	VANDAL-PROOF TRIM		-35	CARRIER FOR WHEELCHAIR HIGH ROUGH	
-1	POSITIONING FRAME		-58	HORIZONTAL NO-HUB CAST LONG BARREL	

DATE OF LAST CHANGE: 4/20/2015 DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA

JOSAM 12674-HS SERIES COATED CAST IRON SINGLE HORIZONTAL 4" HUB & SPIGOT LEFT-HAND OFFSET FITTING WITH 2" HUB & SPIGOT VENT AND ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET.


CLOSET CARRIER LEFT HAND

SERIES

12674-HS

NOTES:

FORMERLY 12004 SERIES



JOSAM COMPANY

MICHIGAN CITY, INDIANA

SPECIFICATION:

DATE OF LAST CHANGE:

IMENSIONS ARE SUBJECT TO MANUFACTURERS


TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.

JOSAM 12674-32 SERIES COATED CAST IRON SINGLE HORIZONTAL 4" NO-HUB LEFT-HAND OFFSET FITTING WITH 2" NO-HUB VENT AND ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP. PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET

CLOSET CARRIER LEFT HAND

12674-32 **SERIES**




JOSAM COMPANY

MICHIGAN CITY, INDIANA


DRAWING No. 05/10/08

A-12623L-K



LEFT HAND 12674-35

CLOSET CARRIER



DATE OF LAST CHANGE: IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA

VANDAL-PROOF TRIM

POSITIONING FRAME

-VP

-1

JOSAM COMPANY MICHIGAN CITY, INDIANA

-35

-58

CARRIER FOR WHEELCHAIR HIGH ROUGH


HORIZONTAL NO-HUB CAST LONG BARREL

SPECIFICATION:

JOSAM 12674-58 SERIES COATED CAST IRON LONG BARREL LEFT-HAND HORIZONTAL 4" NO-HUB FITTING WITH 2" NO-HUB VENT AND ADJUSTABLE CARRIER BODY, ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET. INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS

CLOSET CARRIER LEFT HAND

12674-58 SERIES



JOSAM 12684 SERIES COATED CAST IRON SINGLE HORIZONTAL 4" NO-HUB RIGHT-HAND OFFSET FITTING WITH 2" NO-HUB VENT AND ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET

CLOSET CARRIER

RIGHT HAND


12684 SERIES

CARRIER FOR WIDE CHASE INSTALLATIONS

CARRIER FOR WHEELCHAIR HIGH ROUGH

HORIZONTAL NO-HUB CAST LONG BARREL

NOTES



-32

-35

JOSAM COMPANY

MICHIGAN CITY, INDIANA


SPECIFICATION:

JOSAM 12684-HS SERIES COATED CAST IRON SINGLE HORIZONTAL 4" HUB & SPIGOT RIGHT-HAND OFFSET FITTING WITH 2" HUB & SPIGOT VENT AND ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET.

CLOSET CARRIER RIGHT HAND

12684-HS SERIES

FORMERLY 12024 SERIES



MICHIGAN CITY, INDIANA

-HUB AU

-VP

-1

DATE OF LAST CHANGE:

IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA

AUXILIARY INLET (2" HUB)


VANDAL-PROOF TRIM

POSITIONING FRAME

JOSAM 12684-58 SERIES COATED CAST IRON LONG BARREL RIGHT-HAND HORIZONTAL 4" NO-HUB FITTING WITH 2" NO-HUB VENT AND ADJUSTABLE CARRIER BODY, ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET. INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS.

CLOSET CARRIER RIGHT HAND

12684-58




SPECIFICATION:

JOSAM 12694 SERIES COATED CAST IRON DOUBLE HORIZONTAL 4" NO-HUB FITTING WITH 2" NO-HUB VENT AND ADJUSTABLE CARRIER BODY, ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS.

CLOSET CARRIER BACK-TO-BACK

12694 **SERIES**



DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

VANDAL-PROOF TRIM

POSITIONING FRAME

-VP

-1

JOSAM COMPANY MICHIGAN CITY, INDIANA

-58

-XSD

EXTRA SPECIAL DUTY 1,000 LB CARRIER NOTES

HORIZONTAL NO-HUB CAST LONG BARREL


JOSAM 12694-HS SERIES COATED CAST IRON DOUBLE HORIZONTAL 4" HUB & SPIGOT FITTING WITH 2" HUB & SPIGOT VENT AND ADJUSTABLE CARRIER BODY, ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS

CLOSET CARRIER BACK-TO-BACK

SERIES

12694-HS

FORMERLY 12044 SERIES




MICHIGAN CITY, INDIANA

SPECIFICATION:

JOSAM 12694-58 SERIES COATED CAST IRON LONG BARREL DOUBLE HORIZONTAL 4" NO-HUB FITTING WITH 2" NO-HUB VENT AND ADJUSTABLE CARRIER BODY, ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET. INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS.


CLOSET CARRIER BACK-TO-BACK

12694-58 **SERIES**



MICHIGAN CITY, INDIANA

A-12619-K



5" MAX VENT

FINISHED WALL—

BOWL STABILIZER:

7 1/2"

4 1/2" MIN 10" MAX

TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA

6 3/8"

5 1/2"

ADJUSTABLE

FOOT ⊠

5 3/4"

1 1/4" —

2" NO-HUB

2 1/4"

JOSAM 12704 SERIES COATED CAST IRON SINGLE VERTICAL 4" NO-HUB FITTING WITH 2" NO-HUB LEFT-HAND OFFSET VENT. ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT. PLATED HARDWARE AND NEOPREME FIXTURE GASKET

5 1/8"

5 3/4"

ANCHOR

2 15/16"

1 11/16

3/4"

FIXTURE GASKET

11 1/8" | 13 3/4"

-EXTENSION

FOOT

CLOSET CARRIER
VERTICAL W/ LEFT HAND VENT


SERIES 12704

FOR DIMENSION SHORTER THAN 5-1/2" (1" MIN) CUT EXTENSION. FOR LONGER EXTENSION (10-1/2" MAX) SPECIFY (-10)

☐ RECOMMEND FEET BE SECURED TO FLOOR WITH 1/2" BOLTS AND ANCHORS (BY OTHERS).

SIPHON JET DIMS SHOWN. FOR BLOWOUT DIMS, USE:

MIN 11 & MAX 16-1/2"



MICHIGAN CITY, INDIANA

JOSAM 12704-HS SERIES COATED CAST IRON SINGLE VERTICAL 4" HUB & SPIGOT FITTING WITH 2" HUB & SPIGOT LEFT-HAND OFFSET VENT. ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET.


CLOSET CARRIER VERTICAL W/ LEFT HAND VENT

SERIES

12704-HS

NOTES:

FORMERLY 12114A SERIES



JOSAM COMPANY

MICHIGAN CITY, INDIANA

SPECIFICATION:

JOSAM 12704-LH4 SERIES COATED CAST IRON SINGLE VERTICAL 4" NO-HUB FITTING WITH LEFT-HAND 4" NO-HUB BRANCH INLET AND 2" NO-HUB LEFT-HAND OFFSET VENT, ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET

SUPPLY PIPE SUPPORT (SPECIFY TYPE OF PIPE

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE


WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

CLOSET CARRIER

VERTICAL W/ LEFT HAND VENT AND LEFT HAND INLET

12704-LH4 **SERIES**

NOTES



JOSAM COMPANY

MICHIGAN CITY, INDIANA

DRAWING No. 05/10/08

A-14675-K

DRAWING No. 05/10/08

A-14678-K

SPECIFICATION:


JOSAM 12704-HS-HLH4 SERIES COATED CAST IRON SINGLE VERTICAL 4" HUB & SPIGOT FITTING WITH LEFT-HAND 4" HUB & SPIGOT BRANCH INLET AND 2" HUB & SPIGOT LEFT-HAND OFFSET VENT, ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET

CLOSET CARRIER

VERTICAL W/ LEFT HAND VENT

12704-HS-HLH4 **SERIES**

FORMERLY 12174A SERIES



JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES:

SPECIFICATION:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.


WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM 12704-RH4 SERIES COATED CAST IRON SINGLE VERTICAL 4" NO-HUB FITTING WITH RIGHT-HAND 4" NO-HUB BRANCH INLET AND 2" NO-HUB LEFT-HAND OFFSET VENT. ADJUSTABLE CARRIER BODY. INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS. WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET.

CLOSET CARRIER

VERTICAL W/ LEFT HAND VENT AND RIGHT HAND INLET

12704-RH4 **SERIES**




MICHIGAN CITY, INDIANA

JOSAM 12704-HS-HRH4 SERIES COATED CAST IRON SINGLE VERTICAL 4" HUB & SPIGOT FITTING WITH RIGHT-HAND 4" HUB & SPIGOT BRANCH INLET AND 2" HUB & SPIGOT LEFT-HAND OFFSET VENT, ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET

CLOSET CARRIER VERTICAL W/ LEFT HAND VENT

12704-HS-HRH4 **SERIES**




SPECIFICATION:

JOSAM 12704-D4 SERIES COATED CAST IRON SINGLE VERTICAL 4" NO-HUB FITTING WITH 4" NO-HUB BRANCH INLETS AND 2" NO-HUB LEFT-HAND OFFSET VENT, ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET.

CLOSET CARRIER

VERTICAL W/ LEFT HAND VENT

12704-D4 **SERIES**



DRAWING No. 05/10/08

JOSAM COMPANY A-14681-K MICHIGAN CITY, INDIANA

NOTES:

DATE OF LAST CHANGE: 3/24/09 JOSAM COMPANY DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA

POSITIONING FRAME

NOTES


-35 CARRIER FOR WHEELCHAIR HIGH ROUGH

JOSAM 12704-HS-HD4 SERIES COATED CAST IRON SINGLE VERTICAL 4" HUB & SPIGOT FITTING DOUBLE 4" HUB & SPIGOT BRANCH INLETS AND 2" HUB & SPIGOT LEFT-HAND OFFSET VENT. ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET

CLOSET CARRIER

VERTICAL W/ LEFT HAND VENT

12704-HS-HD4



DRAWING No. 05/10/08 **JOSAM COMPANY** A-14683-K MICHIGAN CITY, INDIANA

NOTES:


SPECIFICATION:

ANCHOR

JOSAM 12714 SERIES COATED CAST IRON SINGLE VERTICAL 4" NO-HUB FITTING WITH 2" NO-HUB RIGHT-HAND OFFSET VENT. ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS. WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET. ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET

CLOSET CARRIER VERTICAL W/ RIGHT HAND VENT

12714 **SERIES**



	-XSD	EXTRA SPECIAL-DUTY 1,000 LB CARRIER		-1	POSITIONING FRAME
	-PF	PYLON FOOT, STD.		-6	SUPPLY PIPE SUPPORT (SPECIFY TYPE OF PIPE)
	-OR	O-RING CARRIER		-10	ABS EXTENSION THROUGH 10-1/2" WALL
	-SD	SPECIAL-DUTY 500 LB. CARRIER		-24	FLOOR MOUNTED BACK OUTLET CHINA BOWL
	-HS	HUB & SPIGOT		-30	CAST IRON ADJ. EXTENSION W/ CONNECTOR
	-LH4	LEFT-HAND 4" NO-HUB BRANCH		-30-2	CAST IRON ADJ. EXTENSION W/ CONNECTOR & TEST CAP
	-HLH4	LEFT-HAND 4" HUB BRANCH		-32	CARRIER FOR WIDE CHASE INSTALLATIONS
	-RH4	RIGHT-HAND 4" NO-HUB BRANCH		-35	CARRIER FOR WHEELCHAIR HIGH ROUGH
ш	-HRH4	RIGHT-HAND 4" HUB BRANCH	П	-49	NO-HUB AUXILIARY INLET, UNDER VENT
Ш	-D4	DOUBLE 4" NO-HUB BRANCHES		-50	NO-HUB AUXILIARY INLET, OPPOSITE VENT
	-HD4	DOUBLE 4" HUB BRANCHES		-53	THREADED AUXILIARY INLET, UNDER VENT
ш	-VP	VANDAL-PROOF TRIM	П	-54	THREADED AUXILIARY INLET, OPPOSITE VENT

DATE OF LAST CHANGE: 4/22/2015 DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

JOSAM 12714-HS SERIES COATED CAST IRON SINGLE VERTICAL 4" HUB & SPIGOT FITTING WITH 2" HUB & SPIGOT RIGHT-HAND OFFSET VENT. ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET.


CLOSET CARRIER

VERTICAL W/ RIGHT HAND VENT

SERIES

12714-HS

FORMERLY 12134A SERIES



MICHIGAN CITY, INDIANA


SPECIFICATION:

JOSAM 12714-RH4 SERIES COATED CAST IRON SINGLE VERTICAL 4" NO-HUB FITTING WITH RIGHT-HAND 4" NO-HUB BRANCH INLET AND 2" NO-HUB RIGHT-HAND OFFSET VENT, ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET

CLOSET CARRIER VERTICAL W/ RIGHT HAND VENT

12714-RH4 SERIES

FORMERLY 12744 SERIES



A-14676-K

DRAWING No. 05/10/08

A-14676-K

SPECIFICATION:

JOSM 12714H5-HRH SERIES COATED CAST IRON SINGLE VERTICAL 4" HUB & SPICOT FITTING WITH RICHT-HAND 4" HUB & SPICOT BRANCH HUET AND 2" HUB & SPICOT BRANCH HUET AND 2" HUB & SPICOT RICHT-HAND OFFSET VENT. ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIHHON, JET OR BLOWGUT CLOSETS, WITH ASSE STETNISION WITH MTEGRAL TEST CAP. PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FOTURE CASKET.


CLOSET CARRIER

VERTICAL W/ RIGHT HAND VENT

SERIES 12714-HS-HRH4

FORMERLY 12194A SERIES

NOTES:



JOSAM COMPANY

MICHIGAN CITY, INDIANA

SPECIFICATION:


A-13769-K

JOSAM 12714-LH4 SERIES COATED CAST IRON SINGLE VERTICAL 4" NO-HUB FITTING WITH LEFT-HAND 4" NO-HUB BRANCH INLET AND 2" NO-HUB RIGHT-HAND OFFSET VENT: ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PUCN FEET. ANCHOR FOOT, PLATED HARDWARE AND MEOPREME FIXTURE GASKET.

CLOSET CARRIER VERTICAL W/ RIGHT HAND VENT

SERIES 12714-LH4

FORMERLY 12774 SERIES




MICHIGAN CITY, INDIANA

JOSAM 12714H-S-HLH SERIES COATED CAST IRON SINGLE VERTICAL 4" HUB & SPIGOT FITTING WITH LET-HAND 4" HUB AS SPIGOT RIGHT AND 2" HUB AS SPIGOT RIGHT HAND OFFSET VENT. ADJUSTABLE CARRIER RODY, NUCRTIBLE LOFOR SIPHON, LET OR BLOWOUT CLOSETS, WITH ASS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FOTURE CASSET.

CLOSET CARRIER

VERTICAL W/ RIGHT HAND VENT

SERIES 12714-HS-HLH4




MICHIGAN CITY, INDIANA

SPECIFICATION:

JOSAM 1274-D4 SERIES COATED CAST IRON SINGLE VERTICAL 4" NO-HUB FITTING WITH TWO 4" NO-HUB BRANCH INLETS AND 2" NO-HUB RIGHT-HAND OFFSET VENT. ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET. ANCHOR FOOT. PLATED HARDWARE AND REOPRENE RIVITURE GASKET.

CLOSET CARRIER VERTICAL W/ RIGHT HAND VENT

SERIES 12714-D4



A-14682-K


JOSAM 12714-HS-HD4 SERIES COATED CAST IRON SINGLE VERTICAL 4" HUB & SPIGOT FITTING DOUBLE 4" HUB & SPIGOT BRANCH INLETS AND 2" HUB & SPIGOT RIGHT-HAND OFFSET VENT. ADJUSTABLE CARRIER BODY. INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET

CLOSET CARRIER

VERTICAL W/ RIGHT HAND VENT

12714-HS-HD4 SERIES

FORMERLY 12294A SERIES



DRAWING No. 05/10/08 **JOSAM COMPANY** A-14684-K MICHIGAN CITY, INDIANA


NOTES:


SPECIFICATION:


JOSAM 12724 SERIES COATED CAST IRON DOUBLE VERTICAL 4" NO-HUB ON STACK FITTING WITH 2" NO-HUB OFFSET VENT, ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET

CLOSET CARRIER VERTICAL BACK-TO-BACK

12724 **SERIES**







FOR DIMENSION SHORTER THAN 5-1/2" (1" MIN) CUT EXTENSION. FOR LONGER EXTENSION (10-1/2" MAX) SPECIFY (-10)

ØRECOMMEND FEET BE SECURED. TO FLOOR WITH 1/2" BOLTS AND ANCHORS (BY OTHERS).

FOR SIPHON JET ROUGHING OVER 6" OR BLOWOUT ROUGHING OVER 12-1/2" SPECIFY ON ORDER.

SIPHON JET DIMS SHOWN. FOR BLOWOUT DIMS. USE:

/ MIN 11 & MAX 16-1/2"

			-1	POSITIONING FRAME
	-XSD	EXTRA SPECIAL-DUTY 1,000 LB CARRIER	-6	SUPPLY PIPE SUPPORT (SPECIFY TYPE OF PIPE)
	-PF	PYLON FOOT, STD.	-10	ABS EXTENSION THROUGH 10-1/2" WALL
	-OR	O-RING CARRIER	-24	FLOOR MOUNTED BACK OUTLET CHINA BOWL
Ш	-HS	HUB & SPIGOT	-30	CAST IRON ADJ. EXTENSION W/ CONNECTOR
Ш	-LH4	LEFT-HAND 4" NO-HUB BRANCH	-30-2	CAST IRON ADJ. EXTENSION W/ CONNECTOR & TEST CAP
Ш	-HLH4	LEFT-HAND 4" HUB BRANCH	-32	CARRIER FOR WIDE CHASE INSTALLATIONS
	-RH4	RIGHT-HAND 4" NO-HUB BRANCH	-35	CARRIER FOR WHEELCHAIR HIGH ROUGH
	-HRH4	RIGHT-HAND 4" HUB BRANCH	-49	NO-HUB AUXILIARY INLET, UNDER VENT
	-D4	DOUBLE 4" NO-HUB BRANCHES	-50	NO-HUB AUXILIARY INLET. OPPOSITE VENT
	-HD4	DOUBLE 4" HUB BRANCHES	-53	THREADED AUXILIARY INLET, UNDER VENT
Ш	-VP	VANDAL-PROOF TRIM	-54	THREADED AUXILIARY INLET, OPPOSITE VENT
			-54	TIREADED AUXILIANT INLET, OFFOSITE VENT

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA


NOTES

JOSAM 12724-HS SERIES COATED CAST IRON DOUBLE VERTICAL 4" HUB & SPIGOT FITTING WITH 2" HUB & SPIGOT OFFSET VENT. ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET.

CLOSET CARRIER VERTICAL BACK-TO-BACK

12724-HS SERIES

FORMERLY 12154A SERIES



SPECIFICATION:


A-13746-K

JOSAM 12724-VS4 SERIES COATED CAST IRON DOUBLE VERTICAL 4" NO-HUB ON STACK FITTING WITH UNDER VENT SIDE 4" NO-HUB BRANCH INLET AND 2" NO-HUB OFFSET VENT. ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP. PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET

CLOSET CARRIER VERTICAL BACK-TO-BACK

SERIES

12724-VS4



MICHIGAN CITY, INDIANA


A-13756-K

SPECIFICATION:

JOSAM 12724-OS SERIES COATED CAST IRON DOUBLE VERTICAL 4"NO-HUB
ON STACK FITTING WITH OPPOSITE VENT SIGE 4"NO-HUB BRANCH INET AND 2"
NO-HUB OFFSET VENT AGUISTABLE CARRIER BODY, INVERTIBLE FOR SIPHON
JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP,
PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE

CLOSET CARRIER VERTICAL BACK-TO-BACK

12724-OS4



MICHIGAN CITY, INDIANA

SPECIFICATION:


A-14680-K

JOSAM 12724-HS-HVS4 SERIES COATED CAST IRON DOUBLE VERTICAL 4" HUB & SPIGOT FITTING WITH RICHT-HAND HUB & SPIGOT BRANCH HUET AND 2" HUB & SPIGOT OFFSET VENT. ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON HE OR BLOWOUT CASETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PVLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET.

CLOSET CARRIER VERTICAL BACK-TO-BACK

SERIES 12724-HS-HVS4

FORMERLY 12214A SERIES



MICHIGAN CITY, INDIANA

JOSAM 12724-D4 SERIES COATED CAST IRON DOUBLE VERTICAL 4" NO-HUB ON STACK FITTING WITH TWO 4" NO-HUB BRANCH INLETS AND 2" NO-HUB OFFSET VENT. ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET.

POSITIONING FRAME

DRAWING No. 05/10/08

A-13753-K

CLOSET CARRIER VERTICAL BACK-TO-BACK

SERIES

12724-D4

CARRIER FOR WHEELCHAIR HIGH ROUGH

NOTES:

FORMERLY 12814 SERIES FINISHED WALL EXTENSION FIXTURE GASKET MIN STABILIZER 14 MIN. 18 6 MAX ▲ FOR DIMENSION SHORTER THAN 5-1/2" (1" MIN) CUT EXTENSION. FOR LONGER EXTENSION (10-1/2" MAX) SPECIFY (-10) ■ RECOMMEND FEET BE SECURED TO FLOOR WITH 1/2" BOLTS AND ANCHORS (BY OTHERS) ⊗ FOR SIPHON JET ROUGHING OVER 6" OR BLOWOUT ROUGHING OVER 12-1/2" SPECIFY ON ORDER SIPHON JET DIMS SHOWN FOR BLOWOUT DIMS, USE → MIN 11 & MAX 16-1/2* PYLON FOOT, STD SUPPLY PIPE SUPPORT (SPECIFY TYPE OF PIPE) -OR O-RING CARRIER -10 ABS EXTENSION THROUGH 10-1/2" WALL -SD SPECIAL-DUTY 500 LB. CARRIER FLOOR MOUNTED BACK OUTLET CHINA BOWL -HS **HUB & SPIGOT** CAST IRON ADJ. EXTENSION W/ CONNECTOR -D4 DOUBLE 4" NO-HUB BRANCHES CAST IRON ADJ. EXTENSION W/ CONNECTOR & TEST CAP -VP VANDAL-PROOF TRIM -32 CARRIER FOR WIDE CHASE INSTALLATIONS

JOSAM COMPANY

MICHIGAN CITY, INDIANA


SPECIFICATION:

JOSAM 12724-HS-HD4 SERIES COATED CAST IRON DOUBLE VERTICAL 4" HUB & SPIGOT FITTING WITH DOUBLE HUB & SPIGOT BRANCH INLETS AND 2" HUB & SPIGOT OFFSET VENT. ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP. PYLON FEET, ANCHOR FOOT, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET

CLOSET CARRIER VERTICAL BACK-TO-BACK

12724-HS-HD4 **SERIES**

FORMERLY 12314A SERIES




JOSAM 14004 SERIES COATED CAST IRON SINGLE VERTICAL 4" HUB AND SHOOT LETT-HAND OFFSET FITTING WITH 2" HUB VENT ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP PYLON FEET, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET.

CLOSET CARRIER

SINGLE, LEFT HAND OFFSET AND 2" VENT

SERIES

14004



			_		
П	-SD	SPECIAL DUTY 500 LB CARRIER		-30	CAST IRON ADJ. EXT. W/ CONNECTOR
	-VP	VANDAL-PROOF TRIM		-30-2	CAST IRON ADJ. EXT. W/ CONNECTOR & TEST CAP
П	-1	POSITIONING FRAME	Г	-50	NO-HUB HIGH AUXILIARY INLET, OPPOSITE VENT
	-6	SUPPLY PIPE SUPPORT (SPECIFY TYPE OF PIPE)	Г	-54	THREADED HIGH AUXILIARY INLET, OPPOSITE VENT
	-21	HANGER TYPE CLOSET ADAPTER	Г	-XSD	EXTRA SPECIAL DUTY 1,000 LB CARRIER
	-54	THREADED AUXILIARY INLET, OPPOSITE VENT			

DATE OF LAST CHANGE: 5/04/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA NOTES

SPECIFICATION:

JOSAM 14024 SERIES COATED CAST IRON SINGLE VERTICAL 4" HUB AND SPIGOT RIGHT-HAND OFFSET FITTING WITH 2" HUB VENT, ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET.

THREADED AUXILIARY INLET, OPPOSITE VENT

-54

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS


TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.

CLOSET CARRIER

SINGLE, RIGHT HAND OFFSET AND 2" VENT

SERIES 14024




JOSAM COMPANY MICHIGAN CITY, INDIANA

JOSAM 14044 SERIES COATED CAST IRON DOUBLE VERTICAL 4" HUB AND SPIGOT OFFSET FITTING WITH 2" HUB VENT, ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET.

CLOSET CARRIER

DOUBLE OFFSET AND 2" VENT

14044 SERIES



-30 CAST IRON ADJ. EXT. W/ CONNECTOR -VP VANDAL-PROOF TRIM -30-2 CAST IRON ADJ. EXT. W/ CONNECTOR & TEST CAP POSITIONING FRAME SUPPLY PIPE SUPPORT (SPECIFY TYPE OF PIPE) NO-HUB HIGH AUXILIARY INLET. OPPOSITE VENT -6 HANGER TYPE CLOSET ADAPTER THREADED HIGH AUXILIARY INLET, OPPOSITE VENT -54 THREADED AUXILIARY INLET, OPPOSITE VENT -XSD EXTRA SPECIAL DUTY 1,000 LB CARRIER

DATE OF LAST CHANGE: IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:


JOSAM 14064 SERIES COATED CAST IRON SINGLE VERTICAL 4" HUB AND SPIGOT FITTING WITH 4" HUB VENT, ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET.


CLOSET CARRIER

VERTICAL SINGLE CLOSE

14064 **SERIES**







- EXTENSION FOR LONGER EXTENSION (10-1/2" MAX) SPECIFY (-10).
- ☑ RECOMMEND FEET BE SECURED TO FLOOR WITH 1/2" BOLTS AND ANCHORS (BY OTHERS).
- FOR SIPHON JET ROUGHING OVER 6" OR BLOWOUT ROUGHING OVER 12-1/2" SPECIFY ON ORDER.

SIPHON JET DIMS SHOWN FOR BLOWOUT DIMS, USE:

MIN 11" & MAX 16 1/2"

				-21	TANGER THE GEOGET ABAITER
П	-SD	SPECIAL DUTY 500 LB CARRIER		-54	THREADED AUXILIARY INLET, OPPOSITE VENT
	-VP	VANDAL-PROOF TRIM		-30	CAST IRON ADJ. EXT. W/ CONNECTOR
	-1	POSITIONING FRAME		-30-2	CAST IRON ADJ. EXT. W/ CONNECTOR & TEST CAP
	-6	SUPPLY PIPE SUPPORT (SPECIFY TYPE OF PIPE)		-50	NO-HUB HIGH AUXILIARY INLET, OPPOSITE VENT
	-44	THREADED LEFT HAND AUXILIARY INLET		-54	THREADED HIGH AUXILIARY INLET, OPPOSITE VENT
	-46	THREADED RIGHT HAND AUXILIARY INLET		-XSD	EXTRA SPECIAL DUTY 1,000 LB CARRIER

-21

DATE OF LAST CHANGE: 4/22/15 **JOSAM COMPANY** IMENSIONS ARE SUBJECT TO MANUFACTURERS. TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA

USE OF SUPERSEDED OR VOID DATA.

- 7 5/8 -

NOTES


HANGER TYPE CLOSET ADAPTER

SPECIFICATION:

JOSAM 14104 SERIES COATED CAST IRON SINGLE VERTICAL 4" HUB AND SPIGOT FITTING WITH 2" HUB VENT, ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET.

CLOSET CARRIER VERTICAL SINGLE CLOSE

14104 SERIES



	-46	THREADED RIGHT HAND AUX	XILIARY INLET		-XSD	EXTRA SPECIAL	DUTY 1,000 LB CARRIER
D	ATE (OF LAST CHANGE: 4/24/15	10041	_			NOTES
		ONS ARE SUBJECT TO MANUFACTURERS	JUSAN	1	CU	MPANY	
	WEC	ANCES AND CHANGE WITHOUT NOTICE. AN ASSUME NO RESPONSIBILITY FOR	MICHIGA	Ν	CITY.	INDIANA	

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.


SPECIFICATION: JOSAM 14404 SERIES COATED CAST IRON SINGLE VERTICAL 4" NO-HUB LEFT-HAND OFFSET FITTING WITH 2" NO-HUB VENT. ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST

CAP, PYLON FEET, PLATED HARDWARE AND NEOPRENE FIXTURE

CLOSET CARRIER SINGLE, LEFT HAND OFFSET AND 2" VENT

14404 **SERIES**

NOTES



JOSAM COMPANY

MICHIGAN CITY, INDIANA

JOSAM 14424 SERIES COATED CAST IRON SINGLE VERTICAL 4" NO-HUB RIGHT-HAND OFFSET FITTING WITH 2" NO-HUB VENT, ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET.


CLOSET CARRIER

SINGLE, RIGHT HAND OFFSET AND 2" VENT

NOTES

SERIES

14424



JOSAM COMPANY

MICHIGAN CITY, INDIANA

SPECIFICATION:

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.


JOSAM 14444 SERIES COATED CAST IRON 4" NO-HUB BACK-TO-BACK VERTICAL OFFSET FITTING WITH 2" NO-HUB VENT, AD JUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, PLATED HARDWARE AND NEOPREME FIXTURE GASKET.

CLOSET CARRIER

BACK-TO-BACK, VERTICAL 4" NO-HUB AND 2" VENT

SERIES 14444

NOTES



JOSAM COMPANY

MICHIGAN CITY, INDIANA

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.


JOSAM 1444 SERIES COATED CAST IRON SINGLE VERTICAL 4" NO-HUB SINGLE FITTING WITH 4" NO-HUB VENT A DIJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET.

CLOSET CARRIER

SINGLE CLOSE WITH 4" VENT

SERIES

14464



-SD	SPECIAL DUTY 500 LB CARRIER	П	-30	CAST IRON ADJ. EXT. W/ CONNECTOR
-VP	VANDAL-PROOF TRIM		-30-2	CAST IRON ADJ. EXT. W/ CONNECTOR & TEST CA
-1	POSITIONING FRAME		-45	THREADED LEFT-HAND AUXILIARY INLET
-6	SUPPLY PIPE SUPPORT (SPECIFY TYPE OF PIPE)		-46	THREADED RIGHT-HAND AUXILIARY INLET
-10	ABS EXTENSION THROUGH 10-1/2" WALL		-XSD	EXTRA SPECIAL DUTY 1,000 LB CARRIER
-24	CARRIER FOR FLOOR MOUNTED BACK OUTLET CHINA BOWLS			•

DATE OF LAST CHANGE: 04/22/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY
MICHIGAN CITY, INDIANA

NOTES

SPECIFICATION:


JOSAM 14484 SERIES COATED CAST IRON DOUBLE VERTICAL 4" NO-HUB BACK-TO-BACK VERTICAL FITTING WITH 4" NO-HUB VENT, ADJUSTABLE CARRIER BODY, FOR SIPHON JET ONLY, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, PI ATED HARDWARF AND NEOPERHE FIXTIJRE GASKET

CLOSET CARRIER

DOUBLE CLOSE WITH 4" VENT

SERIES

14484



ı	-SD	SPECIAL DUTY 500 LB CARRIER	-30	CAST IRON ADJ EXT W/ CONNECTOR
	-VP	VANDAL-PROOF TRIM	-30-2	CAST IRON ADJ. EXT. W/ CONN & TEST CA
	-1	POSITIONING FRAME	-45	THREADED LEFT-HAND AUXILIARY VENT
	-6	SUPPLY PIPE SUPPORT (SPECIFY TYPE OF PIPE)	-46	THREADED RIGHT-HAND AUXILIARY VENT
	-10	ABS EXTENSION THROUGH 10-1/2" WALL	-XSD	EXTRA SPECIAL DUTY 1,000 LB CARRIER
	-24	CARRIER FOR FLOOR MOUNTED BACK OUTLET CHINA BOWLS		

DATE OF LAST CHANGE: 4/23/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY
MICHIGAN CITY, INDIANA

5 1/2"

BOWL

FINISHED

WALL

STABILIZER

JOSAM 14504 SERIES COATED CAST IRON SINGLE VERTICAL 4" NO-HUB SINGLE FITTING WITH 2"NO-HUB VENT, ADJUSTABLE CARRIER BODY, INVERTIBLE FOR SIPHON JET OR BLOWOUT CLOSETS, WITH ABS EXTENSION WITH INTEGRAL TEST CAP, PYLON FEET, PLATED HARDWARE AND NEOPRENE FIXTURE GASKET.

FIXTURE


GASKET

CLOSET CARRIER

SINGLE CLOSE WITH 2" VENT

SERIES

14504




SECURED TO FLOOR WITH 1/2" BOLTS AND ANCHORS (BY OTHERS).

 ⊗ FOR SIPHON JET ROUGHING OVER 6" OR BLOWOUT ROUGHING OVER 12-1/2" SPECIFY ON ORDER.

SIPHON JET DIMS SHOWN. FOR BLOWOUT DIMS, USE:

MIN 11" & MAX 16 1/2"



EXTENSION

Γ	-SD	SPECIAL DUTY 500 LB CARRIER		-30	CAST IRON ADJ. EXT. W/ CONNECTOR
	-VP	VANDAL-PROOF TRIM		-30-2	CAST IRON ADJ. EXT. W/ CONNECTOR & TEST CAP
Γ	-1	POSITIONING FRAME		-45	THREADED LEFT-HAND AUXILIARY INLET
	-6	SUPPLY PIPE SUPPORT (SPECIFY TYPE OF PIPE)		-46	THREADED RIGHT-HAND AUXILIARY INLET
	-10	ABS EXTENSION THROUGH 10-1/2" WALL	Ш	-XSD	EXTRA SPECIAL DUTY 1,000 LB CARRIER
Γ	-24	CARRIER FOR FLOOR MOUNTED BACK OUTLET CHINA BOWLS	_	-	

DATE OF LAST CHANGE: 4/23/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA NOTES

SPECIFICATION:

-10

DATE OF LAST CHANGE:

IMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA

ABS EXTENSION THROUGH 10-1/2" WALL


CARRIER FOR FLOOR MOUNTED BACK OUTLET CHINA BOWLS

JOSAM 15964 SERIES COATED CAST IRON VERTICAL 4* NO-HUB DOUBLE WASTE 90* STACK FITTING WITH 4* BRANCHES, 2* NO-HUB VENT, WITH CLOSE CARRIERS INVERTIBLE FOR SIPHON JET OR BLOW-OUT CLOSETS, ABS EXTENSIONS WITH INTEGRAL TEST CAPS, BUTTRESS FEET, PLATED HARDWARE AND INTURE GASKET

CLOSET CARRIER

90° INSTITUTIONAL FITTING

SERIES 15964




-49


JOSAM COMPANY

MICHIGAN CITY, INDIANA

NO-HUB HIGH AUXILIARY INLET, UNDER VENT

THREADED HIGH AUXILIARY INLET, OPPOSITE VENT





OPTIONS:

-26	FITTING ANCHOR FEET
-49	NO-HUB HIGH AUXILIARY INLET, UNDER VENT
-54	THREADED HIGH AUXILIARY INLET, OPPOSITE VENT


DATE OF LAST CHANGE:	5/21/14
DIMENSIONS ARE SUBJECT TO MA TOLERANCES AND CHANGE WIT	HOUT NOTICE
WE CAN ASSUME NO RESPON USE OF SUPERSEDED OR V	

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTE

SPECIFICATION: JOSAM 16123 SERIES COATED CAST IRON SINGLE COMMERCIAL CLOSET CARRIER AND 3" PVC PLASTIC FITTING ADAPTER WITH EXTENSION AND CHROME PLATED TRIM.





ı			-6	SUPPLY PIPE SUPPORT (SPECIFY TYPE OF PIPE						
			-13 ABS EXTENSION							
	ı		-21	HANGER TYPE CLOSET ADAPTER						
L										


JOSAM RECOMMENDS FEET BE SECURED TO FLOOR WITH 1/2" BOLTS AND ANCHORS (BY OTHERS).

DATE OF LAST CHANGE: 4/23/15
DIMENSIONS ARE SUBJECT TO MANUFACTURES'
TOLERANCES AND CHANGE WITHOUT NOTICE
WILEGE OF SURFISSEDED OF ONE OF THE SURFISSED OF THE

CONCEALED TYPE LAVATORY CARRIER


- 1. Tandem keepers in slots on the arm permit positioning of leveling screws on the job to suit punchings of any lavatory specified.
- 2. Screws in keepers can then easily be moved up or down to level the lavatory.
- 3. The securing lock device is positioned on the arm and tightens against the fixture to hold it rigidly in place.
- 4. The sleeve can be adjusted to suit various wall thicknesses.


- 5. The final setting of the arm out from the wall can be made from the face of the finished wall after the wall is built.
- 6. The set screws are easily accessible for quicker adjustment.
- 7. Arm with the locking device, tandem keepers, and adjustable sleeve, is completely assembled at the factory.
- 8. Hardware is plated to prevent corrosion.



Parts & Details Lavatory, Sink & Urinal Carriers


The drawings on this page show the relationship between mating parts of carriers covered in this section.





(-66) OPTION, SPLIT HEADER FOR STAINLESS STEEL ARMS

In many cases arms are supplied by the manufacturers of stainless steel fixtures. The mounting hole spacing in the back of the arm (Y Dim.) varies widely by sink and manufacturer. The -66 split header is adjustable to allow for the mounting of this type of sink and arm combination.




(-75) OPTION, 2" ESCUTCHEONS


(-76) OPTION, 4" ESCUTCHEONS

Escutcheons provide manufacturers' specified distance from wall to back of a slab type lavatory to prevent water from deteriorating finished wall when concealed arms are used. Furnished in polished chrome.

(-77) OPTION, 6" ESCUTCHEONS also available.

Fixture Carriers 47






JOSAM 17100-BB SERIES FLOOR-MOUNTED BACK-TO-BACK LAVATORY CARRIER WITH CONCEALED ARMS, LEVELING AND SECURING SCREWS, STRUCTURAL UPRIGHTS AND WELDED FEET.

LAVATORY CARRIER

FLOOR-MOUNT CONCEALED ARM

17100-BB **SERIES**



JOSAM COMPANY

MICHIGAN CITY, INDIANA

SPECIFICATION:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.


WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM 17120 SERIES WALL-MOUNTED, SINGLE LAVATORY CARRIER WITH CONCEALED ARMS, LEVELING AND SECURING SCREWS, AND ADJUSTABLE WALL PLATE.

LAVATORY CARRIER

WALL-MOUNT CONCEALED ARM

17120 **SERIES**





MICHIGAN CITY, INDIANA

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

TOLERANCES AND CHANGE WITHOUT NOTICE.






JOSAM 17120-MMB SERIES WALL-MOUNTED, SINGLE LAVATORY CARRIER WITH CONCEALED ARMS, LEVELING AND SECURING SCREWS, AND MOVABLE MOUNTING BRACKETS FOR SECURING TO WALL PLATE BY OTHERS

LAVATORY CARRIER

WALL-MOUNT CONCEALED ARM

17120-MMB SERIES

NOTES



SPECIFICATION:


JOSAM 17120 SERIES WALL-MOUNTED, SINGLE LAVATORY CARRIER WITH CONCEALED ARMS, LEVELING AND SECURING SCREWS, AND ADJUSTABLE WALL PLATE


LAVATORY CARRIER


WALL-MOUNT CONCEALED ARM

17120-203-H SERIES










JOSAM 17380-BB SERIES FLOOR-MOUNTED, BACK-TO-BACK LAVATORY CARRIER WITH EXPOSED ACID-RESISTING WHITE COATED ARMS, LEVELING AND SECURING SCREWS, STRUCTURAL UPRIGHTS, WELDED FEET AND CHROME PLATED TRIM

LAVATORY CARRIER

FLOOR-MOUNT EXPOSED ARM

17380-BB **SERIES**



MICHIGAN CITY, INDIANA

SPECIFICATION:

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.

WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.


JOSAM 17380-HD SERIES FLOOR-MOUNTED, SINGLE HEAVY-DUY SINK CARRIER WITH EXPOSED ACID-RESISTING WHITE COATED ARMS. LEVELING AND SECURING SCREWS, STRUCTURAL UPRIGHTS, WELDED FEET AND CHROME PLATED TRIM.

SINK CARRIER

FLOOR-MOUNT EXPOSED ARM

17380-HD **SERIES**

NOTES



JOSAM COMPANY

MICHIGAN CITY, INDIANA

DIMENSIONS ARE SUBJECT TO MANUFACTURERS


TOLERANCES AND CHANGE WITHOUT NOTICE.

WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.


DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.

WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.



MICHIGAN CITY, INDIANA




JOSAM 17390 SERIES WALL-MOUNTED, SINGLE LAVATORY CARRIER WITH EXPOSED ACID-RESISTING WHITE COATED ARMS, LEVELING AND SECURING SCREWS, ADJUSTABLE WALL PLATE, BACK PLATES AND CHROME PLATED TRIM.

LAVATORY CARRIER

WALL-MOUNT EXPOSED ARM

17390-BP **SERIES**



SPECIFICATION: LAVATORY CARRIER JOSAM 17405 SERIES WALL-MOUNTED, SINGLE LAVATORY CARRIER WALL-MOUNT EXPOSED ARM WITH EXPOSED ACID-RESISTING WHITE COATED ARMS, LEVELING AND SECURING SCREWS, MOUNTING RODS FOR SECURING TO WALL PLATE BY OTHERS AND CHROME PLATED TRIM. 17405 **SERIES** PLATE FURNISHED Ø11/16" BY OTHERS 1 1/2" MIN ___ 1 1/4" 1 7/8" MAX 0 1 1/4" 1 1/2" FINISHED WALL $A \square$ FINISHED



-VP VANDAL-PROOF TRIM -10 STUDS FOR WALLS OVER 4" (SPECIFY WALL THICKNESS)

DATE OF LAST CHANGE: JOSAM COMPANY DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE

WHEN REQUIRED.

FINISHED FLOOR

NOTES

WALL

MANUFACTURER

NUMBER

SIZE

NAME

DIMENSIONS

RIM HEIGHT

BASED ON "A" DIM. SHOWN

WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA. MICHIGAN CITY, INDIANA

3 1/4"

USE OF SUPERSEDED OR VOID DATA

SPECIFICATION: LAVATORY CARRIER JOSAM 17550 SERIES FLOOR-MOUNTED, SINGLE LAVATORY CARRIER FLOOR-MOUNT HANGER PLATE WITH HANGER PLATE, ADJUSTABLE SUPPORTING RODS, STRUCTURAL UPRIGHTS AND WELDED FEET. 17550 **SERIES** REUSABLE ALIGNMENT TOOL AVAILABLE □ VARIABLE - DEPENDS ON FIXTURE EXCEPT WHEN STANDARD PLATE IS FURNISHED C = 18-1/4" 2 1/2" 1 MIN 4 MAX MANUFACTURER \$ 15 v 5. NUMBER HANGER SIZE FURNISHED -WITH FIXTURE NAME **FINISHED** В□ WALL DIMENSIONS

RECOMMEND ALL FEET BE SECURED TO FLOOR WITH 1/2" BOLTS AND ANCHORS BY OTHERS.

4 1/2"

-BB	BACK-TO-BACK CARRIER*		-WCBL	WATER COOLER BI-LEVEL CARRIER*
-CL	CORNER LAVATORY CARRIER*		-10	STUDS FOR WALLS OVER 4"
-UR	URINAL CARRIER*			(SPECIFY WALL THICKNESS)
-WC	WATER COOLER CARRIER*		-60	VALVE PLATE FOR ATTACHING TO UPRIGHT

*SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE

DATE OF LAST CHANGE: 8/11/2009
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

FINISHED

FLOOR

JOSAM COMPANY
MICHIGAN CITY, INDIANA

NOTES

RIM HEIGHT BASED ON "A" DIM SHOWN SPECIFICATION: LAVATORY CARRIER JOSAM 17550-BB SERIES FLOOR-MOUNTED, BACK-TO-BACK LAVATORY FLOOR-MOUNT HANGER PLATE CARRIER WITH HANGER PLATES, ADJUSTABLE SUPPORTING RODS. STRUCTURAL UPRIGHTS AND WELDED FEET. 17550-BB **SERIES** 2 1/2 -C 🗆 — 1 MIN 1 MIN 4 MAX 4 MAX HANGERS **FURNISHED** WITH В□ FIXTURE FINISHED -FINISHED WALL WALL -FINISHED FLOOR MANUFACTURER RECOMMEND ALL FEET BE SECURED TO FLOOR NUMBER WITH 1/2" BOLTS AND ANCHORS BY OTHERS. □ VARIABLE - DEPENDS ON FIXTURE SIZE EXCEPT WHEN STANDARD PLATE IS FURNISHED C = 18-1/4" NAME DIMENSIONS -BB BACK-TO-BACK CARRIER -10 STUDS FOR WALLS OVER 4" (SPECIFY WALL THICKNESS) RIM HEIGHT BASED ON "B" DIM SHOWN -60 VALVE PLATE FOR ATTACHING TO UPRIGHT

DATE OF LAST CHANGE: 3/27/12


DIMENSIONS ARE SUBJECT TO MANUFACTURERS


TOLERANCES AND CHANGE WITHOUT NOTICE.

WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED ON VOID DATA.

JOSAM COMPANY
MICHIGAN CITY. INDIANA






DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS


WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

TOLERANCES AND CHANGE WITHOUT NOTICE.



JOSAM COMPANY

MICHIGAN CITY, INDIANA




JOSAM 17560 SERIES FLOOR-MOUNTED, SINGLE LAVATORY CARRIER WITH HANGER & BEARING PLATE, ADJUSTABLE SUPPORTING RODS, STRUCTURAL UPRIGHTS, WELDED FEET AND CHROME PLATED TRIM

LAVATORY CARRIER

FLOOR-MOUNT BEARING PLATE

SERIES

17560



RECOMMEND ALL FEET BE SECURED TO FLOOR WITH 1/2" BOLTS AND ANCHORS BY OTHERS.

[-BB	BACK-TO-BACK CARRIER∆	-WCBL	
	-UR	URINAL CARRIER△	-10	
	-WC	WATER COOLER CARRIER∆	-10	
			-60	,

	-WCBL	WATER COOLER BI-LEVEL CARRIER*
	-10	STUDS FOR WALLS OVER 4" (SPECIFY WALL THICKNESS)
	-60	VALVE PLATE FOR ATTACHING TO UPRIGHT

NOTES

△SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA

SPECIFICATION:


JOSAM 17560-BB SERIES FLOOR-MOUNTED, BACK-TO-BACK LAVATORY CARRIER WITH HANGER PLATES, ADJUSTABLE SUPPORTING RODS, STRUCTURAL UPRIGHTS, WELDED FEET, AND CHROME PLATED TRIM

LAVATORY CARRIER

FLOOR-MOUNT HANGER PLATE


17560-BB **SERIES**

NOTES



JOSAM COMPANY

MICHIGAN CITY, INDIANA



FLOOR-MOUNT BEARING PLATE CARRIER WITH HANGER & BEARING PLATE, ADJUSTABLE SUPPORTING RODS, STRUCTURAL UPRIGHTS, WELDED FEET AND CHROME PLATED 17560-WC **SERIES** REUSABLE ALIGNMENT TOOL AVAILABLE □ VARIABLE - DEPENDS ON FIXTURE EXCEPT WHEN STANDARD PLATE IS FURNISHED C = 18-1/4" 2 1/2" 1 MIN 4 MAX HANGER FURNISHED-FINISHED WALL WITH FIXTURE, MANUFACTURER Η̈́ NUMBER SIZE ВП NAME Jo H DIMENSIONS ___ **BEARING** STUDS **FINISHED** -NOT FLOOR ATTACHED RIM HEIGHT TO FIXTURE BASED ON "A" DIM SHOWN -| 4 1/2" RECOMMEND ALL FEET BE SECURED TO FLOOR WITH 1/2" BOLTS AND ANCHORS BY OTHERS. lxII-wc WATER COOLER CARRIER STUDS FOR WALLS OVER 4" -10 (SPECIFY WALL THICKNESS) DATE OF LAST CHANGE: 11/10/2011 NOTES **JOSAM COMPANY** DIMENSIONS ARE SUBJECT TO MANUFACTURERS

MICHIGAN CITY, INDIANA

WATER COOLER CARRIER

SPECIFICATION:

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM 17560-WC SERIES FLOOR-MOUNTED, SINGLE WATER COOLER


JOSAM 17560-WCBL SERIES FLOOR-MOUNTED BI-LEVEL WATER COOLER CARRIER WITH HANGER AND BEARING PLATES. ADJUSTABLE SUPPORT RODS, STRUCTURAL UPRIGHTS, WELDED FEET, AND CHROME-PLATED TRIM.

WATER COOLER CARRIER

FLOOR-MOUNT BEARING PLATE


17560-WCBL SERIES


NOTES



LAVATORY CARRIER JOSAM 17590 SERIES WALL-MOUNTED, SINGLE LAVATORY CARRIER WITH HANGER PLATE AND ADJUSTABLE SUPPORTING RODS. WALL-MOUNT HANGER PLATE 17590 **SERIES** 7 MAX -FINISHED WALL MANUFACTURER HANGER(S) FURNISHED WITH FIXTURE -NUMBER SIZE 0 0 V�∕⊃∘ NAME 0 DIMENSIONS ВП ☐ VARIABLE - DEPENDS ON FIXTURE EXCEPT WHEN STANDARD PLATE IS FURNISHED C = 18-1/4" RIM HEIGHT BASED ON "B" DIM SHOWN FINISHED FLOOR -DP DOUBLE PLATE CARRIER△ -UR URINAL CARRIER △ STUDS FOR WALLS OVER 7" (SPECIFY WALL THICKNESS) △SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE DATE OF LAST CHANGE: NOTES

SPECIFICATION:






JOSAM 17590-DP SERIES WALL-MOUNTED, SINGLE URINAL CARRIER WITH HANGER PLATES AND ADJUSTABLE SUPPORTING

URINAL CARRIER

WALL-MOUNT HANGER PLATE

SERIES 17590-UR-DP

NOTES



JOSAM COMPANY

MICHIGAN CITY, INDIANA


SPECIFICATION:

JOSAM 17720 SERIES FLOOR-MOUNTED, SINGLE, HEAVY-DUTY SINK CARRIER WITH HANGER PLATE, ADJUSTABLE SUPPORTING RODS, ACID-RESISTING WHITE COATED ARMS, LEVELING AND SECURING SCREWS, STRUCTURAL UPRIGHTS, WELDED FEET AND CHROME PLATED TRIM.

SINK CARRIER

FLOOR-MOUNT HEAVY-DUTY

SERIES 17720



DATE OF LAST CHANGE: 4/23/15

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY
MICHIGAN CITY, INDIANA

NOTES

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA

SPECIFICATION: JOSAM 17720-66 SERIES FLOOR-MOUNTED, SINGLE, HEAVY-DUTY SINK


CARRIER WITH HANGER PLATE, ADJUSTABLE SUPPORTING RODS, BEARING STUDS, STRUCTURAL UPRIGHTS, WELDED FEET AND CHROME PLATED TRIM.

SINK CARRIER

FLOOR-MOUNT HEAVY-DUTY

SERIES

17720-66



DATE OF LAST CHANGE: 4/23/15	100111 00117111/	NOTES
DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA	JOSAM COMPANY MICHIGAN CITY, INDIANA	
USE OF SUPERSEDED OR VOID DATA.	/	

SPECIFICATION:


TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.

JOSAM 17730 SERIES FLOOR-MOUNTED, SINGLE, HEAVY-DUTY SINK CARRIER WITH SUPPORT PLATES, ADJUSTABLE COUPLING WITH 4" PIPING CONNECTION, MOUNTING STUDS, STRUCTURAL UPRIGHTS, WELDED FEET AND CHROME PLATED TRIM.

SINK CARRIER FLOOR-MOUNT HEAVY-DUTY

17730 **SERIES**




MICHIGAN CITY, INDIANA

JOSAM 17735 SERIES FLOOR-MOUNTED, SINGLE, HEAVY-DUTY SINK CARRIER WITH SUPPORT PLATES, ADJUSTABLE COUPLING WITH 4"X 2" WASTE FITTING, MOUNTING STUDS, STRUCTURAL UPRIGHTS, WELDED FEET AND CHROME PLATED TRIM.

SINK CARRIER

FLOOR-MOUNT HEAVY-DUTY

SERIES 17735



-4	VANDAL-PROOF TRIM
-10	STUDS FOR WALLS OVER 5-3/8" (SPEC. WALL THICKNESS)
-45	THREADED HIGH LEFT-HAND AUXILIARY VENT
-46	THREADED HIGH RIGHT-HAND AUXILIARY VENT


NOTE: OTHER FITTINGS AVAILABLE UPON REQUEST. CONTACT YOUR JOSAM REPRESENTATIVE

DATE OF LAST CHANGE: 4/23/15	100414 0014541114	NOTES
DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPPRSEDED OR VOID DATA	JOSAM COMPANY MICHIGAN CITY, INDIANA	

JOSAM SERIES 19800 ELASTOMERIC NEOPRENE GASKET CONFORMING TO ASTM-C564 STANDARD FOR WATER-TIGHT SEAL WITH PIPE IN JOSAM INSIDE CAULK OUTLETS (-X). GASKET JIFFE JOINT

SERIES

19800



TYPE NO.	DESIGNATION	FOR PI	Α	
TIPE NO.	DESIGNATION	MIN.	MAX.	A
19802	2" SW	2.125	2.390	1-1/2
19803	3" SW	3.125	3.390	1-3/4
19804	4" SW	4.125	4.390	2-1/4
19805	5" SW	5.210	5.390	2-1/2
19806	6" SW	6.210	6.390	2-5/8
19812	2" XH	2.290	2.470	1-1/2
19813	3" XH	3.410	3.590	1-3/4
19814	4" XH	4.410	4.590	2-1/4
19815	5" XH	5.410	5.590	2-1/2
19816	6" XH	6.410	6.590	2-5/8
19825	5" SP	5.550	5.700	2-1/2
19826	6" SP	6.550	6.700	2-5/8

DATE OF LAST CHANGE: 06/20/08

DIMENSIONS ARE SUBJECT TO MANUFACTURER: TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA

JOSAM COMPANY
MICHIGAN CITY, INDIANA

NOTE


Installing JOSAM Products Using the JIFFEE-JOINT Gasket.


- 1. Set drain body to the proper height over pipe.
- 2. Level and support in place.
- 3. After coating gasket and inside of drain with a gasket lubricant, slip gasket over pipe and press down as far as possible by hand.
- 4. Placing a caulking tool in groove at top of gasket, drive the gasket down flush with the pipe top no further. You have made a perfect joint.

	GASKET-PIPE TABLE								
	CAST	IRON		P	۷C				
TYPE NO.	SOII	. PIPE	NO	PLA	STIC	THIN		COPPER	
	XH	SW	HUB	ABS	PVC	WALL	STEEL	DWV	GLASS
19802		•				•		•	•
19803		•	•			•		•	
19804		•	•			•		•	
19805		•	•						
19806		•	•						
19812	•		•	•	•		•		•
19813	•			•	•		•		•
19814	•			•	•		•		•
19815	•								
19816	•								
19825				•	•		•		
19826				•	•		•		•


SW – Service Weight XH – Extra Heavy SP – Steel Pipe
These recommendations apply to pipe that conforms to ANSI, ASTM and other
applicable standards. JIFFEE-JOINT Gaskets are designed for use only with JOSAM
caulk outlet (-X) products.


(-2) DRAIN RECEIVER






(-CR) CLAMPING DRAIN RECEIVER






DRAIN RECEIVER DIMENSIONS						
SERIES NO. A B C D						
21500	24	15-1/2	14-9/16	21/64		
22010	20	12-1/4	11-1/2	21/64		
22080	16	9-1/2	7-1/2	47/64		

554111	APPLICABLE DRAIN RECEIVER							
DRAIN SERIES	OUTLET SIZE							
SEILLES	2" - 4"	5″	6"	8"	10"			
21500	21500	21500	21500	21500	21500			
	21500-CR	21500-CR	21500-CR	21500-CR	21500-CR			
22010	22010	22010	22010					
22080	22080							
23710	22010	22010	22010					
23730	22080							
23740	22080							
25500	21500 21500-CR	21500 21500-CR	21500 21500-CR	21500 21500-CR				
25520	22010	22010	22010					
25540	22080							
28600	21500 21500-CR	21500 21500-CR	21500 21500-CR	21500 21500-CR				




(-1) OPTION, DECK CLAMP

The deck clamp is the most dependable means by which the roof drain can be secured to the roof deck to insure a permanent bond that will prevent damage of flashing and membrane materials caused by movement and vibration. It is secured to the underside of the drain body with heavy-duty threaded rods, which provide adjustment to accommodate various slab or deck thicknesses, and is drawn tightly in place against the underside of the deck to form a positive union.




(-2) OPTION, DRAIN RECEIVER

The drain receiver is recommended for use in all roof drain installations regardless of deck construction and is of particular importance when used in conjunction with drains installed in decks where support is on insulation. The drain receiver is produced in heavy gauge steel, coated for protection, and embodies a recessed flange to carry the drain, and a wide flange to support the assembly on the roof. The drain receiver distributes the weight of the roof drain evenly over the deck and compensates for irregular and misaligned deck openings.




(-3C) OPTION, DRAIN RECEIVER & DRAIN RECEIVER CLIPS

Includes (-2) Optional Drain Receiver and clips, to secure the roof drain body directly to the receiver. Simply position the drain outlet face up, position drain receiver over the drain body and attach the four receiver clips with the hardware provided. Invert body and install the assembly into the deck opening. If necessary, secure assembly to the metal deck with self-tapping screws (by others).




(-10) OPTION, FIXED EXTENSION COLLAR USED WITH LEVELEZE® DRAINS

For roof or deck construction where base slab to surface height is greater than can be accommodated with the standard LEVELEZE® collar, the (-10) Fixed Extension Collar "A" is used along with the (-AE) LEVELEZE® assembly. These collars can be used in multiples where extension requirements dictate. The Fixed Extension Collar can be cast in increments of 1, 2, 3 and 4 inches. Shorter or longer dimensions are available by cutting or stacking extensions



(-VP) OPTION, VANDAL-PROOF SECURED DOME

Where vandalism or mischievous activity is anticipated, it is advisable to specify vandal-proof domes on roof drains. All JOSAM precision-molded plastic large domes incorporate bayonet locking devices as standard equipment; however, when specified vandal-proof, they are further secured with screws to insure permanence of assembly. Other types of domes can also be vandal-proofed when specified.




PIPE SIZE	Α	В	С
2	2-1/2	4-1/2	3-5/8
3	2-13/16	5	4-1/2
4	3-1/2	5-1/2	5-11/16
5	4-5/16	6-1/2	6-15/16
6	4-13/16	7	7-15/16

(-66) NO-HUB SIDE OUTLET

This option converts JOSAM bottom outlet inside caulk drains to no-hub side outlet drains using a 90° no-hub guarter bend and a JIFFEE-JOINT Gasket.

STANDARD ADJUSTABLE LEVELEZE ASSEMBLY (-AE)



INSTALLATION INSTRUCTIONS


- PLACE FLAT GASKET WITH HOLES ALIGNED ON DRAIN BODY
- SECURE SUPPORT RING ON TOP OF GASKET WITH 3/8" WASHER HEAD BOLTS.
 ATTACH WEJLOC CLAMP RING TO ADJUSTABLE COLLAR WITH 3/8" STUDS,
 SECURE CLAMP RING DOWN WITH 3/8" NUTS AND WASHERS

USING #21500 SEAL KIT 3 SEALING INSTRUCTIONS


- SURFACES MUST BE CLEAN AND DRY
- COMPLETELY FILL THE SEALANT WELL BETWEEN ADJUSTABLE EXTENSION AND THE SUPPORT RING TO FORM WATERPROOF SEAL.
 3.) SEALANT SKINS IN 5 MINUTES,
- DRIES TO TOUCH IN 1 HOUR CURES & BONDS IN 24 HOURS


FAILURE TO FOLLOW INSTRUCTIONS MAY RESULT IN LEAKAGE.


ADJUSTABLE LEVELEZE ASSEMBLY WITH OPTIONAL (-4) SECONDARY CLAMP RING





Roof Drains 71




























Replacement Parts

Josam introduced the first non-puncturing clamping device for roof drains in the 1920's. By casting lugs into the body and flat tabs onto the clamp ring, the membrane could be clamped between the drain body and clamp ring using the 410 Clamp Posts. The original design can be identified in the field by the use of these clamp posts to secure the body to the clamp ring. The 410 and 4110 Series replacement parts below are for use with these original drains. Please use these drawings to check dimensions carefully as replacement parts are not returnable.






JOSAM 21500-AE SERIES COATED CAST IRON LEVELEZE® ROOF DRAIN, LARGE POLYPROPYLENE LOCKING DOME, WEJLOC® NON-PUNCTURING CLAMP RING WITH INTEGRAL GRAVEL STOP, BOLTED SUPPORT RING, ADJUSTABLE TOP, LARGE SUMP WITH WIDE ROOF FLANGE AND BOTTOM OUTLET.

ROOF DRAIN

W/ LEVELEZE® ADJUSTABLE EXTENSION

21500-AE **SERIES**



		2"	PIPE SIZE						
	П	3"	PIPE SIZE						
	П	4"	PIPE SIZE						
		5"	PIPE SIZE	Δ					
		6"	PIPE SIZE						
		8"	PIPE SIZE	Δ					
	П	10"	PIPE SIZE (NO-HUB ONLY)						
	П								
	Х	-AE	THREADED LEVELEZE® ADJ. EXT.						
		-CR	CLAMPING DRAIN RECEIVER (MIN. DECK OPENING Ø16*)						
		-VP	SECURED DOME						
		-1	DECK CLAMP ASSEMBLY						
		-1C	DRAIN RECEIVER CLIPS (MIN. DECK OPENING Ø16")						
		-2	DRAIN RECEIVER						
		-3	DECK CLAMP ASY. AND DRAIN RECEIVER						
		-3C	DRAIN RECEIVER AND DRAIN RECEIVER CLIPS						
		-4	SECONDARY FLASHING CLAMP (-AE ONLY)						
Δ	SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE								

_							
	-6	EXTRA WIDE FLANGE DRAIN BODY (-X OUTLET ONLY)					
	-10	FIXED EXT. COLLAR, CAST IRON. 4" STD.(SPECIFY HEIGHT)					
	-10-20	FIXED EXT. COLLAR, GALVANIZED. 4" STD. (SPECIFY HEIGHT)					
_]د	-16*	INTERNAL WATERGUARD (2" THRU 6" OUTLETS ONLY)					
	-17*	2" HIGH SOLID CLAMPING COLLAR					
7	-19	CLAMP COLLAR W/PERF. STAINLESS GRAVEL GUARD					
Г	-20	GALVANIZED CAST IRON PARTS					
	-21	GALVANIZED CAST IRON DOME ONLY					
	-22	CAST IRON DOME					
	-23	ROUGH BRONZE DOME					
	-26	ALUMINUM DOME					
	-33	STAINLESS STEEL MESH-COVERED DOME					
	-66	NO-HUB SIDE OUTLET (2" THRU 6" OUTLETS ONLY)					
	-T	THREADED OUTLET					
	-X	INSIDE CAULK OUTLET					
	-Y	HUB OUTLET W/GASKET (2", 3" & 4" SIZES ONLY)					
	-Z	NO-HUB SPIGOT OUTLET					
* -16 & -17 CANNOT BE FURNISHED TOGETHER							

DATE OF LAST CHANGE: 5/04/15	
DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR	٠
USE OF SUPERSEDED OR VOID DATA.	ı

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION: **ROOF DRAIN**

JOSAM 21500-16 SERIES COATED CAST IRON ROOF DRAIN, INTERNAL WATERGUARD TYPE, LARGE POLYPROPYLENE LOCKING DOME, WEJLOCO NON-PUNCTURING CLAMP RING WITH INTEGRAL GRAVEL STOP, SECURED PLASTIC INTERNAL WATERGUARD FOR 3" WATER DEPTH, LARGE SUMP WITH WIDE ROOF FLANGE AND BOTTOM OUTLET.

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.

LARGE SUMP, INTERNAL WATERGUARD




	_	SEPAR	ATE SUBMITTAL FOR THIS OPTION AVAILABLE				** -10 EXTENSION 4" STANDARD
П	Ť	2"	PIPE SIZE			-3	DECK CLAMP ASY. AND DRAIN RECEIVER
П		3"	PIPE SIZE		П	-3C	DRAIN RECEIVER AND DRAIN RECEIVER CLIPS
		4"	PIPE SIZE		П	-4	SECONDARY FLASHING CLAMP (-AE ONLY)
П		5"	PIPE SIZE			-6	EXTRA WIDE FLANGE DRAIN BODY (-X OUTLET ONLY)
		6"	PIPE SIZE		П	-10	FIXED EXT. COLLAR, CAST IRON (SPECIFY HEIGHT **)
						-10-20	FIXED EXT. COLLAR, GALVANIZED (SPECIFY HEIGHT **)
				Х		-16	INTERNAL WATERGUARD (2" THRU 6" OUTLETS ONLY)
		-X	INSIDE CAULK OUTLET			-16GLV	GALV. STEEL INTERNAL WATERGUARD (2"-6" ONLY)
		-Y	HUB OUTLET W/GASKET (2", 3" & 4" SIZES ONLY)			-19	CLAMP COLLAR W/PERF. STAINLESS GRAVEL GUARD
		-Z	NO-HUB SPIGOT OUTLET			-20	GALVANIZED CAST IRON PARTS
П		-T	THREADED OUTLET			-21	GALVANIZED CAST IRON DOME ONLY
П					П	-22	CAST IRON DOME
П		-AE	THREADED LEVELEZE ® ADJ. EXT.			-23	ROUGH BRONZE DOME
П		-AER	ADJ. EXT. USING THREADED RODS		П	-26	ALUMINUM DOME
П		-IRMA	PERFORATED STAINLESS STEEL EXT.		П	-33	STAINLESS STEEL MESH-COVERED DOME
П	₹	-CR	CLAMPING DRAIN RECEIVER (MIN. DECK OPENING Ø16")			-66	NO-HUB SIDE OUTLET (2" THRU 6" OUTLETS ONLY)
П					П		
П		-1	DECK CLAMP ASY.		П	-VP	VANDAL-PROOF DOME
П		-1C	DRAIN RECEIVER CLIPS (MIN. DECK OPENING Ø16")				
		-2	DRAIN RECEIVER				
			AST CHANGE: 5/04/15	_	_		NOTES
DIN	DATE OF LAST CHANGE: 5/09/15 JOSAM COMPANY NOTES						

MICHIGAN CITY, INDIANA

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.



JOSAM COMPANY

MICHIGAN CITY, INDIANA

EXTENSION RODS, AND BOTTOM OUTLET. 21500-AER **SERIES** 4" MAX FOR MORE DRAIN DIMENSIONS, SEE 21500 DRAWING Ø16" MIN DECK **OPENING** OPTIONS: -IRMA PEFORATED SS EXTENSION 24" SQ. CLAMPING DRAIN RECEIVER -6 EXTRA WIDE FLANGE DRAIN BODY (-X OUTLET ONLY) -16* INTERNAL WATERGUARD (2" - 6" ONLY) -17* 2" HIGH SOLID CLAMPING COLLAR PIPE SIZE -19 CLAMP COLLAR W/ PERF SS GRAVEL GUARD 2" -20 GALVANIZED CAST IRON PARTS **OUTLET TYPES:** -21 GALVANIZED CAST IRON DOME ONLY 3" 4" THREADED -22 CAST IRON DOME -23 BOLIGH BRONZE DOME 5" -X INSIDE CAULK 6" -26 ALUMINUM DOME HUB WITH GASKET -Y (2", 3", 4" ONLY) -33 SS MESH-COVERED DOME 8" 10" 🗆 NO-HUB -VP VANDAL-PROOF DOME □ 10" AVAILABLE IN NO-HUB ONLY * -16 AND -17 CANNOT BE FURNISHED TOGETHER DATE OF LAST CHANGE: NOTES JOSAM COMPANY DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA

ROOF DRAIN

ADJUSTABLE EXTENSION RODS

SPECIFICATION:

USE OF SUPERSEDED OR VOID DATA.

JOSAM 21500-AER SERIES COATED CAST IRON ROOF DRAIN, LARGE POLYPROPYLENE LOCKING DOME, WEJLOC NON-PUNCTURING

CLAMP RING, LARGE SUMP, DRAIN RECEIVER WITH ADJUSTABLE

SPECIFICATION: JOSAM 21500-19 SERIE


JOSAM 21503-19 SERIES COATED CAST IRON ROOF DRAIN, LARGE POLYPROPYLENE LOCKING DOME, WELLOC ONNO. PINOTURING CLAMP RING WITH INTEGRAL GRAVEL STOP AND STAINLESS PERFORATED GRAVEL GUARD, LARGE SUMP WITH WIDE ROOF FLANGE AND BOTTOM OUTLET.

ROOF DRAIN

LARGE SUMP, STAINLESS GRAVEL GUARD

SERIES 21

21500-19



	NO III	*-16 & -17 CAN	E FURN	ISHED TOGETHER ** -10 EXTENSION 4" STANDARD	
	2"	PIPE SIZE		-3	DECK CLAMP ASY. AND DRAIN RECEIVER
	3"	PIPE SIZE		-3C	DRAIN RECEIVER AND DRAIN RECEIVER CLIPS
	4"	PIPE SIZE		-6	EXTRA WIDE FLANGE DRAIN BODY (-X OUTLET ONLY)
	5"	PIPE SIZE		-10	FIXED EXT. COLLAR, CAST IRON (SPECIFY HEIGHT **)
	6"	PIPE SIZE		-10-20	FIXED EXT. COLLAR, GALVANIZED (SPECIFY HEIGHT **)
	8"	PIPE SIZE		-16*	INTERNAL WATERGUARD (2" THRU 6" OUTLETS ONLY)
	10"	PIPE SIZE (AVAILABLE IN NO-HUB ONLY)		-17*	2" HIGH SOLID CLAMPING COLLAR
			Х	-19	CLAMP COLLAR W/PERF. STAINLESS GRAVEL GUARD
	-X	INSIDE CAULK OUTLET		-20	GALVANIZED CAST IRON PARTS
	-Y	HUB OUTLET W/GASKET (2", 3" & 4" SIZES ONLY)		-21	GALVANIZED CAST IRON DOME ONLY
	-Z	NO-HUB SPIGOT OUTLET		-22	CAST IRON DOME
	-T	THREADED OUTLET		-23	ROUGH BRONZE DOME
				-26	ALUMINUM DOME
	-AE	THREADED LEVELEZE @ADJ. EXT.		-33	STAINLESS STEEL MESH-COVERED DOME
	-AER	ADJUSTABLE EXT. USING THREADED RODS		-66	NO-HUB SIDE OUTLET (2" THRU 6" OUTLETS ONLY)
	-IRMA	PERFORATED STAINLESS STEEL EXT.			-
	-CR	CLAMPING DRAIN RECEIVER (MIN. DECK OPENING Ø16")		-VP	VANDAL-PROOF DOME
	-1	DECK CLAMP ASY.			
П	-1C	DRAIN RECEIVER CLIPS (MIN. DECK OPENING Ø16")			
	-2	DRAIN RECEIVER			

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

DATE OF LAST CHANGE: 5/04/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE:
WE CAN ASSUME NO RESPONSIBILITY FOR

DECK CLAMP ASSEMBLY

USE OF SUPERSEDED OR VOID DATA.

DRAIN RECEIVER CLIPS (MIN. DECK OPENING Ø16")

SPECIFICATION:

■ "A" DIM. - SPECIFY DIM. ON ORDER

● THIS DIMENSION IS 5 3/4" ON

JOSAM 21500-IRMA SERIES COATED CAST IRON ROOF DRAIN, LARGE

CLAMP RING WITH INTEGRAL GRAVEL STOP, LARGE SUMP WITH WIDE ROOF FLANGE AND BOTTOM OUTLET.

POLYPROPYLENE LOCKINGDOME, DOME SUPPORT RING, PERFORATED STAINLESS STEEL EXTENSION FILTER, WEJLOC® NON-PUNCTURING

JOSAM COMPANY MICHIGAN CITY, INDIANA


-VP VANDAL-PROOF DOME

NOTES

ROOF DRAIN

WITH PERF. STAINLESS EXTENSION

SERIES 21500-IRMA



Ø15 1/4 -

DATE OF LAST CHANGE:

IMENSIONS ARE SUBJECT TO MANUFACTURERS


TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR

JOSAM 21500-IRMA-6 SERIES COATED CAST IRON ROOF DRAIN, LARGE POLYPROPYLENE LOCKING DOME, DOME SUPPORTING RING, PERFORATED STAINLESS STEEL EXTENSION FILTER, WEJLOC® NON-PUNCTURING CLAMP RING WITH INTEGRAL GRAVEL STOP. LARGE SUMP WITH EXTRA-WIDE ROOF FLANGE AND BOTTOM OUTLET INSIDE CAULK

ROOF DRAIN

WITH PERF. STAINLESS EXTENSION

SERIES 21500-IRMA-6



ш	3"	PIPE SIZE	-19	CLAMP COLLAR W/PERF. STAINLESS GRAVEL GUARD
	4"	PIPE SIZE	-20	GALVANIZED CAST IRON PARTS
П	5"	PIPE SIZE	-21	GALVANIZED CAST IRON DOME ONLY
	6"	PIPE SIZE	-22	CAST IRON DOME
			-23	ROUGH BRONZE DOME
x	-x	INSIDE CAULK OUTLET	-26	ALUMINUM DOME
			-33	STAINLESS STEEL MESH-COVERED DOME
х	-IRMA	PERFORATED STAINLESS STEEL EXTENSION	-66	NO-HUB SIDE OUTLET
	-1	DECK CLAMP ASSEMBLY	-VP	VANDAL-PROOF DOME
X	-6	EXTRA WIDE FLANGE DRAIN BODY		
	-10	FIXED EXT. COLLAR, CAST IRON (SPECIFY HEIGHT **)		
	-10-20	FIXED EXT. COLLAR, GALVANIZED (SPECIFY HEIGHT **)		
П	-16*	INTERNAL WATERGUARD		

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA


NOTES

SPECIFICATION:

JOSAM 22010 SERIESCOATED CAST IRON ROOF DRAIN, MEDIUM BEEHIVE DOME, NON-PUNCTURING CLAMP RING WITH INTEGRAL GRAVEL STOP, MEDIUM SUMP WITH ROOF FLANGHE AND BOTTOM OUTLET.

ROOF DRAIN MEDIUM SUMP. BEEHIVE DOME

22010 **SERIES**



▼ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE

** -10 EXTENSION 1" STANDARD

	2"	PIPE SIZE		-10	FIXED EXT. COLLAR, CAST IRON (SPECIFY HEIGHT **)
	3"	PIPE SIZE		-10-20	FIXED EXT. COLLAR, GALVANIZED (SPECIFY HEIGHT **)
	4"	PIPE SIZE	•	-17	2" HIGH SOLID CLAMPING COLLAR
	5"	PIPE SIZE	Ŧ	-19	CLAMP COLLAR W/PERF. STAINLESS GRAVEL GUARD
	6"	PIPE SIZE		-20	GALVANIZED CAST IRON PARTS
П				-23	ROUGH BRONZE DOME
	-X	INSIDE CAULK OUTLET		-66	NO-HUB SIDE OUTLET (2" THRU 6" OUTLETS ONLY)
	-Z	NO-HUB SPIGOT OUTLET			
	-T	THREADED OUTLET		-VP	VANDAL-PROOF DOME
	-1	DECK CLAMP ASSEMBLY			
	-1C	DRAIN RECEIVER CLIPS (MIN. DECK OPENING Ø16.5")			
	-2	DRAIN RECEIVER			
	-3	DECK CLAMP ASY. AND DRAIN RECEIVER			
	-3C	DRAIN RECEIVER AND DRAIN RECEIVER CLIPS			
0.41	TE 0	E 1 1 0 T 0 1 1 1 1 0 E 0 1 1 1 E			LIGHTEG

DATE OF LAST CHANGE: 5/04/15 **JOSAM COMPANY** DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA USE OF SUPERSEDED OR VOID DATA.


JOSAM 22010-17 SERIES COATED CAST IRON ROOF DRAIN, MEDIUM BEEHIVE DOME, NON-PUNCTURING CLAMP RING WITH INTEGRAL GRAVEL STOP, MEDIUM SUMP WITH ROOF FLANGE AND BOTTOM OUTLET.

ROOF DRAIN

MEDIUM SUMP, BEEHIVE DOME

SERIES

22010-17



SPECIFICATION: **ROOF DRAIN** JOSAM 22010-19 SERIES COATED CAST IRON ROOF DRAIN, MEDIUM BEEHIVE DOME, NON-PUNCTURING CLAMP RING WITH INTEGRAL GRAVEL STOP AND MEDIUM SUMP, BEEHIVE DOME, STAINLESS GRAVEL GUARD STAINLESS PERFORATED GRAVEL GUARD, MEDIUM SUMP WITH ROOF FLANGE AND BOTTOM OUTLET. 22010-19 **SERIES** STAINLESS STEEL PERFORATED GRAVEL GUARD DOME FREE AREA WITH 1/4" OPENINGS -56 SQ. IN. 5 1/4 FLASHING CLAMP DEVICE AND GRAVEL STOP Ø8 3/8 0 MIN 3 1/2 MAX -X = "E" -Z = 5 5/8 -T = "D" DECK PIPE SIZE "D" DIM. "E" DIN 6 1/4" PIPE SIZE 4 1/2" 6 1/4" 5* 6" 4 3/8" Ø10 1/2 MIN. DECK OPENING 4" 5 3/4" ** -10 EXTENSION 1" STANDARD * "K" DIM. SPECIFY ON ORDER - MAX. 4" 2" PIPE SIZE -10 FIXED EXT. COLLAR, CAST IRON (SPECIFY HEIGHT **) 3" PIPE SIZE -10-20 FIXED EXT. COLLAR, GALVANIZED (SPECIFY HEIGHT **) 4" PIPE SIZE 2" HIGH SOLID CLAMPING COLLAR 5" PIPE SIZE -19 CLAMP COLLAR WITH PERF. STAINLESS GRAVEL GUARD 6" PIPE SIZE GALVANIZED CAST IRON PARTS -21 GALVANIZED CAST IRON DOME ONLY -X INSIDE CAULK OUTLET -23 ROUGH BRONZE DOME -Z NO-HUB SPIGOT OUTLET -66 NO-HUB SIDE OUTLET (2" THRU 6" OUTLETS ONLY) -T THREADED OUTLET VANDAL-PROOF DOME -1 DECK CLAMP ASSEMBLY -1C DRAIN RECEIVER CLIPS (MIN. DECK OPENING Ø16.5") DRAIN RECEIVER DECK CLAMP ASY. AND DRAIN RECEIVER -3C DRAIN RECEIVER AND DRAIN RECEIVER CLIPS DATE OF LAST CHANGE: NOTES

JOSAM COMPANY

MICHIGAN CITY, INDIANA

IMENSIONS ARE SUBJECT TO MANUFACTURERS.

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR

TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA


SPECIFICATION: JOSAM 22080 SERIES COATED CAST IRON ROOF DRAIN, REFHIVE DOME

JOSAM 22080 SERIES COATED CAST IRON ROOF DRAIN, BEEHIVE DOME, WEJLOC® NON-PUNCTURING CLAMP RING WITH INTEGRAL GRAVEL STOP, SMALL SUMP WITH ROOF FLANGE AND BOTTOM OUTLET.


ROOF DRAIN SMALL SUMP, HIGH DOME

SERIES

22080



MICHIGAN CITY, INDIANA



JOSAM COMPANY

MICHIGAN CITY, INDIANA

NOTES

DATE OF LAST CHANGE

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.

WE CAN ASSUME NO RESPONSIBILITY FOR


JOSAM SERIES 22080-05 COMBINATION ROOF DRAIN AND OVERFLOW. CONSISTS OF SMALL SUMP ROOF DRAIN WITH CAST IRON BEEHIVE DOME, SMALL SUMP OVERFLOW DRAIN WITH CAST IRON BEEHIVE DOME, SOLID WATER DAM AND ONE PIECE GALVANIZED STEEL DRAIN RECEIVER.

ROOF DRAIN

PRIMARY & OVERFLOW COMBINATION

SERIES

22080-Q5



MICHIGAN CITY, INDIANA

SPECIFICATION:

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR


USE OF SUPERSEDED OR VOID DATA.

JOSAM 22100 SERIES COATED CAST IRON COMBINATION ROOF DRAIN AND OVERFLOW DRAIN WITH CAST IRON DOMES, WEJLOC NON-PUNCTURING CLAMP RINGS WITH INTEGRAL GRAVEL STOPS, INTEGRAL CAST IRON STANDPIPE IN CAST IRON DECK FLANGE AND DUAL NO-HUB BOTTOM OUTLETS.

ROOF DRAIN


CONBINATION DRAIN/OVERFLOW


SERIES **22100**



MICHIGAN CITY, INDIANA

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.






JOSAM 23500 SERIES COATED CAST IRON ROOF DRAIN, SQUARE PEDESTRIAN GRATE SET IN SQUARE FRAME, WEJLOC® NON-PUNCTURING FLASHING COLLAR WITH WEEPHOLES FOR 2" ROOF FILL, LARGE SUMP WITH WIDE ROOF FLANGE AND BOTTOM OUTLET.

ROOF DRAIN LARGE SUMP

23500 **SERIES**

NOTES



l ▼	SE	PARAT	'E SUBMITTAL FOR THIS OPTION AVAILABLE		** -10 EXTENSION 4" STANDARD	
П		2"	PIPE SIZE		-1C	DRAIN RECEIVER CLIPS (MIN. DECK OPENING Ø 16")
		3"	PIPE SIZE		-2	DRAIN RECEIVER
		4"	PIPE SIZE		-3	DECK CLAMP ASY. AND DRAIN RECEIVER
		5"	PIPE SIZE		-3C	DRAIN RECEIVER AND DRAIN RECEIVER CLIPS
		6"	PIPE SIZE		-4	SECONDARY FLASHING CLAMP (-AE ONLY)
		8"	PIPE SIZE	₹	-6	EXTRA WIDE FLANGE DRAIN BODY (-X OUTLET ONLY)
		10"	PIPE SIZE (AVAILABLE IN NO-HUB ONLY)		-10	FIXED EXT. COLLAR, CAST IRON (SPECIFY HEIGHT **)
					-10-20	FIXED EXT. COLLAR, GALVANIZED (SPECIFY HEIGHT **)
		-T	THREADED OUTLET	₹	-18	EXTRA-DEEP SUMP
		-X	INSIDE CAULK OUTLET		-20	GALVANIZED CAST IRON PARTS
П		-Y	HUB OUTLET W/GASKET (2", 3", & 4" SIZES ONLY)		-36	DUCTILE IRON GRATE
П		-Z	NO-HUB SPIGOT OUTLET		-37-50	HVY-DUTY DUCTILE UNDERGRATE LAMINATED TOP, NIKALOY
					-37-51	HVY-DUTY DUCTILE UNDERGRATE LAMINATED TOP, BRONZE
	▼	-AE	THREADED LEVELEZE® ADJ. EXT.		-50	CAST IRON UNDERGRATE LAMINATED TOP, NIKALOY
LT	▼	-IRMA	PERFORATED STAINLESS STEEL EXTENSION		-51	CAST IRON UNDERGRATE LAMINATED TOP, BRONZE
П		-CR	CLAMPING DRAIN RECEIVER (MIN. DECK OPENING Ø 16")		-66	NO-HUB SIDE OUTLET (2" THRU 6" OUTLETS ONLY)
		-PG	PARKING GRATE - 110 SQ. IN. F.A. (DUCTILE IRON ONLY)			
		-1	DECK CLAMP ASSEMBLY		-VP	SECURED GRATE, VANDAL-PROOF SCREWS

JOSAM COMPANY

MICHIGAN CITY, INDIANA


SPECIFICATION:

JOSAM 23500-6 SERIES COATED CAST IRON ROOF DRAIN, SQUARE PEDESTRIAN GRATE IN SQUARE SECURED FRAME, WEJLOC® NON-PUNCTURING FLASHING COLLAR WITH WEEPHOLES FOR 2" ROOF FILL, LARGE SUMP WITH EXTRA-WIDE ROOF FLANGE AND BOTTOM OUTLET.

ROOF DRAIN

EXTRA-DEEP SUMP, EXTRA-WIDE FLANGE

23500-6 **SERIES**



▼ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE

** -10 EXTENSION 4" STANDARD

П		2"	PIPE SIZE - INSIDE CAULK OUTLET			
-		3"	PIPE SIZE - INSIDE CAULK OUTLET		-10	FIXED EXTENSION COLLAR, CAST IRON (SPECIFY HEIGHT **)
- [4"	PIPE SIZE - INSIDE CAULK OUTLET		-10-20	FIXED EXTENSION COLLAR, GALVANIZED (SPECIFY HEIGHT **)
- [5"	PIPE SIZE - INSIDE CAULK OUTLET			
-1	Т	6"	PIPE SIZE - INSIDE CAULK OUTLET	Г	-20	GALVANIZED CAST IRON PARTS
- [8"	PIPE SIZE - NO-HUB OUTLET		-36	DUCTILE IRON GRATE
		10"	PIPE SIZE - NO-HUB OUTLET		-37-50	HVY-DUTY DUCTILE UNDERGRATE LAMINATED TOP, NIKALOY
- [-37-51	HVY-DUTY DUCTILE UNCERGRATE LAMINATED TOP, BRONZE
- [-50	CAST IRON UNDERGRATE LAMINATED TOP, NIKALOY
- [1	-AE	THREADED LEVELEZE® ADJ. EXT.	Г	-51	CAST IRON UNDERGRATE LAMINATED TOP, BRONZE
- [1	-IRM	PERFORATED STAINLESS STEEL EXTENSION		-66	NO-HUB SIDE OUTLET (2" THRU 6" OUTLETS ONLY)
-1		-PG	PARKING GRATE - 110 SQ. IN. F. A. (DUCTILE IRON ONLY)			
- [-1	DECK CLAMP ASSEMBLY		-VP	SECURED GRATE, VANDAL-PROOF SCREWS
	x١	-6	EXTRA WIDE FLANGE DRAIN BODY			

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS. TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

DATE OF LAST CHANGE: 5/04/15

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

SPECIFICATION: **ROOF DRAIN** JOSAM 23500-AE SERIES COATED CAST IRON LEVELEZE® ROOF WITH LEVELEZE® ADJUSTABLE EXTENSION DRAIN, SQUARE PEDESTRIAN GRATE SET IN SQUARE SECURED FRAME, WEJLOC® NON-PUNCTURING FLASHING COLLAR WITH WEEPHOLES FOR 2" ROOF FILL, BOLTED SUPPORT RING, ADJUSTABLE TOP, LARGE SUMP WITH WIDE ROOF FLANGE AND BOTTOM OUTLET. 23500-AE SERIES SLOT WIDTH 5/16" (-50 & -51 SLOT WIDTH 1/4") FORMERLY 23000 SERIES Ø15-1/4 14 SQUARE 13-1/4 SQUARE RIM-GRATE FREE AREA 63.4 SQ. IN. WEEP HOLES 2" ⊠ ADJUSTABLE COLLAR △1-1/2 MIN BOLTED SUPPORT 4 MAX RING & GASKET X = 5-3/8MIN 1" $O_{Y}^{\wedge} = 4-7/8$ MAX 4-3/4" Z = 5-1/8 $O_{T=3-3/4}^{2}$ DECK CLAMP (-1) APPLY SEALANT HERE -AFTER FINAL -PIPE SIZE -ØADD 1/4" WHEN FURNISHED PIPE SIZE ADJUSTMENT W/ NIKALOY OR BRONZE TOP 13-1/4 MINIMUM △WITH (-4) CLAMP RING 3" -DECK OPENING -MIN 2-1/4" 4" MAX 4-1/4" Ø 18" 5" **GASKET ON -Y CONNECTION** 6" CONFORMS WITH ASTM-C564 8" O THIS DIMENSION IS 5-3/4 10" 🗆 ON 8" THREADED OUTLET □ 10" AVAILABLE IN NO-HUB ONLY ** -10 EXTENSIONS 4" STANDARD X .AE THREADED LEVELEZE ADJ. EXT. -18 EXTRA-DEEP SUMP

	-CR	CLAMPING DRAIN RECEIVER (MIN. DECK OPENING Ø16")	-20	GALVANIZED CAST IRON PARTS
П	-IRMA	PERFORATED STAINLESS STEEL EXTENSION	-36	DUCTILE IRON GRATE
	-PG	PARKING GRATE - 110 SQ. IN. F. A. (DUCTILE IRON ONLY)	-37-50	HVY-DUTY DUCTILE UNDERGRATE LAMINATED TOP, NIK
П	-1	DECK CLAMP ASSEMBLY	-37-51	HVYDUTY DUCTILE UNDERGRATE LAMINATED TOP, BRZ
	-1C	DRAIN RECEIVER CLIPS (MIN. DECK OPENING Ø16")	-50	CAST IRON UNDERGRATE LAMINTED TOP, NIKALOY
	-2	DRAIN RECEIVER	-51	CAST IRON UNDERGRATE LAMINTED TOP, BRONZE
П	-3	DECK CLAMP ASSEMBLY AND DRAIN RECEIVER	-VP	SECURED GRATE, VANDAL-PROOF SCREWS
	-3C	DRAIN RECEIVER AND DRAIN RECEIVER CLIPS	-66	NO-HUB SIDE OUTLET (2" THRU 6" OUTLETS ONLY)
П	-4	SECONDARY FLASHING CLAMP	-T	THREADED OUTLET
П	-6	EXTRA WIDE FLANGE DRAIN BODY (-X OUTLET ONLY)	-X	INSIDE CAULK OUTLET
	-10	FIXED EXTENSION COLLAR, CAST IRON (SPECIFY HEIGHT**)	-Y	HUB OUTLET W/ GASKET (2", 3" & 4" SIZES ONLY)
T	-10-20	FIXED EXTENSION COLLAR, GALVANIZED (SPECIFY HEIGHT**)	-Z	NO-HUB SPIGOT OUTLET

DATE OF LAST CHANGE: 4/23/15

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.

WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY
MICHIGAN CITY, INDIANA


NOTES

SPECIFICATION:

JOSAM 23500-18 SERIES COATED CAST IRON ROOF DRAIN, SQUARE PEDESTRIAN GRATE SET IN SQUARE SECURED FRAME, WELLOC® NON-PUNCTURING FLASHING COLLAR WITH WEEPHOLES FOR 2° ROOF FILL, DEEP SUMP WITH WIDE ROOF FLANGE AND BOTTOM OUT!

ROOF DRAIN EXTRA-DEEP SUMP

SERIES 23500-18



SLOT WIDTH 5/16" (-50 & -51 SLOT WIDTH 1/4")

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.

** -10 EXTENSION 4" STANDARD

ı	2"	PIPE SIZE		-2	DRAIN RECEIVER			
Г	3"	PIPE SIZE		-3	DECK CLAMP ASY. AND DRAIN RECEIVER			
Г	4"	PIPE SIZE		-3C	DRAIN RECEIVER AND DRAIN RECEIVER CLIPS			
L	5"	PIPE SIZE		-4	SECONDARY FLASHNING CLAMP (-AE ONLY)			
L	6"	PIPE SIZE		-10	FIXED EXT. COLLAR, CAST IRON (SPECIFY HEIGHT **)			
L				-10-20	FIXED EXT. COLLAR, GALVANIZED (SPECIFY HEIGHT **)			
L	-x	INSIDE CAULK OUTLET	X	-18	EXTRA-DEEP SUMP			
L	-z	NO-HUB SPIGOT OUTLET		-36	DUCTILE IRON GRATE (CAST IRON TOP ONLY)			
L				-37-50	HVY-DUTY DUCTILE UNDERGRATE LAMINATED TOP, NIKALOY			
Г	-AE	THREADED LEVELEZE ADJ. EXT.		-37-51	HVY-DUTY DUCTILE UNDERGRATE LAMINATED TOP, BRONZE			
L	-IRMA	PERFORATED STAINLESS STEEL EXTENSION		-50	CAST IRON UNDERGRATE LAMINATED TOP, NIKALOY			
Г	-CR	CLAMPING DRAIN RECEIVER (MIN. DECK OPENING Ø 16")		-51	CAST IRON UNDERGRATE LAMINATED TOP, BRONZE			
Г	-PG	PARKING GRATE - 110 SQ. IN. FREE AREA		-66	NO-HUB SIDE OUTLET (2" THRU 6" OUTLETS ONLY)			
Г								
I	-1	DECK CLAMP ASSEMBLY		-VP	SECURED GRATE, VANDAL-PROOF SCREWS			
Ĺ	-1C	DRAIN RECEIVER CLIPS (MIN. DECK OPENING Ø 16")						
[DATE OF LAST CHANGE: 5/04/15 NOTES							

JOSAM COMPANY


MICHIGAN CITY, INDIANA

JOSAM 2550-IRMA SERIES COATED CAST IRON ROOF DRAIN, SQUARE PEDESTRIAN GRATE SET IN SQUARE SECURED FRAME, FRAME SUPPORT COLLAR, PERFORATED STAINLESS STEEL EXTENSION FILTER, WELLOC 9 NON-PUNCTURING FLASHING COLLAR, LARGE SUMP WITH WIDE ROOF FLANGE AND BOTTOM OUTLET.

ROOF DRAIN

W/PERFORATED STAINLESS EXTENSION

SERIES 23500-IRMA



	•	SLIF	INVALE SOBMITTALT ON THIS OF HON AVAILABLE			- 10 EXTENSION 4 STANDARD
Г	Т	2"	PIPE SIZE	Т	-1	DECK CLAMP ASY.
Г	Т	3"	PIPE SIZE	Т	-10	DRAIN RECEIVER CLIPS (MIN. DECK OPENING Ø 16")
Г	Т	4"	PIPE SIZE	T	-2	DRAIN RECEIVER
Г	Т	5"	PIPE SIZE	Т	-3	DECK CLAMP ASY. AND DRAIN RECEIVER
Г	Γ	6"	PIPE SIZE		-30	DRAIN RECEIVER AND DRAIN RECEIVER CLIPS
Г	Т	8"	PIPE SIZE	1	-6	EXTRA WIDE FLANGE DRAIN BODY (-X OUTLET ONLY)
Г	Г	10"	PIPE SIZE (AVAILABLE IN NO-HUB ONLY)	Т	-10	FIXED EXT. COLLAR, CAST IRON (SPECIFY HEIGHT **)
L					-10-	PIXED EXT. COLLAR, GALVANIZED (SPECIFY HEIGHT **)
Г	Т	-X	INSIDE CAULK OUTLET	Т	-18	B EXTRA-DEEP SUMP
L		-Y	HUB OUTLET W/GASKET (2", 3" & 4" SIZES ONLY)		-20	GALVANIZED CAST IRON PARTS
Г	Τ	-Z	NO-HUB SPIGOT OUTLET	Т	-36	DUCTILE IRON GRATE
Г	Γ	-T	THREADED OUTLET	T	-37-	50 HVY-DUTY DUCTILE UNDERGRATE LAMINATED TOP, NIKALOY
L					-37-	51 HVY-DUTY DUCTILE UNDERGRATE LAMINATED TOP, BRONZE
L	Γ	-AE	THREADED LEVELEZE® ADJ. EXT.	Т	-50	CAST IRON UNDERGRATE LAMINATED TOP, NIKALOY
Þ	(-IRMA	PERFORATED STAINLESS STEEL EXTENSION		-5	CAST IRON UNDERGRATE LAMINATED TOP, BRONZE
Г	Т	-CR	CLAMPING DRAIN RECEIVER (MIN. DECK OPENING Ø 16")	Т	-66	NO-HUB SIDE OUTLET (2" THRU 6" OUTLETS ONLY)
		-PG	PARKING GRATE - 110 SQ. IN. F. A. (DUCTILE IRON ONLY)			
Г	Т			T	-VI	SECURED GRATE, VANDAL-PROOF SCREWS

JOSAM COMPANY

MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:

JOSAM 23500-IRMA-6 SERIES COATED CAST IRON ROOF DRAIN, SQUARE PEDESTRIAN GRATE SET IN SQUARE SECURED FRAME, FRAME SUPPORT COLLAR, PERPORATED STAINLESS STEEL EXTENSION FILTER, WEJ.OC® NON-PUNCTURING FLASHING COLLAR LARGE SUMP WITH EXTRA-WIDE ROOF FLANGE AND BOTTOM OUTLET.

ROOF DRAIN

W/PERFORATED STAINLESS EXTENSION

SERIES 23500-IRMA-6



-	2	2"	PIPE SIZE		-2	DRAIN RECEIVER
	1 3	3"	PIPE SIZE		-3	DECK CLAMP ASY. AND DRAIN RECEIVER
-	1 4	4"	PIPE SIZE	П	-3C	DRAIN RECEIVER AND DRAIN RECEIVER CLIPS
- 1	1 :	5"	PIPE SIZE	Х	-6	EXTRA WIDE FLANGE DRAIN BODY (-X OUTLET ONLY)
	-	6"	PIPE SIZE	П	-10	FIXED EXT. COLLAR, CAST IRON (SPECIFY HEIGHT **)
П					-10-20	FIXED EXT. COLLAR, GALVANIZED (SPECIFY HEIGHT **)
	x -	-X	INSIDE CAULK OUTLET	П	-37-50	HVY-DUTY DUCTILE UNDERGRATE LAMINATED TOP, NIKALO
-	ᅦ			П	-37-51	HVY-DUTY DUCTILE UNDERGRATE LAMINATED TOP, BRONZE
	-/	AE	THREADED LEVELEZE ADJ. EXT.		-50	CAST IRON UNDERGRATE LAMINATED TOP, NIKALOY
	K -IR	RMA	PERFORATED STAINLESS STEEL EXT.	П	-51	CAST IRON UNDERGRATE LAMINATED TOP, BRONZE
	-0	CR	CLAMPING DRAIN RECEIVER (MIN. DECK OPENING ϕ 16")	П	-66	NO-HUB SIDE OUTLET (2" THRU 6" OUTLETS ONLY)
П	-F	PG	PARKING GRATE - 110 SQ. IN. F. A. (DUCTILE IRON ONLY)	П	-36	DUCTILE IRON GRATE
-				П	-VP	SECURED GRATE, VANDAL-PROOF SCREWS
	-	-1	DECK CLAMP ASY.			
	-1	1C	DRAIN RECEIVER CLIPS (MIN. DECK OPENING Ø 16")	П		

DATE OF LAST CHANGE: 4/23/15


DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.



SPECIFICATION: **ROOF DRAIN** JOSAM 23710 SERIES COATED CAST IRON ROOF DRAIN, ROUND PEDESTRIAN MEDIUM SUMP, PROMENADE TOP GRATE SET IN SQUARE SECURED FRAME, NON-PUNCTURING FLASHING COLLAR WITH WEEPHOLES FOR ROOF FILL. MEDIUM SUMP WITH WIDE ROOF FLANGE AND BOTTOM OUTLET 23710 **SERIES** THIS DRAIN IS COMPLIANT WITH THE SLOT WIDTH 1/4 ANSI/ASME STANDARD A112.6.3-2001 FOR HEEL-RESISTANT STRAINERS AND THE MAXIMUM GRATE SLOT SIZE BE 5/16" (8mm) GRATE FREE AREA 22.8 SQ. IN. Ø 12 11 3/8 SQUARE Ø 10 0 MIN 3 1/2 MAX -X = "D" -Z = 55/8-T = "F" DECK CLAMP PIPE SIZE Ø 10 1/2 MIN. DECK OPENING ** -12 EXTENSION 1" STANDARD 2" PIPE SIZE [DIM "D" = 4 3/4", DIM "E" = 6 1/4"] -1 DECK CLAMP ASY 3" PIPE SIZE [DIM "D" = 4 3/4", DIM "E" = 6 1/4"] -1C DRAIN RECEIVER CLIPS (MIN. DECK OPENING Ø 13.75") 4" PIPE SIZE [DIM "D" = 4 1/2", DIM "E" = 6 1/4"] -2 DRAIN RECEIVER 5" PIPE SIZE [DIM "D" = 4 3/8", DIM "E" = 6" 1 -3 DECK CLAMP ASY, AND DRAIN RECEIVER DRAIN RECEIVER AND DRAIN RECEIVER CLIPS 6" PIPE SIZE [DIM "D" = 4", DIM "E" = 5 3/4"] -3C EXTENSION FLASHING COLLAR, CAST IRON (SPECIFY HEIGHT **) -12 -X INSIDE CAULK OUTLET -20 GALVANIZED CAST IRON PARTS -Z NO-HUB SPIGOT OUTLET -50 SATIN FINISH NIKALOY TOP -T THREADED OUTLET -51 SATIN FINISH BRONZE TOP -66 NO-HUB SIDE OUTLET SECURED GRATE, VANDAL-PROOF SCREWS DATE OF LAST CHANGE:

JOSAM COMPANY

MICHIGAN CITY, INDIANA


DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

JOSAM 23710-IRMA SERIES COATED CAST IRON ROOF DRAIN, ROUND PEDESTRIAN GRATE SET IN SQUARE SECURED FRAME, NON-PUNCTURING FLASHING COLLAR WITH WEEPHOLES FOR ROOF FILL, MEDIUM SUMP WITH WIDE ROOF FLANGE, BOTTOM OUTLET, AND PERFORATED IRMA EXTENSION.

ROOF DRAIN

MEDIUM SUMP, PROMENADE TOP WITH SS PERF EXTENSION

SERIES 23710-IRMA



ш	-	PIPE SIZE [DIM D = 43/4, DIM E = 6 1/4]		-1	DECK CLAMP AST.
	3"	PIPE SIZE [DIM "D" = 4 3/4", DIM "E" = 6 1/4"]		-1C	DRAIN RECEIVER CLIPS (MIN. DECK OPENING Ø 13.75")
П	4"	PIPE SIZE [DIM "D" = 4 1/2", DIM "E" = 6 1/4"]		-2	DRAIN RECEIVER
	5"	PIPE SIZE [DIM "D" = 4 3/8", DIM "E" = 6"]		-3	DECK CLAMP ASY. AND DRAIN RECEIVER
П	6"	PIPE SIZE [DIM "D" = 4", DIM "E" = 5 3/4"]		-3C	DRAIN RECEIVER AND DRAIN RECEIVER CLIPS
				-12	EXTENSION FLASHING COLLAR, CAST IRON (SPECIFY HEIGHT **)
П	-X	INSIDE CAULK OUTLET		-20	GALVANIZED CAST IRON PARTS
П	-Z	NO-HUB SPIGOT OUTLET		-50	SATIN FINISH NIKALOY TOP
П	-T	THREADED OUTLET		-51	SATIN FINISH BRONZE TOP
П				-66	NO-HUB SIDE OUTLET
П					
П			П	-VP	SECURED GRATE, VANDAL-PROOF SCREWS

JOSAM COMPANY MICHIGAN CITY, INDIANA

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

SPECIFICATION:


FLANGE AND BOTTOM OUTLET.

ROOF DRAIN

SMALL SUMP, PROMENADE TOP

SERIES

23730



*-TSO BODY CANNOT BE USED WITH DRAIN RECEIVER (-2, -3 & -3C)

JOSAM 23730 SERIES COATED CAST IRON ROOF DRAIN, ROUND PEDESTRIAN GRATE SET IN SQUARE SECURED FRAME, NON-PUNCTURING FLASHING

COLLAR WITH WEEPHOLES FOR 2" ROOF FILL, SMALL SUMP WITH WIDE ROOF

** -12 EXTENSION 1" STANDARD

	2"	PIPE SIZE		-1C	DRAIN RECEIVER CLIPS (MIN. DECK OPENING Ø10.5")
	3"	PIPE SIZE		-2	DRAIN RECEIVER
	4"	PIPE SIZE		-3	DECK CLAMP ASSEMBLY AND DRAIN RECEIVER
				-3C	DRAIN RECEIVER AND DRAIN RECEIVER CLIPS
	-T	THREADED OUTLET		-12	EXTENSION FLASHING COLLAR, CAST IRON (SPECIFY HEIGHT **)
	-X	INSIDE CAULK OUTLET		-12-20	EXTENSION FLASHING COLLAR, GALVANIZED (SPECIFY HEIGHT **)
П	-Y	HUB OUTLET WITH GASKET		-20	GALVANIZED CAST IRON PARTS
	-Z	NO-HUB SPIGOT OUTLET		-50	SATIN FINISH NIKALOY TOP
	-81	BUCKET		-50TP	PRIMER TAP
	-TSO*	THREADED SIDE OUTLET		-51	SATIN FINISH BRONZE TOP
	-1	DECK CLAMP ASSEMBLY		-VP	SECURED GRATE, VANDAL-PROOF SCREWS
DA	TE OF LA	ST CHANGE: 11/06/14	\equiv		NOTES

JOSAM COMPANY MICHIGAN CITY, INDIANA NOTES

DATE OF LAST CHANGE:

IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

JOSAM SERIES 23730-IRMA COATED CAST IRON ROOF DRAIN, ROUND PEDESTRIAN GRATE SET IN SQUARE FRAME, PERFORATED STAINLESS STEEL EXTENSION FILTER, WEJLOC® NON-PUNCTURING FLASHING COLLAR WITH WEEP HOLES, SMALL SUMP WITH WIDE ROOF FLANGE AND BOTTOM OUTLET.

ROOF DRAINS


SERIES 23730-IRMA

CONFORMS WITH ASTM - C564

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

SLOT WIDTH 1/4" MEETS ADA AND HEEL-PROOF REQUIREMENTS



JOSAM COMPANY

MICHIGAN CITY, INDIANA


ROOF FILL, S

SPECIFICATION:

JOSAM 23740 SERIES COATED CAST IRON ROOF DRAIN, SQUARE HEAVY-DUTD DUCTLE ROON UNDERGRATE WITH NIKALOY TOP SET IN SQUARE SECURED FRAME, NON-PUNCTURING FLASHING COLLAR WITH WEEPHOLES FOR 2" ROOF FILL SMALL SUMP WITH WIDE ROOF FLANGE AND BOTTOM OUTLET. ROOF DRAIN

HEAVY-DUTY, PROMAENADE TOP

SERIES 23740



DATE OF LAST CHANGE: 5/04/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TO LERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

HUB OUTLET WITH GASKET

TSO* DECK CLAMP ASSEMBLY AND DRAIN RECEIVER

NO-HUB SPIGOT OUTLET

-Z

JOSAM COMPANY MICHIGAN CITY, INDIANA

-51

SATIN FINISH BRONZE TOP

SECURED GRATE, VANDAL-PROOF SCREWS


NOTES

JOSAM SERIES 24020 COATED CAST IRON SUPER-FLO $\,$ ROOF DRAIN, ROUND MEDIUM-DUTY ANTI-TILTING GRATE WITH PERIMETER $\,$ DRAINAGE SLOTS, SET IN ROUND NON-PUNCTURING MEMBRANE CLAMP RING, MEDIUM SUMP WITH WIDE DECK FLANGE AND BOTTOM INSIDE CAULK OUTLET CONNECTION.

ROOF DRAIN COMPOSITION DECK

24020 SERIES

NOTES



JOSAM COMPANY

MICHIGAN CITY, INDIANA

SPECIFICATION: **ROOF DRAIN** JOSAM SERIES 24030 COATED CAST IRON SUPER-FLO® ROOF DRAIN, ROUND MEDIUM-DUTY ANTI-TILTING GRATE WITH PERIMETER SLOTS, COMPOSITION DECK SET IN ROUND NON-PUNCTURING MEMBRANE CLAMP RING, LARGE SUMP WITH WIDE DECK FLANGE AND BOTTOM INSIDE CAULK OUTLET CONNECTION. 24030 **SERIES** SLOT WIDTH 9/16 (-50 & -51 SLOT WIDTH 7/16) Ø20" GRATE FREE AREA 61 SQ. IN. * ADD 1/4" WHEN FURNISHED WITH NIKALOY OR BRASS TOP MEMBRANE -Ø 12 3/4" *3/16" CLAMP RING Ø11 13/16' 6 11/16" 3-1/2" MIN. DECK 7-1/2" MAX -CLAMP PIPE (-1) SIZE Ø 15" MIN. DECK OPENING − Ø18" 4" PIPE SIZE -31 CHAIN ANCHORED GRATE PIPE SIZE DUCTILE IRON GRATE (CAST IRON TOP ONLY) PIPE SIZE SATIN FINISH NIKALOY TOP PIPE SIZE SATIN FINISH BRONZE TOP HEEL-PROOF GRATE, CI, 5/16" SLOT WIDTH, 25 SQ. IN FREE AREA DECK CLAMP ASSEMBLY SECURED GRATE GALVANIZED CAST IRON PARTS SEDIMENT BUCKET, CAST IRON INSIDE CAULK OUTLET SEDIMENT BUCKET, GALVANIZED DATE OF LAST CHANGE: NOTES **JOSAM COMPANY** DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR

MICHIGAN CITY, INDIANA

USE OF SUPERSEDED OR VOID DATA

DATE OF LAST CHANGE: 12/23/14


IMENSIONS ARE SUBJECT TO MANUFACTURERS


TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR



ROOF DRAIN COMPOSITION DECK

SERIES **24040**






JOSAM SERIES 24060 COATED CAST IRON ROOF DRAIN, ROUND SPECIAL-DUTY GRATE, LARGE SUMP WITH WIDE DECK FLANGE AND BOTTOM INSIDE CAULK OUTLET CONNECTION.

ROOF DRAIN

COMPOSITION DECK

24060



SPECIFICATION:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR


USE OF SUPERSEDED OR VOID DATA

JOSAM SERIES 24200 COATED CAST IRON ADJUSTABLE "ALL-LEVEL" DRAIN, ROUND PEDESTRIAN GRATE SET IN ROUND ANCHORED FRAME LEVELED ON ADJUSTABLE THREADED RODS, REMOVABLE PERFORATED STAINLESS STEEL FILTER, CONCRETE FORMING AND RETAINING RING, CAST IRON NON-PUNCTURING CLAMP RING, LARGE SUMP WITH WIDE FLANGE AND BOTTOM OUTLET INSIDE-

DRAIN


PROMENADE TOP WIDE FLANGE

24200



JOSAM COMPANY

MICHIGAN CITY, INDIANA



NOTES

	•	-27	HIGH DOME							
								-VP	SECURED DOM	1E
DA	TE C	F LAST (CHANGE:	5/04/15	100411	_	_			N
				ANUFACTURERS	JOSAM	C	U	MP	ANY	ı
			CHANGE WIT E NO RESPON	HOUT NOTICE.	MICHIGAN	CI.	ΓV	INDIA	NΙΛ	ı
			RSEDED OR V		IVIICITIGAN	OI.	и,	IINDIA	11//	1

SPECIFICATION: **ROOF DRAIN** JOSAM SERIES 24500-27 COATED CAST IRON SILL DRAIN, SECURED TALL BRONZE DOME, BRONZE CLAMP RING AND SHALLOW SUMP SILL TYPE WITH TALL DOME WITH FLASHING FLANGE AND BOTTOM THREADED OUTLET CONNECTION. 24500-27 **SERIES** 3 5/8 -DOMÉ FREE AREA 24 SQ. IN. - Ø3 5/8 · DOME FREE AREA 24 SQ. IN. 4-1/2 4-1/2 PIPE SIZE NPT MINIMUM -DECK OPENING-→ ØPIPE SIZE NPT → TYP (2) PLCS 2" & 3" THREADED OUTLET MINIMUM DECK OPENING 4" THREADED OUTLET 2" PIPE SIZE -20 GALVANIZED CAST IRON PARTS 3" PIPE SIZE -24 ROUGH NIKALOY DOME PIPE SIZE -33 STAINLESS STEEL MESH COVERED DOME -45 BODY WITH 45° THREADED OUTLET MODEL DIM. "L' -90 BODY WITH 90 * THREADED OUTLET 24502-27 2 24503-27 2 -VP VANDAL-RESISTANT DOME 24504-27 4 DATE OF LAST CHANGE: NOTES **JOSAM COMPANY** DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA


JOSAM SERIES 24500-35 COATED CAST IRON SILL DRAIN, SECURED GRATE, BRONZE CLAMP RING & SHALLOW SUMP WITH FLASHING FLANGE AND BOTTOM THREADED OUTLET CONNECTION.

ROOF DRAIN

SILL TYPE WITH BRONZE GRATE

SERIES

24500-35



MICHIGAN CITY, INDIANA


SPECIFICATION:

JOSAM SERIES 24500-45 SERIES COATED CAST IRON SILL DRAIN, SECURED BRONZE DOME, BRONZE CLAMP RING AND SHALLOW SUMP WITH FLASHING FLANGE AND 45° SIDE THREADED OUTLET CONNECTION.

ROOF DRAIN

SILL TYPE WITH BRONZE DOME

24500-45 **SERIES**



MODEL NO.	DIA. "B"	DIA. "C"	DIM. "D"	DIM. "E"	DIM. "F"	DIM. "H"	DOME FREE AREA
24502-45	3-3/4	6	1-1/2	4-1/2	2-3/4	1-1/2	4.4 SQ. IN.
24503-45	4-3/4	7-1/4	1-1/2	4-3/4	2-3/4	1-7/8	7.3 SQ. IN.
24504-45	4-3/4	7-1/4	2-3/8	5-5/8	2-1/8	1-7/8	7.3 SQ. IN.
24304-43	4-3/4	7-114	2-3/0	3-3/0	2-1/0	1-770	7.5 50. 114.

Г	2"	PIPE SIZE	-33	STAINLESS STEEL MESH COVERED DOME
Ш	3"	PIPE SIZE	-35	FLAT GRATE (SLOT WIDTH 3/16")
П	4"	PIPE SIZE	-45	BOLTED FLASHING CLAMP DEVICE
Е			-50	SATIN FINISH NIKALOY TOP
П	-20	GALVANIZED CAST IRON PARTS	-51	SATIN FINISH BRONZE TOP
Е	-24	ROUGH NIKALOY DOME		
Г	-27	TALL DOME	-VP	VANDAL-RESISTANT DOME

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

IMENSIONS ARE SUBJECT TO MANUFACTURERS.

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

SPECIFICATION:


JOSAM SERIES 24500-90 COATED CAST IRON SILL DRAIN, SECURED LOW BRONZE DOME, BRONZE CLAMP RING AND SHALLOW SUMP WITH FLASHING FLANGE AND SIDE THREADED OUTLET CONNECTION.

ROOF DRAIN

SILL TYPE WITH BRONZE DOME

SERIES

24500-90



PIPE SIZE	Ø "B"	Ø"C"	DIM. "D"	DIM. "E"	DIM. "F"	DIM. "H"	FREE AREA
2"	3-3/4	6	2-1/2	4	2-3/4	1-1/2	4.4 SQ. IN.
3"	4-3/4	7-1/4	3	5	3-1/2	1-7/8	7.3 SQ. IN.
4"	4-3/4	7-1/4	3-1/2	6	3-1/2	1-7/8	7.3 SQ. IN.

Х	-90	THREADED OUTLET BODY	-35	FLAT GRATE (3/16" SLOT WIDTH)
	-20	GALVANIZED CAST IRON PARTS	-50	SATIN FINISH NIKALOY TOP
П	-24	ROUGH NIKALOY DOME	-51	SATIN FINISH BRONZE TOP
	-27	TALL DOME		
	-33	STAINLESS STEEL MESH COVERED DOME	-VP	VANDAL-RESISTANT DOME

DATE OF LA	ST CHANG	E: 5/04/15
		O MANUFACTURER
		WITHOUT NOTICE.
		PONSIBILITY FOR
USE OF S	UPERSEDED (OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:

JOSAM 24700 SERIES COATED CAST IRON PARAPET TYPE ROOF DRAIN, REMOVABLE SLOPING BRONZE GRATE, FLASHING CLAMP, SHALLOW SUMP WITH FLASHING FLANGE AND SIDE OUTLET THREADED CONNECTION.

ROOF DRAIN

PARAPET TYPE, SLOPING GRATE

SERIES **24700**



PIPE SIZE	B x B1	C x C1	D	E	F	G x G1	H x H1	J	κ	L x L1	GRATE FREE AREA
2"	4-1/2 x 11	6-1/2 x 11	1-1/2	6-3/8	5-5/8	3 x 5-1/8	4-1/8 x 5-1/4	7-3/8	1-1/4	3-1/4 x 5-1/4	19.5 SQ. IN.
3"	4-1/2 x 11	6-1/2 x 11	2-1/8	6-3/8	5-5/8	3 x 5-1/8	4-1/8 x 5-1/4	7-3/8	1-1/4	3-1/4 x 5-1/4	19.5 SQ. IN.
4"	4-1/2 x 11	6-1/2 x 11	2-5/8	6-3/8	5-5/8	3 x 5-1/8	4-1/8 x 5-1/4	7-3/8	1-1/4	3-1/4 x 5-1/4	19.5 SQ. IN.
5"	5-1/2 x 13	7-1/2 x 13	3-1/2	8-1/8	6-5/8	4 x 6-1/8	5 x 7-1/2	10-3/4	1-3/4	4-1/4 x 7-1/2	34.3 SQ. IN.
6"	5-1/2 x 13	7-1/2 x 13	3-1/2	8-1/8	6-5/8	4 x 6-1/8	5 x 7-1/2	10-3/4	1-3/4	4-1/4 x 7-1/2	34.3 SQ. IN.

	2"	PIPE SIZE	-22	CAST IRON GRATE		
	3"	PIPE SIZE	-24	ROUGH NIKALOY GRATI	Ē	
	4"	PIPE SIZE	-45	BODY WITH 45* THREADED OUTLET		
	5"	PIPE SIZE	-50	SATIN FINISH NIKALOY	GRATE	
	6"	PIPE SIZE	-51	SATIN FINISH BRONZE GRATE		
			-61	DOWNSPOUT ELBOW (CAST IRON)	
	-20	GALVANIZED CAST IRON PARTS	-61-20	DOWNSPOUT ELBOW (GALVANIZED)		
DA	TE OF LA	CT CHANCE, 04/45/45			NOTES	

DATE OF LAST CHANGE: 04/15/15

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY
MICHIGAN CITY, INDIANA

NOTES


JOSAM 24700-45 SERIES COATED CAST IRON PARAPET TYPE ROOF DRAIN, REMOVABLE SLOPING BRONZE GRATE, FLASHING CLAMP, SHALLOW SUMP WITH FLASHING AND 45° SIDE OUTLET THREADED CONNECTION.

ROOF DRAIN

PARAPET TYPE, SLOPING GRATE

24700-45 SERIES

NOTES



PIPE SIZE	B x B1	C x C1	D	E	AREA
2"	4-1/2 x 11	6-1/2 x 11	2-1/4	3-7/8	19.5 SQ. IN.
3"	4-1/2 x 11	6-1/2 x 11	2-5/8	4-1/4	19.5 SQ. IN.
4"	4-1/2 x 11	6-1/2 x 11	3	4-5/8	19.5 SQ. IN.
5"	5-1/2 x 13	7-1/2 x 13	3-1/2	5	34.3 SQ. IN.
6"	5-1/2 x 13	7-1/2 x 13	3-5/8	5-1/2	34.3 SQ. IN.

	2"	PIPE SIZE		-22	CAST IRON GRATE
	3"	PIPE SIZE		-24	ROUGH NIKALOY GRATE
П	4"	PIPE SIZE	x	-45	BODY WITH 45° THREADED OUTLET
	5"	PIPE SIZE		-50	SATIN FINISH NIKALOY GRATE
П	6"	PIPE SIZE		-51	SATIN FINISH BRONZE GRATE
				-61	DOWNSPOUT ELBOW (CAST IRON)
	-20	GALVANIZED CAST IRON PARTS		-61-20	DOWNSPOUT ELBOW (GALVANIZED)

JOSAM COMPANY

MICHIGAN CITY, INDIANA


SPECIFICATION:

JOSAM 24720 SERIES COATED CAST IRON PARAPET TYPE ROOF DRAIN, SECURED ANGLE GRATE WITH FLASHING CLAMP, SHALLOW SUMP WITH FLASHING FLANGE AND SIDE OUTLET THREADED CONNECTION.

ROOF DRAIN

PARAPET TYPE, ANGLE GRATE

24720 **SERIES**



П		2"	4-1/2	11	6-1/2	1-1/2	6-3/8	5-5/8	3	5-1/8	4-1/8	5-1/4	7-3/8	1-1/4	3-1/4	5-1/4	25.9	
П		3"	4-1/2	11	6-1/2	2-1/8	6-3/8	5-5/8	3	5-1/8	4-1/8	5-1/4	7-3/8	1-1/4	3-1/4	5-1/4	25.9	
П		4"	4-1/2	11	6-1/2	2-5/8	6-3/8	5-5/8	3	5-1/8	4-1/8	5-1/4	7-3/8	1-1/4	3-1/4	5-1/4	25.9	
П		5"	5-1/2	13	7-1/2	3-1/2	8-1/8	6-5/8	4	6-1/8	5	7-1/2	10-3/4	1-3/4	4-1/4	7-1/2	41.3	
П		6"	5-1/2	13	7-1/2	3-1/2	8-1/8	6-5/8	4	6-1/8	5	7-1/2	10-3/4	1-3/4	4-1/4	7-1/2	41.3	
ш																		
Г	-45 BODY WITH 45° THREADED OUTLET ∆ -50 SATIN FINISH NIKALOY GRATE											ATE						

	-20	GALVANIZED CAST IRON PARTS	
	-23	ROUGH BRONZE GRATE	
	-24	ROUGH NIKALOY GRATE	
^	SEDA	PATE SUBMITTAL FOR THIS OPTION AVAILABLE	

	-51	SATIN FINISH BRONZE GRATE
	-61	DOWNSPOUT ELBOW (CAST IRON)
1	-61-20	DOWNSPOUT ELBOW (GALVANIZED)
	-VP	VANDAL-PROOF GRATE

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

DATE OF LAST CHANGE:

IMENSIONS ARE SUBJECT TO MANUFACTURERS


TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

SPECIFICATION: **ROOF DRAIN**

JOSAM 24720-45 SERIES COATED CAST IRON PARAPET TYPE ROOF DRAIN, SECURED ANGLE GRATE WITH FLASHING CLAMP, SHALLOW SUMP WITH FLASHING FLANGE AND 45° SIDE OUTLET THREADED

PARAPET TYPE, ANGLE GRATE

24720-45 **SERIES**



	PIPE SIZE	A	В	С	D	E	GRATE FREE AREA
	2"	4 1/2	11	6 1/2	2 1/4	3 7/8	25.9
	3"	4 1/2	11	6 1/2	2 5/8	4 1/4	25.9
Г	4"	4 1/2	11	6 1/2	3	4 5/8	25.9
	5"	5 1/2	13	7 1/2	3 1/2	5	41.3
	6"	5 1/2	13	7 1/2	3 5/8	5 1/2	41.3

X		BODY WITH 45* THREADED OUTLET
	-20	GALVANIZED CAST IRON PARTS
	-23	ROUGH BRONZE GRATE
П	-24	ROUGH NIKALOY GRATE

-50	SATIN FINISH NIKALOY GRATE
-51	SATIN FINISH BRONZE GRATE
-61	DOWNSPOUT ELBOW (CAST IRON)
-61-20	DOWNSPOUT ELBOW (GALVANIZED)
-VP	VANDAL-PROOF GRATE

DATE OF	LAST C	HANGE	: 4/23	V15
DIMENSION	IS ARE SU	BJECT TO	MANUFAC	TURERS
TOLERAN	CES AND	CHANGE	1 TUOHTIW	NOTICE.
			ONSIBILITY	
USE (OF SUPER	SEDED O	R VOID DA	TA.


JOSAM COMPANY MICHIGAN CITY, INDIANA


SPECIFICATION:

JOSAM 24900 SERIES COATED CAST IRON PARAPET TYPE ROOF DRAIN, SECURED BRONZE DOME WITH INTEGRAL FLASHING CLAMP, FLASHING FLANGE AND SIDE OUTLET THREADED CONNECTION.

ROOF DRAIN ANGLE PARAPET TYPE

24900 **SERIES**





MICHIGAN CITY, INDIANA

SPECIFICATION:


JOSAM 25010-T SERIES COATED CAST BRONZE DOWNSPOUT NOZZLE, LOOSE WALL FLANGE AND INLET THREADED CONNECTION.

ROOF DRAIN DOWNSPOUT NOZZLE

25010-T **SERIES**

П	TYPE	PIPE SIZE	В	С	D
	25012-T	2"*	4	3 3/8	6
	25013-T	3"	4	3 3/8	6
	25014-T	4"	5	3 7/8	7
	25015-T	5"*	7 1/2	4 7/8	9
	25016-T	6"	7 1/2	4 7/8	9
	25018-T	8"	9 5/8	5 7/8	11
	25019-T	10"	11 1/4	6 3/4	12 3/4





3 1/2	2 5/8 —	_ 5/8
		-
		DIDE
		PIPE ØB
LOOSE WALL FLANGE	 1	/2

-24	ROUGH NIKALOY (NICKEL-BRONZE)
-51	SATIN FINISH BRONZE
-BS	BIRD SCREEN
-PVC	CONNECTS TO PVC PIPE
-Z	NO-HUB OUTLET

*FOR 2" SIZE. FURNISHED WITH 3" BODY WITH 3" X 2" FOR 5" SIZE, FURNISHED WITH 6" BODY WITH 6" X 5"

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS. TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

SPECIFICATION:


JOSAM 25010-Z SERIES COATED CAST BRONZE DOWNSPOUT NOZZLE, LOOSE WALL FLANGE AND NO-HUB INLET CONNECTION.


ROOF DRAIN DOWNSPOUT NOZZLE

SERIES

25010-Z

П	TYPE	PIPE SIZE	<u>A</u>	<u>B</u>	<u>C</u>	D	<u>E</u>
	25012-Z	2"	2 3/8	2 5/8	3	5 1/2	5 3/8
	25013-Z	3"	3 3/8	2 5/8	3 1/2	6 1/2	5 3/8
	25014-Z	4"	3 3/4	2 5/8	4	7 1/2	5 1/2
	25015-Z	5"	4 1/4	2 5/8	4 1/2	8 1/2	5 3/4
П	25016-Z	6"	4 3/4	2 5/8	5	9 1/2	5 3/7
	25018-Z	8"	5 7/8	2 5/8	6	11 1/2	6 1/2
П	25019-Z	10"	6 7/8	3	6 7/8	13	6 1/2
	25010-12-Z	12"	7 7/8	3	7 7/8	15	6 1/2





DATE OF LAST CHANGE:	4/23/15
DIMENSIONS ARE SUBJECT TO N	
TOLERANCES AND CHANGE WI	
WE CAN ASSUME NO RESPON	

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

SPECIFICATION:


JOSAM 25010-PVC SERIES COATED CAST BRONZE DOWNSPOUT NOZZLE, LOOSE WALL FLANGE AND INLET CONNECTION WITH THREE SET SCREWS. CONNECTS TO PVC PIPE.

ROOF DRAIN DOWNSPOUT NOZZLE

SERIES **25010-PVC**

TYPE	PIPE SIZE	В	С	D	E
25012-PVC	2*	4	3-3/8	6	2-5/8
25013-PVC	3	4	3-3/8	6	2-5/8
25014-PVC	4	5	3-7/8	7	2-5/8
25015-PVC	5*	7-1/2	4-7/8	9	2-5/8
25016-PVC	6	7-1/2	4-7/8	9	2-5/8
25018-PVC	8	9-5/8	5-7/8	11	2-5/8
25019-PVC	10	11-1/4	6-3/4	12-3/4	2-5/8





П	-24	ROUGH NIKALOY
	-51	SATIN FINISH BRONZE
П	-BS	BIRD SCREEN


* FOR 2" SIZE, FURNISHED WITH 3" BODY WITH 3" X 2" FOR 5" SIZE, FURNISHED WITH 6" BODY WITH 6" X 5"

DATE OF LAST CHANGE: 4/23/15


DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.

WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA NOTES



SPECIFICATION: **ROOF DRAIN** JOSAM 25500 SERIES COATED CAST IRON FLO-SEPTOR®ROOF DRAIN, CAST IRON INTERNAL DOME STRAINER, COMBINED WEJLOC®NON-FLO-SEPTOR® LARGE SUMP PUNCTURING CLAMP RING AND SOLID WATER DAM, LARGE SUMP WITH WIDE ROOF FLANGE AND BOTTOM OUTLET. 25500 **SERIES** Ø15 1/4 WEJLOC CLAMP -RING AND SOLID WATER DAM 2 1/2 -1 MIN 4-3/4 MAX 5 1/8 (-X&-Z) 3-3/4 (-Y) 2 7/8 -Z SHOWN DECK CLAMP (-1) SIZE PIPE SIZE Ø13 1/4 MIN. DECK OPENING -3" 4" *GASKET ON -Y CONNECTION 5" CONFORMS WITH ASTM-C564 -CR CLAMPING DRAIN RECEIVER (MIN. DECK OPENING Ø16") -66 NO-HUB SIDE OUTLET -1 DECK CLAMP ASSEMBLY -T THREADED OUTLET -2 DRAIN RECEIVER -X INSIDE CAULK OUTLET -Y HUB OUTLET WITH GASKET* -3 DECK CLAMP ASSEMBLY & DRAIN RECEIVER -20 GALVANIZED CAST IRON PARTS -Z NO-HUB SPIGOT OUTLET DATE OF LAST CHANGE: NOTES **JOSAM COMPANY** DIMENSIONS ARE SUBJECT TO MANUFACTURERS. TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA. MICHIGAN CITY, INDIANA



		DECK CLAMP ASSEMBLY
		DRAIN RECEIVER
		DECK CLAMP ASSY & DRAIN RECEIVER
ı	-20	GALVANIZED CAST IRON PARTS


_		
	-66	NO-HUB SIDE OUTLET
	-T	THREADED OUTLET
		INSIDE CAULK OUTLET
	-Z	NO-HUB SPIGOT OUTLET

DATE OF LAST CHANGE: 03/25/14

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA

JOSAM COMPANY
MICHIGAN CITY, INDIANA

NOTES



DATE OF LAST CHANGE: 04/28/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPPERSOED OR VOID DATA.

DECK CLAMP ASSY & DRAIN RECEIVER

-20 GALVANIZED CAST IRON PARTS

JOSAM COMPANY MICHIGAN CITY, INDIANA

-Y

NOTES

HUB OUTLET WITH GASKET**


NO-HUB SPIGOT OUTLET

JOSAM SERIES 26200 COATED CAST IRON EXPANSION JOINT, SCHEDULE 80 PVC SLEEVE, PACKING GLAND WITH BOLTED PRESSURE RING, MALE INLET AND FEMALE THREADED OUTLET CONNECTIONS.

ROOF DRAIN

EXPANSION JOINT

26200 SERIES



	2"	PIPE SIZE				8"	PIPE SIZE	
	3"	PIPE SIZE				10"	PIPE SIZE	
	4"	PIPE SIZE						
	5"	PIPE SIZE				-BR	BRASS SLEEVE	
	6"	PIPE SIZE				-20	GALVANIZED CA	ST IRON PARTS
DA.	TE OF LA	ST CHANGE:	11/03/2014	10041	_			NOTES

JOSAM COMPANY MICHIGAN CITY, INDIANA


DIMENSIONS ARE SUBJECT TO MANUFACTURERS. TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

DATE OF LAST CHANGE:

SPECIFICATION: JOSAM 26440 SERIES COATED CAST IRON STACK FITTING WITH COUNTER FLASHING RECESS, THREADED STACK AND EXTENSION

ROOF DRAIN STACK FLASHING FITTING

26440 **SERIES**



6" 7 1/2 5 3/8


SINGLE THREAD CAN BE FURNISHED WHEN SPECIFIED ON ORDER


JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.






OSAM 28600 SERIES COATED CAST IRON FLO-SET® ROOF DRAIN, LARGE SECURED DOME, ADJUSTABLE CALIBRATED VANDAL-PROOF VANE COLLAR, WEJLOC® NON-PUNCTURING CLAMP RING WITH STATIONARY VANES AND INTEGRAL GRAVEL STOP, LARGE SUMP WITH WIDE ROOF FLANGE AND BOTTOM OUTLET.

ROOF DRAIN

FLO-SET®

28600 **SERIES**



-CR	CLAMPING DRAIN RECEIVER (MIN. DECK OPENING Ø16")
-1	DECK CLAMP ASSEMBLY
-2	DRAIN RECEIVER
-3	DECK CLAMP ASSEMBLY AND DRAIN RECEIVER
	SECONDARY FLASHING CLAMP (-AE ONLY)
	FIXED EXTENSION COLLAR, CAST IRON (SPECIFY HEIGHT*)
-10-20	FIXED EXTENSION COLLAR, GALVANIZED (SPECIFY HEIGHT*)
-20	GALVANIZED CAST IRON PARTS
-23	ROUGH BRONZE DOME
-33	STAINLESS STEEL MESH-COVERED DOME
	VANDAL-PROOF DOME
-66	NO-HUB SIDE OUTLET (2" THRU 6" OUTLETS ONLY)
	THREADED OUTLET
	INSIDE CAULK OUTLET
	HUB OUTLET W/ GASKET (2", 3" & 4" SIZES ONLY)
-Z	NO-HUB SPIGOT OUTLET

SPECIFY DESIRED FLOW RATE AND HEAD AND DRAIN CAN BE FURNISHED WITH THE VANES PRE-SET AND VANDAL-PROOFED TO THESE SPECIFICATIONS.

	PIPE SIZE
	2"
	3"
	4"
П	5"
П	6"
_	

*-10 EXTENSION 4" STANDARD

▼ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE 10/24/14

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:

JOSAM 28600-AE SERIES COATED CAST IRON FLO-SET ROOF DRAIN, LARGE SECURED DOME, ADJUSTABLE CALIBRATED VANDAL-PROOF VANE COLLAR, WEJLOC NON-PUNCTURING CLAMP RING WITH STATIONARY VANES AND INTEGRAL GRAVEL STOP, BOLTED SUPPORT RING, ADJUSTABLE TOP, LARGE SUMP WITH ROOF FLANGE AND BOTTOM OUTLET.

ROOF DRAIN

FLO-SET WITH ADJUSTABLE EXTENSION

28600-AE **SERIES**



-66 NO-HUB SIDE OUTLET (2" THRU 6" OUTLETS ONLY) 4" -T THREADED OUTLET -X INSIDE CAULK OUTLET 5" -Y HUB OUTLET W/ GASKET (2", 3" & 4" SIZES ONLY) 6" -Z NO-HUB SPIGOT OUTLET

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

-23 ROUGH BRONZE DOME

-VP VANDAL-PROOF DOME

*** -10 EXTENSION 4" STANDARD

-33 STAINLESS STEEL MESH-COVERED DOME

-26 ALUMINUM DOME


JOSAM COMPANY MICHIGAN CITY, INDIANA


NOTES

PIPE SIZE

2"

3"






JOSAM SERIES 21500-ORDG1 COATED CAST IRON DRAIN BODY AND CLAMP RING WITH STAINLESS STEEL GRAVEL STOP AND SECURED COVER AND PVC STANDPIPE WITH ORIFICE

ROOF DRAIN GREEN ROOF

SERIES 21500-ORDG1



L			-AE	THREADED LEVELEZE ADJ. EXT.
ΙГ	2"	PIPE SIZE	-AER	ADJ. EXT. USING THREADED RODS
ΙГ	3"	PIPE SIZE	-PC	PERFORATED COVER
ΙГ	4"	PIPE SIZE	-LO	LESS ORIFICE IN STANDPIPE
Ι	5"	PIPE SIZE	-1	DECK CLAMP ASY.
	6"	PIPE SIZE	-2	DRAIN RECEIVER
	8"	PIPE SIZE	-3	DECK CLAMP ASY, AND DRAIN RECEIVER
Ι	10°	PIPE SIZE (NO-HUB ONLY)	-3C	DRAIN RECEIVER AND DRAIN RECEIVER CLIPS
ΙП			-4	SECONDARY FLASHING CLAMP (-AE ONLY)
ΙГ	-X	INSIDE CAULK OUTLET	-6	EXTRA WIDE FLANGE DRAIN BODY (-X OUTLET ONLY)
ΙГ	-Y	HUB OUTLET W/GASKET (2", 3" & 4" SIZES ONLY)	-10	FIXED EXT. COLLAR, CAST IRON (SPECIFY HT. OR 4" STD)
ΙГ	-Z	NO-HUB SPIGOT OUTLET	-10-20	FIXED EXT. COLLAR, GALV. (SPECIFY HT. OR 4" STD.)
	-Т	THREADED OUTLET	-17*	2" HIGH SOLID CLAMPING COLLAR
			-20	GALV. CAST IRON PARTS
ΙŒ	-22	CAST IRON DOME	-66	NO-HUB SIDE OUTLET (2" THRU 6" OUTLETS ONLY)


JOSAM COMPANY
MICHIGAN CITY, INDIANA

SPECIFICATION:

JOSAM SERIES 21500-ORDG1-6 COATED CAST IRON LARGE SUMP WIDE FLANGE DRAIN BODY AND CLAMP RING WITH STAINLESS STEEL GRAVEL STOP AND SECURED COVER AND PVC STANDPIPE WITH ORIFICE.

ROOF DRAIN GREEN ROOF

SERIES 21500-ORDG1-6



A INSIDE CAULK OUTLET

DATE OF LAST CHANGE: 03/25/14

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TO JERRANCES AND CHANGE WITHOUT NOTICE
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEEDE OR VOID DATA
USE OF SUPERSEEDE OR VOID DATA

JOSAM COMPANY MICHIGAN CITY, INDIANA NOTES


NO-HUB SIDE OUTLET (2" THRU 6" OUTLETS ONLY)

DATE OF LAST CHANGE:

IMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.



GREEN ROOF JOSAM SERIES 21500-RDG2 COATED CAST IRON DRAIN BODY AND WEJLOC® CLAMP RING AND STAINLESS STEEL GRAVEL STOP WITH STAINLESS STEEL COVER AND OPTIONAL AUXILIARY INLET. 21500-RDG2 SERIES 5-3/4" FOR 8" -T OUTLET Ø15 1/4 -Y GASKET -SS SOLID COVER Ø13 3/8 CONFORMS WITH ASTM-C564 Ø3/8 PERF, SS GRAVEL STOP (40 - 50% OPEN) -AI2 2". 3". 4" AUXILIARY INLET (-AI OPTION) -2". 3". OR 4" (CIRCLE ONE) (12" STD.) X = 5.3/8Y = 4 7/8 Z = 5 1/8MIN. 1 T = 3 3/4MAX. 4 3/4 PIPF SIZE -DECK CLAMP (-1) Ø13 1/4 MIN DECK OPENING Ø18 · 2" PIPE SIZE THREADED LEVELEZE ADJ. EXT 3" PIPE SIZE -AER ADJ. EXT. USING THREADED RODS 4" PIPE SIZE PERFORATED COVER 5" PIPE SIZE DECK CLAMP ASY 6" PIPE SIZE -2 DRAIN RECEIVER 8" PIPE SIZE -3 DECK CLAMP ASY. AND DRAIN RECEIVER 10" PIPE SIZE (NO-HUB ONLY) -3C DRAIN RECEIVER AND DRAIN RECEIVER CLIPS SECONDARY FLASHING CLAMP (-AE ONLY) INSIDE CAULK OUTLET EXTRA WIDE FLANGE DRAIN BODY (-X OUTLET ONLY) -6 HUB OUTLET W/GASKET (2", 3" & 4" SIZES ONLY -10 FIXED EXT. COLLAR, CAST IRON (SPECIFY HT. 4" STD) NO-HUB SPIGOT OUTLET -10-20 FIXED EXT. COLLAR, GALV. (SPECIFY HT. 4" STD) -T THREADED OUTLET -20 GALV. CAST IRON PARTS -33 SS MESH COVERED GRAVEL STOP (16 X 16 MESH) -AI AUX INLET (SPECIFY SIZE) NO-HUB SIDE OUTLET (2" THRU 6" OUTLETS ONLY) -AI2 SECOND AUX INLET (SPECIFY SIZE) DATE OF LAST CHANGE: NOTES JOSAM COMPANY DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA USE OF SUPERSEDED OR VOID DATA

ROOF DRAIN


SPECIFICATION:

JOSAM SERIES 21500-RDG3 COATED CAST IRON DRAIN BODY AND WEJLOC® CLAMP RING WITH STAINLESS STEEL GRAVEL STOP, SECURED COVER AND PLASTIC DOME.

ROOF DRAIN GREEN ROOF

SERIES 21500-RDG3

NOTES



				I
ш	2"	PIPE SIZE	-AE	THREADED LEVELEZE ADJ. EXT.
	3"	PIPE SIZE	-AER	ADJ. EXT. USING THREADED RODS
	4"	PIPE SIZE	-PC	PERFORATED COVER
П	5"	PIPE SIZE	-1	DECK CLAMP ASY.
	6"	PIPE SIZE	-2	DRAIN RECEIVER
	8"	PIPE SIZE	-3	DECK CLAMP ASY. AND DRAIN RECEIVER
	10"	PIPE SIZE (NO-HUB ONLY)	-3C	DRAIN RECEIVER AND DRAIN RECEIVER CLIPS
	-T	THREADED OUTLET	-4	SECONDARY FLASHING CLAMP (-AE ONLY)
	-X	INSIDE CAULK OUTLET	-6	EXTRA WIDE FLANGE DRAIN BODY (-X OUTLET ONLY)
П	-Y	HUB OUTLET W/GASKET (2", 3" & 4" SIZES ONLY)	-10	FIXED EXT. COLLAR, CAST IRON (SPECIFY HT. 4" STD.)
	-Z	NO-HUB SPIGOT OUTLET	-10-20	FIXED EXT. COLLAR, GALV. (SPECIFY HT. 4" STD.)
	-21	GALV. CAST IRON DOME ONLY		
П	-22	CAST IRON DOME		
П	-23	ROUGH BRONZE DOME	-20	GALV. CAST IRON PARTS
	-26	ALUMINUM DOME	-66	NO-HUB SIDE OUTLET (2" THRU 6" OUTLETS ONLY)
	-33	STAINLESS MECH SCREEN-COVERED DOME		
	-VP	VANDAL-PROOF DOME		

JOSAM COMPANY


MICHIGAN CITY, INDIANA

SPECIFICATION:

JOSAM SERIES 21500-Q602 COATED CAST IRON LOWER DRAIN AND WEJLOC CLAMP RING WITH SS MESH COVERED CAST IRON DOME MODIFIED FOR THREADED PVC STANDPIPE. TOP SECTION IS 32100 FLOOR DRAIN.

ROOF DRAIN PLANTING AREA

SERIES 21500-Q602



-1	UNDERDECK CLAMP
-2	DRAIN RECEIVER (24" SQ.)
-VP	VANDALPROOF DOME
-X	CAULK OUTLET
-Y	PUSH-ON OUTLET
-T	THREADED OUTLET
-Z	NO-HUB OUTLET

	SIZE
	2"
	3"
	4"
	5"
	6"
	8"

DIDE

DATE OF LAST CHANGE: 05/04/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA NOTES

DATE OF LAST CHANGE:

IMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.


Green Roof Drains


SPECIFICATION:


JOSAM SERIES 21500-Q606 COATED CAST IRON LOWER DRAIN AND WEJLOC CLAMP RING. COATED CAST IRON THREADED OUTLET UPPER BODY WITH BRONZE CLAMP RING AND DOME.

ROOF DRAIN PLANTING AREA

21500-Q606 SERIES







		BODY FLANGE
	-1	UNDERDECK CLAMP
	-2	DRAIN RECEIVER (24" SQ.)
П	-VP	VANDALPROOF DOME
П		
П	-X	CAULK OUTLET
П	-Y	PUSH-ON OUTLET
	-T	THREADED OUTLET
	-Z	NO-HUB OUTLET

	PIPE SIZE	
П	2"	
	3"	
	4"	
	5"	
	6"	
	8"	

ATE O	F LAS	CHAN	GE:	4/24/1	5
MENSIC	NS ARE	SUBJECT	TO MA	NUFACT	JREF
		ND CHANG			
		ME NO RE			OR
LISE	OF SHE	PERSENEI	OR V	ATAN OIL	

JOSAM COMPANY MICHIGAN CITY, INDIANA


NOTES


SPECIFICATION:


JOSAM 21500-Q515 SERIES CAST IRON DRAIN WITH BOTTOM OUTLET, WEJLOC NON-PUNCTURING CLAMP RING, PVC STANDPIPE. AND BRASS DOME.

DRAIN WITH STANDPIPE

21500-Q515 SERIES







OUTLET TYPE		
-X	INSIDE CAULK	
-Y	HUB WITH GASKET (2"-4")	
-Z	NO-HUB	
-T	THREADED	

PIPE SIZE

2"

3"

4	
5"	
6"	
8"	
10"	

- LESS DOME -24 -PF PERFORATED STANDPIPE
 - * SPECIFY "N" AT TIME OF ORDER ♦ GASKET CONFORMS WITH ASTM-C564
- ☑ THIS DIM. 5 3/4" FOR 21508-T SEE 21500 DRAWING FOR MORE BODY DIMS.

DATE OF LAST CHANGE: 04/27/15 DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES


JOSAM SERIES 21500-Q265 COATED CAST IRON ROOF DRAIN, NON-PUNCTURING CLAMP RING WITH INTEGRAL GRAVEL STO, LARGE CAST IRON DOME COVERED WITH STAINLESS STEEL MESH SCREEN, AND PVC CLEANOUT WITH ROUND NIKALOY TOP, BRONZE PLUG AND 3"-4" SOLVENT WELD QU'TLET.

SEE 21500 AND CO-430 SUBMITTALS FOR SPECIFIC DETAILS.

DRAIN

SUBSURFACE WITH CLEANOUT

SERIES 21500-Q265



4	UNDERDECK CLAMP
-1	UNDERDECK CLAWP
-2	DRAIN RECEIVER (24" SQ.)
-VP	VANDALPROOF DOME
-X	CAULK OUTLET
-Y	PUSH-ON OUTLET
-T	THREADED OUTLET
-Z	NO-HUB OUTLET

	PIPE SIZE
	2"
	3"
	4"
	5"
	6"
	8"

DATE OF LAST CHANGE: 04/05/13

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR


JOSAM COMPANY MICHIGAN CITY, INDIANA NOTES

SPECIFICATION:

JOSAM SERIES 21500-0600 COATED CAST IRON LOWER DRAIN AND WELLOC CLAMP RING WITH SS MESH COVERED CAST IRON DOME MODIFIED FOR THREADED PVC STANDPIPE. COATED CAST IRON THREADED OUTLET UPPER BODY WITH BRONZE CLAMP RING AND SS MESH COVERED SECURED BRONZE HIGH DOME

ROOF DRAIN PLANTING AREA

SERIES 21500-Q600



	-1	UNDERDECK CLAMP
	-2	DRAIN RECEIVER (24" SQ.)
П	-VP	VANDALPROOF DOME
П	-X	CAULK OUTLET
	-Y	PUSH-ON OUTLET
	-T	THREADED OUTLET
П	-Z	NO-HUB OUTLET

	SIZE
	2"
	3"
	4"
	5"
	6"
П	8"


PIPE

DATE OF LAST CHANGE: 05/05/15

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY
MICHIGAN CITY, INDIANA

NOTES



DRAIN JOSAM SERIES 21500-Q603 COATED CAST IRON ROOF DRAIN, NON-PUNCTURING CLAMP RING WITH INTEGRAL GRAVEL STOP, LARGE SUBSURFACE CAST IRON DOME COVERED WITH STAINLESS STEEL MESH SCREEN, SS PERF EXTENSION. CI FIXED EXTENSION, AND PVC CLEANOUT WITH CLEANOUT WITH ROUND NIKALOY TOP, BRONZE PLUG AND 3"-4" SOLVENT WELD OUTLET 21500-Q603 **SERIES** SEE 21500 AND CO-430 SUBMITTALS FOR MORE DETAIL CLEANOUT CO-430 ADJUSTABLE 4" PVC PIPE (BY OTHERS) THREADED ADAPTER 070262 SS MESH - FIXED EXT (-10) HT. = _ COVERED DOME DRAIN ASSY. 21500-IRMA-10 (PERFORATIONS VARY) UNDERDECK - IRMA HT. = CLAMP (-1) OPTION -1 UNDERDECK CLAMP PIPE SIZE -2 DRAIN RECEIVER (24" SQ.) 2" -VP VANDALPROOF DOME 3" 4" -X CAULK OUTLET -Y PUSH-ON OUTLET 5" -T 6" THREADED OUTLET 8" -Z NO-HUB OUTLET 04/08/13 DATE OF LAST CHANGE: NOTES **JOSAM COMPANY** DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

MICHIGAN CITY, INDIANA


SPECIFICATION:


JOSAM SERIES 21500-Q604 COATED CAST IRON ROOF DRAIN, NON-PUNCTURING CLAMP RING WITH INTEGRAL GRAVEL STOP, LARGE CAST IRON DOME COVERED WITH STAINLESS STEEL MESH SCREEN, SS PERF EXTENSION, AID FIXED EXTENSION, AND PVC 3X4 SOLVENT WELD FERRULE WITH STANDPIPE AND BRONZE DOME.

DRAIN

SUBSURFACE WITH STANDPIPE/DOME

21500-Q604 **SERIES**





JOSAM SERIES 21500-Q700 COATED CAST IRON ROOF DRAIN, NON-PUNCTURING CLAMP RING WITH INTEGRAL GRAVEL STOP, 4" PVC PERFORATED STANDPIPE, AND 22080 TOP ASSEMBLY.


SEE 29000 AND 22080 SUBMITTALS FOR MORE DETAIL.


DRAIN

SUBSURFACE WITH STANDPIPE/DOME

21500-Q700 SERIES







			PIPE SIZE
			2"
			3"
	CAULK OUTLET		4"
•	PUSH-ON OUTLET		5"
-	THREADED OUTLET		6"
_	NO-HUB OUTLET		8"

DATE OF LAST CHANGE:	05/04/15
DIMENSIONS ARE SUBJECT TO MA	NUFACTURE
TOLERANCES AND CHANGE WIT	HOUT NOTICE
WE CAN ASSUME NO RESPONS	

JOSAM COMPANY MICHIGAN CITY, INDIANA


NOTES

SPECIFICATION:

JOSAM SERIES 29000-32200 ISOLATION COMBINATIONDECK DRAIN, COATED CAST IRON DRAIN ASSEMBLIES WITH NON-PUNCTURING WEJLOC CLAMP RINGS.

DECK DRAIN ISOLATION

29000-32200 **SERIES**




MICHIGAN CITY, INDIANA

JOSAM SERIES 30000-22080 CAST IRON DRAIN, WEJLOC NON-PUNCTURING CLAMP RINGS, ADJUSTABLE HEIGHT ASSEMBLY, WEEPHOLES, CAST IRON DOME, AVAILABLE TRAP PRIMER CONNECTION, AND BOTTOM OUTLET.

ROOF DRAIN

DECK STYLE WITH SECONDARY DRAINAGE

SERIES 30000-22080




MICHIGAN CITY, INDIANA

SPECIFICATION:

JOSAM SERIES 30000-23500 COATED CAST IRON COMBINATION DRAIN, SQUARE PEDESTRIAN TOP, WEJLOC NON-PUNCTURING CLAMP COLLARS, AND BOTTOM OUTLET.

COMBINATION DRAIN PROMENADE TOP

SERIES **30000-23500**



* ADD 1/4" WHEN FURNISHED WITH NIKALOY OR BRONZE TOP

Ø9 1/4" -

DATE OF LAST CHANGE: 03/20/14


DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.


JOSAM COMPANY
MICHIGAN CITY, INDIANA

USE MODIFIED 004674 COLLAR

NOTES

IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.






JOSAM SERIES 30000-49360A COATED CAST IRON COMBINATION DRAIN, 12" SQUARE TOP, DOUBLE DRAINAGE FLANGE, AND WEJLOC NON-PUNCTURING CLAMP RINGS.

COMBINATION DRAIN

12" SQUARE TOP

SERIES 30000-49360A



MICHIGAN CITY, INDIANA


SPECIFICATION:

WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM SERIES 30000-M-1-2 CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE AND 1/2" PRIMER TAP, WEJLOC® INVERTIBLE FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET CONNECTION AND CHROME PLATED ADJUSTABLE STANDPIPE WITH DOME.

FLOOR DRAIN ADJUSTABLE FLOOR DRAIN

SERIES 30000-M-1-2



MICHIGAN CITY, INDIANA

WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.

Floor Drains

WEIGHT LOADS

Apart from their primary purpose of receiving and conveying liquids, floor drains, as integral components of the floor, must be structurally suitable to withstand the anticipated loads that will be imposed on the floor. Weight support requirements of the drain vary with the location, construction, and service condition. The top loading classifications as published in Floor Drain Standard ANSI A112.21.1M-1980 are as follows:

Light-Duty– All grates testing under 2000 lb. (900 kg.).

Medium-Duty- All grates testing between 2000 lb. (900 kg.)

and 4999 lb. (2250 kg.).

Heavy-Duty– All grates testing between 5000 lb. (2250 kg.)

and 7499 lb. (3375 kg.).


Extra Heavy-Duty— All grates testing between 7500 lb. (3375 kg.)

and 10,000 lb. (4500 kg.).


Special-Duty– Grates testing over 10,000 lb. (4500 kg.) should

be considered special and treated accordingly.


When the top loading requirements for a drain have been determined, the duty type needed can be resolved. Selection is easily accomplished as all JOSAM Floor Drains are classified according to duty type in this section. For specific detail loading data, contact JOSAM Engineering.



PEDESTRIAN GRATE




HEAVY-DUTY GRATE



MEDIUM-DUTY GRATE

-44 Option, Fixed Extension Collar




ORDERING INFORMATION

To specify or order a fixed extension collar with floor drain, add Option (-44) and height required to type number of drain.

Example: Type 32103 with a 6" extension would be designated: Type 32103 (-44)-6".

SERIES NO.	B In	D In	E In
32100, 32150, 32160	9-1/8	8-1/8	2
32200, 32300	12-5/8	11-3/4	2


(-AE) Option, LEVELEZE® Adjustable Extension




The adjustable integral top is mated to the body and support ring with a heavy machined thread which permits virtually unlimited top level adjustment to accommodate various deck thicknesses. The line contact between the threads provides positive circumferential support of the top at any adjusted elevation.

Outlet Connections

JOSAM drains are furnished with outlets for connection to most types of pipe. The timesaving, economical JIFFEE-JOINT Gasket is used for inside caulk connections (-X) to extra heavy or service weight soil pipe. No-hub spigot outlets (-Z) are also available for connection to no-hub soil pipe. The JIFFEE-SET Outlet (-Y) is for connecting hub outlet drains to PVC and ABS, service weight or no-hub soil pipe. Threaded outlets (-T) can be obtained on many series.







(-66) OPTION


This option converts JOSAM bottom outlet inside caulk drains to no-hub side outlet drains using a 90° no-hub quarter bend and a JIFFFF-JOINT Gasket.

PIPE SIZE	A	В	С
2	2-1/2	4-1/2	3-5/8
3	2-13/16	5	4-1/2
4	3-1/2	5-1/2	5-11/16
5	4-5/16	6-1/2	6-15/16
6	4-13/16	7	7-15/16






Floor Drains 123




30000-WF6S Series SUPER-FLO® Adjustable Strainer Floor Drain shown installed in a composition deck floor. Wide flange assures that bonding of floor material is watertight and permanent.




32100-81 Series SUPER-FLO® Floor Drain shown installed in a medium-duty single-pour concrete floor supported by steel construction.

124 Floor Drains





32100-AE-81 Series SUPER-FLO® Floor Drain shown installed in a poured concrete floor with floor finish. LEVELEZE® Adjustable Collar provides vertical adjustment, facilitating installation and forming a perfect surface between top of drain and floor finish.



39600 Series Planting Area Drain shown in a typical installation providing drainage for an indoor planting area. Stainless mesh screen covered dome prevents entrance of dirt and gravel at the base of the planting area.

Floor Drains 125







SPECIFICATION: FLOOR DRAIN JOSAM SERIES "AF" ADJUSTABLE SATIN FINISH NIKALOY ROUND STRAINER WITH WIDE FLANGE, THREADED WITH JOSAM ADJUSTABLE ADJUSTABLE STRAINER STRAINER THREAD. ΑF **SERIES** SLOT SIZE 7/16" SQUARE (JOSAM) Ø5.28 GRATE FREE .22 -1/8" AREA 10.4-WIN N 2-1/4 1-1/8 3-3/4 BACKWATER VALVE BRONZE ADJUSTABLE STRAINER PERFORATED STAINLESS STEEL BASKET SECIRED GRATE, VANDAL-PROOF SCREWS DATE OF LAST CHANGE: **JOSAM COMPANY** DIMENSIONS ARE SUBJECT TO MANUFACTURERS

MICHIGAN CITY, INDIANA

SPECIFICATION: **FLOOR DRAIN** JIOSAM SERIES "C" ADJUSTABLE SATIN FINISH NIKALOY ROUND STRAINER WITH INTEGRAL SEDIMENT BUCKET, THREADED WITH ADJUSTABLE STRAINER JOSAM ADJUSTABLE STRAINER THREAD. C SERIES Ø3-1/2 Ø4-11/16 - 1/4" 1-7/8 1-1/8 Ø3-3/4 -STRAINER FREE AREA OPTIONS BRONZE ADJUSTABLE STRAINER SECURED GRATE, VANDAL-PROOF SCREWS 7/14/2010 DATE OF LAST CHANGE: **JOSAM COMPANY** DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA. MICHIGAN CITY, INDIANA

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.






JOSAM SERIES "E1" ADJUSTABLE SATIN FINISH NIKALOY ROUND STRAINER WITH EXTENDED RIM, THREADED WITH JOSAM ADJUSTABLE STRAINER THREAD.

FLOOR DRAIN

ADJUSTABLE STRAINER

SERIES

E1



		TYPE No.	Α	В	С	D	E	F	н	FREE AREA	LBS.
Г	Т	6E1	5-3/4	3-3/8	1	1-1/4	7/32	7/16	1-1/4	4	5
Г	Т	7E1	7-1/8	3	1-1/8	6-3/8	7/32	3/8	1	8.2	7
	Ι	9E1	8-7/8	3-1/8	7/8	8-3/8	9/32	1/2	1-1/2	21.2	9

		-2	BRONZE ADJUSTABLE STRAIN	ER			-J	BACKWATER VALVE				
г	Π	-80	PERFORATED STAINLESS STE	EL BASKET			-VP	SECURED GRATE, VANDAL-PROOF SCREWS				
DA	TE	OF LAST	T CHANGE: 07/12/10					NOTES				

JOSAM COMPANY

MICHIGAN CITY, INDIANA


SPECIFICATION:

JOSAM SERIES "E2" ADJUSTABLE SATIN FINISH NIKALOY ROUND SUPER-FLO® STRAINER WITH SECURED ROUND FUNNEL, THREADED WITH JOSAM ADJUSTABLE STRAINER THREAD.

FLOOR DRAIN ADJUSTABLE STRAINER

SERIES

E2



7E2	3.3			
		1		
-2	BRONZE ADJUSTABLE STRAINER		-J	BACKWATER VALVE
-80	PERFORATED STAINLESS STEEL BASKET		-VP	SECURED GRATE, VANDAL-PROOF SCREWS
	·			
		-80 PERFORATED STAINLESS STEEL BASKET		

DATE OF LAST CHANGE: 04/23/15


DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED ON VOID DATA.


JOSAM COMPANY MICHIGAN CITY, INDIANA


NOTES


DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.












SPECIFICATION: FLOOR DRAIN JOSAM SERIES "F8" SATIN FINISH NIKALOY OVAL FUNNEL FOR **FUNNEL** ATTACHMENT TO ANY FLAT GRGATE BY SECURING SCREWS. (SCREWS NOT SHOWN) F8 SERIES 2-5/8 4-1/2 -2 SATIN FINISH BRONZE GALVANIZED CAST IRON -92

JOSAM COMPANY

MICHIGAN CITY, INDIANA

NOTES



Floor Drains

-93

DATE OF LAST CHANGE:

CAST IRON

DATE OF LAST CHANGE. PLANTERS

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.

WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.


JOSAM SERIES G ADJUSTABLE SATIN FINISH NIKALOY ROUND STRAINER WITH SOLID HINGED COVER AND INTERNAL STRAINER GRATE THREADED WITH JOSAM ADJUASTABLE STRAINER THREAD

FLOOR DRAIN

ROUND NIKALOY STRAINER WITH SOLID HINGED COVER

SERIES

G



	-2	BRONZE ADJUSTABLE STRAINER			STRAINER	Α	В	С	D	E	FREE AREA
	-J	BACKWATER VALVE		Г	-5G	5	2	1-1/8	4-5/8	1/4	4.1
	-VP	SECURED GRATE, VANDAL-PROOF SCREWS		Г	-6G	6	2-1/4	15/16	5-1/4	3/16	4.5
				Г	-7G	7	3-1/4	2	6-1/2	3/16	5.7
					-8G	8	3-1/4	1-1/8	7-1/8	7/32	7.8

DATE OF LAST CHANGE: 7/26/2010
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY
MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:

JOSAM SERIES "H" ADJUSTABLE SATIN FINISH NIKALOY ROUND STRAINER WITH HINGED GRATE, THREADED WITH JOSAM ADJUSTABLE STRAINER THREAD.

FLOOR DRAIN

ADJUSTABLE STRAINER

SERIES H




OPTIONS:


	-2	BRONZE ADJUSTABLE STRAINER	STRAINER	A	В	С	D	FREE AREA
	7	BACKWATER VALVE	-5H	5	2	1-1/8	4-5/8	6.0
	-80	PERFORATED STAINLESS STEEL BASKET	-6H	6	2-1/4	1-1/8	5-1/4	7.8
П	-VP	SECURED GRATE, VANDAL-PROOF SCREWS	-7H	7	2-1/8	1	6-1/2	12.2
			-8H	8	2-1/2	1	7-1/8	16.1

DATE OF LAST CHANGE: 11/20/14

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA NOTES






JOSAM SERIES "R" ADJUSTABLE SATIN FINISH NIKALOY RECTANGULAR STRAINER, THREADED WITH JOSAM ADJUSTABLE STRAINER THREAD


FLOOR DRAIN

ADJUSTABLE STRAINER

SERIES

R





-2	BRONZE ADJUSTABLE STRAINER
-80	PERFORATED STAINLESS STEEL BASKET
7	BACKWATER VALVE
-VP	SECURED GRATE VANDAL-PROOF

	STRAINER	AL	Aw	В	С	DL	Dw	FREE AREA
П	-5R	9	5	3-1/4	1-1/8	8-3/8	4-3/8	14.9
	-6R	13	5	3-1/4	1-3/8	12	4	20.0
	-7R	17	5	3-1/4	1-3/8	16-1/4	4-3/8	22.4
П	-8R	21	5	3-1/4	1-1/4	20-3/8	4-3/8	47.0

DATE OF LAST CHANGE: 05/04/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR YOUID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:

JOSAM SERIES "S" ADJUSTABLE SATIN FINISH NIKALOY SQUARE "SUPER - FLO" \circ STRAINER THREADED WITH JOSAM ADJUSTABLE STRAINER THREAD.

FLOOR DRAIN

ADJUSTABLE STRAINER

SERIES S




* NOT "SUPER - FLO" ® DESIGN


1	-SS	STAINLESS STEEL (5S, 6S, 7S, & 8S)		-CP	CHROME PLATED STRAINER (5S & 6S)
1	-2	BRONZE ADJUSTABLE STRAINER		-J	BACKWATER VALVE
	-80	PERFORATED STAINLESS STEEL BASKET	П	-VP	SECURED GRATE, VANDAL-PROOF SCREWS
7					

DATE OF LAST CHANGE: 10/14/2013

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED ON VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA NOTES





JOSAM SERIES WF6A ADJUSTABLE COATED CAST IRON SQUARE WIDE FLANGE STRAINER BODY WITH ROUND SATIN FINISH NIKALOY SUPER-FLO® RIM AND GRATE, THREADED WITH JOSAM ADJUSTABLE STRAINER THREAD.


FLOOR DRAIN

ADJUSTABLE STRAINER

WF6A SERIES

NOTES

SLOT SIZE 1/4"



JOSAM COMPANY


MICHIGAN CITY, INDIANA

SPECIFICATION:

JOSAM SERIES WF6S ADJUSTABLE COATED CAST IRON SQUARE GRATE, WIDE FLANGE STRAINER BODY, WITH SQUARE SATIN FINISH NIKALOY SUPER-FLO RIM AND GRATE, THREADED WITH JOSAM ADJUSTABLE STRAINER THREAD.

FLOOR DRAIN ADJUSTABLE STRAINER

WF6S **SERIES**



MICHIGAN CITY, INDIANA

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS


TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

SPECIFICATION: JOSAM 30000 SERIES CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE AND 1/2" PRIMER TAP WITH PLUG BOTTOM OUTLET CONNECTION, WEJ.DOC INVERTIBLE FLASHING, COLLAR, WEEPHOLES AND THREADED TO RECEIVE JOSAM ADJUSTABLE STRAINER.

FLOOR DRAIN BODY ONLY

SERIES

30000



	-PD	PRISON DRAIN (2" AND 3" ONLY)*			-T	THREADED OUTL	.ET	
-ARE ACID-RESISTING EPOXY				-X	INSIDE CAULK OF	JTLET		
-49 3/4" PRIMER TAP					-Y	HUB OUTLET WIT	'H GASKET**	
*00	DADA	TE SUBMITTAL FOR THIS OPTION AVAIL	ADIE		-Z	NO-HUB SPIGOT	OUTLET	
3L	SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE							
ATI	E OF L	AST CHANGE: 04/23/15		_			NOTES	

DATE OF LAST CHANGE: 04/23/15

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

-ST WITH SHALLOW TRAP (2" AND 3" ONLY)*

JOSAM COMPANY
MICHIGAN CITY, INDIANA

NOTE


-92 GALVANIZED CAST IRON PARTS

SPECIFICATION:

3000.PFB SERIES FLOOR DRAIN ASSEMBLY, GALVANIZED STEEL DRAIN BASE AND 2-PIECE COATED CAST IRON BODY, DOUBLE DRAINAGE FLANGE, WELLOC FLASHING COLLAR WITH WEEPHOLES THREADED TO RECEIVE ADJUSTABLE STRAINER. NO-HUB BOTTOM OUTLET AND THREADED ROD AND HARDWARE FOR HEIGHT ADJUSTMENT.

FLOOR DRAIN ADJUSTABLE BASE

SERIES 30000-PFB




JOSAM SERIES 30000-ST COATED CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE, 1/2" PRIMER TAP WITH PLUG, WEJLOC INVERTIBLE CLAMP COLLAR THREADED FOR JOSAM ADJUSTABLE STRAINERS WITH SIDE OUTLET SHALLOW TRAP.

FLOOR DRAIN

WITH SHALLOW TRAP

SERIES 30000-ST



MODEL	PIPE SIZE	A	В
30002-ST	2	2-1/2"	7-1/2"
30002-ST-Z	2	2-1/2"	8"
30003-ST	3	2-1/4"	9-7/8"
30003-ST-Z	3	2-1/4"	10-1/4"

OPTIONS

	-ARE	ACID-RESISTING EPOXY
	-49 3/4" PRIMER TAP	
ſ	-92	GALVANIZED CAST IRON PARTS
ſ	-Z	NO-HUB SIDE OUTLET TRAP

DATE OF LAST CHANGE: 06/18/08

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA


NOTES


SPECIFICATION:


JOSAM 30000-TSO SERIES CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE, INTEGRAL THREADED SIDE OUTLET, WEJLOC® NON-PUNCTURING FLASHING COLLAR WITH WEEPHOLES AND THREADED TO RECEIVE JOSAM ADJUSTABLE STRAINER.

FLOOR DRAIN BODY ONLY

SERIES 30000-TSO








	Х	-TSO	THREADED SIDE OUTLET
-ARE ACID-RESISTING EPOXY			
		-49	3/4" PRIMER TAP
		-50	1/2" PRIMER TAP
	П	-92	GALVANIZED CAST IRON PARTS

PIPE SIZE	<u>A</u>	<u>B</u>	<u>C</u>	<u>D</u>
2"	3	9-1/8	4-5/8	4
3"	2-1/2	9-1/8	4-5/8	4
4"	3-1/4	10-1/4	6	4-1/4

DATE OF LAST CHANGE: 04/23/15

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA NOTES



SPECIFICATION: FLOOR DRAIN JOSAM 30500 SERIES COATED CAST IRON COMBINED FLOOR DRAIN AND INTEGRAL DEEP DRUM TYPE "P" TRAP WITH DOUBLE DRAINAGE FLANGE, NO-HUB SPIGOT SIDE OUTLET, WEEPHOLES, BRONZE INTEGRAL FLUSH-FLOOR CLEANOUT AND THREADED TO RECEIVE **BODY ONLY** JOSAM ADJUSTABLE STRAINERS. 30500 **SERIES** 1-1/2" ADJUSTABLE BUSHING WITH CLEANOUT PLUG-14 X 10 -5/16" 11/16" 3 1/4" 6 3/8" 9 3/8" SEAL SPIGOT * IPS PRIMER TAPPING (-49) & (-50) AUX. THREADED INLET (-51) & (-52) OPTIONS BOLTED FLASHING CLAMP DEVICE -C -49 3/4" PRIMER TAP MODEL ĸ SIZE 1/2" PRIMER TAP 30502 2" 3 14-1/8 -51 1-1/2" THREADED AUXILIARY INLET 30503 3" 3-1/2 11 -52 2" THREADED AUXILIARY INLET 30504 4" 4-1/8 11 GALVANIZED CAST IRON PARTS

JOSAM COMPANY

MICHIGAN CITY, INDIANA

NOTES

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.


JOSAM SERIES 30000-A CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE AND 1/2" PRIMER TAP, WELLOC 9 INVERTIBLE FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET CONNECTION AND NIKALOY ADJUSTABLE ROUND SUPER-FLO STRAINER.

FLOOR DRAIN

ADJUSTABLE FLOOR DRAIN

SERIES

30000-A



STRAINER	DIA. B	X	Y	FREE ARE	A			
-5A	5	3/4	2-1/8	7.8				
-6A	6	1-1/4	2-3/8	11.0				
-7A	7	1-1/8	2-7/8	13.2				
-8A	8	1-5/8	2-5/8	16.2				
-9A ■	9	1-1/8	2-1/4	21.1				
-10A ■	10	1-1/8	2-3/8	28.0				
NOT SUPER-FLO DESIGN 1" x 1/2" OPENINGS								

SLOT WIDTH 1/4" (5" THRU 8" TOPS)

♦ GASKET ON -Y CONNECTION CONFORMS WITH ASTM-C564

_	SEPARATE SUBMITTAL	EOD TUIC	OPTION	AVAII ABI
•	OLI FILOTTE GODINIT TALE		0, ,,0,,,	

	2"	PIPE SIZE	▼	-J	BACKWATER VALVE
	3"	PIPE SIZE	▶	-PD	PRISON DRAIN (2" & 3" SIZES ONLY)
П	4"	PIPE SIZE		-SS	STAINLESS STEEL
			▼	-ST	WITH SHALLOW TRAP (2" & 3" SIZES ONLY)
	-2	BRONZE ADJUSTABLE STRAINER	▼	-TSO	THREADED SIDE OUTLET
	-49	3/4" PRIMER TAP		-VP	SECURED GRATE
П	-80	PERFORATED STAINLESS STEEL BASKET			
	-91	ROUGH BRONZE BODY		-T	THREADED OUTLET
	-92	GALVANIZED CAST IRON PARTS		-X	INSIDE CAULK OUTLET
				-Y	HUB OUTLET WITH GASKET ♦
	-ARE	ACID-RESISTING EPOXY		-Z	NO-HUB SPIGOT OUTLET
	-CP	CHROME PLATED STRAINER (5A & 6A)			

DATE OF LAST CHANGE: 04/24/15 DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPPRESEDED OR VOID DATA. MICH

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:

JOSAM 30000-6AD SERIES CAST IRON FLOOR DRAIN WITH DOUBLE DRAINAGE FLANGE, WEEPHOLES, BOTTOM OUTLET, NIKALOY 6" ADJUSTABLE ROUND STRAINER WITH CLAMPING COLLAR TO SECURE FLASHING OR WATER PROOFING AT FINISHED FLOOR.

FLOOR DRAIN

ADJUSTABLE FLOOR DRAIN

SERIES 30000-6AD



	-2	BRONZE ADJ. STRAINER
-49 3/4" PRIMER TAP		3/4" PRIMER TAP
-66 NO-HUB SIDE OF		NO-HUB SIDE OUTLET
	-80	PERFORATED SS BASKET
	-92	GALVANIZED CAST IRON PARTS

-VP	SECURED GRATE, VP SCREWS			
-T THREADED OUTLET				
-X INSIDE CAULK OUTLET				
-Y	HUB OUTLET WITH GASKET ♦			
-Z	NO-HUB SPIGOT OUTLET			
	-T -X			

DATE OF LAST CHANGE: 04/24/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.


JOSAM COMPANY MICHIGAN CITY, INDIANA NOTES

CONFORMS WITH ASTM-C564

JOSAM SERIES 30000-AF CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANCE AND 1/2" PRIMER TAP WEJLOC®INVERTIBLE FLASHING COLLAR, WEEPHOLES, BOTTÓM OUTLET CONNECTION AND NIKALOY ADJUSTABLE ROUND STRAINER WITH TILE FLANGE.

FLOOR DRAIN ADJUSTABLE FLOOR DRAIN

SERIES 30000-AF



STRAINER	X	Y	FREE AREA
-6AF	1-1/4	2-3/8	10.4

◆ GASKET ON -Y CONNECTION CONFORMS WITH ASTM-C564

-2	BRONZE ADJUSTABLE STRAINER		-ST	WITH SHALLOW TRAP (2" & 3" SIZES ONLY)	
-49	3/4" PRIMER TAP		-TSO	THREADED SIDE OUTLET	
-80	PERFORATED STAINLESS STEEL BASKET		-VP	SECURED GRATE	
-91	ROUGH BRONZE BODY				
-92	GALVANIZED CAST IRON PARTS		-T	THREADED OUTLET	
-7	BACKWATER VALVE		-X	INSIDE CAULK OUTLET	
-ARE	ACID-RESISTING EPOXY		-Y	HUB OUTLET WITH GASKET ♦	
-PD	PRISON DRAIN (2" AND 3" SIZES ONLY)		-Z	NO-HUB SPIGOT OUTLET	

DATE OF LAST CHANGE: 04/24/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VIOLD DATA.

JOSAM COMPANY
MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:

USE OF SUPERSEDED OR VOID DATA.

JOSAM SERIES 30000-C CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE AND 1/2" PRIMER TAP, WEJLOC © INVERTIBLE FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET CONNECTION AND NIKALOY ADJUSTABLE ROUND "C" SERIES NON-CLOS STRAINER WITH BUCKET.

FLOOR DRAIN ADJUSTABLE FLOOR DRAIN

SERIES 30000-C




JOSAM SERIES 30000-D CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE AND 1/2" PRIMER TAP, WEJLOC ◎ INVERTIBLE FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET CONNECTION AND NIKALOY ADJUSTABLE DOME STRAINER.

FLOOR DRAIN

ADJUSTABLE FLOOR DRAIN

SERIES

30000-D



JOSAM COMPANY

MICHIGAN CITY, INDIANA

SPECIFICATION:

JOSAM SERIES 30000-E CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE AND 1/2" PRIMER TAP, WEJLOC © INVERTIBLE FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET CONNECTION AND NIKALOY ADJUSTABLE ROUND STRAINER WITH TRACTOR GRATE.

ARE ACID-RESISTING EPOXY

-91 ROUGH BRONZE BODY

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR


USE OF SUPERSEDED OR VOID DATA

-92 GALVANIZED CAST IRON PARTS

-49 3/4" PRIMER TAP

DATE OF LAST CHANGE:

FLOOR DRAIN ADJUSTABLE FLOOR DRAIN



JOSAM COMPANY

MICHIGAN CITY, INDIANA

THREADED OUTLET

INSIDE CAULK OUTLET

NO-HUB SPIGOT OUTLET

HUB OUTLET WITH GASKET*


NOTES

DATE OF LAST CHANGE: 4/24/2014

TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.

IMENSIONS ARE SUBJECT TO MANUFACTURERS



-49 3/4" PRIMER TAP HUB OUTLET WITH GASKET* -91 ROUGH BRONZE BODY -Z NO-HUB SPIGOT OUTLET DATE OF LAST CHANGE: 04/24/15 NOTES **JOSAM COMPANY** DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA USE OF SUPERSEDED OR VOID DATA.


SPECIFICATION:

Ø9 1/4'

JOSAM SERIES 30000-E2 CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE AND 1/2" PRIMER TAP, WEJLOC @ INVERTIBLE FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET CONNECTION AND NIKALOY ADJUSTABLE ROUND STRAINER WITH ROUND FUNNEL

FLOOR DRAIN ADJUSTABLE FLOOR DRAIN

30000-E2 **SERIES**




JOSAM 30000-23 SERIES CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE AND 1/2* PRIMER TAP, WEJLOC* INVERTIBLE FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET CONNECTION AND NIKALOY ADJUSTABLE ROUND STRAINER WITH OVAL FUNNEL.

FLOOR DRAIN ADJUSTABLE FLOOR DRAIN

SERIES

30000-E3




SPECIFICATION:

JOSAM 30000-F SERIES CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE AND 1/2" PRIMER TAP, WEJLOC" INVERTIBLE FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET CONNECTION AND NIKALOY ADJUSTABLE ROUND STRAINER WITH SOLID THREADED COVER.

FLOOR DRAIN ADJUSTABLE FLOOR DRAIN

series 30000-F



A-15601-K


SPECIFICATION:

JOSAM 30000-G SERIES CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE AND 1/2" PRIMER TAP, WEJLOC" INVERTIBLE FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET CONNECTION AND NIKALOY ADJUSTABLE ROUND STRAINER WITH SOLID HINGED COVER.

FLOOR DRAIN ADJUSTABLE FLOOR DRAIN

SERIES

30000-G



JOSAM COMPANY
MICHIGAN CITY, INDIANA


NOTES:

SPECIFICATION:

JOSAM 30000-H SERIES CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE AND 1/2" PRIMER TAP, WEJLOC" INVERTIBLE FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET CONNECTION AND NIKALOY ADJUSTABLE ROUND STRAINER WITH SOLID HINGEO GRATE.

FLOOR DRAIN ADJUSTABLE FLOOR DRAIN

series 30000-H




JOSAM 30000-M SERIES CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE AND 1/2" PRIMER TAP, WEJLOC® INVERTIBLE FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET CONNECTION AND CHROME PLATED ADJUSTABLE STANDPIPE WITH DOME

FLOOR DRAIN ADJUSTABLE FLOOR DRAIN

30000-M

SERIES




SPECIFICATION:

JOSAM SERIES 30000-P CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE AND 1/2" PRIMER TAP, WEJLOC ♥ INVERTIBLE FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET CONNECTION AND NIKALOY ADJUSTABLE ANGLE STRAINER.

FLOOR DRAIN ADJUSTABLE FLOOR DRAIN

30000-P **SERIES**




L		-6P	6-1/8	6-1/4	1-5/8	3-7/8	3-1/8		18.7				
	2"	PIPE S	SIZE					-92	GALVAN	ALVANIZED CAST IRON PARTS			
	3"	PIPE S	IZE					-2	BRONZE	ADJU	STABLE S	STRAINER	
	4"	PIPE S	IZE					-80	PERFORA	ATED S	TAINLESS	STEEL BA	SKET
	-TSO	THRE/	ADED S	IDE OUT	LET			-VP	SECURED	GRATE	, VANDAL-F	PROOF SCR	EWS
	-ST	WITH S	SHALLC	W TRAI	2" AN	D 3" ON	LY)						
	-PD	PRISO	N DRAI	N (2" AN	ID 3" ON	ILY)		-T	THREAD	ED OU	ITLET		
	-ARE	ACID-F	RESISTI	NG EPC	XY			-X	INSIDE C	AULK	OUTLET		
	-49	3/4" PF	RIMER 1	ΓAΡ				-Y	HUB OU	TLET V	VITH GAS	KET*	
	-91	ROUG	H BRON	NZE BOD	ΣΥ			-Z	NO-HUB	SPIGO	T OUTLE	T	
DA	ATE OF LAST CHANGE: 04/24/15									NOTES			


RAWING No. 06/18/08

JOSAM COMPANY A-15603-K MICHIGAN CITY, INDIANA

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA






JOSAM 30000-T SERIES CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE AND 1/2" PRIMER TAP, WELLOC" INVERTIBLE FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET CONNECTION AND NIKALOY ADJUSTABLE SQUARE HINGED GRATE.

FLOOR DRAIN ADJUSTABLE FLOOR DRAIN

SERIES

. 30000-T




SPECIFICATION:

A-15608-K

JOSAM 30000-PD-A SERIES GALVANIZED SECURITY FLOOR DRAIN, FLASHING FLANGE THREADED SIDE OUTLET CONNECTION, INTEGRAL TRAP WALL AND NIKALOY ADJUSTABLE ROUND SUPER-FLO® STRAINER.

SECURITY FLOOR DRAIN WITH INTEGRAL TRAP WALL

SERIES 30000-PD-A




MICHIGAN CITY, INDIANA

JOSAM 30000-PD-S SERIES GALVANIZED SECURITY FLOOR DRAIN, FLASHING FLANGE THREADED SIDE OUTLET CONNECTION, INTEGRAL TRAP WALL AND NIKALOY ADJUSTABLE SQUARE SUPER-FLO® STRAINER.

SECURITY FLOOR DRAIN WITH INTEGRAL TRAP WALL

30000-PD-S




SPECIFICATION:

JOSAM 30000-ST-A SERIES COATED CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE AND 1/2" PRIMER TAP WITH PLUG. WEJLOC INVERTIBLE NON-PUNCTURING FLASHING COLLAR WITH WEEPHOLES AND JOSAM ADJUSTABLE ROUND NIKALOY STRAINER.

FLOOR DRAIN

SHALLOW TRAP, ADJUSTABLE STRAINER

30000-ST-A **SERIES**



MODEL	PIPE SIZE	A	В	TRAP WIDTH
30002-ST	2	2-1/2"	7-1/2"	3-1/8
30002-ST-Z	2	2-1/2"	8"	3-1/8
30003-ST	3	2-1/4"	9-7/8"	5-1/2
30003-ST-Z	3	2-1/4"	10-1/4"	5-1/2

	ADJUSTABLE STRAINERS							
TYPE NO.		С	х	Y	FREE AREA			
	5A	5	3/4	2-1/8	7.8			
	6A	6	1-1/4	2-3/8	11.0			
	7A	7	1-1/8	2-7/8	13.2			
	8A	8	1-5/8	2-5/8	16.2			

-SS	STAINLESS STEEL STRAINER PARTS
-2	SATIN FIN. BRONZE STRAINER PARTS
-80	PERF. STAINLESS STEEL BASKET
-CP	CHROME PLATED STRNR (5A,6A)
-VP	SECURED GRATE, VANDAL-PROOF SCREWS
-ARE	ACID-RESISTING EPOXY
-49	3/4" PRIMER TAP
-92	GALVANIZED CAST IRON PARTS
-Z	NO-HUB SIDE OUTLET TRAP

ı	DATE OF LAST CHANGE:	04/24/15
ı	DIMENSIONS ARE SUBJECT TO N	IANUFACTURERS
ı	TOLERANCES AND CHANGE WI WE CAN ASSUME NO RESPO	THOUT NOTICE.
- 1	WE CAN ASSUME NO RESPON	


JOSAM COMPANY MICHIGAN CITY, INDIANA

JOSAM 30000-TSO-A SERIES CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE, INTEGRAL THREADED SIDE OUTLET, WELLOC® INVERTIBLE FLASHING COLLAR WITH WEEPHOLES AND THREADED TO RECEIVE JOSAM ADJUSTABLE STRAINER AND NIKALOY ADJUSTABLE ROUND SUPER-FLO® STRAINER.

FLOOR DRAIN WITH THREADED SIDE OUTLET

SERIES 30000-TSO-A

SLOT WIDTH 1/4"




SPECIFICATION:

JOSAM 3000-TSO-S SERIES CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE, INTEGRAL THREADED SIDE OUTLET, WEJLOC* INVERTIBLE FLASHING COLLAR WITH WEEPHOLES AND THREADED TO RECEIVE JOSAM ADJUSTABLE STRAINER, AND NIKALDY ADJUSTABLE SQUARE SUPER-FLO* STRAINER.

FLOOR DRAIN WITH THREADED SIDE OUTLET

SERIES 30000-TSO-S




JOSAM SERIES 30304-Z-A COATED CAST IRON FLOOR DRAIN WITH JOSAM ADJUSTABLE ROUND NIKALOY STRAINER.

FLOOR DRAIN

4" NO-HUB ROUND ADJUSTABLE STRAINER

SERIES

30304-Z-A



	ADJU:	STABLE S	TRAINER	S
TYPE NO.	С	х	Y	FREE AREA
5A	5	3/4	2-1/8	7.8
6A	6	1-1/4	2-3/8	11.0
7A	7	1-1/8	2-7/8	13.2
8A	8	1-5/8	2-5/8	16.2

	-SS	STAINLESS STEEL STRAINER PARTS
	-2	SATIN FIN. BRONZE STRAINER PARTS
ſ	-80	PERF. STAINLESS STEEL BASKET
	-CP	CHROME PLATED STRNR (5A,6A)
ſ	-J	BACKWATER VALVE
	-VP	SECURED GRATE, VANDAL-PROOF SCREWS
	-ARE	ACID-RESISTING EPOXY
ſ	-92	GALVANIZED CAST IRON PARTS

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA


NOTES

SPECIFICATION:

JOSAM 30500-A SERIES COATED CAST IRON COMBINED FLOOR DRAIN AND INTEGRAL DEEP DRUM TYPE "P" TRAP WITH DOUBLE DRAINAGE FLANGE, NO-HUB SPIGOT SIDE OUTLET, WEEPHOLES, BRONZE INTEGRAL FLUSH-FLOOR CLEANOUT AND NIKALOY ADJUSTABLE ROUND SUPER-FLO STRAINER.

FLOOR DRAIN ADJUSTABLE FLOOR DRAIN

30500-A **SERIES**



IPS PRIMER TAPPING (-49) & (-50) AUX. THREADED INLET (-51) & (-52)

MODEL	PIPE SIZE	J*	K
30502	2"	3	14-1/8
30503	3"	3-1/2	11
30504	4"	4-1/8	11

STRAINER	В	х	Y	FREE AREA
-5A	5	1-3/8	2-1/8	7.8
-6A	6	1-5/8	2-3/8	11.0
-7A	7	1-5/8	2-3/8	13.2
-8A	8	2	2-5/8	16.2

DATE OF LAST CHANGE:	04/24/15
DIMENSIONS ARE SUBJECT TO MA	ANUFACTURERS
TOLERANCES AND CHANGE WIT	
WE CAN ASSUME NO RESPON	
USE OF SUPERSEDED OR V	OID DATA.

BOLTED FLASHING CLAMP DEVICE -C 3/4" PRIMER TAP -49 -50 1/2" PRIMER TAP 1-1/2" THREADED AUXILIARY INLET 2" THREADED AUXILIARY INLET GALVANIZED CAST IRON PARTS -92 BRONZE ADJUSTABLE STRAINER STAINLESS STEEL ADJ. STRAINER -SS -80 PERFORATED SS BASKET -CP CHROME PLATED STRAINER (5A, 6A) BACKWATER VALVE SECURED GRATE, VANDAL-PROOF SCREWS

JOSAM COMPANY MICHIGAN CITY, INDIANA

OPTIONS:


JOSAM 30500-S SERIES COATED CAST IRON COMBINED FLOOR DRAIN AND INTEGRAL DEEP DRUM TYPE "P" TRAP WITH DOUBLE DRAINAGE FLANGE, NO-HUB SPIGOT SIDE OUTLET, WEEPHOLES, BRONZE INTEGRAL FLUSH-FLOOR CLEANOUT AND NIKALOY ADJUSTABLE SQUARE SUPER-FLO STRAINER.

FLOOR DRAIN

ADJUSTABLE FLOOR DRAIN

SERIES 30500-S

NEGOTI DEL TEGOTI EN



AUX. THREADED INLET (-51) & (-52)

MODEL	PIPE	J*	K
30502	2"	3	14-1/8
30503	3"	3-1/2	11
30504	4"	4-1/8	11

STRAINER	В	х	Y	FREE AREA
-5S	5	1-1/4	2	9.1
-6S	6	1-1/2	2-1/4	13.8
-8S	8	2	2-5/8	24.5

-C BOLTED FLASHING		-C	BOLTED FLASHING CLAMP DEVICE
		-49	3/4" PRIMER TAP
		-50	1/2" PRIMER TAP
		-51	1-1/2" THREADED AUXILIARY INLET
-52		-52	2" THREADED AUXILIARY INLET
		-92	GALVANIZED CAST IRON PARTS
ſ		-2	BRONZE ADJUSTABLE STRAINER
-[П	-SS	STAINLESS STEEL ADJ. STRAINER
ſ		-80	PERFORATED SS BASKET
ſ		-CP	CHROME PLATED STRAINER (5S, 6S)
[-J	BACKWATER VALVE
Ī		-VP	SECURED GRATE, VANDAL-PROOF SCREWS

DATE OF LAST CHANGE: 04/24/15 DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR YOUT DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

SPECIFICATION:


COATED CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH INVERTIBLE CLAMP COLLAR AND DRAINAGE SLOTS, 4" ROUND ADJUSTABLE CHROME-PLATED BRASS STRAINER, 2" THREADED SIDE OUTLET SHALLOW TRAP

FLOOR DRAIN

ADJUSTABLE WITH 2" SHALLOW TRAP

SERIES 30

30802-4CP



OPTIONS


	-SQ SQUARE STRAINER							
	-LT	LESS TRAP						
	-Z	SHALLOW TRAP WITH NO-HUB SIDE OUTLET						


STRAINER	"A"
-4CP	Ø4 3/16"
-4CP-SQ	4 1/16" SQUARE

DATE OF LAST CHANGE: 08/20/09

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY
MICHIGAN CITY, INDIANA





P	TI	10	SI	

	-2	BRONZE ADJUSTABLE STRAINER
П	-66	NO-HUB SIDE OUTLET
	-92	GALVANIZED CAST IRON PARTS
	-VP	VANDAL-PROOF SCREWS

	-T	THREADED OUTLET				
	-X	INSIDE CAULK OUTLET				
	-Y	HUB OUTLET WITH GASKET *				
П	-Z	NO-HUB SPIGOT OUTLET				

DATE OF LAST CHANGE:	09/18/13
DIMENSIONS ARE SUBJECT TO MA	
TOLERANCES AND CHANGE WIT WE CAN ASSUME NO RESPON	
USE OF SUPERSEDED OR V	OID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

OUTLET TYPE

NOTES

PIPE SIZE

3" 4"

SPECIFICATION:


JOSAM 31000 SERIES COATED CAST IRON FLOOR DRAIN, 1/2" PRIMER TAP WITH PLUG, BOTTOM OUTLET, AND 5" ROUND ADJUSTABLE NIKALOY TOP.

FLOOR DRAIN

5" TOP ADJUSTABLE

SERIES

31000



MODEL	PIPE SIZE
31002	2"
31003	3"
31004	4"

Ī	OUTLET	DESC.	
1	-Y	HUB OUTLET WITH GASKET (2" OR 3")	
-Z NO-HUB OUTLET			

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA


JOSAM 32100 SERIES COATED CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE, WEJLOC ® NON-PUNCTURING FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET, ROUND TOP, MEDIUM-DUTY LOOSE-SET ANT-TILTING SUPER-FLO ® GRATE WITH PERIMETER DRAINAGE SLOTS.

FLOOR DRAIN

9" ROUND TOP, SUPER-FLO®

SERIES **32100**

NOTES



JOSAM COMPANY

MICHIGAN CITY, INDIANA

SPECIFICATION:

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.


JOSAM 32106 SERIES COATED CAST IRON FLOOR DRAIN, TWO PIECE BODY WITH DOUBLE DRAINAGE FLANGE, WEEPHOLES, 6" BOTTOM OUTLET, ROUND TOP, MEDIUM DUTY LOOSE-SET ANTI-TILTING SUPER - FLO GRATE WITH PERIMETER DRAINAGE SLOTS.

FLOOR DRAIN

9" ROUND TOP, SUPER-FLO®

SERIES **32106**

NOTES



JOSAM COMPANY

MICHIGAN CITY, INDIANA

DATE OF LAST CHANGE:

IMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE
WE CAN ASSUME NO RESPONSIBILITY FOR


USE OF SUPERSEDED OR VOID DATA.


JOSAM 32100-81 SERIES COATED CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE, WEJLOC NON-PUNCTURING FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET. ROUND TOP WITH REMOVABLE SEDIMENT BUCKET WHICH SUPPORTS A MEDIUM-DUTY LOOSE-SET ANTI-TILTING SUPER-FLO GRATE WITH PERIMETER DRAINAGE SLOTS.

FLOOR DRAIN

9" ROUND TOP, SUPER-FLO

32100-81 **SERIES**





П		-AE	LEVELEZE ADJUSTABLE EXTENSION		\blacksquare	-49	3/4" PRIMER TAP
П	Х	-81	SLOTTED CAST IRON BUCKET		\mathbb{I}	-50	1/2" PRIMER TAP
ΙГ		-TG	TRACTOR GRATE	П	Т	-66	NO-HUB SIDE OUTLET
		-1	SATIN FINISH NIKALOY TOP	Г	T	-84	STAINLESS STEEL MESH BUCKET LINER
Г		-2	SATIN FINISH BRONZE TOP	Г	T	-88	SUPPLEMENTARY STRAINER
		-7	DUCTILE IRON GRATE	Г	T	-92	GALVANIZED CAST IRON PARTS
		-15	CHAINED GRATE	Г	\blacksquare	-T	THREADED OUTLET
		-VP	SECURED GRATE, VANDAL-PROOF			-X	INSIDE CAULK OUTLET
		-ARE	ACID-RESISTING EPOXY	Г	T	-Y	HUB OUTLET WITH GASKET
		-44	FIXED EXTENSION, CAST IRON (3" STD OR SPECIFY HEIGHT)		T	-Z	NO-HUB OUTLET
		-44-92	FIXED EXTENSION, GALVANIZED (3" STD. OR SPECIFY HEIGHT)				SEE 32100 SUBMITTAL FOR OTHER DIMENSIONS, DETAILS, AND OPTIONS.

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

PIPE SIZE

2"

3"

4"

JOSAM COMPANY MICHIGAN CITY, INDIANA

SPECIFICATION:

TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR


USE OF SUPERSEDED OR VOID DATA

JOSAM 32100-AE SERIES COATED CAST IRON LEVELEZE FLOOR DRAIN, TWO PIECE BODY WITH DOUBLE DRAINAGE FLANGE. WEJLOC® NON-PUNCTURING FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET, ROUND TOP, ADJUSTABLE COLLAR WITH ROLLED THREAD AND MEDIUM-DUTY LOOSE-SET ANTI-TILTING SUPER-FLO GRATE WITH PERIMETER DRAINAGE SLOTS.

FLOOR DRAIN

9" ROUND TOP LEVELEZE®, SUPER-FLO®

32100-AE **SERIES**



Х	-AE	LEVELEZE ADJUSTABLE EXTENSION		-39	SOLID CAST IRON COVER	
Г			П	-VP	SECURED GRATE, VP SCREWS	
Г				-ARE	ACID-RESISTING EPOXY COATING	
	-TG	TRACTOR GRATE		-49	3/4" PRIMER TAP	
	-HP	HEEL-PROOF GRATE, CI, 5/16" SLOT WIDTH, 25 SQ IN FREE AREA		-50	1/2" PRIMER TAP	
	-1	SATIN FINISH NIKALOY TOP		-66	NO-HUB SIDE OUTLET	
	-2	SATIN FINISH BRONZE TOP			SLOTTED CAST IRON BUCKET	
	-7	DUCTILE IRON GRATE			SUPPLEMENTARY STRAINER	
	-11	EXTRA HEAVY-DUTY GRATE, CAST IRON		-92	GALVANIZED CAST IRON PARTS	
П	-13	DOME GRATE, CAST IRON		-T	THREADED OUTLET	
П	-13-1	DOME GRATE, NIKALOY		-X	INSIDE CAULK OUTLET □	
П	-13-2 DOME GRATE, BRONZE		П	-Y	HUB OUTLET WITH GASKET □	
	-15 CHAINED GRATE			-Z	NO-HUB OUTLET	
DA	TE OF L	AST CHANGE: 04/25/15	$\overline{}$	845	NOTES	
	DIMENSIONS ARE SUBJECT TO MANUFACTURERS JOSAM COMPANY					


MICHIGAN CITY, INDIANA


JOSAM 32100-AE-81 SERIES COATED CAST IRON LEVELEZE FLOOR DRAIN, TWO PIECE BODY WITH DOUBLE DRAINAGE FLANGE, WEJLOC NON-PUNCTURING FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET, ADJUSTABLE COLLAR WITH ROLLED THREAD AND ROUND TOP WITH REMOVABLE SEDIMENT BUCKET THAT SUPPORTS A MEDIUM-DUTY LOOSE-SET ANTI-TILTING SUPER-FLO GRATE WITH PERIMETER DRAINAGE SLOTS

FLOOR DRAIN

9" ROUND TOP LEVELEZE®, SUPER-FLO®

32100-AE-81 SERIES





OPTIONS:

X	-AE	LEVELEZE ADJUSTABLE EXTENSION	-50	1/2" PRIMER TAP
Х	-81	SLOTTED CAST IRON BUCKET	-66	NO-HUB SIDE OUTLET
	-1	SATIN FINISH NIKALOY TOP	-84	STAINLESS STEEL MESH BUCKET LINER
	-2	SATIN FINISH BRONZE TOP	-88	SUPPLEMENTARY STRAINER
	-7	DUCTILE IRON GRATE	-92	GALVANIZED CAST IRON PARTS
	-15	CHAINED GRATE	-T	THREADED OUTLET
	-VP	SECURED GRATE, VP SCREWS	-X	INSIDE CAULK OUTLET
	-ARE	ACID-RESISTING EPOXY COATING	-Y	HUB OUTLET WITH GASKET
	-49	3/4" PRIMER TAP	-Z	NO-HUB OUTLET

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

SPECIFICATION:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS.

TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR


USE OF SUPERSEDED OR VOID DATA.

JOSAM 32100-AE-LC1-88 SERIES COATED CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE, WEJLOC® NON-PUNCTURING FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET, ROUND SATIN NIKALOY HINGED KEY-LOCKING COVER, ADJUSTABLE COLLAR AND INTERNAL STRAINER.

FLOOR DRAIN

9" ROUND TOP, LOCKING COVER

SERIES 32100-AE-LC1-88



	2"	PIPE SIZE		-39	SOLID CAST IRON COVER	
	3"	PIPE SIZE		-VP	SECURED GRATE, VANDAL-PROOF SCREWS	
	4"	PIPE SIZE		-ARE	ACID-RESISTING EPOXY	
Х	-AE	LEVELEZE @ ADJUSTABLE EXTENSION		-44	FIXED EXTENSION COLLAR, CAST IRON (SPEC. HT.) 3" STD.	
	-81	SLOTTED CAST IRON BUCKET		-44-92	FIXED EXTENSION COLLAR, GALVANIZED (SPEC. HT.) 3" STD.	
	-TG	TRACTOR GRATE		-49	3/4" PRIMER TAP	
Х	-LC1	LOCKING COVER, SATIN FINISH NIKALOY		-50	1/2" PRIMER TAP	
	-LC2	LOCKING COVER, SATIN FINISH BRONZE		-84	STAINLESS STEEL MESH BUCKET LINER	
	-1	SATIN FINISH NIKALOY TOP	X	-88	SUPPLEMENTARY STRAINER	
	-2	SATIN FINISH BRONZE TOP		-92	GALVANIZED CAST IRON PARTS	
	-7	DUCTILE IRON GRATE		-66	NO-HUB SIDE OUTLET	
	-11	EXTRA-HEAVY GRATE, CAST IRON				
	-13	DOME GRATE, CAST IRON		-T	THREADED OUTLET	
	-13-1	DOME GRATE, NIKALOY		-X	INSIDE CAULK OUTLET	
	-13-2	DOME GRATE, BRONZE		-Y	HUB OUTLET WITH GASKET	
	-15	CHAINED GRATE		-Z	NO-HUB OUTLET	
DA	DATE OF LAST CHANGE: 04/25/15 NOTES					

JOSAM COMPANY


MICHIGAN CITY, INDIANA

JOSAM 3210-AE-TG SERIES COATED CAST IRON LEVELEZ®FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE, WEEPHOLES, WEJLOC®NON-PUNCTURING FLASHING COLLAR, BOTTOM OUTLET, ROUND TOP, ADJUSTABLE COLLAR WITH ROLLED THREAD AND HEAVY-DUTY, DEEP-SET TRACTOR GRATE.

FLOOR DRAIN

9" ROUND TOP, TRACTOR GRATE

SERIES 32100-AE-TG



Х	-AE	LEVELEZE® ADJUSTABLE EXTENSION	-49	3/4" PRIMER TAP
X	-TG	TRACTOR GRATE	-50	1/2" PRIMER TAP
	-1	SATIN FINISH NIKALOY TOP	-88	SUPPLEMENTARY STRAINER
	-2	SATIN FINISH BRONZE TOP	-92	GALVANIZED CAST IRON PARTS
	-7	DUCTILE IRON GRATE	-66	NO-HUB SIDE OUTLET
	-15	CHAINED GRATE	-T	THREADED OUTLET
	-VP	SECURED GRATE, VANDAL-PROOF SCREWS	-X	INSIDE CAULK OUTLET
	-ARE	ACID-RESISTING EPOXY	-Y	HUB OUTLET WITH GASKET
			-7	NO-HUR OUTLET

PIPE

SIZE

DATE OF LAST CHANGE: 04/25/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

PIPE SIZE

3"

4"

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

-Z (NO-HUB) OUTLET SHOWN

SPECIFICATION:


USE OF SUPERSEDED OR VOID DATA

JOSAM 32100-TG SERIES COATED CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE, WEEPHOLES, WEJLOO®NON-PUNCTURING FLASHING COLLAR, BOTTOM OUTLET, ROUND TOP WITH HEAVY-DUTY, LOOSE-SET TRACTOR GRATE.

FLOOR DRAIN

9" ROUND TOP, TRACTOR GRATE

SERIES **32100-TG**




JOSAM 32150 SERIES COATED CAST IRON FLOOR DRAINS, TWO-PIECE BODIES WITH DOUBLE DRAINAGE FLANGE, WEEPHOLES, BOTTOM OUTLETS, 9" ROUND TOPS, ONE BODY FURNISHED WITH A SOLID BRONZE PLUG, OTHER BODY FURNISHED WITH AN EXTRA-HEAVY, ANTI-TILLTING, SUPER-FLO® GRATE WITH PERIMETER DRAINAGE SLOTS.

FLOOR DRAIN

9" ROUND TOP, BLOOD DRAIN

SERIES

32150



-1	SATIN FINISH NIKALOY TOP
-2	SATIN FINISH BRONZE TOP
-7	DUCTILE IRON GRATE
-44	FIXED EXTENSION, CAST IRON (3" STD. OR SPECIFY HEIGHT)
-44-92	FIXED EXTENSION, GALVANIZED (3" STD. OR SPECIFY HEIGHT)
-92	GALVANIZED CAST IRON PARTS

-ARE	ACID RESISTING EPOXY
-T	THREADED OUTLET
-X	INSIDE CAULK OUTLET
-Y	HUB OUTLET WITH GASKET
-Z	NO-HUB OUTLET

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM 32160 SERIES COATED CAST IRON FLOOR DRAIN WITH DOUBLE DRAINAGE FLANGE, WEEP-HOLES, BOTTOM OUTLET, INSIDE CAULK CONNECTION, ROUND TOP AND HEAVY-DUTY LOOSE-SET TRACTOR GRATE.

FLOOR DRAIN 9" ROUND TRACTOR TOP

32160 **SERIES**



				≜ C	ANNOT BE	INSTALLED W	THH (-60) BACKWATER VALVE OPTION
	3"	PIPE SIZE ("F" DIM. = 10 - 7/8")			-54-92	2" AUXILARY	SPIGOT INLET, GALVANIZED
	4"	PIPE SIZE ("F" DIM. = 11 - 1/4")			-60	BACKWATER	VALVE
			Т	\blacksquare	-62	"T"-HANDLE B	RONZE CLOSURE PLUG
	-7	DUCTILE IRON GRATE			-66	NO-HUB SIDE	OUTLET
	-12	SQUARE TOP, CAST IRON		▶	-71	SOLID CAST I	RON BUCKET
	-15	CHAINED GRATE	Т	\blacksquare	-81	SLOTTED CAS	ST IRON BUCKET
	-19	CAST IRON UNDERGRATE W/SATINFINISH NIKALOY TOP		▶	-88	SUPPLEMENT	ARY STRAINER
	-44	FIXED EXTENSION COLLAR (3" STD. OR SPECIFY HT.)	Т		-92	GALVANIZED	CAST IRON PARTS
	-49	3/4" PRIMER TAP	П				
	-50	1/2" PRIMER TAP	Т		-ARE	ACID-RESISTI	NG EPOXY
	-51	1-1/2" AUXILARY THREADED INLET			-92	GALVANIZED (CAST IRON PARTS
	-52	2" AUXILARY THREADED INLET			-ARE	ACID RESISTA	NT EPOXY COATING
	-53	2" AUXILARY HUB INLET	Т		-VP	SECURED GR	ATE, VANDAL-PROFF SCREWS
	-54	2" AUXILARY SPIGOT INLET					
	-53-92	2" AUXILARY HUB INLET, GALVANIZED		Х	-x	INSIDE CAULE	OUTLET
		ST CHANGE: 04/25/15	~	$\overline{}$	MD	ANV	NOTES
DIM	ENSIONS AF	RE SUBJECT TO MANUFACTURERS JOSAM	C	U	IVI P	ANI	l

MICHIGAN CITY, INDIANA

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR


USE OF SUPERSEDED OR VOID DATA

SPECIFICATION: FLOOR DE

JOSAM 32200 SERIES COATED CAST IRON FLOOR DRAIN, SHALLOW TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE, WEJLOC⊗ NON-PUNCTURING FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET, ROUND TOP, MEDIUM-DUTY LOOSE-SET ANTI-TILTING SUPER-FLO GRATE WITH PERIMETER DRAINAGE SLOTS. FLOOR DRAIN

12" ROUND TOP, SUPER-FLO®

SERIES 32200



		-1	SATIN FINISH NIKALOY TOP	Δ		-81	SLOTTED CAST IRON BUCKET
		-2	SATIN FINISH BRONZE TOP			-84	SS MESH BUCKET LINER (MUST SPEC81)
Δ		-4	SECONDARY FLASH. CLAMP (W/-AE ONLY)			-88	SUPPLEMENTARY STRAINER
		-7	DUCTILE IRON GRATE			-92	GALVANIZED CAST IRON PARTS
		-13	DOME GRATE, CAST IRON			-AE	LEVELEZE ADJUSTABLE EXTENSION
		-13-1	DOME GRATE, NIKALOY			-ARE	ACID-RESISTANT EPOXY COATING
		-13-2	DOME GRATE, BRONZE	Δ		-SD	SPECIAL-DUTY GRATE
		-15	CHAINED GRATE			-HP	HEEL-PROOF GRATE, CI, 5/16" SLOT WIDTH, 25 SQ IN FREE AREA
		-44	FIXED EXTENSION, CI (2" STD OR SPECIFY)			-VP	SECURED GRATE, VP SCREWS
		-44-92	FIXED EXTENSION, GALVANIZED			-T	THREADED OUTLET
		-49	3/4" PRIMER TAP			-X	INSIDE CAULK OUTLET
		-50	1/2" PRIMER TAP			-Y	HUB OUTLET W/ GASKET (2" - 4" SIZES ONLY)
		-66	NO-HUB SIDE OUTLET (2" - 6")			-Z	NO-HUB OUTLET
△SEPARATE SUBMITTAL AVIALABLE FOR THIS OPTION AVAILABLE							

DE OUTLET (2"	- 6")		П	-Z	NO-HUB OUTLET
TAL AVIALABLI	E FOR THIS OPTION	N A	VAI	LABLE	
04/25/15	10041		_		
MANUFACTURERS	JOSAM		C	ON	/IPANY

MICHIGAN CITY, INDIANA

NOTES

SPECIFICATION:

SLOT WIDTH 9/16"

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR


USE OF SUPERSEDED OR VOID DATA

JOSAM 32200-13 SERIES COATED CAST IRON FLOOR DRAIN, SHALLOW TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE, WELLOC® NON-PINCTURING FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET, ROUND TOP, MEDIUM-DUTY LOOSE-SET ANTI-TILTING SUPER-FLO® DOME WITH PERIMITER BRAINAGE SI OTS.

FLOOR DRAIN

12" DOME TOP, SUPER-FLO®

SERIES **32200-13**



	2"	PIPE SIZE	-15	CHAINED GRATE		
Г	3"	PIPE SIZE	-ARE	ACID-RESISTING EPOXY		
	4"	PIPE SIZE	-VP	SECURED GRATE, VANDAL-PROOF SCREWS		
	5"	PIPE SIZE	-44	FIXED EXTENSION COLLAR, C.I. (SPEC. HT.) 2" STD.		
	6"	PIPE SIZE	-44-92	FIXED EXTENSION COLLAR, GALV. (SPEC. HT.) 2" STD.		
	8"	PIPE SIZE	-49	3/4" PRIMER TAP		
			-50	1/2" PRIMER TAP		
	-AE	LEVELEZE® ADJUSTABLE EXTENSION	-84	STAINLESS STEEL MESH BUCKET LINER		
	-81	SLOTTED CAST IRON BUCKET		SUPPLEMENTARY STRAINER		
	-SD	SPECIAL-DUTY GRATE	-92	GALVANIZED CAST IRON PARTS		
	-1	SATIN FINISH NIKALOY TOP				
	-2	SATIN FINISH BRONZE TOP	-66	NO-HUB SIDE OUTLET (2" - 6" ONLY)		
	-4	SECONDARY FLASHING CLAMP (USE WITH -AE ONLY)				
	-7	DUCTILE IRON GRATE	-T	THREADED OUTLET		
X	-13	DOME GRATE, CAST IRON	-X	INSIDE CAULK OUTLET		
	-13-1	DOME GRATE, NIKALOY	-Y	HUB OUTLET WITH GASKET (2" THRU 4" SIZES)		
	-13-2	DOME GRATE, BRONZE	-Z	NO-HUB OUTLET		
DA.	TE OF LA	ST CHANGE: 04/25/15		NOTES		

JOSAM COMPANY

MICHIGAN CITY, INDIANA


JOSAM 32200-81 SERIES COATED CAST IRON FLOOR DRAIN, SHALLOW TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE, WEJLOC® NON-PUNCTURING FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET, ROUND TOP WITH REMOVABLE SEDIMENT BUCKET THAT SUPPORTS A MEDIUM-DUTY LOOSE-SET ANTI-TILTING SUPER-FLO GRATE WITH PERIMETER DRAINAGE SLOTS.

FLOOR DRAIN

12" ROUND TOP, SUPER-FLO®

SERIES

32200-81



	OATHVI HVIOTI BITOTVZE TOI	-0-	SO MEST BOOKET ENTER (MOST SI EG61)
-4	SECONDARY FLASH. CLAMP (W/-AE ONLY)	-88	SUPPLEMENTARY STRAINER
-7	DUCTILE IRON GRATE	-92	GALVANIZED CAST IRON PARTS
-13	DOME GRATE, CAST IRON	-AE	LEVELEZE ADJUSTABLE EXTENSION
-13-1	DOME GRATE, NIKALOY	-ARE	ACID-RESISTANT EPOXY COATING
-13-2	DOME GRATE, BRONZE	-SD	SPECIAL-DUTY GRATE
-15	CHAINED GRATE	-HP	HEEL-PROOF GRATE, CI, 5/16" SLOT WIDTH, 25 SQ IN FREE AREA
-44	FIXED EXTENSION, CI (2" STD OR SPECIFY)	-VP	SECURED GRATE, VP SCREWS
-44-92	FIXED EXTENSION, GALVANIZED	-T	THREADED OUTLET
-49	3/4" PRIMER TAP	-X	INSIDE CAULK OUTLET
-50	1/2" PRIMER TAP	-Y	HUB OUTLET W/ GASKET (2" - 4" SIZES ONLY)
-66	NO-HUB SIDE OUTLET (2" - 6")	-Z	NO-HUB OUTLET

DATE OF LAST CHANGE: 12/23/14 **JOSAM COMPANY** IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA USE OF SUPERSEDED OR VOID DATA.

SATIN FINISH NIKALOY TOP

SATIN FINISH BRONZE TOP

-1

SLOTTED CAST IRON BUCKET

-84 SS MESH BLICKET LINER (MUST SPEC -81)


SPECIFICATION:

JOSAM 32200-AE SERIES COATED CAST IRON LEVELEZE® FLOOR DRAIN WITH ROUND TOP, GRATE SUPPORT COLLAR WITH DOUBLE DRAINAGE FLANGE AND WEEPHOLES, BOTTOM OUTLET, ADJUSTABLE UNAILY PLANGE AND WEEPHOLES, BUTTOM OUTLET, ADJUSTAB COLLAR, SUPPORT RING, LARGE SUMP BODY AND A MEDIUM-DUTY LOOSE-SET ANTI-TILTING SUPER-FLO® GRATE WITH PERIMETER DRAINAGE SLOTS.

FLOOR DRAIN

12" ROUND SUPER-FLO® TOP LEVELEZE®

32200-AE **SERIES**



	-1	SATIN FINISH NIKALOY TOP	Δ		-81	SLOTTED CAST IRON BUCKET
	-2	SATIN FINISH BRONZE TOP			-84	SS MESH BUCKET LINER (MUST SPEC81)
Δ	-4	SECONDARY FLASH. CLAMP (W/ -AE ONLY)			-88	SUPPLEMENTARY STRAINER
	-7	DUCTILE IRON GRATE			-92	GALVANIZED CAST IRON PARTS
	-13	DOME GRATE, CAST IRON		Х	-AE	LEVELEZE ADJUSTABLE EXTENSION
	-13-1	DOME GRATE, NIKALOY			-ARE	ACID-RESISTANT EPOXY COATING
	-13-2	DOME GRATE, BRONZE	Δ		-SD	SPECIAL-DUTY GRATE
	-15	CHAINED GRATE			-HP	HEEL-PROOF GRATE, CI, 5/16" SLOT WIDTH, 25 SQ IN FREE AREA
	-44	FIXED EXTENSION, CI (2" STD OR SPECIFY)			-VP	SECURED GRATE, VP SCREWS
	-44-92	FIXED EXTENSION, GALVANIZED			-T	THREADED OUTLET
	-49	3/4" PRIMER TAP			-X	INSIDE CAULK OUTLET
	-50	1/2" PRIMER TAP			-Y	HUB OUTLET W/ GASKET (2" - 4" SIZES ONLY)
	-66	NO-HUB SIDE OUTLET (2" - 6")			-Z	NO-HUB OUTLET

Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE

DATE OF LAST CHANGE: IMENSIONS ARE SUBJECT TO MANUFACTURERS. TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.


JOSAM COMPANY MICHIGAN CITY, INDIANA

JOSAM 32200-AE-31 SERIES COATED CAST IRON LEVELEZE® FLOOR DRAIN WITH ROUND TOP, GRAITE SUPPORT COLLAR WITH POUBLE DRAINAGE FLANGE AND WEEPHOLES, BOTTOM OUTLET, ADJUSTABLE COLLAR, SUPPORT RING, LARGE SUMP BODY, REMOVABLE SEDIMENT BUCKET WHICH SUPPORTS A MEDIUM-DUTY LOOSE-SET ANTI-TILTING SUPER-FLOØ GRAITE WITH PERIMETER DRAINAGE SLOTS.

FLOOR DRAIN

12" ROUND SUPER-FLO® TOP, LEVELEZE®

SERIES 32200-AE-81



	-2	SATIN FINISH BRONZE TOP		-84	SS MESH BUCKET LINER (MUST SPEC81)
	-4	SECONDARY FLASH. CLAMP (W/-AE ONLY)		-88	SUPPLEMENTARY STRAINER
	-7	DUCTILE IRON GRATE		-92	GALVANIZED CAST IRON PARTS
	-13	DOME GRATE, CAST IRON	Х	-AE	LEVELEZE ADJUSTABLE EXTENSION
	-13-1	DOME GRATE, NIKALOY		-ARE	ACID-RESISTANT EPOXY COATING
	-13-2	DOME GRATE, BRONZE		-SD	SPECIAL-DUTY GRATE
	-15	CHAINED GRATE		-HP	HEEL-PROOF GRATE, CI, 5/16" SLOT WIDTH, 25 SQ IN FREE AREA
	-44	FIXED EXTENSION, CI (2" STD OR SPECIFY)		-VP	SECURED GRATE, VP SCREWS
	-44-92	FIXED EXTENSION, GALVANIZED		-T	THREADED OUTLET
П	-49	3/4" PRIMER TAP		-X	INSIDE CAULK OUTLET
П	-50	1/2" PRIMER TAP		-Y	HUB OUTLET W/ GASKET (2" - 4" SIZES ONLY)
П	-66	NO-HUB SIDE OUTLET (2" - 6")		-Z	NO-HUB OUTLET

DATE OF LAST CHANGE: 12/23/14

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

SATIN FINISH NIKALOY TOP

JOSAM COMPANY
MICHIGAN CITY, INDIANA

NOTES

SLOTTED CAST IRON BUCKET


SPECIFICATION:

JOSAM 32200-AE-SD SERIES COATED CAST IRON LEVELEZ® FLOOR DRAIN WITH ROUND TOP, GRATE SUPPORT COLLAR WITH DOUBLE DRAINAGE FLANGE AND WEEPHOLES, BOTTOM OUTLET, ADJUSTABLE COLLAR, SUPPORT RING, LARGE SUMP BODY AND LOOSE-SET SPECIAL-DUTY GRATE.

FLOOR DRAIN

12" ROUND SPECIAL-DUTY TOP, LEVELEZE®

SERIES 32200-AE-SD



X	-AE	LEVELEZE® ADJUSTABLE EXTENSION				
	-81	SLOTTED CAST IRON BUCKET				
Х	-SD	SPECIAL-DUTY GRATE				
	-1	SATIN FINISH NIKALOY TOP				
	-2	SATIN FINISH BRONZE TOP				
	-4	SECONDARY FLASHING CLAMP				
	-15	CHAINED GRATE				
	-49	3/4" PRIMER TAP				
	-50	1/2" PRIMER TAP				
	-66	NO-HUB SIDE OUTLET (2"-6")				
A SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE						

-44	FIXED EXTENSION, CAST IRON (2" STD. OR SPEC. HEIGHT)
-44-92	FIXED EXTENSION, GALVANIZED (2" STD. OR SPEC. HEIGHT)
-84	SS MESH BUCKET LINER (MUST SPECIFY -81 BUCKET)
-88	SUPPLEMENTARY STRAINER
-92	GALVANIZED CAST IRON PARTS
-VP	SECURED GRATE, VANDAL-PROOF SCREWS
-ARE	ACID-RESISTING EPOXY
-T	THREADED OUTLET
-X	INSIDE CAULK OUTLET
-Y	HUB OUTLET WITH GASKET (2"-4") SIZES ONLY
-Z	NO-HUB OUTLET
	-44-92 -84 -88 -92 -VP -ARE -T -X

DATE OF LAST CHANGE: 10/30/14

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA


JOSAM 32200-SD SERIES COATED CAST IRON FLOOR DRAIN, SHALLOW TWO-PEICE BODY WITH DOUBLE DRAINAGE FLANGE, WEJLOC® NON-PUNCTURING FLASHING CLAMP, WEEPHOLES, BOTTOM OUTLET, ROUND TOP AND LOOSE-SET SPECIAL-DUTY GRATE.


FLOOR DRAIN

12" ROUND TOP, SPECIAL-DUTY

SERIES

32200-SD





-44

Δ		-AE	LEVELEZE® ADJUSTABLE EXTENSION
Δ	Δ -81		SLOTTED CAST IRON BUCKET
	х	-SD	SPECIAL-DUTY GRATE
		-1	SATIN FINISH NIKALOY TOP
		-2	SATIN FINISH BRONZE TOP
		-15	CHAINED GRATE
		-49	3/4" PRIMER TAP
		-50	1/2" PRIMER TAP
		-66	NO-HUB SIDE OUTLET (2" -6")
			•

T	-66	NO-HUB SIDE OUTLET (2"
S	EPARA PTION /	TE SUBMITTAL FOR THIS AVAILABLE

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.

DATE OF LAST CHANGE:

0	• 4	A I	VI C	OMDANY NOTES						
			-Z	NO-HUB OUTLET						
			-Y	HUB OUTLET WITH GASKET (2"-4") SIZES ONLY						
			-X	INSIDE CAULK OUTLET						
			-T	THREADED OUTLET						
			-ARE	ACID-RESISTING EPOXY						
			-VP	SECURED GRATE, VANDAL-PROOF SCREWS						
			-92	GALVANIZED CAST IRON PARTS						
	-88 SUPPLEMENTARY STRAINER									
			-84	SS MESH BUCKET LINER						

FIXED EXTENSION, CAST IRON (2" STD. OR SPEC. HEIGHT)

-44-92 FIXED EXTENSION, GALVANIZED (2" STD. OR SPEC. HEIGHT)

JOSAM CUMPANT MICHIGAN CITY, INDIANA


SPECIFICATION:

JOSAM 32300 SERIES COATED CAST IRON FLOOR DRAIN, MEDIUM-DEEP TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE, WEJLOC® NON-PUNCTURING CLAMP COLLAR, WEEPHOLES, BOTTOM OUTLET, ROUND-TOP, MEDIUM-DUTY LOOSE-SET ANTI-TILTING SUPER-FLO® GRATE WITH PERIMETER DRAINAGE SLOTS.

FLOOR DRAIN

12" ROUND SUPER-FLO® TOP MEDIUM SUMP

32300 **SERIES**



-1	SATIN FINISH NIKALOY TOP			
-2	SATIN FINISH BRONZE TOP			
-7	DUCTILE IRON GRATE			
-13 DOME GRATE, CAST IRON				
-13-1 DOME GRATE, NIKALOY				
-13-2	DOME GRATE, BRONZE			
-15	CHAINED GRATE			
-44	FIXED EXTENSION, CAST IRON (2" STD. OR SPEC. HEIGHT)			
-44-92	FIXED EXTENSION, GALVANIZED (2" STD. OR SPEC. HEIGHT)			
-49	3/4" PRIMER TAP			

Δ SEPARATE SUBMITTAL FOR THIS	
OPTION AVAILABLE	

J
_

IOSAM COMPANY MICHIGAN CITY, INDIANA

-50 1/2" PRIMER TAP

-66 NO-HUB SIDE OUTLET (2"-6")

-SD SPECIAL-DUTY GRATE

INSIDE CAULK OUTLET NO-HUB OUTLET

-81 SLOTTED CAST IRON BUCKET -84 SS MESH BUCKET LINER (MUST SPECIFY -81 BUCKET) SUPPLEMENTARY STRAINER -92 GALVANIZED CAST IRON PARTS ARE ACID-RESISTING EPOXY

NOTES

SECURED GRATE, VANDAL-PROOF SCREWS

HEEL-PROOF GRATE, CI, 5/16" SLOT WIDTH, 25 SQ. IN FREE AREA

JOSAM 32300-81 SERIES COATED CAST IRON FLOOR DRAIN,

OUTLET, ROUND-TOP, REMOVABLE SEDIMENT BUCKET WHICH SUPPORTS A MEDIUM-DUTY LOOSE-SET ANTI-TILTING

SUPER-FLO® GRATE WITH PERIMETER DRAINAGE SLOTS


MEDIUM-DEEP TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE,

WEJLOC® NON-PUNCTURING CLAMP COLLAR, WEEPHOLES, BOTTOM

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.



JOSAM COMPANY

MICHIGAN CITY, INDIANA

SPECIFICATION:

FLOOR DRAIN

12" ROUND SUPER-FLO® TOP

MEDIUM SUMP

SERIES


32300-81

JOSAM 2230 SERIES COATED CAST IRON FLOOR DRAIN, DEEP TWO PIECE BODY WITH DOUBLE DRAINAGE FLANGE, WELLOC® NON-PUNTURING CLAMP COLLAR, WEEPHOLES, BOTTOM OUTLET, ROUND-TOP AND REMOVABLE SEDIMENT BLUCKET WHICH SUPPORTS A MEDIUM-DUTY LOGSE-SET ANTI-TILTING SUPER-FLO® GRATE WITH PERIMETER DRAINAGE SLOTS.

FLOOR DRAIN

12" FLOOR SUPER-FLO® TOP, DEEP SUMP WITH BUCKET

SERIES 32330



DATE OF LAST CHANGE: 6/19/14

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANGES AND CHANGE WITHOUT NOTICE.

WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERRSEDED OR VOID DATA.

Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE

JOSAM COMPANY MICHIGAN CITY, INDIANA


JOSAM 32330-SD SERIES COATED CAST IRON FLOOR DRAIN WITH DOUBLE DRAINAGE FLANGE, WEJLOC®, NON-PUNTURING CLAMP COLLAR, WEEPHOLES, BOTTOM OUTLET, ROUND TOP, REMOVABLE SEDIMENT BUCKET AND SPECIAL-DUTY LOOSE-SET GRATE.

FLOOR DRAIN

12" FLOOR TOP, DEEP SUMP WITH BUCKET

32330-SD **SERIES**





Х	-SD	SPECIAL-DUTY GRATE	
	-15	CHAINED GRATE	Γ
	-19	CAST IRON UNDERGRATE WITH SATIN FINISH NIKALOY TOP	Γ
	-20	CAST IRON UNDERGRATE WITH SATIN FINISH BRONZE TOP	Γ
	-44	FIXED EXTENSION, CAST IRON (1" STD. OR SPECIFY HEIGHT)	Γ
	-44-92	FIXED EXTENSION, GALVANIZED (1" STD. OR SPECIFY HEIGHT)	Γ
	-49	3/4" PRIMER TAP	Γ
	-50	1/2" PRIMER TAP	Γ

-66	NO-HUB SIDE OUTLET
-70	LESS BUCKET
-84	STAINLESS STEEL MECH BUCKET LINER
-88	SUPPLEMENTARY STRAINER
-92	GALVANIZED CAST IRON PARTS
-VP	SECURED GRATE, VANDAL-PROOF SCREWS
-X	INSIDE CAULK OUTLET
-Z	NO-HUB OUTLET

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

SPECIFICATION:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR


USE OF SUPERSEDED OR VOID DATA.

JOSAM 34710 SERIES COATED CAST IRON FLOOR DRAIN WITH TWO PIECE BODY, WEJLOC NON-PUNCTURING FLASHING CLAMP COLLAR WITH DOUBLE DRAINAGE FLANGE, WEEPHOLES, BOTTOM OUTLET, ROUND TOP AND EXTRA HEAVY-DUTY LOOSE-SET GRATE.


FLOOR DRAIN EXTRA HEAVY-DUTY TOP

SERIES

34710




					• • • • • • • • • • • • • • • • • • • •				
	4"	PIPE SIZE		-19	CAST IRON UNDERGRATE LAMINATED TOP, NIKALOY				
	5"	PIPE SIZE		-20	CAST IRON UNDERGRATE LAMINATED TOP, BRONZE				
	6"	PIPE SIZE		-49	3/4" PRIMER TAP				
	8"	PIPE SIZE		-50	1/2" PRIMER TAP				
				-88	SUPPLEMENTARY STRAINER				
	-AE	LEVELEZE ADJUSTABLE EXTENSION		-92	GALVANIZED CAST IRON PARTS				
	-ARE	ACID RESISTING EPOXY							
	-VP	SECURED GRATE		-T	THREADED OUTLET				
				-X	INSIDE CAULK OUTLET				
П	-4	SECONDARY FLASHING CLAMP (USE WITH -AE ONLY)		-Y	HUB OUTLET WITH GASKET (4" SIZE ONLY)				
	-7	DUCTILE IRON GRATE		-Z	NO-HUB SPIGOT OUTLET				
	-15	CHAINED GRATE							
DA	DATE OF LAST CHANGE: 04/25/15 NOTES								



SPECIFICATION: JOSAM 3/920 SERIES COATED CAST IRON FLOOR DRAIN WITH DOUBLE DRAINAGE FLANGE, WEEPHOLES, BOTTOM OUTLET, ROUND TOP WITH REMOVABLE SEDIMENT BUCKET DESIGNED SO EXTRA HEAVY-DUTY NON-CLOG GRATE CANNOT BE REPLACED WITHOUT BUCKET IN PLACE.

FLOOR DRAIN NON-CLOG 21" ROUND W/ BUCKET

SERIES 34920



GRATE FREE AREA


14.4 SQ. IN.

JOSAM 35100 SERIES CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE AND 1/2" PRIMER TAP WITH PLUG, WELLOC NON-PUNCTURING FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET, SQUARE TOP WITH HEAVY-DUTY LOOSE-SET GRATE.

FLOOR DRAIN 8" SQUARE TOP

SERIES **35100**

8" SQ Q 9 1/4" 7 1/2" SQ 7 1/2" SQ



- 3/8" TYP

- 11/16"

 GASKET ON Y-CONNECTION CONFORMS WITH ASTM-C564

	-TSO	THREADED SIDE OUTLET	-ARE	ACID-RESISTING EPOXY
	-1	SATIN FINISH NIKALOY TOP	-92	GALVANIZED CAST IRON PARTS
	-2	SATIN FINISH BRONZE TOP	-T	THREADED OUTLET
	-7	DUCTILE IRON GRATE	-X	INSIDE CAULK OUTLET
	-15	CHAINED GRATE	-Y	HUB OUTLET WTIH GASKET
Г	-49	3/4" PRIMER TAP	-Z	NO-HUB SPIGOT OUTLET

DATE OF LAST CHANGE: 04/25/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:

JOSAM 35130 SERIES CAST IRON FLOOR DRAIN, TWO-PIECE BODY, SEEPAGE SLOTS, BOTTOM OUTLET, MEDIUM-DUTY SECURED GRATE AND REMOVABLE SEDIMENT BUCKET, TOP FRAME SERVES AS CLAMP RING.

FLOOR DRAIN

9" SQUARE TOP WITH BUCKET

SERIES **35130**



		-1	SATIN FINISH NIKALOY TOP		Г			
		-2	SATIN FINISH BRONZE TOP		Г			
Δ		-14-1	HINGED GRATE, SATIN FINISHED NIKALOY		Г			
-14-2 HINGED GRATE, SATIN FINISH BRONZE								
		-15	CHAINED GRATE					
		-49	9 3/4" PRIMER TAP					
		-50	1/2" PRIMER TAP					
		-66	NO-HUB SIDE OUTLET					

-70	LESS BUCKET
-84	STAINLESS STEEL MESH BUCKET LINES
-88	SUPPLEMENTARY STRAINER
-92	GALVANIZED CAST IRON PARTS
-ARE	ACID-RESISTING EPOXY
-VP	SECURED GRATE, VANDAL-PROOF SCREWS
-X	INSIDE CAULK OUTLET
-7	NO-HUB SPIGOT OUTLET

Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE

DATE OF LAST CHANGE: 6/17/14

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.


JOSAM COMPANY MICHIGAN CITY, INDIANA

JOSAM 35130-14-1 SERIES CAST IRON FLOOR DRAIN, TWO-PIECE BODY, FLASHING FLANGE, SEEPAGE SLOTS, BOTTOM OUTLET, SQUARE MEDIUM-DUTY SATIN NIKALOY HINGEO BRATE AND REMOVABLE SEDIMENT BUCKET, TOP FRAME SERVES AS CLAMP RING.

FLOOR DRAIN

9" SQUARE HINGED TOP WITH BUCKET

SERIES 35130-14-1



Х	-14-1	HINGED GRATE, SATIN FINISHED NIKALOY
	-49	3/4" PRIMER TAP
	-50	1/2" PRIMER TAP
	-66	NO-HUB SIDE OUTLET
	-70	LESS BUCKET

∠NO-HUB (-Z)

-84	STAINLESS STEEL MESH BUCKET LINER
-92	GALVANIZED CAST IRON PARTS
-ARE	ACID-RESISTING EPOXY
-X	INSIDE CAULK OUTLET
-Z	NO-HUB SPIGOT OUTLET

35130-14-2 SAME, EXCEPT BRONZE TOP USED (FORMERLY 35230-2)

DATE OF LAST CHANGE: 6/17/14

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

JOSAM COMPANY
MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:

JOSAM 35170 SERIES COATED CAST IRON FLOOR DRAIN, BOTTOM OUTLET, SQUARE TOP, MEDIUM-DUTY LOOSE-SET TRACTOR GRATE AND REMOVABLE SEDIMENT BUCKET. FLOOR DRAIN

10" TRACTOR TOP

WITH BUCKET

SERIES 35170



DATE OF LAST CHANGE: 6/17/14

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

3/4" PRIMER TAP

1/2" PRIMER TAP

LESS BUCKET

-49

-50

-70

JOSAM COMPANY
MICHIGAN CITY, INDIANA

-VP

NOTES

SECURED GRATE, VANDAL-PROOF SCREWS

INSIDE CAULK OUTLET

NO-HUB SPIGOT OUTLET

JOSAM 37800 SERIES COATED CAST IRON FLOOR DRAIN WITH FLASHING FLANGE AND 1/2" PRIMER TAP WITH PLUG, SHALLOW BODY, WEJLOO® NON-PUNCTURING FLASHING COLLAR, WEEPHOLES, BOTTOM OUTLET CONNECTION, SQUARE TOP AND HEAVY-DUTY LOOSE-SET GRATE.


FLOOR DRAIN

NOTES

12" HEAVY-DUTY TOP, SHALLOW SUMP

SERIES

37800



JOSAM COMPANY

MICHIGAN CITY, INDIANA


SPECIFICATION:

JOSAM 37810 SERIES COATED CAST IRON FLOOR DRAIN, TWO-PIECE MEDIUM-DEEP BODY WITH DOUBLE DRAINAGE FLANGE, NON-PUNCTURING FLASHING FRAME, WEEPHOLES, BOTTOM OUTLET, SQUARE TOP, HEAVY DUTY LOOSE-SET GRATE AND REMOVABLE SEDIMENT BUCKET.

FLOOR DRAIN

MEDIUM SUMP, 12" HEAVY DUTY TOP

37810 **SERIES**



2"	PIPE SIZE
3"	PIPE SIZE
4"	PIPE SIZE
5"	PIPE SIZE
6"	PIPE SIZE
-X	INSIDE CAULK OUTLET
-Y	PUSH-ON
-Z	NO-HUB
-T	THREADED OUTLET
-AE	LEVELEZE ADJUSTABLE EXTENSION
-4*	SECONDARY FLASHING CLAMP
-7	DUCTILE IRON GRATE
-14	HINGED GRATE

	-VP	SECURED GRATE, VANDAL-PROOF SCREWS
П	-18	HINGED GRATE W/ LATCHING DEVICE
	-19	C.I. UNDERGRATE W/ SATIN NIKALOY TOP
П	-20	C.I. UNDERGRATE W/ SATIN BRONZE TOP
	-39	SOLID CAST IRON COVER
	-49	3/4" PRIMER TAP
	-50	1/2" PRIMER TAP
	-66	NO-HUB SIDE OUTLET
П	-70	LESS BUCKET
	-84	STAINLESS STEEL MESH BUCKET LINER
П	-88	SUPPLEMENTARY STRAINER
	-92	GALVANIZED CAST IRON PARTS
	-ARE	ACID RESISTANT EPOXY COATING
П		
П		

* AVAILABLE WITH -AE ONLY

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR


USE OF SUPERSEDED OR VOID DATA.


DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.

WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.







□ ADD 1/4" WHEN FURNISHED WITH BRONZE OR NIKALOY TOP

∆ 2-1/4" MIN - 4-1/4" MAX WHEN USED WITH (-4) SECONDARY CLAMP

NOTES

FLOOR DRAIN

12" HEAVY-DUTY TOP.

ADJUSTABLE EXTENSION


SERIES

37810-AE

SPECIFICATION: FLOOR DRAIN

JOSAM 37820 SERIES COATED CAST IRON FLOOR DRAIN WITH TWO-PIECE DEEP BODY WITH DOUBLE DRAINAGE FLANGE, NON-PUNCTURING FLASHING FRAME, WEEPHOLES, BOTTOM OUTLET, SQUARE TOP, HEAVY-DUTY LOOSE SET GRATE AND REMOVABLE

12" HEAVY-DUTY TOP, DEEP SUMP



ш	-AE	THREADED LEVELEZE ADJ. EXT.			-50	1/2" PRIMER TAP	
Г	-4	SECONDARY FLASHING CLAMP (-AE ONLY)			-66	NO-HUB SIDE OUT	LET (2"-6" SIZES ONLY)
Е	-7	DUCTILE IRON GRATE			-70	LESS BUCKET	
L	-14	HINGED GRATE			-84	STAINLESS STEEL	MESH BUCKET LINER
Г	-VF	SECURED GRATE, VANDAL-PROOF SCREWS			-88	SUPPLIMENTARY	STRAINER
Г	-18	HINGED GRATE WITH LATCHING DEVICE			-92	GALVANIZED CAS	T IRON PARTS
г	-19	HVY-DUTY DUCTILE UNDERGRATE, SATIN FINIS	H NIKALOY TOP		-ARE	ACID RESISTING E	POXY
Е	-20	HVY-DUTY DUCTILE UNDERGRATE, SATIN FINIS	H BRONZE TOP		-X	INSIDE CAULK OU	TLET
Г	-49	3/4" PRIMER TAP			-Z	NO-HUB SPIGOT (OUTLET
	ATE	OF LAST CHANGE: 04/25/15		_			NOTES
C	IMENS	IONS ARE SUBJECT TO MANUFACTURERS	DSAM C	;С	M	PANY	

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA

JOSAM COMPANY MICHIGAN CITY, INDIANA


JOSAM 37830 SERIES COATED CAST IRON FLOOR DRAIN, DOUBLE DRAINAGE FLANGE, SEEPAGE SLOTS, BOTTOM OUTLET, SQUARE TOP AND HEAVY-DUTY HINGED LATCHING GRATE AND REMOVABLE SEDIMENT BUCKET.

FLOOR DRAIN

12" TOP WITH LATCHING GRATE

SERIES

37830



-7	DUCTILE IRON GRATE			-66	NO-HUB SIDE OUTLET
-19	HVY-DUTY DUCTILE UNDERGRATE, SATIN FINISH NIKALOY TOP	Г	П	-69	LIFT HANDLE FOR SEDIMENT BUCKET
-20	HVY-DUTY DUCTILE UNDERGRATE, SATIN FINISH BRONZE TOP	Г		-84	STAINLESS STEEL MESH BUCKET LINER
-21	LOOSE-SET GRATE	Г		-92	GALVANIZED CAST IRON PARTS
-22	LESS LATCHING GRATE			-X	INSIDE CAULK OUTLET
-49	3/4" PRIMER TAP			-Z	NO-HUB SPIGOT OUTLET
-50	1/2" PRIMER TAP	_			

DATE OF LAST CHANGE: 6/16/14 DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

SPECIFICATION: FLOOR DRAIN JOSAM 37840 SERIES COATED CAST IRON FLOOR DRAIN DOUBLE DRAINAGE FLANGE, SEEPAGE SLOTS, BOTTOM OUTLET, SQUARE 12" TOP WITH BUCKET TOP AND HEAVY-DUTY SECURED GRATE AND REMOVABLE SEDIMENT BUCKET. TOP FRAME SERVES AS CLAMP RING 37840 **SERIES** FORMERLY 35330 SERIES SLOT WIDTH 3/8" (-19 & -20 SLOT WIDTH 3/8") Ø 15 1/4" GRATE FREE AREA 54 SQ. IN. PIPE SIZE - 11 9/16 3" 4" 5" 1ИИИППРПИИИППР/п 6" □ADD 1/4" WHEN FURNISHED 5 5/16' WITH NIKALOY OR BRONZE TOP X = 11 3/16" $Z = 10 \ 15/16$ " -- PIPE SIZE -13 1/4" MIN OPENING -70 LESS BUCKET -7 DUCTILE IRON GRATE SUPPLEMENTARY STRAINER -14 HINGED GRATE STAINLESS STEEL MESH BUCKET LINER -19 HVY-DUTY DUCTILE UNDERGRATE, SATIN FINISH NIKALOY TOP GALVANIZED CAST IRON PARTS -20 HVY-DUTY DUCTILE UNDERGRATE, SATIN FINISH BRONZE TOP -VP SECURED GRATE, VANDAL-PROOF SCREWS -49 3/4" PRIMER TAP INSIDE CAULK OUTLET -50 1/2" PRIMER TAP NO-HUB SIDE OUTLET -66 NO-HUB SIDE OUTLET (2"-6" SIZES ONLY) -Q1 SOLID COVER DATE OF LAST CHANGE: **JOSAM COMPANY** DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR

MICHIGAN CITY, INDIANA

USE OF SUPERSEDED OR VOID DATA

TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR


USE OF SUPERSEDED OR VOID DATA

SPECIFICATION: FLOOR DRAIN

JOSAM 37900 SERIES COATED CAST IRON LEVELEZE © FLOOR DRAIN WITH SQUARE GRATE SET IN SQUARE FRAME, GRATE SUPPORT COLLAR WITH DOUBLE DRAINAGE FLANGE AND WEEPHOLES, BOTTOM OUTLET, ADJUSTABLE COLLAR, SUPPORT RING, LARGE SUMP BODY, REMOVABLE SEDIMENT BUCKET AND HEAVY-DUTY DUCTILE IRON

14" PACKING HOUSE TYPE

37900 **SERIES**




MICHIGAN CITY, INDIANA

SPECIFICATION: JOSAM 37960 SERIES COATED CAST IRON FLOOR DRAIN DOUBLE DRAINAGE FLANGE, WEEPHOLES, BOTTOM OUTLET WITH INSIDE CAULK CONNECTION, SQUARE TOP, MEDIUM-DUTY LOOSE-SET

SUPERFLO® GRATE AND SECONDARY STRAINER.

FLOOR DRAIN 16" SUPER-FLO® TOP

37960 **SERIES**



DATE OF LAST CHANGE:	6/13/14
DIMENSIONS ARE SUBJECT TO MA TOLERANCES AND CHANGE WIT WE CAN ASSUME NO RESPON LISE OF SUPERSTREED OR M	HOUT NOTICE. SIBILITY FOR

-11

-15

-LF

LESS GRATE, NIKALOY

LESS GRATE BRONZE

CHAINED GRATE

EXTRA-HEAVY DUTY GRATE

LESS DOUBLE DRAINAGE FLANGE

JOSAM COMPANY MICHIGAN CITY, INDIANA

-92

-92-LF

NOTES

SS MESH BUCKET LINER (MUST SPECIFY -81)

GALVANIZED CAST IRON PARTS

-92-LG-LF GALV. PARTS, LESS GRATE, LESS FLANGE

GALVANIZED PARTS, LESS FLANGE


ACID RESISTING EPOXY (SEE 49400)

JOSAM 38040 SERIES COATED CAST IRON COMBINATION FLOOR DRAIN AND INTEGRAL DEEP SEAL TRAP, SIDE OUTLET SPIGOT CONNECTION, ROUND TOP, MEDIUM-DUTY LOOSE-SET SUPERFLO® GRATE AND CLEANOUT PROTECTED BY TRACTOR COVER.

FLOOR DRAIN

ROUND TOP AND CLEANOUT

38040 SERIES



PIPE SIZE	B X B	C	E	F	G	н
2"	14-1/8 x 9	21-1/8	5-3/4	13-1/2	16-5/8	4
*3"	16-1/4 x 9	23-13/16	6-3/4	17	19-3/8	5
4"	16-1/4 x 9	23-13/16	6-3/4	17	19-3/8	5

*NOTE: 3" SIZE USES A 4" BODY WITH 4" x 3" REDUCING COUPLING

-1	SATIN FINISH NIKALOY TOP	-51	1-1/2" AUXILARY THREAD INLET
-2	SATIN FINISH BRONZE TOP	-52	2" AUXILARY THREAD INLET
-7	DUCTILE IRON GRATE	-60	BACKWATER VALVE
-11	EXTRA HEAVY-DUTY GRATE	-81	SLOTTED CAST IRON BUCKET
-15	CHAINED GRATE	-81-92	SLOTTED IRON BUCKET, GALVANIZED PARTS
-VP	SECURED GRATE, VANDAL-PROOF SCREWS	-84	SS MESH BUCKET LINER (MUST SPECIFY -81)
-HP	HEEL-PROOF GRATE, CI, 5/16" SLOT WIDTH, 25 SQ IN FREE AREA	-88	SUPPLEMENTAY STRAINER
-49	3/4" PRIMER TAP	-92	GALVANIZED CAST IRON PARTS
-50	1/2" PRIMER TAP		

DATE OF LAST CHANGE: IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:

JOSAM 38250A SERIES COATED CAST IRON COMBINATION FLOOR DRAIN AND INTEGRAL DEEP SEAL TRAP, SIDE OUTLET SPIGOT CONNECTION, ROUND TOP, MEDIUM-DUTY LOOSE-SET GRATE, FLUSH-WITH-FLOOR CLEANOUT AND BALL-FLOAT TYPE BACKWATER VALVE.

FLOOR DRAIN

ROUND TOP W/CLEANOUT & BWV

38250A **SERIES**



SIZE	ØΒ	DIM C	ØD	DIM E	DIM F	DIM G	AREA
2"	9"	15"	8"	4-1/2"	11-7/8"	10-1/2"	17.7
3"	10"	18"	9"	3-7/8"	12-3/4"	13"	18.3
4"	12-1/4"	21"	11"	5-3/8"	15-5/8"	15"	29.4

SATIN FINISH NIKALOY TOP SECURED GRATE, VANDAL-PROOF SCREWS SATIN FINISH BRONZE TOP LESS BACKWATER VALVE CHAINED GRATE GALVANIZED CAST IRON PARTS


DATE OF LAST CHANGE: **JOSAM COMPANY** DIMENSIONS ARE SUBJECT TO MANUFACTURERS. TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA

USE OF SUPERSEDED OR VOID DATA

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.



JOSAM COMPANY MICHIGAN CITY, INDIANA


SPECIFICATION:

JOSAM 38420-IGS SERIES COATED CAST IRON COMBINATION FLOOR EXTRA DEEP DRAIN AND INTEGRAL DEEP SEAL TRAP WITH DOUBLE DRAINAGE FLANGE, WEEPHOLES, SIDE OUTLET HUB VENT CONNECTION, ROUND TOP, FLUSH-WITH-FLOOR CLEANOUT AND REMOVABLE SEDIMENT BUCKET, FUNNEL SHAPED INTERNAL SEAL WITH INTEGRAL RIM DESIGNED SO THAT HEAVY-DUTY GRATE CANNOT BE REPLACED UNLESS FUNNEL IS IN POSITION.

FLOOR DRAIN WITH INTERNAL GAS SEAL

FORMERLY 39420 SERIES

38420-IGS SERIES





BOLTED FLASHING CLAMP DEVICE BACKWATER VALVE STAINLESS STEEL MESH BUCKET LINER GALVANIZED CAST IRON PARTS

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA


JOSAM 38620-40 SERIES COATED CAST IRON COMBINATION FLOOR DRAIN AND INTEGRAL DEEP SEAL TRAP, SIDE OUTLET THREADED CONNECTION, RECTANGULAR TOP, FLUSH-WITH-FLOOR CLEANOUT, REMOVABLE MEDIUM-DEEP SEDIMENT BUCKET AND HEAVY-DUTY HINGED GRATE.

FLOOR DRAIN

13" x 11" TOP WITH HINGED GRATE

SERIES

38620-40



JOSAM 38640 SERIES COATED CAST IRON FLOOR DRAIN WITH SIDE OUTLET HUB CONNECTION, RECTANGULAR TOP, REMOVABLE 13" x 11" TOP W/BUCKET SEDIMENT BUCKET AND EXTRA HEAVY-DUTY HINGED GRATE. 38640 **SERIES** SLOT WIDTH 9/16" (-1 & -2 SLOT WIDTH 9/16") FORMERLY 36640 SERIES 12-7/8 x 10-7/8 11-3/4 x 8-5/8 10-1/8 x 7-3/8 GRATE FREE AREA 1-1/4 43.5 SQ. IN. 8-1/4 PIPE SIZE PIPE SIZE Ε F G 8-3/4 * ADD 1/4" WHEN FURNISHED WITH NIKALOY OR BRONZE TOP 3* 6-1/2 8-7/8 8-1/4 4" 8-7/8 8-5/8 PIPE SIZE -7 DUCTILE IRON GRATE PIPE SIZE LESS BUCKET -70 PIPE SIZE STAINLESS STEEL MESH BUCKET LINER GALVANIZED CAST IRON PARTS SATIN FINISH NIKALOY TOP SATIN FINISH BRONZE TOP SECURED GRATE, VANDAL-PROOF SCREWS

1/2" PRIMER TAP

NOTES

DATE OF LAST CHANGE:

SPECIFICATION:

FLOOR DRAIN


JOSAM 38820 SERIES COATED CAST IRON FLOOR DRAIN WITH FLASHING FLANGE, BOTTOM OUTLET, RECTANGULAR TOP, REMOVABLE DEEP SEDIMENT BUCKET AND MEDIUM-DUTY LOOSE-SET TRACTOR GRATE. TOP FRAME SERVES AS CLAMP RING.

FLOOR DRAIN

15" x 13" TOP WITH TRACTOR GRATE

SERIES





ATE OF	LAST	CHANG	GE:	6/6/14	
IMENSION TOLERAN	ICES AND	CHANG	E WITH	TON TUO	ICE.
	N ASSUM OF SUPE			IBILITY FO IID DATA.	OR

-49

3/4" PRIMER TAP

1/2" PRIMER TAP

JOSAM COMPANY MICHIGAN CITY, INDIANA

-X

INSIDE CAULK OUTLET

NO-HUB SPIGOT OUTLET


SPECIFICATION:


JOSAM 38830 SERIES COATED CAST IRON COMBINATION FLOOR DRAIN AND INTEGRAL DEEP SEAL TRAP WITH DOUBLE DRAINAGE FLANGE. WEEPHOLES, SIDE OUTLET HUB CONNECTION, RECTANGULAR TOP HEAVY-DUTY HINGED GRATE, REMOVABLE DEEP SEDIMENT BUCKET AND INTERNAL BRONZE CLEANOUT.

FLOOR DRAIN

13-3/4" x 14-1/8" TOP WITH HINGED GRATE


38830 **SERIES**





	PIPE SIZE	F	J	
	3"	8-7/8"	5	
	4"	9-3/8"	4-1/2	

☐ ADD 1/4" WHEN FURNISHED WITH NIKALOY OR BRONZE TOP



-1	SATIN FINISH NIKALOY TOP		-49	3/4" PRIMER TAP
-2	SATIN FINISH BRONZE TOP		-50	1/2" PRIMER TAP
-7	DUCTILE IRON GRATE		-84	STAINLESS STEEL MESH BUCKET LINER
-VP	SECURED GRATE, VANDAL-PROOF SCREWS		-92	GALVANIZED CAST IRON PARTS


DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

JOSAM COMPANY

NOTES

MICHIGAN CITY, INDIANA

SPECIFICATION: FLOOR DRAIN JOSAM 38850 SERIES COATED CAST IRON FLOOR DRAIN, BOTTOM OUTLET INSIDE CAULK CONNECTION, RECTANGULAR TOP, HEAVY: DUTY LOOSE-SET GRATE AND REMOVABLE INTERNAL DOME 22" x 14" TOP WITH INTERNAL DOME STRAINER SERIES GRATE FREE AREA: 50.2 IN2 STD. CAST IRON SLOT WIDTH: 13/16"



		(-X)		
	-7	DUCTILE IRON COVER		
	-15	CHAINED GRATE		
	-VP	SECURED GRATE, VANDAL-PROOF SCREWS		
	-92	GALVANIZED CAST IRON PARTS		
TF O	F LAST CH	IANGE: 6/3/14		

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

DATE OF LAST CHANGE: TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.


SPECIFICATION:

JOSAM 38930 SERIES COATED CAST IRON COMBINATION FLOOR DRAIN AND INTEGRAL TRAF WITH DOUBLE DRAINAGE FLANGE, WEEPHOLES, BOTTOM OUTLET INSIDE CAULK CONNECTION, RECTANGULAR TOP, HEAVY-DUTY LOOSE-SET GRATE, REMOVABLE SEDIMENT BUCKET AND FLUSH-WITH-LOOR CLEANOUT.


FLOOR DRAIN


21" x 14-1/2" TOP, CLEANOUT, BUCKET

38930 **SERIES**



JOSAM COMPANY DIMENSIONS ARE SUBJECT TO MANUFACTURERS MICHIGAN CITY, INDIANA





JOSAM 39720 SERIES COATED CAST IRON AREA DRAIN WITH COMPOSITION DECK FLANGE, BOTTOM OUTLET, 11" ROUND TOP, HEAVY-DUTY LOOSE-SET GRATE AND REMOVABLE SEDIMENT BUCKET.

FLOOR DRAIN


11" TOP COMPOSITION DECK FLANGE

SERIES

39720

SLOT WIDTH 5/8" (-1 & -2 SLOT WIDTH 1/2")

 ADD 1/4" WHEN FURNISHED W/ NIKALOY OR BRONZE TOP



- -1 SATIN FINISH NIKALOY TOP
 - -2 SATIN FINISH BRONZE TOP
 - -7 DUCTILE IRON GRATE
- -13 DOME GRATE, CAST IRON -13-1 DOME GRATE, NIKALOY -13-2 DOME GRATE, BRONZE

- -15 CHAINED GRATE
 -VP SECURED GRATE, VANDAL-PROOF SCREWS
 -70 LESS BUCKET
 - -70 LESS BUCKET
 -92 GALVANIZED CAST IRON PARTS
 - -T THREADED OUTLET
 - X INSIDE CAULK OUTLET

DRAWING No. 05/16/08

A-10972-K JOSAM COMPANY
MICHIGAN CITY, INDIANA

NOTES:


SPECIFICATION:

JOSAM 39960 SERIES COATED CAST IRON FLOOR DRAIN, BOTTOM OUTLET, INSIDE CAULK CONNECTION AND SQUARE TOP WITH ROUND HINGED GRATE.

FLOOR DRAIN

SQUARE TOP W/ HINGED GRATE

SERIES 39960




-ARE ACID-RESISTING EPOXY
-92 GALVANIZED CAST IRON PARTS

DATE OF LAST CHANGE: 04/27/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

Cast Stainless Steel Butt-Weld Outlet Connection Data

Josam cast stainless steel drains and cleanouts are regularly furnished with Schedule 40S butt-weld outlet connections. Butt-weld outlet connections can also be furnished in Schedule 10S and 80S as specified.




PIPE SCHEDULE	PIPE SIZE 2"	PIPE SIZE 2"	PIPE SIZE 3"	PIPE SIZE 3"	PIPE SIZE 4"	PIPE SIZE 4"	PIPE SIZE 6"	PIPE SIZE 6"	PIPE SIZE 8"	SIZE 8"
Dimension	А	В	А	В	Α	В	А	В	А	В
105	2.157	2.375	3.260	3.500	4.260	4.500	6.357	6.625	8.329	8.625
40\$	2.067	2.375	3.068	3.500	4.026	4.500	6.065	6.625	7.981	8.625
80S	1.939	2.375	2.900	3.500	3.826	4.500	5.761	6.625	7.625	8.625

JOSAM 30000-A-SS-T SERIES TYPE 316 CAST STAINLESS STEEL FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE, WEJLOC® INVERTIBLE FLASHING COLLAR, WEEPHOLES, BOTTOM THREADED OUTLET CONNECTION AND ADJUSTABLE ROUND SUPER-FLO® STRAINER.

STAINLESS STEEL

ADJUSTABLE FLOOR DRAIN

SERIES 30000-A-SS-T



	STAINER	В	×	Y	FREE AREA (SQ. IN.)
	-5A-SS	5	3/4"	2-1/8"	7.8
	-6A-SS	6	1-1/4"	2-3/8"	11.0
	-7A-SS	7	1-1/8"	2-7/8"	13.2
	-8A-SS	8	1-5/8"	2-5/8"	16.2

	-VP	SECURED GRATE, VANDAL-PROOF SCREWS
	-49	3/4" PRIMER TAP
П	-50	1/2" PRIMER TAP
П	-80	PERFORATED STAINLESS STEEL BASKET

USE OF SUPERSEDED OR VOID DATA.

3" 4"

NOTES

PIPE SIZE

DATE OF LAST CHANGE: **JOSAM COMPANY** DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

MICHIGAN CITY, INDIANA

DATE OF LAST CHANGE: IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

SPECIFICATION:

JOSAM SERIES 30000-E-SS STAINLESS STEEL FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE AND 1/2" PRIMER TAP, WEJLOC®INVERTIBLE FLASHING COLLAR, WEEPHOLES, BOTTOM

OUTLET CONNECTION AND STAINLESS STEEL ADJUSTABLE ROUND STRAINER WITH TRACTOR GRATE.


PIPE SIZE -22 6" DIAMETER FUNNEL SECURED GRATE, VANDAL-PROOF SCREWS -T THREADED OUTLET -50 1/2" PRIMER TAP

> **JOSAM COMPANY** MICHIGAN CITY, INDIANA

NOTES

FLOOR DRAIN ADJUSTABLE FLOOR DRAIN


30000-E-SS **SERIES**



JOSAM 30000-S-SS-T SERIES TYPE 316 CAST STAINLESS STEEL FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE, WEJLOC® INVERTABLE FLASHING COLLAR, WEEPHOLES, BOTTOM THEADDED OUTLET CONNECTION AND ADJUSTABLE SQUARE SUPER-FLO® STRAINER.

STAINLESS STEEL ADJUSTABLE FLOOR DRAIN

SERIES 30000-S-SS-T




DATE OF LAST CHANGE: 5/28/14 NOTES	
JOSAM COMPANY NOTES AND CHANGE WITHOUT NOTICE. JOSAM COMPANY	
WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA. MICHIGAN CITY, INDIANA	

SPECIFICATION:

JOSAM 32100-SS SERIES TYPE 316L CAST STAINLESS STEEL FLOOR DRAIN, DOUBLE DRAINAGE FLANGE, WEEPHOLES, ROUND TOP, HEAVY-DUTY LOOSE-SET ANTI-TILTING SUPER-FLO® GRATE WITH PERIMETER DRAINAGE SLOTS, BOTTOM OUTLET, BUTT WELD CONNECTION FOR SCHEDULE 40 PIPE.

FLOOR DRAIN
9" ROUND TOP, STAINLESS STEEL

SERIES 32100-SS




JOSAM 32100-SS-AE SERIES TYPE 316 CAST STAINLESS STEEL LEVELEZE® FLOOR DRAIN, DOUBLE DRAINAGE FLANGE, WEEPHOLES, ROUND TOP, ADJUSTABLE COLLAR WITH ROLLED THREADS AND HEAVY-DUTY LOOSE-SET ANTI-TILTING SUPER-FLO® GRATE WITH PERIMETER DRAINAGE SLOTS, BOTTOM OUTLET, BUTT WELL CONNECTION FOR SCHEDULE 40 PIPE.

FLOOR DRAIN

9" ROUND TOP, STAINLESS STEEL

32100-SS-AE SERIES



□ ADD 1/4" WHEN FURNISHED WITH NIKALOY (-1)

	х	-AE	LEVELEZE® ADJUSTABLE EXTENSION		-23	9" x 3" OVAL FUNNEL
Δ		-81	SHALLOW STAINLESS STEEL SEDIMENT BUCKET		-25	STAINLESS STEEL RECESSED CLOSURE PLUG
		-8	SOLID COVER		-26	MOLDED ABS RECESSED CLOSURE PLUG
		-9	STAINLESS STEEL MESH ON UNDERSIDE OF GRATE		-34	"T" HANDLE FOR RECESSED PLUG
		-21	4" ROUND FUNNEL		-61	FLASHING CLAMP DEVICE
		-22	6" ROUND FUNNEL		-69	SCHEDULE 10 S BUTT WELD CONNECTION

ΔSEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:

JOSAM 32100-SS-AE-81 SERIES TYPE 316 CAST STAINLESS STEEL LEVELEZE® FLOOR DRAIN, DOUBLE DRAINAGE FLANGE, WEEPHOLES, ADJUSTABLE COLLAR WITH ROLLED THREADS, ROUND TOP, LOOSE-SET ANTI-TILTING SUPER-FLO® GRATE WITH PERIMETER DRAINAGE SLOTS, SHALLOW SEDIMENT BUCKET, BOTTOM OUTLET, BUTT WELD CONNECTION FOR SCHEDULE 40 PIPE.

FLOOR DRAIN

9" ROUND TOP, STAINLESS STEEL W/ ADJ. EXTENSION AND BUCKET

SERIES 32100-SS-AE-81



Х	-AE	LEVELEZE® ADJUSTABLE EXTENSION	
Х	-81	SHALLOW STAINLESS STEEL SEDIMENT BUCKET	L
	-8	SOLID COVER	
	-9	STAINLESS STEEL MESH ON UNDERSIDE OF GRATE	
	-21	4" ROUND FUNNEL	Г
	-22	6" ROUND FUNNEL	Г

-23	9" x 3" OVAL FUNNEL
-25	STAINLESS STEEL RECESSED CLOSURE PLUG
-26	MOLDED ABS RECESSED CLOSURE PLUG
-34	"T" HANDLE FOR RECESSED PLUG
-61	FLASHING CLAMP DEVICE
-69	SCHEDULE 10 S BUTT WELD CONNECTION

DATE OF LAST CHANGE:


NIKALOY (-1)

JOSAM COMPANY DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA USE OF SUPERSEDED OR VOID DATA.

DATE OF LAST CHANGE:


DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.



JOSAM COMPANY

MICHIGAN CITY, INDIANA




JOSAM 55000-SS SERIES COATED CAST IRON KLEENATRON II LEVELEZE FLOOR CLEANOUT, INTERNAL ABS CLEANOUT PLUG, ADJUSTABLE CAST IRON HOUSING WITH MEDIUM-DUTY SCORIATED SECURED ROUND STAINLESS STEEL COVER.

CLEANOUT

ROUND STAINLESS TOP

SERIES

55000-SS



x	-SS	STAINLESS STEEL TOP	-F	FLANGE ONLY
П	-14	CARPET CLEANOUT MARKER	-WF	WIDE FLANGE
	-VP	SECURED COVER, VANDAL-PROOF SCREWS	-CFC	CARPET CLEANOUT FLANGE COVER
П	-22	TAPER THREAD BRONZE PLUG	-X	INSIDE CAULK OUTLET
	-31	GALVANIZED CAST IRON PARTS	-Y	HUB OUTLET W/ GASKET (2",3"&4" SIZES ONLY)
П	-41	CLAMP BING AND FLANGE	-Z	NO-HUB OUTLET

DATE OF LAST CHANGE: 6/19/2014

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:

JOSAM 56670-SS SERIES TYPE 316 CAST STAINLESS STEEL ROUND FLUSH CLEANOUT WITH FLANGED RING AND SCORIATED SPANNER TYPE FLANGED SCREW PLUG AND BOTTOM OUTLET WITH BUTT WELD CONNECTION FOR SCHEDULE 40 PIPE.

STAINLESS STEEL

FLOOR CLEANOUT SPANNER TYPE

SERIES 56670-SS



	SIZE	В	С	D
	2"	2-7/8	3-3/4	1-1/2
Г	3"	4	4-7/8	1-1/2
Г	4"	5	6	1-5/8
	6"	7-1/4	8-3/8	1-5/8


OPTIONS:

-45	SPANNER WRENCH
-69	SCHED 10S BUTT WELD CONNECTION

DATE OF LAST CHANGE: 04/27/10


DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA



(-8) OPTION, DEPRESSED GRATE

serves as a shallow sediment bucket to intercept solids in areas where limited space between floor sink and equipment prevents the use of a standard removable bucket.




(-55) OPTION, TRAP PRIMER ADAPTER


with Trap Primer Adapter.

Used to convert any standard drain to a trap primer drain. Install shallow trap primer adapter on all outlet types: -X Caulk, -Y Push-On or -Z No-Hub. (See 88450 for details.)


Primer Adapter.



49320A-NB Series SUPER-FLO-SEPTOR® Floor Sink shown installed in a heavy-duty structural concrete finish floor.



49580A-NB Series SUPER-FLO-SEPTOR® Floor Sink shown installed in a poured concrete floor on the ground level.



BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER AND CAST IRON NON-TRAFFIC, ACID-RESISTING, ANTI-TILTING, SUPER-FLO® GRATE. 49300-LF **SERIES** SLOT WIDTH 7/16" FORMERLY 49310 SERIES محما لمک 7 1/4" (Y///) (TT\\Y) - 3/8" **GRATE FREE** AREA 21 SQ. IN. ALUMINUM DOME 8 1 PIPE SIZE 2" 3" NO-HUB (-Z) 4" SHOWN PIPE SIZE -LF LESS FLANGE -31 SEDIMENT BUCKET, ALUMINUM -NB NICKEL BRONZE TRAFFIC TOP -33 SEDIMENT BUCKET, ACID RESISTANT FINISH -LG LESS GRATE -35 BUCKET LINER (STAINLESS STEEL MESH) -3 HALF (1/2) GRATE -43 INTERNAL DOME STRAINER, ACID RESISTANT FINISH THREE-QUARTER (3/4) GRATE -45 LESS INTERNAL DONE STRAINER FULL GRATE WITH 2-1/2" CENTER OPENING -55 1/2" PRIMER ADAPTER, 88450 PROVIDED -8 STAINLESS STEEL DEPRESSED GRATE -X INSIDE CAULK OUTLET -16 GRATE WITH 4" ROUND FUNNEL -Z NO-HUB OUTLET -17 GRATE WITH 6" ROUND FUNNEL -18 GRATE WITH 9" x 3-1/2" OVAL FUNNEL *MUST ALSO SPECIFY -31 OR -33 OPTION Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE DATE OF LAST CHANGE: NOTES **JOSAM COMPANY** IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA USE OF SUPERSEDED OR VOID DATA

SANITARY FLOOR SINK

8" SQUARE TOP, 6" DEEP

SPECIFICATION:

JOSAM 49300-LF SERIES SQUARE CAST IRON 6" DEEP


SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR.

JOSAM 49300-NB SERIES SQUARE CAST IRON 6-1/4" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, DOUBLE DRAINAGE FLANGE WITH WEEPHOLES, BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER AND NIKALOY SANITARY SLOPED RIM AND NIKALOY LIGHT-DUTY, ANTI-TILTING, SUPER-FLO® GRATE.

SANITARY FLOOR SINK

8" SQUARE TOP, 6" DEEP

SERIES 49300-NB



4			LESS FLANGE	ı	L
	Х	-NB	NICKEL BRONZE TRAFFIC TOP	1	l
	П	-LG	LESS GRATE	1	l
		-3	HALF (1/2) GRATE		l
			THREE-QUARTER (3/4) GRATE	*	L
			FULL GRATE WITH 2-1/2" CENTER OPENING		ļ
	П	-8	STAINLESS STEEL DEPRESSED GRATE	1	ļ
		-VP	SECURED GRATE, VANDAL-PROOF SCREWS]	ŀ
		-16	GRATE WITH 4" ROUND FUNNEL		ŀ
			GRATE WITH 6" ROUND FUNNEL		ŀ
ı		-18	GRATE WITH 9" x 3-1/2" OVAL FUNNEL	l	L

-31	SEDIMENT BUCKET, ALUMINUM
	SEDIMENT BUCKET, ACID RESISTANT FINISH
	BUCKET LINER (STAINLESS STEEL MESH)
	INTERNAL DOME STRAINER, ACID RESISTANT FINISH
	LESS INTERNAL DONE STRAINER
	1/2" PRIMER ADAPTER, 88450 PROVIDED
	CLAMP DEVICE
-X	INSIDE CALILK OUTLET

Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE

*MUST ALSO SPECIFY -31 OR -33 OPTION

DATE OF LAST CHANGE: 05/04/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

-Z NO-HUB OUTLET


NOTES

SPECIFICATION:

JOSAM 49300-LF-NB SERIES SOUARE CAST IRON 6-1/4" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER AND NIKALOY SANITARY SLOPED RIM AND NIKLOY LIGHT-DUTY, ANT-ILLTING, SUPER-FLO® GRATE.

SANITARY FLOOR SINK 8" SQUARE TOP. 6" DEEP

SERIES 49300-LF-NB



<	-LF	LESS FLANGE		-18	GRATE WITH 9" x 3-1/2" OVAL FUNNEL
(-NB	NICKEL BRONZE TRAFFIC TOP		-20	SOLID NIKALOY COVER
T	-LG	LESS GRATE		-24	CHAINED GRATE
T	-3	HALF (1/2) GRATE		-31	SEDIMENT BUCKET, ALUMINUM
T	-4	THREE-QUARTER (3/4) GRATE		-33	SEDIMENT BUCKET, ACID RESISTANT FINISH
T	-7	FULL GRATE WITH 2-1/2" CENTER OPENING	*	-35	BUCKET LINER (STAINLESS STEEL MESH)
T	-8	STAINLESS STEEL DEPRESSED GRATE		-43	INTERNAL DOME STRAINER, ACID RESISTANT FINIS
I	-VP	SECURED GRATE, VANDAL-PROOF SCREWS	lf	-45	LESS INTERNAL DONE STRAINER
Т	-16	GRATE WITH 4" ROUND FUNNEL	l f	-55	1/2" PRIMER ADAPTER, 88450 PROVIDED
I	-17	GRATE WITH 6" ROUND FUNNEL		-X	INSIDE CAULK OUTLET
				-Z	NO-HUB OUTLET


*MUST ALSO SPECIFY -31 OR -33 OPTION

DATE OF LAST CHANGE: 5/2/14

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TO LERANCES AND CHANGE WITHOUT NOTICE. WILLIAM COMPANY MICHIGAN CITY, INDIANA

MICHIGAN CITY, INDIANA

NOTE



Δ		-LF	LESS FLANGE	ιГ	П	-18	GRATE WITH 9" x 3-1/2" OVAL FUNNEL
Δ	╗	-NB	NICKEL BRONZE TRAFFIC TOP	ιГ	┰	-31	SEDIMENT BUCKET, ALUMINUM
		-LG	LESS GRATE	ıE	\mathbb{T}	-33	SEDIMENT BUCKET, ACID RESISTANT FINISH
			HALF (1/2) GRATE	*			BUCKET LINER (STAINLESS STEEL MESH)
		-4	THREE-QUARTER (3/4) GRATE		\Box	-43	INTEGRAL DOME STRAINER, ACID RESISTANT FINISH
		-5	NIK. EXTRA HVY-DUTY GRATE & RIM (NOT SUPER-FLO)	ıE			LESS INTERNAL DONE STRAINER
		-7	FULL GRATE WITH 2-1/2" CENTER OPENING		\Box	-55	1/2" PRIMER TAP (6") ADAPTER, 88450 PROVIDED (2"-4")
			STAINLESS STEEL DEPRESSED GRATE	ıE			CLAMP DEVICE
		-15	STAINLESS STEEL RIM & GRATE	ıΕ	\Box	-X	INSIDE CAULK OUTLET
	П	-16	GRATE WITH 4" ROUND FUNNEL	ıΓ	П	-Y	HUB OUTLET WITH GASKET (2"-4")
		-17	GRATE WITH 6" ROUND FUNNEL	ıΓ	Т	-Z	NO-HUB OUTLET
		SEP.	ARATE SUBMITTAL FOR THIS OPTION AVAILA	ABLE	Ε		*MUST ALSO SPECIFY -31 OR -33 OPTION

Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE DATE OF LAST CHANGE: 2/27/15 **JOSAM COMPANY** IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA USE OF SUPERSEDED OR VOID DATA.

NOTES


SPECIFICATION:

JOSAM 49320A-LF SERIES SQUARE CAST IRON 5-7/8" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR. BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER AND CAST IRON NON-TRAFFIC, ACID RESISTING, ANTI-TILTING GRATE.

SANITARY FLOOR SINK

12" SQUARE TOP, 6" DEEP

49320A-LF **SERIES**



-NB	NICKEL BRONZE TRAFFIC TOP			
-LG	LESS GRATE	ı		ſ
	HALF (1/2) GRATE	*		
-4	THREE-QUARTER (3/4) GRATE			I
-5	NIK. EXTRA HVY-DUTY GRATE & RIM (NOT SUPER-FLO)			ſ
-7	FULL GRATE WITH 2-1/2" CENTER OPENING			I
-8	STAINLESS STEEL DEPRESSED GRATE	ı		ſ
-15	STAINLESS STEEL RIM & GRATE	ı		Ī
	GRATE WITH 4" ROUND FUNNEL	i	П	ľ
-17	GRATE WITH 6" ROUND FUNNEL			I
ΔSEF	PARATE SUBMITTAL FOR THIS OPTION AVAIL	ABI	E	

-43 INTERNAL DOME STRAINER, ACID RESISTANT FINISH -52 PAINT INSIDE AND OUTSIDE -55 1/2" PRIMER TAP (6") ADAPTER, 88450 PROVIDED (2"-4") -X INSIDE CAULK OUTLET

-45 LESS INTERNAL DONE STRAINER -Y HUB OUTLET WITH GASKET (2"-4")

-31 SEDIMENT BUCKET, ALUMINUM -33 SEDIMENT BUCKET, ACID RESISTANT FINISH -35 BUCKET LINER (STAINLESS STEEL MESH)

-Z NO-HUB OUTLET *MUST ALSO SPECIFY -31 OR -33 OPTION

DATE OF LAST CHANGE: IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY


JOSAM 49320A-NB SERIES SQUARE CAST IRON 6-1/4" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, DOUBLE DRAINAGE FLANGE WITH WEEPHOLES, BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER, NIKALOY SANITARY SLOPED RIM AND NIKALOY LIGHT-DUTY SUPER-FLO®, ANTI-TILTING GRATE.

SANITARY FLOOR SINK

12" SQUARE TOP, 6" DEEP

SERIES

49320A-NB



Δ			LESS FLANGE
	X	-NB	NICKEL BRONZE TRAFFIC TOP
			LESS GRATE
	П	-3	HALF (1/2) GRATE
	П	-4	THREE-QUARTER (3/4) GRATE
	П		NIK. EXTRA HVY-DUTY GRATE & RIM (NOT SUPER-FLO)
		-7	FULL GRATE WITH 2-1/2" CENTER OPENING
		-8	STAINLESS STEEL, DEPRESSED GRATE
			SECURED GRATE, VANDAL-PROOF SCREWS
	П	-15	STAINLESS STEEL RIM & GRATE
		-16	GRATE WITH 4" ROUND FUNNEL
	П	-17	GRATE WITH 6" ROUND FUNNEL

ı			GRATE WITH 9" x 3-1/2" OVAL FUNNEL
I		-20	SOLID NIKALOY COVER
I		-24	CHAINED GRATE
I	П	-31	SEDIMENT BUCKET, ALUMINUM
I			SEDIMENT BUCKET, ACID RESISTANT FINISH
I	П	-35	BUCKET LINER (STAINLESS STEEL MESH)
I		-43	INTERNAL DOME STRAINER, ACID RESISTANT FINISH
I	П	-45	LESS INTERNAL DONE STRAINER
I		-55	1/2" PRIMER TAP (6") ADAPTER, 88450 PROVIDED (2"-4")
Į			CLAMP DEVICE
I	П	-X	INSIDE CAULK OUTLET

Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE

-Y HUB OUTLET WITH GASKET (2"-4")

-Z NO-HUB OUTLET

JOSAM COMPANY MICHIGAN CITY, INDIANA


*MUST ALSO SPECIFY -31 OR -33 OPTION

SPECIFICATION:

JOSAM 49320A-LF-NB SERIES SQUARE CAST IRON 6-1/4" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER, NIKALOY SANITARY SLOPED RIM AND NIKALOY LIGHT-DUTY SUPER-FLO®, ANTI-TILTING GRATE.

SANITARY FLOOR SINK 12" SQUARE TOP, 6" DEEP

SERIES 49320A-LF-NB



X		LESS FLANGE
X		NICKEL BRONZE TRAFFIC TOP
		LESS GRATE
	-3	HALF (1/2) GRATE
	-4	THREE-QUARTER (3/4) GRATE
	-5	NIK. EXTRA HVY-DUTY GRATE & RIM (NOT SUPER-FLO)
	-7	FULL GRATE WITH 2-1/2" CENTER OPENING
	-8	STAINLESS STEEL, DEPRESSED GRATE
	-VP	SECURED GRATE, VANDAL-PROOF SCREWS
	-15	STAINLESS STEEL RIM & GRATE
	-16	GRATE WITH 4" ROUND FUNNEL
	-17	GRATE WITH 6" ROUND FUNNEL
	-18	GRATE WITH 9" x 3-1/2" OVAL FUNNEL

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.

٦	-20	SOLID NIKALOY COVER
	-24	CHAINED GRATE
	-31	SEDIMENT BUCKET, ALUMINUM
	-33	SEDIMENT BUCKET, ACID RESISTANT FINISH
	-35	BUCKET LINER (STAINLESS STEEL MESH)
	-43	INTERNAL DOME STRAINER, ACID RESISTANT FINISH
	-45	LESS INTERNAL DONE STRAINER
	-55	1/2" PRIMER TAP (6") ADAPTER, 88450 PROVIDED (2"-4")
T	-X	INSIDE CAULK OUTLET
	-Y	HUB OUTLET WITH GASKET (2"-4")

*MUST ALSO SPECIFY -31 OR -33 OPTION

JOSAM COMPANY MICHIGAN CITY, INDIANA


-Z NO-HUB OUTLET


DATE OF LAST CHANGE:

IMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.





SANITARY FLOOR SINK


SPECIFICATION:

JOSAM 49340A-NB SERIES SQUARE CAST IRON 8-3/8" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, DOUBLE DRAINAGE FLANGE WITH WEEPHOLES, BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER, NIKALOY SANITARY SLOPED RIM AND NIKALOY LIGHT-DUTY SUPER-FLO®, ANTI-TILTING GRATE.

SANITARY FLOOR SINK

12" SQUARE TOP, 8" DEEP

49340A-NB SERIES



	_		
Δ	Ш	-LF	LESS FLANGE
	Х	-NB	NICKEL BRONZE TRAFFIC TOP
	П	-LG	LESS GRATE
		-3	HALF (1/2) GRATE
		-4	THREE-QUARTER (3/4) GRATE
		-5	NIK. EXTRA HVY-DUTY GRATE & RIM (NOT SUPER-FLO)
		-7	FULL GRATE WITH 2-1/2" CENTER OPENING
		-VP	SECURED GRATE, VANDAL-PROOF SCREWS
			STAINLESS STEEL RIM & GRATE
			GRATE WITH 4" ROUND FUNNEL
			GRATE WITH 6" ROUND FUNNEL
		-18	GRATE WITH 9" x 3-1/2" OVAL FUNNEL

- -14 HINGED GRATE
- -20 SOLID NIKALOY COVER -24 CHAINED GRATE
- -31 SEDIMENT BUCKET, ALUMINUM
- -33 SEDIMENT BUCKET, ACID RESISTANT FINISH -35 BUCKET LINER (STAINLESS STEEL MESH)
- -43 INTERNAL DOME STRAINER, ACID RESISTANT FINISH -45 LESS INTERNAL DONE STRAINER
- -55 1/2" PRIMER ADAPTER, 88450 PROVIDED C CLAMP DEVICE
- -X INSIDE CAULK OUTLET
- -Y HUB OUTLET WITH GASKET -Z NO-HUB OUTLET

*MUST ALSO SPECIFY -31 OR -33 OPTION

Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE 6/27/14

DATE OF LAST CHANGE:

JOSAM COMPANY DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA USE OF SUPERSEDED OR VOID DATA.


SPECIFICATION:

JOSAM 49340A-LF-NB SERIES SQUARE CAST IRON 8-3/8" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, BOTTOM OUTLET, ALLMINUM INTERNAL DOME STRAINER. NIKALOY SANITARY SLOPED RIM AND NIKALOY LIGHT-DUTY SUPER-FLO®, ANTI-TILTING GRATE.

SANITARY FLOOR SINK

12" SQUARE TOP, 8" DEEP


SERIES 49340A-LF-NB



MICHIGAN CITY, INDIANA

DATE OF LAST CHANGE: **JOSAM COMPANY** DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.



Δ			LESS FLANGE		
Δ		-NB	NICKEL BRONZE TRAFFIC TOP		П
		-LG	LESS GRATE		
		-3	HALF (1/2) GRATE	*	
		-4	THREE-QUARTER (3/4) GRATE		
		-5	NIK. EXTRA HVY-DUTY GRATE & RIM (NOT SUPER-FLO)		
		-7	FULL GRATE WITH 2-1/2" CENTER OPENING		
	П	-8	STAINLESS STEEL DEPRESSED GRATE		П
		-15	STAINLESS STEEL RIM & GRATE		
		-16	GRATE WITH 4" ROUND FUNNEL		
		-17	GRATE WITH 6" ROUND FUNNEL		
		-18	GRATE WITH 9" x 3-1/2" OVAL FUNNEL		

		SEDIMENT BUCKET, ALUMINUM
\neg		SHALLOW SEDIMENT BUCKET, ALUMINUM
		SEDIMENT BUCKET, ACID RESISTANT FINISH
	-35	BUCKET LINER (STAINLESS STEEL MESH)
	-43	INTERNAL DOME STRAINER, ACID RESISTANT FINISH
	-45	LESS INTERNAL DONE STRAINER
		1/2" PRIMER ADAPTER, 88450 PROVIDED
П	-C	CLAMP DEVICE

-X INSIDE CAULK OUTLET

HUB OUTLET WITH GASKET

NO HUB OUTLET

Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE

*MUST ALSO SPECIFY -31, -32 OR -33 OPTION

DATE OF LAST CHANGE:	2/27/15
DIMENSIONS ARE SUBJECT TO M.	ANUFACTURE
TOLERANCES AND CHANGE WIT	
WE CAN ASSUME NO RESPON	
USE OF SUPERSEDED OR V	OID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA


SPECIFICATION:

JOSAM 49360A SERIES SQUARE CAST IRON 10" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER AND CAST IRON NON-TRAFFIC, ACID RESISTING, ANTI-TILTING GRATE.

SANITARY FLOOR SINK

12" SQUARE TOP, 10" DEEP

49360A-LF **SERIES**



DATE OF LAST CHANGE: IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

-18 GRATE WITH 9" x 3-1/2" OVAL FUNNEL

Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE

JOSAM COMPANY MICHIGAN CITY, INDIANA


*MUST ALSO SPECIFY -31, -32 OR -33 OPTION NOTES

JOSAM 49360A-NB SERIES SQUARE CAST IRON 10-1/4" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR. DOUBLE DRAINAGE FLANGE WITH WEEPHOLES, BOTTOM OUTLET. ALUMINUM INTERNAL DOME STRAINER, NIKALOY SANITARY SLOPED RIM AND NIKALOY LIGHT-DUTY SUPER FLO® ANTI-TILTING GRATE.

SANITARY FLOOR SINK

12" SQUARE TOP, 10" DEEP

49360A-NB SERIES



-16 GRATE WITH 4" ROUND FUNNEL -17 GRATE WITH 6" ROUND FUNNEL -18 GRATE WITH 9" x 3-1/2" OVAL FUNNEL

-Y HUB OUTLET WITH GASKET -Z NO HUB OUTLET

Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE

DATE OF LAST CHANGE:

*MUST ALSO SPECIFY -31, -32 OR -33 OPTION

JOSAM COMPANY DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA. MICHIGAN CITY, INDIANA


SPECIFICATION:

JOSAM 49360A-LF-NB SERIES SQUARE CAST IRON 10-1/4" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR. BOTTOM OUTLET. ALUMINUM INTERNAL DOME STRAINER. NIKALOY SANITARY SLOPED RIM AND NIKALOY LIGHT-DUTY SUPER FLO® ANTI-TILTING GRATE.

SANITARY FLOOR SINK

12" SQUARE TOP, 10" DEEP

SERIES 49360A-LF-NB



STAINLESS STEEL DEPRESSED GRATE -45 LESS INTERNAL DONE STRAINER -VP SECURED GRATE, VANDAL-PROOF SCREWS -55 1/2" PRIMER ADAPTER, 88450 PROVIDED -15 STAINLESS STEEL RIM & GRATE -X INSIDE CAULK OUTLET -16 GRATE WITH 4" ROUND FUNNEL


 Y HUB OUTLET WITH GASK -Z NO HUB OUTLET

*MUST ALSO SPECIFY -31, -32 OR -33 OPTION

DATE OF LAST CHANGE: **JOSAM COMPANY** DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA. MICHIGAN CITY, INDIANA

-17 GRATE WITH 6" ROUND FUNNEL

-18 GRATE WITH 9" x 3-1/2" OVAL FUNNEL



BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER AND CAST IRON NON-TRAFFIC, ACID-RESISTING, ANTI-TILTING, SUPER-FLO® GRATE. 49400-LF **SERIES** SLOT WIDTH 9/16" FORMERLY 49410 SERIES 16" SQ GRATE FREE AREA 94 SQ. IN. 9/16 - 14 1/2" SQ. ı– 6" ALUMINUM PIPE SIZE В DOME 9-1/2" 9-1/2" 9-7/8" PIPE SIZE NOTE: 49403 USES 49404 BODY WITH 4x3 REDUCER -LF LESS FLANGE SEDIMENT BUCKET, ALUMINUM -NB NICKEL BRONZE TRAFFIC TOP -33 SEDIMENT BUCKET, ACID RESISTANT FINISH -LG LESS GRATE -35 BUCKET LINER (STAINLESS STEEL MESH) -3 HALF (1/2) GRATE -43 INTERNAL DOME STRAINER, ACID RESISTANT FINISH -4 THREE-QUARTER (3/4) GRATE -45 LESS INTERNAL DONE STRAINER -7 FULL GRATE WITH 2-1/2" CENTER OPENING -55 1/2" PRIMER ADAPTER (6"), ADAPTER 88450 PROVIDED (3"-4") -16 GBATE WITH 4" BOUND FUNNEL FOR PAINTED OR GALVANIZED, SEE 37960 SERIES -17 GRATE WITH 6" ROUND FUNNEL -18 GRATE WITH 9" x 3-1/2" OVAL FUNNEL Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE *MUST ALSO SPECIFY -31 OR -33 OPTION DATE OF LAST CHANGE: JOSAM COMPANY DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA

JOSAM 49400-LF SERIES SQUARE CAST IRON 6" DEEP

SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR.

SANITARY FLOOR SINK


16" SQUARE TOP, 6" DEEP

JOSAM 49400-NB SERIES SQUARE CAST IRON 6-1/4" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, DOUBLE DRAINAGE FLANGE WITH WEEPHOLES, BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER, NIKALOY SANITARY SLOPED RIM AND NIKALOY LIGHT-DUTY, ANTI-TILTING, SUPER-FLO® GRATE.

SANITARY FLOOR SINK

16" SQUARE TOP, 6" DEEP

49400-NB SERIES



SPECIFICATION:

JOSAM 49400-LF-NB SERIES SQUARE CAST IRON 6-1/4" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER, NIKALOY SANITARY SLOPED RIM AND NIKALOY LIGHT-DUTY, ANTI-TILTING, SUPER-FLO® GRATE.

SANITARY FLOOR SINK 16" SQUARE TOP, 6" DEEP

49400-LF-NB SERIES



GRATE FREE

AREA 93 SQ. IN.

CAULK (-X)

PIPE SIZE	В
3"	9-3/4"
4"	9-3/4"
6"	10-1/8"

5/16 — 14 1/2" SQ. —► 6 5/16' ALUMINUM DOME

Х	-LF	LESS FLANGE	i [Г	
Х	-NB	NICKEL BRONZE TRAFFIC TOP			
	-LG	LESS GRATE	*		
		HALF (1/2) GRATE			
П	-4	THREE-QUARTER (3/4) GRATE	[I
		FULL GRATE WITH 2-1/2" CENTER OPENING	[
	-VP	SECURED GRATE, VANDAL-PROOF SCREWS		F	
П	-16	GRATE WITH 4" ROUND FUNNEL		•	
П	-17	GRATE WITH 6" BOLIND FLINNEL			

-18 GRATE WITH 9" x 3-1/2" OVAL FUNNEL

PIPE SIZE

-31	SEDIMENT BUCKET, ALUMINUM	
-33	SEDIMENT BUCKET, ACID RESISTANT FI	NIS

-35 BUCKET LINER (STAINLESS STEEL MESH) -43 INTERNAL DOME STRAINER, ACID RESISTANT FINISH -45 LESS INTERNAL DONE STRAINER

-55 1/2" PRIMER TAP (6"), ADAPTER 88450 PROVIDED (3"-4") OR PAINTED OR GALVANIZED, SEE 37960 SERIES

*MUST ALSO SPECIFY -31 OR -33 OPTION


DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY

MICHIGAN CITY, INDIANA



JOSAM 49420-LF SERIES SQUARE CAST IRON 12" DEEP 16" SQUARE TOP, 12" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER AND CAST IRON NON-TRAFFIC, ACID RESISTING SUPER FLO® ANTI-TILTING GRATE. 49420-LF SERIES FORMERLY 49430 SERIES SLOT WIDTH 9/16" 16" SQ. PIPE SIZE В 3" 15-1/2" 15-1/2" GRATE FREE 6" 15-7/8" AREA 94 SQ. IN. NOTE: 49403 USES 49404 BODY WITH 4x3 REDUCER - 12" 9/16" 14 1/2" SQ ALUMINUM DOME PIPE SIZE -CAULK (-X) -LF LESS FLANGE -31 SEDIMENT BUCKET, ALUMINUM -33 SEDIMENT BUCKET, ACID RESISTANT FINISH -NB NICKEL BRONZE TRAFFIC TOP -35 BUCKET LINER (STAINLESS STEEL MESH) -LG LESS GRATE -43 INTERNAL DOME STRAINER, ACID RESISTANT FINISH -3 HALF (1/2) GRATE -45 LESS INTERNAL DOME STRAINER -4 THREE-QUARTER (3/4) GRATE -7 FULL GRATE WITH 2-1/2" CENTER OPENING -51 GALV, CAST IRON, INSIDE AND OUTSIDE (NO ARE) -52 PAINTED, INSIDE AND OUTSIDE (NO ARE) -16 GRATE WITH 4" ROUND FUNNEL -17 GRATE WITH 6" ROUND FUNNEL -55 1/2" PRIMER TAP (6"), ADAPTER 88450 PROVIDED (3"-4") -18 GRATE WITH 9" x 3-1/2" OVAL FUNNEL Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE *MUST ALSO SPECIFY -31, -33 OPTION DATE OF LAST CHANGE: JOSAM COMPANY DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA USE OF SUPERSEDED OR VOID DATA

SANITARY FLOOR SINK


SPECIFICATION:

JOSAM 49420-NB SERIES SQUARE CAST IRON 12-1/4" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, DOUBLE DRAINAGE FLANGE WITH WEEPHOLES, BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER, NIKALOY SANITARY SLOPED RIM AND NIKALOY LIGHT-DUTY SUPER FLO® ANTI-TILTING GRATE.

SANITARY FLOOR SINK

16" SQUARE TOP, 12" DEEP

49420-NB **SERIES**




SPECIFICATION:

JOSAM 49420-LF-NB SERIES SQUARE CAST IRON 12-1/4" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER, NIKALOY SANITARY SLOPED RIM AND NIKALOY LIGHT-DUTY SUPER FLO® ANTI-TILTING GRATE.

SANITARY FLOOR SINK

16" SQUARE TOP, 12" DEEP

SERIES 49420-LF-NB



X -LF LESS FLANGE						
-NB	NICKEL BRONZE TRAFFIC TOP					
-LG	LESS GRATE					
-3	HALF (1/2) GRATE					
-4	THREE-QUARTER (3/4) GRATE					
-7	FULL GRATE WITH 2-1/2" CENTER OPENING					
-VP	SECURED GRATE, VANDAL-PROOF SCREWS					
-16	GRATE WITH 4" ROUND FUNNEL					
-17	GRATE WITH 6" ROUND FUNNEL					
-18	GRATE WITH 9" x 3-1/2" OVAL FUNNEL					
	-NB -LG -3 -4 -7 -VP -16 -17					

	-31	SEDIMENT BUCKET, ALUMINUM
	-33	SEDIMENT BUCKET, ACID RESISTANT FINISH
	-35	BUCKET LINER (STAINLESS STEEL MESH)
	-43	INTERNAL DOME STRAINER, ACID RESISTANT FINISH
	-45	LESS INTERNAL DOME STRAINER
	-51	GALV. CAST IRON, INSIDE AND OUTSIDE (NO ARE)
T	-52	PAINTED, INSIDE AND OUTSIDE (NO ARE)
	-55	1/2" PRIMER TAP (6"), ADAPTER 88450 PROVIDED (3"-4")

*MUST ALSO SPECIFY -31, -33 OPTION

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

ALUMINUM

DOME

JOSAM COMPANY MICHIGAN CITY, INDIANA

CAULK (-X)


DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

-18 GRATE WITH 9" x 3-1/2" OVAL FUNNEL

Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE

JOSAM COMPANY MICHIGAN CITY, INDIANA

*MUST ALSO SPECIFY -31, -33 OPTION



-18 GRATE WITH 9" x 3-1/2" OVAL FUNNEI -X INSIDE CAULK OUTLET -Z NO HUB OUTLET Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE *MUST ALSO SPECIFY -31, -33 OPTION DATE OF LAST CHANGE: 2/27/15 **JOSAM COMPANY** IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA USE OF SUPERSEDED OR VOID DATA.


SPECIFICATION:

JOSAM 49500-LF SERIES ROUND CAST IRON 3-5/16" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR. BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER AND CAST IRON NON-TRAFFIC, ACID RESISTING SUPER FLO® ANTI-TII TING GRATE.

SANITARY FLOOR SINK

8" ROUND TOP, 3" DEEP

49500-LF **SERIES**



Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE

*MUST ALSO SPECIFY -31, -33 OPTION

DATE OF LAST CHANGE: IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA


JOSAM COMPANY MICHIGAN CITY, INDIANA

JOSAM 49500-NB SERIES ROUND CAST IRON 3-9/16" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, DOUBLE DRAINAGE FLANGE WITH WEEPHOLES, BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER, NIKALOY SANITARY SLOPED RIM AND NIKALOY LIGHTY-DUTY SUPER FLO® ANTI-TILTING GRATE.

SANITARY FLOOR SINK

8" ROUND TOP, 3" DEEP

49500-NB




SPECIFICATION:

JOSAM 49500-LF-NB SERIES ROUND CAST IRON 3-9/16" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER, NIKALOY SANITARY SLOPED RIM AND NIKALOY LIGHTY-DUTY SUPER FLO® ANTI-TILTING GRATE.

SANITARY FLOOR SINK

8" ROUND TOP, 3" DEEP

SERIES 49500-LF-NB



DATE OF LAST CHANGE: 5/13/14 IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA

Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE


JOSAM COMPANY MICHIGAN CITY, INDIANA

DATE OF LAST CHANGE:

USE OF SUPERSEDED OR VOID DATA.

*MUST ALSO SPECIFY -31, -33 OPTION

5/13/14 **JOSAM COMPANY** TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA



BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER AND CAST IRON, NON-TRAFFIC, ACID-RESISTING, ANTI-TILTING SUPER-FLOR GRATE. 49520A-LF SERIES FORMERLY 49530A SERIES SLOT WIDTH 7/16" GRATE FREE Ø8' AREA 15.5 SQ. IN. 3/8" Ø7 3/16" ALUMINUM DOME PIPE SIZE 2" 3" 4" PIPE SIZE CAULK (-X) X | LF LESS FLANGE SEDIMENT BUCKET, ALUMINUM -NB NICKEL BRONZE TRAFFIC TOP SEDIMENT BUCKET, ACID RESISTANT FINISH -LG LESS GRATE -35 BUCKET LINER (STAINLESS STEEL MESH) -3 HALF (1/2) GRATE -43 INTERNAL DOME STRAINER, ACID RESISTANT FINISH -4 THREE-QUARTER (3/4) GRATE -45 LESS INTERNAL DONE STRAINER GALV. CAST IRON, INSIDE AND OUTSIDE (NO ARE) -7 FULL GRATE WITH 2-1/2" CENTER OPENING -8 STAINLESS STEEL DEPRESSED GRATE -52 PAINTED, INSIDE AND OUTSIDE (NO ARE) -55 1/2" PRIMER TAP -16 GRATE WITH 4" ROUND FUNNEL -17 GRATE WITH 6" ROUND FUNNEL INSIDE CAULK OUTLET -18 GRATE WITH 9" x 3-1/2" OVAL FUNNEL -Z NO-HUB OUTLET Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE *MUST ALSO SPECIFY -31 OR -33 OPTION DATE OF LAST CHANGE: **JOSAM COMPANY** IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA USE OF SUPERSEDED OR VOID DATA

SANITARY FLOOR SINK

8" ROUND TOP, 6" DEEP

SPECIFICATION:

JOSAM 49520A-LF SERIES ROUND CAST IRON 6" DEEP

SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR.


JOSAM 49520A-NB SERIES ROUND CAST IRON 6-1/4" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, DOUBLE DRAINAGE FLANGE WITH WEEPHOLES, BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER, NIKALOY SANITARY SLOPED RIM AND NIKALOY LIGHT-DUTY SUPER-FLO® ANTI-TILTING GRATE.

SANITARY FLOOR SINK

8" ROUND TOP, 6" DEEP

SERIES

49520A-NB




SPECIFICATION:

JOSAM 49520A-LF-NB SERIES ROUND CAST IRON 6-1/4" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER, NIKALOY SANITARY SLOPED RIM AND NIKALOY LIGHT-DUTY SUPER-FLO® ANTI-TILTING GRATE.

SANITARY FLOOR SINK

8" ROUND TOP, 6" DEEP

SERIES 49520A-LF-NB



DATE OF LAST CHANGE: 5/14/14 DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE


JOSAM COMPANY MICHIGAN CITY, INDIANA

*MUST ALSO SPECIFY -31, -33 OPTION

DATE OF LAST CHANGE: JOSAM COMPANY IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA USE OF SUPERSEDED OR VOID DATA

SPECIFICATION: SANITARY FLOOR SINK JOSAM 49580A SERIES ROUND CAST IRON 8" DEEP 12" ROUND TOP, 8" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR. DOUBLE DRAINAGE FLANGE WITH WEEPHOLES, BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER AND CAST IRON NON-TRAFFIC,

ACID RESISTING SUPER-FLO® ANTI-TILTING GRATE.



$\Delta \Gamma$	II-L	F	LESS FLANGE	1		-31	SEDIMENT BUCKET, ALUMINUM			
Δ	II-N	ΙB	NICKEL BRONZE TRAFFIC TOP	1			SEDIMENT BUCKET, ACID RESISTANT FINISH			
	I-L	G	LESS GRATE	*		-35	BUCKET LINER (STAINLESS STEEL MESH)			
		3	HALF (1/2) GRATE]		-43	INTERNAL DOME STRAINER, ACID RESISTANT FINISH			
Г	-4	4	THREE-QUARTER (3/4) GRATE	1		-45	LESS INTERNAL DOME STRAINER			
	-:	7	FULL GRATE WITH 2-1/2" CENTER OPENING]		-51	GALV. CAST IRON, INSIDE AND OUTSIDE (NO ARE)			
Г	1 -8	3	STAINLESS STEEL DEPRESSED GRATE	7		-52	PAINTED, INSIDE AND OUTSIDE (NO ARE)			
	-1	6	GRATE WITH 4" ROUND FUNNEL]		-55	1/2" PRIMER TAP			
Г	-1	7	GRATE WITH 6" ROUND FUNNEL	1		-C	CLAMP DEVICE			
	-1	8	GRATE WITH 9" x 3-1/2" OVAL FUNNEL]		-X	INSIDE CAULK OUTLET			
				-		-Z	NO HUB OUTLET			
Δ	Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE *MUST ALSO SPECIFY -31, -33 OPTION									

DATE OF LAST CHANGE: 2/27/15	
DIMENSIONS ARE SUBJECT TO MANUFACTURERS	Š
TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR	
USE OF SUPERSEDED OR VOID DATA.	

JOSAM COMPANY MICHIGAN CITY, INDIANA

49580A

SERIES

SPECIFICATION:


USE OF SUPERSEDED OR VOID DATA.

JOSAM 49580A-LF SERIES ROUND CAST IRON 8" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER AND CAST IRON, NON-TRAFFIC, ACID-RESISTING, ANTI-TILTING SUPER-FLO® GRATE.

SANITARY FLOOR SINK

12" ROUND TOP, 8" DEEP

49580A-LF **SERIES**




JOSAM 49580A-NB SERIES ROUND CAST IRON 8-1/4" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, DOUBLE DRAINAGE FLANGE WITH WEEPHOLES, BOTTOM OUTLET," ALUMINUM INTERNAL DOME STRAINER, NIKALOY SANITARY SLOPED RIM AND NIKALOY LIGHT-DUTY SUPER-I-LOW ANTI-TILTING GRATE.

SANITARY FLOOR SINK

12" ROUND TOP, 8" DEEP

49580A-NB SERIES



Δ		-LF	LESS FLANGE
	Х	-NB	NICKEL BRONZE TRAFFIC TOP
		-LG	LESS GRATE
		-3	HALF (1/2) GRATE
		-4	THREE-QUARTER (3/4) GRATE
		-7	FULL GRATE WITH 2-1/2" CENTER OPENING
		-8	ALUMINUM DEPRESSED GRATE
		-VP	SECURED GRATE, VANDAL-PROOF SCREWS
		-16	GRATE WITH 4" ROUND FUNNEL
		-17	GRATE WITH 6" ROUND FUNNEL
		-18	GRATE WITH 9" x 3-1/2" OVAL FUNNEL
		-24	CHAINED GRATE

T	-33	SEDIMENT BUCKET, ACID RESISTANT F
۱	-35	BUCKET LINER (STAINLESS STEEL MES
T	-43	INTERNAL DOME STRAINER, ACID RESISTAN
П	45	LEGG INTERNAL DOME OTRAINER

- NT FINISH
- -45 LESS INTERNAL DOME STRAINER -51 GALV. CAST IRON, INSIDE AND OUTSIDE (NO ARE)
- -52 PAINTED, INSIDE AND OUTSIDE (NO ARE)
- 1/2" PRIMER TAP
- CLAMP DEVICE INSIDE CAULK OUTLET
- -Z NO HUB OUTLET

Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE

*MUST ALSO SPECIFY -31, -33 OPTION

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA


SPECIFICATION:

JOSAM 49580A-LF-NB SERIES ROUND CAST IRON 8-1/4" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, BOTTOM OUTLET, ALUMINUM INTERNAL DOME STRAINER. NIKALOY SANITARY SLOPED RIM AND NIKALOY LIGHT-DUTY SUPER-FLO® ANTI-TILTING GRATE.

SANITARY FLOOR SINK

12" ROUND TOP, 8" DEEP

SERIES 49580A-LF-NB



X - LF LESS FLANGE X - NB NICKEL BRONZE TRAFFIC TOP - LG LESS GRATE - 3 HALF (1/2) GRATE - 4 THRE-GUARTER (3/4) GRATE - 7 FULL GRATE WITH 2-1/2" CENTER OPENING - 8 ALUMINUM DEPRESSED GRATE - VP SCURED GRATE (- AVNDAL-PROOF SCREWS - 16 GRATE WITH 4" ROUND FUNNEL - 17 GRATE WITH 6" ROUND FUNNEL - 18 GRATE WITH 9" 3-1/2" OVAL FUNNEL			
-LG LESS GRATE -3 HALF (1/2) GRATE -4 THREE-QUARTER (3/4) GRATE -7 FULL GRATE WITH 2-1/2" CENTER OPENING -8 ALUMINUM DEPRESSED GRATE -VP SECURED GRATE, VANDAL-PROOF SCREWS -16 GRATE WITH 4" ROUND FUNNEL -17 GRATE WITH 6" ROUND FUNNEL	Х	-LF	LESS FLANGE
-3 HALF (1/2) GRATE -4 THREE-QUARTER (3/4) GRATE -7 FULL GRATE WITH 2-1/2" CENTER OPENING -8 ALUMINUM DEPRESSED GRATE -VP SECURED GRATE, VANDAL-PROOF SCREWS -16 GRATE WITH 4" ROUND FUNNEL -17 GRATE WITH 6" ROUND FUNNEL	Х	-NB	NICKEL BRONZE TRAFFIC TOP
-4 THREE-QUARTER (3/4) GRATE -7 FULL GRATE WITH 2-1/2" CENTER OPENING -8 ALUMINUM DEPRESSED GRATE -VP SECURED GRATE, VANDAL-PROOF SCREWS -16 GRATE WITH 4" ROUND FUNNEL -17 GRATE WITH 6" ROUND FUNNEL		-LG	LESS GRATE
-7 FULL GRATE WITH 2-1/2" CENTER OPENING -8 ALUMINUM DEPRESSED GRATE -VP SECURED GRATE, VANDAL-PROOF SCREWS -16 GRATE WITH 4" ROUND FUNNEL -17 GRATE WITH 6" ROUND FUNNEL			
-8 ALUMINUM DEPRESSED GRATE -VP SECURED GRATE, VANDAL-PROOF SCREWS -16 GRATE WITH 4" ROUND FUNNEL -17 GRATE WITH 6" ROUND FUNNEL		-4	THREE-QUARTER (3/4) GRATE
-VP SECURED GRATE, VANDAL-PROOF SCREWS -16 GRATE WITH 4" ROUND FUNNEL -17 GRATE WITH 6" ROUND FUNNEL	П	-7	FULL GRATE WITH 2-1/2" CENTER OPENING
-16 GRATE WITH 4" ROUND FUNNEL -17 GRATE WITH 6" ROUND FUNNEL		-8	ALUMINUM DEPRESSED GRATE
-17 GRATE WITH 6" ROUND FUNNEL	П	-VP	SECURED GRATE, VANDAL-PROOF SCREWS
		-16	GRATE WITH 4" ROUND FUNNEL
-18 GRATE WITH 9" x 3-1/2" OVAL FUNNEL		-17	GRATE WITH 6" ROUND FUNNEL
	П	-18	GRATE WITH 9" x 3-1/2" OVAL FUNNEL


-24 CHAINED GRATE

1	-31	SEDIMENT BUCKET, ALUMINUM
T	-33	SEDIMENT BUCKET, ACID RESISTANT FINISH
1	-35	BUCKET LINER (STAINLESS STEEL MESH)
T	-43	INTERNAL DOME STRAINER, ACID RESISTANT FINIS

- -45 LESS INTERNAL DOME STRAINER -51 GALV. CAST IRON, INSIDE AND OUTSIDE (NO ARE)
- -52 PAINTED, INSIDE AND OUTSIDE (NO ARE)
- -55 1/2" PRIMER TAP
- -X INSIDE CAULK OUTLET -Z NO HUB OUTLET

*MUST ALSO SPECIFY -31, -33 OPTION

DATE OF LAST CHANGE: **JOSAM COMPANY** IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA. MICHIGAN CITY, INDIANA



SANITARY FLOOR SINK JOSAM 49700-LF SERIES RECTANGULAR CAST IRON 3-1/2" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, 4"x8" RECTANGULAR TOP, BOTTOM OUTLET, ALUMINUM INTERNAL SECONDARY STRAINER. 3-1/2" DEEP CAST IRON NON-TRAFFIC ACID-RESISTING GRATE. 49700-LF **SERIES** FORMERLY 49710 SERIES SLOT WIDTH 3/8" GRATE FREE AREA 7 SQ. IN. PIPE SIZE 2" 9/16" 3" **-** 3 3/8" x 7 3/8" **-**ianum manana 3 1/2" 6 7/8" -SECONDARY STRAINER CAULK (-X) PIPE SIZE X | -LF | LESS FLANGE -30 STAINLESS STEEL SEDIMENT BUCKET -43 INTERNAL SECONDARY STRAINER, ACID RESISTANT FINISH -NB NICKEL BRONZE TRAFFIC TOP LG LESS GRATE LESS INTERNAL SECONDARY STRAINER -3 HALF (1/2) GRATE -51 GALV, CAST IRON, INSIDE AND OUTSIDE (NO ARE) -4 THREE-QUARTER (3/4) GRATE -52 PAINTED, INSIDE AND OUTSIDE (NO ARE) -7 FULL GRATE WITH 2-1/2" CENTER OPENING -55 1/2" PRIMER ADAPTER, 88450 PROVIDED -8 STAINLESS STEEL DEPRESSED GRATE -X INSIDE CAULK OUTLET -16 GRATE WITH 4" ROUND FUNNEL Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE DATE OF LAST CHANGE: NOTES **JOSAM COMPANY** IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA USE OF SUPERSEDED OR VOID DATA

SPECIFICATION:


JOSAM 49700-NB SERIES RECTANGULAR CAST IRON 4" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, DUBLE DRAINAGE FLANGE WITH WEEPHOLES, BOTTOM OUTLET, ALUMINUM INTERNAL SECONDARY STRAINER, NIKALOY RIM AND LIGHT-DUTY ANTI-TILTING NIKALOY GRATE.

SANITARY FLOOR SINK

4"x8" RECTANGULAR TOP, 4" DEEP

SERIES 49700-NB

NOTES



JOSAM COMPANY

MICHIGAN CITY, INDIANA

SPECIFICATION: SANITARY FLOOR SINK JOSAM 49700-LF-NB SERIES RECTANGULAR CAST IRON 4" DEEP 4"x8" RECTANGULAR TOP. SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, BOTTOM OUTLET, ALUMINUM INTERNAL SECONDARY STRAINER, NIKALOY RIM AND LIGHT-DUTY ANTI-TILTING NIKALOY GRATE. 4" DEEP SERIES 49700-LF-NB FORMERLY 49610 SERIES SLOT WIDTH 1/4" GRATE FREE AREA 10 SQ. IN. PIPE SIZE – 4 1/2" x 8 1/2" – 2" 7/32" 3" — 3 3/8" x 7 3/8" —**►** NIIIINIIIIINIII 3 15/16 7 5/16" SECONDARY STRAINER CAULK (-X) PIPE SIZE -LF LESS FLANGE -16 GRATE WITH 4" ROUND FUNNEL -NB NICKEL BRONZE TRAFFIC TOP -30 STAINLESS STEEL SEDIMENT BUCKET -LG LESS GRATE -43 INTERNAL SECONDARY STRAINER, ACID RESISTANT FINISH -3 HALF (1/2) GRATE -45 LESS INTERNAL SECONDARY STRAINER -4 THREE-QUARTER (3/4) GRATE GALV. CAST IRON, INSIDE AND OUTSIDE (NO ARE) -7 FULL GRATE WITH 2-1/2" CENTER OPENING -52 PAINTED, INSIDE AND OUTSIDE (NO ARE) -8 ALUMINUM DEPRESSED GRATE -55 1/2" PRIMER ADAPTER, 88450 PROVIDED -VP SECURED GRATE, VANDAL-PROOF SCREWS -X INSIDE CAULK OUTLET DATE OF LAST CHANGE: NOTES

JOSAM COMPANY

MICHIGAN CITY, INDIANA

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.


5/16/14

DATE OF LAST CHANGE: 2/27/15

IMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA



JOSAM COMPANY

MICHIGAN CITY, INDIANA

NOTES

CAST IRON NON-TRAFFIC ACID-RESISTING GRATE. 49720-LF **SERIES** FORMERLY 49730 SERIES SLOT WIDTH 3/8" GRATE FREE AREA 22 SQ. IN. 6 1/4" x 12 3/8" -5/16" -- 5 5/8" x 11 1/2" TRIIN II ARIINI II ARIINI Y 6 9/16" 11 1/4" PIPE SIZE 3' 4" SECONDARY STRAINER - PIPE SIZE -CAULK (-X) -LF LESS FLANGE -30 STAINLESS STEEL SEDIMENT BUCKET -NB NICKEL BRONZE TRAFFIC TOP -43 INTERNAL SECONDARY STRAINER, ACID RESISTANT FINISH -LG LESS GRATE -45 LESS INTERNAL SECONDARY STRAINER -3 HALF (1/2) GRATE -51 GALV, CAST IRON, INSIDE AND OUTSIDE (NO ARE) THREE-QUARTER (3/4) GRATE -52 PAINTED, INSIDE AND OUTSIDE (NO ARE) -55 1/2" PRIMER TAP (6"), ADAPTER 88450 PROVIDED (3"-4") FULL GRATE WITH 2-1/2" CENTER OPENING -8 STAINLESS STEEL DEPRESSED GRATE -X INSIDE CAULK OUTLET -16 GRATE WITH 4" ROUND FUNNEL -18 GRATE WITH 9" x 3-1/2" OVAL FUNNEL Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE DATE OF LAST CHANGE: NOTES **JOSAM COMPANY** IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA USE OF SUPERSEDED OR VOID DATA

SANITARY FLOOR SINK

6" x 12" RECTANGULAR TOP.

6-1/2" DEEP

SPECIFICATION:

JOSAM SERIES 49720-LF RECTANGULAR CAST IRON 6-1/2" DEEP

BOTTOM OUTLET, ALUMINUM INTERNAL SECONDARY STRAINER,

SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR.


JOSAM SERIES 49720-NB RECTANGULAR CAST IRON 7" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, DOUBLE DRAINAGE FLANGE WITH WEEPHOLES, BOTTOM OUTLET, ALUMINUM INTERNAL SECONDARY STRAINER, NIKALOY RIM AND LIGHT-DUTY ANTI-TILTING NIKALOY GRATE.

SANITARY FLOOR SINK

6" x 12" RECTANGULAR TOP, 7" DEEP

SERIES

49720-NB



			'	,
Δ		-LF	LESS FLANGE	-30
	Х	-NB	NICKEL BRONZE TRAFFIC TOP	-43
		-LG	LESS GRATE	-45
		-3	HALF (1/2) GRATE	-51
		-4	THREE-QUARTER (3/4) GRATE	-52
		-7	FULL GRATE WITH 2-1/2" CENTER OPENING	-55
		-8	ALUMINUM DEPRESSED GRATE	-C
		-VP	SECURED GRATE, VANDAL-PROOF SCREWS	-X
		-16	GRATE WITH 4" ROUND FUNNEL	
		-18	GRATE WITH 9" x 3-1/2" OVAL FUNNEL	

Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

CLAMP DEVICE INSIDE CAULK OUTLET

NOTES

STAINLESS STEEL SEDIMENT BUCKET INTERNAL SECONDARY STRAINER, ACID RESISTANT FINISH LESS INTERNAL SECONDARY STRAINER GALV, CAST IRON, INSIDE AND OUTSIDE (NO ARE) PAINTED, INSIDE AND OUTSIDE (NO ARE) 1/2" PRIMER TAP (6"), ADAPTER 88450 PROVIDED (3"-4")


SPECIFICATION:

JOSAM SERIES 49720-LF-NB RECTANGULAR CAST IRON 7" DEEP SUPER-FLO-SEPTOR® FLOOR SINK WITH ACID RESISTING INTERIOR, BOTTOM OUTLET, ALUMINUM INTERNAL SECONDARY STRAINER, NIKALOY RIM AND LIGHT-DUTY ANTI-TILTING NIKALOY GRATE.

SANITARY FLOOR SINK 6" x 12" RECTANGULAR TOP, 7" DEEP

49720-LF-NB SERIES

FORMERLY 49630 SERIES





Х	-LF	LESS FLANGE		-30	STAINLESS STEEL SEDIMENT BUCKET
Х	-NB	NICKEL BRONZE TRAFFIC TOP		-43	INTERNAL SECONDARY STRAINER, ACID RESISTANT FINISH
	-LG	LESS GRATE		-45	LESS INTERNAL SECONDARY STRAINER
	-3	HALF (1/2) GRATE		-51	GALV. CAST IRON, INSIDE AND OUTSIDE (NO ARE)
	-4	THREE-QUARTER (3/4) GRATE		-52	PAINTED, INSIDE AND OUTSIDE (NO ARE)
	-7	FULL GRATE WITH 2-1/2" CENTER OPENING		-55	1/2" PRIMER TAP (6"), ADAPTER 88450 PROVIDED (3"-4")
	-8	ALUMINUM DEPRESSED GRATE		-X	INSIDE CAULK OUTLET
	-VP	SECURED GRATE, VANDAL-PROOF SCREWS			
	-16	GRATE WITH 4" ROUND FUNNEL			
	-18	GRATE WITH 9" x 3-1/2" OVAL FUNNEL			

Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE


DATE OF LAST CHANGE: IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA





55000 Series KLEENATRON® II ASSEMBLY



Cleanouts 211


JOSAM 55000 SERIES COATED CAST IRON KLEENATRON® II LEVELEZE® FLOOR CLEANOUT, INTERNAL ABS CLEANOUT PLUG. ADJUSTABLE CAST IRON HOUSING WITH SPECIAL-DUTY SCORIATED SECURED ROUND CAST IRON COVER.

CI FANOUT

ROUND CAST IRON TOP

SERIES

55000



PIPE SIZE	Α	В	С	D	x	Y
2" *	6	3-3/4	7-1/2	5-9/16	2-3/4	4-1/4
3" *	6	3-3/4	7-1/2	5-9/16	2-3/4	4-1/4
4" *	6	3-3/4	7-1/2	5-9/16	2-3/4	4-1/4
4" -X **	7-1/2	4-1/4	9-3/16	7	2-5/8	4-5/16
5" -Z **	6	3-3/4	7-1/2	5-9/16	2-3/4	4-1/4
6" -Z**	7-1/2	4-1/4	9-3/16	7	2-5/8	4-5/16

* PLUG SIZE = 3-1/2" NPT ** PLUG SIZE = 5-1/2" NPT

		-3	BUFF POLISH NIKALOY
Δ		-1	SATIN FINISH NIKALOY TOP
Δ	П	-1-12	COVER RECESSED FOR TILE, SATIN FINISH NIKALOY
Δ	П	-1-13	TERRAZO TILE COVER, SATIN FINISH NIKALOY
Δ		-1-SD	SPECIAL-DUTY SATIN FINISH NIKALOY TOP
Δ			SQUARE TOP, SATIN FINISH NIKALOY
	П	-2	SATIN FINISH BRONZE TOP
	П	-2-12	COVER RECESSED FOR TILE, SATIN FINISH BRONZE
	П	-2-13	TERRAZO TILE COVER, SATIN FINISH BRONZE
		-2-SD	SPECIAL-DUTY SATIN FINISH BRONZE TOP
	П	-2-SQ	SQUARE TOP, SATIN FINISH BRONZE TOP
Δ	П	-5	DUCTILE IRON TOP
		-14	CARPET CLEANOUT MARKER
	Δ	SEPAR	ATE SUBMITTAL FOR THIS OPTION AVAILAB

BUFF POLISH BRASS -22 BRONZE PLUG -31 GALVANIZED CAST IRON PARTS -41 CLAMP RING AND FLANGE -CFC CARPET CLEANOUT FLANGE COVER -F FLANGE ONLY -SS STAINLESS STEEL TOP -SS-SD SPECIAL DUTY STAINLESS STEEL TOP (N/A 4"X AND 6"Z) -SS-SQ SQUARE TOP, STAINLESS STEEL -VP SECURED COVER, VANDAL-PROOF SCREWS -X INSIDE CAULK OUTLET -Y HUB OUTLET W/GASKET (2", 3", & 4" SIZES ONLY) -Z NO-HUB OUTLET

BLE

DATE OF LAST CHANGE:	10/28/14
DIMENSIONS ARE SUBJECT TO MA TOLERANCES AND CHANGE WIT WE CAN ASSUME NO RESPON:	HOUT NOTICE.
USE OF SUPERSEDED OR V	

JOSAM COMPANY MICHIGAN CITY, INDIANA


SPECIFICATION: JOSAM 55000-1 SERIES COATED CAST IRON KLEENATRON II LEVELEZE FLOOR CLEANOUT, INTERNAL ABS CLEANOUT PLUG, ADJUSTABLE CAST IRON HOUSING WITH MEDIUM-DUTY SCORIATED SECURED

ROUND SATIN NIKALOY COVER.

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

CLEANOUT **ROUND NIKALOY TOP**

55000-1 **SERIES**



	-14	CARPET CLEANOUT MAR	KNEK		-vvr	WIDE FLANGE
-VP SECURED COVER, VANDAL-PROOF SCREWS					-CFC	CARPET CLEANOUT FLANGE COVER
	-22	TAPER THREAD BRONZE	PLUG		-X	INSIDE CAULK OUTLET
	-31	GALVANIZED CAST IRON	PARTS		-Y	HUB OUTLET W/ GASKET (2",3"&4" SIZES ONLY)
	-41	CLAMP RING AND FLANG	E		-Z	NO-HUB OUTLET
DA [*]	TE OF	LAST CHANGE: 9/03/2014	10044	_		MDANY NOTES
 DIM	NICION	C ADE CUID IECT TO MANUEACTUDEDO				NIPARY

MICHIGAN CITY, INDIANA

JOSAM 55000-1-SD SERIES COATED CAST IRON KLEENATRON® II LEVELEZE® FLOOR CLEANOUT, INTERNAL ABS CLEANOUT PLUG, ADJUSTABLE CAST IRON HOUSING WITH SPECIAL-DUTY SCORIATED SECURED ROUND LAMINATED SATIN NIKALOY COVER.


CLEANOUT


ROUND NIKALOY LAMINATE TOP

55000-1-SD SERIES

FLANGE STANDARD ON 4" -X AND 6" SIZES.







	PIPE SIZE	Α	В	С	D	X	Υ
	2"	6-9/16	3-3/4	7-1/2	5-9/16	3	4-1/2
	3"	6-9/16	3-3/4	7-1/2	5-9/16	3	4-1/2
	4"	6-9/16	3-3/4	7-1/2	5-9/16	3	4-1/2
	4" -X	8-3/16	4-1/4	9-3/16	7	2-7/8	4-9/16
	5" -Z	6-9/16	3-3/4	7-1/2	5-9/16	3	4-1/2
lΠ	6" -Z	8-3/16	4-1/4	9-3/16	7	2-7/8	4-9/16

Х	-1-SD	SPECIAL-DUTY SATIN FINISH NIKALOY TOP	-F	FLANGE ONLY
	-14	CARPET CLEANOUT MARKER	-WF	WIDE FLANGE
	-VP	SECURED COVER, VANDAL-PROOF SCREWS	-CFC	CARPET CLEANOUT FLANGE COVER
	-22	TAPER THREAD BRONZE PLUG	-X	INSIDE CAULK OUTLET
	-31	GALVANIZED CAST IRON PARTS		HUB OUTLET W/GASKET (2", 3", & 4"
	-41	CLAMP RING AND FLANGE		SIZES ONLY)
			-Z	NO-HUB OUTLET

DATE OF LAST CHANGE: IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

SPECIFICATION:

JOSAM 55000-1-SQ SERIES COATED CAST IRON KLEENATRON® II LEVELEZE® FLOOR CLEANOUT, INTERNAL ABS CLEANOUT PLUG, ADJUSTABLE CAST IRON HOUSING WITH MEDIUM-DUTY SCORIATED SECURED SQUARE SATIN NIKALOY COVER.


CLEANOUT

SQUARE NIKALOY TOP

55000-1-SQ **SERIES**

FLANGE STANARD ON 4" -X AND 6" SIZES





	PIPE SIZE	A	В	C	טן	Х	Y
	2"	5-3/8	3-3/4	7-1/2	5-9/16	2-1/8	3-5/8
	3"	5-3/8	3-3/4	7-1/2	5-9/16	2-1/8	3-5/8
	4"	5-3/8	3-3/4	7-1/2	5-9/16	2-1/8	3-5/8
	4"-X	7	4-1/4	9-3/16	7	2	3-11/16
	5"-Z	5-3/8	3-3/4	7-1/2	5-9/16	2-1/8	3-5/8
[6"-Z	7	4-1/4	9-3/16	7	2	3-11/16

Х	-1-SQ	SQUARE TOP, SATIN FINISH NIKALOY	-F	FLANGE ONLY
L	-14	CARPET CLEANOUT MARKER	-WF	WIDE FLANGE
	-VP	SECURED COVER, VANDAL-PROOF SCREWS	-CFC	CARPET CLEANOUT FLANGE COVER
	-22	TAPER THREAD BRONZE PLUG	-X	INSIDE CAULK OUTLET
\perp		GALVANIZED CAST IRON PARTS	-Y	HUB OUTLET W/GASKET (2", 3", 4" SIZES ONLY)
L	-41	CLAMP RING AND FLANGE	-Z	NO-HUB OUTLET

DATE OF LAST CHANGE:

JOSAM COMPANY DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA. MICHIGAN CITY, INDIANA

Cleanouts

SPECIFICATION:


JOSAM 55000-1-12 SERIES COATED CAST IRON KLEENATRON® II LEVELEZE® FLOOR CLEANOUT, INTERNAL ABS CLEANOUT PLUG, ADJUSTABLE CAST IRON HOUSING WITH MEDIUM-DUTY SCORIATED SECURED ROUND SATIN NIKALOY COVER RECESSED FOR TILE.

CLEANOUT

ROUND NIKALOY TOP, RECESSED FOR TILE

SERIES

55000-1-12



		PIPE SIZE	Α .	В	C	D	X	Y
[2"	5-1/8	3-3/4	7-1/2	5-9/16	2-1/8	3-5/8
		3"	5-1/8	3-3/4	7-1/2	5-9/16	2-1/8	3-5/8
Ī		4"	5-1/8	3-3/4	7-1/2	5-9/16	2-1/8	3-5/8
	П	4" -X	6-5/8	4-1/4	9-3/16	7	2	3-11/16
		5" -Z	5-1/8	3-3/4	7-1/2	5-9/16	2-1/8	3-5/8
		6" -Z	6-5/8	4-1/4	9-3/16	7	2	3-11/16

Х	-1-12	COVER RECESSED FOR TILE, SATIN FINISH NIKALOY	-F	FLANGE ONLY
	-14	CARPET CLEANOUT MARKER	-WF	WIDE FLANGE
	-VP	SECURED COVER, VANDAL-PROOF SCREWS	-CFC	CARPET CLEANOUT FLANGE COVER
	-22	TAPER THREAD BRONZE PLUG		INSIDE CAULK OUTLET
	-31	GALVANIZED CAST IRON PARTS		HUB OUTLET W/GASKET (2", 3", & 4" SIZES ONLY)
	-41	CLAMP RING AND FLANGE		NO-HUB OUTLET

DATE OF LAST CHANGE:	04/18/15
DIMENSIONS ARE SUBJECT TO M	
TOLERANCES AND CHANGE WIT	
WE CAN ASSUME NO RESPON	ISIBILITY FOR
USE OF SUPERSEDED OR V	OID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:

JOSAM 55000-1-12-SQ SERIES COATED CAST IRON KLEENATRON®II LEVELEZE® FLOOR CLEANOUT, INTERNAL ABS CLEANOUT PLUG, ADJUSTABLE CAST IRON HOUSING WITH MEDIUM-DUTY SCORIATED SECURED SQUARE SATIN NIKALOY COVER RECESSED FOR TILE.

CLEANOUT

SQUARE NIKALOY TOP, RECESSED FOR TILE

55000-1-12-SQ



JOSAM 55000-1-13 SERIES COATED CAST IRON KLEENATRON® II LEVELEZE® FLOOR CLEANOUT, INTERNAL ABS CLEANOUT PLUG, ADJUSTABLE CAST IRON HOUSING WITH MEDIUM-DUTY SCORIATED SECURED ROUND SATIN NIKALOY COVER RECESSED FOR TERRAZZO FLOORING

FLANGE STANDARD ON 4" -X AND 6" SIZES.

CLEANOUT

ROUND TERRAZZO TOP


55000-1-13 SERIES



-OPTIONAL (-F) FLANGE

THREADED

ABS PLUG



PIPE SIZE	Α	В	С	D	х	Y
2"	5-1/4	3-3/4	7-1/2	5-9/16	2-7/8	4-3/8
3"	5-1/4	3-3/4	7-1/2	5-9/16	2-7/8	4-3/8
4"	5-1/4	3-3/4	7-1/2	5-9/16	2-7/8	4-3/8
4" -X	6-5/8	4-1/4	9-3/16	7	2-3/4	4-7/16
5" -Z	5-1/4	3-3/4	7-1/2	5-9/16	2-7/8	4-3/8
6" -Z	6-5/8	4-1/4	9-3/16	7	2-3/4	4-7/16

Х	-1-13	COVER RECESSED FOR TILE, SATIN FINISH NIKALOY	-F	FLANGE ONLY
	-14	CARPET CLEANOUT MARKER	-CFC	CARPET CLEANOUT FLANGE COVER
	-VP	SECURED COVER, VANDAL-PROOF SCREWS	-X	INSIDE CAULK OUTLET
	-22	TAPER THREAD BRONZE PLUG	-Y	HUB OUTLET W/GASKET (2", 3", & 4" SIZES ONLY)
	-31	GALVANIZED CAST IRON PARTS	-1	
	-41	CLAMP RING AND FLANGE	-Z	NO-HUB OUTLET

DATE OF LAST CHANGE: IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:

JOSAM 55000-2-SD SERIES COATED CAST IRON KLEENATRON® II LEVELEZE® FLOOR CLEANOUT, INTERNAL ABS CLEANOUT PLUG, ADJUSTABLE CAST IRON HOUSING WITH SPECIAL-DUTY SCORIATED SECURED ROUND LAMINATED SATIN BRONZE COVER.


CLEANOUT

ROUND BRONZE LAMINATE TOP

55000-2-SD **SERIES**



FLANGE STANDARD ON 4" -X AND 6" SIZES.



	PIPE SIZE	Α	В	С	D	х	Υ
Г	2"	6-9/16	3-3/4	7-1/2	5-9/16	3	4-1/2
	3"	6-9/16	3-3/4	7-1/2	5-9/16	3	4-1/2
	4"	6-9/16	3-3/4	7-1/2	5-9/16	3	4-1/2
	4" -X	8-3/16	4-1/4	9-3/16	7	2-7/8	4-9/16
	5" -Z	6-9/16	3-3/4	7-1/2	5-9/16	3	4-1/2
1	6" -Z	8-3/16	4-1/4	9-3/16	7	2-7/8	4-9/16

X	-2-SD	SPECIAL-DUTY SATIN FINISH BRONZE TOP		-F	FLANGE ONLY
	-14	CARPET CLEANOUT MARKER		-WF	WIDE FLANGE
Ш	-VP	SECURED COVER, VANDAL-PROOF SCREWS		-CFC	CARPET CLEANOUT FLANGE COVER
	-22	TAPER THREAD BRONZE PLUG		-X	INSIDE CAULK OUTLET
	-31	GALVANIZED CAST IRON PARTS	П		HUB OUTLET W/GASKET (2", 3", & 4"
	-41	CLAMP RING AND FLANGE	Ш	-1	SIZES ONLY)
				-Z	NO-HUB OUTLET

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA


JOSAM 55000-5 SERIES COATED CAST IRON KLEENATRON® II LEVELEZE® FLOOR CLEANOUT, INTERNAL ABS CLEANOUT PLUG, ADJUSTABLE CAST IRON HOUSING WITH SPECIAL-DUTY SCORIATED SECURED ROUND DUCTILE IRON COVER.

CLEANOUT

ROUND DUCTILE IRON TOP

SERIES

55000-5



х	-5	DUCTILE IRON TOP
		CARPET CLEANOUT MARKER
	-VP	SECURED COVER, VANDAL-PROOF SCREWS
	-22	TAPER THREAD BRONZE PLUG
	-31	GALVANIZED CAST IRON PARTS
	-41	CLAMP RING AND FLANGE

-F	FLANGE ONLY			
-CFC	CARPET CLEANOUT FLANGE COVER			
-X	INSIDE CAULK OUTLET			
	HUB OUTLET W/GASKET (2", 3", & 4" SIZES ONLY)			
-Z	NO-HUB OUTLET			

DATE OF LAS	ST CHANGE:	04/23/15
DIMENSIONS AR	E SUBJECT TO M	IANUFACTURER
	AND CHANGE WI	
	UME NO RESPON	
LISE OF SI	IPERSEDED OR V	/OID DATA

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

SPECIFICATION:

JOSAM 56670 SERIES ROUND CAST NIKALOY FLOOR CLEANOUT,


BOTTOM OUTLET INSIDE CAULK CONNECTION AND THREADED SATIN

SCORIATED ROUND COVER WITH SPANNER WRENCH SOCKETS.


CLEANOUT

SPANNER TYPE FLOOR CLEANOUT









PIPE SIZE	В	С	Е
2"	4-1/16	5-3/8	3-1/4
3"	6-1/4	7-3/8	3-1/4
4"	6-1/4	7-3/8	3-1/4
5"	8-3/16	9-3/8	3-1/2
6"	8-3/16	9-3/8	3-1/2

-2 SATIN FINISH BRONZE TOP	
-11	SMOOTH TOP
-14	CARPET CLEANOUT MARKER
-24	SPANNER WRENCH

DATE OF LAST CHANGE: 11/14/14

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.


JOSAM COMPANY MICHIGAN CITY, INDIANA

JOSAM 57008-Z-CI SERIES COATED CAST IRON LEVELEZE® KLEENATRON® FLOOR CLEANOUT, INTERNAL GASKETED ABS CLEANOUT PLUG, NO-HUB CONNECTION AND ADJUSTABLE ABS HOUSING WITH SPECIAL-DUTY SCORIATED SECURED ROUND CAST IRON TOP.

CLEANOUT

LEVELEZE® KLEENATRON®

57008-Z-CI **SERIES**



Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE

JOSAM COMPANY

MICHIGAN CITY, INDIANA


SPECIFICATION:

JOSAM 57008-Z-1 SERIES COATED CAST IRON KLEENATRON® LEVELEZE® FLOOR CLEANOUT, INTERAL GASKETED ABS CLEANOUT PLUG. NO-HUB CONNECTION AND ADJUSTABLE ABS HOUSING WITH MEDIUM-DUTY SCORIATED SECURED ROUND SATIN NIKALOY TOP.

CLEANOUT

LEVELEZE® KLEENATRON® NO-HUB OUTLET

57008-Z-1 **SERIES**



MICHIGAN CITY, INDIANA

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.


SPECIFICATION:

JOSAM 57008-Z-1-SD SERIES COATED CAST IRON KLEENATRON® LEVELEZE® FLOOR CLEANOUT; INTERNAL GASKETED ABS CLEANOUT PLUG, NO-HUB CONNECTION AND ADJUSTABLE ABS HOUSING WITH SPECIAL-DUTY SCORIATED SECURED ROUND LAMINATED SATIN NIKAI OY TOP


CLEANOUT

LEVELEZE® KLEENATRON®

SERIES 57008-Z-1-SD



MICHIGAN CITY, INDIANA




JOSAM 57008-Z-1-12 SERIES COATED CAST IRON KLEENATRON® LEVELEZE® FLOOR CLEANOUT, INTERNAL GASKETED ABS CLEANOUT PLUG, NO-HUB CONNECTION AND ADJUSTABLE ABS HOUSING WITH MEDIUM-DUTY SCORIATED SECURED ROUND SATIN NIKALOYTOP RECESSED FOR TILE.

CLEANOUT

LEVELEZE® KLEENATRON®

57008-Z-1-12 SERIES



MICHIGAN CITY, INDIANA

SPECIFICATION: **CLEANOUT** JOSAM 57008-Z-LT SERIES COATED CAST IRON CLEANOUT FERRULE WITH NO-HUB CONNECTION AND GASKETED ABS CLEANOUT PLUG. LEVELEZE® KLEENATRON® 57008-Z-LT **SERIES** FORMERLY 58190 SERIES NO-HUB CONNECTION 6" GASKETED ABS CLEANOUT PLUG Ø8' -LT LESS TOP -22 TAPER THREAD BRONZE PLUG -31 GALVANIZED CAST IRON PARTS -WF WIDE FLANGE -Z NO-HUB OUTLET NOTES DATE OF LAST CHANGE: JOSAM COMPANY DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

MICHIGAN CITY, INDIANA

TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.


JOSAM 58360 SERIES COATED CAST IRON FERRULE AND ADJUSTABLE CAST NIKALOY FLOOR CLEANOUT, INTEGRAL BRONZE COUNTERESUNK PLUG AND SOLID SCORIATED SECURED ROUND

CLEANOUT

ADJUSTABLE FLOOR CLEANOUT

SERIES

58360



PIPE SIZE	Α	В	С	D
2"-Z	2	1-1/2	4	4-1/2
3"-Z	2	1-1/2	4	3-1/8
4"-Z	3	2-3/4	5	3-3/8
5"-Z	3	2-3/4	5	4-1/4
6"-Z	3	2-3/4	5	4-1/4

	PIPE SIZE	Α	В	С	D	
	2"-Y	2	1-1/2	4	3-1/8	
	3"-Y	3	2-3/4	5	3-3/8	
	4"-Y			4-1/4		
GASKET ON -Y CONNECTION						

CONFORMS WITH ASTM-C564

-2	SATIN FINISH BRONZE TOP
-14	CARPET CLEANOUT MARKER
-31	GALVANIZED CAST IRON PARTS
-VP	SECURED COVER, VANDAL-PROOF SCREWS
-Y	HUB OUTLET W/GASKET (2"-4" SIZES) ONLY
-Z	NO-HUB SPIGOT OUTLET

DATE OF LAST CHANGE:	04/23/15
DIMENSIONS ARE SUBJECT TO N TOLERANCES AND CHANGE WI	THOUT NOTICE.
WE CAN ASSUME NO RESPON USE OF SUPERSEDED OR	

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

SPECIFICATION:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.


WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM 58460A SERIES COATED CAST IRON FLOOR CLEANOUT. INTERNAL BRONZE COUNTERSUNK PLUG. INSIDE CAULK OUTLET AND SCORIATED ROUND TOP.

CLEANOUT FLOOR CLEANOUT

SERIES

58460A



JOSAM COMPANY MICHIGAN CITY, INDIANA

JOSAM 58460A-AE SERIES COATED CAST IRON LEVELEZE® FLOOR CLEANOUT, ADJUSTABLE COLLAR WITH ROLLED THREAD AND INTERNAL BRONZE COUNTERSUNK PLUG, INDICATED COUNTER SUNK PLUG, INDICATED COUNTED CONNECTION, SATIN NIKALOY RIM AND SCORIATED ROUND NIKALOY COVER.

CLEANOUT


WITH LEVELEZE® ADJUSTABLE EXTENSION

SERIES

s 58460A-AE







	PIPE SIZE	D
	2"	3
П	3"	4
	4"	5

*THIS DIM 9" SQ. ON (-6) SQUARE TOP

\[\bar{\bar{\bar{\bar{\bar{\bar{\bar{	X	-AE	ADJUSTABLE EXTENSION
Г	Т	-1	SATIN FINISH NIKALOY TOP
Г	Т	-2	SATIN FINISH BRONZE TOP
		-6	SQUARE TOP, CAST IRON
Г	Т	-6-1	SQUARE TOP, NIKALOY
		-6-2	SQUARE TOP, BRONZE
	I	-12	TOP RECESSED FOR TILE
Г	Т	-14	CARPET CLEANOUT MARKER
	Т	-VP	SECURED COVER, VANDAL-PROOF SCREWS
Г		-20	RAISED HEAD BRONZE PLUG
Г	T	-31	GALVANIZED CAST IRON PARTS

DATE OF LAST CHANGE: 04/23/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

SPECIFICATION:

JOSAM 58540 SERIES COUNTERSINK BRONZE N.P.T. THREADED PLUG FOR USE IN CONJUNCTION WITH JOSAM CLEANOUTS OR STANDARD PIPE FITTINGS.


CLEANOUT

THREADED BRONZE PLUG


SERIES

58540

	PIPE SIZE	В	С
	1"	1/2	3/8
П	1-1/4"	1/2	3/8
	1-1/2"	1/2	3/8
\exists	2"	5/8	3/8
	2-1/2"	7/8	3/8
	3"	1/2	3/8
П	3-1/2"	1/2	3/8
	4"	1/2	3/8
П	5"	5/8	1/2
П	6"	1/2	1/2
П	8"	3/4	1/2







PIPE SIZE	В	С
1"	3/8	5/16
1-1/4"	3/8	5/16
1-1/2"	3/8	5/16
2"	3/8	5/16
2-1/2"	3/8	3/8
3"	1/2	3/8
3-1/2"	1/2	3/8
4"	1/2	3/8
5"	1/2	3/8
5-1/2"	5/8	3/8
6"	1	1
8"	1	1
10"	1	1-1/8

-19 PLUG TAPPED FOR CENTER SCREW

-20 RAISED HEAD FOR BRONZE PLUG

*10" SIZE AVAILABLE IN RAISED HEAD BRONZE PLUG ONLY

DATE OF LAST CHANGE: 05/04/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSECED OR YOUID DATA.

JOSAM COMPANY
MICHIGAN CITY, INDIANA


DAT



JOSAM 58580 SERIES ABS FLOOR ACCESS HOUSING WITH SPECIAL-DUTY SCORIATED SECURED ROUND CAST IRON TOP AND LEVELOC® SCREWS

ACCESS HOUSING & COVER

58580 **SERIES**




14	OCARA OOMBA
	OSAM COMPA
NOTICE. Y FOR	MICHIGAN CITY, INDIANA
TA.	WINCH TOATS OF THE INDIANA

NOTES

SPECIFICATION: JOSAM 58580-1 SERIES ABS FLOOR ACCESS HOUSING WITH SCORIATED SECURED ROUND SATIN NIKALOY TOP AND LEVELOC®

CLEANOUT **ACCESS HOUSING & COVER**

58580-1 **SERIES**



JOSAM COMPANY MICHIGAN CITY, INDIANA

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

LEVELOC

SCREWS

JOSAM 58580-1-SD SERIES ABS FLOOR ACCESS HOUSING WITH SPECIAL-DUTY SCORIATED SECURED ROUND LAMINATED SATIN NIKALOY TOP AND LEVELOC® SCREWS

FORMERLY 56060-88-1 SERIES


CLEANOUT

ACCESS HOUSING & COVER

SERIES

58580-1-SD

HOUSING



J <u> </u>	*B CLEANOUT PIPE SUPPLIED BY OTHERS	PING

Х	-1	SATIN FINISH NIKALOY TOP
Х	-SD	SPECIAL-DUTY TOP, NIKALOY

PIPE SIZE	Α	*B	С	D
2"	6	3-3/16	4-1/8	2-9/16
3"	7-5/8	5-3/16	4-1/8	2-9/16
4"	7-5/8	5-3/16	4-1/8	2-9/16
5"	9-3/4	7-3/8	4-1/8	2-9/16
6"	9-3/4	7-3/8	4-1/8	2-9/16

* MAXIMUM SPACE AVAILABLE FOR PIPE FITTING ENCLOSURE ETC.

DATE OF LAST CHANGE: 04/23/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

SPECIFICATION:


FORMERLY 56020-88 SERIES

JOSAM 58580-1-SQ SERIES ABS FLOOR ACCESS HOUSING WITH MEDIUM-DUTY SCORIATED SECURED SQUARE SATIN NIKALOY TOP AND LEVELOC® SCREWS

CLEANOUT

ACCESS HOUSING & COVER

SERIES 58580-1-SQ



X	-1	ISATIN FINISH NIKALOY TOP
X	-SQ	SQUARE TOP


	PIPE SIZE	A	В	С	D	*E	
	2"	5-3/8	3-9/16	3-1/4	2-9/16	4	
	3"	7	5-3/16	3-1/4	2-9/16	5-3/4	
	4"	7	5-3/16	3-1/4	2-9/16	5-3/4	
	5"	9-1/4	7-3/8	3-1/4	2-9/16	7-15/16	
	6"	9-1/4	7-3/8	3-1/4	2-9/16	7-15/16	


* MAXIMUM SPACE AVAILABLE FOR PIPE FITTING ENCLOSURE ETC.

DATE OF LAST CHANGE: 04/23/15

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA






JOSAM 58600-COT SERIES ROUND STAINLESS STEEL WALL ACCESS COVER WITH SCREW AND NO-HUB CLEANOUT TEE.

CLEANOUT

WALL ACCESS COVER WITH CLEANOUT TEE

SERIES

58600-COT



1	PIPE SIZE	В	С	D	Е	F
[2"	3-3/16"	2	6-3/8	2	5-3/8
ſ	3"	3-7/8"	2-11/16	7-3/4	3	5-3/8
Γ	4"	4-7/16"	3	8-7/8	4	5-3/8
[6"	6-1/4"	5	12-1/2	6	7-5/8

Г	П	-VP	SECURED COVER, VANDAL-PROOF SCREWS
	X	-COT	NO-HUB CLEANOUT TEE
	\Box	-17	CENTER SCREW LONGER THAT STANDARD
	\Box	-20	RAISED HEAD BRONZE PLUG
		-31	GALVANIZED CAST IRON PARTS

DATE OF LAST CHANGE: 04/23/15

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA NOTES


SPECIFICATION:

JOSAM 58600-PLG SERIES ROUND STAINLESS STEEL WALL ACCESS COVER WITH SCREW AND THREADED NPT BRONZE PLUG.

CLEANOUT
WALL ACCESS COVER W/ PLUG

series 58600-PLG

FORMERLY 58890 SERIES



-VP SECURED COVER, VANDAL-PROOF SCREWS

-PLG BRONZE NPT PLUG (SPECIFY PLUG SIZE)
-17 CENTER SCREW LONGER THAN STANDARD

-20 RAISED HEAD BRONZE PLUG

	TYPE NO.	PIPE SIZE	В
	58604-PLG1-1/2	1-1/2	5-3/8
	58604-PLG2	2	5-3/8
	58604-PLG2-1/2	2-1/2	5-3/8
	58604-PLG3	3	5-3/8
	58604-PLG3-1/2	3-1/2	5-3/8
	58606-PLG4	4	8
Î	58606-PLG5	5	8
i I	58606-PLG6	6	8

DRAWING No. 08/01/13


A-07781-K JOSAM COMPANY
MICHIGAN CITY, INDIANA

DATE OF LAST CHANGE: 4/7/14

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.

WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.



JOSAM COMPANY

MICHIGAN CITY, INDIANA

NOTES

FORMERLY 58700 SERIES -COVER PIPE SIZE ØB-NPT ØЕ ØF ØC- OPENING TYPE NO. PIPE SIZE В Ε F 58614-CO2 2" 1-1/2 4-5/8 6 5-1/2 58614-CO3 2-1/2 4-5/8 6 5-1/2 58614-CO4 58616-CO5 8-1/4 -CO NO-HUB CLEANOUT (SPECIFY PIPE SIZE) SECURED COVER, VANDAL-PROOF SCREWS SATIN FINISH BRONZE SCORIATED COVER CARPET CLEANOUT MARKER -20 RAISED HEAD BRONZE PLUG -31 GALVANIZED CAST IRON PARTS DATE OF LAST CHANGE: NOTES **JOSAM COMPANY** DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA USE OF SUPERSEDED OR VOID DATA.

CLEANOUT

WALL OR FLOOR ACCESS COVER WITH CLEANOUT

SERIES

58610-CO

SPECIFICATION:

COVER AND NO-HUB CLEANOUT.

JOSAM 58610-CO SERIES ROUND CAST NIKALOY ACCESS

FRAME AND ANCHOR LUGS AND SATIN SMOOTH SECURED


JOSAM 58610-COT SERIES ROUND CAST NIKALOY ACCESS FRAME AND ANCHOR LUGS AND SATIN SMOOTH SECURED COVER AND NO-HUB CLEANOUT TEE.

CLEANOUT

WALL OR FLOOR ACCESS COVER WITH CLEANOUT TEE

SERIES

58610-COT



TYPE NO.	PIPE SIZE	В	С	D	E	F
58614-COT2	2"	3-3/16"	2	6-3/8	2	6
58614-COT3	3"	3-7/8"	2-11/16	7-3/4	3	6
58614-COT4	4"	4-7/16"	3	8-7/8	4	6
58616-COT6	6"	6-1/4"	5	12-1/2	6	8-1/4

Х	-COT	NO-HUB CLEANOUT TEE (SPECIFY PIPE SIZE)
	-VP	SECURED COVER, VANDAL-PROOF SCREWS
	-2	SATIN FINISH BRONZE
	-10	SCORIATED COVER
	-14	CARPET CLEANOUT MARKER
	-20	RAISED HEAD BRONZE PLUG
	-31	GALVANIZED CAST IRON PARTS

DATE OF LAST CHANGE: 04/23/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

SPECIFICATION:

JOSAM 58620 SERIES ROUND CAST NIKALOY ACCESS FRAME AND ANCHOR FLANGE AND SATIN SMOOTH HINGED COVER.

CLEANOUT


WALL OF FLOOR ACCESS COVER

SERIES

58620



Ε



6-5/8

6-1/4

3/4

$\overline{}$		
Ш	-VP	SECURED COVER, VANDAL-PROOF SCREWS
	-2	SATIN FINISH BRONZE
	-10	SCORIATED COVER
	-14	CARPET CLEANOUT MARKER
	-20*	RAISED HEAD BRONZE PLUG
	-31*	GALVANIZED CAST IRON PARTS
	-CO2	NO-HUB CLEANOUT, 2"
	-CO3	NO HUB CLEANOUT, 3"
	-CO4	NO-HUB CLEANOUT, 4"
	-CO6	NO-HUB CLEANOUT, 6"
	-COT2	NO-HUB CLEANOUT TEE, 2"
П	-COT3	NO-HUB CLEANOUT TEE, 3"
П	-COT4	NO-HUB CLEANOUT TEE, 4"
	-COT6	NO-HUB CLEANOUT TEE, 6"

2", 3" & 4" 5-3/8 5" & 6" 6-7/8


*SPECIFY -CO OR -COT

DATE OF LAST CHANGE: 04/23/15

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.

WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA



58630-CO **SERIES** FORMERLY 58730 SERIES -HINGED SCORIATED COVER 1 1/2" ANCHOR LUGS CLEANOUT PLUG-ØB-NPT → SIZE PIPE SIZE TYPE NO. В CxC 58631-CO2 1-1/2 8 x 8 58631-CO3 3" 2-1/2 8 x 8 58631-CO4 3-1/2 8 x 8 58632-CO6 5-1/2 12 x 12 NO-HUB CLEANOUT (SPECIFY PIPE SIZE) -CO -VP SECURED COVER, VANDAL-PROOF SCREWS -2 SATIN FINISH BRONZE RAISED HEAD BRONZE PLUG GALVANIZED CAST IRON PARTS DATE OF LAST CHANGE: NOTES **JOSAM COMPANY** DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA USE OF SUPERSEDED OR VOID DATA.

CLEANOUT

WALL OR FLOOR ACCESS COVER WITH CLEANOUT

SPECIFICATION:

JOSAM 58630-CO SERIES CAST NIKALOY ACCESS

HINGED COVER AND NO-HUB CLEANOUT.

FRAME AND ANCHOR LUGS, SATIN SCORIATED SECURED


JOSAM 58630-COT SERIES SQUARE CAST NIKALOY ACCESS FRAME AND ANCHOR LUGS, SATIN SCORIATED SECURED HINGED COVER AND NO-HUB CLEANOUT TEE.

CLEANOUT

WALL OR FLOOR ACCESS COVER WITH CLEANOUT TEE

SERIES

58630-COT



	TYPE NO.	PIPE SIZE	В	С	D	E	FxF
	58631-COT2	2"	3-3/16"	2	6-3/8	2	8 x 8
\Box	58631-COT3	3"	3-7/8"	2-11/16	7-3/4	3	8 x 8
	58631-COT4	4"	4-7/16"	3	8-7/8	4	8 x 8
	58632-COT6	6"	6-1/4"	5	12-1/2	6	12 x 12

	X	-COT	NO-HUB CLEANOUT TEE (SPECIFY PIPE SIZE)
Г		-VP	SECURED COVER, VANDAL-PROOF SCREWS
Г	П	-2	SATIN FINISH BRONZE
		-20	RAISED HEAD BRONZE PLUG
Γ		-31	GALVANIZED CAST IRON PARTS

DATE OF LAST CHANGE: 04/23/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA


NOTES

SPECIFICATION:

JOSAM 58640 SERIES SQUARE CAST NIKALOY ACCESS FRAME AND ANCHOR LUGS AND SATIN SMOOTH SECURED COVER.

CLEANOUT WALL OF FLOOR ACCESS COVER

SERIES 58640



JOSAM COMPANY
MICHIGAN CITY, INDIANA

Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

*SPECIFY -CO OR -COT

SPECIFICATION:

JOSAM 58640-CO SERIES SQUARE CAST NIKALOY ACCESS

FRAME AND ANCHOR LUGS, SATIN SMOOTH SECURED COVER

CLEANOUT


WALL ACCESS COVER WITH CLEANOUT

SERIES

58640-CO



AND NO-HUB CLEANOUT.



1	Х	-CO	NO-HUB CLEANOUT (SPECIFY PIPE SIZE)
	П	-VP	SECURED COVER, VANDAL-PROOF SCREWS
	П	-2	SATIN FINISH BRONZE
1			SCORIATED COVER
		-20	RAISED HEAD BRONZE PLUG
		-31	GALVANIZED CAST IRON PARTS

DATE OF LAST CHANGE: 04/23/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA NOTES


SPECIFICATION:

JOSAM 58640-COT SERIES SQUARE CAST NIKALOY ACCESS FRAME AND ANCHOR LUGS, SATIN SMOOTH SECURED COVER AND NO-HUB CLEANOUT TEE.

CLEANOUT

WALL ACCESS COVER WITH CLEANOUT TEE

SERIES 58640-COT



111 - 110.	I II L OILL	"	"	"	_	' ^ '
58642-COT2	2"	3-3/16	1-3/4	6-3/8	2	7 x 7
58642-COT3	3"	3-7/8	2-1/2	7-3/4	3	7 x 7
58642-COT4	4"	4-7/16	3-1/2	8-7/8	4	7 x 7
58644-COT6	6"	6-1/4	4-1/2	12-1/2	6	9 x 9

X	-COT	NO-HUB CLEANOUT TEE (SPECIFY PIPE SIZE)
		SECURED COVER, VANDAL-PROOF SCREWS
	-2	SATIN FINISH BRONZE
	-10	SCORIATED COVER
	-20	RAISED HEAD BRONZE PLUG
	-31	GALVANIZED CAST IRON PARTS

DATE OF LAST CHANGE: 04/23/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY
MICHIGAN CITY, INDIANA


JOSAM 58656 SERIES SQUARE STAINLESS STEEL ACCESS FRAME, ANCHOR SLOTS AND HINGED SMOOTH SECURED COVER

CLEANOUT

WALL ACCESS COVER

SERIES

58656



	-20*	RAISED HEAD BRONZE PLUG
	-31*	GALVANIZED CAST IRON PARTS
	-CO2	NO-HUB CLEANOUT, 2"
	-CO3	NO-HUB CLEANOUT, 3"
Г	-CO4	NO-HUB CLEANOUT, 4"
	-CO6	NO-HUB CLEANOUT, 6"
	-COT2	NO-HUB CLEANOUT TEE, 2"
	-COT3	NO-HUB CLEANOUT TEE, 3"
	-COT4	NO-HUB CLEANOUT TEE, 4"
	-COT6	NO-HUB CLEANOUT TEE, 6"

^{*} SPECIFY -CO OR -COT

DATE OF LAST CHANGE: 04/23/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

SPECIFICATION:


JOSAM 58680 SERIES ROUND COATED CAST IRON ACCESS FRAME WITH ANCHOR FLANGES AND HEAVY-DUTY SCORIATED SECURED COVER.

CLEANOUT

ACCESS COVER

SERIES

58680




SPECIAL WORDING ON COVER SAN OR STORM (SPECIFY ON ORDER)


	-VP	SECURED COVER, VANDAL-PROOF SCREWS
	-5	DUCTILE IRON COVER
П	-20	RAISED HEAD BRONZE PLUG
	-26	GASKETED COVER
	-31	GALVANIZED CAST IRON PARTS
	-CO2	NO-HUB CLEANOUT, 2"
П	-CO3	NO-HUB CLEANOUT, 3"
П	-CO4	NO-HUB CLEANOUT, 4"
П	-CO6	NO-HUB CLEANOUT, 6"


DATE OF LAST CHANGE: 04/23/15

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.


JOSAM COMPANY MICHIGAN CITY, INDIANA









60100H-GRD Series Interceptor on floor, servicing a sink, shown installed with an optional -GRD Grease Removal Device.







60100-SA-RT Series Semi-Automatic Interceptor recessed flush with floor, servicing a dishwasher.




60115A Series Interceptor installed on floor under sink. (Recommended only if there is adequate head room for cover removal and service.)



60115-SA Series Semi-Automatic shallow Interceptor installed on floor, servicing a double compartment sink and dishwasher.



60210A-EGOLD Series Interceptor with factory installed Josam EGOLD-1000 Electronic Grease/Oil Level Detector for installation in high volume applications such as hotels, hospitals and schools.



FLOW CONTROLS • ESSENTIAL FOR MAXIMUM EFFICIENCY

Flow control fittings are furnished at no extra cost with all JOSAM Interceptors and Separators. These devices govern flow rate to the interceptor or separator being used, thereby assuring the maximum retention of the material being intercepted.

The appropriate flow control will be shipped with every JOSAM Grease Interceptor or Oil Separator. They were designed after many years of tests and field experiments with interceptor installations under varying conditions and ensure 90% or more grease or oil retention efficiency of the interceptor.

When consideration isn't given to the flow rate of the waste water to be handled, generally the actual flow rate through the interceptor or separator exceeds its rated maximum. With such flow rate, the interceptor or separator would be overloaded. Retention time within the unit would not be sufficient for maximum separation. The result would be low efficiency and pollutants left in the waste water would pass through the interceptor or separator making the installation less than effective. When the flow is controlled by use of a JOSAM flow control fitting so that it can never exceed the maximum rating of the interceptor or separator, and the unit is cleaned on a regular basis, the maximum pollutant retention efficiency will be achieved and maintained.


All flow controls are provided with an air intake and should be connected to vent stack or vent not lower than the flow level of highest drain serviced or terminated in a return bend at the same elevation outside of building.

This table indicates which series flow control is furnished with the JOSAM interceptors or separators shown.

FLOW CONTROLS										
Series	Flow Control Series	Series	Flow Control Series	Series	Flow Control Series					
60100-SA	60730	60110A	60730	60210A*	60710					
60110-SA	60730	60100H-EXT	60740	60500B	60740					
60100-SA-RT	60730	60100H-RT	60740	60500B-EXT	60740					
60100-SA-ET	60730	60100H-ET	60740	60610-EXT*	60710					
60100H	60740	60210A-EXT*	60710	60610A*	60710					

^{*} All interceptors or separators in this series with a flow rate of 150 G.P.M. or less are shipped with a 60733 & 60734 Type Flow Control.

	DIMENSIONS IN INCHES											
Туре	Α	В	С	D	E	F	G	Н	J	K	LBS.	
60712	2	1-1/4	2-1/2	2	1-1/8	2	3-1/4	3-3/8	6-1/2	3	7	
60713	3	1-1/2	3	2-7/8	1-3/8	2-3/4	4-1/8	4-1/2	8-5/8	4-1/4	14	
60714	4	2-1/2	3-3/4	4-1/8	1-7/8	4-1/4	6-1/2	6-7/8	12	6-7/8	52	
60715	5	2-1/2	3-3/4	4-1/8	1-7/8	4-1/4	6-1/2	6-7/8	12	6-7/8	54	
60716	6	3	4-3/8	5-1/8	2-1/8	4-3/4	7-7/8	8	14-1/4	8	85	




JOSAM 60100H SERIES ACID-RESISTING EPOXY COATED FABRICATED STEEL GREASE INTERCEPTOR, NO-HUB CONNECTIONS, INTERNAL TRAP, REMOVABLE BAFFLE, GASKETED NON-SKID COVER AND FLOW CONTROL FITTING.

GREASE INTERCEPTOR

MANUAL TYPE

SERIES 60100H



Δ		GREASE/OIL LEVEL DETECTOR (15-100GPM SIZES) STAINLESS STEEL INTERCEPTOR	TYPE	FLOW (GPM)	CAP. (LBS.)			D	Е	F	G
Δ	-GRD	GREASE REMOVAL DEVICE (TIMER)	60102H	7	14	2	8-1/4	3-3/8	14-7/8	13	11-5/8
l [-40	COVER RECESS FOR FLOOR FINISH	60103H	10	20	2	8-1/2	3-3/8	16-5/8	14-1/2	11-7/8
Ι[-61	FLANGE AND CLAMP DEVICE	60104H	15	30	2	9-1/2	3-3/8	20-3/8	17	12-7/8
[-85	ENZYMATIC PORT IN COVER	60105H	20	40	3	12	4-7/8	20-7/8	19	16-7/
П	-ISI	INTEGRATED SOLIDS INTERCEPTOR	60106H	25	50	3	13	4-7/8	23-3/8	21-1/2	17-3/8
Δ	-EXT	EXTENSION, 6" STANDARD (SPECIFY EXT. HEIGHT)	60107H	35	70	3	14-1/2	4-7/8	26-1/8	23	19-3/8
$ \Delta $	-RT	RECESSED TYPE	60108H	50	100	3	16-1/2	4-7/8	27-7/8	25-1/2	21-3/8
$ \Delta $	-ET	ENCLOSED TYPE	60109H	75	150	3	21	6	41	31	27
Ιĺ	-HD	HEAVY-DUTY COVER	60110H	100	200	4	23	8	47	35	31

Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE

DATE OF LAST CHANGE: 7/25/14

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA


NOTES


SPECIFICATION:

JOSAM SERIES 60100H-BXT EPOXY COATED FABRICATED STEEL BOLT-ON EXTENSION FOR 60100H SERIES INTERCEPTORS WITH RUBBER GASKET THAT ALLOWS RE-USE OF COVER SHIPPED WITH STANDARD UNIT.

GREASE INTERCEPTOR BOLT-ON EXTENSION

SERIES 60100H-BXT





SPECIFY "C"


:=



MODEL	Α	В		
60102H-BXT	13	14-7/8		
60103H-BXT	14-1/2	16-5/8		
60104H-BXT	17	20-3/8		
60105H-BXT	19	20-7/8		
60106H-BXT	21-1/2	23-3/8		
60107H-BXT	23	26-1/8		
60108H-BXT	25-1/2	27-7/8		
60109H-BXT	31	41		
60110H-BXT	35	47		

DATE OF LAST CHANGE: 08/05/10
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY
MICHIGAN CITY, INDIANA



			TYPE	FLOW (GPM)	CAP. (LBS.)
			60104H	15	30
Х	-EGOLD	GREASE LEVEL DETECTOR	60105H		40
	-SS	STAINLESS STEEL INTERCEPTOR	60106H		50
П	-61	FLANGE AND CLAMP DEVICE	60107H	35	70
	-ISI	INTEGRATED SOLIDS INTERCEPTOR	60108H	50	100
П	-EXT	EXTENSION, 6" STD. (SPECIFY EXT. HT)	60109H	75	150
	-HD	HEAVY-DUTY COVER	60110H	100	200

-BAFFLE

1	60105H		40	3			20-7/8		16-7/8
1	60106H	25	50	3	13	4-7/8	23-3/8	21-1/2	17-3/8
11	60107H	35	70	3	14-1/2	4-7/8	26-1/8	23	19-3/8
11	60108H	50	100	3	16-1/2	4-7/8	27-7/8	25-1/2	21-3/8
1	60109H	75	150	3	21	6	41	31	27
1	60110H	100	200	4	23	8	47	35	31

NO-HUB

OUTLET

STATIC WATER LINE

DATE OF LAST CHANGE: IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA

INLET

JOSAM COMPANY MICHIGAN CITY, INDIANA

С D

SIZE

Ε

2 9-1/2 3-3/8 20-3/8 17 12-7/8

GREASE INTERCEPTOR

GREASE LEVEL SENSING AND ALARM

> EGOLD-1000 WALL BOX AND PROBE

> > G

SERIES 60100H-EGOLD

SPECIFICATION: JOSAM 60100H-GRD SERIES EPOXY COATED FABRICATED STEEL GREASE INTERCEPTOR, NO-HUB CONNECTIONS, INTERNAL TRAP. REMOVABLE DIFFUSER BAFFLE, GASKETED NON-SKID CENTER BOLT COVER, FLOW CONTROL FITTING AND PDI SEAL OF APPROVAL (60104-60108 SIZES). ADJUSTABLE TIMER (1-99 DAYS) CONTROLS INTERNAL PUMP FOR REMOVAL OF GREASE TO FACTORY STORAGE

TANK.


GREASE INTERCEPTOR WITH GREASE REMOVAL DEVICE

SERIES 60100H-GRD

10 FT.

TIMER / CONTROLLER

ALARM



- 1		*60104H-GRD	15	30	2	9-1/2	3-3/8	20-3/8	17	12-7/8
- 1		*60105H-GRD	20	40	3	12	4-7/8	20-7/8	19	16-7/8
- 1		*60106H-GRD	25	50	3	13	4-7/8	23-3/8	21-1/2	17-7/8
- 1		**60107H-GRD	35	70	3	14-1/2	4-7/8	26-1/8	23	19-3/8
- 1		**60108H-GRD	50	100	3	16-1/2	4-7/8	27-7/8	25-1/2	21-3/8
- 1	Г	***60109H-GRD	75	150	3	21	6	41	31	27
- 1	Г	***60110H-GRD	100	200	4	23	8	47	35	31
	,	5 Gal. Tank	** 10 Gal. T	ank	*** 30 Gal. T	ank				
- 17	\ A T	E OF LACT OUANOR	0/4/44					NOTE	0	

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

JOSAM SERIES 60100H-ISI EPOXY COATED STEEL SOLIDS BASKET FOR USE IN SERIES 60100H GREASE INTERCEPTORS. PERFORATED SCREEN ON SIDES AND BOTTOM TO BE ϕ 5/32" HOLES WITH 62% OPEN AREA.


INTERCEPTOR


INTEGRATED SOLIDS BASKET

60100H-ISI SERIES


FOR 60109H - 60110H STAND AND BASKET SET







USE OF SUPERSEDED OR VOID DATA.



NOTES

DATE OF LAST CHANGE: **JOSAM COMPANY** IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

MICHIGAN CITY, INDIANA

DATE OF LAST CHANGE DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.


SPECIFICATION:

JOSAM 60100H-EXT SERIES EPOXY COATED FABRICATED STEEL GREASE INTERCEPTOR, DEEP ROUGHING INTEGRAL EXTENSION FLUSH-WITH-FLOOR TYPE, NO-HUB CONNECTIONS, INTERNAL TRAP, REMOVABLE DIFFUSER BAFFLE, GASKETED NON-SKID COVER, FLOW CONTROL FITTING AND PDI SEAL OF APPROVAL.

GREASE INTERCEPTOR MANUAL TYPE


60100H-EXT **SERIES**








ACCEPTED FOR USE CITY OF NEW YORK DEPARTMENT OF BUILDINGS MEA 255-06-E VOL. 1



For Custom Extension Height:
Specify "D" Dimension = in.
New "G" Dimension =in.

		GREASE/OIL LEVEL DETECTOR (15-100gpm sizes)		TYPE	FLOW	CAP.	PIPE	С	*D	F	-	*G
	-SS	STAINLESS STEEL INTERCEPTOR		11176	(GPM)	(LBS.)	SIZE		"	-	F	1 4
	-GRD	GREASE REMOVAL DEVICE (TIMER)	П	60102H-EXT	7	14	2	8-1/4	9-3/8	14-7/8	13	17-5/8
	-40	COVER RECESS FOR FLOOR FINISH	П	60103H-EXT	10	20	2	8-1/2	9-3/8	16-5/8	14-1/2	17-7/8
	-61	FLANGE AND CLAMP DEVICE	П	60104H-EXT	15	30	2	9-1/2	9-3/8	20-3/8	17	18-7/8
	-85	ENZYMATIC PORT IN COVER		60105H-EXT	20	40	3	12	10-7/8	20-7/8	19	22-7/8
Х	-EXT	EXTENSION, 6" STANDARD (SPECIFY EXT. HEIGHT)	П	60106H-EXT	25	50	3	13	10-7/8	23-3/8	21-1/2	23-3/8
	-ISI	INTEGRATED SOLIDS INTERCEPTOR	П	60107H-EXT	35	70	3	14-1/2	10-7/8	26-1/8	23	25-3/8
	-HD	HEAVY-DUTY COVER	П	60108H-EXT	50	100	3	16-1/2	10-7/8	27-7/8	25-1/2	27-3/8
				60109H-EXT	75	150	3	21	12	41	31	33
				60110H-EXT	100	200	4	23	14	47	35	37
				*DIMENSIO	NS BA	SED (ON ST	TANDA	RD 6"	EXTE	NSION	1


JOSAM COMPANY MICHIGAN CITY, INDIANA



JOSAM 60:00H.RT SERIES EPOXY COATED FABRICATED STEEL GREASE INTERCEPTOR. DEEP ROUGHING FLUSH-WITH-FLOOR TYPE, NO-HUB CONNECTIONS, INTERNAL TRAP, REMOVABLE DIFFUSER BAFFLE, GASKETED NON-SKID COVER, FLOW CONTROL FITTING, PID SEAL OF APPROVAL AND STEEL FRAME WITH NON-SKID COVER AND ADJUSTABLE INTERCEPTOR CARRER BRACKET.

GREASE INTERCEPTOR
MANUAL RECESSED TYPE

SERIES 60100H-RT



	-EGOLD	GREASE/OIL LEVEL DETECTOR (15-100gpm)			CAP.			С	*D	F	F	G
	-40	COVER RECESS FOR FLOOR FINISH	ITPE	RATE	LBS.	SIZE	ь	C	U		Г	G
П	-61	FLANGE AND CLAMP DEVICE	60102H-RT	7	14	2	15	8-1/4	8-3/4	14-7/8	23	15-3/4
П	-85	ENZYMATIC PORT IN COVER	60103H-RT	10	20	2	16-1/2	8-1/2	8-3/4	16-5/8	24-3/4	15-3/4
П	-ISI	INTEGRATE SOLIDS INTERCEPTOR	60104H-RT	15	30	2	19	9-1/2	8-3/4	20-3/8	28-1/2	15-3/4
Х	-RT	RECESSED TYPE	60105H-RT	20	35	3	21	12	10-1/4	20-7/8	29	15-3/4
П	-HD	HEAVY-DUTY COVER	60106H-RT	25	50	3	23-1/2	13	10-1/4	23-3/8	31-1/2	15-3/4
-			60107H-RT	35	70	3	25	14-1/2	10-1/4	26-1/8	34-1/4	15-3/4
			60108H-RT	50	100	3	27-1/2	16-1/2	10-1/4	27-7/8	36	15-3/4
			60109H-RT	75	150	3	33	21	11-3/8	41	49-1/8	15-3/4
			60110H-RT	100	200	4	37	23	13-3/8	47	55-1/8	15-3/4
			-									

*DIMENSIONS BASED ON INTERCEPTOR IN POSITION #1 ADD 1-1/4" PER EACH SUCCEEDING LOWER POSITION

DATE OF LAST CHANGE: 4/24/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.


JOSAM COMPANY MICHIGAN CITY, INDIANA

JOSAM 60100-SA SERIES EPOXY COATED FABRICATED STEEL SEMI-AUTOMATIC GREASE INTERCEPTOR WITH THREADED CONNECTIONS. INTERNAL AIR-RELIEF, VISIBLE DOUBLE WALL TRAP, REMOVABLE BAFFLE, GASKETED NON-SKID COVER, GREASE RECOVERY COME FLEXIBLE HOSE, GREASE DRAW-OFF VALVE AND FLOW CONTROL

GREASE INTERCEPTOR

SEMI-AUTOMATIC ON-FLOOR TYPE

60100-SA **SERIES**



JOSAM COMPANY MICHIGAN CITY, INDIANA

50 100 *3"

60108-SA

60109-SA 75 150 *3"

*3" SIZES NORMALLY FURNISHED WITH 4" x 3" REDUCING BUSHING

15-1/2 4-7/8 37-1/4 19-3/4 20-3/8

17-1/2 6 40-5/8 22 23-1/2

SPECIFICATION:

4"x3" REDUCING BUSHING

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.

DATE OF LAST CHANGE:


JOSAM 60100-SA-ET SERIES EPOXY COATED FABRICATED STEEL SEMI-AUTOMATIC GREASE INTERCEPTOR, DEEP ROUGHING FLUSH-WITH-FLOOR TYPE WITH THREADED CONNECTIONS, INTERNAL AIR-RELIEF, VISIBLE DOUBLE WALL TRAP, REMOVABLE BAFFLE, GASKETED NON-SKID COVER, GREASE RECOVERY COME, FLEXIBLE HOSE, GREASE DRAW-OFF VALVE, FLOW CONTROL FITTING AND STEEL ENCLOSURE CABINET WITH NON-SKID COVER AND ADJUSTABLE INTERCEPTOR CARRIER BRACKETS.

GREASE INTERCEPTOR

SEMI-AUTOMATIC **ENCLOSED TYPE**

60100-SA-ET SERIES

FORMERLY 60140-50A SERIES



JOSAM COMPANY

ADD 1-1/4" PER EACH SUCCEEDING LOWER POSITION.

MICHIGAN CITY, INDIANA

OPTION AVAILABE

IMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.

WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.

DATE OF LAST CHANGE:


JOSAN 80100 SA PT SERIES EPOXY COATED FABRICATED STEEL SEMI-AUTOMATIC GREASE INTERCEPTOR DEEP FOLIGHING FLUSH WITH-FLOOR TYPE WITH THREADED CONNECTIONS, INTERNAL AIR-RELIEF, VISIBLE DOUBLE WALL TRAP, REMOVABLE BAFFLE, GASKETED NON-SKID COVER, GREASE RECOVERY CONE, FLEXIBLE HOSE, GREASE DRAW-OFF VALVE, FLOW ADJUSTABLE WITERCEPTOR CARRIER BRACKETSKID COVER AND

GREASE INTERCEPTOR

SEMI-AUTOMATIC RECESS TYPE

SERIES 60100-SA-RT

FORMERLY 60130-50A SERIES



*3" SIZES NORMALLY FURNISHED WITH 4"x3" REDUCING BUSHING

☐ DIMENSIONS BASED ON INTERCEPTOR IN POSITION #1; ADD 1-1/4" PER EACH SUCCEEDING LOWER POSITION.

DATE OF LAST CHANGE: 9/4/14

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA

JOSAM COMPANY
MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:

JOSAM 60110A SERIES EPOXY COATED FABRICATED STEEL GREASE INTERCEPTOR, SHALLOW TYPE, THREADED CONNECTIONS, INTERNAL AIR-RELIEF, VISIBLE DOUBLE WALL TRAP, REMOVABLE BAFFLE, GASKETED NON-SKID COVER AND FLOW CONTROL FITTING.

GREASE INTERCEPTOR

MANUAL LOW TYPE

SERIES 60110A



	-65	HUB INLET, SPIGOT OUTLET 2"	TVDE	FLOW	CAP.	PIPE	_	_	_	G	
	-66	HUB INLET, SPIGOT OUTLET 3"	ITTE	RATE	(LBS.)	SIZE	٦,	_	-	G	
Г	-68	3" INLET & OUTLET (AVAILABLE ON STD. 2" SIZES)	60115A	20	40	*2"	3-1/2	36-3/8	22-5/8	10-1/2	31-5
	-85	ENZYMATIC PORT IN COVER	60117A	35	70	3"	4-1/2	47-3/4	28-5/8	11-1/2	42-5
	-SS	FABRICATED STAINLESS STEEL MATERIAL									

2" SIZES NORMALLY FURNISHED WITH 3" x 2" REDUCING BUSHING

DATE OF LAST CHANGE: 9/5/14

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.


JOSAM COMPANY
MICHIGAN CITY, INDIANA

JOSAM 60110A-SA SERIES EPOXY COATED FABRICATED STEEL SEMI-AUTOMATIC GREASE INTERCEPTOR, SHALLOW TYPE, THREADED CONNECTIONS, INTERNAL AIR RELIEF, VISIBLE DOUBLE WALL TRAP, REMOVABLE BAFFLE, GASKETED NON-SKID COVER GREASE RECOVERY CONE, FLEXIBLE HOSE, GREASE DRAW-OFF VALVE AND FLOW CONTROL FITTING.

GREASE INTERCEPTOR

SEMI-AUTOMATIC LOW TYPE

60110-SA **SERIES**



MICHIGAN CITY, INDIANA


SPECIFICATION:

JOSAM 60210A SERIES ACID RESISTANT EPOXY COATED (INSIDE AND OUT) FABRICATED STEEL GREASE INTERCEPTOR, HIGH VOLUME, THREADED CONNECTIONS, INTERNAL AIR-RELIEF, VISIBLE DOUBLE WALL TRAP, REMOVABLE DIFFUSER BAFFLE, GASKETED NON-SKID COVER AND FLOW CONTROL FITTING.

GREASE INTERCEPTOR

MANUAL HIGH-VOLUME TYPE

60210A **SERIES**



						II TYPE						ΙF		G	
Δ		-EGOLD	ELECTRIC GREASE/OIL LEVEL DETECTOR	·		ITPE	RATE	(LBS)	SIZE	C	ľ	-	г	G	
Δ		-EXT	EXTENSION, 6" STANDARD (SPECIFY EXT. HEIGHT)			60213A	150	300	4	27	8	60	39	35	53
ı		-60	ANCHOR FLANGE	. [60214A	200	400	5	31-1/2	10	67	42	41-1/2	58
ı		-61	FLANGE AND CLAMP DEVICE			60215A	250	500	5	35-1/2	10	72	46	45-1/2	63
Δ		-ISI	INTEGRATED SOLIDS INTERCEPTOR	.		60216A	350	700	6	39-1/2	12	80	52	51-1/2	71
ı		-HD	HEAVY-DUTY COVER	. [60217A	500	1000	6	43-1/2	12	91	59	55-1/2	82
ı	△ SEPERATE SUBMITTAL FOR THIS OPTION AVAILABLE *THIS SIZE FURNISHED WITH ONE-PIECE COVER														

DATE OF LAST CHANGE

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR


USE OF SUPERSEDED OR VOID DATA.


JOSAM COMPANY

MICHIGAN CITY, INDIANA

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.






JOSAM 60210A-ISI SERIES ACID RESISTANT EPOXY COATED FABRICATED STELL GREASE INTERCEPTOR, HIGH VOLUME, THREADED CONNECTIONS, INTERNAL AIR-RELIEF, VISIBLE DOUBLE WALL TRAP, INTEGRATED SOLIDS INTERCEPTOR, GASKETED NON-SKID COVER AND FLOW CONTROL FITTING.

GREASE INTERCEPTOR

MANUAL HIGH-VOLUME TYPE

60210A-ISI **SERIES**



	-EGOLD ELECTRIC GREASE/OIL LEVEL DETECTOR		TYPE	FLOW	CAP.	PIPE	_	٦	F	_	9	н	
	-60	ANCHOR FLANGE		ITPE	RATE	(LBS)	SIZE	٠	٦	_	_	u	
	-61	FLANGE AND CLAMP DEVICE	*	60213A-ISI	150	300	4	27	8	60	39	35	53
Х	-ISI	INTEGRATED SOLIDS INTERCEPTOR		60214A-ISI	200	400	5	31-1/2	10	67	42	41-1/2	58
	-HD	HEAVY-DUTY COVER		60215A-ISI	250	500	5	35-1/2	10	72	46	45-1/2	63
				60216A-ISI	350	700	6	39-1/2	12	80	52	51-1/2	71
				60217A-ISI	500	1000	6	43-1/2	12	91	59	55-1/2	82

*THIS SIZE FURNISHED WITH ONE-PIECE COVER

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

SPECIFICATION:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR


USE OF SUPERSEDED OR VOID DATA.

JOSAM 60300A (GI-2000A) SERIES AUTOMATIC GREASE RECOVERY DEVICE. 304 STAINLESS STEEL SHELL WITH INTEGRATED SUPPLEMENTAL REMOVABLE SOLIDS BASKET, STAINLESS STEEL DRAW LATCHES AND NON-ADHESIVE "U" CHANNEL GASKET, 55 GALLON POLYPROPYLENE RECLAIM TANK WITH ALARM. FACTORY INSTALLED GREASE/OIL LEVEL DETECTOR, HEATING ELEMENTS AND GREASE REMOVAL PUMP.

GREASE INTERCEPTOR

AUTOMATIC GREASE RECOVERY DEVICE

SERIES 60300A (GI-2000A)



_																
	-(CIS	CENTRAL INFO SYSTEM CONNECT			TYPE		CAP.		Α	В	C	D	F	F	G
Г	1	24	EXTENDED WARRANT	TY PACKAGE		ITPE	FLOW	(LBS)	SIZE	^	Р	L C	U	_	Г	G
Г	1	33	55 GAL. STAINLESS R	ECLAIM TANK		60306A	25	50	3	24-3/8	9	3-1/2	16	35-1/2	25-5/8	11
Г	-	34	55 GAL. STEEL RECLA	AIM TANK		60307A	35	70	3	24-3/8	9	3-1/2	20	40-5/8	31-1/2	15-1/2
						60308A	50	100	3	25-7/8	9	3-1/2	22-1/2	42-3/8	33	17-1/2
						60309A	75	150	4	25-7/8	9	3-1/2	26	56-1/8	46-3/4	21-1/2
						60310A+	100	200	4	35	9	3-1/2	31	67-1/2	58	23
						60311A+	150	300	4	39	9	3-1/2	35	73-3/4	64	27
						60312A+	200	400	6	43	9	3-1/2	41	80-3/4	71	31-1/2
						60313A+	250	500	6	47	9	3-1/2	44-3/4	85-3/4	76	35-1/2
					П	60314A+	350	700	6	47	9	3-1/2	48	105-1/2	96	39-1/2
						60315A**	500	1000	6	47	9	3-1/2	51	130-7/8	120	44
1	MI.	NIN	IUM CLEARANCES	+ INCLU	JDES	SEXTERNAL	MACER	RATING	PUMP	** [JTII	LIZES	TWO PL	JMPS & R	ECLAIM	TANKS
DA	ATF	OF	LAST CHANGE:	10/3/14								_ T	NOTES			

JOSAM COMPANY MICHIGAN CITY, INDIANA

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.


SPECIFICATION:

JOSAM EGOLD-1000 SERIES ELECTRONIC GREASE/OIL LEVEL DETECTOR WITH WALL MOUNTED CONTROLLER, POWERED BY ULLISTED 9VDC TRANSFORMER, L.E.D. INDICATORS WITH AUDIBLE ALARM AND 304 STAINLESS STELL PROBE MOUNTING BRACKET (ATTACHED TO INSIDE WALL OF INTERCEPTOR)

GREASE/OIL INTERCEPTOR ELECTRONIC GREASE/OIL LEVEL DETECTOR

SERIES **EGOLD-1000**

NOTES



JOSAM COMPANY


MICHIGAN CITY, INDIANA

SPECIFICATION:

JOSAM CEGOLD-2000 SERIES ELECTRONIC GREASE/OIL LEVEL DETECTOR WITH WALL MOUNTED CONTROLLER POWERED BY UL LISTED BYDC TRANSFORMER, LE D. INDICATORS WITH AUDIBLE ALARM AND PERMANENT MEMORY, STANLESS STEEL MOUNTING PIPE AND BRACKETS. FOR USE IN OUTDOOR PIT STYLE GREASE/ OIL INTERCEPTORS. GREASE/OIL INTERCEPTOR
PIT ELECTRONIC GREASE/
OIL LEVEL DETECTOR

050015 0000

SERIES CEGOLD - 2000



MODEL NUMBER	DISTANCE FROM GRADE TO STATIC WATER LEVEL
CEGOLD-2000-04	22" - 48"
CEGOLD-2000-06	49" - 72"
CEGOLD-2000-08	73" - 96"
CEGOLD-2000-10	97" - 120"

WHEN ORDERING, SPECIFY DISTANCE FROM GRADE TO STATIC WATER LEVEL. LONGER LENGTHS AVAILABLE UPON REQUEST.

DATE OF LAST CHANGE: 5/9/12 DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR	JOSAM COMPANY MICHIGAN CITY INDIANA	NOTES
USE OF SUPERSEDED OR VOID DATA.	MICHIGAN CITY, INDIANA	


JOSAM 60500B SERIES EPOXY COATED FABRICATED STEEL OIL SEPARATOR. THREADED CONNECTIONS, INTERNAL TRAP, SEDIMENT BUCKET, TWO-VENT CONNECTIONS ON EACH SIDE, GASKETED NON-SKID COVER AND FLOW-CONTROL FITTING.

OIL SEPARATOR


DRAW-OFF, GRAVITY TYPE

SERIES

60500B







Δ		-EXT	EXTENSION, 6" STANDARD (SPECIFY EXT. HEIGHT)
Δ		-EST	EXTRA STORAGE TANK
		-60	ANCHOR FLANGE (-EXT REQUIRED)
		-61	FLANGE AND CLAMP DEVICE (-EXT REQUIRED)
		-HD	HEAVY-DUTY COVER
	ΔSE	PARATI	E SUBMITTAL FOR THIS OPTION AVAILABLE

	TYPE	FLOW RATE (GPM)	PIPE SIZE	С	D	E	F	G	М	R	s	
	60503B	10	2"	10 1/2"	4 1/8"	15 1/2"	12 3/8"	14 5/8"	6 5/8"	2 7/8"	8 1/2"	ı
	60504B	15	2"	12 3/4"	3 3/8"	18 1/4"	14 1/2"	16 1/8"	8"	2 5/8"	10 3/4"	ı
	60505B	20	*3"	14 5/8"	4 3/8"	20"	16 3/8"	19"	8 7/8"	2 3/4"	12"	ı
	60506B	25	*3"	16"	4"	21 3/4"	17 1/2"	20"	9 3/4"	2 3/4"	13 1/2"	ı
	60507B	35	*3"	16 3/4"	4 7/8"	25 1/4"	19 1/4"	21 5/8"	11 1/2"	2 3/4"	14 1/4"	ı
	60508B	50	*3"	18 1/2"	6 1/4"	28 3/4"	21 1/2"	24 3/4"	13 1/4"	3"	16"	ı

* 3" SIZES NORMALLY FURNISHED WITH 4" x 3" REDUCING BUSHINGS

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA


NOTES

SPECIFICATION:

JOSAM 60500B-EXT SERIES EPOXY COATED FABRICATED STEEL OIL SEPARATOR, THREADED CONNECTIONS, DEEP ROUGHING, INTERNAL EXTENSION, INTERNAL TRAP, SEDIMENT BUCKET, TWO-VENT, CONNECTIONS ON EACH SIDE, GASKETED NON-SKID COVER AND FLOW-CONTROL FITTING.

OIL SEPARATOR DRAW-OFF, GRAVITY TYPE

60500B-EXT **SERIES**



Х	-EXT	EXTENSION, 6" STANDARD (SPECIFY EXT. HEIGHT)	Н	٢
	-EST	EXTRA STORAGE TANK	П	ľ
П	-60	ANCHOR FLANGE (4" DOWN FROM TOP)	Н	ŀ
	-61	FLANGE AND CLAMP DEVICE (4" DOWN FROM TOP)	П	ı
	Пυ	HEAVY DUTY COVER	П	١

FOR CUSTOM EXTENSION HEIGHT:	
SPECIFY "D" DIMENSION=I	N.
NEW "G" DIMENSION= IN. ("C" + "D")	

	TYPE	FLOW RATE (GPM)	PIPE SIZE	С	□ D	E	F	□G	М	R	s	
	60503B	10	2"	10 1/2"	10 1/8"	15 -1/4"	12 3/4"	20 5/8"	7 1/2"	2 3/4"	8 1/2"	
	60504B	15	2"	13"	10"	18"	14 3/4"	23"	9"	2 3/4"	10 5/8"	
	60505B	20	*3"	14 3/8"	10 3/8"	19 15/16"	16 3/8"	25"	10"	2 3/4"	12"	
	60506B	25	*3"	16"	10"	21 11/16"	17 1/2"	26 1/4"	10 1/2"	2 3/4"	13 1/2"	
	60507B	35	*3"	16 3/4"	10 7/8"	25 1/8"	19 1/4"	27 7/8"	12 1/2"	2 3/4"	14 1/4"	
	60508B	50	*3"	18 1/2"	12 1/4"	28 1/2"	21 1/2"	19 1/4"	14 1/4"	2 3/4"	16"	
DIM	ENSIONS BAS	SED ON STANDA	NRD 6" E	EXTENSI	ON							

* 3" SIZES NORMALLY FURNISHED WITH 4" x 3" REDUCING BUSHINGS

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.


JOSAM COMPANY MICHIGAN CITY, INDIANA

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.

WE CAN ASSUME NO RESPONSIBILITY FOR LISE OF SUPERSEDED OR VOID DATA



*3" PIPE SIZE NORMALLY FURNISHED WITH 4" x 3" REDUCING BUSHING

JOSAM COMPANY MICHIGAN CITY, INDIANA

SPECIFICATION:


JOSAM 60610A SERIES EPOXY COATED FABRICATED STEEL OIL
SEPARATOR, HIGH-VOLUME, THREADED CONNECTIONS, VISIBLE
DOUBLE WALL TRAP AND SEDIMENT BUCKET, ADJUSTABLE GRAVITY
DRAW-OFF EITHER SIDE, TWO VENT CONNECTIONS ON EACH SIDE,

GASKETED NON-SKID COVER AND FLOW-CONTROL FITTING.

OIL SEPARATOR

DRAW-OFF,
HIGH-VOLUME TYPE

SERIES 60610A



		TYPE	FLOW RATE	PIPE SIZE	С	D	Е	F	G	Н	М	N	Р	S
		*60611A	75	3	21	6	46-1/4	31	27	41	8-1/4	12-1/2	10-1/4	13-1/2
Γ		*60612A	100	4	23	8	54	35	31	47	9-1/2	14-1/2	12-1/2	15-1/4
		*60613A	150	4	27	8	60	39	35	53	10-1/2	16-1/2	14-1/2	19-1/4
		60614A	200	5	31-1/2	10	67	42	41-1/2	58	11-1/2	18-1/8	16	26-1/4
		60615A	250	5	35-1/2	10	72	46	45-1/2	63	12-1/2	20-1/4	17-1/2	29-3/4
Γ		60616A	350	6	39-1/2	12	80	52	51-1/2	71	13-1/2	23	19-3/4	34-1/4
		60617A	500	6	43-1/2	12	91	59	55-1/2	82	16	27	23	38-1/4
*T	HE	SE SIZES	FURNISH	ED WIT	H ONE-F	PIECE	COVER							

DATE OF LAST CHANGE: 4/10/15

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.


JOSAM COMPANY MICHIGAN CITY, INDIANA

JOSAM 60610A-EXT SERIES EPOXY COATED FABRICATED STEEL OIL SEPARATOR, HIGH-VOLUME, DEEP ROUGHING, INTEGRAL EXTENSION, THREADED CONNECTIONS, VISIBLE DOUBLE WALL TRAP AND SEDIMENT BUCKET, ADJUSTABLE GRAVITY DRAW-OFF EITHER SIDE, TWO VENT CONNECTIONS ON EACH SIDE, GASKETED NON-SKID COVER AND FLOW-CONTROL FITTING.

OIL SEPARATOR

DRAW-OFF. HIGH-VOLUME TYPE

60610A-EXT SERIES



	X	-EXT	EXTENSION, 6" STANDARD (SPECIFY EXT. HEIGHT)	SPECIFY:
Δ		-EST	EXTRA STORAGE TANK	SPECIFT.
	П	-EXT-60	ANCHOR FLANGE WITH EXTENSION, 6" STANDARD (SPECIFY EXT. HEIGHT)	D =
			FLANGE AND CLAMP DEVICE WITH EXTENSION, 6" STANDARD (SPECIFY EXT. HEIGHT)	G =
		-HD	HEAVY-DUTY COVER	

Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE

		TYPE	FLOW RATE	PIPE SIZE	С	ΠD	E	F	□G	Н	М	N	Р	S
Г		*60611A	75	3	21	12	46-1/4	31	33	41	8-1/4	12-1/2	10-1/4	13-1/2
	П	*60612A	100	4	23	14	54	35	37	47	9-1/2	14-1/2	12-1/2	15-1/4
	\Box	*60613A	150	4	27	14	60	39	41	53	10-1/2	16-1/2	14-1/2	19-1/4
	П	60614A	200	5	31-1/2	16	67	42	47-1/2	58	11-1/2	18-1/8	16	26-1/4
	П	60615A	250	5	35-1/2	16	72	46	51-1/2	63	12-1/2	20-1/4	17-1/2	29-3/4
	\Box	60616A	350	6	39-1/2	18	80	52	57-1/2	71	13-1/2	23	19-3/4	34-1/4
	T	60617A	500	6	43-1/2	18	91	59	61-1/2	82	16	27	23	38-1/4

□DIMENSIONS BASED ON STANDARD 6" EXTENSION *THESE SIZES FURNISHED WITH ONE-PIECE COVER

DATE OF LAST CHANGE: IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:

JOSAM 60610-EST STEEL OIL SEPARATOR, FLUSH-WITH-FLOOR TYPE WITH OIL STORAGE TANK, THREADED CONNECTIONS, FLAT BOTTOM, VISIBLE DOUBLE WALL TRAP, SEDIMENT BUCKET, GASKETED COVER, ACID RESISTANT COATING (INSIDE AND OUT), CHECK VALVE, AND FLOW CONTROL FITTING**.

OIL SEPARATOR

WITH EXTERNAL STORAGE TANK

60610-EST **SERIES**




	-19	RECLAIM TANK ALARM
	-EST-EXT	EXTENSION (SPECIFY "D" DIMENSION) MINIMUM "D" DIMENSION = 8"
Х	-EST	EXTERNAL STORAGE TANK
	-HD	HEAVY DUTY COVER (MUST SPECIFY WITH SEPARATOR ORDER)

	TYPE	FLOW RATE	TANK SIZE (GAL.)	PIPE SIZE	D	E	F	G	н	N	т	v	w	WEIGHT (LBS.)	** FLOW CONTROL
	60611-EST	75	100	3	8	46	31	29	41	12	37	24	59	1200	60714
	60612-EST	100	250	4	8	54	35	31	47	14	48	35	70	1500	60714
	60613-EST	150	250	4	10	60	39	37	53	16	45	35	74	2000	60714
Ī	*60614-EST	200	250	5	15	67	42	49	54	18	48	35	77	2400	60715
Ī	*60615-EST	250	500	5	15	72	46	51	63	20	60	45	91	3000	60715
	*60616-EST	350	500	6	15	80	52	55	71	23	56	45	97	3800	60716
	*60617-EST	500	500	6	26	91	59	70	83	27	66	45	104	5200	60716

*FURNISHED WITH 2-PIECE COVER


USE OF SUPERSEDED OR VOID DATA.

DATE OF LAST CHANGE: **JOSAM COMPANY** IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA



OIL SEPARATOR
WITH EXTERNAL
STORAGE TANK

SERIES 60610-EST-EXT



DATE OF LAST CHANGE: 04/28/15

DIMENSIONS ARE SUBJECT TO MANUFACTURER:
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
LISE OF SUPPERSPED OR YOUR DATA

250 500 5 21 72 46 57 63 20 66 45 91 3000

350 500 6 21 80 52 61 71 23 62 45 97 3800

500 500 6 31 91 59 76 83 27 72 45

*FURNISHED WITH 2-PIECE COVER

*60615-EST

*60616-EST

*60617-EST

JOSAM COMPANY
MICHIGAN CITY, INDIANA

NOTES

5200

60715

60716

60716

SPECIFICATION:


DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA

JOSAM 60610-EST-EXT STEEL OIL SEPARATOR, FLUSH-WITH-FLOOR TYPE WITH OIL STORAGE TANK, THREADED CONNECTIONS, FLAT BOTTOM, VISIBLE DOUBLE WALL TRAP, SEDIMENT BUCKET, GASKETED COVER, ACID RESISTANT COATING (INSIDE AND OUT), CHECK VALVE, AND FLOW CONTROL FITTING**.

OIL SEPARATOR
WITH EXTERNAL
STORAGE TANK

SERIES 60610-EST-EXT-60




JOSAM COMPANY
MICHIGAN CITY, INDIANA

JOSAM 60810 SERIES STEEL OIL SEDIMENT SEPARATOR WITH ACID-RESISTING COATING, THREADED CONNECTION, FLAT BOTTOM, VISIBLE DOUBLE WALL TRAP, REMOVABLE SEDIMENT BUCKET, PRIMARY AND SECONDARY SCREENS AND MEDIUM-DUTY CAST IRON GRATE(S).

OIL SEPARATOR OIL SEDIMENT INTERCEPTOR

60810



DRAWING No. 01/17/13 **JOSAM COMPANY** A-15122-K MICHIGAN CITY, INDIANA

NOTES:

SPECIFICATION:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR


USE OF SUPERSEDED OR VOID DATA.

JOSAM 61000 SERIES NIKALOY SOLIDS INTERCEPTOR, BOTTOM ACCESS FIXTURE TRAP TYPE, SLIP JOINT INLET AND THREADED OUTLET CONNECTIONS, GASKETED COVER AND REMOVABLE PERFORATED STAINLESS STEEL BASKET.

SOLIDS INTERCEPTOR

BOTTOM ACCESS FIXTURE TRAP

61000 **SERIES**



MICHIGAN CITY, INDIANA

DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.

WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

10/16/14

SPECIFICATION:


JOSAM 61030 SERIES COATED CAST IRON SOLIDS INTERCEPTOR, TOP ACCESS FIXTURE TRAP TYPE, THREADED CONNECTIONS, GASKETED COVER, REMOVABLE GALVANIZED STEEL BASKET AND STAINLESS STEEL SCREEN.

SOLIDS INTERCEPTOR TOP ACCESS FIXTURE TRAP

61030

NOTES

SERIES



JOSAM COMPANY

MICHIGAN CITY, INDIANA

SPECIFICATION:

61042A

USE OF SUPERSEDED OR VOID DATA.


JOSAM SERIES 61040A STEEL SOLID INTERCEPTOR, TOP ACCESS ON FLOOR TYPE WITH ACID RESISTING COATING, THREADED CONNECTIONS, LOW INLET AND HIGH OUTLET, GASKETED NON-SKID COVER, REMOVABLE GALVANIZED STEEL BASKET WITH STAINLESS STEEL SCREENS.

SOLIDS INTERCEPTOR

TOP ACCESS ON-FLOOR TRAP

61040A

SERIES



61043A 3 4-1/2 17-5/8 32 -16 MONEL SCREENS 61044A 18-5/8 33 -80SS STAINLESS STEEL BASKET AND SCREENS 4 5-1/2 DATE OF LAST CHANGE: 2/11/2015 DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

16-5/8

3-1/2


JOSAM COMPANY MICHIGAN CITY, INDIANA


SPECIFICATION: SOLIDS INTERCEPTOR JOSAM 61070 SERIES CAST IRON SOLIDS INTERCEPTOR WITH ACID RESISTING COATING, TOP ACCESS, IN-LINE TYPE, THREADED TOP ACCESS IN-LINE TRAP CONNECTIONS, 2" THREADED DRAIN OR BLOW-OFF CONNECTION REMOVABLE PERFORATED COPPER BASKET WITH CONICAL SOLID BOTTOM, GASKETED CAST IRON SUPPORT RIM AND GASKETED COVER SEALED ON BASKET SUPPORT RIM SECURED WITH HEX HEAD BOLTS. 61070 SERIES BASKET FREE AREA: Ö 85.0 SQ. INCHES Ø10 1/2" 13" MIN. CLEARANCE -LIFT LUGS-ACCESS COVER TO LIFT BASKET GASKET-THREADED THREADED OUTLET INLET 4 1/2" 13 1/8" 9 1/2" Ø8 1/2" PERFORATED COPPER BASKET WITH 3/16" HOLES SLOPING BOTTOM WITH BLOWOUT NECK DRAIN CONN SIZE -4 GALVANIZED CAST IRON PARTS 2" -15 STAINLESS STEEL BASKET 3" -86 FLAT BOTTOM BASKET DATE OF LAST CHANGE: NOTES **JOSAM COMPANY** DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.

MICHIGAN CITY, INDIANA

SPECIFICATION: SOLIDS INTERCEPTOR JOSAM 61080 SERIES CAST IRON SOLIDS INTERCEPTOR WITH ACID RESISTING COATING, TOP ACCESS, IN-LINE TYPE, THREADED TOP ACCESS IN-LINE TRAP CONNECTIONS, 2" THREADED DRAIN OR BLOW-OFF CONNECTION. REMOVABLE PERFORATED COPPER BASKET WITH CONICAL SOLID BOTTOM, GASKETED CAST IRON SUPPORT RIM AND GASKETED COVEF SEATED ON BASKET SUPPORT RIM SECURED WITH HEX HEAD BOLTS. 61080 **SERIES** BASKET FREE AREA: 250 SQ. INCHES Ø21 5/8" Ø16 1/2" 16" MIN. ACCESS -LIFT LUGS-CLEARANCE COVER TO LIFT BASKET GASKET-THREADED THREADED OUTLET INLET 6 5/8" PIPE SIZE 20 3/4" 19 5/16" 12 7/8" Ø14 1/2" PERFORATED COPPER BASKET WITH 3/16" HOLES SLOPING BOTTOM WITH BLOWOUT NECK 2" NPT -DRAIN PIPE SIZE -4 GALVANIZED CAST IRON PARTS 4" -15 STAINLESS STEEL BASKET 5" -86 FLAT BOTTOM BASKET 6" DATE OF LAST CHANGE: NOTES **JOSAM COMPANY** IMENSIONS ARE SUBJECT TO MANUFACTURERS. TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA USE OF SUPERSEDED OR VOID DATA.

WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.






JOSAM 61300 SERIES STAINLESS STEEL SOLIDS INTERCEPTOR, MAY BE ON-FLOOR, PARTIALLY RECESSED, OR BELOW GRADE IN VAULTED ENCLOSURE, WITH NO-HUB CONNECTIONS, GASKETED COVER AND REMOVABLE SOLIDS COLLECTION BASKET

SOLIDS INTERCEPTOR


S.S. 3" AND 4" PIPE DIA.


61300 **SERIES**




MICHIGAN CITY, INDIANA


SPECIFICATION: SOLIDS INTERCEPTOR DRAWER TYPE JOSAM SERIES 61402 STAINLESS STEEL (TYPE 304) SOLIDS INTERCEPTOR - DRAWER TYPE, ADJUSTABLE HEIGHT, WITH LATCHED AND GASKETED SOLIDS BASKET, AND 2" NO-HUB INLET AND OUTLET CONNECTIONS ON BOTH SIDES. 61402 **SERIES** FLOW RATE: 35 GPM ere St DRAWER TYPE SOLIDS BASKET WITH Ø5/32 [4] PERF. SIDES AND BOTTOM 2" INLET BOTH SIDES 15 1/2" [395] 1 1/2" [38] 7 1/2" [191] 1/2" [38] 1" MIN. 4" MAX. 2" OUTLET BOTH SIDES-OPTIONS: THREADED CONNECTIONS -T -316 TYPE 316L MATERIAL NOTES DATE OF LAST CHANGE: **JOSAM COMPANY** DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA. MICHIGAN CITY, INDIANA







67800 Series swing-check Backwater Valve shown installed in a manhole terminal.



TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.


SPECIFICATION:

JOSAM 67100A SERIES COATED CAST IRON BACKWATER VALVE, PLASTIC BALL-FLOAT, ELASTOMER SEAT, BRONZE CAGE AND BOTTOM OUTLET SPIGOT CONNECTION.


BACKWATER VALVE BALL-FLOAT ADAPTER

SERIES

67100A



MICHIGAN CITY, INDIANA



DATE OF LAST CHANGE: 4/7/14

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPPERSEDED OR VOID DATA.

JOSAM COMPANY
MICHIGAN CITY, INDIANA


JOSAM 67360-DH SERIES COATED CAST IRON COMBINATION BACKWATER VALVE, STRAIGHT-THROUGH TYPE, BRONZE SWING-CHECK ASSEMBLY, BRONZE MANUALLY OPERATED SHEAR-GATE WITH NON-RISING STEM AND HUB CONNECTIONS.

BACKWATER VALVE


SHEAR-GATE & SWING-CHECK

SERIES

67360-DH







STRAIGHT-THROUGH TYPE FOR EXISTING INSTALLATIONS.

NOTE: SWING-CHECK VALVE NORMALLY HANGS IN CLOSED POSITION BUT CAN BE SET TO HANG OPEN BY SPECIFYING (-15) OPEN FLAP OPTION.

PIPE SIZE	В	С	D
3"	8	12	16
4"	8	12	16
5"	10-1/2	14-1/2	16
6"	10-1/2	14-1/2	16

Х	-DH	DOUBLE HUB
	-15	OPEN FLAP
	-28	12" CAST IRON EXTENS

-28 12" CAST IRON EXTENSION AND STEM -29 24" CAST IRON EXTENSION AND STEM

DATE OF LAST CHANGE: 04/18/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA


NOTES

SPECIFICATION:

JOSAM 67400 SERIES COATED CAST IRON BACKWATER VALVE, OFFSET TYPE, BRONZE FIXED SWING-CHECK ASSEMBLY, BOLTED GASKETED COVER AND NO-HUB CONNECTIONS.

BACKWATER VALVE NO-HUB SWING-CHECK

SERIES 67400




	PIPE SIZE	D	C	D		г
	2"	3-5/8	5-1/4	4	8	1/2
	3"	4	6	5	10	1/2
П	4"	4-3/4	7	6	12	1/2
	6"	5-3/4	9	6	12	5/8


DATE OF LAST CHANGE: 04/18/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS

JIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

MICHIGAN CITY, INDIANA

JOSAM COMPANY





PIPE SIZE	В	С	D	F	
2" 3-5/8 [92]		5-1/4 [133]	4 [102]	1/2 [13]	
3"	4 [102]	6 [152]	5 [127]	1/2 [13]	
4"	4-3/4 [121]	7 [178]	6 [152]	1/2 [13]	

DATE OF LAST CHANGE:	11/07/14
DIMENSIONS ARE SUBJECT TO MA TOLERANCES AND CHANGE WIT WE CAN ASSUME NO RESPON:	HOUT NOTICE. SIBILITY FOR
USE OF SUPERSEDED OR V	OID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

SPECIFICATION: **BACKWATER VALVES** JOSAM SERIES 67500 COATED CAST IRON BACKWATER VALVE, HUB & SPIGOT SWING-CHECK OFFSET TYPE, BRONZE SWING-CHECK ASSEMBLY, BOLTED GASKETED COVER AND HUB & SPIGOT CONNECTIONS. 67500 REF. XH PIPE DIMENSIONS **SERIES** VALVE NORMALLY HANGS IN CLOSED -10 OPTION POSITION, CAN BE SET TO HANG OPEN (-15) OPEN FLAP POSITION N NPT -ACCESS FERRUI E BRONZE PLUG AND PLUG BY JOSAM HUB END RISER PIPE SUPPLIED BY OTHERS THREADED BRONZE COVER (-10) C (FERRULE O.D.) BOLTED COVER. OFFSET TYPE 1/2 2" THREADED BRONZE PLUG, EITHER OR BOTH-SIDES (-30) PIPE SIZE PIPE SIZE SWING CHECK VALVE DIA. "B" DIA. "C" DIM. "D" DIM. "E" DIM. "F" DIM. "H" DIM. "K" DIM. "M" "N" NP1 PIPE SIZE DIM. "J" 2" 6-7/8 N/A 6-1/4 5 1-1/2 6-1/2 12 5-1/4 N/A 3" 7-7/8 5-7/8 7-1/2 10 5-3/4 1-1/4 9 15-3/4 6-3/4 4 4" Q 6-7/8 8-1/8 10-3/4 6-3/8 1-1/2 17-1/8 7-1/4 5 6" 11-1/4 9 10 11-3/4 7-3/4 1-3/4 10-3/4 19-1/2 8-3/4 7 8" 7-3/4 2-1/4 9 13-3/4 11-1/8 11-3/4 12-1/2 11 20-1/4 10 * FOR EXTENSION, USE "-10" OPTION WITH HUB & SPIGOT PIPE BY OTHERS -10* THREADED BRONZE COVER (3" - 8" SIZES ONLY -30 2" AUXILIARY INLET WITH BRONZE PLUG -15 FLAP IN PARTIALLY OPEN POSITION DATE NOTES

DATE OF LAST CHAN	GE:	05/04/15	100414	_		~~-	_	
DIMENSIONS ARE SUBJECT TOLERANCES AND CHAN			JOSAM	C	J	OMI	A	NY
WE CAN ASSUME NO RE	SPON	SIBILITY FOR	MICHIGAN	CI.	T	Y, INDI	ANA	

USE OF SUPERSEDED OR VOID DATA.

JOSAM 67600 SERIES COATED CAST IRON BACKWATER VALVE, OFFSET TYPE, BRONZE FIXED SWING-CHECK ASSEMBLY, BOLTED GASKETED COVER AND HUB & SPIGOT CONNECTIONS.

BACKWATER VALVE


HUB & SPIGOT SWING-CHECK

SERIES

67600

OFFSET

NOTE: SWING-CHECK VALVE NORMALLY HANGS IN CLOSED POSITION BUT CAN BE SET TO HANG OPEN BY SPECIFYING (-15) OPEN FLAP OPTION.



SWING-CHECK

VALVE

-FLOW

BOLTED COVER.

* HUB & SPIGOT DIMENSIONS ARE IN ACCORDANCE WITH E.H.C.I. SOIL PIPE STANDARD.

-15	OPEN FLAP

PIPE SIZE OFFSET		C D		E.	F	G
10"	2	8-1/2	10-1/2	23	10-1/2	13
12"	2	9-1/4	11-1/4	25-3/4	12	15

DATE OF LAST CHANGE: 04/18/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR YOUID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

ØPIPE_ SIZE *

NOTES

SPECIFICATION:


JOSAM 67650 SERIES COATED CAST IRON BACKWATER VALVE, PIT TYPE, BRONZE SWING-CHECK ASSEMBLY, VERTICAL INLET GRATE AND SPIGOT OUTLET CONNECTION.

BACKWATER VALVE

COMBINED DRAIN/SWING-CHECK

SERIES

67650




	PIPE SIZE	BXB'	CXC'	D	E	GRATE FREE AREA	
	3"	9-5/16 X 7-5/8	12-3/4 X 10-7/8	5-1/8	13	19	
	4"	9-5/16 X 7-5/8	12-3/4 X 10-7/8	5-1/8	13	19	
	6"	11 X 8-7/8	14-3/4 X 12-3/8	5-1/2	14	22	

	-1	SATIN FINISH NIKALOY FACE
П	-2	SATIN FINISH BRONZE FACE
П	-5	GALVANIZED CAST IRON PARTS


-25	FLASHING CLAMP DEVICE
-VP	SECURED FACE, VANDAL-PROOF SCREWS
-LBV	LESS BACKWATER VALVE


DATE OF LAST CHANGE: 04/18/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.


JOSAM COMPANY MICHIGAN CITY, INDIANA




						,
		TYPE	PIPE SI	ZE	"A" DIM	
		67723	3"		5	
-15 OPEN FLAP		67724	4"		6-1/4	1
DATE OF LAST CHANGE: 04/18/15	IOCARI C		NIV	NOTE	S	
DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE	JOSAM C		IN I			
WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.	MICHIGAN CIT	Y, INDIANA	4			








Hydrants 265





266 Hydrants

JOSAM SERIES 71300 CHROME-PLATED HYDRANT/SILL-COCK, STAINLESS STEEL BOX, HINGED LATCHING COVER, 3/4" HPT OUTLET, INTEGRAL VACUUM BREAKER - BACKFLOW PREVENTER, AND 1/2" OR 3/4" INLET CONNECTION.

HYDRANT

1/4 TURN, NON-FREEZE WITH BOX


SERIES


71300

HYDRANT APPROVED TO NSF/ANSI 61 FOR USE IN POTABLE WATER SYSTEMS.

RECOMMENDED MIN. WALL OPENING: 5-1/2" X 7-3/4"







MODEL	Α
71300-6-QTR	6-1/4 [159]
71300-7-QTR	7-1/4 [184]
71300-9-QTR	9-1/4 [235]
71300-11-QTR	11-1/4 [286]
71300-13-QTR	13-1/4 [337]
71300-15-QTR	15-1/4 [387]

17-1/4 [438]

	10	

	-52	CAST SATIN FINISH BR FACE
-54		CAST SATIN FINISH NIKALOY FACE
	-72	WALL CLAMP
	-81*	HOSE BIBB VACUUM BREAKER
	-91*	1" HOSE PIPE THREADED OUTLET
	-95	CYLINDER SECURED LOCK

ASSE 1019 ASME A112.18.1

DATE OF LAST CHANGE: 04/29/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

71300-17-QTR

JOSAM COMPANY MICHIGAN CITY, INDIANA

, NOTES

SPECIFICATION:


JOSAM SERIES 71350 CHROME-PLATED HYDRANT/SILL-COCK, 3/4" HPT OUTLET, INTEGRAL VACUUM BREAKER - BACKFLOW PREVENTER, AND 1/2" OR 3/4" INLET CONNECTION.


HYDRANT


1/4 TURN, NON-FREEZE

SERIES

71350







STANDARDS: NSF/ANSI 61 NSF/ANSI 372 ASSE 1019 ASME A112.18.1

INCOLL		
71350-MC-QTR	3 [76]	
71350-4-QTR	4 [102]	
71350-6-QTR	6 [152]	
71350-8-QTR	8 [203]	
71350-10-QTR	10 [254]	
71350-12-QTR	12 [305]	
71350-14-QTR	14 [356]	

MODEL

OP	HONS:
_	

		WALL CLAMP
П	-81	HOSE BIBB VACUUM BREAKER
Т	-91	1" HOSE PIPE THREADED OUTLET

DATE OF LAST CHANGE: 04/29/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.


JOSAM COMPANY MICHIGAN CITY, INDIANA

^{* -81} AND -91 CANNOT BE ORDERED TOGETHER

JOSAM SERIES 71350 REPLACEMENT PARTS GUIDE.

HYDRANT REPLACEMENT PARTS






NO.	PART NO.	DESCRIPTION		
1	71350P01U	KEY (1/4")		
2	71350P02U	BONNET ASSY (INCL. 3 O-RINGS)		
3	SEE TABLE	STEM TUBE ASSY (INCL. WASHER, SEAL, SCREW)		
4	4 71350P04U VALVE ASSY (INCL. 2 O-RINGS)			
5	71350P05U	VACUUM BREAKER ASSY		
6	71350P06U	VACUUM BREAKER CAP		

POS. NO. 3 - STEM TUBE ASSY - PART NOS.

71350 MODEL	71300 MODEL	A DIM. [mm]	PART NO.
71350-MC-QTR	71300-6-QTR	3-5/8" [92]	09600B
71350-4-QTR	71300-7-QTR	4-5/8" [117]	09600C
71350-6-QTR	71300-9-QTR	6-5/8" [168]	09600D
71350-8-QTR	71300-11-QTR	8-5/8" [219]	09600E
71350-10-QTR	71300-13-QTR	10-5/8" [270]	09600F
71350-12-QTR	71300-15-QTR	12-5/8" [321]	09600G
71350-14-QTR	71300-17-QTR	14-5/8" [371]	09600H



10/31/14 DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

268 **Hydrants**

JOSAM SERIES 71400 FREEZELESS GROUND HYDRANT WITH CAST IRON HEAD, $3/4^{\prime\prime}$ FPT BRASS INLET AND BRASS HOSE ADAPTOR OUTLET. CAM-TYPE OPERATING CONTROL LEVER FOR FULL OR VARIABLE FLOW. STAINLESS STEEL OPERATING ROD AND ONE PIECE PLUNGER AND GALVANIZED STEEL PIPE.


HYDRANTS


FREEZELESS GROUND HYDRANT

33









-91	1" HOSE PIPE THREADED OUTLET

TYPE	BURY SIZE	OVERALL LENGTH		
71400-1	1' BURY	45"		
71400-2	2' BURY	57"		
71400-3	3' BURY	69"		
71400-4	4' BURY	81"		
71400-5	5' BURY	93"		
71400-6	6' BURY	105"		

DATE OF LAST CHANGE: IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

SPECIFICATION:

JOSAM SERIES 71450 FREEZELESS GROUND HYDRANT WITH HEAVY-DUTYCAST IRON HEAD, 3/4" OR 1" FPT BRASS INLET AND BRASS HOSE ADAPTOR OUTLET. CAM TYPE OPERATING CONTROL LEVER FOR FULL OR VARIABLE FLOW. STAINLESS STEEL OPERATING ROD, ONE PIECE PLUNGER AND GALVANIZED STEEL PIPE.

HYDRANTS

FREEZELESS GROUND HYDRANT

33"

BURY

DEPTH

OVERALL

LENGTH

45"

57"


69"

81"

93"

105"

71450 SERIES



	TYPE	SIZE	BURY SIZE	OVERALL LENGTH		
	71450-1	3/4"	1' BURY	45"		
	71450-2	3/4"	2' BURY	57"]	Г
	71450-3	3/4"	3' BURY	69"]	
	71450-4	3/4"	4' BURY	81"		
	71450-5	3/4"	5' BURY	93"		
	71450-6	3/4"	6' BURY	105"	1	

DATE OF LAST CHANGE:

IMENSIONS ARE SUBJECT TO MANUFACTURERS.

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.

SAM COMPANY					Ν	IOTES
05"			71451-6	1"		6' BURY
93"			71451-5	1"		5' BURY
31"			71451-4	1"		4' BURY

MICHIGAN CITY, INDIANA

TYPE

71451-1

71451-2

71451-3

BURY

SIZE

1' BURY

2' BURY

3' BURY

INLET

SIZE

1"

1"


JOSAM 71600 SERIES CAST BRONZE NON-FREEZE YARD HYDRANT WITH SATIN NIKALDY HINGED LATCHING COVER, INTEGRAL 3/4" OR 1" HPT OUTLET, BRONZE CASING, NEOPRENE PLUNGER, BRONZE OPERATING PARTS AND 3/4" FEMALE & 1" MALE NPT INLET CONNECTION

HYDRANTS

YARD TYPE, NON-FREEZE WITH BOX

SERIES

71600



	NIKALOY DEEP BOX (*2-5/8" DEEP)
	VACUUM BREAKER (UPC, ASSE 1011)
-91	1" HOSE PIPE THREADED OUTLET
-95	CYLINDER VANDAL-PROOF LOCK
-97	1/8" TAPPED DRAIN HOLE IN BOX

VAC BREAKER (-81) REQUIRES DEEP BOX (-80) FOR COVER TO CLOSE

DATE OF LAST CHANGE: 1/16/15

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR YOUD DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA NOTES

5'

6'

71600-5

71600-6

SPECIFICATION:

JOSAM 71650 SERIES TRI-TEMP CAST BRONZE NON-FREEZE WALL
HYDRANT WITH SATIN NIKALOY HINGED LATCHING COVER, BRONZE
CASINGS NEEDHELE PLANCERS, REMOVALE NYLONG LESTING.
CONNECTIONS FOR HOT AND COLD WATER AND MIKING CHAMBER
CONNECTIONS FOR HOT AND COLD WATER AND MIKING CHAMBER


WITH 3/4" HPT OUTLET.

TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

HYDRANTS

TRI-TEMP, NON-FREEZE W/BOX

SERIES **71650**



MICHIGAN CITY, INDIANA

HYDRASAN I® HYDRANT MAINTENANCE

HYDRASAN® I will seldom require service. However, continuous drainage from the outlet is a signal that inspection and possible replacement of certain parts are in order. A self-contained tool, Actuator Rod (3), when reversed, makes the job easy. The procedure for removal and replacement of hydrant sealing parts is as follows:

- **A.** Shut off water in supply line to hydrant, and turn hydrant on to relieve pressure.
- **B.** Use pliers. Firmly grip Cap Retainer (8) and turn counterclockwise to remove it, then remove Deflector Cap (7). Shut off hydrant as tight as possible with Control Key (1) and use an adjustable open end wrench or channel-lock type plyers to "break" Draw Nut (11) loose, the remove it with Control Key (1), turning counterclockwise until threads are free from Hydrant Head (12). Grasp Draw Nut (11) firmly and pull toward you to remove Actuator (2) and Actuator Rod (3).
- **C.** Loosen Set Screw (13) with a ³/₃₂" hex. key and separate Actuator (2) from Actuator Plug (21) on end of Actuator Rod (3).
- **D.** Reverse Actuator Rod (3) and insert into hydrant as far as possible, using Control Key (1) secured to Actuator Rod (3) with Set Screw (14). With Actuator Plug (21) (hex.) on end of Actuator Rod (3) inserted in Hex. Hole (22) in Seat (15), which places Rod Extension (20) in Hole (23) in Shuttle (4), firmly rotate Control key (1) counterclockwise to unscrew Seat (15) and pull out entire Valve (15, 5 and 4).
- **E.** Replace worn parts with new parts as required. Reassemble hydrant, reversing the procedure in Steps A through D to place it back in service. Be sure to make Cap Retainer (8) tight to prevent tampering.

NOTE: If pressure reliev Valve "O" Ring (6) appears worn, it should be replaced when hydrant is apart. This part can be checked and, if necessary, replaced without turning off water supply to hydrant because the Pressure Assist Seal (Parts 4, 5, and 15) prevents any water from entering. This feature makes possible removal of all parts downstream (in front) of the Seal (or Valve) with water supply on.

Should it ever be necessary to service the Vacuum Breaker-Backflow Preventer in the outlet of HYDRASAN I, the procedure for removal and replacement of operating parts is as follows:


- **F.** After Deflector Cover (7) has been removed (see Maintenance Step B), remove the four housing retaining screws with a $\frac{5}{32}$ " hex. key and take off Outlet Housing (27). Lift out Vent Ring (28) and operating parts, Seal (29) Primary and Secondary Pistons (30 and 31). Inspect for wear.
- **G.** Replace worn parts with new parts as required. Reassemble Vacuum Breaker-Backflow Preventer, reversing the procedure in Step F to place it back in service.

Service kits containing all parts necessary for this maintenance can be obtained through your plumbing supply dealer.

Hydrants 271

Parts Drawings, HYDRASAN® Non-Freeze


Hydrant replacement parts are available in Repair Kits only. Kits #6, #7, #8 and #23 apply to the Non-Freeze HYDRASAN® Hydrants depicted below. See page 270 for parts included in kits. For replacement rod assemblies, contact your local representative.



HYDRASAN®I 71000 & 71050 Series NON-FREEZE

Parts Drawings, HYDRASAN® Mild Climate

Hydrant replacement parts are available in Repair Kits only. Kits #6, #9, #10 and #23 apply to the Mild-Climate HYDRASAN® Hydrants depicted below. See page 270 for parts included in kits. For replacement rod assemblies, contact your local representative.



Repair Kits • We recommend that a complete HYDRANT REPAIR KIT be installed when it becomes necessary to repair a hydrant.

PART NO.	ITEM	QTY.	PART NO.	ITEM	QTY.	PART NO.	ITEM	QTY.
71550P0)2U KIT #2		71950P12U	KIT #12		71550P21U	KIT #21	
#1	5/16" Key	12		For 1420N - 71950		F	or 1400N – 1410N Old Style	
71050P0	06U KIT #6		#1	5/16" Key	1	1	550 – 71650 – Previous Desi	gn
#4	Shuttle	2	#2	Worm Stem	1	#1	5/16" Key	1
#5/15	Seal/Seat	2	#3	Brass Washer	1	#2	Worm Stem	1
71050P0	07U KIT #7		#5	Packing	1	#3	Brass Washer	1
#1	1/4" Key with set screw	12	#12	Nylon Seat	1	#4	Packing Nut	1
	Allen Wrench	12	#15	Plunger	1	#5	Packing	1
71050P0	08U KIT #8		71600P14U	KIT #14		#12	Nylon Seat	1
	or HYDRASAN® I or II Non-Freez	ze		r 1430N Old Style 3/4" or 1"		#15	Plunger	1
#1	1/4" Key with set screw	1		1440N or 71700 3/4"		71550P22U	KIT #22	
#2	Actuator	1		71600 3/4" O.S.		'	For 71500 – 71550 – 71650	
#4	Shuttle	1	#1	5/16" Key	1		New Style	
#5	Pressure Assist Rubber Seal	1	#2	Worm Stem	1	#1	5/16" Key	1
#6	Pressure Relief Valve (O-Ring)	1	#3	Brass Washer	1	#2	Worm Stem	1
#15	Seat	1	#5	Packing	1	#3	Brass Washer	1
	Allen Wrench	1	#15	Plunger	1	#6	Worm Assy. Nut	1
71070P0	09U KIT #9		71600P15U	KIT #15		#12	Nylon Seat	1
#4	Shuttle	2		For 71600 3/4" or 1"		#15 #37	Plunger Retainer Seal	1
#5/15	Seal/Seat	2		New Style		#37	Worm Stem Seal	1
71070P1	10U KIT #10		#1	5/16" Key	1		KIT #23	'
For HYDRASAN® I or II – Mild Climate			#2	Worm Stem	1	71050P23U	For HYDRASAN® I	
#1	1/4" Key with set screw	1	#3	Brass Washer	1	#28		2
#2	Actuator	1	#15	Plunger	1	#28	Vent Ring Boot for Vacuum Breaker	2 2
#4	Shuttle	1	#37	Nylon Seal	1	#30	Primary Piston	2
#5	Pressure Assist Rubber Seal	1	#38	Worm Stem Seal	1	#31	Secondary Piston	2
#6	Pressure Relief Valve (O-Ring)	1				#32	Snap Ring	2
#15	Seat	1				π 3 2	map ming	2
	Allen Wrench	1						

Selection for Long Piping Runs

The majority of sizing and selection applications will involve single and multiple fixture branch lines. These are easily handled with Table IV. The remainder of applications involves individual runs of piping to a remote item of equipment. The properly sized water hammer arresters for such applications can be determined by Table V and Table V-A.

TABLE V FOR WATER PRESSURES UP TO 65 P.S.I.G.

P.D.I. Water Hammer Arrester Sizes						
Length of			Nom	inal Pipe	Diameter	
Pipe	1/2"	3/4"	1″	1-1/4"	1-1/2"	2"
25	Α	Α	В	С	D	Е
50	Α	В	С	D	Е	F
75	В	С	D	AE	F	EF
100	С	D	Е	F	CF	FF
125	С	D	F	AF	EF	EFF
150	D	E	F	DF	FF	FFF

Ideally the flow pressure in branch lines serving fixtures should never exceed 60 P.S.I.G. Pressure reducing valves should be installed to maintain proper pressure. However, when flow pressures of 65 to 85 P.S.I.G. are used, the next larger size water hammer arrester should be selected. Refer to Table V-A.

All sizing data in this section are based on flow velocities of 10 F.P.S. or less. The certification testing was conducted with a velocity of 10 F.P.S. to offer assurance that P.D.I. approved units were capable of handling shocks of maximum intensity that may be encountered.

TABLE V-A
FOR WATER PRESSURES OVER 65 P.S.I.G. AND UP TO 85 P.S.I.G.

Р	.D.I. W	ater Ha	mmer <i>i</i>	Arreste	r Sizes				
Length of		Nominal Pipe Diameter							
Pipe	1/2"	3/4"	1"	1-1/4"	1-1/2"	2"			
25	В	В	С	D	Е	F			
50	В	С	D	E	F	CF			
75	С	D	E	F	CF	FF			
100	D	Е	F	CF	EF	EFF			
125	D	Е	CF	DF	FF	BFFF			
150	E	F	CF	FF	DFF	FFFF			


When long runs of piping are employed to serve a remote item of equipment, the water hammer arrester should be located as close as possible to the point of quick closure. At this location, the water hammer arrester will control the developed energy and prevent the shock wave from surging through the piping system.

NOTE: For best performance results, the ABSORBOTRON® II should always be installed in an upright position and located as close as possible to the fixture or equipment closure valve.

JOSAM 75000 SERIES ABSORBOTRON II[®]SHOCK ABSORBER WITH STAINLESS STEEL SHELL. HYDRO-PNEUMATIC CUSHION OF NITROGEN, STAINLESS STEEL BELLOWS AND STAINLESS STEEL MALE THREADED PIPE NIPPLE.

SHOCK ABSORBER STAINLESS STEEL

SERIES **75000**



		PDI SIZE	FIXTURE UNITS	PIPE SIZE	н
		AA	1 -11	1/2	3-1/8 [80]
		Α	1 - 11	3/4	3-1/8 [80]
		В	12 - 32	1	4 [102]
		С	33 - 60	1	4-5/8 [117]
		D	61 - 113	1	5-1/2 [140]
l		E	114 - 154	1	7-1/16 [180]
		F	155 - 330	1	7-1/16 [180]

COMPLIES WITH LEAD-FREE REQUIREMENTS LESS THAN 0.25% LEAD CONTENT OVER THE WETTED SURFACE AREA OF THE PRODUCT.

DATE OF L	AST CHA	NGE:	05/04/15
DIMENSIONS	ARE SUBJE	CT TO MAN	UFACTURE
TOLERANCE			
	SSUME NO		
USE OF	SUPERSE	DED OR VO	ID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA


NOTES

SPECIFICATION:

JOSAM 75000-S SERIES ABSORBOTRON II SHOCK ABSORBER WITH WROUGHT COPPER SHELL, HYDRO-PNEUMATIC AIR CUSHION, WROUGHT COPPER ADAPTER AND MALE THREADED CONNECTIONS.

SHOCK ABSORBER

SERIES **75000-S**




L	S	IZE	FIXTURE UNITS	THRD SIZE	В	С	MODEL
		Α	1-11	1/2"	8-1/4	1-3/8	75001-S
		В	12-32	3/4"	8-3/4	1-3/8	75002-S
		С	33-60	1"	11	1-3/8	75003-S
Г		D	61-113	1"	10-1/8	2-1/8	75004-S
		E	114-154	1"	12-5/8	2-1/8	75005-S
		F	155-330	1"	15-1/8	2-1/8	75006-S

DATE OF LAST CHANGE: 04/30/15


DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA



(-11) OPTION, HEAVY-DUTY CONVEX GRATE

allows drainage through openings in top of grate even in the event of perimeter blockages by leaves or debris.




Trench Drains 277

JOSAM 76000 SERIES COATED CAST IRON RECTANGULAR SECTIONAL TRENCH DRAIN WITH HEAVY-DUTY BODY SECTIONS AND INTEGRAL ANCHOR FLANGE, HEAVY-DUTY LOOSE-SET SUPER-FLO GRATES WITH PERIMETER DRAINAGE SLOTS, SECONDARY LOOSE-SET DOME STRAINER AND BOTTOM INSIDE CAULK OUTLET CONNECTION.

TRENCH DRAIN

SUPER-FLO 6" WIDE, RECTANGULAR

76000 SERIES



-EXT	EXTENSION SECTION		П	PIPE
-1	SATIN FINISH NIKALOY TOP			SIZE
-2	SATIN FINISH BRONZE TOP		Т	2"
-7	DUCTILE IRON GRATE		₩	3"
-30	FLASHING CLAMP DEVICE		#	3"
-40	GALVANIZED CAST IRON PARTS			4"
-VP	SECURED GRATE-VANDAL-PROOF SCREWS	_		

USED WITH ONE (1) OUTLET SECTION

□ ADD 1/4" FOR NIKALOY OR BRONZE TOP ALSO ADD 1/4" TO OVERALL LENGTH

FOR INSTALLATIONS EXPOSED TO VEHICULAR TRAFFIC, SPECIFY -VP SECURED GRATE OPTION

DATE OF LAST CHANGE: IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA


NOTES


SPECIFICATION:

JOSAM 76010 SERIES COATED CAST IRON RECTANGULAR SECTIONAL TRENCH DRAIN WITH HEAVY-DUTY BODY SECTIONS AND INTEGRAL ANCHOR FLANGE, HEAVY-DUTY LOOSE-SET GRATES AND BOTTOM OUTLET INSIDE-CAULK CONNECTION.

TRENCH DRAIN 12" WIDE, RECTANGULAR

76010 **SERIES**






OUTLET

SECTION

EXTENSION

SECTION





9/32 WEEPHOLES STANDARD ON ALL SECTIONS IT IS RECOMMENDED THAT NO MORE THAN EIGHT (8) EXTENSION SECTIONS BE USED WITH

*ADD 1/4" FOR NIKALOY OR BRONZE TOP. △ADD 3/8" TO WIDTH & OVERALL LENGTH FOR NIKALOY OR BRONZE TOP.

	PIPE SIZE
П	3"
	4"
	6"

l		-EXI	EXTENSION SECTION
ĺ		-1	SATIN FINISH NIKALOY TOP
I	П	-2	SATIN FINISH BRONZE TOP
ĺ	П	-7	DUCTILE IRON GRATE
ſ		-11	CONVEX GRATE

EXTENSION

SECTION

ı		SECURED GRATE, VANDAL-PROOF SCREW
ı	-30	FLASHING CLAMP DEVICE
ı		GALVANIZED CAST IRON PARTS
ı	-70	SEDIMENT BUCKET, CAST IRON
ı	-40-70	BUCKET, GALVANIZED
ı	-ARE	ACID RESISTANT EPOXY COATING


DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

SPECIFICATION: TRENCH DRAIN JOSAM 76300 SERIES COATED CAST IRON 12" x 20" RECTANGULAR LIGHT-DUTY SECTIONAL TRENCH GRATE. LIGHT-DUTY RECTANGULAR 76300 SERIES SLOT WIDTH 5" x 1/2" (-1 & -8-2 SLOT WIDTH 3-1/4" x 5/16") FLAT BAR ANCHOR AND NAILING CLIP 5 1/2" DESIGN REPEATED 18 7/8" 'C' = (# OF GRATES x 20") + 3/8" INSIDE CHANNEL WIDTH = 'C' - 1 1/2" GRATE FREE AREA (EACH) 110 SQ IN. GRATE ONLY DIMS = 20" x 12" x 5/8" FRAME MADE OF 3/4" x 3/4" x 1/8" ANGLE 763__ (INDICATE ## OF GRATES) -1 SATIN FINISH NIKALOY GRATE, STAINLESS STEEL FRAME SATIM THINIST MINISTORY POUCTILE IRON GRATE SECURED WITH SATIN FINISH TOP SECURED GRATE, VANDAL-PROOF SCREWS -40 GALVANIZED DATE OF LAST CHANGE: NOTES **JOSAM COMPANY** IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR MICHIGAN CITY, INDIANA

SPECIFICATION: TRENCH DRAIN JOSAM 76400 SERIES COATED CAST IRON 20" x 12" RECTANGULAR LIGHT-DUTY RECTANGULAR LIGHT-DUTY SECTIONAL TRENCH GRATE 76400 SERIES SLOT WIDTH 5" x 1/2" (-1 & -8-2 SLOT WIDTH 3-1/4" x 5/16") FLAT BAR ANCHOR SECTION A-A SECTION B-B DESIGN 203/A REPEATED 'C' = (# OF GRATES x 12") + 3/8" 764 INSIDE CHANNEL WIDTH = 'C' - 1 1/2" GRATE FREE AREA (EACH) 110 SQ IN. (INDICATE ## OF GRATES) GRATE ONLY DIM'S = 12" x 20" x 5/8" FRAME MADE OF 3/4" x 3/4" x 1/8" ANGLE -1 SATIN FINISH NIKALOY GRATE, STAINLESS STEEL FRAME -7 DUCTILE IRON GRATE -8-2 ALL BRONZE WITH SATIN FINISH TOP -VP SECURED GRATE, VANDAL-PROOF SCREWS -40 GALVANIZED DRAWING No. 07/01/08 NOTES: JOSAM COMPANY A-15574-K MICHIGAN CITY, INDIANA

USE OF SUPERSEDED OR VOID DATA




TRENCH DRAIN JOSAM 76600 SERIES COATED CAST IRON 24" x 12" RECTANGULAR MEDIUM-DUTY RECTANGULAR MEDIUM-DUTY SECTIONAL TRENCH GRATE. 76600 SERIES SLOT WIDTH 4-3/8" x 1/2" (-1 & -8-2 SLOT WIDTH 4-3/8" x 1/2") FLAT BAR ANCHOR авинивавайнива SECTION A-A SECTION B-B DESIGN -----'C' = (# OF GRATES x 12") + 5/8" □ 766 INSIDE CHANNEL WIDTH = 'C' - 3" GRATE FREE AREA (EACH) 90 SQ IN. GRATE ONLY DIM'S = 24" x 12" x 5/8" (INDICATE ## OF GRATES) FRAME MADE OF 1-1/2" x 1-1/2" x 1/4" ANGLE -1 SATIN FINISH NIKALOY GRATE, STAINLESS STEEL FRAME DUCTILE IRON GRATE -8-2 ALL BRONZE WITH SATIN FINISH TOP -VP SECURED GRATE, VANDAL-PROOF SCREWS -40 GALVANIZED DRAWING No. 07/01/08 NOTES: JOSAM COMPANY A-15575-K MICHIGAN CITY, INDIANA

SPECIFICATION:


SPECIFICATION: TRENCH DRAIN JOSAM 76700 SERIES COATED CAST IRON 12" x 24" RECTANGULAR HEAVY-DUTY SECTIONAL TRENCH GRATE. HEAVY-DUTY RECTANGULAR 76700 SERIES SLOT WIDTH 4-1/4" x 1-1/2" (-1 & -8-2 SLOT WIDTH 4-1/4" x 1-1/2") -FLAT BAR ANCHOR AND NAILING CLIP 12 5/8" ─ 12 5/8" 9 5/8" ∠TYPE 76701 GRATE AND FRAME SHOWN 24" DESIGN REPEATED - 5 1/2' 'C' = (# OF GRATES x 24") + 5/8" INSIDE CHANNEL WIDTH = 'C' - 3" GRATE FREE AREA (EACH) 100 SQ. IN. GRATE ONLY DIMENSIONS = 24" x 12" x 1-1/4" FRAME MADE OF 1-1/2" x 1-1/2" x 1/4" ANGLE 767 (INDICATE ## OF GRATES) -1 SATIN FINISH NIKALOY GRATE, STAINLESS STEEL FRAME -7 DUCTILE IRON GRATE -8-2 ALL BRONZE WITH SATIN FINISH FINISH TOP -VP SECURED GRATE, VANDAL-PROOF SCREWS -40 GALVANIZED DATE OF LAST CHANGE: NOTES **JOSAM COMPANY**


MICHIGAN CITY, INDIANA





IMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA










TRAP SEAL PRIMER VALVE

INSTRUCTIONS

APPLICATION - INSTALLATION - OPERATION - MAINTENANCE



ITEM NO.	DESCRIPTION
1	Valve Seat
2	Poppet Assembly
3	0-Ring
4	Сар
5	0-Ring

APPLICATION

This valve, when properly installed in a cold water supply line and connected to a floor drain trap, will ensure a constant seal of fresh water in the drain trap. Frequently, without such a device, the water seal will evaporate from the trap and allow sewer gas and vermin to enter buildings from the sewer lines.

OPERATING PRINCIPLE

As water is drawn through the supply line by an appliance or water closet, the resulting flow tips the valve mechanism to one side which meters water from the supply line into the primer trap line. Water flow can be observed at the bottom outlet side slots. These side slots act as a vacuum breaker.


INSTALLATION REQUIREMENTS


- 1. Water lines to which the primer valve will be connected must be clear of dirt.
- 2. Primer valve must be mounted vertically with sufficient clearance above valve to remove Cap. Connect primer valve to a horizontal cold water supply line near the drain trap.
- The pipe connecting the primer valve bottom outlet to the drain trap should be at least 1/2 in. inside diameter and must be vertically straight for at least one foot directly below the primer valve.
- 4. Elbows, tees and reducers must not be connected to the primer valve bottom outlet because they will cause water to flow out through the outlet side slots.
- 5. The Cap, Valve Seat, Poppet Assembly and O-Rings must be removed prior to any soldering that may be required.
- 6. Check all connections for leaks and repair as needed. No adjustments are required.

MAINTENANCE INSTRUCTIONS

- 1. Close supply line valve to shut off water pressure to the primer valve.
- 2. Remove Cap with a 1-1/4 in. hex wrench. Lift out Poppet Assembly.
- 3. Unscrew Valve Seat with a 5/8 in, thin wall socket wrench.
- 4. Insert new Valve Seat and O-Ring in Valve Body and tighten Valve Seat.
- 5. Place Poppet Assembly on Valve Seat. Small stem must extend into seat orifice.
- 6. Attach Cap and O-Ring to Valve Body and tighten Cap.

Open water supply line valve. Check for leaks around Cap. Observe flow of water into trap when water is flowing through supply line. No Adjustments are required.






JOSAM 88250 SERIES BRONZE PRIMER VALVE WITH INTEGRAL VACUUM BREAKER AND GASKETED ACCESS COVER FOR INSTALLATION IN A COLD WATER SERVICE LINE TO A SINGLE PLUMBING FIXTURE WITH TRAP CONNECTION FOR MAINTAINING TRAP SEAL.

TRAPS & ACCESSORIES


TRAP SEAL PRIMER VALVE

SERIES

88250







	-10	POLISHED CHROME PLATED
	-90	1/2" FEMALE COPPER CONNECTION
	-91	1/2" FEMALE UNION CONNECTION

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA


NOTES


TRAP PRIMER VALVE SPECIFICATION: JOSAM SERIES 88300 BRASS TRAP PRIMER VALVE WITH 1/2" NPT INLET, INTEGRAL BACKFLOW PREVENTER, VACUUM BREAKER PORT, AND PLASTIC DISTRIBUTION UNIT FOR TWO TO FOUR PLUMBING FIXTURES. 88300 **SERIES** ACTIVATES AT 10 PSIG DROP OPERATING PRESSURE: 20 - 80 PSIG UPC ASSE 1018 APPROVED -1 7/16-TYPICAL INSTALL 4 3/8 8 3/4 BRASS PRIMER VALVE: 88280 PLASTIC DIST. UNIT: 88290 2 3/4 DATE OF LAST CHANGE: NOTES **JOSAM COMPANY**

MICHIGAN CITY, INDIANA

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.






JOSAM 88550 SERIES COATED CAST IRON HUB ADAPTER WITH STANDARD CAST IRON SOIL PIPE HUB AND FEMALE THREADED OILTIET

TRAPS & ACCESSORIES


HUB ADAPTER, THREADED OUTLET

SERIES

88550







	TYPE NO.	PIPE SIZE	B*	С	D	E	LBS.
П	88553	3	4-1/4	5-1/4	3	2-1/4	5
	88554	4	5-3/8	6-1/4	2-7/8	2-3/8	5
П	88555	5	6-1/4	7-1/4	3-1/2	2-7/8	7
	88556	6	7-1/2	8-1/4	3-5/8	3	8

* MEETS ASTM A-74 XH CAST IRON SOIL PIPE STANDARD

-40 GALVANIZED CAST IRON PARTS

DATE OF LAST CHANGE: 11/05/14

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VIOLD DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:

JOSAM 88560 SERIES COATED CAST IRON HUB ADAPTER WITH STANDARD CAST IRON SOIL PIPE HUB AND MALE THREADED OUTLET.


TRAPS & ACCESSORIES

HUB ADAPTER, THREADED OUTLET

SERIES **88560**







*MEETS ASTM A-47 XH CAST IRON SOIL PIPE STANDARD


	PIPE SIZE	В*	С	D	E	F
	2"	3	3-7/8	4	2-1/4	1-1/2
	3"	4-1/4	5-1/8	4-1/4	2-3/8	1-1/2
	4"	5-1/4	6-1/8	4-3/8	2-3/8	1-5/8
П	5"	6-1/4	7-1/8	4-3/8	2-3/8	1-3/4
	6"	7-1/4	8	4-3/8	2-3/8	1-5/8
	8"	9-1/4	10-1/2	4-3/8	2-1/4	1-3/4


DATE OF LAST CHANGE: 4/24/15

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

-40 GALVANIZED CAST IRON PARTS

JOSAM COMPANY MICHIGAN CITY, INDIANA






JOSAM 88910 SERIES COATED CAST IRON AIR GAP WITH INTEGRALLY CAST AIR PORTS, FEMAILE THREADED INLET AND OUTLET.

TRAPS & ACCESORIES

AIR GAP

SERIES

88910




SPECIFICATION:

JOSAM 88950 SERIES NIKALOY FRESH AIR INLET WITH SATIN PERFORATED GRILLE, STEEL PIPE EXPANSION ANCHORING DEVICE AND VANDAL-PROOF SPANNER LOCKING DEVICE.

TRAPS & ACCESSORIES

FRESH AIR INLET

SERIES **88950**



DATE OF LAST CHANGE: 4/24/15

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

-40 GALVANIZED CAST IRON PARTS

JOSAM COMPANY MICHIGAN CITY, INDIANA


NOTE: INSTALL AIR GAP IN EXPOSED LOCATION WHERE MINOR SPLASHING WILL NOT BE A PROBLEM.

NOTES

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

DATE OF LAST CHANGE:

JOSAM COMPANY MICHIGAN CITY, INDIANA




JOSAM SERIES FD-100-A "LEVELEZE II" CAST IRON FLOOR DRAIN WITH 5" ROUND NIKALOY TOP, 2-STAGE HEIGHT ADJUSTMENT, AND BOTTOM OUTLET.

LITE LINE

FLOOR DRAIN LEVELEZE II, 5" TOP

SERIES

FD-100-A



OPTIONS:

	MODEL	PIPE SIZE
	FD-102-A	2"
	FD-103-A	3"
	FD-104-A	4"
	FD-105-A*	5"-Z

^{* 5&}quot; AVAIL. IN NO-HUB ONLY

DATE OF LAST CHANGE: 11/14/14

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

HUB OUTLET WITH GASKET

NO-HUB OUTLET

, NOTES

SPECIFICATION:


JOSAM SERIES FD-100-S "LEVELEZE II" CAST IRON FLOOR DRAIN WITH 5" SQUARE NIKALOY TOP, 2-STAGE HEIGHT ADJUSTMENT, AND BOTTOM OUTLET.

LITE LINE

FLOOR DRAIN LEVELEZE II, 5" TOP

SERIES

FD-100-S



OPTIONS:

MODEL	PIPE SIZE
FD-102-S	2"
FD-103-S	3"
FD-104-S	4"
FD-105-S*	5"-Z

* 5" AVAIL. IN NO-HUB ONLY

DATE OF LAST CHANGE: 11/14/14

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

HUB OUTLET WITH GASKET

NO-HUB OUTLET

JOSAM SERIES FD-200-4CP COATED CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH INVERTIBLE CLAMP COLLAR AND DRAINAGE SLOTS AND 4" ROUND ADJUSTABLE CHROME-PLATED BRASS STRAINER.


FLOOR DRAIN

ADJUSTABLE TOP WITH 2" BOTTOM OUTLET

SERIES

GRATE FREE AREA: 3.75 in² MEETS ADA AND HEEL-PROOF REQS.





OUTLET: -T NPT THREADED NO-HUB

ATE OF LAST CHANGE:	11/16/13
MENSIONS ARE SUBJECT TO M	
OLERANCES AND CHANGE WIT	
WE CAN ASSUME NO RESPON	
USE OF SUPERSEDED OR \	OID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

FD-200-4CP

SPECIFICATION:


JOSAM SERIES FD-200-4CP-SQ COATED CAST IRON FLOOR DRAIN, TWO-PIECE BODY WITH INVERTIBLE CLAMP COLLAR AND DRAINAGE SLOTS AND 4" SQUARE ADJUSTABLE CHROME-PLATED BRASS STRAINER.


FLOOR DRAIN


ADJUSTABLE TOP WITH 2" BOTTOM OUTLET

SERIES FD-200-4CP-SQ

GRATE FREE AREA: 5.5 in² MEETS ADA AND HEEL-PROOF REQS.







OUTLET:

NPT THREADED NO-HUB

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.


JOSAM COMPANY MICHIGAN CITY, INDIANA

JOSAM SERIES FD-210-4CP FLOOR DRAIN WITH PVC BODY, INVERTIBLE CLAMP COLLAR WITH DRAINAGE SLOTS, AND 4" ROUND ADJUSTABLE CHROME-PLATED BRASS STRAINER.


FLOOR DRAIN PVC

SERIES FD-210-4CP

GRATE FREE AREA: 3.75 in²
MEETS ADA AND HEEL-PROOF REQS.







MODEL	PIPE SIZE	Н
FD-212	2"	2-1/8
FD-213	3"	2-3/4
FD-214	4"	2-3/4

DATE OF LAST CHANGE: 11/16/13

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

SPECIFICATION:


JOSAM SERIES FD-210-4CP-SQ FLOOR DRAIN WITH PVC BODY, INVERTIBLE CLAMP COLLAR WITH DRAINAGE SLOTS, AND 4" SQUARE ADJUSTABLE CHROME-PLATED BRASS STRAINER.

FLOOR DRAIN PVC


SERIES FD-210-4CP-SQ

GRATE FREE AREA: 3.75 in²

MEETS ADA AND HEEL-PROOF REQS.









	MODEL	PIPE SIZE	н
	FD-212	2"	2-1/8
	FD-213	3"	2-3/4
	FD-214	4"	2-3/4

DATE OF LAST CHANGE:	11/16/13

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

MICHIGA





MICHIGAN CITY, INDIANA


JOSAM SERIES FD-250J-A COATED CAST IRON FLOOR DRAIN WITH JOSAM ADJUSTABLE ROUND NIKALOY STRAINER.

FLOOR DRAIN

4" NO-HUB ROUND ADJUSTABLE STRAINER

SERIES

FD-250J-A



	П	AD II I	STARLE S	TRAINERS	\$
	TYPE NO.	С	X	Y	FREE AREA
	5A	5	3/4	2-1/8	7.8
Г	6A	6	1-1/4	2-3/8	11.0
	7A	7	1-1/8	2-7/8	13.2
	8A	8	1-5/8	2-5/8	16.2

-SS	STAINLESS STEEL STRAINER PARTS
-2	SATIN FIN. BRONZE STRAINER PARTS
-80	PERF. STAINLESS STEEL BASKET
-CP	CHROME PLATED STRNR (5A,6A)
-J	BACKWATER VALVE
-VP	SECURED GRATE, VANDAL-PROOF SCREWS
-ARE	ACID-RESISTING EPOXY
-92	GALVANIZED CAST IRON PARTS

DATE OF LAST CHANGE: 05/07/12
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:

JOSAM SERIES FD-250J-S COATED CAST IRON FLOOR DRAIN WITH JOSAM ADJUSTABLE SQUARE NIKALOY STRAINER.

FLOOR DRAIN

4" NO-HUB SQUARE ADJUSTABLE STRAINER

SERIES FD-250J-S



			ADJUSTABLE STRAINERS			
		TYPE NO.	В	×	Y	FREE AREA
Ī		5S	5	3/4	1-3/4	9.1
Γ	П	6S	6	3/4	2	13.8
Γ		88	8	1	2-1/2	24.5

-SS	STAINLESS STEEL STRAINER PARTS
-2	SATIN FIN. BRONZE STRAINER PARTS
-80	PERF. STAINLESS STEEL BASKET
-CP	CHROME PLATED STRNR (5S,6S)
-J	BACKWATER VALVE
-VP	SECURED GRATE, VANDAL-PROOF SCREWS
-ARE	ACID-RESISTING EPOXY
-92	GALVANIZED CAST IRON PARTS

DATE OF LAST CHANGE: 05/24/12

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.


JOSAM COMPANY MICHIGAN CITY, INDIANA

SPECIFICATION: FLOOR DRAIN


JOSAM FD-300 SERIES PVC FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE-DRAINAGE FLANGE, 1/2" PRIMER TAP WITH PLUG, WEJLOC INVERTIBLE NON-PUNCTURING CLAMP COLLAR WITH WEEPHOLES, AND SOLVENT WELD BOTTOM OUTLET FOR SCHED 40 PIPE.

PVC

SERIES FD-300







PIPE SIZE	н
2"	3-1/4
3"	4
4"	4

ATE OF I	LAST CHA	ANGE:	11/16/13	
IMENSIONS	ARE SUBJE	CT TO MA	NUFACTURE	RS
TOLERANC	ES AND CH	ANGE WIT	HOUT NOTIC	E.
			SIBILITY FOR	
USE O	F SUPERSE	DED OR V	OID DATA.	

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:

JOSAM FD-300-A SERIES PVC FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE-DRAINAGE FLANGE, 1/2" PRIMER TAP WITH PLUG, WEJLOC INVERTIBLE NON-PUNCTURING CLAMP COLLAR WITH WEEPHOLES, SOLVENT WELD BOTTOM OUTLET FOR SCHED 40 PIPE, WITH ADJUSTABLE 5" ROUND TOP.


FLOOR DRAIN

PVC

SERIES FD-300-A









PIPE SIZE	н	
2"	3-1/4	
3"	4	
4"	4	

OPTIONS:

			X	Y
	-J5PVC	PVC STRAINER	3/4"	2-3/4"
	-J5NB	NICKEL-BRONZE STRAINER	3/4"	2-1/8"
	-J5PB	POLISHED BRONZE STRAINER	3/4"	2-1/8"
	-J5SC	SCORIATED GASKETED SOLID COVER	3/4"	2-1/8"


DATE OF LAST CHANGE:	05/04/15
DIMENSIONS ARE SUBJECT TO M.	
TOLERANCES AND CHANGE WIT WE CAN ASSUME NO RESPON	
THE OF CHIPEDCEDED ON	

JOSAM COMPANY MICHIGAN CITY, INDIANA


JOSAM FD-300J-A SERIES FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE, 1/2" PRIMER TAP WITH PLUG, WEJLOC INVERTIBLE NON-PUNCTURING FLASHING COLLAR WITH WEEPHOLES, SOLVENT-WELD BOTTOM OUTLET FOR SCHEDULE 40 PIPE AND ROUND SUPER-FLO NIKALOY ADJUSTABLE STRAINER.

FLOOR DRAIN PVC

SERIES FD-300J-A







OPTIONS:

	-49	3/4" PRIMER TAP	
	-2	 BRONZE ADJUSTABLE STRAINER 	
	-VP	SECURED GRATE	
П	-CP	5A AND 6A ONLY	

STRAINER	В	х	Y	FREE AREA
-5A	5	3/4	2-1/8	7.8
-6A	6	1-1/4	2-3/8	11.0
-7A	7	1-1/8	2-7/8	13.2
-8A	8	1-5/8	2-5/8	16.2

	PIPE SIZE	н
	2"	3-1/4
	3"	4
	4"	4

DATE OF LAST CHANGE: 05/04/15
DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.


JOSAM COMPANY MICHIGAN CITY, INDIANA NOTES

SPECIFICATION:


JOSAM FD-300J-S SERIES FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE, 1/2" PRIMER TAP WITH PLUG, WEJLOC INVERTIBLE NON-PUNCTURING FLASHING COLLAR WITH WEEPHOLES, SOLLENT-WELD BOTTOM OUTLET FOR SCHEDULE 40 PIPE AND SQUARE SUPER-FLO NIKALOY ADJUSTABLE STRAINER.

FLOOR DRAIN PVC

SERIES FD-300J-S







OPTIONS

П	-49	3/4" PRIMER TAP
П	-2	BRONZE ADJUSTABLE STRAINER
	-VP	SECURED GRATE
	-CP	5S AND 6S ONLY

STRAINER	В	х	Y	FREE AREA
-5S	5	7/8	1-7/8	9.1
-6S	6	7/8	2-1/4	13.8
-85	8	1-1/4	2-1/2	24.5

PIPE SIZE	н
2"	3-1/4
3"	4
4"	4

DATE OF LAST CHANGE: 05/24/12

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.


JOSAM COMPANY MICHIGAN CITY, INDIANA

JOSAM FD-310 SERIES 2-PIECE COATED CAST IRON FLOOR DRAIN, 1/2" PRIMER TAP WITH PLUG, INVERTIBLE CLAMP COLLAR, AND 5" ADJUSTABLE ROUND NIKALOY STRAINER.

FLOOR DRAIN 5" TOP CAST IRON

SERIES

FD-310



OPTIONS:

-VP	SECURED GRATE, VANDAL PROOF SCREWS
-80	PERFORATED STAINLESS STEEL BASKET

DATE OF LAST CHANGE:	02/27/14
DIMENSIONS ARE SUBJECT TO MA	ANUFACTURER
TOLERANCES AND CHANGE WIT	
WE CAN ASSUME NO RESPON	
USE OF SUPERSEDED OR V	OID DATA.

JOSAM COMPANY
MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION:

JOSAM FD-350-A SERIES PVC FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE, 1/2" PRIMER TAP WITH PLUG, WELLOC INVERTIBLE, NON-PUNCTURING CLAMP COLLAR WITH WEEPHOLES, SOLVENT WELD BOTTOM FOR SCHED 40 PIPE AND ROUND ADJUSTABLE TOP WITH METAL RIM AND GRATE.


FLOOR DRAIN

PVC

SERIES FD-350-A







	PIPE SIZE	н
	2"	3-1/4
П	3"	4
	4"	4
_		

0	PT	$\Gamma I C$	NC	19

-5NBRG	ROUND NICKEL-BRONZE RIM AND GRATE
-5PBRG	ROUND POLISHED BRONZE RIM AND GRATE
-5SCRG	ROUND SCORIATED GASKETED SOLID COVER

DATE OF LAST CHANGE: 11/16/13

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.

WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.


JOSAM COMPANY
MICHIGAN CITY, INDIANA

JOSAM FD-350-SQ SERIES PVC FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE, 1/2" PRIMER TAP WITH PLUG, WEJLOC INVERTIBLE NON-PUNCTURING CLAMP COLLAR WITH WEEPHOLES, SOLVENT WELD BOTTOM FOR SCHED 40 PIPE AND SQUARE ADJUSTABLE TOP WITH METAL RIM AND GRATE.


FLOOR DRAIN

PVC

FD-350-SQ SERIES







	PIPE SIZE	н
П	2"	3-1/4
П	3"	4
	4"	4

OPTIONS:

-5NBRG	NICKEL-BRONZE RIM AND GRATE
-5PBRG	POLISHED BRONZE RIM AND GRATE
-5SCRG	SCORIATED GASKETED SOLID COVER

DATE OF LAST CHANGE: 11/16/13 DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

SPECIFICATION:


JOSAM FD-370 SERIES PVC FLOOR DRAIN, TWO-PIECE BODY WITH DOUBLE DRAINAGE FLANGE, WEJLOC NON-PUNCTURING CLAMP COLLAR WITH WEEPHOLES, 9" ROUND PVC GRATE AND SOLVENT WELD BOTTOM OUTLET FOR SCHEDULE 40 PVC PIPE.

FLOOR DRAIN PVC, 9" ROUND

FD-370 SERIES









П	2"	PIPE SIZE - FD-372
	3"	PIPE SIZE - FD-373
	4"	PIPE SIZE - FD-374
\neg		
	-HG	HALF GRATE
	-В	BUCKET
	-49	3/4" PRIMER TAP
П	-50	1/2" PRIMER TAP
		3" 4" -HG -B -49

DATE OF LAST CHANGE:	07/24/2012
DIMENSIONS ARE SUBJECT TO M	ANUICACTURERO

JOSAM COMPANY TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA. MICHIGAN CITY, INDIANA





SPECIFICATION: **FLOOR DRAIN** PVC JOSAM FD-450-SQ SERIES PVC FLOOR DRAIN WITH SQUARE ADJUSTABLE TOP AND METAL RIM AND GRATE. FD-450-SQ SERIES 5 3/8" SQ. 4-3/8" 5-1/8"


SPECIFICATION:

JOSAM FD-450.1-A SERIES PVC DRAIN BODY WITH THREADED ADJUSTABLE SUPER-FLO ROUND NIKALOY STRAINER. COMBINATION 3" X 4" SOLVENT WELD BOTTOM OUTLET FITS OVER 3" OR INSIDE 4" SCHEDULE 40 PVC PIPE. FLOOR DRAIN PVC

SERIES FD-450J-A









	SIKAINER	DIA. B	X	Y	FREE AREA
	-5A	5	1	2	7.8
Ī	-6A	6	1-1/2	2-1/2	11.0
Ī	-7A	7	1-1/2	3	13.2
1	-84	8	1-3/4	2-3/4	16.2

	-2	SATIN FINISH BRONZE TOP		
	-VP	SECURED GRATE, VP SCREWS		

DATE OF LAST CHANGE: 02/27/14

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA NOTES

DATE OF LAST CHANGE: 02/28/14

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

Ø3 1/2"

PVC OUTLET FITS OVER 3" AND INSIDE 4" SCHED 40 DWV

JOSAM COMPANY MICHIGAN CITY, INDIANA

OPTIONS:

-5NBRG

-5PBRG

-5SCRG

ROUND NICKEL-BRONZE RIM AND GRATE

ROUND POLISHED BRONZE RIM AND GRATE

ROUND SCORIATED GASKETED SOLID COVER




JOSAM FD-450J-S SERIES PVC DRAIN BODY WITH THREADED ADJUSTABLE SUPER-FLO SQUARE NIKALOY STRAINERS. COMBINATION 3" X 4" SOLVENT WELD BOTTOM OUTLET FITS OVER 3" OR INSIDE 4" SCHEDULE 40 PVC PIPE.


FLOOR DRAIN **PVC**

SERIES

FD-450J-S







OP	TI	0	N.	S

-VP

STRAINER	DIA. B	X	Y	FREE AREA
-5S	5	1	2	9.1
-6S	6	1-1/4	2-1/4	13.8
-8S	8	1-1/2	2-3/4	24.5

DATE OF LAST CHANGE: DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

SATIN FINISH BRONZE TOP

SECURED GRATE, VP SCREWS

SPECIFICATION:


JOSAM FD-500 SERIES PVC NON-ADJUSTABLE FLOOR DRAIN WITH 5" ROUND TOP AND SOLVENT WELD BOTTOM OUTLET.


FLOOR DRAIN

PVC


FD-500 SERIES

STRAINER OPENINGS = 1/4" SQ. SPECIFY BODY AND TOP OPTIONS BELOW.











BODY:

MODEL	PIPE SIZE	н	h
FD-502	2"	1-7/8	1-1/8
FD-503	3"	2-5/8	1
FD-504	4"	2-1/2	3/4

TOP	OPTION	S:
\Box	155110	_

	Ш	-J5PVC	PVC STRAINER		
Δ	П	-J5NB	NICKEL-BRONZE STRAINER		
		-J5SC	SCORIATED GASKETED SOLID COVER		
Δ SEPARATE SUBMITTAL FOR THIS OPTION AVAILABLE					


DATE OF LAST CHANGE: NOTES


JOSAM COMPANY DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA. MICHIGAN CITY, INDIANA


JOSAM FD-500 SERIES PVC NON-ADJUSTABLE FLOOR DRAIN WITH 5" ROUND NIKALOY TOP AND SOLVENT WELD BOTTOM OUTLET.

FLOOR DRAIN PVC

FD-500-J5NB SERIES







SIZE

BODY:

MODEL	PIPE SIZE	н	h
FD-502	2"	1-7/8	1-1/8
FD-503	3"	2-5/8	1
FD-504	4"	2-1/2	3/4

DATE OF LAST CHANGE: 6/24/14 DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES


SPECIFICATION: **ROOF DRAIN** PVC JOSAM SERIES RD-300 ROOF DRAIN WITH PVC ROOF DRAIN BODY. CAST IRON NON-PUNCTURING CLAWP RING WITH INTEGRAL GRAVEL STOP, SMALL CAST IRON DOME AND SOLVENT WELD BOTTOM OUTLET. **RD-300 SERIES** 5 1/2" 3-3/4" PIPE SIZE MODEL RD-302 2" RD-303 3" 4" -UC OPTION RD-304 OPTIONS: PIPE --UC UNDERDECK CLAMP DRAIN RECEIVER DRAIN RECEIVER AND CLIPS 2" HIGH SOLID CLAMP COLLAR -VP SECURED DOME, VP SCREWS NOTES DATE OF LAST CHANGE: 08/18/14 JOSAM COMPANY DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA. MICHIGAN CITY, INDIANA

SPECIFICATION: JOSAM SERIES RD-700 ROOF DRAIN TOP ASSEMBLY WITH FITSALL CLAMP RING WITH INTEGRAL GRAVEL STOP TO FIT BOLT CIRCLE DIAMETERS OF 7-1/2" TO 11". LARGE DOME, AND HARDWARE.


ROOF DRAIN "FITSALL" TOP ASSEMBLIES


SERIES


RD-700





MICHIGAN CITY, INDIANA















JOSAM COMPANY

MICHIGAN CITY, INDIANA

NOTES





DATE OF LAST CHANGE:

DIMENSIONS ARE SUBJECT TO MANUFACTURERS

TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR

USE OF SUPERSEDED OR VOID DATA.






JOSAM SERIES CO-430 PVC CLEANOUT, ROUND NIKALOY ADJUSTABLE TOP WITH INTERNAL BRONZE PLUG, COMBINATION 3" X 4" SOLVENT WELD BOTTOM OUTLET FITS OVER 3" OR INSIDE 4" SCHEDULE 40 PVC PIPE.

CLEANOUT

PVC

SERIES CO-430





SPECIFICATION:

JOSAM SERIES CO-600 CLEANOUT, CAST IRON 4" NO-HUB BODY, INTEGRAL THREADED PLUG AND ROUND SECURED TOP.

CLEANOUT NO-HUB

SERIES CO-600







CO-600 CI RIM AND COVER STANDARD



CO-600-NB NIKALOY RIM AND COVER



CO-600-NB-SQ SQUARE NIKALOY RIM AND COVER

	MODEL	Α	Н
	CO-600	Ø6	3-1/8
П	CO-600-NB	Ø5-1/8	2-1/2
	CO-600-NB-SQ	5-3/8 SQ.	2-1/2

JOSAM COMPANY

MICHIGAN CITY, INDIANA

DATE OF LAST CHANGE: 11/16/13

DIMENSIONS ARE SUBJECT TO MANUFACTURERS
TOLERANCES AND CHANGE WITHOUT NOTICE.
WE CAN ASSUME NO RESPONSIBILITY FOR
USE OF SUPERSEDED OR VOID DATA.

JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCES AND CHANGE WITHOUT NOTICE. WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA.


JOSAM SA LITE LINE SERIES SHOCK ABSORBER WITH COPPER SHELL, PISTON TYPE AIR CUSHION AND MALE THREADED CONNECTION.

SHOCK ABSORBER

LITE LINE - COPPER

SERIES

SA



MODEL	FIXTURE UNITS	THREAD	A	В
SA-A	1 - 11	1/2"	8-1/4	1-3/8
SA-B	12 - 32	3/4"	8-3/4	1-3/8
SA-C	33 - 60	1"	11	1-3/8
SA-D	61 - 113	1"	10-1/8	2-1/8
SA-E	114 - 154	1"	12-5/8	2-1/8
SA-F	155 - 330	1"	15-1/8	2-1/8

CONFORMS TO ASSE 1010 COMPLIES WITH LEAD FREE REQUIREMENTS

DATE OF	LAST (CHANG	E: 0	4/30/15
DIMENSION	IS ARE SU	JBJECT T	O MANU	FACTURERS
				JT NOTICE.
				LITY FOR
USE (OF SUPER	RSEDED	OR VOID	DATA.


JOSAM COMPANY MICHIGAN CITY, INDIANA

NOTES

SPECIFICATION:

JOSAM JG-0100S SERIES ACID-RESISTANT EPOXY COATED FABRICATED STEEL GREASE INTERCEPTOR, NO-HUB CONNECTIONS, INTERNAL TRAP, REMOVABLE BAFFLE, GASKETED NON-SKID COVER, AND FLOW CONTROL GREASE INTERCEPTOR MANUAL TYPE

JG-0100S





JOSAM CORPORATE

525 West Highway 20 Michigan City, IN 46360

800.36.JOSAM F 800.627.0008

JOSAM EXECUTIVE

2501 S. Front Street Philadelphia, PA 19148

215.339.5370 F 800.962.3312

www.JOSAM.com

