



C



C



B



B



NOTES:

- Extreme Temperature Durability (-40°F to 260°F).
- High Tensile Strength.
- Crack/Split/Leak/Rust Resistant.
- Self Extinguishing.
- Made With Pride in the USA

UNLESS OTHERWISE SPECIFIED:

DIMENSIONS ARE IN INCHES
TOLERANCES:
FRACTIONAL $\pm .032$
ANGULAR: MACH $\pm .5^\circ$ BEND $\pm 2^\circ$
TWO PLACE DECIMAL $\pm .010$
THREE PLACE DECIMAL $\pm .005$

INTERPRET GEOMETRIC
TOLERANCING PER: ANSI Y14.5, 1994

ENGINEERING	NAME	DATE
DRAWN BY ENG.	DS	5/25/09
CHECKED BY ENG.	DS	5/25/09
ENG APPR.	DS	5/25/09
MFG APPR.	DS	5/25/09

PROPRIETARY AND CONFIDENTIAL

THE INFORMATION CONTAINED IN
THIS DRAWING IS THE SOLE
PROPERTY OF RECTORSEAL.
ANY REPRODUCTION IN PART OR
AS A WHOLE WITHOUT THE
WRITTEN PERMISSION OF
RECTORSEAL IS PROHIBITED.

2601 Spenwick Drive,
Houston, TX 77055
800-231-3345

TITLE:

AG-G 30x50 SPECIFICATION SHEET

SIZE
A

SCALE: 1:15

SHEET 1 OF 1

A