




PBV® SERIES 6800 TWO-PIECE FLANGED TRUNNION SUPPORTED BALL VALVE

The Professional Choice for Dependable, Long Lasting Service.

Standard Features

- WCB/WCC Bodies and Adapters
- O-Ring Stem Seal Design backed by Firesafe Seal
- · Valves Built to API 6D
- Valves meet ASME B16.34, B16.10, B16.5 and BS 5351
- ISO 5211 Compatible Mounting Pads
- Firesafe to API 607 or 6FA
- All Materials Meet NACE MR0175
- Emergency Seat and Stem Sealant Injection
- Carbon Steel with ENP Standard on Internal Trim (Ball, Seat and Stem)
- Locking Devices Standard for Lever or Gear Operated Valves
- Double Bock & Bleed (DBB) in Both Opened and Closed Position
- Equipped with Drain Valve for DBB and Seat Integrity Verification





Dimensional Data (in.), Full Port

SIZE (IN.)	CLASS	Α	В	С	D1	E	F	G	Н	К	N	М	Р	L
	150	2.06	3.62	6.00	0.62	7.00	4.30	3.94	6.53	0.06	4	0.75	4.75	17.00
2	300	2.06	3.62	6.50	0.88	8.50	4.30	3.94	6.53	0.06	8	0.75	5.00	17.00
	600	2.06	3.62	6.50	1.25	11.50	4.30	4.13	6.41	0.25	8	0.75	5.00	20.00
	150	3.13	5.00	7.50	0.75	8.00	5.80	4.88	7.17	0.06	4	0.75	6.00	20.00
3	300	3.13	5.00	8.25	1.12	11.12	5.80	4.88	7.17	0.06	8	0.88	6.62	20.00
	600	3.13	5.00	8.25	1.50	14.00	5.80	5.38	9.28	0.25	8	0.88	6.62	28.00
	150	4.06	6.19	9.00	0.94	9.00	6.86	6.10	10.01	0.06	8	0.75	7.50	28.00
4	300	4.06	6.19	10.00	1.25	12.00	6.86	7.06	10.97	0.06	8	0.88	7.88	28.00
	600	4.06	6.19	10.75	1.75	17.00	6.86	7.06	10.97	0.25	8	1.00	8.50	28.00
	150	6.00	8.50	11.00	1.00	15.50	8.27	8.75	10.91	0.06	8	0.88	9.50	20.00
6	300	6.00	8.50	12.50	1.44	15.88	8.27	8.75	10.91	0.06	12	0.88	10.62	20.00
	600	6.00	8.50	14.00	2.13	22.00	8.27	8.75	10.91	0.25	12	1.13	11.50	20.00
	150	8.00	10.62	13.50	1.12	18.00	10.38	11.92	14.05	0.06	8	0.88	11.75	24.00
8	300	8.00	10.62	15.00	1.63	19.75	10.38	11.92	14.05	0.06	12	1.00	13.00	24.00
	600	8.00	10.62	16.50	2.25	26.00	10.38	11.92	14.05	0.25	12	1.25	13.75	24.00
	150	10.00	12.75	16.00	1.18	21.00	12.05	13.76	15.89	0.06	12	1.00	14.25	24.00
10	300	10.00	12.75	17.50	1.88	22.38	12.05	13.76	15.89	0.06	16	1.13	15.25	24.00
	600	10.00	12.75	20.00	2.75	31.00	12.05	13.76	15.89	0.25	16	1.38	17.00	24.00
	150	12.00	15.00	19.00	1.25	24.00	14.17	16.34	22.91	0.06	12	1.00	17.00	30.00
12	300	12.00	15.00	20.50	2.00	25.50	14.17	16.34	22.91	0.06	16	1.25	17.75	30.00
	600	12.00	15.00	22.00	2.88	33.00	14.17	16.34	22.91	0.25	20	1.38	19.25	30.00

Reduced Port valves available upon request.



PBV® SERIES 6800 ENGINEERING DATA ▶ ▶ ▶


Parts & Materials • Typical 4" Steel Valve

NO.	QTY.	DESCRIPTION	MATERIAL / CARBON STEEL						
1	1	Body	A216-WCB/WCC						
2	1	Adapter Cap	A216-WCB/WCC						
4	1	Ball	A105/A350 LF2 ENP						
5**	1	Stem	A105/A350 LF2 ENP						
6*	2	Seat Assembly	A105/A350 LF2 G/PTFE						
		Seat Assembly	or Devlon®						
9	1	Trunnion	A105/A350 LF2 ENP						
10	1	Trunnion Plate	A352-LCC						
11**	1	Snap Ring	Stainless Steel						
22**	1	Bearing	TFMC						
25*	1	Stem Thrust Bearing	TFMC						
28*	2	Bearing Washer	Steel/PTFE						
31**	2	Spring	Inconel® X-750						
32*	1	O-Ring, Body	HNBR						
33*	2	O-Ring, Seat	HNBR						
34*	2	O-Ring, Stem	HNBR						
35*	2	O-Ring, Trunnion	HNBR						
36*	_	Packing	Graphite						
39	See Dim.	Stud	A193-B7M						
40	See Dim.	Nut	A194-2HM						
45	4	Cap Screw, Trunnion	A574 Modified						
60	1	Handle	Carbon Steel						
62	1	Handle Screw	F912						
67	1	Handle Adapter	Ductile Iron						
68	1	Cap Screw, Stop	A574 Modified						
70*	1	Gasket, Body	Graphite						
71*	1	Gasket, Trunnion	Graphite						
72*	_	Packing, Stem	Graphite						
73**	1	Stop Plate	Carbon Steel						

Recommended spare parts: *after 2 yrs. service, **after 5 yrs. service.

Product Range • Full Port, Flanged Ends

	SHELL MATERIAL	CL	DESIGN Feature	END CONNECT.	2	3			(IN 8	.) 10	12
	WCB/	150	End Entry	RF	Х	Χ	Χ	Χ	Х	Х	Χ
	WCG/	300	End Entry	RF	Х	Χ	Х	Χ	Х	Χ	Χ
	VVCC	600	End Entry	RF	Χ	Х	Х	Х	Х	Χ	Χ



Pressure Temperature





SPECIFYING PBV® SERIES 6800 VALVE FIGURE NUMBERS

Example: 6" C-6830-71-2200-DH-NG This number represents a 6" ANSI Class 300, Full Port, Two-Piece Trunnion Ball Valve, Fire Tested with Emergency Grease Seals, with Raised Face, WCB Body Material, Carbon Steel with ENP Trim, Devlon® Seats, HNBR Seals, for NACE MR0175 Service and Gear Operated.

C	- 6	8	30	- 7	1 .	- 22	00	- D	Н -	- N	G	
MAT.	PORT CONFIG.	VALVE TYPE	PRESS. CLASS	FIRE TESTED	END CONN.	BODY MAT.	TRIM MAT.	SEAT MAT.	SEAL MAT.	NACE OPTION	OPER.	MODIFIER CODE
C	5	8	10	7	1	22	00	D	Н	N	Α	
Carbon	Reduced	Two-	150 CL	Fire Tested	RF	WCB/	Same	Devlon®	HNBR	NACE	Act.	
Steel	6	Piece	30	w/Emerg.	3	WCC	as	or Equiv.			В	
	Full	Trunn.	300 CL	Grease Seals	RTJ	28	Body	G			Bare	
		Type	60			LCC	36	Glass			Stem	
			600 CL				316SS	Filled			G	
								Teflon®			Gear	
											L	
											Lever	

Other body, trim, seat and seal materials are available upon request. Lever mounting pads are designed to dimensions in ISO 5211.

For more information about our products and full Terms & Conditions please visit www.f-e-t.com.



