



GEOTEX® 401

GEOTEX® 401 is a polypropylene, staple fiber, needle-punched nonwoven geotextile produced by Propex, and will meet the following Minimum Average Roll Values (MARV) when tested in accordance with the methods listed below. The fibers are needled to form a stable network that retains dimensional stability relative to each other. The geotextile is resistant to ultraviolet degradation and to biological and chemical environments normally found in soils.

GEOTEX® 401 conforms to the property values listed below¹. Propex performs internal Manufacturing Quality Control (MQC) tests that have been accredited by the Geosynthetic Accreditation Institute – Laboratory Accreditation Program (GAI-LAP). This product is NTPEP tested for AASHTO standards.

		$MARV^2$	
PROPERTY	TEST METHOD	ENGLISH	METRIC
ORIGIN OF MATERIALS	•		
% U.S. Manufactured		100%	100%
MECHANICAL			
Grab Tensile Strength	ASTM D-4632	120 lbs	534 N
Grab Elongation	ASTM D-4632	50%	50%
CBR Puncture	ASTM D-6241	310 lbs	1379 N
Trapezoidal Tear	ASTM D-4533	50 lbs	222 N
ENDURANCE			
UV Resistance at 500 hrs	ASTM D-4355	70%	70%
HYDRAULIC	•		
Apparent Opening Size (AOS) ³	ASTM D-4751	70 US Std. Sieve	0.212 mm
Permittivity	ASTM D-4491	1.7 sec ⁻¹	1.7 sec ⁻¹
Water Flow Rate	ASTM D-4491	140 gpm/ft ²	5704 l/min/m²
	•		
ROLL SIZES ⁴		12.5 ft x 360 ft	3.81 m x 109.8 m
NOLE SIZES		15 ft x 360 ft	4.57 m x 109.8 m

NOTES:

- 1. The property values listed above are effective 12/17/2018 and are subject to change without notice.
- 2. Values shown are in weaker principal direction. Minimum average roll values (MARV) are calculated as the typical minus two standard deviations. Statistically, it yields a 97.7% degree of confidence that any samples taken from quality assurance testing will exceed the value reported. Values represent testing at time of manufacture.
- 3. Maximum average roll value.
- 4. Contact your local Territory Business Manager (TBM) for custom widths and colors. Lead times may vary depending on customer requirements and volume requested.



ENGINEERED EARTH SOLUTIONSTM

www.propexglobal.com

Propex Operating Company, LLC \cdot 4019 Industry Drive Chattanooga, TN 37416 \cdot ph 800 621 1273 \cdot ph 423 855 1466 \cdot ph 800 621 1273 \cdot ph 423 855 1466

ARMORMAX®, PYRAMAT®, LANDLOK®, X3®, PYRAWALL®, SCOURLOK®, GEOTEX®, PETROMAT®, PETROTAC®, REFLECTEX®, and GRIDPRO™ are registered trademarks of Propex Operating Company, LLC.

This publication should not be construed as engineering advice. While information contained in this publication is accurate to the best of our knowledge, Propex does not warrant its accuracy or completeness. The ultimate customer and user of the products should assume sole responsibility for the final determination of the suitability of the information and the products for the contemplated and actual use. The only warranty made by Propex for its products is set forth in our product data sheets for the product, or such other written warranty as may be agreed by Propex and individual customers. Propex specifically disclaims all other warranties, express or implied, including without limitation, warranties of merchantability or fitness for a particular purpose, or arising from provision of samples, a course of dealing or usage of trade.