

AREA DRAINS

20C, 30C, 40C

Specification Sheet




Part Number	Description
20C	Drain, Cesspool/Area, Instant Set®, 6" strainer diameter
30C	Drain, Cesspool/Area, Instant Set®, 7" strainer diameter
40C	Drain, Cesspool/Area, Instant Set®, 8" strainer diameter

SPECIFICATION


Recommended for use on concrete floors to facilitate drainage where water can collect. Drain unit consists of cast iron main body and grate. Assembly is secured to pipe using Instant Set® clamp with stainless steel fasteners.

DIMENSIONS

Top View



Side View



DESIGN FEATURES

- Cast iron main body and grate assembly with corrosion resistant coating
- Instant Set® drain pipe attachment. No additional hardware required
- Removable grate for drain cleaning and replacement
- Stainless steel fasteners with stainless steel & neoprene washers.

INSTALLATION

1. Position drain assembly in place with drain pipe connected prior to pouring concrete.
2. Instant Set® joint clamps on outside of drain pipe. Remove grate and simply slide over pipe. Evenly tighten 3 internal bolts with rubber washer seals, torque to 20 inch-pounds. Re-install grate.
3. Pour concrete flooring to level of grate.

COMPLIANCES/LISTINGS

- Compliant to ASME A112.6.3 standards listed in IAPMO File: 0848
- Uniform Plumbing Code (UPC®)



Part Number	Nominal Pipe Connection	Dimensions (Inches)			
		A	B	C Area	D
20C	2"	3-5/8	4-3/8	7.21 sq. n.	1-5/16
30C	3"	4-5/8	4-1/4	9.26 sq. in.	1-5/16
40C	4"	5-1/2	4-1/8	14.24 sq. in.	1-5/16



3689 Arrowhead Drive, Carson City, NV 89706

Phone (800) 854-3215 Fax (800) 243-1777

E-mail sales@lspproducts.com

Website www.lspproducts.com

Content matter is subject to change at any time. It is the user's responsibility to ensure the most updated revisions are obtained.

Revised 05/2019

Product Submittal	
Job Name:	
Date:	
Part Number	Quantity
Architect:	
Contractor:	