



INDIRECT WATER HEATERS

List Prices 2017
FOB Uxbridge, MA USA

Model No.	List Price (\$)	Capacity (gal.)	Height (in.)	Diameter (in.)	Ship Wt. (lbs.)
HF-30	1177	30	32	23.5	85
HF-40	1211	40	42	23.5	100
HF-40 LOW	1289	42	34	28.0	110
HF-50	1461	50	52	23.5	115
HF-60	1712	60	60	23.5	125
HF-60 LOW	1762	60	44	28.0	130
HF-60-HO	2031	60	60	23.5	138
HF-80	1936	80	54	28.0	140
HF-80-HO	2255	80	54	28.0	155
HF-115	2734	115	72	28.0	185
HF-115-HO	3054	115	72	28.0	200

DUAL COIL INDIRECT WATER HEATERS

Used with solar and many other applications.

Model No.	List Price (\$)	Capacity (gal.)	Height (in.)	Diameter (in.)	Ship Wt. (lbs.)
HF-60-D	2316	60	60	23.5	155
HF-80-D	2639	80	54	28.0	170
HF-115-D	3380	115	72	28.0	205

HOT WATER STORAGE TANKS

Insulated with thermostat, use with tankless coils or instantaneous water heaters

Model No.	List Price (\$)	Capacity (gal.)	Height (in.)	Diameter (in.)	Ship Wt. (lbs.)
HF-30-ST	1044	30	32	23.5	75
HF-40-ST	1079	40	42	23.5	90
HF-40L-ST	1140	42	42	28.0	100
HF-60-ST	1573	60	60	23.5	115
HF-60L-ST	1623	60	44	28.0	115
HF-80-ST	1787	80	54	28.0	130
HF-115-ST	2574	115	72	28.0	190

HYDRONIC BUFFER TANKS

Insulated thermal buffer and hydraulic separator tanks. Used with chillers and low mass boilers.
-XX denotes connection size Specify 1 1/4", 1 1/2", or 2" NPT connections.

Model No.	List Price (\$)	Capacity (gal.)	Height (in.)	Diameter (in.)	Ship Wt. (lbs.)
HF-22-BT-2	648	22	27.0	23.5	38
HF-22-BT-4	747	22	27.0	23.5	38
HF-40-BT-XX	1467	40	42.0	23.5	100
HF60-BT-XX	2011	60	42.0	28.0	125
HF80-BT-XX	2220	80	52.0	28.0	135
HF115-BT-XX	2909	115	72.0	28.0	170

List Prices: 07/01/17 REV, FOB Uxbridge, MA

Heat-Flo, Inc., 15 Megan Court, P.O. Box 612, Uxbridge, MA 01569 USA
Tel: 508-278-2400 Fax: 508-278-2466 www.heat-flo.com



List Prices 2017
FOB Uxbridge, MA USA

INDIRECT WATER HEATERS
- HO = HIGH OUTPUT

1 1/2" NPT COLD AND HOT CONNECTIONS
1 1/4" NPT BOILER SUPPLY AND RETURN

HF-80-C	2116	80	54	28.0	140
HF-115-C	2915	115	72	28.0	185
HF-80-HO-C	2436	80	54	28.0	155
HF-115-HO-C	3234	115	72	28.0	200

INDIRECT WATER HEATERS
- XHO = EXTRA HIGH OUTPUT

1 1/2" NPT COLD AND HOT CONNECTIONS
1 1/4" NPT BOILER SUPPLY AND RETURN

HF-85-XHO	3809	86	63	28.0	195
HF-115-XHO	4373	115	75	28.0	240

HOT WATER STORAGE TANKS with 1 1/2" NPT COLD AND HOT CONNECTIONS

HF-80-ST-C	1967	80	54	28.0	130
HF-115-ST-C	2754	115	72	28.0	190

HYDRONIC BUFFER TANKS WITH COIL (S) **

Insulated thermal buffer and hydraulic separator tanks. Used with water source heat pumps, chillers, and low mass boilers.

-XX denotes connection size Specify 1 1/4", 1 1/2", or 2" NPT connections.

Internal coil can be used to add heat from solar panels, remove heat, and many other applications.

Model No.	List Price (\$)	Capacity (gal.)	Height (in.)	Diameter (in.)	Ship Wt. (lbs.)
HF-40-BT-XX with coil	1775	40	42.0	23.5	115
HF60-BT-XX with coil	2302	60	42.0	28.0	140
HF80-BT-XX with coil	2510	80	52.0	28.0	150
HF115-BT-XX with coil	3215	115	72.0	28.0	175

**** Buffer tanks can be fabricated with dual coils. Add \$275.00 to the single coil list price for a second coil.**

List Prices: 7/1/17 REV FOB Uxbridge, MA

Heat-Flo, Inc., 15 Megan Court, P.O. Box 612, Uxbridge, MA 01569 USA
Tel: 508-278-2400 Fax: 508-278-2466 www.heat-flo.com



List Prices 2017
FOB Uxbridge, MA USA

INDIRECT WATER HEATERS WITH ELECTRIC BACKUP

Includes single coil, control box, thermostat, and 3500 watt element

Model No.	List Price (\$)	Capacity (gal.)	Height (in.)	Diameter (in.)	Ship Wt. (lbs.)
HF-40E	1628	40	42	23.5	105
HF-60E	2177	60	60	23.5	135
HF-80E	2512	80	54	28.0	150
HF-115E	3392	115	72	28.0	195

DUAL COIL INDIRECT WATER HEATERS

Used with solar and many other applications.

Model No.	List Price (\$)	Capacity (gal.)	Height (in.)	Diameter (in.)	Ship Wt. (lbs.)
HF-60-D	2316	60	60	23.5	155
HF-80-D	2639	80	54	28.0	170
HF-115-D	3380	115	72	28.0	205

DUAL COIL INDIRECT WATER HEATERS WITH ELECTRIC BACKUP

Includes dual coils, control box, thermostat, and 3500 watt element

Model No.	List Price (\$)	Capacity (gal.)	Height (in.)	Diameter (in.)	Ship Wt. (lbs.)
HF-60-DE	2779	60	60	23.5	165
HF-80-DE	3234	80	54	28.0	180
HF-115-DE	4056	115	72	28.0	215

REPLACEMENT PARTS

	Trade List Price	Wholesale Price
T+P Valve, Watts LLL100XL	27.72	19.96
T+P Valve, Watts 100XL8	22.62	16.29
T+P Valve, Watts 40XL8	173.00	124.56
Tstat, Honeywell 4080B	63.26	45.55
Replacement Well, SS 1/2"	43.44	31.28
Drain Valve 1/2"	18.71	13.47
Drain Valve Nipple 1/2 x 3-1/2	8.61	6.20
Magnesium Anode Rod Assy, 1 1/4" NPT, 1.31" DIA. X 18.5" long	60.67	43.68
Electric Element 3500W, SS	135.00	97.20
Electric Tstat With High Limit	27.00	19.44

List Prices: 7/1/17 REV, FOB Uxbridge, MA

Heat-Flo, Inc., 15 Megan Court, P.O. Box 612, Uxbridge, MA 01569 USA
Tel: 508-278-2400 Fax: 508-278-2466 www.heat-flo.com