Printing date 01/04/2018 Revised On 01/04/2018

1 Identification of the substance and manufacturer

HANDICAP DARK BLUE Trade name:

0000200649 **Product code:**

Seymour of Sycamore Manufacturer/Supplier: 917 Crosby Avenue

Sycamore, IL 60178 USA phone: 815-895-9101 www.seymourpaint.com

Emergency telephone number: 1-800-255-3924 Seymour of Sycamore 3041 Dougall Avenue, Suite 503 Windsor, ONT N9E 1S3 CANADA phone: 800-435-4482

www.seymourpaint.com

2 Hazard(s) identification

Classification of the substance or mixture

Flam. Aerosol 1 H222 Extremely flammable aerosol.

Press. Gas H280 Contains gas under pressure; may explode if heated.

STOT SE 3 H335 May cause respiratory irritation.

STOT RE 2 H373 May cause damage to organs through prolonged or repeated exposure.

GHS Hazard pictograms

Precautionary statements

GHS02 GHS04 GHS07 GHS08

Signal word Danger

Hazard statements Extremely flammable aerosol.

Contains gas under pressure; may explode if heated.

May cause respiratory irritation.

May cause damage to organs through prolonged or repeated exposure. Keep away from heat/sparks/open flames/hot surfaces. - No smoking.

Do not spray on an open flame or other ignition source.

Pressurized container: Do not pierce or burn, even after use.

Do not breathe dust/fume/gas/mist/vapors/spray.
Use only outdoors or in a well-ventilated area.
IF INHALED: Remove person to fresh air and keep comfortable for breathing.
Call a poison center/doctor if you feel unwell.

Store in a well-ventilated place.

Store locked up.

Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.

Dispose of contents/container in accordance with local/regional/national/international

regulations.

3 Composition/information on ingredients

Chemical characterization: Mixtures

Chemical Description: This product is a mixture of the substances listed below with nonhazardous additions.

Dangerous components:				
	VM&P Naphtha	20.77%		
	Calcium Carbonate	13.75%		
74-98-6	propane	12.6%		
	n-butane	7.4%		
64742-47-8	Mineral Spirits	4.33%		
	titanium dioxide	2.91%		
	PM acetate	1.39%		
1330-20-7	xylene (mix)	1.38%		

4 First-aid measures

After inhalation:

Supply fresh air; consult doctor in case of complaints.
Remove contaminated clothing. Wash exposed area with soap and water. After skin contact: After eye contact: Rinse opened eye for several minutes under running water. Then consult a doctor.

After swallowing: Rinse out mouth and then drink plenty of water. Rinse mouth with water. Do not induce vomiting.

Most important symptoms and

effects:

Indication of any immediate medical

Dizziness

attention needed: No further relevant information available.

5 Fire-fighting measures

Extinguishing agents:

CO2, extinguishing powder or water spray. Fight larger fires with water spray.

Special hazards: Can form explosive gas-air mixtures.

Protective equipment for firefighters:

A respiratory protective device may be necessary.

6 Accidental release measures

Personal precautions, protective equipment and emergency

procedures:

Wear protective equipment. Keep unprotected persons away.

Use respiratory protective device against the effects of fumes/dust/aerosol.

(Contd. on page 2)

Printing date 01/04/2018 Revised On 01/04/2018

Trade name: HANDICAP DARK BLUE

Methods and material for containment and cleaning up: Ensure adequate ventilation. (Contd. of page 1)

7 Handling and storage

Precautions for safe handling

Use only in well ventilated areas.

Storage requirements:

Components with limit values that require monitoring at the workplace:

Keep away from sources of heat and direct sunlight. Do not warehouse in subfreezing conditions. Store locked up.

8 Exposure controls/personal protection

74-96-6 propane			
PEL (USA)	Long-term value: 1800 mg/m³, 1000 ppm		
REL (USA)	Long-term value: 1800 mg/m³, 1000 ppm		
TLV (USA)	refer to Appendix F inTLVs&BEIs book: D_FX		

106-97-8 n-butane

REL (USA) Long-term value: 1900 mg/m³, 800 ppm TLV (USA) Short-term value: 2370 mg/m³, 1000 ppm

(EX) 108-65-6 PM acetate

WEEL (USA) Long-term value: 50 ppm

1330-20-7 xylene (mix)

Long-term value: 435 mg/m³, 100 ppm PEL (USA) REL (USA) Short-term value: 655 mg/m³, 150 ppm Long-term value: 435 mg/m³, 100 ppm Short-term value: 651 mg/m³, 150 ppm Long-term value: 434 mg/m³, 100 ppm TLV (USA)

Ingredients with biological limit values:

1330-20-7 xylene (mix)

BEI (USA) 1.5 g/g creatinine Medium: urine Time: end of shift

Parameter: Methylhippuric acids

Keep away from foodstuffs and animal feed. Wash hands after use. Hygienic protection:

Immediately remove all soiled and contaminated clothing.

Wash hands after use.

Avoid contact with the skin. Avoid contact with the eyes and skin. Do not eat or drink while working.

Breathing equipment: A respirator is generally not necessary when using this product outdoors or in large open areas.

In cases where short and/or long term overexposure exists, a charcoal filter respirator should be worn. If you suspect overexposure conditions exist, please consult an authority on chemical

hygeine.

Hand protection: Nitrile gloves.

The glove material must be impermeable and resistant to the substance.

Eye protection: Tightly sealed goggles

9 Physical and chemical properties

Appearance: Aerosol. Odor: Aromatic Odor threshold: Not determined. pH-value: Not determined. Melting point/Melting range Undetermined. -44 °C (-47.2 °F) **Boiling point:** Flash point: -19 °C (-2.2 °F) Flammability (solid, gas): Extremely flammable.

Decomposition temperature: Not determined.

Auto igniting: Product is not self-igniting.

Danger of explosion: In use, may form flammable/explosive vapour-air mixture.

Lower Explosion Limit: 1.7 Vol % **Upper Explosion Limit:** 10.9 Vol % Vapor pressure: Not determined.

Relative Density: Between 0.77 and 0.85 (Water equals 1.00)

Vapor density Not determined. Evaporation rate Not applicable. Partition coefficient: n-octonal/water: Not determined. Solubility: Not determined. Viscosity: Not determined. Water: 21.7 %

10 Stability and reactivity

Reactivity: Stable at normal temperatures.

(Contd. on page 3)

Printing date 01/04/2018 Revised On 01/04/2018

Trade name: HANDICAP DARK BLUE

(Contd. of page 2)

Conditions to avoid: Do not allow can to exceed 120 degrees Fahrenheit. Do not warehouse in subfreezing

temperatures.

Chemical stability: Not fully evaluated.

No dangerous reactions known.

Possibility of hazardous reactions: Incompatible materials: No further relevant information available. Hazardous decomposition: No dangerous decomposition products known.

11 Toxicological information

LD/LC50 values that are relevant for classification:				
106-97-8 n-butane				
Inhalative	LC50/4 h	658 mg/l (rat)		
13463-67-7 titanium dioxide				
Oral	LD50	>20,000 mg/kg (rat)		
Dermal	LD50	>10,000 mg/kg (rbt)		
Inhalative	LC50/4 h	>6.82 mg/l (rat)		
108-65-6 PM acetate				
Oral	LD50	8,500 mg/kg (rat)		
Inhalative	LC50/4 h	35.7 mg/l (rat)		
1330-20-7 xylene (mix)				
Oral	LD50	8,700 mg/kg (rat)		
Dermal	LD50	2.000 mg/kg (rbt)		

Information on toxicological effects: No data available

Skin effects: Irritant to skin and mucous membranes.

Eye effects: No irritating effect.

Sensitization: No sensitizing effects known.

12 Ecological information

Inhalative LC50/4 h 6,350 mg/l (rat)

Aquatic toxicity: Hazardous for water, do not empty into drains.

Persistence and degradability: The product is degradable after prolonged exposure to natural weathering processes.

Bioaccumulative potential: No further relevant information available. Mobility in soil: No further relevant information available. Other adverse effects: No further relevant information available.

13 Disposal considerations

Dispose of in accordance with local, state, and federal regulations. Do not puncture, incinerate, or compact. Partially empty cans must be disposed of responsibly. Do not heat or cut empty containers with electric or gas torches.

Recommendation: Completely empty cans should be recycled.

14 Transport information

UN-Number UN1950 DOT N/A UN1950

DOT Consumer Commodity ORM-D

Aerosols, flammable ADR 1950 Aerosols

Transport hazard class(es):

2.1 Class Marine pollutant: No

Special precautions for user: Warning: Gases F-D.S-Ŭ

EMS Number:

Packaging Group: UN "Model Regulation":

UN1950, Aerosols, 2.1

15 Regulatory information

SARA Section 355 (extremely hazardous substances):

None of the ingredients in this product are listed.

SARA Section 313 (Specific toxic chemical listings):

1330-20-7 xylene (mix)

Toxic Substances Control Act

(TSCA): All hazardous ingredients for this product are found on the inventory list of substances. Consumer Product Safety

Comission (CPSC): This product complies with 16 CFR 1303 and does not contain more than 90 ppm of lead.

California Proposition 65 chemicals known to cause cancer:

13463-67-7 titanium dioxide

100-41-4 ethyl benzene

California Proposition 65 chemicals known to cause birth defects or reproductive harm:

None of the ingredients in this product are listed.

CANADIAN ENVIRONMENTAL

PROTECTION ACT: All hazardous ingredients for this product appear on the Canadian Domestic Substance List.

(Contd. on page 4)

I

Safety Data Sheet

Printing date 01/04/2018 Revised On 01/04/2018

Trade name: HANDICAP DARK BLUE

WHMIS Symbols for Canada:

A - Compressed gas D2B - Toxic material causing other toxic effects

EPA:

1330-20-7 xylene (mix)

16 Other information

Regulatory Affairs 01/04/2018 / -Contact: Date of preparation / last revision

(Contd. of page 3)