
ACT D'MAND KONTROLS® Systems






JOB/CUSTOMER: SUBMITTED BY: ENGINEER: APPROVED BY: CONTRACTOR: ORDER NO: SPECIFICATION REF:



NOMENCLATURE					
C	Composite				
3	3- Speed				
100	Series				



TECHNICAL DATA

FLOW RANGE 0-18 GPM

HEAD RANGE 0-17 feet

PHONE: 800-200-1956

MOTORS 2-Pole Single Phase

MIN. FLUID TEMPERATURE 36° F

MAX. FLUID TEMPERATURE 230° F


MAX. WORKING PRESSURE 145 PSI.


CONNECTORS Male Adaptors
(3/4" Composite MIP)

HP MAX SPEED .116 hp

VOLTAGE (max. spd.) 115v/ 245 watts

APPROX. SHIP WEIGHT 8 LBS





NOMENCLATURE GUIDE

TYPE KEY

Example	С	S	BR	3	100	200	PF
C: Composite Pump							
S: Stainless Steel Pump							
BR: Bronze Pump							
3: 3 Speed							
100: 100 Series Small Stator Motor					•		
200: 200 Series Large Stator Moto	r					J	
PF: Pre Fabrication Kit- Under sink in	ıstallati	on Kit Inc	cludes Cust	tom T's 8	Flex Line	es	ı

SIZING GUIDE

	C3-100	S3-100	BR3-200		
TANK	Homes up to 4,000 sqft	Homes up to 4,000 sqft	Homes over 4,000 sqft		
TANKLESS Dedicated Return Line	Pipe runs up to 120 lineal feet	Pipe runs up to 200 lineal feet	Pipe runs over 200 lineal feet		
TANKLESS Standard Plumbing	Pipe runs up to 60 lineal ft. between a tankless water heater and installation location of the D'MAND KONTROLS® System	Pipe runs up to 100 lineal ft. between a tankless water heater and installation location of the D'MAND KONTROLS® System	Pipe runs over 100 lineal ft. between a tankless water heater and installation location of the D'MAND KONTROLS® System		

WARRANTY

ACT, Inc. D'MAND KONTROLS® Systems will replace without charge (at the Company's option) any D'MAND KONTROLS® pump, valve, or component part which is proven defective under normal use. Models C3-100, S3-100, and BR3-200: Warranty – (Five Years from date of purchase) Accessories: Hard-Wired Buttons, Wireless Transmitters and Receivers, all Hard-Wired or Wireless Motion Sensors and Receivers: Warranty – (One Year from date of purchase) Labor is not included with Limited Warranty.

In order to obtain services under this warranty, it is the responsibility of the purchaser to promptly notify the Company in writing and promptly deliver the item in question, delivery prepaid to the factory. The address for notification and delivery is ACT, Inc. D'MAND KONTROLS® Systems, 3176 Pullman Street, Suite 119, Costa Mesa CA 92626.

If the product or part in question contains no defects as covered in the warranty, the purchaser will be notified and billed for parts and labor charges in effect at the time of factory examination and repair.

Any product or part not installed or operated in conformity with instructions or which has been subject to misuse, misapplication, the addition of petroleum based fluids or certain chemical additives to the system, or other abuse, will not be covered by this warranty.

ACT, Inc. D'MAND KONTROLS® Systems OFFERS THIS WARRANTY IN LIEU OF ALL OTHER EXPRESS WARRANTIES. ANY WARRANTY IMPLIED BY LAW INCLUDING WARRANTIES OF MERCHANTABILITY OR FITNESS IS IN EFFECT ONLY FOR THE DURATION OF THE EXPRESS WARRANTY SET FORTH IN THE PARAGRAPH ENTITLED "LIMITED WARRANTY" AS SHOWN ABOVE.

THE ABOVE WARRANTIES ARE IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR STATUTORY, OR ANY OTHER WARRANTY OBLIGATION ON THE PART OF ACT, INC. D'MAND KONTROLS® SYSTEMS.

ACT, INC. D'MAND KONTROLS® SYSTEMS WILL NOT BE LIABLE FOR ANY SPECIAL INCIDENTAL, INDIRECT OR CONSEQUENTIAL DAMAGES RESULTING FROM THE USE OF ITS PRODUCTS OR ANY INCIDENTAL COSTS OF REMOVING OR REPLACING DEFECTIVE PRODUCTS.

This warranty gives you specific rights, and you may have other rights, which vary from state to state. Some states do not allow limitations on how long an implied warranty lasts or on the exclusion of incidental or consequential damages, so those limitations or exclusions may not apply to you.













