

272 Duchaine Blvd · New Bedford, MA 02745 · 508-763-8071 · Fax: 508-763-3769

SSC Water Heater Submittal Sheet

## SuperStor Contender Water Heaters

JOB NAME:

LOCATION:

ARCH./ENGR.:

WHOLESALER:

MECH. CONTRACTOR:

MODEL NUMBER:

NOTES:

## **High Efficiency Heat Exchanger**


- Specially formulated Enamel Flow Coated steel heat exchanger provides maximum heat transfer of energy to domestic water and corrosion resistance
- Low pressure drop
- Gasketless heat exchanger design
- 1" NPT heat exchanger outlet size all models

## **Glass-Lined Tank**

- Specially formulated Enamel Flow Coat guarantees 100% tank coverage, ensuring no exposed welds
- Insulated with approximately 2" of environmentally safe, CFC free, water-blown, extra thick foam insulation
- Allows less than 1/2 degree Fahrenheit per hour heat loss
- Outer shell constructed of grey finished durable plastic for rust and impact resistance
- <sup>3</sup>/<sub>4</sub>" NPT inlet and outlet domestic connection size for 30 and 50 gallon models 1 <sup>1</sup>/<sub>2</sub>" NPT for 80 and 119 gallon models
- Included temperature and pressure relief valve
- Surface mounted control for accurate current temperature measurement inside vessel

## **Additional Features**

- Oversized anode rod protects tank from corrosion
- Limited warranty 7 years residential and 5 years commercial coverage
- Lead Free Compliant, as required by the Safe Drinking Water Act, Section 1417



EQUALS LONGER RECOVERY TIME.