Printing date 02/22/2019 Revised On 02/22/2019

1 Identification of the substance and manufacturer

Trade name: PRECAUTION BLUE (SOLVENT)

0000200953 Product code:

Recommended use: Paint and coating applications.

Uses advised against: Any that differs from the recommended use.

Manufacturer/Supplier: Seymour of Sycamore

917 Crosby Avenue Sycamore, IL 60178 USA phone: 815-895-9101 www.seymourpaint.com

Seymour of Sycamore 3041 Dougall Avenue, Suite 503 Windsor, ONT N9E 1S3 CANADA phone: 800-435-4482 www.seymourpaint.com

Emergency telephone number: 1-800-255-3924

2 Hazard(s) identification

Classification of the substance or mixture

Flam. Aerosol 1 H222 Extremely flammable aerosol.

H280 Contains gas under pressure; may explode if heated. Press. Gas.

Skin Irrit. 2 H315 Causes skin irritation.

STOT SE 3 H335 May cause respiratory irritation.

H373 May cause damage to organs through prolonged or repeated exposure. STOT RE 2

GHS Hazard pictograms

GHS02 GHS04 GHS07 GHS08

Signal word Danger

Hazard statements

Extremely flammable aerosol.

Contains gas under pressure; may explode if heated. Causes skin irritation.

May cause respiratory irritation.
May cause damage to organs through prolonged or repeated exposure.
Keep away from heat/sparks/open flames/hot surfaces. - No smoking. **Precautionary statements**

Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use.

Do not breathe dust/fume/gas/mist/vapors/spray.
Wash hands thoroughly after handling.
Use only outdoors or in a well-ventilated area.
IF INHALED: Remove person to fresh air and keep comfortable for breathing.

Call a poison center/doctor if you feel unwell. Specific treatment (see on this label).

Take off contaminated clothing and wash it before reuse.

Store in a well-ventilated place.

Store locked up.

Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.

Dispose of contents/container in accordance with local/regional/national/international

regulations.

3 Composition/information on ingredients

Chemical characterization: Mixtures

Chemical Description: This product is a mixture of the substances listed below with nonhazardous additions

| Onomiou. De | 500pt0 | This product is a mixture of the substances herea below with normazardous additions. | |
|-----------------------|-------------------|--|--------|
| Dangerous components: | | | |
| 1317-65-3 | Calcium Carbonate | | 20.97% |
| 64742-89-8 | VM&P Naphtha | | 18.47% |
| 74-98-6 | propane | | 17.65% |
| 106-97-8 | n-butane | | 10.37% |
| 142-82-5 | | | 8.18% |
| | Mineral Spirits | | 5.88% |
| 13463-67-7 | titanium dioxide | | 1.41% |
| | | | |

4 First-aid measures

After inhalation: Supply fresh air; consult doctor in case of complaints.

Remove contaminated clothing. Wash exposed area with soap and water. Rinse opened eye for several minutes under running water. Then consult a doctor. After skin contact: After eye contact:

After swallowing: Rinse mouth with water. Do not induce vomiting.

Most important symptoms and

effects:

Indication of any immediate medical

attention needed: No further relevant information available.

5 Fire-fighting measures

Extinguishing agents: CO2, extinguishing powder or water spray. Fight larger fires with water spray.

Special hazards: Can form explosive gas-air mixtures. Protective equipment for

firefighters: A respiratory protective device may be necessary. Printing date 02/22/2019 Revised On 02/22/2019

Trade name: PRECAUTION BLUE (SOLVENT)

(Contd. of page 1)

6 Accidental release measures

Personal precautions, protective

equipment and emergency procedures:

Methods and material for

Use respiratory protective device against the effects of fumes/dust/aerosol.

containment and cleaning up: Absorb liquid components with liquid-binding material.

7 Handling and storage

Precautions for safe handling

Use only in well ventilated areas.

Storage requirements:

Keep away from sources of heat and direct sunlight. Do not warehouse in subfreezing conditions. Store locked up.

8 Exposure controls/personal protection

Components with limit values that require monitoring at the workplace:

74-98-6 propane

PEL (USA) Long-term value: 1800 mg/m³, 1000 ppm REL (USA) Long-term value: 1800 mg/m³, 1000 ppm TLV (USA) refer to Appendix F inTLVs&BEIs book; D. EX

106-97-8 n-butane

REL (USA) Long-term value: 1900 mg/m³, 800 ppm TLV (USA) Short-term value: 2370 mg/m³, 1000 ppm

142-82-5 heptane

PEL (USA) Long-term value: 2000 mg/m³, 500 ppm REL (USA) Long-term value: 350 mg/m³, 85 ppm Ceiling limit value: 1800* mg/m³, 440* ppm *15-min

Short-term value: 2050 mg/m³, 500 ppm Long-term value: 1640 mg/m³, 400 ppm TLV (USA)

Hygienic protection: Immediately remove all soiled and contaminated clothing.

Wash hands after use. Avoid contact with the skin.

Avoid contact with the eyes and skin.

Do not eat or drink while working.

Breathing equipment: A respirator is generally not necessary when using this product outdoors or in large open areas. In cases where short and/or long term overexposure exists, a charcoal filter respirator should be

worn. If you suspect overexposure conditions exist, please consult an authority on chemical

hygeine.

Nitrile gloves. Hand protection:

The glove material must be impermeable and resistant to the substance.

Eye protection: Tightly sealed goggles

9 Physical and chemical properties

Appearance: Aerosol Odor: Aromatic Odor threshold: Not determined. pH-value: Not determined. Melting point/Melting range Undetermined. **Boiling point:** -44 °C (-47.2 °F)

-19 °C (-2.2 °F) Flash point: Flammability (solid, gas): Extremely flammable. **Decomposition temperature:** Not determined.

Auto igniting: Product is not self-igniting.

Danger of explosion: In use, may form flammable/explosive vapour-air mixture.

Lower Explosion Limit: 1.5 Vol % **Upper Explosion Limit:** 10.9 Vol % Vapor pressure: Not determined.

Relative Density: Between 0.77 and 0.85 (Water equals 1.00)

Vapor density Not determined. **Evaporation rate** Not applicable. Partition coefficient: n-octonal/water: Not determined. Not determined. Solubility: Viscosity: Not determined. VOC content (less exempt solvents): 62.2 % 0.0 % Water:

10 Stability and reactivity

Reactivity: Stable at normal temperatures.

Conditions to avoid: Do not allow can to exceed 120 degrees Fahrenheit. Do not warehouse in subfreezing

temperatures.

Chemical stability: Not fully evaluated.

(Contd. on page 3)

D

Printing date 02/22/2019 Revised On 02/22/2019

Trade name: PRECAUTION BLUE (SOLVENT)

Possibility of hazardous reactions: No dangerous reactions known.

Incompatible materials: No further relevant information available. Hazardous decomposition: No dangerous decomposition products known. (Contd. of page 2)

11 Toxicological information

LD/LC50 values that are relevant for classification:

106-97-8 n-butane

Inhalative LC50/4 h 658 mg/l (rat)

13463-67-7 titanium dioxide

Oral LD50 >20,000 mg/kg (rat) Dermal LD50 >10,000 mg/kg (rbt) Inhalative LC50/4 h >6.82 mg/l (rat)

Information on toxicological effects: No data available.

Skin effects: Irritant to skin and mucous membranes.

Eye effects: No irritating effect.

Sénsitization: No sensitizing effects known.

12 Ecological information

Aquatic toxicity: Hazardous for water, do not empty into drains.

Persistence and degradability: The product is degradable after prolonged exposure to natural weathering processes.

This product does not contain any chlorofluorocarbons (CFC's), hydrochlorofluorocarbons (HCFC's), perfluorocarbons (PFC's), heavy metals (chromium, lead, cadmium), or chlorinated Other information:

solvents.

Bioaccumulative potential: No further relevant information available. Mobility in soil: No further relevant information available. **Ecotoxical effects:**

Remark: Toxic for fish

Other adverse effects: No further relevant information available.

13 Disposal considerations

Dispose of in accordance with local, state, and federal regulations. Do not puncture, incinerate, or compact. Partially empty cans must be disposed of responsibly. Do not heat or cut empty containers with electric or gas torches.

Recommendation: Completely empty cans should be recycled.

14 Transport information

UN-Number UN1950 DOT N/A

DOT Consumer Commodity ORM-D Aerosols, flammable

ADR 1950 Aerosols, ENVIRONMENTALLY HAZARDOUS

Transport hazard class(es):

Class

Marine pollutant: Symbol (fish and tree) Special precautions for user: Warning: Gases EMS Number: F-D,S-Ù

Packaging Group: UN "Model Regulation": UN 1950 AEROSOLS, 2.1, ENVIRONMENTALLY HAZARDOUS

15 Regulatory information

SARA Section 355 (extremely hazardous substances):

None of the ingredients in this product are listed.

SARA Section 313 (Specific toxic chemical listings):

None of the ingredients is listed.

Toxic Substances Control Act

(TSCA): All hazardous ingredients for this product are found on the inventory list of substances.

Consumer Product Safety

Comission (CPSC): This product complies with 16 CFR 1303 and does not contain more than 90 ppm of lead.

California Proposition 65 chemicals known to cause cancer:

13463-67-7 titanium dioxide 100-41-4 ethyl benzene

1333-86-4 Carbon black

California Proposition 65 chemicals known to cause birth defects or reproductive harm:

None of the ingredients in this product are listed.

CANADIAN ENVIRONMENTAL

PROTECTION ACT: All hazardous ingredients for this product appear on the Canadian Domestic Substance List.

EPA: 142-82-5 heptane

16 Other information

Contact: Regulatory Affairs