

TUBOLIT[®] Self Seal Pipe Insulation

- 25/50 Rated
- Cost-effective polyethylene
- Self-sealing
- Ideal for domestic plumbing lines

PRICE LIST 5/2011

TUBOLIT SS PIPE INSULATION NOMINAL 3/8" WALL								
Item Code	Pipe Covering size (6-ft. Length)	Tubing & Pipe Size			WALL THICKNESS-NOMINAL 3/8 INCH			
		Copper Tubing		Iron/PVC Piping	List Price Per Lin. Ft.	Packaging Data		
		Nominal ID Size	Outside Diameter	Iron Pipe/PVC Pipe		Lin. Ft. per Ctn.	Tubes per Carton	Weight Per CTN (lbs)
DGS03838	3/8"ID	1/4"	3/8"	-	\$0.581	540	90	10.6
DGS01238	1/2"ID	3/8"	1/2"	1/4"	\$0.607	456	76	10.8
DGS05838	5/8"ID	1/2"	5/8"	3/8"	\$0.681	396	66	11.0
DGS03438	3/4"ID	5/8"	3/4"	-	\$0.752	300	50	9.4
DGS07838	7/8"ID	3/4"	7/8"	1/2"	\$0.765	276	46	9.6
DGS11838	1-1/8"ID	1"	1-1/8"	3/4"	\$0.901	222	37	9.3
DGS13838	1-3/8"ID	1-1/4"	1-3/8"	1"	\$1.015	180	30	9.1
DGS15838	1-5/8"ID	1-1/2"	1-5/8"	1-1/4"	\$1.241	138	23	9.8
DGS11038	1-1/2"IPS	-	1-7/8"	1-1/2"	\$1.565	126	21	9.0
DGS21838	2-1/8"ID	2"	2-1/8"	-	\$1.821	96	16	9.7
DGS20038	2"IPS	-	2-3/8"	2"	\$2.076	84	14	8.0
DGS25838	2-5/8"ID	2-1/2"	2-5/8"	-	\$2.520	72	12	9.0
DGS21038	2-1/2"IPS	-	2-7/8"	2-1/2"	\$2.654	60	10	7.5
DGS31838	3-1/8"ID	3"	3-1/8"	-	\$3.481	54	9	7.7
DGS35838	3-5/8"ID	3-1/2"	3-5/8"	3"	\$4.055	48	8	6.8
DGS41838	4-1/8"ID	4"	4-1/8"	3-1/2"	\$4.388	36	6	10.0
DGS40038**	4" IPS	-	4-3/8"	4"	\$5.054	36	6	10.0

TUBOLIT SS PIPE INSULATION NOMINAL 1/2" WALL								
Item Code	Pipe Covering size (6-ft. Length)	Tubing & Pipe Size			WALL THICKNESS-NOMINAL 1/2 INCH			
		Copper Tubing		Iron/PVC Piping	List Price Per Lin. Ft.	Packaging Data		
		Nominal ID Size	Outside Diameter	Iron Pipe/PVC Pipe		Lin. Ft. per Ctn.	Tubes per Carton	Weight Per CTN (lbs)
DGS03812	3/8"ID	1/4"	3/8"	-	\$0.861	414	69	10.4
DGS01212	1/2"ID	3/8"	1/2"	1/4"	\$0.917	336	56	10.4
DGS05812	5/8"ID	1/2"	5/8"	3/8"	\$1.008	300	50	11.1
DGS03412	3/4"ID	5/8"	3/4"	-	\$1.067	264	44	11.5
DGS07812	7/8"ID	3/4"	7/8"	1/2"	\$1.133	240	40	12.3
DGS11812	1-1/8"ID	1"	1-1/8"	3/4"	\$1.283	186	31	12.1
DGS13812	1-3/8"ID	1-1/4"	1-3/8"	1"	\$1.439	150	25	11.4
DGS15812	1-5/8"ID	1-1/2"	1-5/8"	1-1/4"	\$1.695	120	20	10.6
DGS11012	1-1/2"IPS	-	1-7/8"	1-1/2"	\$2.012	96	16	10.2
DGS21812	2-1/8"ID	2"	2-1/8"	-	\$2.400	84	14	10.4
DGS20012	2"IPS	-	2-3/8"	2"	\$2.899	72	12	9.3
DGS25812	2-5/8"ID	2-1/2"	2-5/8"	-	\$3.231	60	10	10
DGS21012	2-1/2"IPS	-	2-7/8"	2-1/2"	\$3.552	54	9	9.6
DGS31812	3-1/8"ID	3"	3-1/8"	-	\$4.274	48	8	9.2
DGS35812	3-5/8"ID	3-1/2"	3-5/8"	3"	\$4.858	36	6	8.7
DGS41812	4-1/8"ID	4"	4-1/8"	3-1/2"	\$5.510	24	4	7.9
DGS40012**	4" IPS	-	4-3/8"	4" IPS	\$6.262	24	4	12

** Made to order items requiring lead times and minimum order quantities.

• Loading Factor for tubes = .25 / 396 CTNS per 53' trailer

No returns on made to order items.

TUBOLIT SS Pipe Insulation

TUBOLIT SS PIPE INSULATION NOMINAL 3/4" WALL								
Item Code	Pipe Covering size (6-ft. Length)	Tubing & Pipe Size			WALL THICKNESS-NOMINAL 3/4 INCH			
		Copper Tubing		Iron/PVC Piping	List Price Lin. Ft.	Packaging Data		
		Nominal ID Size	Outside Diameter	Iron Pipe/PVC Pipe		Lin. Ft. per Ctn.	Tubes per Carton	Weight Per CTN (lbs)
DGS03834	3/8"ID	1/4"	3/8"	-	\$1.298	228	38	11.1
DGS01234	1/2"ID	3/8"	1/2"	1/4"	\$1.379	210	35	12.2
DGS05834	5/8"ID	1/2"	5/8"	3/8"	\$1.596	180	30	13.0
DGS03434	3/4"ID	5/8"	3/4"	-	\$1.722	162	27	13.5
DGS07834	7/8"ID	3/4"	7/8"	1/2"	\$1.918	150	25	13.9
DGS11834	1-1/8"ID	1"	1-1/8"	3/4"	\$2.305	120	20	13.9
DGS13834	1-3/8"ID	1-1/4"	1-3/8"	1"	\$2.647	96	16	13.1
DGS15834	1-5/8"ID	1-1/2"	1-5/8"	1-1/4"	\$3.571	84	14	11.7
DGS11034	1-1/2"IPS	-	1-7/8"	1-1/2"	\$4.056	66	11	12.7
DGS21834	2-1/8"ID	2"	2-1/8"	-	\$4.590	54	9	9.3
DGS20034	2"IPS	-	2-3/8"	2"	\$5.102	54	9	10.8
DGS25834	2-5/8"ID	2-1/2"	2-5/8"	-	\$5.397	48	8	11.3
DGS21034	2-1/2"IPS	-	2-7/8"	2-1/2"	\$6.144	42	7	9.8
DGS31834	3-1/8"ID	3"	3-1/8"	-	\$7.398	36	6	9.1
DGS35834	3-5/8"ID	3-1/2"	3-5/8"	3"	\$8.113	30	5	9.6
DGS41834	4-1/8"ID	4"	4-1/8"	3-1/2"	\$8.945	24	4	7.6
DGS40034**	4" IPS	-	4-3/8"	4" IPS	\$9.987	24	4	14.0

TUBOLIT SS PIPE INSULATION NOMINAL 1" WALL								
Item Code	Pipe Covering size (6-ft. Length)	Tubing & Pipe Size			WALL THICKNESS-NOMINAL 1 INCH			
		Copper Tubing		Iron/PVC Piping	List Price Per Lin. Ft.	Packaging Data		
		Nominal ID Size	Outside Diameter	Iron Pipe/PVC Pipe		Lin. Ft. per Ctn.	Tubes per Carton	Weight Per CTN (lbs)
DGS03810	3/8"ID	1/4"	3/8"	-	\$2.699	150	25	11.5
DGS01210	1/2"ID	3/8"	1/2"	1/4"	\$2.781	126	21	13.1
DGS05810	5/8"ID	1/2"	5/8"	3/8"	\$2.831	120	20	12.6
DGS03410	3/4"ID	5/8"	3/4"	-	\$3.164	120	20	12.8
DGS07810	7/8"ID	3/4"	7/8"	1/2"	\$3.526	96	16	12.9
DGS11810	1-1/8"ID	1"	1-1/8"	3/4"	\$4.081	84	14	12.7
DGS13810	1-3/8"ID	1-1/4"	1-3/8"	1"	\$4.900	72	12	13.0
DGS15810	1-5/8"ID	1-1/2"	1-5/8"	1-1/4"	\$5.587	54	9	12.8
DGS11010	1-1/2"IPS	-	1-7/8"	1-1/2"	\$6.386	54	9	10.6
DGS21810	2-1/8"ID	2"	2-1/8"	-	\$6.934	48	8	14.3
DGS20010	2"IPS	-	2-3/8"	2"	\$8.311	42	7	9.6
DGS25810	2-5/8"ID	2-1/2"	2-5/8"	-	\$9.299	36	6	11.1
DGS21010	2-1/2"IPS	-	2-7/8"	2-1/2"	\$10.751	30	5	9.0
DGS31810	3-1/8"ID	3"	3-1/8"	-	\$11.727	24	4	8.7
DGS35810**	3-5/8"ID	3-1/2"	3-5/8"	3"	\$12.082	24	4	12.0
DGS41810**	4-1/8"ID	4"	4-1/8"	3-1/2"	\$12.648	18	3	14.0
DGS40010**	4" IPS	-	4-3/8"	4" IPS	\$13.301	18	3	16.0

** Made to order items requiring lead times and minimum order quantities.

● Loading Factor for tubes = .25 / 396 CTNS per 53' trailer

No returns on made to order items.

CONDITIONS OF SALE

Stated below are the terms and conditions upon which Armacell (or "Seller"), will accept orders for the merchandise that Armacell as sole SELLER delivers to you. Such merchandise shall be identified on an invoice or other communication to you. By entering an order directly with SELLER or by the transmission of your order from an affiliate of SELLER to SELLER for acceptance, you agree that the terms and conditions set forth below shall be incorporated in your order.

No order placed with the SELLER shall be considered as accepted until officially acknowledged by the SELLER. If SELLER'S acknowledgement contains terms additional to or different from the PURCHASER'S order, it shall be effective as an acceptance of such order only if such additional or different items are included in the order, and they shall be so included if not objected to in writing within ten (10) days from the date of SELLER'S acknowledgement.

All sales are F.O.B. shipping point, notwithstanding freight allowance (if any) noted herein.

Shipping dates are approximate and are based on receipt of complete information with the order. In no event is SELLER liable for any deliver delays. If drawing approval is required, drawings must be returned on schedule to maintain shipping date. SELLER will determine the point of origin of shipment, the method of transportation and the routing of shipment. PURCHASER will be billed for transportation charges advanced by SELLER, if any. In no event will SELLER be responsible for demurrage or detention charges.

PURCHASER shall have a reasonable amount of time after receipt of merchandise to inspect and reject or accept such merchandise. In any event, acceptance will be deemed to have occurred no later than thirty (30) days after shipment.

Merchandise sold shall remain the property of SELLER and shall remain personal property until fully paid for in cash, and PURCHASER agrees to perform all acts that may be necessary to perfect and assure retention of title to such merchandise by SELLER. Risk of loss of the merchandise, or any part of the merchandise, shall pass to PURCHASER upon delivery of such merchandise or part at the designated delivery (F.O.B.) point.

Terms of payment shall be subject to approval of SELLER'S Credit Department and in case of doubt arising at any time as to PURCHASER'S financial responsibility, SELLER may require payment in advance, or production may be stopped and shipments suspended until satisfactory assurances are received. SELLER shall be under no obligation to make any shipment when PURCHASER is in default hereunder or under any other agreement between SELLER and PURCHASER.

Prices of all goods are those applicable on date of shipment and to PURCHASER. All prices contained herein are the best current estimate of SELLER and are subject to change without notice.

Unless otherwise specified by SELLER, payment terms are net thirty (30) days from the date of invoice. Payments will be credited to PURCHASER'S account when the funds paid are available to SELLER without any restriction related to the collectability of funds received from PURCHASER. If payments are not made when due, PURCHASER shall pay, in addition to the overdue payment, a late charge equal to the lesser of 1.5% per month or the highest applicable rate allowed by law on all such overdue amounts.

The goods sold hereunder are warranted to be free from material defect in material and workmanship for a period of thirty (30) days following shipment of such goods. ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTY THAT THE GOODS ARE MERCHANTABILITY OR FIT FOR A PARTICULAR PURPOSE ARE HEREBY EXCLUDED. Defective goods may be returned to SELLER after inspection by SELLER and upon receipt of definite instruction from SELLER.

- Tube carton size - 14" x 14" x 73"

ARMACELL LLC
7600 Oakwood Street Extension
Mebane, NC 27302
TEL. 1 800 866-5638 or 919 304-3846
FAX. 919 304-3847
E-MAIL info.us@armacell.com
INTERNET www.armacell.us

055-002-05-11-NA-NA

Goods so returned and found to be defective will be replaced or repaired without charge but SELLER shall not be liable to PURCHASER or any other person for loss or damage directly or indirectly arising from the use of the goods, from breach of any warranty, or from any other cause, the exclusive remedy against the SELLER being to require replacement or repair of defective goods. Every claim on account of defective goods, short count, or for any other cause, shall be deemed waived by PURCHASER unless made in writing within thirty (30) days from the date of shipment of goods to which such claim relates.

SELLER, its contractors and suppliers of any tier, shall not be liable in contract, in tort (including negligence and strict liability) or otherwise for damage or loss of other property or equipment, loss of profits or revenue, loss of use of equipment, cost of capital, claims of customers of PURCHASER, or for any special, indirect, exemplary, punitive, incidental or consequential damages whatsoever.

The remedies of PURCHASER set forth herein are exclusive and the total cumulative liability of SELLER with respect to this contract or anything done in connection therewith, such as the performance or breach thereof, or from the manufacture, sale, delivery, resale or use of any merchandise covered by or furnished under the contract, whether in contract, in tort (including negligence and strict liability) or otherwise, shall not exceed the price of the merchandise or part on which such liability is based.

In the event PURCHASER transfers to a third party any merchandise supplied hereunder or any right or interest therein, PURCHASER agrees to indemnify, defend and hold SELLER harmless from any and all liability to such transferee or any subsequent transferee in excess of what SELLER'S liability would have been if such transferee had been bound by these Conditions of Sale in the same manner as PURCHASER.

Sales hereunder are subject to the condition that the PURCHASER pay the SELLER the amount which SELLER is required to pay on account of any excise, manufacturer's payroll, value-added, use, or sales taxes or charges which may be established or levied by any sales taxes or charges which may be established or levied by any governmental authority (domestic or foreign) upon the merchandise sold hereunder or any part thereof, or the manufacture, use, sale, or delivery thereof, or upon the materials entering into the manufacture thereof, insofar as the same may be applicable to the merchandise sold hereunder or the manufacture, use, sale, or delivery thereof.

Delay or failure of SELLER to perform any contract in accordance with the terms shall be excused by (a) sabotage, fire flood, differences with workmen, riot, insurrection, war, act of any governmental authority, priorities granted at the request or for the benefit, directly or indirectly, of any government or agency thereof, shortage of raw material, inability to meet current sales requirements, act of God, act of PURCHASER, or (b) any causes beyond the reasonable control of SELLER. Any of the foregoing conditions resulting in delay or failure to perform any contract shall excuse such delay or failure whether the condition exists now or arises hereafter. In case of such delay or failure to perform for any of the above causes which continue, for more than thirty (30) days, the date of delivery or time for completion will be extended by a period of time necessary to overcome the effect of such delay, or either party may cancel the contract upon notice in writing given to the other.

These Conditions of Sale shall be interpreted and construed in accordance with the laws of the state of North Carolina, without regard to conflicts-of-law rules of such state. The parties expressly exclude the applicability of the United Nations Convention on Contracts for the International Sales of Goods. Any action or proceeding arising out of or related to this Agreement shall be brought only in a federal or state court located in Alamance County, North Carolina, and the parties hereby consent to such venue and the jurisdiction of such courts over the subject matter of such proceeding and themselves.

© 2011 Armacell LLC

all information is subject to change without notice