

### Safety data sheet according to 1907/2006/EC, Article 31

Printing date 18.07.2018

Version number 43

Revision: 27.06.2018

#### SECTION 1: Identification of the substance/mixture and of the company/undertaking

##### 1.1 Product identifier

Product name: **Iron HR**

Catalog number: 00515381, (4)515380BT, (4)515381BT, 515383(0), 00515389BT

##### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Application of the substance / the preparation: Reagent for water analysis

##### 1.3 Details of the supplier of the safety data sheet

##### Supplier:

Tintometer GmbH  
Schleefstraße 8-12  
44287 Dortmund  
Made in Germany  
www.lovibond.com

phone: +49 231 94510-0  
e-mail: sales@tintometer.de

Tintometer GmbH  
Division AQUALYTIC®  
Schleefstr. 12  
44287 Dortmund  
Made in Germany  
www.aqualytic.de

phone: +49 231 94510-755  
e-mail: sales@aqualytic.de

The Tintometer Limited  
Lovibond® House  
Sun Rise Way  
Amesbury  
Wiltshire SP4 7GR  
United Kingdom

phone : +44 1980 664800  
e-mail: SDS@tintometer.com

##### Informing department:

e-mail: sds@tintometer.de  
Product Safety Department

##### 1.4 Emergency telephone number:

+44 1235 239670  
Languages: English

#### SECTION 2: Hazards identification

##### 2.1 Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008



GHS07

Acute Tox. 4 H302 Harmful if swallowed.

Eye Irrit. 2 H319 Causes serious eye irritation.

Skin Sens. 1 H317 May cause an allergic skin reaction.

STOT SE 3 H335 May cause respiratory irritation.

##### 2.2 Label elements

Labelling according to Regulation (EC) No 1272/2008 The product is classified and labelled according to the CLP regulation.

(Contd. on page 2)

GB

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 18.07.2018

Version number 43

Revision: 27.06.2018

**Product name: Iron HR**

(Contd. of page 1)

**Hazard pictograms**

GHS07

**Signal word** Warning**Hazard-determining components of labelling:**

ammonium chloride  
calcium thioglycolate trihydrate

**Hazard statements**

H302 Harmful if swallowed.  
H319 Causes serious eye irritation.  
H317 May cause an allergic skin reaction.  
H335 May cause respiratory irritation.

**Precautionary statements**

P261 Avoid breathing dust.  
P280 Wear protective gloves / eye protection.  
P301+P330+P331 IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.  
P302+P352 IF ON SKIN: Wash with plenty of water.  
P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.  
P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

**2.3 Other hazards** CAS 65208-41-5: Danger by skin resorption.**Results of PBT and vPvB assessment**

This mixture does not contain any substances that are assessed to be persistent, bioaccumulative and toxic (PBT) or very persistent and very bioaccumulative (vPvB), according to the criteria given in Annex XIII of Regulation (EC) No. 1907/2006.

## SECTION 3: Composition/information on ingredients

**3.2 Mixtures****Description:** Mixture of organic and inorganic compounds**Dangerous components:**

CAS: 12125-02-9 EINECS: 235-186-4 Index No: 017-014-00-8 Reg.nr.: 01-2119487950-27-XXXX	ammonium chloride ⚠ Acute Tox. 4, H302; Eye Irrit. 2, H319	30-40%
CAS: 65208-41-5 EINECS: 249-881-5	calcium thioglycolate trihydrate ⚠ Met. Corr. 1, H290; ⚠ Acute Tox. 4, H302; Eye Irrit. 2, H319; Skin Sens. 1, H317; STOT SE 3, H335	20-<25%

**Additional information** For the wording of the listed hazard phrases refer to section 16.

## SECTION 4: First aid measures

**4.1 Description of first aid measures****General information** Instantly remove any clothing soiled by the product.**After inhalation** Supply fresh air; consult doctor in case of symptoms.**After skin contact**

Instantly rinse with water.  
If skin irritation continues, consult a doctor.

**After eye contact** Rinse opened eye for several minutes (at least 15 min) under running water. Then consult doctor.**After swallowing**

Rinse out mouth and then drink 1-2 glasses of water.  
Seek medical treatment.

**4.2 Most important symptoms and effects, both acute and delayed:**

irritations  
allergic reactions  
after inhalation:  
coughing  
breathing difficulty

(Contd. on page 3)

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 18.07.2018

Version number 43

Revision: 27.06.2018

**Product name: Iron HR**

(Contd. of page 2)

mucous membrane irritation

after swallowing:

sickness

vomiting

headache

thirst

after swallowing of large amounts:

cramps

drop in blood pressure

narcotic conditions

CNS disorders

respiratory paralysis

• **Danger** risk of skin sensitization• **4.3 Indication of any immediate medical attention and special treatment needed:** No further relevant information available.

### SECTION 5: Firefighting measures

#### • 5.1 Extinguishing media

• **Suitable extinguishing agents** Use fire fighting measures that suit the environment.

#### • 5.2 Special hazards arising from the substance or mixture

The product is not combustible.

Formation of toxic gases is possible during heating or in case of fire.

Can be released in case of fire:

Hydrogen chloride (HCl)

Sulphur oxides (SO<sub>x</sub>)Nitrogen oxides (NO<sub>x</sub>)Ammonia (NH<sub>3</sub>)

hydrogen sulfide

#### • 5.3 Advice for firefighters

##### • Protective equipment:

Wear self-contained breathing apparatus.

Wear full protective suit.

##### • Additional information

Collect contaminated fire fighting water separately. It must not enter drains.

Dispose of fire debris and contaminated fire fighting water in accordance with official regulations.

Ambient fire may liberate hazardous vapours.

### SECTION 6: Accidental release measures

#### • 6.1 Personal precautions, protective equipment and emergency procedures

##### • Advice for non-emergency personnel:

Wear protective equipment. Keep unprotected persons away.

Ensure adequate ventilation

Avoid inhalation of dust.

##### • Advice for emergency responders: Protective equipment: see section 8

#### • 6.2 Environmental precautions: Do not allow product to reach sewage system or water bodies.

#### • 6.3 Methods and material for containment and cleaning up:

Ensure adequate ventilation.

Collect mechanically.

Dispose of contaminated material as waste according to item 13.

#### • 6.4 Reference to other sections

See Section 8 for information on personal protection equipment.

See Section 13 for information on disposal.

### SECTION 7: Handling and storage

#### • 7.1 Precautions for safe handling

• **Advice on safe handling:** No special precautions necessary if used correctly.

##### • Hygiene measures:

Do not inhale dust / smoke / mist.

Avoid contact with the skin.

Avoid contact with the eyes.

(Contd. on page 4)

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 18.07.2018

Version number 43

Revision: 27.06.2018

**Product name: Iron HR**

(Contd. of page 3)

Take off immediately all contaminated clothing.  
Wash hands during breaks and at the end of the work.  
Do not eat, drink or smoke when using this product.

• **7.2 Conditions for safe storage, including any incompatibilities**

• **Storage**

• **Requirements to be met by storerooms and containers:**

Store in cool location.  
Store only in the original container.  
Unsuitable material for container: aluminium.  
Unsuitable material for container: metals, metal alloys

• **Information about storage in one common storage facility:** Do not store together with alkalis (caustic solutions).

• **Further information about storage conditions:**

Store in cool, dry conditions in well sealed containers.  
Protect from heat and direct sunlight.  
Protect from the effects of light.  
Store under dry conditions.  
Protect from humidity and keep away from water.  
This product is hygroscopic.

• **Recommended storage temperature:** 20°C +/- 5°C

• **7.3 Specific end use(s)** No further relevant information available.

## SECTION 8: Exposure controls/personal protection

• **8.1 Control parameters**

• **Components with limit values that require monitoring at the workplace:**

**CAS: 12125-02-9 ammonium chloride**

WEL (Great Britain)	Short-term value: 20 mg/m <sup>3</sup> Long-term value: 10 mg/m <sup>3</sup>
---------------------	---

• **Regulatory information** WEL (Great Britain): EH40/2011

• **DNELs**

Derived No Effect Level (DNEL)

**CAS: 12125-02-9 ammonium chloride**

Oral	DNEL	55.2 mg/kg (Consumer / long-term / systemic effects)
Dermal	DNEL	128.9 mg/kg (Worker / long-term / systemic effects)
		55.2 mg/kg (Consumer / long-term / systemic effects)
Inhalative	DNEL	43.97 mg/m <sup>3</sup> (Worker / long-term / systemic effects)
		9.4 mg/m <sup>3</sup> (Consumer / long-term / systemic effects)

• **Recommended monitoring procedures:**

Methods for measurement of the workplace atmosphere have to correspond to the requirements of norms DIN EN 482 and DIN EN 689.

• **PNECs**

Predicted No Effect Concentration (PNEC)

**CAS: 12125-02-9 ammonium chloride**

PNEC	13.1 mg/l (Sewage treatment plant)
	0.025 mg/l (Marine water)
	0.43 mg/l (Aquatic intermittent release)
	0.25 mg/l (Fresh water)
PNEC	50.7 mg/kg (Soil)
	0.09 mg/kg (Marine sediment)
	0.9 mg/kg (Fresh water sediment)

• **Additional information:** The lists that were valid during the compilation were used as basis.

• **8.2 Exposure controls**

• **Engineering measures:**

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.  
See item 7.

(Contd. on page 5)

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 18.07.2018

Version number 43

Revision: 27.06.2018

**Product name: Iron HR**

(Contd. of page 4)

- **Personal protective equipment**
- **Breathing equipment:** Use breathing protection against the effects of fumes/dust/aerosol.
- **Recommended filter device for short term use:** Filter P2
- **Protection of hands:**  
Protective gloves.  
Preventive skin protection by use of skin-protecting agents is recommended.  
After use of gloves apply skin-cleaning agents and skin cosmetics.
- **Material of gloves**  
nitrile rubber, NBR  
Recommended thickness of the material:  $\geq 0.11$  mm
- **Penetration time of glove material**  
Value for the permeation: Level = 1 ( < 10 min )  
The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye protection:** Safety glasses
- **Body protection:** Protective work clothing.
- **Limitation and supervision of exposure into the environment:** Do not allow product to reach sewage system or water bodies.

### SECTION 9: Physical and chemical properties

· <b>9.1 Information on basic physical and chemical properties</b>	
· <b>Appearance:</b>	
Form / Physical state:	Tablets
Colour:	White
· <b>Odour:</b>	Unpleasant
· <b>Odour threshold:</b>	Not determined.
· <b>pH-value (9 g/l) at 20°C:</b>	8.5
· <b>Melting point/Freezing point:</b>	Not determined
· <b>Initial boiling point and boiling range:</b>	Not determined
· <b>Flash point:</b>	Not applicable
· <b>Flammability (solid, gas):</b>	The product is not combustible.
· <b>Ignition temperature:</b>	> 400°C
· <b>Decomposition temperature:</b>	Not determined.
· <b>Auto-ignition temperature:</b>	Product is not self-igniting.
· <b>Explosive properties:</b>	Product is not explosive.
· <b>Flammability or explosive limits:</b>	
Lower:	Not applicable
Upper:	Not applicable
· <b>Oxidising properties:</b>	none
· <b>Vapour pressure:</b>	Not applicable.
· <b>Density:</b>	Not determined
· <b>Relative density:</b>	Not determined.
· <b>Vapour density:</b>	Not applicable.
· <b>Evaporation rate:</b>	Not applicable.
· <b>Solubility(ies):</b>	
Water:	Soluble
· <b>Partition coefficient: n-octanol/water:</b>	Not applicable.
· <b>Viscosity:</b>	Not applicable.
· <b>Solvent content:</b>	
Organic solvents:	0.0 %
Solids content:	100.0 %
· <b>9.2 Other information</b>	No further relevant information available.

GB  
(Contd. on page 6)

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 18.07.2018

Version number 43

Revision: 27.06.2018

Product name: Iron HR

(Contd. of page 5)

### SECTION 10: Stability and reactivity

- **10.1 Reactivity** see section 10.3
- **10.2 Chemical stability** Stable at ambient temperature (room temperature).
- **10.3 Possibility of hazardous reactions**  
 Reacts with acids, alkalis and oxidizing agents  
 Reacts with halogenated compounds  
 Violent reactions possible with:  
 chlorine
- **10.4 Conditions to avoid** Strong heating (decomposition)
- **10.5 Incompatible materials:**  
 metals  
 aluminium  
 copper  
 Iron
- **10.6 Hazardous decomposition products:**  
 nitrous gases  
 Hydrogen chloride (HCl)  
 hydrogen sulphide  
 Ammonia (NH<sub>3</sub>)  
 In case of fire: see section 5.

### SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity**  
 Classification according to calculation procedure:  
 Harmful if swallowed.

#### • Acute toxicity estimate (ATE<sub>(MIX)</sub>) - Calculation method:

Oral	CLP ATE <sub>(MIX)</sub>	1102 mg/kg (.)
------	--------------------------	----------------

#### • LD/LC50 values that are relevant for classification:

##### CAS: 12125-02-9 ammonium chloride

Oral	LD50	1410 mg/kg (rat) (OECD 1410) (Merck)
------	------	---

##### CAS: 65208-41-5 calcium thioglycolate trihydrate

Oral	LD50	352 mg/kg (rat) (Merck)
------	------	----------------------------

- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation** Causes serious eye irritation.

#### • Information on components:

##### CAS: 12125-02-9 ammonium chloride

Irritation of eyes	OECD 405	(rabbit: irritation)
--------------------	----------	----------------------

##### CAS: 65208-41-5 calcium thioglycolate trihydrate

Irritation of skin	OECD 404	(rabbit: slight irritation)
Irritation of eyes	OECD 405	(rabbit: irritation)

- **Respiratory or skin sensitisation**  
 May cause an allergic skin reaction.

#### • Information on components:

##### CAS: 12125-02-9 ammonium chloride

Sensitisation	OECD 406	(guinea pig: negative) (EPA OPP 81-6: Guinea pig maximisation test)
---------------	----------	---

##### CAS: 65208-41-5 calcium thioglycolate trihydrate

Sensitisation	OECD 429	positiv (mouse)
---------------	----------	-----------------

- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)** The following statements refer to the mixture:
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.

(Contd. on page 7)

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 18.07.2018

Version number 43

Revision: 27.06.2018

**Product name: Iron HR**

(Contd. of page 6)

- **STOT (specific target organ toxicity) -single exposure**  
May cause respiratory irritation.
- **STOT (specific target organ toxicity) -repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

- **Information on components:**

OECD 414: Teratogenicity testing

OECD 473: Mutagenicity testing

OECD 471, 474, 476, 487: Germ cell mutagenicity testing

**CAS: 12125-02-9 ammonium chloride**

OECD 471 (guinea pig: negative)

- **Additional toxicological information:** Other dangerous properties can not be excluded.

## SECTION 12: Ecological information

- **12.1 Toxicity**

- **Aquatic toxicity:**

**CAS: 12125-02-9 ammonium chloride**

EC50 &gt; 100 mg/l/48h (Daphnia magna)

LC50 42.91 mg/l/96h (rainbow trout)  
(Merck)

- **Other information:**

Toxic for fish:

NH<sub>4</sub><sup>+</sup> > 0.3 mg/l

- **12.2 Persistence and degradability** No further relevant information available.

- **12.3 Bioaccumulative potential**

Pow = n-octanol/wasser partition coefficient

log Pow &lt; 1 = Does not accumulate in organisms.

**CAS: 12125-02-9 ammonium chloride**

log Pow -4.37 (.)

- **12.4 Mobility in soil** No further relevant information available.

- **12.5 Results of PBT and vPvB assessment**

This mixture does not contain any substances that are assessed to be persistent, bioaccumulative and toxic (PBT) or very persistent and very bioaccumulative (vPvB), according to the criteria given in Annex XIII of Regulation (EC) No. 1907/2006.

- **12.6 Other adverse effects** Avoid transfer into the environment.

- **Water hazard:**

Do not allow product to reach ground water, water bodies or sewage system.

Danger to drinking water if even small quantities leak into soil.

## SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**

- **Recommendation**

Must not be disposed of together with household garbage. Do not allow product to reach sewage system.

Hand over to disposers of hazardous waste.

- **European waste catalogue**

16 05 06\* laboratory chemicals, consisting of or containing hazardous substances, including mixtures of laboratory chemicals

- **Uncleaned packagings:**

- **Recommendation:** Disposal must be made according to official regulations.

- **Recommended cleaning agent:** Water, if necessary with cleaning agent.

## SECTION 14: Transport information

- **14.1 UN-Number**

- **ADR, IMDG, IATA**

Void

(Contd. on page 8)

— GB —

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 18.07.2018

Version number 43

Revision: 27.06.2018

**Product name: Iron HR**

(Contd. of page 7)

· <b>14.2 UN proper shipping name</b>	
· <b>ADR</b>	Void
· <b>IMDG, IATA</b>	Void
· <b>14.3 Transport hazard class(es)</b>	
· <b>ADR, IMDG, IATA</b>	
· <b>Class</b>	Void
· <b>14.4 Packing group</b>	
· <b>ADR, IMDG, IATA</b>	Void
· <b>14.5 Environmental hazards:</b>	Not applicable.
· <b>14.6 Special precautions for user</b>	Not applicable.
· <b>14.7 Transport in bulk according to Annex II of Marpol and the IBC Code</b>	Not applicable.
· <b>Transport/Additional information:</b>	Not dangerous according to the above specifications.

### SECTION 15: Regulatory information

#### · 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

##### · Regulation (EC) No 1005/2009 on substances that deplete the ozone layer:

None of the ingredients is listed.

##### · Directive 2012/18/EU (SEVESO III):

· **Named dangerous substances - ANNEX I** None of the ingredients is listed.· **REGULATION (EC) No 1907/2006 ANNEX XVII** Conditions of restriction: 65

##### · Information about limitation of use:

Observe employment restrictions for pregnant and nursing mothers according to the 'mother protection guideline' (92/85/EEC).  
Employment restrictions concerning young persons must be observed.

· **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

### SECTION 16: Other information

These data are based on our present knowledge. However, they shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

#### · Relevant phrases

H290 May be corrosive to metals.

H302 Harmful if swallowed.

H317 May cause an allergic skin reaction.

H319 Causes serious eye irritation.

H335 May cause respiratory irritation.

· **Training hints** Provide adequate information, instruction and training for operators.

#### · Abbreviations and acronyms:

OECD: Organisation for Economic Co-operation and Development

STOT: specific target organ toxicity

SE: single exposure

RE: repeated exposure

EC50: half maximal effective concentration

IC50: half maximal inhibitory concentration

NOEL or NOEC: No Observed Effect Level or Concentration

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

DNEL: Derived No-Effect Level (REACH)

PNEC: Predicted No-Effect Concentration (REACH)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

(Contd. on page 9)



# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 18.07.2018

Version number 43

Revision: 27.06.2018

---

**Product name: Iron HR**

---

(Contd. of page 8)

PBT: Persistent, Bioaccumulative and Toxic  
vPvB: very Persistent and very Bioaccumulative  
Met. Corr.1: Corrosive to metals – Category 1  
Acute Tox. 4: Acute toxicity – Category 4  
Eye Irrit. 2: Serious eye damage/eye irritation – Category 2  
Skin Sens. 1: Skin sensitisation – Category 1  
STOT SE 3: Specific target organ toxicity (single exposure) – Category 3

• **Sources** Data arise from safety data sheets, reference works and literature.

---

GB