

Steel Fire Sprinkler Pipe





Wheatland Tube Fire Sprinkler Products

Wheatland Tube began producing steel fire sprinkler pipe in 1931, and today offers the most complete line of products in the industry. Engineers and contractors across the continent depend on us for steel fire sprinkler pipe and a number of proprietary products always in stock and ready to deliver.

100% Compatibility

We guarantee our steel pipe is 100% compatible with fire protection systems that use only steel pipe. Why risk incompatibility? Wheatland's complete line of steel sprinkler pipe makes design easy and brings you peace of mind.*

Accurate and Efficient

Our products help you work safer and smarter — not harder. With our extensive in-house capabilities, we offer the shortest production cycle times in the industry, and we deliver to you accurately and on time, every time.

*Wheatland Tube has never warranted compatibility between its steel pipe products and CPVC products.

Green and Sustainable

Our steel fire sprinkler pipe contains recycled steel and provides decades of reliable service. At the end of its life, the steel may be almost fully recycled, supporting your green policies.

Zekelman Industries

Wheatland Tube is a division of Zekelman Industries, the largest independent manufacturer of steel hollow structural sections (HSS) and steel pipe in North America. We leverage our 100-plus years of pipe and tube manufacturing experience and expertise to produce 2 million tons of pipe and tube annually. Backed by Zekelman Industries, you can count on Wheatland for **strength, innovation and service** — bringing exceptional value to your business.

Schedule 10 and Schedule 40



Proprietary mill coating ensures clean, corrosionresistant surface

> Outperforms and outlasts standard lacquer-coated pipe

Easily painted, without special preparation

> Available with hot-dip galvanizing

Also available in black

High quality, high performance

Wheatland's Schedule 10 and Schedule 40 steel fire sprinkler pipe are subjected to the toughest possible testing to ensure the highest possible quality – not to mention reliable, long-lasting performance.

TECHNICAL DATA

NPS	NOM ID	WT./FT. (LBS.)	WT./FT. H ₂ 0 FILLED	PCS./LIFT	WT./LIFT 21'	WT./ LIFT 24'	WT./LIFT 25'
1¼	1.442	1.807	2.514	61	2315	2645	2756
1½	1.682	2.087	3.049	61	2673	3055	3183
2	2.157	2.640	4.222	37	2051	2344	2442
2 1/2	2.635	3.534	5.895	30	2226	2544	2651
3	3.260	4.336	7.949	19	1730	1977	2060
4	4.260	5.619	11.789	19	2242	2562	2669
5	5.295	7.780	17.309	13	2124	2427	2529
6	6.357	9.298	23.038	10	1953	2232	2325
8	8.249	16.960	40.086	7	2493	2849	2968

SCHEDULE 10 SPECIFICATIONS

NPS	NOM OD		NOM ID		NOMINAL WALL		NOMINAL WEIGHT		UL	PIECES
	in.	mm	in.	mm	in.	mm	lbs./ft.	kg/m	CRR*	Lift
1¼	1.660	42.2	1.442	36.6	0.109	2.77	1.81	2.69	7.3	61
1½	1.900	48.3	1.682	42.7	0.109	2.77	2.09	3.11	5.8	61
2	2.375	60.3	2.157	54.8	0.109	2.77	2.64	3.93	4.7	37
21⁄2	2.875	73.0	2.635	66.9	0.120	3.05	3.53	5.26	3.5	30
3	3.500	88.9	3.260	82.8	0.120	3.05	4.34	6.46	2.6	19
4	4.500	114.3	4.260	108.2	0.120	3.05	5.62	8.37	1.6	19
5	5.563	141.3	5.295	134.5	0.134	3.40	7.78	11.58	1.5	13
6	6.625	168.3	6.357	161.5	0.134	3.40	9.30	13.85	1.0	10
8	8.625	219.1	8.249	209.5	0.188	4.78	16.96	25.26	2.1	7

* Calculated using Standard UL CRR formula, UL Fire Protection Directory, Category VIZY. The CRR is a ratio value used to measure the ability of a pipe to withstand corrosion. Threaded Schedule 40 steel pipe is used as the benchmark (value of 1.0).

WEIGHTS AND DIMENSIONS

	SCHEDULE 40							
in.	Wall Inches	Wt. Ibs./ft.	Wt./Ft. H₂O Filled					
1.315	0.133	1.68	2.055					
1.660	0.140	2.27	2.922					
1.900	0.145	2.72	3.602					
2.375	0.154	3.66	5.109					
2.875	0.203	5.80	7.871					
3.500	0.216	7.58	10.783					
4.000	0.226	9.12	_					
4.500	0.237	10.80	16.311					
5.563	0.258	14.63	23.262					
6.625	0.280	18.99	31.498					
	1.315 1.660 1.900 2.375 2.875 3.500 4.000 4.500 5.563	in. Inches 1.315 0.133 1.660 0.140 1.900 0.145 2.375 0.154 2.875 0.203 3.500 0.216 4.000 0.226 4.500 0.237 5.563 0.258	in. inches lbs./ft. 1.315 0.133 1.68 1.660 0.140 2.27 1.900 0.145 2.72 2.375 0.154 3.66 2.875 0.203 5.80 3.500 0.216 7.58 4.000 0.226 9.12 4.500 0.237 10.80 5.563 0.258 14.63					

SCHEDULE 40 SPECIFICATIONS

NPS	NOM OD		NOM ID		NOMINAL WALL		NOMINAL WEIGHT		UL	PIECES
	in.	mm	in.	mm	in.	mm	lbs./ft.	kg/m	CRR*	Lift
1	1.315	33.4	1.049	26.6	0.133	3.38	1.68	2.50	1.00	70
1¼	1.660	42.2	1.380	35.1	0.140	3.56	2.27	3.39	1.00	51
1½	1.900	48.3	1.610	40.9	0.145	3.68	2.72	4.05	1.00	44
2	2.375	60.3	2.067	52.5	0.154	3.91	3.66	5.45	1.00	30

* Calculated using Standard UL CRR formula, UL Fire Protection Directory, Category VIZY. The CRR is a ratio value used to measure the ability of a pipe to withstand corrosion. Threaded Schedule 40 steel pipe is used as the benchmark (value of 1.0).

Schedule 10 and Schedule 40 Meet or Exceed These Standards:

- ASTM A135, Type E, Grade A (Schedule 10)
- ASTM A795, Type E, Grade A (Schedule 40)
- UL and C-UL Listed

- FM Approved
- NFPA 13

Mega-Flow



ID up to 7% larger than Schedule 10 and 11% larger than Schedule 40

Saves freight, labor and installation costs

Standard hanger spacing (15')

Available in standard lengths; custom lengths can be ordered

Roll groove available from mill inventory

Proprietary mill coating provides superior primer for printing

Greater hydraulics, greater value

Wheatland's Mega-Flow is an engineered, light-wall steel sprinkler pipe that offers ID up to 7% larger than Schedule 10 and 11% larger than Schedule 40 for improved hydraulics. Mega-Flow saves freight, labor and installation costs with standard hanger spacing (15') and standard and custom lengths. With its proprietary mill coating, Mega-Flow is an excellent alternative to standard wall products so you can downsize your entire sprinkler system with the same or greater quality.

TECHNICAL DATA

NPS	NOM ID	WT./FT. (LBS.)	WT./FT. H ₂ 0 FILLED	PCS./LIFT	WT./LIFT 21'	WT./LIFT 24'	WT./LIFT 25'
1¼	1.530	1.108	1.904	61	1419	1622	1690
1½	1.740	1.556	2.586	61	1993	2278	2373
2	2.215	1.961	3.631	37	1524	1741	1814
2 1⁄2	2.707	2.504	4.998	30	1578	1803	1878
3	3.316	3.349	7.090	19	1336	1527	1591
4	4.316	4.331	10.669	19	1728	1975	2057
6	6.395	8.000	21.900	10	1680	1920	2000

SPECIFICATIONS

NPS	NOM OD	NOM ID			ULC	CRR*	MEGA	FLOW
		Mega-Flow	Schedule 10	Schedule 40	Mega-Flow	Schedule 40	Nominal wt./ft.	Pcs./Lift
1¼	1.660	1.530	1.442	1.380	1.80	1.00	1.108	61
1½	1.900	1.740	1.682	1.610	2.64	1.00	1.556	61
2	2.375	2.215	2.157	2.067	2.14	1.00	1.961	37
2 1/2	2.875	2.707	2.635	2.469	1.43	1.00	2.504	30
3	3.500	3.316	3.260	3.068	1.34	1.00	3.349	19
4	4.500	4.316	4.260	4.026	1.00	1.00	4.331	19
6	6.625	6.395	6.357	6.065	0.75	1.00	8.000	10

* Calculated using Standard UL CRR formula, UL Fire Protection Directory, Category VIZY. The CRR is a ratio value used to measure the ability of a pipe to withstand corrosion. Threaded Schedule 40 steel pipe is used as the benchmark (value of 1.0).

Mega-Flow Meets or Exceeds These Standards:

- ASTM A795, Type E, Grade A
- UL and C-UL Listed and FM Approved for use with roll grooved, swage grooved, plain-end couplings and welded joints for wet, dry preaction and deluge systems
- FM Approved for roll grooved, plain-end and welded joints for wet systems
- NFPA 13 and NFPA 14

Mega-Thread



ID 3.6% larger than Schedule 40

Saves costs in threadable applications

Superior flow characteristics

Can be joined by screwed, grooved or plain-end fittings, or welded

Threads smoothly and easily; requires no thread warning

Proprietary mill coating extends shelf life, makes painting quicker and easier

Approved for standard hanger spacing

Greater hydraulics, greater value

Wheatland's Mega-Thread is an engineered, light-wall steel sprinkler pipe that offers ID 3.6% larger than Schedule 40 for superior flow. Mega-Thread saves costs in threadable applications and can be joined by screwed, grooved or plain-end fittings, or welded. With its proprietary mill coating, Mega-Thread is an excellent Schedule 40 alternative that threads smoothly and easily so you can downsize your entire sprinkler system with the same or greater quality.

TECHNICAL DATA

NPS	NOM ID	WT./FT. (LBS.)	WT./FT. H ₂ 0 FILLED	PCS./LIFT	WT./LIFT 21'	WT./ LIFT 24'	WT./LIFT 25'
1	1.087	1.462	1.865	70	2149	2456	2559
1¼	1.416	1.989	2.674	51	2130	2435	2536
1½	1.650	2.370	3.297	44	2190	2503	2607
2	2.117	3.094	4.621	30	1949	2228	2321

SPECIFICATIONS

NPS	NOM OD	NOM ID			UL CRR*		MEGA-THREAD		
		Mega- Thread	Schedule 40	Mega- Thread	Schedule 40	L.W.T. Pipe	Nominal wt./ft.	Pcs./Lift	
1	1.315	1.087	1.049	1.00	1.00	0.61	1.462	70	
1¼	1.660	1.416	1.380	1.00	1.00	0.39	1.989	51	
1½	1.900	1.650	1.610	1.00	1.00	0.31	2.370	44	
2	2.375	2.117	2.067	1.00	1.00	0.25	3.094	30	

Calculated using Standard UL CRR formula, UL Fire Protection Directory, Category VIZY. The CRR is a ratio value used to measure the ability of a pipe to withstand corrosion. Threaded Schedule 40 steel pipe is used as the benchmark (value of 1.0).

Mega-Thread Meets or Exceeds These Standards:

- ASTM A795, Type E, Grade A
- UL and C-UL Listed and FM Approved for wet, dry and preaction sprinkler systems
- Hot-dip galvanized finish meets FM requirements for dry systems
- NFPA 13 and NFPA 14
- Rated 300 psi working pressure

GL Galvanized, Light Wall, Threadable



Ideal for exposed, open areas

Wheatland's GL steel fire sprinkler pipe is an OD galvanized, lighter-wall, threadable product. The nominal OD provides improved hydraulics—resulting in an exceptional value.

TECHNICAL DATA

NPS	NOM ID	WT./FT. (LBS.)	WT./FT. H ₂ 0 FILLED	PCS./LIFT	WT./LIFT 21'	WT./ LIFT 24'	WT./LIFT 25'
1	1.103	1.370	1.701	91	2618	2992	3117
1¼	1.448	1.761	2.365	61	2256	2578	2686
1½	1.688	2.033	2.875	61	2604	2976	3100
2	2.153	2.686	4.142	37	2087	2385	2485

Ideal for branch line use in wet, dry, preaction or deluge systems

Comparable mechanical strength to Schedule 40

Readily paintable galvanized exterior

Reduces freight and installation costs

SPECIFICATIONS

NPS	NOM ID		UL	THREADED C	GL		
	GL	Schedule 40	GL	Schedule 40	Mega- Thread	Nominal wt./ft.	Pcs./Lift
1	1.103	1.049	0.61	1.00	1.00	1.370	91
1¼	1.448	1.380	0.39	1.00	1.00	1.761	61
1½	1.688	1.610	0.31	1.00	1.00	2.033	61
2	2.153	2.067	0.25	1.00	1.00	2.686	37

* Calculated using Standard UL CRR formula, UL Fire Protection Directory, Category VIZY. The CRR is a ratio value used to measure the ability of a pipe to withstand corrosion. Threaded Schedule 40 steel pipe is used as the benchmark (value of 1.0).

nreaded Schedule 40 steel pipe is used as the benchmark (value of i.

GL Meets or Exceeds These Standards:

- ASTM A795, Type E, Grade A for fire sprinkler applications up to 300 psi working pressure
- UL and C-UL Listed and FM Approved for wet, dry, preaction and deluge sprinkler systems
- Threaded and welded fittings are approved in accordance with NFPA 13

MLT Black, Light Wall, Threadable



A smooth, customized look

Wheatland's MLT is a black-coated, light-wall engineered product, with a nominal OD and reduced wall thickness that provide improved hydraulics.

TECHNICAL DATA

NPS	NOM ID	WT./FT. (LBS.)	WT./FT. H ₂ 0 FILLED	PCS./LIFT	WT./LIFT 21'	WT./ LIFT 24'	WT./LIFT 25'
1	1.103	1.370	1.701	91	2618	2992	3117
1¼	1.448	1.761	2.365	61	2256	2578	2686
1½	1.688	2.080	2.875	61	2604	2976	3100
2	2.153	2.630	4.142	37	2087	2385	2485

Ideal for previously installed systems and expansions

Saves freight and installation costs

As mechanically strong as Schedule 40 pipe

Easily paintable for a customized look

Can be used in wet, dry, preaction and deluge systems

Can be joined with threaded couplings, roll grooved or plain-end couplings, or welded

SPECIFICATIONS

NPS	NOM ID		UL	THREADED C	RR*	MLT		
	MLT	Schedule 40	MLT	Schedule 40	Mega- Thread	Nominal wt./ft.	Pcs./Lift	
1	1.103	1.049	0.61	1.00	1.00	1.370	91	
1¼	1.448	1.380	0.39	1.00	1.00	1.761	61	
1½	1.688	1.610	0.31	1.00	1.00	2.033	61	
2	2.153	2.067	0.25	1.00	1.00	2.686	37	

* Calculated using Standard UL CRR formula, UL Fire Protection Directory, Category VIZY. The CRR is a ratio value used to measure the ability of a pipe to withstand corrosion. Threaded Schedule 40 steel pipe is used as the benchmark (value of 1.0).

MLT Meets or Exceeds These Standards:

- ASTM A795, Type E, Grade A for fire sprinkler applications up to 300 psi working pressure
- UL and C-UL Listed and FM Approved for wet, dry, preaction and deluge sprinkler systems
- Threaded and welded fittings are approved in accordance with NFPA 13



700 South Dock Street Sharon, PA 16146

800.257.8182 info@wheatland.com wheatland.com



Corporate Office 227 West Monroe Street Suite 2600 Chicago, IL 60606

312.275.1600 info@zekelman.com zekelman.com

About Wheatland Tube

Wheatland Tube, a division of Zekelman Industries, produces a wide range of steel tubular products, including standard steel pipe, galvanized mechanical tubing, fence framework, fire sprinkler pipe, electrical conduit, elbows, couplings and nipples.

For more information, contact Wheatland Tube at: 800.257.8182 or info@wheatland.com Or, visit our website at wheatland.com

Follow us on:

- twitter.com/WheatlandTube
- in linkedin.com/company/zekelman-industries
 - youtube.com/ZekelmanIndustries
 - wheatland.com/blog