



410 Stainless Steel

Blue Climaseal[™]

DESCRIPTION/SUGGESTED SPECIFICATIONS

Tapcon Anchors —

SPECIFIED FOR ANCHORAGE INTO CONCRETE, BRICK OR BLOCK



The "original masonry" anchor that cuts its own threads into concrete, brick, or block. Maximum performance is achieved because the Tapcon Anchor, the Condrive Installation Tool, and the carbide-tipped Tapcon Drill Bits are designed to work as a system. It is essential to use the Condrive tool and the correct drill bit to assure consistent anchor performance.

ADVANTAGES

- Works in all masonry base materials.
- Fast and easy—3 anchors per minute.
- No hole spotting or inserts required.
- Removable.

- Slotted hex and phillips flat head styles.
- Extended corrosion protection— Blue Climaseal[®].
- Available in 410 Stainless Steel.

Tapcon Anchors

Blue Climaseal[®] provides extended corrosion protection

Also available in 410 Stainless Steel

Hex Head style on Tapcon Anchors is available for majority of fixture anchoring needs

Phillips Flat Head style is available when flush seating is necessary in countersink applications

Advanced Threadform cuts into concrete and masonry for reduced installation torque and increased pullout performance

Lengths of Tapcon Anchors range from 1-1/4" to 4" in 3/16" and up to 6" in 1/4" diameters.

Nail-Type Point guides the anchor into the pre-drilled hole. Excellent for wood to concrete applications

Tapcon Starter Kit

Starter Kit Part Number: 7904050 Kit Contains: 1 Box HW4-114 (includes 1 drill bit) 1 Box HW4-134 (includes 1 drill bit) 1 Condrive 1000



Tapcon® is a registered trademark of Buildex, a divison of Illinois Tool Works, Inc.

Tapcon[®] Anchors

APPLICATIONS





well in block and brick. The picture shows the Condrive 1000

The Tapcon Anchor is especially well suited for window and door frames

because it performs well in block, is

available in a flat head style, and is

Many horizontal or "wall" applications are attached with Tapcon Anchor

because it is removable and works

fast to install.

Installation Kit in action. The kit makes for fast and easy change over from drill bit to driver and controls the driving torque to prevent thread stripping and head snapping in hard base materials.

APPROVAL/LISTINGS

Blue Climaseal[™]

ICC Evaluation Service, Inc. – #ESR-1671 ICC Evaluation Service, Inc. – #ESR-2202 Miami-Dade County - #07-0315.03 Florida Building Code

410 Stainless Steel

Miami-Dade County - #07-1126.10 Florida Building Code

INSTALLATION STEPS

Read instructions before using (installation)!




If there are any questions concerning proper installation, applications or appropriate use of WARNING: this product, please call our Technical Services Department at 1-800-899-7890. Failure to follow these instructions can result in serious personal injury.

- 1. Select proper fastener diameter / head style / length. a) Use selection chart to choose proper length.
- 2. Drill Hole use selection chart to determine drill bit length and depth of hole.
 - a) Choose appropriate drill of Tapcon Anchor.
 - b) Drill hole minimum ¼" deeper than Tapcon Anchor to be embedded.

Minimum anchor embedment: 1" Maximum anchor embedment: 1-3/4"

3. Drive Anchor.





Fixture Thickness—determine the fixture thickness to be anchored

Anchor Embedment—with a minimum recommended embedment of 1", the correct Tapcon anchor choice can be made. Hole depth must be a minimum 1/4" deeper than the anchor embedment to allow for displaced material

Hole Diameter—proper hole diameter is very important to insure consistent performance and maximum pullout strength. 3/16" anchors require 5/32" diameter bits, and 1/4" anchors require 3/16" diameter bits



WARNING:

Failure to wear safety glasses with side shields can result in serious personal injury. Always wear ANSI compliant eye protection (ANSI Z87.1-2003).

Using the wrong size drill bit will affect performance values and may cause failure.

Head Styles

3/16" diameter has a 1/4" slotted hex washer head (HWH) 1/4" diameter has a 5/16" slotted hex washer head (HWH)



3/16" diameter uses a #2 phillips flat head (PFH) 1/4" diameter uses a #3 phillips flat head (PFH)



SELECTION CHART

Diameter......3/16" and 1/4"

Thread Form.....Advanced Threadform Technology™ Finish.....Blue Climaseal™

3461907

Tapcon[®] Anchors with Blue Climaseal™

Point Type.....Nail

All boxes of ITW Tapcon come packaged with matching carbide-tipped bit. Tapcon is packaged 100 pieces per box and 500 pieces per master carton except HW4-600 and PF4-600 (400 in master carton).

FIXTURE THICKNESS INCHES	RECOMMENDED TAPCON LENGTH In. (mm)	PART NO. 3/16" HEX HEAD	PART NO. 1/4" Hex Head	PART NO. 3/16" Flat head	PART NO. 1/4" Flat head	BIT LENGTH In. (mm)	STRAIGHT SHANK BITS FOR 3/16" TAPCON PART NO.	STRAIGHT SHANK Bits for 1/4" Tapcon Part No.
0" - 1/4"	1-1/4 (31.8)	HW3-114	HW4-114	PF3-114	PF4-114	3-1/2 (88.9)	7900814	7901014
1/4″ - 3/4″	1-3/4 (44.5)	HW3-134	HW4-134	PF3-134	PF4-134	3-1/2 (88.9)	7900814	7901014
3/4" - 1-1/4"	2-1/4 (57.2)	HW3-214	HW4-214	PF3-214	PF4-214	4-1/2 (114.3)	7900818	7901018
1-1/4 "- 1-3/4"	2-3/4 (69.9)	HW3-234	HW4-234	PF3-234	PF4-234	4-1/2 (114.3)	7900818	7901018
1-3/4″ - 2-1/4″	3-1/4 (82.6)	HW3-314	HW4-314	PF3-314	PF4-314	5-1/2 (139.7)	7900822	7901022
2-1/4" - 2-3/4"	3-3/4 (95.3)	HW3-334	HW4-334	PF3-334	PF4-334	5-1/2 (139.7)	7900822	7901022
2-1/2" - 3"	4 (101.6)	HW3-400	HW4-400	PF3-400	PF4-400	5-1/2 (139.7)	7900822	7901022
3-1/2" - 4"	5 (127.0)		HW4-500		PF4-500	6-1/2 (165.1)		7901026
4-1/2" - 5"	6 (152.4)		HW4-600		PF4-600	7-1/2 (190.5)		7901030

CDCONPoint TypeNailFinish410 Stainless Steel with Silver Climaseal™410 SS AnchorAll boxes of ITW Tapcon come packaged with matching carbide-tipped bit. Tapcon is packaged 100 pieces per box and 500 pieces per master carton except 3461907 (400 in master carton).								
FIXTURE RECOMMENDED PART NO. PART NO. PART NO. BIT STRAIGHT SHANK STRAIGHT SHANK THICKNESS TAPCON LENGTH 1/4" 3/16" 1/4" LENGTH BITS FOR BITS FOR INCHES In. (mm) HEX HEAD FLAT HEAD FLAT HEAD In. (mm) 1/4" TAPCON	PART NUMBER							
PARI NU. PARI NU.	790059	7						
0" - 1/4" 1-1/4 (31.8) SHW4-114 3434907 SPF4-114 3-1/2 (88.9) 7900814 7901014								
1/4" - 3/4" 1-3/4 (44.5) SHW4-134 3418907 SPF4-134 3-1/2 (88.9) 7900814 7901014	7901060	5						
3/4" - 1-1/4" 2-1/4 (57.2) SHW4-214 3419907 SPF4-214 4-1/2 (114.3) 7900818 7901018	7001050	-						
1-1/4 "- 1-3/4" 2-3/4 (69.9) SHW4-234 3420907 SPF4-234 4-1/2 (114.3) 7900818 7901018	7901059	'						
1-3/4" - 2-1/4" 3-1/4 (82.6) SHW4-314 3421907 SPF4-314 5-1/2 (139.7) 7900822 7901022	L							
2-1/4" - 2-3/4" 3-3/4 (95.3) SHW4-334 SHW4-334 SPF4-334 5-1/2 (139.7) 7900822 7901022								
2-1/2" - 3" 4 (101.6) 3459907 5-1/2 (139.7) 3100910								
3-1/2" - 4" 5 (127.0) 3460907 6-1/2 (165.1) 3102910								

Tapcon SDS Bits				
PART NUMBER	DESCRIPTION			
790059	7" (SDS Rotohammer Bits for use with 3/16" Tapcon)			
7901060	5" (SDS Rotohammer Bits for use with 1/4" Tapcon)			
7901059	7" (SDS Rotohammer Bits for use with 1/4" Tapcon)			

PERFORMANCE TABLE

6 (152.4)

3461907

4-1/2" - 5"

		CON [®] nchors	Ultimate	Tension	and Shea	ır Values	(Lbs/kN)	in Concr	ete
ANCHOR	MIN. DEPTH OF	f'c = 2000 PSI (13.8 MPa)		f'c = 3000 PSI (20.7 MPa)		f'c = 4000 PSI (27.6 MPa)		f'c = 5000 PSI (34.5 MPa)	
DIA. In. (mm)	EMBEDMENT In. (mm)	TENSION Lbs. (kN)	SHEAR Lbs. (kN)	TENSION Lbs. (kN)	SHEAR Lbs. (kN)	TENSION Lbs. (kN)	SHEAR Lbs. (kN)	TENSION Lbs. (kN)	SHEAR Lbs. (kN)
3/16 (4.8)	1 (25.4)	600 (2.7)	720 (3.2)	625 (2.8)	720 (3.2)	650 (2.9)	720 (3.2)	800 (3.6)	860 (3.8)
	1-1/4 (31.8)	845 (3.7)	720 (3.2)	858 (3.8)	720 (3.2)	870 (3.9)	720 (3.2)	1,010 (4.5)	860 (3.8)
	1-1/2 (38.1)	1,090 (4.8)	860 (3.8)	1,090 (4.8)	860 (3.8)	1,090 (4.8)	860 (3.8)	1,220 (5.4)	860 (3.8)
	1-3/4 (44.5)	1,450 (6.5)	870 (3.9)	1,455 (6.5)	870 (3.9)	1,460 (6.5)	990 (4.4)	1,730 (7.7)	990 (4.4)
1/4 (6.4)	1 (25.4)	750 (3.3)	900 (4.0)	775 (3.4)	900 (4.0)	800 (3.6)	1,360 (6.1)	950 (4.2)	1,440 (6.4)
	1-1/4 (31.8)	1,050 (4.7)	900 (4.0)	1,160 (5.2)	900 (4.0)	1,270 (5.6)	1,360 (6.1)	1,515 (6.7)	1,440 (6.4)
	1-1/2 (38.1)	1,380 (6.1)	1,200 (5.3)	1,600 (7.2)	1,200 (5.3)	1,820 (8.1)	1,380 (6.1)	2,170 (9.7)	1,670 (7.4)
	1-3/4 (44.5)	2,020 (9.0)	1,670 (7.4)	2,200 (9.8)	1,670 (7.4)	2,380 (10.6)	1,670 (7.4)	2,770 (12.3)	1,670 (7.4)

7-1/2 (190.5)

Safe working loads for single installation under static loading should not exceed 25% of the ultimate load capacity.

PERFORMANCE TABLES

Tapcon®Ultimate Tension and ShearAnchorsValues (Lbs/kN) in Hollow Block

ANCHOR	ANCHOR	LIGHTWEI	GHT BLOCK	MEDIUM WEIGHT BLOCK			
DIA. In. (mm)	EMBEDMENT In. (mm)	TENSION Lbs. (kN)	SHEAR Lbs. (kN)	TENSION Lbs. (kN)	SHEAR Lbs. (kN)		
3/16 (4.8)	1 (25.4)	220 (1.0)	400 (1.8)	340 (1.5)	730 (3.2)		
1/4 (6.4)	1 (25.4)	250 (1.1)	620 (2.8)	500 (2.2)	1,000 (4.4)		

Safe working loads for single installation under static loading should not exceed 25% of the ultimate load capacity.

Tapcon

NOTE: 3/16" Tapcon requires 5/32" bit, 1/4" Tapcon requires 3/16" bit.

Allowable Edge and Spacing Distances

PARAMETER	ANCHOR	1	IORMAL WEIGHT CONCRET	E	CONCRETE MASONRY UNITS (CMU)			
	DIA. In. (mm)	FULL CAPACITY (Critical Distance Inches)	REDUCED CAPACITY (Minimal Distance Inches)	LOAD REDUCTION Factor	FULL CAPACITY (Critical Distance Inches)	REDUCED CAPACITY (Minimal Distance Inches)	LOAD REDUCTION Factor	
Spacing Between	3/16	3	1-1/2	0.73	3	1-1/2	1.00	
Anchors - Tension	1/4	4	2	0.66	4	2	0.84	
Spacing Between	3/16	3	1-1/2	0.83	3	1-1/2	1.00	
Anchors - Shear	1/4	4	2	0.82	4	2	0.81	
Edge Distance -	3/16	1-7/8	1	0.83	4	2	0.91	
Tension	1/4	2-1/2	1-1/4	0.82	4	2	0.88	
Edge Distance	3/16	2-1/4	1-1/8	0.70	4	2	0.93	
-Shear	1/4	3	1-1/2	0.59	4	2	0.80	

For SI: 1 inch = 25.4 mm


Tapcon[®] Condrive 1000 Tool Kit

DESCRIPTION/SUGGESTED SPECIFICATIONS Condrive 1000 Installation Tool— SPECIFIED FOR ANCHORAGE INTO CONCRETE, BRICK OR BLOCK

The key to Tapcon's fast and easy installation is the multi-purpose Condrive Installation Tool. The drive sleeve, along with the hex head and phillips sockets provide the installer with the flexibility necessary for the complete variety of Tapcon applications (tool does not include drill bit).

Condrive[®] 1000 - A multi-purpose tool designed for installation of Tapcon hex head and Phillips flat head anchors up to 3-3/4" long. If driving hex head Tapcon, driver will automatically disengage. The Condrive 1000 has a reusable plastic case.

Condrive Tools are designed to specifically install Tapcon Anchors and to fit standard hammer drills.





Part No. C1000 (Does not include drill bit)

ADVANTAGES

- Fast change from drilling to driving
- Eliminates need to change out chucks and bits
- Eliminates need for two tools
- Special nut driver is recessed for torque control to reduce head breakage



© 2010 Illinois Tool Works. Tapcon products are registered trademarks of ITW Buildex and Illinois Tool Works Inc. Red Head is a registered trademark of Illinois Tool Works Inc. RH BC/4105S 05/10

APPLICATIONS



The picture shows the Condrive 1000 Installation Kit in action. The kit makes for fast and easy change over from drill bit to driver and controls the driving torque to prevent thread stripping and head snapping in hard base materials.

Condrive 1000 Spare Parts

PART NO.	DESCRIPTION	QTY/WT
(A) 7901001	Drill Adapter	1/.06
(B) 7901002	Sleeve	1/.01
7901003	Black Band	1/.02
7901004	5/32" Ball Bearing	1/.02
(C) 7901006	3/16" Socket	1/.04
(D) 7901007	1/4″ Socket	1/.05
7901008	#2 Phillips bit for 3/16" anchor	1/.10
7901009	#3 Phillips bit for 1/4" anchor	1/.12
(E) 7901010	Phillips Socket	1/.44
7902006	Set Screw	1/.02
7902008	7902008 1/16" Ball Bearing	
7902010 1/8″ Hex Key		1/.10

