

5IN AND 6IN LED RETROFIT

Specifications:

Description:

The HS56 is ideal for use in both new construction as well as remodel/retrofit. Light output is comparable to that of a typical 65W incandescent downlight, providing up to 75% energy savings. The HS56 is equipped with both Edison base adaptor and quick link connector allowing easy installation in many standard incandescent recessed housings.

Construction:

- Satin White finish
- Diffused polycarbonate lens controls direct glare from the LEDs
- Easy installation with (2) friction spring clips
- Can be installed in most 6" and 5" recessed housings
- Dimmable to 10% with many dimmers
- Lumen output and distribution comparable to a 65W incandescent lamp
- Suitable for use in IC or NON-IC Applications
- · Provided with quick link for use with E26 Edison Base adapter
- Meets California Title 24 JA8 2016

Performance:

Input Power	10.1W
Input Voltage	120V
Input Frequency	60Hz
Lumens/LPW	763/75 (LM-79)
ССТ	3000K
CRI	90
Life	50,000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Min. Start Temp	-30° C
Max. Operating Temp	30° C
Warranty	5 year warranty
Labels	cCSAus Wet location listed
	ENERGY STAR [®] qualified
	Meets California Title 24 - JA8 - 2016

Project:

Fixture Type: Location:

Contact:


HS56-WH-30K9

Images:



Dimensions:

Diameter: 7.4" Height: 3.4"





5IN AND 6IN LED RETROFIT

Photometrics:

HS56-WH-30K9

ELECTRICAL DATA	HS56-WH-30K9					
Input Voltage	120V					
Input Frequency	60Hz					
Input Current	0.09A					
Input Power	10.1W					
Power Factor	>0.90					
THD	<20%					
EMI Filtering	FCC Title 47, Part 15, Class B					
Operating Temperature	-30° C to 30° C					
Dimming	Yes*					
Over-voltage, over-current, short-circuit protected						
*See Dimming Notes for more information						

HS56-WH-30K9				ZONAL LUMEN SUMMARY		
LED Light Engine: 3000K 94 CRI				ZONE	LUMENS	%LUMINAIRE
System Wattage: 10.1 Fixture delivered lumens: 763				0-30	281	36.9%
Fixture Efficacy: 75.5				0-40	447	58.5%
Spacing Criteria: 1.2				0-60	688	90.1%
				0-90	763	100.0%
		CANDELA		90-180	0	0%
90°		DISTRIBUTION		0-180	763	100.0%
	DEG	CANDELA	LUMENS		1 705	1
75°	0	375				
	5	370	35			
130	15	354	100			
60°	25	319	147			
	35	266	165			
	45	187	144			
260	55	108	97			
45°	65	50	51			
	75	18	20			
	-		_			

4

0

5

Test No. 16.01512

15°

390

Tested at 25°C Ambient in accordance to IESNA LM-79-2008

30°

85

90



5IN AND 6IN LED RETROFIT



HS56-WH-30K9

Dimming Notes:

HS56 is designed to be compatible with many Triac/Forward Phase controls. LED rated dimmer controls may offer favorable dimming performance.

The following is a partial list of known compatible dimmer controls.

Triac/Forward Phase Controls

Lutron AYCL–153P
Lutron TGCL–153P
Leviton 6681
Leviton 6672
Leviton 6674

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.