





World's first bullet-design Machinist Vise is manufactured. Witon creates a name for themselves in the market place.



Wilton expands into clamping products With new and innovative ideas.

1941

1950

1960

1970



Wilton supports war efforts in WW2 to support our us troops overseas.



Wilton is the brand of choice in the Automotive boom of the 50's.



Pow-r-arms are introduced into the Wilton product line and allowed assembly-line workers hands-free production.



## HOLDING STRONG SINCE 1941

It was 75 years ago when Wilton® designed the first Bullet-Design machinist vise and created the groundwork of quality craftsmanship from which the Wilton brand would rise. As it was in 1941, so it remains now. The same high level of workmanship is in every tool that bares the name Wilton®. And the rest is truly history.....



The Invention of the patented replaceable Perma-Pads allows users to replace the the pad instead of the entire clamp.



For the jobs that demand function, strength and mobilty Wilton introduces the innovative ATV All-terrain Vise

1980

1990

2000

2014



The new Tradesman Vise sets the new standard of quality and durability in vises.



B.A.S.H<sup>®</sup> Unbreakable<sup>®</sup> Handle Sledge Hammers are introduced as the world's most durable sledge hammer.

# WILTON®: A CONSUMER FOCUSED BRAND

WILTONTOOLS.COM

WIN HOLDING STRONG SING



## **CHALLENGER VAN TOUR**

With our consumers in mind, we set out on a national tour to reach as many as possible. The Challenger Van Tour launched in 2011 and has made hundreds of stops throughout industrial America.

Aboard the Challenger Van you will find an assortment of our most popular Wilton products, new products, videos, demonstrations, as well as free giveaways.

## FOLLOW THE TOUR AND FIND UPCOMING APPEARANCES AT: CHALLENGERVANTOUR.COM







## FIND WILTON ONLINE

Find Wilton on these social media sites to get the latest product news, share your projects and connect with others.



LIKE US ON FACEBOOK www.facebook.com/WiltonTools



FOLLOW US ON TWITTER @Wilton\_Tools



CONNECT WITH US ON YOUTUBE www.youtube.com/WiltonTools

# WILTON®: LIFETIME WARRANTY



We are confident of every Wilton® tool we manufacture. To prove it, we back every product that bears the Wilton® name with a Lifetime Warranty. This includes everything from Vises to Clamps, Pipe Wrenches to B.A.S.H® Hammers. We hope you are as proud and confident of our equipment as we are.

The Wilton® lifetime warranty is for the product's lifetime with no end date. This warranty covers manufacturer's defect only and does not cover misuse, abuse, accidents, negligence, wear and tear, improper repair or alterations, etc. For more information please visit wiltontools.com



WILTONTOOLS.COM — 5

# NEW PRODUCTS



## 5" ATV ALL-TERRAIN VISE

The innovative ATV All-Terrain Vise line is expanding and is now available in a 5" jaw width. The 5" ATV fits a standard 2" hitch - hitch pin included. It features the same patented 360 degree locking handle, drive tight set screws and carrying handle in a smaller format. Now it's even easier to get locked, loaded and ready to go with the Wilton ATV.

**SEE PAGE 33** 



## HEAVY DUTY CLASSIC F-CLAMPS

At Wilton, we know welding. As the leader in professional grade workholding equipment for 75 years, we understand the intricacies of your work. That's why we're proud to introduce Heavy Duty F-clamp to our Classic Series. This new clamp features 2660 lbs of clamping force, a heavy duty replaceable pad and replaceable parts.

**SEE PAGE 50** 



## B.A.S.H<sup>®</sup> DEAD BLOW HAMMERS

The world's most durable line of striking tools continues to expand with all new Dead Blow Hammers. These hammers are designed to help eliminate bounce back when striking hardened objects and are non-marring. The steel reinforced handle and head capsule are fully enclosed in Vulcanized Rubber for comfort and to ensure they're also non-sparking.

**SEE PAGE 76** 

# TABLE OF CONTENTS

## VISES

<b>USA Bullet Bench Vises</b>	8-15
Industrial Bench Vises	16-27
Pow-R-Arms	28-29
Truck Hitch Vise	30-33
Machine Vises	34-43

## **CLAMPS**

F-Clamps	44-53
C-Clamps	54-65
Specialty Clamps	66-67

## **HAND TOOLS**

B.A.S.H <sup>®</sup> Unbreakable	
Handle Striking Tools	<b>68-78</b>
Pipe Wrenches	79












# BULLET VISES

MADE IN AMERICA. MADE TO LAST.









The Wilton® Bullet Vise family has improved over the years, but has always maintained the same high quality and integrity since 1941. This trademarked design has proven it's superiority for 75 years. Bullet vises are proudly built in the USA.





# **BULLET VISES**

THE BULLET ADVANTAGE



THE WILTON® BULLET DESIGN



**FULLY ENCLOSED DESIGN** 



**60,000 PSI DUCTILE IRON BODY** 



**PRECISION SLIDE BAR** 



## DURABILITY

## A FULLY ENCLOSED DESIGN:

Extends the life of the vise by protecting all internal components and keeping out dust and debris. Lifetime lubricated and permanently sealed for trouble free service.

## **B** 60,000 PSI DUCTILE IRON BODY:

Virtually indestructible with 2X the strength of grey casted vises.

## **C** PRECISION SLIDE BAR

Keyed for a .003" fit, eliminating movement in the front jaw regardless of opened distance



## **FUNCTIONALITY**

## D LONGER SPINDLE NUT:

3X longer and 2X thicker, ensures a lifetime of smooth spindle movement and straight-line pull.

## E LARGER ANVIL

2X larger than the average anvil. Designed to take a beating while forming and shaping materials.

## F 4 BOLT MOUNTING PATTERN:

4 bolt pattern sturdier than industry-average 3 bolt pattern, maximizing stability during use.



LONGER SPINDLE NUT



LARGER ANVIL



4 BOLT MOUNTING PATTERN



WILTON'S WORKHORSE






LARGE ANVIL



PRECISION SLIDE BAR





### NOTE

- · The all weather vise is the same as combo pipe vise with rust inhibitive features
- Meets federal spec # GGG-V-410a, Type IV.

## **FEATURES**

#### **SELF CENTERING PIPE JAWS:**

- Hold up to 6" pipe safely and securely.
- Great for irregularly shaped objects

#### **DEEP THROAT STYLE:**

 Up to 50% added depth to meet tough job requirements requiring large capacity

- Plant Maintenance
- Oil Field Service
- Heavy Construction
- Mechanical Trades
- Steel Fabrication

Stock Model No.		Jaw Width (in.)	Maximum Opening (in.)	Throat Depth (in.)	Pipe Jaw Capacity (in.)	Net Weight (lbs.)			
COMBO PIPE AND BENCH – SWIVEL BASE									
10200	C-0	3-1/2	5	4-1/2	1/8 – 2 1/2	51			
10225	C-1	4-1/2	6	4-3/4	1/8 – 3 1/2	78			
10250	C-2	5	7	5-5/16	1/8 – 4 1/2	100			
10275	C-3	6	9	6-5/8	1/4 – 6	204			
ALL WEATHER COMBO PIPE AND BENCH – SWIVEL BASE									
10400	AW35	3-1/2	5	4-1/2	1/8 – 2 1/2	51			
10500	AW45	4-1/2	6	4-3/4	1/8 – 3 1/2	79			

Stock No.	Replacement Jaw Insert No.	Replacement Pipe Jaw Insert No.		
10200	2904960	2908050		
10225	2905000	2900770		
10250	2903240	2900830		
10275	2907370	2907600		
10400	2905040	2901100		
10500	2907430	2907420		





**SEALED CONSTRUCTION** 



LARGEST WORKING CAPACITY



**PRECISION SLIDE BAR** 



- Swivel Base Meets federal spec # GGG-V-410a, Type VI, Class 2
- · Stationary Base Meets federal spec # GGG-V-410a, Type VI, Class 1

## **FEATURES**

#### STATIONARY / 360° SWIVEL BASE:

· All sizes available in both stationary and swivel base

## MAX JAW CAPACITY:

• Up to 12" jaw opening for jobs demanding maximum holding capacity

### **LARGE ANVIL:**


 Designed to take a pounding while forming and shaping materials

## **IDEAL FOR**

- Machine Shops
- Automotive Maintenance
- Maintenance and Repair
- Metal Fabrication

Stock No.	Model	Jaw Width (in.)	Jaw Opening (in.)	Throat Depth (in.)	Replacement Jaw Insert No.	Net Weight (lbs.)
MACHINI	ST – SWI	VEL BASE				
10006	300S	3	4-3/4	2-5/8	2903080	30
10011	350S	3-1/2	5-1/4	2-3/4	2904960	44
10016	400S	4	6-1/2	3-1/2	2904980	62
10021	450S	4-1/2	7-1/2	4	2905000	71
10026	500S	5	8	4-1/4	2905020	96
10031	600S	6	10	5-1/2	2903280	156
10036	800S	8	12	5-13/16	2904940	238
MACHINI	ST – STA	TIONARY BA	SE			
10056	300N	3	4-3/4	2-5/8	2903080	25
10066	350N	3-1/2	5-1/4	2-3/4	2904960	35
10076	400N	4	6-1/2	3-1/2	2904980	54
10086	450N	4-1/2	7-1/2	4	2905000	63
10096	500N	5	8	4-1/4	2905020	88
10107	600N	6	10	5-1/2	2903280	143
10116	800N	8	12	5-13/16	2904940	218

WILTONTOOLS.COM 13



## **FEATURES**

#### STEEL PIPE JAWS:

- Fixed jaws hold up to 3-1/2" pipe safely and securely
- Great for irregularly shaped objects

#### **MAX JAW CAPACITY:**

 Up to 7" jaw opening for jobs demanding maximum holding capacity

#### **REVERSIBLE JAW INSERTS:**

 Standard serrated jaws for extra grip or smooth to prevent marring on softer surfaces

- Tradesmen
- Automotive
- Construction Sites
- Metal Fabrication
- Service and MRO
- Utility

Stock No.	Model	Jaw Width (in.)	Jaw Opening (in.)	Throat Depth (in.)	Pipe Jaw Capacity (in.)	Net Weight (lbs.)		
TRADESMAN – SWIVEL BASE								
63199	1745	4-1/2	4	3-1/4	1/4 – 2-1/2	42		
63200	1755	5-1/2	5	3-3/4	1/4 – 3	52		
63201	1765	6-1/2	6-1/2	4	1/4 – 3-1/2	71		
63202	1780A	8	7	4-3/4	1/8 – 3-1/2	111		

Stock No.	Replacement Jaw Insert No.	Replacement Pipe Jaw Insert No.		
63199	2908060	2904200		
63200	2908070	2904200		
63201	2908080	2904200		
63202	2908100	2908050		





**SEALED CONSTRUCTION** 



**LARGE ANVIL** 



**PRECISION SLIDE BAR** 



## **PEDESTAL BASE**

#### BASE:


- 18" x 18" x 1/4", Top: 10-1/2" x 8-1/2" x 1/4"
- Great for irregularly shaped objects

#### PERFECT FOR:

• 1755 and 1765 Tradesman Swivel base models

Stock No.	Model	Ship Wt. (Lbs.)
TRADESI		
63185	55	





# INDUSTRIAL BENCH VISES

VERSATILE AND DEPENDABLE



MECHANICS



UTILITY



REVERSIBLE



SHOP









Wilton's expansive Industrial Bench Vise line ensures we have you covered in any industrial setting.











HARDENED STEEL JAWS PIPE JAWS



SEALED CONSTRUCTION



**4 MOUNTING POSTS** 



## **FEATURES**

#### 30,000 PSI IRON BODY:

 Heavy-Duty castings are built for rugged use and extended life

#### LIFETIME LUBRICATION:

 Grease is permanently sealed in for trouble-free service

#### **HI-VISIBILITY YELLOW:**

• Conforms to OSHA standards for Physical Hazards Regulation #1910.144


- Professional Mechanics
- Automotive Maintenance
- Maintenance and Repair

Stock No.	Model	Jaw Width (in.)	Maximum Opening (in.)	Throat Depth (in.)	Pipe Jaw Capacity (in.)	Weight (Ibs.)		
740 SERIES MECHANICS VISES								
21300	744	4	4-1/2	3-7/16	1/4 – 2	36		
21400	745	5	5-1/4	3-3/4	1/4 – 2-1/2	53		
21500	746	6	5-3/4	4-1/8	1/4 – 3-1/2	69		
21800	748A	8	8-1/4	4-3/4	1/4 – 3-1/2	92		
HIGH-VISIBILITY SAFETY VISES								
63187	1550	5	5-1/4	3-3/4	1/4 – 2-1/2	49		
63188	1560	6	5-3/4	4-1/8	1/4 – 3-1/2	64		

Stock No.	Replacement Jaw Insert No.	Replacement Pipe Jaw Insert No.			
21300	21300-03	21300-03			
21400	2904110	2904110			
21500	21500-03	21500-03			
21800	21800-03	21800-03			
63187	21400-03	21400-03			
63188	21500-03	21500-03			

# WILTON® REVERSIBLE MECHANICS

## VERSATILITY, REVERSABILITY



**HARDENED STEEL JAWS** 



PRECISION SLIDE HANDLE



INDUSTRIAL 360° LOCKING SWIVEL BASE

LIFETIA





#### 30,000 PSI IRON BODY:

 Heavy-Duty castings are built for rugged use and extended life

#### PIPE JAWS:

• Built-In Steel Jaws Handle Pipe From 1/8" - 3"

#### **DUAL ANVILS:**

 Two working anvil surfaces for forming and shaping materials

#### **HARDENDED STEEL JAWS:**

 Furnished with a serrated pattern to insure strength and long life

## **IDEAL FOR**

- Professional Mechanics
- Automotive Maintenance
- Maintenance and Repair

Stock No.	Model	Jaw Width (in.)	Maximum Opening Reversed (in.)	Throat Depth Reversed (in.)	Pipe Jaw Capacity (in.)	Replacement Jaw Insert No.	Net Weight (lbs.)
REVERS	SIBLE MEC	CHANICS	VISE				
14500	4500	5-1/2	6 / 9-3/4	3-3/4 / 2-3/4	1/4 – 2	14500S41	48
14600	4600	6-1/2	8 / 9-3/4	4 / 3	1/8 – 3-1/2	14600S03	50
14800	4800	8	9-1/2 / 11-3/4	5 / 2-3/4	1/8 – 4-1/2	14800S03	81

WILTONTOOLS.COM



## **IDEAL FOR ANY JOB**





**PIPE JAWS** 



LARGE ANVIL



**4 MOUNTING POSTS** 



## **FEATURES**

#### REPLACEABLE STEEL JAWS:

 Furnished with a serrated pattern to insure strength and long life

#### LARGE ANVIL:

 Designed to take a pounding while forming and shaping materials

#### 180° LOCKING SWIVEL BASE:

Single lockdown provides quick and easy positioning

- General Purpose
- · Light Tradesman
- Utility and Service
- Automotive

Stock No.	Model	Jaw Width (in.)	Maximum Opening (in.)	Throat Depth (in.)	Pipe Jaw Capacity (in.)	Replacement Jaw Insert No.	Net Weight (Ibs.)		
UTILITY VISES – SWIVEL BASE									
11126	674	4-1/2	4	2-5/8	1/8 – 2	76654S41	19		
11127	675	5-1/2	5	3-1/4	1/8 – 2-1/2	11127S41	29		
11128	676	6-1/2	5-1/2	3-13/16	1/8 – 2-1/2	11128S41	42		
191	656HD	6-1/4	6	4-3/8	1/8 – 3	11106S41	63		
11800	648HD	8	7-1/2	4-1/2	1/8 – 3	2904130	86		







**PIPE JAWS** 



**POLISHED ANVIL** 



**4 MOUNTING POSTS** 



## **FEATURES**

#### **HARDENED STEEL JAWS:**

 Furnished with a serrated pattern to insure strength and long life

#### **DOUBLE LOCK DOWNS:**

• 2 Lockdowns for a sturdier base and less rotation

#### 360° LOCKING SWIVEL BASE:

• 360° swivel ability for ideal positioning on workbench


Stock No.	Model	Jaw Width (in.)	Maximum Opening (in.)	Throat Depth (in.)	Pipe Jaw Capacity (in.)	Replacement Jaw Insert No.	Net Weight (Ibs.)
SHOP VIS	SES						
63300	WS4	4	4	2-3/4	5/8" - 2"	310041W	23
63301	WS5	5	5	3	5/8" - 2 3/8"	310051W	30
63302	WS6	6	6	3-1/2	5/8" - 2 1/2"	310061W	46
63304	WS8	8	8	4	3/4" - 3"	310081W	70

## **IDEAL FOR**

- General Purpose
- · Light Tradesman
- Utility and Service
- Automotive

# WILTON® MULTI-PURPOSE

360° JAW ROTATION





**LARGE ANVIL** 







## **FEATURES**

### **ROTATING HEAD:**

• Great for clamping material at any angle

#### V-JAW:

• Holds 1" - 3" diameter round stock vertically

#### **INDEXING:**

• 90° left and right for quick setup

#### LARGE ANVIL:


• Built-in anvil for flat shaping

- General Purpose
- · Light Tradesman
- Utility and MRO

Stock No.	Model	Jaw Width (in.)	Maximum Opening (in.)	Throat Depth (in.)	Pipe Jaw Capacity (in.)	Replacement Jaw Insert No.	Net Weight (Ibs.)	
UTILITY VISES – SWIVEL BASE								
69999	· ·	5	5-1/4	3	3/8-3	69999S41	46	

# WILTON® GENERAL PURPOSE

**WEEKEND WARRIOR** 





HIGH STRENGTH STEEL CONSTRUCTION



**BUILT-IN ANVIL** 



DIAMOND SERRATED JAW FACES



## **FEATURES**

#### **VISE BODY:**

· Made from high strength steel

#### **JAW FACES:**

· Diamond serrated for positive gripping

#### BASE

Swivel base with double lock down

#### ANVIL

• Built-in anvil for flat shaping

## **IDEAL FOR**

- · Light Duty Use
- General Purpose
- Home Shop
- Weekend Projects

Stock No.	Model	Jaw Width (in.)	Maximum Opening (in.)	Throat Depth (in.)	Pipe Jaw Capacity (in.)	Net Weight (lbs.)
GENERAI	L PURPOS	E				
11104		4	4	2-1/4		16
11105		5	5	2-1/2		27
11106	<u>-</u>	6	6	3		39

WILTONTOOLS.COM — 23



## THE MINI BULLET



**BROAD ANVIL** 



LIGHTWEIGHT AND PORTABLE



**FULLY ENCLOSED DESIGN** 

CLAMP-ON BASE

NOTE:

· Clamp-On has 3" opening



## **FEATURES**

#### **STEEL TOP JAWS:**

 Replaceable and grooved for strong holding action

#### 45° LOCKING SWIVEL BASE:

 Double lockdowns for quick and easy positioning in any working position

## **IDEAL FOR**

- General Purpose
- Light Tradesman
- Home Shop

Stock No.	Model	Jaw Width (in.)	Jaw Opening (in.)	Throat Depth (in.)	Replacement Jaw Insert No.	Net Weight (lbs.)			
WILTON® SUPER-JUNIOR® – CLAMP-ON BASE									
63198	CBV-65	2-1/2	2-1/8	1-3/4	2900270	11			
63247	CBV-100	4	2-1/4	2	2900300	18			
WILTON®	WILTON® SUPER-JUNIOR® – SWIVEL BASE								
63244	SBV-65	2-1/2	2-1/8	1-3/4	2900270	9			
63248	SBV-100	4	2-1/4	2	2900300	14			

SWIVEL BASE







DOUBLE STEEL GUIDE BARS



**CAST JAWS** 



LIFETIA

**VACUUM BASE** 

## FEATURES - Clamp-On

### **DOUBLE STEEL GUIDE BARS:**

 Insures parallel alignment of pipe jaws for consistent holding pressure

#### CAST JAWS:

· Holds workpiece firmly

#### **PORTABLE:**

 Vise can quickly and easily be transferred to new work station

## **IDEAL FOR**

- General Purpose
- · Light Tradesman
- Woodworking

## FEATURES - Vacuum

### 360° SWIVEL BASE AND 180° HEAD TILT:

Can be used in a wide variety of working positions

#### **SEAL VACUUM BASE:**

 Secure base to any flat, clean and dry surface by pressing base to surface and pulling lock arm

#### **CAST ALUMINUM BODY:**

Strong and durable

Stock No.	Model	Jaw Width (in.)	Maximum Opening (in.)	Net Weight (lbs.)				
WILTON®	CLAMP-ON	VISE – STAT	ONARY BASE					
33150	150	3	2-1/2	4				
WILTON®	CLAMP-ON	VISE – SWIV	EL BASE					
33153	153	3	2-1/2	6				
WILTON® VACUUM VISE								
63500	3VB	2-3/4	2-1/2	3				



## WOODWORKING MADE TOUGH





SELF CENTERING JAW



REPLACEABLE MAPLE JAW INSERTS



STURDY STEEL HANDLE

## **WOODWORKING FEATURES**

#### **SELF CENTERING JAW:**

• Ensure a strong hold on all workpieces no matter what the shape

#### **FRONT JAW:**

• Pivots 10° to allow for irregular shaped parts

#### **PIVOT JAW:**

• Can be removed for wider clamping requirements

## **IDEAL FOR**

- Woodworking
- · Light Tradesman

## **LIGHT-DUTY FEATURES**

### **HIGH-TENSILE IRON JAWS:**

• Provide strength and durability

#### LIGHTWEIGHT DESIGN:

Perfect for home craftsmen

#### **COLD ROLLED STEEL GUIDE BARS:**

· Offer strength and integrity to the tool

Stock No.	Model	Jaw Width (in.)	Jaw Opening (in.)	Type of Nut	Replacement Jaw Insert No.	Net Weight (lbs.)		
WOODWORKING VISES								
63144	78A	4 x 7	10	Rapid	63142	32		
63218	79A	4 x 10	13	Rapid	63143	36		
LIGHT-DUTY WOODWORKING VISE								
33176	176	6-1/2	4-1/2	-	<u> </u>	6		

## BENCH VISE ACCESSORIES



#### MODEL P-PRISM MAGNEFIX JAW CAPS

- · Aluminum alloy with synthetic rubber cover
- Jaw construction includes a 120° horizontal V-groove, three vertical V-grooves and a 90° groove for marking out and center punching
- · Ideal for light tapping and thread cutting



### MODEL R-RUBBER FACE MAGNEFIX JAW CAPS

- Aluminum alloy with synthetic rubber cover
- Jaw cap conforms to workpiece and grips firmly without slipping while protecting work surface
- Use in combination with aluminum and prism jaw caps to clamp taper pins or tapered workpieces

## MODEL A-ALUMINUM MAGNEFIX JAW CAPS

- Aluminum alloy design includes six grooves to compensate for the unevenness of the workpiece
- Deeper V-groove ensures more secure clamping of circular workpieces
- Use together with rubber magnefix iaw caps



#### **COPPER JAW CAPS**

- Designed to avoid marring the surface of materials
- 100% copper jaw caps have polished faces and pliable copper extensions for a sure-grip fit

### MODEL F-FIBER FACE MAGNEFIX JAW CAPS

- Aluminum alloy with laminated fiber cover to prevent the absorption of outside materials
- Heat parts rapidly by concentrating heat into part
- Use on workpieces to avoid distortion and clamping marks



#### **MULTI-GRIP VISE JAWS**

- Soft polyurethane jaws designed to avoid marring the surface of softer metals and to protect jaw face
- Designed to fit any 3" 6" vise jaws, including all WILTON® and Columbian® vises
- Magnetic back mounts securely to jaw
- Great for holding wood, metal and tubing
- · One size fits all

Stock No.	Model	Jaw Width (in.)	Net Weight (lbs.)
MODEL P	PRISM		
14846	P-4	4	1
14847	P-4.5	4-1/2	1
14848	P-5	5	1
14873	P-5.5	5-1/2	1
14849	P-6	6	1
14876	P-6.5	6-1/2	1
MODEL R-	RUBBER I	FACE	
14838	R-3	3	1
14840	R-4	4	1
14841	R-4.5	4-1/2	1
14842	R-5	5	1
14872	R-5.5	5-1/2	1
14843	R-6	6	1
14875	R-6.5	6-1/2	1

Stock No.	Model	Jaw Width (in.)	Net Weight (lbs.)					
MODEL	MODEL A-ALUMINUM							
14828	A-4	4	1					
14829	A-4.5	4-1/2	1					
14830	A-5	5	1					
14871	A-5.5	5-1/2	1					
14831	A-6	6	1					
14874	A-6.5	6-1/2	1					
COPPER	JAW CAPS							
24403	404-3	3	1					
24404	404-3-1/2	3-1/2	1					
24405	404-4	4	1					
24406	404-4-1/2	4-1/2	1					
24407	404-5	5	1					
63203	404-5-1/2	5-1/2	2					
24408	404-6	6	2					
63204	404-6-1/2	6-1/2	3					
24409	404-8	8	4					

Stock No.	Model	Jaw Width (in.)	Net Weight (lbs.)					
MODEL F	-FIBER FAC	CE						
14834	F-4	4	1					
14835	F-4.5	4-1/2	1					
14836	F-5	5	1					
14837	F-6	6	1					
MULTI-GI	MULTI-GRIP VISE JAWS							
21111	21111	5-1/2	1					



## WILTON® POW-R-ARMS

WORKHOLDING SUPPORT FOR PRODUCTION LINES







- Extra-strong, positioner with exceptionally fast on-off action, the 301 is designed for high production assembly line applications.
- Body is machined cast iron with all steel parts
- Two mounting holes at top (5/16-18) are 1" apart

## POW-R-ARM™ HYDRAULIC NO. 303

- Same size and strength as Model 301 with hydraulic locking action
- Rated for heavy-duty assembly, welding, maintenance and tool room work
- Hydraulic system is hand operated, self-contained and sealed with replaceable cups
- Two mounting holes at top (5/16-18) holes 1" apart



## POW-R-ARM™ JUNIOR NO. 343

- Fast on-off action with horizontal-moving lock handle
- · Body is cast aluminum with steel parts
- 3" diameter mounting pad with two 1/4 – 20 holes
- 180° apart. Four slotted equally spaced 9/32" diameter mounting holes

- Production Environments
- Assembly Lines
- Intricate Work
- Fab Shops
- Electronic MRO



POW-R-ARMs have been popular in production lines for decades. Seen here in use at Burroughs Corporation, circa 1956.





**ERGONOMIC HANDLES** 



**MACHINED STEEL PARTS** 



CAST IRON & ALUMINUM BODY CONSTRUCTION



## POW-R-ARM™ VEEP NO. 344


- Design provides more work-holding capacity and faster on-off action
- Horizontal handle is easily accessible and dwells below level of work
- Steel body is cadmium plated with cast iron base
- Mounting hole at top is 1/2" diameter x 1/2" deep with set screw to hold a fixture
- Four 1/4" diameter equally spaced slotted mounting holes
- For light production assembly or electronic applications



- Recommended for intricate electronic work including small printed circuits.
- · Fast on/off action with horizontal handle
- All steel parts
- Mounting stud at top is 5/16-24 x 15/32" long



Stock No.	Model	Workholding Capacity (lbs.)	Base Diameter (in.)	Diameter Bolt Circle (in.)	Extended Height (in.)	Net Weight (lbs.)
POW-R-ARM	MECHANICAL N	10. 301				
16240	301	70	5-15/16	5	10-1/2	14
POW-R-ARM	HYDRAULIC NO.	. 303				
16300	303	150	5-7/8	5	10-1/2	15
POW-R-ARM	JUNIOR NO. 343	3				
16180	343	30	4-1/4	2-1/4	5	4
POW-R-ARM	VEEP NO. 344					
16120	344	20	3-3/4	3-3/8	4-1/4	3
POW-R-ARM	MIDGET NO. 345	5				
16060	345	6	2-1/2	1-7/8	1-1/4	1



# TRUCK HITCH VISE

YOUR TRUCK JUST GOT ONE HELL OF AN UPGRADE





6" ATV®





Some jobs go beyond the workshop. Some jobs make you come to them. For the jobs that demand function, strength and mobility, we present the ATV All-Terrain Vise.



6" ATV® WITH CARRYING CASE

## ATV ALL-TERRAIN VISE

## SECURE IT IN YOUR HITCH OR MOUNT IT ON YOUR BENCH



6" ATV WITH CARRYING CASE



6" ATV

## **FEATURES**

#### **DRIVE TIGHT SET SCREWS:**

 Patented set screws adjust to provide a tight fit in the hitch and reduce vibration while driving

#### **360 LOCKING HANDLE**

 Secures the handle while driving or repositions it while working

#### **PIPE JAWS:**

 Pipe jaws clamp round objects up to 3"

#### **REPLACEABLE JAWS:**

• Include a V-groove for verticle clamping of round objects

#### LARGE ANVIL:

 Large striking anvil for forming and shaping materials.

#### **MOUNTING BRACKET**

- Can be mounted on a bench or trailer for even greater versatility
- Included with 6" ATV (SKUs 10010 and 10015)

- Construction
- Automotive
- Farm and ranch
- Off roaders







5" ATV



**MOUNTING BRACKET** (INCLUDED WITH 6" ATV)



**LARGE STRIKING** ANVIL



**DRIVE TIGHT SET SCREWS** 



FITS 2" HITCH, HITCH PIN INCLUDED




**360° LOCKING HANDLE** 



**CARRYING HANDLE** 









WILTONTOOLS.COM 33



## **WILTON MACHINE VISES**

PRECISION WORKHOLDING












Wilton® Machine Vises - the definition of durability and precision. With a vise for every application, our machine vise lineup is what you would expect from North America's leader in industrial bench vises.





# VERTI-LOCK® MILLING MACHINE VISE

**ACCURATE, SOLID & TRUE** 



## **COMMON FEATURES**

#### VISE BODY:

 The ductile alloy vise body with flame-hardened bed provides solid work support, accuracy, and longevity

#### **VISE JAWS:**

• The fixed jaw is rated at 85,000 PSI and the annealed, surface ground sliding jaw at 70,000 PSI

#### SPINDLE

- Fully enclosed spindle is protected from milling elements
- · Cut from special alloy steel, hardened and ground





FLAME HARDENED BED





**HARDENED JAWS** 



**COOLANT DRAIN** 





SWIVEL BASE



Stock No.	Model	Jaw Width (in.)	Jaw Depth (in.)	Jaw Opening (in.)	Net Weight (lbs.)
STANDAR	D VISE ON	ILY			
12390	1250N	5	1-7/16	4-1/2	50
63186	1275N	6	1-3/4	7-1/2	75
12375	1280N	8	2-1/4	7-1/2	164
SWIVEL B	ASE ONLY				
12285	5S	5	<u>-</u>		20
12290	6S	6	<u>-</u>	•	26
12295	88	8	<u>-</u>		48



WILTONTOOLS.COM \_\_\_\_\_\_\_\_\_37

## SUPER PRECISION MACHINE VISES

#### ANGULAR & SELF CENTERING PRECISION



### SUPER PRECISION 3-AXIS

- Perfect vise for 3-axis jobs in milling, drilling, grinding, shaping and jig boring
- Vise bodies are constructed of close grained, high tensile,seasoned alloy castings
- Ergonomically designed all steel handle with spring loaded ball attachment
- Durable polychromatic finish
- Hardness of Jaws 55 ± 3HRC



### SUPER PRECISION 2-AXIS ANGULAR

- Perfect vise for applications where the workpiece requires machining on an angle
- Vise bodies are constructed of close grained, high tensile, seasoned alloy castings
- · All ground surfaces made to close tolerances
- Ergonomically designed all steel handle with spring loaded ball attachment
- · Hardness of Jaws 55 ± 3HRC



### SUPER PRECISION SELF CENTERING

- Very convenient for use with drilling and milling machines where quick centering is required
- Allows for accurate centering of jobs automatically
- Special design allows accurate setting up of jobs with only a single machine setting

Stock No.	Model	Jaw Width (in.)	Jaw Depth (in.)	Jaw Opening (in.)	Net Weight (Ibs.)
SUPER	PRECISIO	ON 3-AX	IS TILTIN	G	
11700	TLT/ SP-50	2	1	2	10
11701	TLT/ SP-75	3	1-5/16	3	26
11702	TLT/ SP-100	4	1-1/2	4	52
11803	TLT/ SP-125	5	1-3/4	5	84
11804	TLT/ SP-150	6	1-3/4	6	119


Stock No.	Model	Jaw Width (in.)	Jaw Depth (in.)	Jaw Opening (in.)	Net Weight (Ibs.)
SUPER	RPRECISIO	ON 2-AX	IS TILTIN	G	
11703	AMV/ SP-50	2	15/16	2	8
11704	AMV/ SP-75	3	1-5/16	3	22
11705	AMV/ SP-100	4	1-9/16	4	43
11706	AMV/ SP-125	5	2	5	74
11707	AMV/ SP-150	6	2	6	101

Stock No.	Model	Jaw Width (in.)	Jaw Depth (in.)	Jaw Opening (in.)	Net Weight (lbs.)
SUPER	PRECISIO	N SELF	CENTER	ING VISE	
11713	SCV/ SP-100	4	1-1/2	4	34



## **DRILL PRESS VISES**

#### VERSATILITY AND SPEED





#### **VERSATILE DRILL PRESS VISES**

- · Rapid acting nut disengages spindle for quick adjustments
- · Made from high grade cast iron
- · Ground vise bed for smooth, consistent jaw movement
- · Hardened top V-groove jaws
- · Rugged design and large workload capacity

#### **CAM ACTION DRILL PRESS VISES**

- Simple push or pull on the center bar knob sets the jaw in position
- Easy press locking lever cams the jaw ahead 3/32", exerting a holding pressure that is adjustable from 400 to 1100 lbs.
- · Base is designed for clear through drilling applications
- Unique top locking lever can be raised or lowered to tighten or loosen against the work piece.

Stock No.	Model	Jaw Width (in.)	Jaw Opening (in.)	Jaw Depth (in.)	Net Weight (lbs.)
VERSATILE	– CONTIN	UOUS NUT			
63238	1335	3	2-3/4	1-7/8	6
63239	1345	4	4	2-1/8	12
63240	1360	5	5	2-1/8	20
VERSATILE	– RAPID <i>A</i>	ACTING NUT			
63242	1445	4-1/2	4-3/4	1-7/8	15
63243	1460	6	6-3/4	2-1/8	29

Stock No.	Model	Jaw Width (in.)	Jaw Opening (in.)	Jaw Depth (in.)	Net Weight (lbs.)
CAM ACT	ION				
13400	1203	3	3	1-1/4	10
13401	1204	4	4-11/16	1-5/16	18
13402	1206	6	6-3/16	1-13/16	35
13403	1208	8	8-3/16	2	53



WILTONTOOLS.COM — 35

## DRILL PRESS VISES

#### **GENERAL PURPOSE**



#### STANDARD DRILL PRESS VISE

- 4" Jaw width opens to a maximum of 4-1/2"
- Grooved jaws provide a firm, secure grip on your work material
- Elongated holes for easy fastening onto drill presses or work surfaces



#### **INDUSTRIAL DRILL PRESS VISES**

- Designed for applications including drilling, tapping, reaming and grinding
- Durable base has bolt lugs for easy mounting on a machine table
- Hardened V Grooved Jaws hold round shaped objects both vertically and horizontally
- Zinc plated fine threaded screw provides smooth clamping action
- Durable construction with fine grain cast iron castings and hardened steel vise jaws
- Highly accurate with beds and bases parallel to ±.001" on drill press vises and ±.0001" on industrial drill press vises

Stock No.	Model	Jaw Width (in.)	Jaw Opening (in.)	Jaw Depth (in.)	Replacement Jaw Insert No.	Net Weight (lbs.)
STAND	ARD DRILI	L PRESS VIS	E			
69997	1203	4	4-1/2	1-1/2		7

Stock No.	Model	Jaw Width (in.)	Jaw Opening (in.)	Jaw Depth (in.)	Replacement Jaw Insert No.	Net Weight (Ibs.)
INDUST	TRIAL DRI	LL PRESS VI	SES			
11674	D144	4	4	1-1/2	11674-01	10
11676	D166	6	6	2	11676-01	35



## **DRILL PRESS VISES**

#### **GENERAL PURPOSE**



### STANDARD THREE-SIDED DRILL PRESS VISES

- Precision grinding of sides and front side face permits additional mounting positions for drilling, tapping or reaming
- Combining a smooth moveable jaw plate with a cross-patterned 90° V groove stationary jaw.
- · The vise is recommended for general use.



#### **LOW PROFILE DRILL PRESS VISES**

- Designed for applications including drilling, tapping and reaming
- Low profile clearance for increased working room on machine table
- Hardened V Grooved Jaws hold round shaped objects both vertically and horizontally
- Durable construction with fine grain cast iron castings and hardened steel vise jaws
- Black oxide coated ACME threaded screw provides consistent clamping pressure
- · Highly accurate with beds and bases parallel to ±.001"

Stock No.	Model	Jaw Width (in.)	Jaw Opening (in.)	Jaw Depth (in.)	Net Weight (lbs.)
STANDAR	D THREE-	SIDED DRILL	. PRESS VISES		
12800	25	2-1/2	2-9/16	1-1/2	6
12860	30	3	3-1/8	1-3/4	10

Stock No.	Model	Jaw Width (in.)	Jaw Opening (in.)	Jaw Depth (in.)	Replacement Jaw Insert No.	Net Weight (lbs.)
LOW P	ROFILE [	ORILL PRES	S VISES			
11743	LP3	3	3	1-1/8	11743-01	8
11744	LP4	4	4	1-1/2	11744-01	12
11746	LP6	6	6	2	11746-01	30
11748	LP8	8	8	2	11748-01	50




# ANGLED DRILL PRESS VISES

#### PRECISE ANGLED DRILLING



#### CRADLE STYLE ANGLE DRILL PRESS VISE

- Designed for applications including drilling, tapping and reaming requirin g angle setup
- · Cradle design with 90° vertical indexing, scaled in 1° increments
- Side tommy bar allows secure locking at any increment from 0° - 90°
- Pin hard stops at 0°, 15°, 30°, 45°, 60°, 75° and 90° for common applications
- Durable construction with fine grain cast iron castings and hardened smooth vise jaws



#### **ANGLE DRILL PRESS VISES**

- Precision grinding of sides and front side face permits additional mounting positions for drilling, tapping or reaming
- Combining a smooth moveable jaw plate with a cross-patterned 90° V groove stationary jaw
- · The vise is recommended for general use

Stock No.	Model	Jaw Width (in.)	Jaw Opening (in.)	Jaw Depth (in.)	Replacement Jaw Insert No.	Net Weight (lbs.)
CRADLI	E STYLE A	ANGLE DRIL	L PRESS VIS	E		
11753	CR3	4	3	1-1/8	11753-01	12
11754	CR4	6	4	1-1/2	11754-01	17
	<u> </u>		· ·			

Stock No.	Model	Jaw Width (in.)	Jaw Opening (in.)	Jaw Depth (in.)	Net Weight (lbs.)
ANGLE D	RILL PRES	S VISES			
12850	25A	2-1/2	2-1/2	1-1/2	10
12870	30A	3-1/8	3-1/8	1-3/4	16



## 2 AXIS DRILL PRESS VISES

#### **ACCURATE IN-LINE DRILLING**



#### **CROSS SLIDE DRILL PRESS VISES**

- Accurately moves your workpiece horizontal and longitudinal for precise positioning
- · Cast side knobs accurately dial in .1mm increments
- Hardened V Grooved Jaws hold round shaped objects both vertically and horizontally
- · Durable construction with fine grain cast iron castings
- · Black oxide coated screw provides consistent clamping pressure
- Durable base has 5 bolt lugs for easy mounting on a machine table

Stock No.	Model	Jaw Width (in.)	Jaw Opening (in.)	Jaw Depth (in.)	X-Travel (in.)	Y-Travel (in.)	Replacement Jaw Insert No.	Net Weight (lbs.)
CROSS	SLIDE [	ORILL PR	ESS VISE	S				
11693	CS3	3	3	1-1/8	4-9/10	4-9/10	11693-01	16
11694	CS4	4	4	1-3/8	4-9/10	4-9/10	11694-01	20
11695	CS5	5	5	1-1/2	5-9/10	5-9/10	11695-01	45
11696	CS6	6	6	2	7-9/10	7-9/10	11696-01	59
11698	CS8	8	8	2	7-9/10	7-9/10	11698-01	77



WILTONTOOLS.COM 43



## WILTON F-CLAMPS

THE WELDER'S CHOICE










At Wilton®, we know welding. As the leader in professional grade workholding equipment for 75 years, we understand the intricacies of your work. That's why we are proud to introduce our full line of welding F-Clamps.





## SPARK-DUTY<sup>TM</sup> COPPER-PLATED F-CLAMPS

#### THE SERIOUS WELDER'S CHOICE



#### **FEATURES**

#### **DROP-FORGED ARM:**

· Minimal flex under heavy workloads

#### SPARK-DUTY™ COPPER-PLATED SPINDLE:

• Extends the life of the clamp by protecting the spindle and pad from harmful welding spatter

#### QUICK-TWIST PADS:

 Simple and fast replaceable pads in V-Groove or serrated surfaces

#### **V-GROOVE PAD**


 Included with every clamp. Clamp round objects up to 14" in diameter

#### **ERGONOMIC WILTON-GRIP®:**

 Anti-Fatigue Wilton-Grip® provides comfort during repetitive clamping

Stock No.	Model	Nominal Opening Capacity (in.)	Throat Depth (in.)	Clamping Force (lbs.)	Net Weight (lbs.)
SPARK-DUTY	™ 4800S SERIES	– HEAVY-DUTY			
86500	4800S-12C	12	7	4,880	12
86510	4800S-18C	18	7	4,880	15
86520	4800S-24C	24	7	4,880	16
86530	4800S-36C	36	7	4,880	21
86540	4800S-48C	48	7	4,880	24
86550	4800S-60C	60	7	4,880	27
SPARK-DUTY	™ 2400S SERIES	– REGULAR-DU	ГҮ		
86400	2400S-8C	8	5-1/2	2,660	6
86410	2400S-12C	12	5-1/2	2,660	7
86420	2400S-16C	16	4-3/4	2,660	7
86430	2400S-20C	20	5-1/2	2,660	8
86440	2400S-24C	24	4-3/4	2,660	9
86450	2400S-36C	36	5-1/2	2,660	12
86460	2400S-48C	48	5-1/2	2,660	14
86470	2400S-60C	60	5-1/2	2,660	15
SPARK-DUTY	™ 2000S SERIES	– LIGHT-DUTY			
86300	2000S-8C	8	4-3/4	2,000	5
86310	2000S-12C	12	5-1/2	2,000	5
86320	2000S-18C	18	4-3/4	2,000	6
86330	2000S-24C	24	4-3/4	2,000	7







V-GROOVE PAD INCLUDED



ERGONOMIC GRIP INCLUDED



COPPER-PLATED SPINDLE

#### **FEATURES**

#### J-SHAPED RAIL (J-SERIES):

· Steps over I-Beams and irregular shapes

#### **INCREASED THROAT DEPTH (DEEP REACH):**

• Provides deeper reach for unique projects

#### SPARK-DUTY™ COPPER-PLATED SPINDLE:

 Extends the life of the clamp by protecting the spindle and pad from harmful welding spatter

#### **QUICK-TWIST PADS:**

 Simple and fast replaceable pads in V-Groove or serrated surfaces

#### **V-GROOVE PAD**

 Included with every clamp. Clamp round objects up to 16" in diameter

#### ERGONOMIC WILTON-GRIP®:

 Anti-Fatigue Wilton-Grip® provides comfort during repetitive clamping

Stock No.	Model	Nominal Opening Capacity (in.)	Throat Depth (in.)	Clamping Force (lbs.)	Net Weight (lbs.)				
SPARK-DUTY <sup>™</sup> J-SERIES									
86900	1200J-10C	10	4-3/4	1,200	4				
86910	2400J-12C	12	5-1/2	2,400	8				
86920	4800J-20C	20	7	4,800	19				
SPARK-DU	SPARK-DUTY™ DEEP REACH								
86700	DT2400S-12C	12	8	1,770	8				
86710	DT2400S-24C	24	8	1,770	10				



# SPARK-DUTY\*\* WELDERS SHOE CLAMP





**FORGED SLIDE ARM** 



PERMA-PADS



COPPER-PLATED SPINDLE

#### **FEATURES**

#### SPARK-DUTY™ COPPER-PLATED SPINDLE:

• Extends the life of the clamp by protecting the spindle and pad from harmful welding spatter

#### **HEAVY-DUTY SHOE:**

· Bolt or weld shoe to workstation for maximum stability

#### **DROP-FORGED ARM:**

· Slides up and down robust rail for rapid loading

Stock No.	Model	Nominal Opening Capacity (in.)	Throat Depth (in.)	Nominal Rail Size (in.)	Clamp Pressure (in.)	Nominal Spindle Diameter (in.)	Net Weight (Ibs.)
SPARK-D	UTY™ W	ELDERS SHO	E CLAMP				
63295	·	8-1/2	5-1/2	1-3/16 x 9/16	2,600	3/4	8

- Production work
- Repetitive welding
- High-efficiency



# COPPER PLATED SPARK-DUTY\*\* F-CLAMP ACCESSORIES



Stock No.	Model	Wilton Grip Stock No.	Plain Pad Stock No.	Serrated Pad Stock No.	V-Pad Stock No.	Nut Stock No.	Joint with Spring Pin Stock No.	Spindle and Handle with Spring Pin Stock No.
SPARK-DUT	Y™ 2000S SERIES							
86300	2000S-8C	1713511	2909101	2909201	2909301	1701701	1701501	1701601
86310	2000S-12C	1713551	2909101	2909201	2909301	1701701	1701501	1701601
86320	2000S-18C	1713511	2909101	2909201	2909301	1701701	1701501	1701601
86330	2000S-24C	1713511	2909101	2909201	2909301	1701701	1701501	1701601
SPARK-DUTY	Y™ 2400S SERIES							
86400	2400S-8C	1713551	2909102	2909202	2909302	1701702	1701502	1701602
86410	2400S-12C	1713551	2909102	2909202	2909302	1701702	1701502	1701602
86420	2400S-16C	1713551	2909102	2909202	2909302	1701702	1701502	1701602
86430	2400S-20C	1713551	2909102	2909202	2909302	1701702	1701502	1701602
86440	2400S-24C	1713551	2909102	2909202	2909302	1701702	1701502	1701602
86450	2400S-36C	1713551	2909102	2909202	2909302	1701702	1701502	1701602
86460	2400S-48C	1713551	2909102	2909202	2909302	1701702	1701502	1701602
86470	2400S-60C	1713551	2909102	2909202	2909302	1701702	1701502	1701602
SPARK-DUTY	Y™ 4800S SERIES							
86500	4800S-12C	1713561	2909102	2909202	2909302	1701702	1701502	1701603
86510	4800S-18C	1713561	2909102	2909202	2909302	1701702	1701502	1701603
86520	4800S-24C	1713561	2909102	2909202	2909302	1701702	1701502	1701603
86530	4800S-36C	1713561	2909102	2909202	2909302	1701702	1701502	1701603
86540	4800S-48C	1713561	2909102	2909202	2909302	1701702	1701502	1701603
86550	4800S-60C	1713561	2909102	2909202	2909302	1701702	1701502	1701603
SPARK-DUT	Y™ DEEP REACH SER	RIES						
86700	DT2400S-12C	1713551	2909101	2909201	2909301	1701701	1701501	1701601
86710	DT2400S-24C	1713551	2909101	2909201	2909301	1701701	1701501	1701601
SPARK-DUTY	Y™ J SERIES							
86900	1200J-10C	1713551	2909100	2909200	2909300	1701700	1701500	1701600
86910	2400J-12C	1713551	2909102	2909202	2909302	1701702	1701502	1701602
86920	4800J-20C	1713561	2909102	2909202	2909302	1701702	1701502	1701603

## CLASSIC<sup>™</sup> SERIES HEAVY-DUTY F-CLAMPS

#### NOTHING BEATS A CLASSIC





**FORGED SLIDE ARM** 



STURDY TOMMY BAR



HEAVY DUTY
REPLACEABLE PAD

#### **FEATURES**

#### **BLACK OXIDE SPINDLES:**

· Resist wear and tear while impeding rust

#### **DROP-FORGED ARM:**

• Provides minimal flex under heavy workloads

#### **QUICK TWIST PADS:**

• Heavy duty pads are simple and fast to replace

#### STURDY TOMMY BAR:

• Engineered for durability and comfort

- Fabrication
- Welding
- Repetitive Clamping

Stock No.	Model	Nominal Opening Capacity (in.)	Throat Depth (in.)	Clamping Force (lbs.)	Net Weight (Ibs.)		
CLASSIC HEAVY-DUTY F-CLAMPS							
86640	GSM20	8	5-1/2	2,660	6		
86650	GSM30	12	5-1/2	2,660	7		
86660	GSM40	16	4-3/4	2,660	7		
86670	GSM50	20	5-1/2	2,660	8		
86680	GSM60	24	4-3/4	2,660	9		

Stock No.	Plain Pad Stock No.	Serrated Pad Stock No.	V Pad Stock No.	Nut Stock No.	Joint w/ Spring Pin Stock No.	Spindle and Handle w/ Spring Pin Stock No.				
REPLACEMENT PARTS CLASSIC HEAVY-DUTY F-CLAMP										
86640	2909102A	2909202A	2909302A	1701702A	1701502A	1701602B				
86650	2909102A	2909202A	2909302A	1701702A	1701502A	1701602B				
86660	2909102A	2909202A	2909302A	1701702A	1701502A	1701602B				
86670	2909102A	2909202A	2909302A	1701702A	1701502A	1701602B				
86680	2909102A	2909202A	2909302A	1701702A	1701502A	1701602B				

# CLASSIC<sup>™</sup> SERIES REGULAR & LIGHT DUTY F-CLAMPS

#### NOTHING BEATS A CLASSIC





FORGED SLIDE ARM



STURDY TOMMY BAR



**OSCILLATING PAD** 

#### **FEATURES**

#### **BLACK OXIDE SPINDLES:**

· Resist wear and tear while impeding rust

#### **DROP-FORGED ARM:**

Provides minimal flex under heavy workloads

#### **SWIVEL PAD:**

· Centers on workpiece for a sturdy hold

#### STURDY TOMMY BAR:

• Engineered for durability and comfort

#### **IDEAL FOR**

- Fabrication
- Welding
- Repetitive Clamping

Stock No.	Model	Nominal Opening Capacity (in.)	Throat Depth (in.)	Clamping Force (lbs.)	Net Weight (lbs.)				
CLASSIC	REGULAR-DI	UTY F-CLAMP	S						
86200	1800S-8	8	4-3/4	1,800	4				
86210	1800S-12	12	5-1/2	1,800	5				
86220	1800S-18	18	4-3/4	1,800	6				
86230	1800S-24	24	4-3/4	1,800	6				
CLASSIC	CLASSIC LIGHT-DUTY F-CLAMPS								
86100	660S-8	8	4	660	2				
86110	660S-12	12	4	660	2				
86120	660S-18	18	4	660	3				
86130	1200S-8	8	4-3/4	1,200	2				
86140	1200S-12	12	4-3/4	1,200	3				
86150	1200S-18	18	4-3/4	1,200	4				
86160	1200S-24	24	4-3/4	1,200	4				

## CLASSIC™ SERIES MINI F-CLAMPS

#### NOTHING BEATS A CLASSIC





FORGED SLIDE ARM



STURDY TOMMY BAR



**OSCILLATING PAD** 

#### **FEATURES**

#### **BLACK OXIDE SPINDLES:**

· Resist wear and rear while impeding rust

#### DROP-FORGED ARM:

• Provides minimal flex under heavy workloads

#### SWIVEL PAD:

• Centers on workpiece for a sturdy hold

#### STURDY TOMMY BAR:

• Engineered for durability and comfort

- Fabrication
- Welding
- Repetitive Clamping

Stock No.	Model	Nominal Opening Capacity (in.)	Throat Depth (in.)	Clamping Force (lbs.)	Net Weight (lbs.)
CLASSIC					
86000	MMS-4	4	2-1/4	400	1
<b>86010</b> MMS-8		8	2-1/4	400	1
86020	MMS-12	12	2-1/4	400	1

## HEAVY-DUTY LEVER CLAMPS

#### SPINDLELESS CLAMPS





QUICK RATCHETING DESIGN



**SELF CENTERING PAD** 



**ERGONOMIC HANDLE** 

#### **FEATURES**

#### **RATCHETING DESIGN:**

• Allows easy, spindle-free operation

#### QUICK-TRIGGER RELEASE:

• Release clamp pressure with one squeeze

#### WILTON® BLUE ALUMINUM HANDLE:

 Ergonomically designed for repetitive clamping and resistant to heat

#### **SELF CENTERING PAD:**

· Centers on workpiece for a sturdy hold

Stock No.	Model	Nominal Opening Capacity (in.)	Throat Depth (in.)	Clamping Force (lbs.)	Net Weight (lbs.)
LEVER CLA	MPS				
86800	LC4	4	2-3/8	350	2
86810	LC8	8	4	770	3
86820	LC12	12	5-1/2	1,100	3
86830	LC20	20	4-3/4	1,200	4









## WILTON® C-CLAMPS

**QUALITY CLAMPING SOLUTIONS** 



BRUTE FORCET C-CLAMPS



400 SERIES C-CLAMPS



4400 & 800 C-CLAMP5



Tried and true, Wilton® C-Clamps have been a part of American history stemming all the way back to the automotive boom in the 1950's. To this day, through evolutionary innovation, you will find the clamp for your application in our offering of over 135 different C-Clamps.





## BRUTE FORCE™ O-SERIES C-CLAMPS

#### BRIDGE / BOILER CLAMPS





**FULL LENGTH SPINDLE** 



**SOUARE SPINDLE HEAD** 



40,000 LBS. OF PURE CLAMPING PRESSURE



#### NOTE:

· Meets federal spec # GGG-C-406D, Type I, Class D Heavy Service

#### **FEATURES**

#### **HIGHEST CLAMPING PRESSURE:**

 Ranging up to 40,000 lbs. standing up to the demands of the heaviest industrial applications

#### SPINDLE:

• Full length, machined from a single piece of square, cold drawn steel, hardened and tempered

#### **SQUARE SPINDLE HEAD:**

 Stands up to heavy wrench tightening use, including both hand and torque wrench

- Heavy Construction
- Bridge Building
- Heavy Fabrication
- Ship Building

Stock No.	Model	Nominal Opening Capacity (in.)	Throat Depth (in.)	Clamp Pressure (lbs.)	Spindle Size(in.)	Net Weight (lbs.)				
BRUTE FORCE – O SERIES										
14518	1 F.C.	0 – 1-3/8	1-3/32	5,600	7/16	1				
14527	1-1/2 F.C.	0 – 1-3/4	1-3/16	8,750	5/8	2				
14536	2 F.C.	0 – 2-3/8	1-7/8	12,500	3/4	3				
14545	3 F.C.	0 – 3-5/16	2-5/16	16,250	7/8	7				
14554	4 F.C.	0 – 4-1/2	2-3/4	20,000	1	10				
14563	5 F.C.	0 — 5-1/4	3-1/8	23,800	1	14				
14572	6 F.C.	0 - 6-1/4	3-3/8	27,500	1-1/8	19				
14581	8 F.C.	0 - 8-1/2	3-5/8	31,250	1-1/4	26				
14590	10 F.C.	0 - 10-1/4	3-15/16	35,000	1-1/4	37				
14599	12 F.C.	0 - 12-3/8	4-1/4	40,000	1-1/4	44				

## BRUTE FORCE™ 100-SERIES C-CLAMPS

15,000 LBS. OF PRESSURE





HARDENED AND TEMPERED STEEL SPINDLE



REPLACEABLE PERMA-PADS



**SOUARE HEAD HANDLE** 



#### NOTE:

• Meets federal spec # GGG-C-406D, Type I, Class B Medium Service

#### **FEATURES**

#### SPINDLE:

 Full length, machined from a single piece of square, cold drawn steel, hardened and tempered

#### **SQUARE HEAD HANDLE:**

- Designed for maximum torque and flexible usage
- · Can be tightened by hand or wrench

Stock No.	Model	Nominal Opening Capacity (in.)	Throat Depth (in.)	Clamp Pressure (lbs.)	Spindle Size (in.)	Net Weight (lbs.)
BRUTE FO	RCE – 100	SERIES				
14114	102	0 – 2	1-1/2	7,500	9/16	2
14128	103	0 – 3	2	8,750	5/8	3
14142	104	0 – 4	2-1/4	10,000	3/4	4
14156	106	2-6	2-1/2	11,250	3/4	6
14170	108	4 – 8	2-3/4	12,500	3/4	8
14184	110	6 – 10	2-7/8	13,750	3/4	9
14198	112	8 – 12	2-15/16	15,000	3/4	12

#### **IDEAL FOR**

- Heavy Construction
- Mining and Extraction
- Machine Tool Fixtures
- Press Work

WILTONTOOLS.COM \_\_\_\_\_\_\_ 57

## CLASSIC 400 SERIES™ C-CLAMPS

#### DEEP THROAT CLAMPS





V GROOVED ANVIL



HI-VIS SAFETY YELLOW FRAME



REPLACEABLE PERMA-PADS



#### NOTE

- Meets federal spec # GGG-C-406a, Type I, Class A, Grade a, Style 1 & 2
- · Hi Vis conforms to OSHA safety color standard for physical regulation #1910.144

#### **FEATURES**

#### DROP FORGED:

Manufactured for greater strength under regular strength applications

#### **ACME ROLLED SPINDLE:**

• Threads provide continuous smooth operation for faster clamping action and maximum strength

#### **BLACK OXIDE COATING:**

 Spindles and PERMA-PADS® are freated to resist corrosion

#### V GROOVED ANVIL:

• Feature allows secure holding of all materials including rounds, squares and flats

- Steel Fabrication
- Industrial Maintenance
- Production
- Repair Operations

Stock No.	Model	Nominal Opening Capacity (in.)	Throat Depth (in.)	Clamp Pressure (lbs.)	Spindle Size(in.)	Net Weight (Ibs.)				
CLASSIC	CLASSIC 400 SERIES™									
14214	402	0 – 2-1/8	2-1/4	3,500	9/16	2				
14228	403	0-3	2-1/2	3,500	9/16	2				
14242	404	0 – 4-1/4	3-1/4	6,200	3/4	4				
14256	406	0 – 6-1/16	4-1/8	6,600	3/4	5				
14270	408	0 – 8-1/4	5	6,900	3/4	8				
14284	410	2 – 10-1/8	6	8,000	3/4	11				
14298	412	2 – 12-1/4	6-5/16	9,300	7/8	14				
CLASSIC	400 SERIES	™ HI-VIS SAFET	Υ							
14300	402-SF	0 – 2-1/8	2-1/4	3,500	9/16	1				
14301	403-SF	0-3	2-1/2	3,500	9/16	2				
14302	404-SF	0 – 4-1/4	3-1/4	6,200	3/4	4				
14303	406-SF	0 – 6-1/16	4-1/8	6,600	3/4	5				
14305	408-SF	0 — 8-1/4	5	6,900	3/4	7				
14306	410-SF	2 – 10-1/8	6	8,000	3/4	11				
14307	412-SF	2 – 12-1/4	6-5/16	9,300	7/8	15				

### SPARK-DUTY™ 400P AND HI-VIS C-CLAMPS

#### SPATTER RESISTANT COPPER





V-GROOVED ANVIL



HI-VIS SAFETY YELLOW FRAME



COPPER PLATED SPINDLE AND PERMA-PADS®



Hi Vis conforms to OSHA safety color standard for physical regulation #1910.144

#### **FEATURES**

#### **DROP FORGED:**

Manufactured for greater strength under regular strength applications

#### **V GROOVED ANVIL:**

• Feature allows secure holding of all materials including rounds, squares and flats

#### ACME ROLLED SPINDLE:

 Threads provide continuous smooth operation for faster clamping action and maximum strength

#### COPPER PLATED:

 Spindles and pads are copper plated to provide resistance to welding splatter and corrosion

#### **IDEAL FOR**

- Steel Fabrication
- Industrial Welders

Stock No.	Model	Nominal Opening Capacity (in.)	Throat Depth (in.)	Clamp Pressure (lbs.)	Spindle Size(in.)	Net Weight (lbs.)
SPARK-DI	JTY 400P					
14215	402-P	0-2-1/8	2-5/8	3,500	9/16	2
14229	403-P	0-3	2-1/2	3,500	5/8	2
14243	404-P	0-4-1/4	3-1/4	6,200	3/4	4
14257	406-P	0-6-1/16	4-1/8	6,600	3/4	5
14271	408-P	0-8-1/4	5	6,900	3/4	8
14285	410-P	2-10-1/8	6	8,000	3/4	10
14299	412-P	2-12-1/4	6-5/16	9,300	7/8	15
SPARK-DI	JTY 400CS H	I-VIS				
20479	H402CS	0 – 2	2	3,500	1/2	2
20481	H403CS	0-3	2-3/8	3,500	5/8	2
20483	H404CS	0 – 4	2-3/4	6,200	3/4	3
20484	H406CS	0-6	3-5/8	6,600	3/4	5
20485	H408CS	0 – 8	4-1/2	6,900	3/4	8
20486	H410CS	2 – 10	5-3/8	8,000	7/8	12
20487	H412CS	2 – 12	5-3/4	9,500	7/8	15

## CLASSIC 400 SERIES™ COLUMBIAN ECONOMY C-CLAMPS

#### SAFE AND ECONOMICAL





DROP FORGED CONSTRICTION



OSCILLATING HEAD



**BLACK OXIDE COATING** 



#### **FEATURES**

#### **DROP FORGED:**

Manufactured for greater strength under regular strength applications

#### **BLACK OXIDE COATING:**

Spindles and pads are treated to resist corrosion

#### **PATENTED DESIGN:**

• Frame geometry allows for maximum strength with greater throat depth and lower weight

Stock No.	Model	Nominal Opening Capacity (in.)	Throat Depth (in.)	Clamp Pressure (lbs.)	Spindle Size (in.)	Net Weight (lbs.)
400 SERI	ES COLUM	BIAN				
20301	H402	0-2	2	3,500	1/2	2
20302	H403	0-3	2-3/8	3,500	5/8	2
20303	H404	0 – 4	2-3/4	6,200	3/4	3
20304	H406	0-6	3-5/8	6,600	3/4	5
20305	H408	0 – 8	4-1/2	6,900	3/4	8
20306	H410	0 – 10	5-3/8	8,000	7/8	12
20307	H412	0 – 12	5-3/4	9,500	7/8	14

- Steel Fabrication
- Industrial Maintenance
- Production
- Repair Operations

## 4400 & 800 SERIES C-CLAMPS

#### **SOUARE THROAT AND STANDARD DEPTH**





PERMA-PADS®



BLACK OXIDE COATING



DROP FORGED CONSTRUCTION



#### NOTE

• 800 Series C-Clamp meets federal spec # GGG-C-406a, Type I, Class A, Grade a, Style 1

#### **FEATURES**

#### **SQUARE THROAT DESIGN** (4400 SERIES):

 Up to 37% more throat depth than standard deep throat C-Clamps

#### PERMA-PADS®:

 Exclusive black oxide coated pad swivels and adapts to angular work pieces for tighter holding

#### **REPLACEABLE PARTS:**

• Both the spindle and PERMA-PADS® are replaceable and can be individually ordered

#### **DROP FORGED:**

 Manufactured for greater strength under regular strength applications

strength applications	

#### **IDEAL FOR**

- Steel Fabrication
- Industrial Maintenance
- Production
- Repair Operations

Stock No.	Model	Nominal Opening Capacity (in.)	Throat Depth (in.)	Clamp Pressure (lbs.)	Spindle Size(in.)	Net Weight (Ibs.)
4400 SERI	ES SQUAI	RE THROAT				
14350	4404	0 – 4	4	4,100	3/4	5
14375	4406	0-6	5	5,400	3/4	6
14400	4408	2-8	6	5,900	3/4	10
800 SERIE	S STAND	ARD DEPTH				
14714	802	0-2	1-13/16	2,700	9/16	1
14728	803	0-3	1-15/16	3,000	9/16	2
14742	804	0-4	2-5/16	3,700	5/8	2
14756	806	0-6	2-15/16	4,500	5/8	4
14770	808	0-8	3-7/16	5,200	3/4	7
14784	810	1-1/2-10	3-3/4	6,000	3/4	8
14798	812	1-1/8-12	3-7/8	8,000	3/4	15

WILTONTOOLS.COM — 61

## 540A SERIES CARRIAGE C-CLAMPS

#### INDUSTRY'S CLASSIC DESIGN





**OSCILLATING HEAD** 



SLIDING CROSS PIN HANDLE



**DUCTILE IRON FRAMES** 



#### **FEATURES**

#### **DUCTILE IRON FRAMES:**

Rugged frames designed for maximum clamping pressure

#### **CLASSIC DESIGN:**

• Most popular C-Clamp for over 50 years

#### **BLACK OXIDE COATING:**

• Spindles and pads are treated to resist corrosion

#### **OSCILLATING HEAD:**

• High quality steel pad is built to last and provide firm gripping action on angular surfaces

- Light Industrial
- Home Craftsman
- Woodworking
- Repair

Stock No.	Model	Nominal Opening Capacity (in.)	Throat Depth (in.)	Clamp Pressure (lbs.)	Spindle Size(in.)	Net Weight (lbs.)
540 SEF	IES CARRIAGE					
22001	540A-2-1/2	0 – 2-1/2	1-3/4	1,110	1/2	1
22002	540A-3	0-3	1-7/8	1,800	1/2	2
22003	540A-4	0 – 4	2-1/16	2,150	5/8	2
22004	540A-5	0-5	2-1/2	2,250	5/8	2
22005	540A-6	0-6	2-3/4	2,450	5/8	3
22006	540A-8	0-8	3-1/4	2,750	3/4	5
22007	540A-10	0 – 10	3-5/8	2,850	7/8	7
22008	540A-12	0 – 12	3-5/8	2,850	7/8	9
22009	540A-14	0 – 14	3-3/4	2,850	7/8	10

## 140 SERIES CARRIAGE C-CLAMPS

#### LIGHT INDUSTRIAL





**DUCTILE IRON FRAMES** 



EXTRA DEEP REACH DESIGN



BLACK OXIDE COATING

XTRA DEEP REACH



#### **FEATURES**

#### **DEEP REACH PATTERN:**

Provided maximum depth for applications requiring increased throat capacity

#### **DUCTILE IRON FRAMES:**

 Rugged frames designed for maximum clamping pressure

#### **BLACK OXIDE COATING:**

• Spindle and pads are treated to resist corrosion

#### **IDEAL FOR**

- · Light Industrial
- · Home Craftsman
- Woodworking
- Repair

Stock		Nominal Opening	Throat	Clamp Pressure	Spindle Size	Net Weight				
No.	Model	Capacity (in.)	Depth (in.)	(lbs.)	(in.)	(lbs.)				
140 SERI	140 SERIES STANDARD CARRIAGE									
41411	141C	0-1	1-1/16	645	1/4	1				
41416	141-1/2C	0 – 1-1/2	1-1/2	820	5/16	1				
41421	142C	0 – 2	1-1/8	800	5/16	1				
41423	1422C	0 – 2-1/2	1-7/16	850	3/8	1				
41426	142-1/2C	0 – 2-1/2	2-1/2	1,005	3/8	1				
41405	143C	0-3	2	1,430	7/16	1				
41406	144C	0 – 4	2-3/4	1,535	1/2	1				
41407	145C	0 – 5	3	1,225	5/8	2				
41408	146C	0-6	3-1/4	1,400	5/8	3				
41409	148C	0 – 8	4	1,700	3/4	4				
DEEP RE	ACH CARRIA	GE								
42510	251	0 – 1	3	350	1/4	1				
42520	252	0 – 2	3-1/2	450	5/16	1				
42525	252-1/2	0 – 2-1/2	4	600	3/8	1				
42530	253	0-3	4-1/2	700	7/16	2				
XTRA DE	EEP REACH CA	ARRIAGE								
42450	245	2-1/2	4-3/4	1,600	7/16	2				
42460	246	2-1/2	6-1/4	1,600	7/16	2				



SUPER SMALL, SUPER TOUGH





ZINC PLATED SCREW



FORGED STEEL FRAMES



NYLON CAPS/FOOT INSERTS

#### **FEATURES**

#### **ZINC PLATED SCREW:**

Steel spindles are treated to resist corrosion extending life

#### **FORGED STEEL FRAMES:**

 Heat treated to provide a strong weight to strength ratio

#### NYLON CAPS / FOOT INSERTS (566/588 JUNIOR):

 Optional feature to protect the work surface from marring

#### **OSCILLATING HEAD:**

• Firm gripping action on angular surfaces

- Light-Duty Clamping
- Pattern and Mold Making
- Aircraft/Aerospace Industry

Stock No.	Model	Nominal Opening Capacity (in.)	Throat Depth (in.)	Clamp Pressure (lbs.)	Spindle Size(in.)	Net Weight (lbs.)			
SUPER JUNIOR®									
21301	50	0 – 1	1	500	_	1			
21302	51	0 – 1	1-1/2	500	<u>-</u>	1			
21303	52	0 – 1-1/4	1-1/4	800	<u> </u>	1			
21304	53	0 – 1-1/2	1-1/2	850		1			
21305	54	0-2	1-1/4	875	_	1			
21306	55	0-3	1-3/8	1,100	_	1			
21307	56	0 – 2-1/2	2-1/2	850	_	1			
566/588 JI	UNIOR®								
22105	H566	0 – 1-1/4	1-1/4	450	1/4	1			
22115	H566N	0 - 1-1/4	1-3/16	550	1/4	1			
22116	H568N	0 – 2-1/2	2-5/16	550	3/4	1			








Stock No.	Model	Spindle Assembly Stock No.	Perma-Pad® witl Ring Stock No.				
BRUTE FORCE O-SERIES							
14518	1 F.C.	20203-35	N/A				
14527	1-1/2 F.C.	20203-35	N/A				
14536	2 F.C.	07142-35	N/A				
14545	3 F.C.	07161-35	N/A				
14554	4 F.C.	07147-35	N/A				
14563	5 F.C.	07162-35	N/A				
14572	6 F.C.	07149-35	N/A				
14581	8 F.C.	07150-35	N/A				
14590	10 F.C.	07151-35	N/A				
14599	12 F.C.	07152-35	N/A				
BRUTE FOR	CE 100 SERIE	S					
14114	102	1700010	2901300				
14128	103	1700020	2901300				
14142	104	1700030	2901310-1				
14156	106	1700030	2901310-1				
14170	108	1700030	2901310-1				
14184	110	1700030	2901310-1				
14198	112	1700030	2901310-1				
CLASSIC 40	O SERIES						
14214	402	1701080	2901300				
14228	403	1701160	2901300				
14242	404	1700150	2901310				
14256	406	1700170	2901310				
14270	408	1700190	2901310				
14284	410	1700190	2901310				
14298	412	1700220	2901310				

Stock No.	Model	Spindle Assembly Stock No.	Perma-Pad® with Ring Stock No.
CLASSIC 400	SERIES HI-	VIS SAFETY	
14300	402-SF	1701080	2901300
14301	403-SF	1701160	2901300
14302	404-SF	1700150	2901310
14303	406-SF	1700170	2901310
14305	408-SF	1700190	2901310
14306	410-SF	1700190	2901310
14307	412-SF	1700220	2901310
SPARK-DUT	Y 400P		
14215	402-P	1701090	2901330
14229	403-P	1701110	2901330
14243	404-P	1700160	2901340
14257	406-P	1700180	2901340
14271	408-P	1700210	2901340
14285	410-P	1700210	2901340
14299	412-P	1700230	2901340
SPARK-DUT	Y 400CS HI-	VIS SAFETY	
20479	H402CS	1701090	2901330
20481	H403CS	1701110	2901330
20483	H404CS	1700160	2901340
20484	H406CS	1700180	2901340
20485	H408CS	1700210	2901340
20486	H410CS	1700210	2901340
20487	H412CS	1700230	2901340

Stock No.	Model	Spindle Assembly Stock No.	Perma-Pad® with Ring Stock No.						
4400 SERIES DEEP THROAT									
14350	4404	1700150	2901310						
14375	4406	1700170	2901310						
14400	4408	1700170	2901310						
800 SERIES S	TANDARD	DEPTH							
14714	802	1701080	2907920						
14728	803	1701160	2907920						
14742	804	1700750	2901320						
14756	806	1700740	2901320						
14770	808	1700190	2907930						
14784	810	1700190	2907930						
14798	812	1700630	2907930						







**SELF CENTERING JAW** 



**VERSATILE MOUNTING** 



**COPPER PLATED SPINDLE** (64000 & 64002 ONLY)

#### **FEATURES**

#### **HEAVY DUTY FRAME:**

• The 90° angle clamp is made of high-quality cast iron (SKUs 64000 and 64002) or solid aluminum construction (SKU 44324)

#### **VERSATILE MOUNTING SLOTS:**

• Slotted holes are provided in the base for convenient workbench mounting

#### PRECISION:

• Work surfaces (including base) are milled for added precision

- Welding
- Woodworking
- Light Industrial

Stock No.	Model	Capacity Miter (in.)	Jaw Height (in.)	Jaw Length (in.)	Net Weight (lbs.)			
HEAVY-DUTY STEEL ANGLE CLAMPS								
64000	AC-325	3-11/32	1-3/8	4-1/8	11			
64002	AC-326	4-3/8	2-3/8	4-1/8	21			
REGULAR-DUTY ALUMINUM ANGLE CLAMP								
44324	AC-324	2-3/4	1-3/8	2-1/4	3			



## **SPECIALTY CLAMPS**



#### EXTRA DEEP STEEL PIPE CLAMP

- Ideal for any applications where extra deep-reach is required
- Moveable and stationary parts are made of heavy-duty, ductile cast iron for added strength
- Multiple disc clutch provides sliding jaws with instant adjustment, secure hold and quick release
- 2-Piece design universal fit for any 3/4" pipe



#### THE GRIPPER

- · Non-conductive and static free
- · Fiberglass reinforced nylon design
- Light 0.1 lb weight still exerts a high clamping force of 80 PSI

#### **REGULAR-DUTY I BAR CLAMPS**

- A rapid acting powerful clamp designed and constructed for hard, everyday production work
- Patented, quick action, no slip clutches are 3/4" apart and formed in the web for greater bar strength
- High strength ductile slide cannot slip or bind, easily released
- Steel handle, with comfortable wood crank handle for fast clamping
- Bar dimension is 7/16" x 1-1/2" x 5/32", screw diameter is 5/8"

Stock No.	Pipe Size (in.)	Clamp Face (in.)	Net Weight (lbs.)		
EXTRA DEEP PIPE CLAMP					
14870	3/4	2 x 1-3/4	8		

Stock No.	Clamp Pressure (PSI)	Grounding Hole Diameter (in.)	Net Weight (Ibs.)
THE GRIF	PPER		
40105	80	1/4	1

Stock No.	Bar Length (ft.)	Throat Depth (in.)	Clamp Face (in.)	Clamp Pressure (lbs.)	Net Weight (lbs.)
I BAR	CLAMPS				
21801	2	1-13/16	1-7/8	6,000	8
21803	3	1-13/16	1-7/8	6,000	8
21804	4	1-13/16	1-7/8	6,000	10
21805	5	1-13/16	1-7/8	6,000	13
21806	6	1-13/16	1-7/8	6,000	14





## WILTON B.A.S.H®

THE WORLD'S MOST DURABLE STRIKING TOOLS





At Wilton®, we are on a never-ending journey to create the highest quality, most indestructible tools on the market. On this journey we've managed to design patents for the world's most durable hammers with Unbreakable® Handle Technology, revolutionary design, and engineered no-slip rubber grip.





### THE WORLD'S MOST DURABLE SLEDGE HAMMER

## A: UNBREAKABLE® HANDLE TECHNOLOGY

Steel core design prevents breaking during overstrikes

#### **B: SAFETY PLATE**

Locks head firmly to handle eliminating dislodging

#### C: NO-SLIP GRIP

Textured handle for secure grip while striking

#### D: TRADEMARK GREEN HEAD

Hi-Vis, Drop forged 46 HRC head endures the most demanding applications and adds instant identification.





#### **FLAT HEAD**

CONVENIENTLY DESIGNED TO STAND UPRIGHT FOR EASY REACH



#### ANTI-VIBE NECK

ERGONOMICALLY DESIGNED TO PREVENT INJURY FROM REPEATED JOB SITE USE



#### LANYARD HOLE

SAFELY SECURE SLEDGE HAMMER TO YOUR WRIST

## BAD ASS... & WE'LL PROVE IT

400% TOUGHER...

STRIKE AFTER STRIKE THE RESULTS SPEAK FOR THEMSELVES

**OVERSTRIKE TEST** Number of mechanical overstrikes before handle breaks

NUMBER OF OVERSTRIKES



WOOD

**FIBERGLASS** 



#### **SLEDGE HAMMER TYPE**



#### **WE PUT OUR MONEY WHERE OUR MOUTH IS**

The WILTON B.A.S.H® Sledge Hammer with Unbreakable™ Handle Technology is quite simply the most durable hammer on the market, outperforming wood and fiberglass handled hammers strike after strike. We are so confident in the WILTON B.A.S.H® Unbreakable® Technology that for 2 full years after purchase, break the handle of a B.A.S.H® Sledge Hammer under normal wear and tear and receive \$1,000.

FOR COMPLETE GUARANTEE DETAILS VISIT YOUR LOCAL DEALER OR WILTONTOOLS.COM.



Wilton Unbreakable® Handled Sledgehammers meet ANSI Specifications: "Hand Tools – Heavy Striking Tools Safety Requirements'

# B.A.S.H<sup>®</sup> SLEDGE HAMMERS

#### THE WORLD'S MOST DURABLE SLEDGE HAMMER



#### **DURABILITY & SAFETY FEATURES**

#### UNBREAKABLE® HANDLE TECHNOLOGY:

 Steel core eliminates breaking during overstrikes

#### **TRADEMARK GREEN HEAD:**

 Patented hi-vis drop forged 46 HRC head endures the most demanding applications

#### **SAFETY PLATE:**

 Secures head to handle preventing head from dislodging

#### **ANTI-VIBE NECK:**

• Thick, tapered neck absorbs vibration reducing worker fatigue

#### **NO-SLIP GRIP:**

Vulcanized rubber handle for secure grip while striking

#### **LANYARD HOLE:**

 Safely secure hammer to wrist or stationary object

Stock No.	Head Size (Ibs.)	Handle Size (in.)	Net Weight (Ibs.)
B.A.S.H®	SLEDGE HAM	IMERS (46 HRC	C)
20212	2-1/2	12	4
20412	4	12	5
20416	4	16	6
20424	4	24	6
20616	6	16	8
20624	6	24	9
20630	6	30	10
20636	6	36	11
20816	8	16	11
20824	8	24	11
20830	8	30	12
20836	8	36	13

- Demolition Work
- Fracturing Stone and Concrete
- Driving Fence Posts
- Police, Fire & Rescue







UNBREAKABLE® HANDLE TECHNOLOGY



**SAFETY PLATE** 



ANTI-VIBE NECK

#### B.A.S.H® SOFT FACE

Stock No.	Head Size (Ibs.)	Handle Size (in.)	Net Weight (lbs.)
B.A.S.H®	SLEDGE HAN	MERS (46 HR	C)
21016	10	16	13
21024	10	24	13
21030	10	30	15
21036	10	36	15
21224	12	24	16
21230	12	30	17
21236	12	36	18
21424	14	24	18
21430	14	30	19
21436	14	36	20
22024	20	24	24
22030	20	30	25
22036	20	36	27

Stock No.	Head Size (Ibs.)	Handle Size (in.)	Net Weight (Ibs.)
	SOFT FACE IAMMERS (30	D HRC)	
40212	2-1/2	12	4
40412	4	12	5
40416	4	16	6
40624	6	24	9
40636	6	36	11
40824	8	24	11
40836	8	36	11
41036	10	36	15
41236	12	36	18
41436	14	36	20

- Maintenance on hard metal surfaces
- Mining
- Cutting Tools



# B.A.S.H<sup>®</sup> BRASS SLEDGE HAMMERS

THE WORLD'S MOST DURABLE





UNBREAKABLE® HANDLE TECHNOLOGY



**SAFETY PLATE** 



**ANTI-VIBE NECK** 



NON-SPARKING BRASS HEAD

#### **DURABILITY & SAFETY FEATURES**

#### UNBREAKABLE® HANDLE TECHNOLOGY:

 Steel core eliminates breaking during overstrikes

#### **BRASS HEAD:**

 Non-sparking for use near combutible materials and nonmarring to reduce work damage

#### **SAFETY PLATE:**

 Secures head to handle preventing head from dislodging

#### ANTI-VIBE NECK:

 Thick, tapered neck absorbs vibration reducing worker fatigue

#### **NO-SLIP GRIP:**

 Vulcanized rubber handle for secure grip while striking

#### **LANYARD HOLE:**

 Safely secure hammer to wrist or stationary object

Stock No.	Head Size (Ibs.)	Handle Size (in.)	Net Weight (lbs.)
B.A.S.H® E	BRASS SLEDGE	HAMMERS	
90212	2.5	12	4
90412	4	12	5
90416	4	16	6
90616	6	16	8
90816	8	16	10
90830	8	30	12

- Use near combustible materials
- Where surface protection is required
- Oil & gas

- Mining
- Aerospace



## B.A.S.H®BALL & CROSS PEIN HAMMERS

THE WORLD'S MOST DURABLE







UNBREAKABLE® HANDLE TECHNOLOGY



SAFETY PLATE



ANTI-VIBE NECK

#### **DURABILITY & SAFETY FEATURES**

#### UNBREAKABLE® HANDLE TECHNOLOGY:

 Steel core eliminates breaking during overstrikes

#### SAFETY PLATE:

 Secures head to handle preventing head from dislodging

#### **ANTI-VIBE NECK:**

• Thick, tapered neck absorbs vibration reducing worker fatigue

#### **NO-SLIP GRIP:**

Vulcanized rubber handle for secure grip while striking

#### TRADEMARK GREEN HEAD:

 Patented hi-vis drop forged 46 HRC head endures the most demanding applications

#### **LANYARD HOLE:**

 Safely secure hammer to wrist or stationary object

Stock No.	Head Size (oz.)	Handle Size (in.)	Net Weight (lbs.)
B.A.S.H®	BALL PEIN H	AMMERS	
32414	24	14	2
33214	32	14	3
34014	40	14	3
B.A.S.H®	CROSS PEIN	HAMMERS	
30216	24	16	3
30316	32	16	4

#### **IDEAL FOR**

- Light Forging
- Bending
- Forming
- Peining



WILTONTOOLS.COM

# B.A.S.H® DEAD BLOW HAMMERS

THE WORLD'S MOST DURABLE





DEAD BLOW



**SOFT FACE** 



SPARK-RESISTANT

#### **DURABILITY & SAFETY FEATURES**

#### **DEAD BLOW:**

 Eliminates bounce back when striking hardened surfaces

#### SPARK-RESISTANT:

 Safe for use near combustible materials no exposed metal on face, head or shaft

#### **SOFT FACE:**

Helps prevent marring

#### UNBREAKABLE® HANDLE TECHNOLOGY:

Steel core eliminates breaking during overstrikes

#### **ERGONOMIC HANDLE:**

Shaped and thickened for improved comfort and less vibration

#### **NO-SLIP GRIP:**

 Vulcanized rubber handle for secure grip while striking

#### **LANYARD HOLE:**

 Safely secure hammer to wrist or stationary object

Stock No.	Hammer Weight (lbs.)	Handle Size (in.)
B.A.S.H®	DEAD BLOW	HAMMERS
55114	1-1/2	14
55214	2	14
55314	3	14
55416	4	16
55830	8	30



- Automotive
- Metal Fabrication
- Oil and Mining
- Wood and Metal Assembly
- Aerospace Industry



## B.A.S.H<sup>®</sup> SPIKE & SPLITTING MAULS

#### THE WORLD'S MOST DURABLE





**UNBREAKABLE® HANDLE TECHNOLOGY** 



**SAFETY PLATE** 



**ANTI-VIBE NECK** 

#### **DURABILITY & SAFETY FEATURES**

#### UNBREAKABLE® HANDLE TECHNOLOGY:

· Steel core eliminates breaking during overstrikes

#### SAFETY PLATE:

· Secures head to handle preventing head from dislodging

#### ANTI-VIBE NECK:

 Thick, tapered neck absorbs vibration reducing worker fatigue

#### **NO-SLIP GRIP:**

· Vulcanized rubber handle for secure grip while striking

#### TRADEMARK GREEN HEAD:

• Patented hi-vis drop forged 46 HRC head endures the most demanding applications

#### LANYARD HOLE:

· Safely secure hammer to wrist or stationary object

Stock No.	Head Size (Ibs.)	Handle Size (in.)	Net Weight (lbs.)
B.A.S.H®	SPIKE MAUL		
31036	10	36	14
B.A.S.H®	SPLITTING N	MAUL	
50630	6	30	9
50636	6	36	10
50830	8	30	11
50836	8	36	11

#### **IDEAL FOR**

- Driving Railroad Spikes (Spike Maul)
- Splitting Wood (Splitting Maul)
- Striking Wedges (Splitting Maul)



WILTONTOOLS.COM 77

# B.A.S.H<sup>®</sup> 3 PC HAMMER KIT

#### THE WORLD'S MOST DURABLE



#### **DURABILITY & SAFETY FEATURES**

#### UNBREAKABLE® HANDLE TECHNOLOGY:

Steel core eliminates breaking during overstrikes

#### **SAFETY PLATE:**

 Secures head to handle preventing head from dislodging

#### **ANTI-VIBE NECK:**

 Thick, tapered neck absorbs vibration reducing worker fatigue

#### **NO-SLIP GRIP:**

 Vulcanized rubber handle for secure grip while striking

#### TRADEMARK GREEN HEAD:

 Patented hi-vis drop forged 46 HRC head endures the most demanding applications

#### **LANYARD HOLE:**

 Safely secure hammer to wrist or stationary object

Stock No.	Qty.	Description
B.A.S.H®	3-Pied	ce Hammer Kit 3PCBASH
20212	1	2-1/2 Lb. Head, 12" Handle Hammer
32414	1	24 Oz. Head, 14" Handle Ball Pein Hammer
30216	1	2 Lb. Head, 16" Handle Cross Pein Hammer
	1	Protective Carrying Case

# DUCTILE IRON & ALUMINUM PIPE WRENCHES

#### **HEAVY-DUTY AND BUILT TO LAST**





**DROP FORGED JAWS** 



DUCTILE CAST IRON HANDLE



HEAVY-DUTY
ADJUSTABLE RING



LIGHTWEIGHT ALUMINUM BODY

#### **DUCTILE FEATURES**

#### JAW CONSTRUCTION

Drop forged upper and lower jaws

#### IAW TVDE

Floating hook jaw with spring suspension for easier gripping

#### **RING AND HANDLE:**

Heavy-Duty adjustable ring and ductile cast iron handle

#### **CAPACITY:**

• 1.5" to 5"

Stock No.	Description	Pipe Capacity (in.)	Net Weight (lbs.)		
WILTON® DUCTILE IRON PIPE WRENCHES					
38110	10" Ductile Pipe Wrench	1-1/2	2		
38114	14" Ductile Pipe Wrench	2	4		
38118	18" Ductile Pipe Wrench	2-1/2	6		
38124	24" Ductile Pipe Wrench	3	9		
38136	36" Ductile Pipe Wrench	5	21		

#### **ALUMINUM FEATURES**

#### HANDLE CONSTRUCTION

· High quality cast aluminum body

#### JAWS.

Drop forged upper and lower jaws

#### **ADJUSTING RING**

Heavy-Duty adjustable ring

#### CAPACITY:

• 1.5" to 5"

Stock No.	Description	Pipe Capacity (in.)	Net Weight (lbs.)
WILTON® ALUMINUM PIPE WRENCHES			
38210	10" Aluminum Pipe Wrench	1-1/2	1
38214	14" Aluminum Pipe Wrench	2	2
38218	18" Aluminum Pipe Wrench	2-1/2	4
38224	24" Aluminum Pipe Wrench	3	6
20226	26" Aluminum Pina Wrongh	5	11





### **HOLDING STRONG SINCE 1941**

WILTONTOOLS.COM