

PF-25 PUMP CHECK FLAP VALVE

FOR PUMP DISCHARGE

- EASY-ON COMPRESSION MOUNTING OR STANDARD 125# FLANGE FRAME
- CAST IRON OR ALUMINUM FLAP COVER
- GROUND NEOPRENE, BRONZE, OR IRON SEATS FOR TIGHT SEALING
- 7½° SEATING ANGLE
- FULL-OPENING

USES:

Model PF-25 Pump Flap Valve is furnished in various styles to fit most installation needs. The popular compression mounting style uses time-proven Wedge-Lock seals and fits standard ASA pipe sizes as well as SDR-35. The PF-25 Pump Flap Valve is also available with a flanged frame drilled for 125# standard mounting.

FEATURES:

The body is cast iron. Hinge bars, bearing washers and cotter pins are brass. There are positive stops to prevent jamming. The modest price of this free-opening, tight-closing valve makes it a noteworthy unit.

Compression style available in 4" - 14" diameter.

Flange style available in 4" - 24" diameter.

For Model PF-25W, specify gaskets for:

standard size pipe (O.D. sizes 4½", 6½", 8⅝", 10¾", 12¾", 14"),

O.D. size pipe (O.D. size is nominal, i.e. 10" = 10")

or SDR-35.



Model PF-25W
Compression Style



Model PF-25F
Flanged Style