

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 18.07.2018

Version number 27

Revision: 11.07.2018

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier**Product name:** Hardcheck P**Catalog number:** 00515661, (4)515660BT, (4)515661BT, (4)515663(0), 00515669BT**1.2 Relevant identified uses of the substance or mixture and uses advised against****Application of the substance / the preparation:** Reagent for water analysis**1.3 Details of the supplier of the safety data sheet****Supplier:**

Tintometer GmbH
Schleefstraße 8-12
44287 Dortmund
Made in Germany
www.lovibond.com

phone: +49 231 94510-0
e-mail: sales@tintometer.de

Tintometer GmbH
Division AQUALYTIC®
Schleefstr. 12
44287 Dortmund
Made in Germany
www.aqualytic.de

phone: +49 231 94510-755
e-mail: sales@aqualytic.de

The Tintometer Limited
Lovibond® House
Sun Rise Way
Amesbury
Wiltshire SP4 7GR
United Kingdom

phone : +44 1980 664800
e-mail: SDS@tintometer.com

Informing department:

e-mail: sds@tintometer.de
Product Safety Department

1.4 Emergency telephone number:

+44 1235 239670
Languages: English

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture**Classification according to Regulation (EC) No 1272/2008**

The product is not classified as hazardous according to the CLP regulation.

2.2 Label elements**Labelling according to Regulation (EC) No 1272/2008** Void**Hazard pictograms** Void**Signal word** Void**Hazard statements** Void**2.3 Other hazards** No further relevant information available.**Results of PBT and vPvB assessment**

This mixture does not contain any substances that are assessed to be persistent, bioaccumulative and toxic (PBT) or very persistent and very bioaccumulative (vPvB), according to the criteria given in Annex XIII of Regulation (EC) No. 1907/2006.

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 18.07.2018

Version number 27

Revision: 11.07.2018

Product name: Hardcheck P

(Contd. of page 1)

SECTION 3: Composition/information on ingredients

- **3.2 Mixtures**
- **Description:** Mixture of organic and inorganic compounds
- **Dangerous components:** Void

SECTION 4: First aid measures

- **4.1 Description of first aid measures**
- **General information** Instantly remove any clothing soiled by the product.
- **After inhalation** Supply fresh air.
- **After skin contact** Instantly wash with water and soap and rinse thoroughly.
- **After eye contact**
Rinse opened eye for several minutes under running water (at least 15 min). If symptoms persist, consult doctor.
- **After swallowing**
Rinse out mouth and then drink 1-2 glasses of water.
In case of persistent symptoms consult doctor.
- **4.2 Most important symptoms and effects, both acute and delayed:** No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed:** No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents** Use fire fighting measures that suit the environment.
- **5.2 Special hazards arising from the substance or mixture**
The product is not combustible.
Formation of toxic gases is possible during heating or in case of fire.
nitrous gases
Phosphorus oxides (PxOx)
Carbon monoxide (CO) and carbon dioxide (CO₂)
- **5.3 Advice for firefighters**
- **Protective equipment:**
Wear self-contained breathing apparatus.
Wear full protective suit.
- **Additional information**
Collect contaminated fire fighting water separately. It must not enter drains.
Dispose of fire debris and contaminated fire fighting water in accordance with official regulations.
Ambient fire may liberate hazardous vapours.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
- **Advice for non-emergency personnel:** No special measures required.
- **Advice for emergency responders:** Protective equipment: see section 8
- **6.2 Environmental precautions:** Do not allow product to reach sewage system or water bodies.
- **6.3 Methods and material for containment and cleaning up:**
Ensure adequate ventilation.
Collect mechanically.
Dispose of contaminated material as waste according to item 13.
- **6.4 Reference to other sections**
See Section 8 for information on personal protection equipment.
See Section 13 for information on disposal.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling**
- **Advice on safe handling:** Prevent formation of dust.
- **Hygiene measures:**
The usual precautionary measures should be adhered to general rules for handling chemicals.
Wash hands during breaks and at the end of the work.

(Contd. on page 3)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 18.07.2018

Version number 27

Revision: 11.07.2018

Product name: Hardcheck P

(Contd. of page 2)

Do not eat, drink or smoke when using this product.

7.2 Conditions for safe storage, including any incompatibilities**Storage****Requirements to be met by storerooms and containers:** Store in cool location.**Information about storage in one common storage facility:** Not required.**Further information about storage conditions:**

Protect from heat and direct sunlight.

Protect from the effects of light.

Store under dry conditions.

Protect from humidity and keep away from water.

Recommended storage temperature: 20°C +/- 5°C**7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters**Components with limit values that require monitoring at the workplace:**

The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.

Additional information: The lists that were valid during the compilation were used as basis.**8.2 Exposure controls****Engineering measures:**

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

See item 7.

Personal protective equipment**Breathing equipment:** Use breathing protection against the effects of fumes/dust/aerosol.**Recommended filter device for short term use:** Filter P1**Protection of hands:**

Preventive skin protection by use of skin-protecting agents is recommended.

After use of gloves apply skin-cleaning agents and skin cosmetics.

Material of gloves

nitrile rubber, NBR

Recommended thickness of the material: ≥ 0.11 mm**Penetration time of glove material**

Value for the permeation: Level = 1 (< 10 min)

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

Eye protection:

Safety glasses

use against the effects of fumes / dust

Body protection: Protective work clothing.**Limitation and supervision of exposure into the environment:** Do not allow product to reach sewage system or water bodies.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties**Appearance:**

Form / Physical state:	Tablets
Colour:	Light beige

Odour:	Odourless
Odour threshold:	Not applicable

pH-value (10 g/l) at 20°C:	9.9
-----------------------------------	-----

Melting point/Freezing point:	Not determined
Initial boiling point and boiling range:	Not determined

Flash point:	Not applicable
---------------------	----------------

Flammability (solid, gas):	The product is not combustible.
-----------------------------------	---------------------------------

Decomposition temperature:	Not determined.
-----------------------------------	-----------------

(Contd. on page 4)

GB

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 18.07.2018

Version number 27

Revision: 11.07.2018

Product name: Hardcheck P

(Contd. of page 3)

· Auto-ignition temperature:	Product is not self-igniting.
· Explosive properties:	Product is not explosive.
· Flammability or explosive limits:	
Lower:	Not determined.
Upper:	Not determined.
· Oxidising properties:	none
· Vapour pressure:	Not applicable.
· Density at 20°C:	1.6 g/cm ³
· Relative density:	Not determined.
· Vapour density:	Not applicable.
· Evaporation rate:	Not applicable.
· Solubility(ies):	
Water:	Partially insoluble.
· Partition coefficient: n-octanol/water:	Not applicable.
· Viscosity:	Not applicable.
· dynamic:	Not applicable.
· kinematic:	Not applicable.
· Solvent content:	
Organic solvents:	0.0 %
Solids content:	100.0 %
· 9.2 Other information	No further relevant information available.

SECTION 10: Stability and reactivity

- **10.1 Reactivity** Dust can combine with air to form an explosive mixture.
- **10.2 Chemical stability** Stable at ambient temperature (room temperature).
- **10.3 Possibility of hazardous reactions** Reacts with oxidizing agents
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:**
Nitrogen oxides (NOx)
see section 5

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.
- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)** The following statements refer to the mixture:
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT (specific target organ toxicity) -single exposure** Based on available data, the classification criteria are not met.
- **STOT (specific target organ toxicity) -repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.
- **Additional toxicological information:**
When used and handled according to specifications, the product does not have any harmful effects according to our experience and the information provided to us.

GB
(Contd. on page 5)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 18.07.2018

Version number 27

Revision: 11.07.2018

Product name: Hardcheck P

(Contd. of page 4)

SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **12.5 Results of PBT and vPvB assessment**
This mixture does not contain any substances that are assessed to be persistent, bioaccumulative and toxic (PBT) or very persistent and very bioaccumulative (vPvB), according to the criteria given in Annex XIII of Regulation (EC) No. 1907/2006.
- **12.6 Other adverse effects**
Depending on the concentration, phosphorus and/or nitrogen compounds may contribute to the eutrophication of water supplies.
- **Water hazard:**
Do not allow undiluted product or large quantities of it to reach ground water, water bodies or sewage system.
Must not reach sewage water or drainage ditch undiluted or unneutralised.

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation**
Must not be disposed of together with household garbage. Do not allow product to reach sewage system.
Disposal must be made according to official regulations.
- **European waste catalogue**
16 05 09 | discarded chemicals other than those mentioned in 16 05 06, 16 05 07 or 16 05 08
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.
- **Recommended cleaning agent:** Water, if necessary with cleaning agent.

* SECTION 14: Transport information

• 14.1 UN-Number	
• ADR, IMDG, IATA	Void
• 14.2 UN proper shipping name	
• ADR	Void
• IMDG, IATA	Void
• 14.3 Transport hazard class(es)	
• ADR, IMDG, IATA	
• Class	Void
• 14.4 Packing group	
• ADR, IMDG, IATA	Void
• 14.5 Environmental hazards:	
• Marine pollutant:	No
• 14.6 Special precautions for user	Not applicable.
• 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code	Not applicable.
• Transport/Additional information:	Not dangerous according to the above specifications.

SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Regulation (EC) No 1005/2009 on substances that deplete the ozone layer:**

None of the ingredients is listed.

(Contd. on page 6)

GB

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 18.07.2018

Version number 27

Revision: 11.07.2018

Product name: Hardcheck P

(Contd. of page 5)

- **Directive 2012/18/EU (SEVESO III):**
- **Named dangerous substances - ANNEX I** None of the ingredients is listed.
- **Information about limitation of use:** Not required.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

These data are based on our present knowledge. However, they shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Training hints** Provide adequate information, instruction and training for operators.
- **Abbreviations and acronyms:**
 - IATA-DGR: Dangerous Goods Regulations by the "International Air Transport Association" (IATA)
 - ICAO: International Civil Aviation Organisation
 - ICAO-TI: Technical Instructions by the "International Civil Aviation Organisation" (ICAO)
 - EC50: effective concentration, 50 percent (in vivo)
 - STOT: specific target organ toxicity
 - SE: single exposure
 - RE: repeated exposure
 - EC50: half maximal effective concentration
 - IC50: half maximal inhibitory concentration
 - NOEL or NOEC: No Observed Effect Level or Concentration
 - ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
 - RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)
 - IMDG: International Maritime Code for Dangerous Goods
 - IATA: International Air Transport Association
 - GHS: Globally Harmonised System of Classification and Labelling of Chemicals
 - EINECS: European Inventory of Existing Commercial Chemical Substances
 - ELINCS: European List of Notified Chemical Substances
 - CAS: Chemical Abstracts Service (division of the American Chemical Society)
- **Sources**
 - Data arise from safety data sheets, reference works and literature.
 - RTECS (Registry of Toxic Effects of Chemical Substances)

GB