

# D-060 NS PN 16 D-060-C NS PN 16 D-062 NS PN 25 D-065 NS PN 40





## Non Slam Combination Air Valve for High Flow

### **Description**

The D-060 NS series Combination Air Valve is a surge-dampening, slam-preventing, 3-stage combination air valve.

It has the features of both an air release valve and an air & vacuum valve.

The air release component is designed to automatically release small pockets of air to the atmosphere as they accumulate along a pipeline or piping system when it is full and operating under pressure. The air & vacuum component is designed to automatically discharge or admit large volumes of air during the filling or draining of a

pipeline or piping system. This valve will open to relieve negative pressures whenever water column separation occurs.

### **Applications**

- Water pipelines with anticipated conditions of surge and water
- On the peaks of water pipelines with steep slopes.
- Water pipelines where water column separation occurs.

### **D-060-C** - additional applications

- Water pipelines vulnerable to vandalism and/or water theft.
- Water systems found in remote areas.

D-062 NS and D-065 NS - additional applications

- Water systems with pressure demands of 25 bar and 40 bar (D-062 NS and D-065 NS respectively).

### Operation

The D-060 NS series Combination Non Slam Air Valve is a surge-dampening, slam-preventing, 3-stage combination air valve.

The air valve provides high capacity vacuum protection and, at the same time, efficient surge suppression.

At sudden drainage and/or water column separation (sudden pump trips or valve closure, for instance), the air & vacuum orifice admits air at high flow rates, thus preventing vacuum.

As the water column and/or pressure wave returns, large volumes of air are discharged at high velocities, raising the non-slam disc, partially closing the air & vacuum orifice and allowing air to exhaust slowly through the smaller orifice of the non-slam disc.

This slowly exhausting air pocket dampens the slam of the returning water column, thus suppressing the pressure surge. As the water flow arrives at a much slower rate, dampened by the slower air discharge, it buoys up the main float, gently closing the air & vacuum component of the air valve.

The S-050-C, S-052, S-015 air release component continues releasing air while the pipeline and the air valve are pressurized.

### **Main Features**

- Working pressure range:

D-060 NS: 0.2 -16 bar D-060-C NS: 0.2 - 16 bar D-062 NS: 0.2 - 25 bar

D-065 NS: 0.2 - 40 bar

- Testing pressure for the air valve is 1.5 times its working pressure.
- Maximum working temperature: 60° C.
- Maximum intermittent temperature: 90° C.
- All main flow cross-sections are equal or greater than the nominal port area.
- Aerodynamic design enables high flow rates of air both at intake and at discharge.
- Reliable operation reduces water hammer incidents.
- Dynamic design allows for high capacity air discharge while preventing premature closure.
- Special orifice seat design: bronze and E.P.D.M. rubber, assures long-term maintenance-free operation.
- Screen protected outlet.
- The upper screen is protected with a protective cover.

### Air Release Component

- Body made of high strength materials.
- All operating parts are made of specially selected corrosion-resistant polymer materials.
- Large sized air release orifice:
- Dramatically reduces the possibility of obstruction by debris.
- Discharges high air flow rates.
- One size orifice for a wide pressure range (up to 40 bar), achieved by the rolling seal mechanism.

### **Valve Selection**

- Size Range: 1"- 10"

2" - 8" (for model D-065 NS only)

- D-060 NS, rated for 16 bar
- D-060-C NS vandalism protected by a metal shell covering the air release component, rated for 16 bar.
- D-062 NS vandalism protected by a metal shell covering the air release component, rated for 25 bar.
- D-065 NS, rated for 40 bar.



- These valves are manufactured with flanged ends to meet any requested standard.
- The 2" valve is also available with a threaded BSP or NPT connection.
- Valve coating: fusion bonded epoxy coating in compliance with the standard DIN 30677-2.
- Other coatings are available upon request.
- The automatic air release component and the air & vacuum component are available as separate units.
- For best suitability, it is recommended to send the fluid chemical properties along with the valve request.

### **Non-Slam Disc**

The built- in throttling device on the Non-Slam disc of the D-060 NS Combination Air Valves will allow for the graduated opening and closing of the disc orifice.


### Advantages:

- 1. The orifice size of the disc can be adjusted to control and throttle the discharge of air during pipeline filling and during the return of the water column after separation.
- 2. The controlled discharge of air will reduce surge effects and provide for a silent closure of the air valve.
- 3. The closure of the orifice can be determined by running a surge analysis or by a decision taken in the field.
- 4. The orifice throttling device allows for a wide range of options from 100% open, partially open, partially closed to 100% closed.

### **Note**

For best suitability, it is recommended to send the fluid chemical properties along with the valve request.


Upon ordering, please specify: model, size, working pressure, threads standard and type of liquid.




### D-060 NS / D-060-C NS AUTOMATIC AIR RELEASE FLOW RATE



### D-062 NS AUTOMATIC AIR RELEASE FLOW RATE



### D-065 NS AUTOMATIC AIR RELEASE FLOW RATE



D-060 Non-Slam Orifice Data Table


Nominal Size	Discharge orifice mm	Total NS area mm²	NS orifice mm	Switching point cm	Flow at 0.4 bar m³/h
1" (25 mm)	37.5	12.6	4	Spring loaded normally closed	17.5
2" (50mm)	50	63	9	10	90
3" (80mm)	75	175.4	15	23	240
4" (100mm)	100	476.4	24.5	23	350
6" (150mm)	150	900.6	34	23	600
8" (200mm)	200	1696.9	46.5	30	1200
10" (250mm)	250	1575.7	45	25	5100



### **AIR & VACUUM FLOW RATE**




### AIR DISCHARGE SWITCHING REGION




Flow Rate [m³/h]


### **AIR & VACUUM FLOW RATE**




### AIR DISCHARGE SWITCHING REGION



### **AIR & VACUUM FLOW RATE**



### **AIR DISCHARGE SWITCHING REGION**





### **D-060 DIMENSIONS AND WEIGHTS**

Nominal	Dimer	nsions mm	Connections		Weight	Orifice A	Area mm²
Size	Α	В	С	D	Kg.	A/V	Auto.
1" (25mm) Threaded	250	303	1/8" BSP Female	1½" BSP Female	4.4	506.7	12
1" (25mm) Flanged	250	303	1/8" BSP Female	$1\frac{1}{2}$ " BSP Female	5.4	506.7	12

Nominal	Dime	nsions mm	Connection	Weight	Orifice A	rea mm²
Size	Α	В	С	Kg.	A/V	Auto.
2" (50mm) Threaded	215	367	1/8" BSP Female	14	1960	12
2" (50mm) Flanged	215	350	1/8" BSP Female	14	1960	12
3" (80mm)	249	422	1/8" BSP Female	21	5030	12
4" (100mm)	286	465	1/8" BSP Female	29	7850	12
6" (150mm)	375	689	1/8" BSP Female	78	17662	12
8" (200mm)	463	849	1/8" BSP Female	156	31400	12
10" (250mm)	586	993	1/8" BSP Female	291	49087	12



### D-060-C / D-062 DIMENSIONS AND WEIGHTS

Nominal	Dimensions mm		Connections		Weight	Ori	fice Area mm²	
Size	Α	В	С	D	Kg.	A/V	D-060-C Auto.	D-062
1" (25mm) Threaded	250	311	1/8" BSP Female	1½" BSP Female	5.3	506.7	12	9
1" (25mm) Flanged	250	311	1/8" BSP Female	1½" BSP Female	6.3	506.7	12	9

Nominal	Dimens	ions mm	Connection	Weight	Ori	fice Area mm²	!
Size	A	В	С	Kg.	A/V	D-060-C Auto.	D-062
2" (50mm) Threaded	209	375	1/8" BSP Female	15	1960	12	9
2" (50mm) Flanged	209	362	1/8" BSP Female	15	1960	12	9
3" (80mm)	243	430	1/8" BSP Female	22	5030	12	9
4" (100mm)	280	473	1/8" BSP Female	30	7850	12	9
6" (150mm)	375	700	1/8" BSP Female	93	17662	12	9
8" (200mm)	463	800	1/8" BSP Female	157	31400	12	9
10" (250mm)	586	987	1/8" BSP Female	292	49087	12	9



### **D-065 DIMENSIONS AND WEIGHTS**

Nominal	Dimen	sions mm	Connection	Weight	Orifice A	rea mm²
Size	Α	В	С	Kg.	A/V	Auto.
2" (50mm) Threaded	246	519	1/2" BSP Female	15.3	1960	15
2" (50mm) Flanged	246	506	1/2" BSP Female	16.9	1960	15
3" (80mm)	280	572	1/2" BSP Female	25.5	5030	15
4" (100mm)	317	616	1/2" BSP Female	35	7850	15
6" (150mm)	382	774	1/2" BSP Female	94.9	17662	15
8" (200mm)	476	973	1/2" BSP Female	151.9	31400	15






### 1" PARTS LIST AND SPECIFICATION

No. Part	Material
1. Body	Reinforced Nylon
2. Air Release Outlet	Polypropylene
3. Rolling Seal	EPDM
4. Clamping Stem	Reinforced Nylon
5. Float	Foamed Polypropylene
6. O-Ring	BUNA-N
7. Base	Reinforced Nylon
8. Strainer	Nylon
9. Cover	Ductile Iron
10. One Way Check Valve	Acetal
11. Orifice Seat	Bronze
12. Orifice Seal	EPDM
13. Bolt, Nut & Washer	Steel, Zinc Cobalt Coated
14. O-Ring	BUNA-N
15. Body	Ductile Iron
16. Float	Polycarbonate /Stainless Steel
17. Discharge Outlet	Polypropylene








### 2"-10" PARTS LIST AND SPECIFICATION

No	.Part	Material
1.	Body	Reinforced Nylon
2.	Air Release Outlet	Polypropylene
3.	Rolling Seal	EPDM
4.	Clamping Stem	Reinforced Nylon
5.	Float	Foamed Polypropylene
6.	O-Ring	BUNA-N
7.	Base	Brass
8.	Strainer	Nylon
9.	Domed Nut & Washer	Stainless Steel 304
10.	Screen Cover	Polyethylene / Ductile Iron
11.	Threaded Rod	Stainless Steel 304
12.	Screen	Stainless Steel 304
13.	Cover	Ductile Iron
14.	Ring	Stainless Steel 316
15.	Non-Slam Disc 2"-4"	Stainless Steel 316
	6"-10"	Ductile Iron
16.	Bolt, Nut & Washer	Steel, Zinc Cobalt Coated
17.	Orifice Seat	Bronze
18.	Orifice Seal	EPDM
19.	O-Ring	BUNA-N
20.	Float	Polycarbonate / Stainless Steel
21.	Body	Ductile Iron





### 6"-8" SPECIAL PARTS

Screen Cover	Polyethylene
Cover	Ductile Iron
NS Housing	Polyethylene
Ring	Carbon Steel
Non-Slam Disc	Ductile Iron
	Cover NS Housing Ring

### 10" SPECIAL PARTS

10.	Screen Cover	Polyethylene
13.	Cover	Ductile Iron
14.	Ring	Carbon Steel
15.	Non-Slam Disc	Ductile Iron






# D-060-C NS / D-062 NS



### PARTS LIST AND SPECIFICATION

No.Part	Material
1. Shell	Ductile Iron
2. Body	Reinforced Nylon
3. Air Release Outlet	Brass
4. Rolling Seal	EPDM
5. Float	Foamed Polypropylene
6. Clamping Stem	Reinforced Nylon
7. O-Ring	BUNA-N
8. Base	Brass
9. Strainer	Nylon
10. Domed Nut & Washer	Stainless Steel 304
11. Screen Cover	Polyethylene / Ductile Iron
12. Threaded Rod	Stainless Steel 304
13. Screen	Stainless Steel 304
14. Cover	Ductile Iron
6", 8" NS Housing	Polyethylene
Cover	Ductile Iron
15. Ring 2"-4"	Stainless Steel 316
6"-10"	Carbon Steel
16. Non-Slam Disc 2"-4"	Stainless Steel 316
6"-10"	Ductile Iron
17. Bolt, Nut & Washer	Steel, Zinc Cobalt Coated
18. Orifice Seat	Bronze
19. Orifice Seal	EPDM
20. O-Ring	BUNA-N
21. Float	Polycarbonate / Stainless Steel
22 P. I	D-062 NS 8" Stainless Steel only
22. Body	Ductile Iron





### **6"-8" SPECIAL PARTS**

10.	Screen Cover	Polyethylene
14.	Cover	Ductile Iron
13.1	NS Housing	Polyethylene
15.	Ring	Carbon Steel
16.	Non-Slam Disc	Ductile Iron

### 10" SPECIAL PARTS

10.	Screen Cover	Polyethylene
14.	Cover	Ductile Iron
15.	Ring	Carbon Steel
16.	Non-Slam Disc	Ductile Iron





# **D-065 NS**



### PARTS LIST AND SPECIFICATION

No.Part		Material	
1. Air Release Outle		PVC	
2. Orifice	CL	Reinforced Nylon	
3. Rollpin		Stainless Steel 304	
4. O-Ring		BUNA-N	
5. Rolling Seal		EPDM	
6. Rollpin		Stainless Steel 304	
7. Lever		Reinforced Nylon	
8. Rollpin		Stainless Steel 304	
9. Cover		Ductile Iron	
10. O-Ring		BUNA-N	
11. Bolt Nut & Was	her	Steel, Zinc Cobalt Coated	
12. Float		Polycarbonate / Stainless Steel	
13. Body		Ductile Iron	
14. Adaptor		Brass	
15. Domed Nut & V	Washer	Stainless Steel 304	
16. Screen Cover		Polyethylene / Ductile Iron	
17. Threaded Rod		Stainless Steel 304	
18. Screen		Stainless Steel 304	
19. Cover		Ductile Iron	
6", 8" NS H	Iousing	Polyethylene	
	Cover	Ductile Iron	
20. Ring	2"-4" 6"-8"	Stainless Steel 316 Carbon Steel	
21. Non-Slam Disc	2"-4" 6"-8"	Stainless Steel 316 Ductile Iron	
22. Bolt, Nut & Wa	sher	Steel, Zinc Cobalt Coated	
23. Orifice Seat		Bronze	
24. Orifice Seal		EPDM	
25. O-Ring		BUNA-N	
26. Float	2"-4"	Polycarbonate / Stainless Steel 304	
	6"-8"	Stainless Steel	

Ductile Iron





27. Body


16.	Screen Cover	Polyethylene
19.	Cover	Ductile Iron
19.1	NS Housing	Polyethylene
20.	Ring	Carbon Steel
21.	Non-Slam Disc	Ductile Iron

### 10" SPECIAL PARTS

16.	Screen Cover	Polyethylene
19.	Cover	Ductile Iron
20.	Ring	Carbon Steel
21.	Non-Slam Disc	Ductile Iron












### **Operation in Rapid Filling of the Pipeline:**




1. When water, rapidly filling the pipe line, pushes the air out through the Air Valve, a differential air pressure is created across the valve orifice.



When this differential pressure reaches a prefixed level (usually it will be prefixed at 0.02 - 0.03 bar) the orifice disc will close.
 Air will continue to come out through the small orifice disc - until all the air will be exhausted and water will reach the kinetic float.
 This double stage kinetic air discharge prevents the slam effect and therefore suppresses water hammer.



- 4. When water reaches the kinetic float, it lifts it up, closing the kinetic orifice and completing the kinetic cycle.
- 5. The «vented Check Valve Orifice Disc» will come back to its normal open position.



6. When water is drained out of the pipe line, the resulting pressure drop lets the kinetic float fall down, opening the orifice fully for intake of high volume of air into the line.

