D2.1.0

juno

Project:

Fixture Type:

Location:

Contact/Phone:

One Circuit Trac System **TRAC SECTIONS, JOINERS & FEEDS**

R2, R4, R6, and R8

TRAC-LITES

PRODUCT DESCRIPTION

Reduced-profile, single-circuit trac sections for surface or pendant mounting. Compatible with a full range of feed, connector and mounting accessories, as listed on back of this page. Accepts all Trac-Lites and Trac-Master trac fixtures.

PRODUCT SPECIFICATIONS

Construction Extruded aluminum with thermoplastic insulator

- Injection molded polycarbonate dead-end with set screw
- Standard lengths may be cut-to-length by installer.

Electrical Two 12 gauge solid copper conductors • Rated 20 amps at 120 volts • Aluminum channel used as system ground • One-piece insulator insures consistent conductor spacing for reliable electrical contact • Insulating bushings supplied at mounting hole locations to prevent shorts to ground.

Labels UL/CUL listed.

PRODUCT INSTALLATION


Debossed polarity line provides visual cue to proper trac, trac connector and fixture alignment • Supplied with toggle bolts for surface mounting • Insulator stays same length as extrusion to simplify field-cutting of trac • Connectors and feeds simply push into trac sections.


Product specifications subject to change without notice.

PRODUCT CODES

| Catalog Number | Description | Actual Length | Finish |
|----------------|-----------------|----------------|---------|
| R2WH | 2' Trac Section | 19 7/8" | White |
| R2BL | 2' Trac Section | 19 7/8" | Black |
| R2SL | 2' Trac Section | 19 7/8" | Silver |
| R2NA | 2' Trac Section | 19 7/8" | Natural |
| R2BZ | 2' Trac Section | 19 7/8" | Bronze |
| R4WH | 4' Trac Section | 43 7/8" | White |
| R4BL | 4' Trac Section | 43 7/8″ | Black |
| R4SL | 4' Trac Section | 43 7/8″ | Silver |
| R4NA | 4' Trac Section | 43 7/8″ | Natural |
| R4BZ | 4' Trac Section | 43 7/8″ | Bronze |
| R6WH | 6' Trac Section | 67 7/8" | White |
| R6BL | 6' Trac Section | 67 7/8" | Black |
| R6SL | 6' Trac Section | 67 7/8" | Silver |
| R6NA | 6' Trac Section | 67 7/8" | Natural |
| R6BZ | 6' Trac Section | 67 7/8" | Bronze |
| R8WH | 8' Trac Section | 91 7/8" | White |
| R8BL | 8' Trac Section | 91 %" | Black |
| R8SL | 8' Trac Section | 91 7⁄8″ | Silver |
| R8NA | 8' Trac Section | 91 7⁄8″ | Natural |
| R8BZ | 8' Trac Section | 91 7/8" | Bronze |

DIMENSIONS







D2.1.0

TRAC-LITES

R2, R4, R6, and R8

T90-12, **T90-18**,

T90-24, **T90-36**,

T-Bar Pendant Stem Kit (12",

18", 24", 36", 48") - Use

two for 2', 4', 6' of trac or

feed, order **T93** wireway

cover. WH, BL, SL, BZ

T91-12, T91-18,

T91-24, T91-36,

Rigid Ceiling Pendant Stem Kit

(12", 18", 24", 36", 48") -

Use two for 2', 4', 6' of trac or

three for 8' of trac. For electrical

Wireway Cover for Pendant Stem

electrical feed wires from stem to

connector. One cover required for

Kits T90 and T91. Conceals

feed, order **T93** wireway

cover. WH, BL, SL, BZ

T93WH, T93BL,

T93SL, T93BZ

each trac feed.

T91-48


three for 8' of trac. For electrical

T90-48

One Circuit Trac System

TRAC SECTIONS, JOINERS & FEEDS

Electrical End Feeds





R29WH, R29BL, R29SL, R29BZ Floating Electrical Feed. Permits mounting any point of trac under outlet box. Includes floating connector, outlet box cover plus extra trac dead end.

R34WH, R34BL,

R34SL, R34BZ

Conduit Feed. For surface

wiring. Use standard 1/2"

R36WH, R36BL,

T-Bar End Feed. Wiring com

partment contains standard

1/2" KO's. Feeds surface

R38WH, R38BL,

Live End Feed Connector. Feed

trac from above with flexible

conduit, BX, etc., or end feed

in pendant systems. Accepts

R22WH, R22BL,

R22SL, R22BZ

Cord and Plug Connector.

Comes with 15' two-wire

white cord. Includes surface

Max cap. 7 amps.

wire retainers and in-line switch.

R122WH, R122BL,

matching color 3-wire grounded

R122SL, R122BZ

Same as above but with

cord and plug. No switch.

Product specifications subject to change without notice.

standard 1/2" connector.

R38SL, R38BZ

is directly above trac.

trac from above, when T-bar

R36SL, R36BZ

connector.

around screw

R21WH, R21BL,

R21SL, R21BZ

End Feed Connector and

Outlet Box Cover. For outlet

box feed. Includes: outlet

box cover, fixture strap and



4 1/8"





Trac Joiners















R2OSL, R2OBZ Accordion Adjustable Joiner. Can flex to 90° angle to left, right, up or down. Joins two

trac sections.

R20WH, R20BL,

R23WH, R23BL, R23SL, R23BZ Miniature Straight Connector. Joins two trac sections end to end



‡ R25WH, R25BL, R25SL, R25BZ "T" Connector. Joins three trac sections. For outlet box feed, No. T27 cover plate required.


> Nos. R24/R25 for outlet box electrical feed. Includes: nipple, locknut and ground screw.

R49SL, R49BZ trac to continue a run around obstructions. Includes one left and one right R34 Conduit

R28WH, R28BL, R28SL, R28BZ field-cut trac sections

Pendant Stems











T94WH, T94BL, 194SL, 194BZ Sloped Ceiling Adapter. Allows **T90** or **T91** pendant to hang straight down from sloped ceilings. Can be used to feed

electrical wires to Trac at up to

T96WH, T96BL, T96SL, T96BZ Pendant Stem Threaded Coupling. Enables multiple pendant stems to be joined for

higher ceiling applications.

60° anale.

T56WH, T56BL, T56SL, T56BZ Solid Rod Pendant Mounting Kit. Attaches solid 5/16" threaded rod to Trac. Includes: plastic cap, mounting bracket and hardware.

Rod not supplied.

‡ R24 and R25 may not be used as feed connectors in Canada due to special grounding requirements.



1300 S. Wolf Road • Des Plaines, IL 60018 • Phone (847) 827-9880 • Fax (847) 827-2925 220 Chrysler Drive • Brampton, Ontario • Canada L6S 6B6 • Phone (905) 792-7335 • Fax (905) 792-0064 Visit us at www.junolightinggroup.com Printed in U.S.A. ©2014 Juno Lighting, LLC.

T27WH, T27BL, T27SL, T27BZ Outlet Box Cover. Use with

R49WH, R49BL, Trac Continuation Kit. Permits

Feed. Fits standard 1/2" conduit.

Trac Dead End. For use with

D2.1.0


TRAC-LITES

One Circuit Trac System

TRAC SECTIONS, JOINERS & FEEDS

R2, R4, R6, and R8

Cable Suspension



T595-48-WH, T595-48-BL T595-144-WH, T595-144-BL

T-Bar Ceiling Cable Suspension Kit Mechanical-only cable suspension Kit for 1-circuit or 2-circuit trac. Adjustable 48" or 144" stainless steel cable length. Includes mini-canopy, T-bar dip and cable hardware. Trac requires support every 4'.

T597-48-WH, T597-48-BL T597-144-WH, T597-144-BL

Rigid Ceiling Cable Suspension Kit Mechanical-only cable suspension Kit for 1-circuit or 2-circuit trac. Adjustable 48" or 144" stainless steel cable length. Includes mini-canopy, toggle bolt and cable hardware. Trac requires support every 4'.



T596-48-WH, T596-48-BL T596-144-WH, T596-144-BL

T-Bar Ceiling Cable Suspension/Feed Kit Cable suspension kit with 48" or 144" electrical feed cable for 1-circuit trac. Includes canopy, T-bar clip, mounting plate, cable hardware and flexible electrical feed cable. Trac requires support every 4'.

T598-48-WH, T598-48-BL

T598-144-WiH, T598-144-BL Rigid Ceiling Cable Suspension/Feed Kit Cable suspension kit with 48" or 144" electrical feed cable for 1-circuit trac. Includes canopy, J-box mounting strap, cable hardware and flexible electrical feed cable. Trac requires support every 4'.

Note: Cable suspension is recommended for pattern installations only, or those installations that are supplemented with additional rigid mounting points (stems, threaded rod, etc.).

Accessories



R37F 15/16" T-bar Attachment Clip. To attach to inverted tee ceilings using flush tiles. Use two for 2' or 4' trac and three for 6' or 8' trac. **R37D** Same as above with spacer for ceilings using drop tiles.

R37-9-16 9/16" T-bar Attachment Clip. To attach Trac-Lites trac to inverted tee ceilings using flush or drop tiles. Use two for 2' or 4' trac and three for 6' or 8' trac.



T31WH, T31BL, T31SL Pendant Adapter. Adapts swag or chain-hung fixture to trac. Supports up to 25 lbs. Not UL Listed.

| IÇ | T S |
|----|--------|
| 凩 | |

T32WH, T32BL, T32SL

Plant or Utility Hook. Supports up to

25 lbs. Not UL Listed.



Outlet Adapter. Provides electrical receptacle. Not UL Listed.

Product specifications subject to change without notice.

