

NLCBC-55 COBALT Series 5" 95CRI Recessed Retrofit Downlight

PRODUCT DESCRIPTION

Nora Lighting's 5" LED Cobalt Luminaires are cULus listed for use in existing 5" IC or Non-IC housings manufactured by Nora and others. The units provide 1000 Lumen output, drawing 16W and rendering 95CRI. Nora's 5" Cobalt LEDs intergrate the latest from the Cree® COB family of LED arrays, giving bright spectacular light output and low power consumption. An obvious and smart choice for Green Energy efficient lighting in commercial and residential applications.

FEATURES

- 5 year limited warranty
- CREE® COB LED
- Dimmable
- cULus Listed, Energy Star & Title 24 compliant
- 1000lm utilizes only 16W
- Available in 2700K, 3000K and 4000K color temperature, 95 CRI
- GU24 Socket adapter available for use with GU24 base housings- Includes Medium-Base Socket kit

CONSTRUCTION

Trim: Aluminum spun reflector (NLCBC-551) with deep set diffused lens for excellent visual comfort while providing high lumen output.

Aluminum spun baffle trim (NLCBC-552) with deep set diffused lens and deep grooves to reduce aperture glare while providing high lumen output.

Lens: Shatter proof diffused poly carbonate lens.

RETROFIT

Cobalt Series Downlights include NRA-211 Medium Base screw-in socket for retrofiting into existing Medium Base downlight housings.

ELECTRICAL SYSTEM

Voltage: 120VAC Current: 400mA Power Consumption: 16 Watts Light Source: Cree COB Lumens: 1000 lm CRI: 95 CRI LED Driver: Built-in driver Operating Temperature: 0°C to 50°C ambient temperature Life Expectancy: 50,000 hours

Dimmable

Nora LED Cobalt Series works with standard leading and trailing edge dimming technologies. Dimming with trailing-edge dimmers (electronic) are 5-100% and for leading-edge dimmers (incandescent) 10-100%. There may be some cases that require more than one lighting fixture to be used to meet minimum dimmer load. Consult with dimmer manfacturer. Click Here or refer to www.NoraLighting.com for complete updated dimmer list in the "Compatibility" page under the "Resource" tab.

LABELS & LISTINGS

cULus Wet Label Listed Title 24 Compliant Energy Star Rated



5" Cobalt 95CRI Recessed Retrofit Downlight

Catalog No.	Color Temp.	Finish	Option	N
NLCBC-551 = Reflector	27 = 2700K	BZ = Bronze	Blank = 120V	N
NLCBC-552 = Baffle	30 = 3000K	DW* = Diffused Clear / White	$\mathbf{EM} = \mathbf{Pre}$ -Wired for \mathbf{EM} use with	
	40 = 4000K	HZW* = Haze / White	EM housing ³	Rem
		WW = White		N N N
				N N


Туре Project

Catalog No.

Lamp/Wattage

Source: 16W Chip on Board 1000Lm LED

DIMENSIONS



Diffused Clear (DW) - Diffused Refl.

with White Flange

Haze (HZW) - Haze Refl with White Flange White (WW) - White Refl. or Baffle

with White Flance

	IIVIENS
cturer:	Model Numb
Leviton	IPE04
	6161
	IPI06-1LZ
Lightolier	ZP260QEW
Lutron	DVCL153P
	TGCL-153P
	S600P
	CT103P
	MAELV600
	FAELV500

Compatible Housings

FireBox	
NFBIC-5LMRAT	5" ICAT Dedicated LED 2-Hour Fire Rated
No. O state the	
New Construction	
NHIC-501QAT	5" ICAT Line Voltage
NH-501Q	5" Line Voltage
NHIC-5G24ATFL	5" ICAT GU24 (Specify NRA-212 adaptor separately)
NHIC-5LMRAT	5" ICAT Dedicated LED
NHIC-5LMRAT/277	5" ICAT Dedicated LED, 277V
NHIC-527LMRAT	5" IC AT Shallow Dedicated Housing
NHIC-5LMRAT/EM	5" IC Air Tight Dedicated Housing Pre-wired for Emergency
	Cobalt Series - Includes EM battery and remote test switch
NHIC-5LMRAT/6WEM	5" IC Air Tight Dedicated Housing Pre-wired for Emergency and
	0-10V dimming Cobalt Series - Includes EM battery
	and remote test switch

model

NHRIC-504QA NHR-504Q NHRIC-5G24ATFL NHRIC-5LMRAT NHRIC-527LMRAT

5" ICAT Line Voltage

- 5" Line voltage
 - 5" ICAT GU24 (Specify NRA-212 adaptor separately)
- 5" ICAT Dedicated LED
- 5" IC AT Shallow Remodel Dedicated Housing

*Finish only available on Reflector Style Compatible with NHIC-5LMRAT/EM housing

Example: NLCBC-55127WW 5" Cobalt with Smooth White Reflector and flange - 2700K. Create a complete Item number:

Page 1 of 1

ENORA NSPEC

6505 Gayhart St., Commerce, CA 90040 | Phone: 800.686.6672 | FAX: 800.500.9955 www.noralighting.com | e-mail: nora@noralighting.com Specifications subject to change without notice. © 2016