

BEAM CLAMPS



RETAINING STRAP (For Fig. 345, 350 & 360)

Function: Designed for use with Fig. 345, Fig. 350, and Fig. 360 to offer more secure fastening of beam clamps to beam where seismic protection is provided.

Material: Carbon steel (Type 304 or 316 Stainless Steel upon request)

Finish: Pre-galvanized

Approvals: Underwriters' Laboratories Listed in the U.S. (UL) and Canada (CUL) for $\frac{3}{8}$ " and $\frac{1}{2}$ " rod sizes only. Meets NFPA13 requirements for hangers and fasteners subject to earthquakes.

Ordering: Specify figure number, length, rod size, and material.

NOTE: Use jam nut over hanger rod to secure retaining strap. 2 inches (50.8) should be added to beam flange width to determine length.

Rod Size	Wt. Each											
	Length C											
	4 1/2 (114.3)		6 (152.4)		8 (203.2)		10 (254.0)		12 (304.8)		14 (355.6)	
3/8 & 1/2	.09	(.04)	.12	(.05)	.15	(.07)	.21	(.10)	.22	(.10)	.29	(.13)
5/8	.19	(.09)	.25	(.11)	.34	(.15)	.42	(.19)	.50	(.23)	.59	(.27)
3/4	.19	(.09)	.25	(.11)	.33	(.15)	.41	(.19)	.49	(.22)	.57	(.26)
7/8	.28	(.23)	.37	(.17)	.50	(.23)	.62	(.28)	.75	(.34)	.87	(.39)

FIG. 359

