
2^{°°} Self-Priming Centrifugal Pumps

- 300 Series Investment Cast Stainless Steel Construction with Viton[®] Seals
- Cast Iron Construction with Buna-N Seals
- Optional Silicon Carbide Seals Available
- 2" NPT Port Size

Model 276D-95

- Maximum Temperature
 - Stainless Steel 200° F
 Cast Iron 180° F
- Maximum Flow 150 GPM
- Maximum Head 102 Ft. (44 PSI)
- Self-Priming up to 20 Feet with Built-in Check Valve
- Self-Cleaning, Clog Resistant Impeller
- 1-1/2 to 3 HP Single or Three Phase 3450 RPM Motors



This line of AMT Self-Priming Centrifugal pumps is designed for industrial and commercial applications requiring high volume liquid transfer, waste water drainage and processing. These pumps feature a self-cleaning clog resistant impeller capable of handling up to 3/8" diameter semisolids. Built-in flapper/check valve enables consistent self-priming to 20 feet. Dual volute design reduces radial load on motor. Stainless steel models are especially effective in applications where rust and/or corrosion can develop in systems and also are highly resistant to erosion and chemicals.

400 Spring Street • Royersford, PA 19468 USA

www.amtpump.com • 888-amt-pump (268-7867)

A Gorman-Rupp Company

For use with nonflammable liquids compatible with pump component materials. Viton* and Teflon* are registered trademarks of E. I. Dupont.

2"Self-Priming Centrifugal Pumps

| Model ‡ | Curve | HP | PH | ENC | Voltage @ 60 Hz + | Full Load Amps | SUC* | DIS* | L** | W** | Н | ‡ Ship Wt. (Lbs.) |
|---------|-------|----|----|------|----------------------|-------------------|------|------|-------------|------------|-------------|----------------------|
| 2762 | A | 1½ | 1 | ODP | 115/230 | 17/9 | 2 | 2 | 19.3 [49.0] | 7.5 [19.0] | 11.1 [28.1] | 73 |
| 2764 | | 1½ | 3 | ODP | 230/460 | 7/4 | 2 | 2 | 18.8 [47.7] | 7.5 [19.0] | 11.1 [28.1] | 70 |
| 276B | | 2 | 1 | TEFC | 115/230 | 22/11 | 2 | 2 | 20.3 [51.5] | 9.1 [23.1] | 11.1 [28.1] | 81 |
| 276D | | 2 | 3 | TEFC | 230/460 | 6/3 | 2 | 2 | 19.8 [50.3] | 9.1 [23.1] | 11.1 [28.1] | 74 |
| 2761 | В | 2 | 1 | ODP | 115/230 | 28/14 | 2 | 2 | 19.3 [49.0] | 7.5 [19.0] | 11.1 [28.1] | 81 |
| 2763 | | 2 | 3 | ODP | 230/460 | 7/4 | 2 | 2 | 19.3 [49.0] | 7.5 [19.0] | 11.1 [28.1] | 77 |
| 276A | | 3 | 1 | TEFC | 230 | 16 | 2 | 2 | 20.8 [52.8] | 9.1 [23.1] | 11.1 [28.1] | 90 |
| 276C | | 3 | 3 | TEFC | 230/460 | 8/4 | 2 | 2 | 20.3 [51.5] | 9.1 [23.1] | 11.1 [28.1] | 78 |
| 2767 | С | 3 | 1 | ODP | 230 | 18 | 2 | 2 | 20.5 [52.1] | 7.5 [19.0] | 11.1 [28.1] | 87 |
| 2766 | | 3 | 3 | ODP | 230/460 | 9/5 | 2 | 2 | 20.3 [51.5] | 7.5 [19.0] | 11.1 [28.1] | 87 |

Pump Dimensional & Specification Data

(*) Standard NPT (Female) pipe thread.


 $(\ensuremath{^{\star\star}})$ This dimension may vary due to motor manufacturer's specifications.


(+) 3-Phase models can also operate on 50 Hz (This will change full load

amps and service factor, RPM and priming capabilities).

- NOTE: Dimensions are in inches (centimeters) and have a tolerance of $\pm~1/4^{\prime\prime}.$
- NOTE: Electric supply for **ALL** motors must be within ±10% of nameplate voltage rating (e.g. 230V ±10%= 207 to 253).







Standard Features

- \bullet 300 Series Investment Cast Stainless Steel Construction with Viton $^{\ensuremath{\$}}$ Seals
- Cast Iron Construction with Buna-N Seals
- Handles 3/8" Diameter Semi-solids
- NEMA 56J Motors with Stainless Steel Shaft
- Maximum Working Pressure 75 PSI
- Available in ODP or TEFC, Single or Three Phase Motors
- Self-primes to 20 Ft.



Self-cleaning, Clog Resistant Impeller

- Steel Base and Handle Included
- Dual Volute Design
- QSP Quick Ship Pump for Many Models

Hazardous Duty/Xplosion Proof motors available from stock ranging from 1 to 10 HP; *CALL FOR QUOTATION & LEAD TIME!*

Manufacturer of AMT & IPT Pumps 400 Spring Street • Royersford, PA 19468 USA www.amtpump.com • 888-amt-pump (268-7867)



The Gorman-Rupp Company reserves the right to discontinue any model or change specifications at any time without incurring any obligation. ©2012 American Machine and Tool Company. All rights reserved.