


The Warwick Hanger Company (a prime manufacturer and direct importer) has emerged a leader in the distribution and fabrication of residential and light commercial pipe hangers. Since our manufacturing facility's establishment in 1971, we have incorporated into our production process the latest techniques in advanced automation and robotics. This has resulted in a superior product line, competitive pricing, and immediate shipping, allowing our customers to maintain minimum inventories.



We currently occupy 80,000 square feet of manufacturing and warehouse space. We are fully confident you will be satisfied with our quality and performance. We are currently on line for EDI Transfers, and offer bar-coding on all of our products.

We would welcome a visit to our facilities by you or any of your staff, and look forward to a lasting, mutually successful relationship for our companies.





Plated Tubing Clips



Plastic Pipe /JClips



Bend Support



Glide Lock Clips



Page: 4

Page: 5

Page: 6

Galvanized 2-Hole Pipe

Page: 7

Manifold Pipe Clip



Gas Vent Sign—Air Intake-Exhaust Labels





Bell Hangers



AIR INTAKE

EXHAUST



Page: 11, 12, 13

Page: 8

Page: 9

Hangers

Page: 10

Hooks



Trap Covers



Nailing Hooks

Page: 14



Page: 15, 16, 17, 18, 24, 26, 27, 28, 29, 30,



Page: 19, 20, 21, 22

Tube Support Bracket

Page: 14



Perforated Hanger



Glide Lock J Hook



Plastic J Hook

Page: 23



Page: 25



Page: 31



Page: 32

Nailing Plates



Page: 33

Split Ring Hangers



Page: 34, 35, 36

Adjustable Band Hanger



Page: 37, 38

Swivel Hangers

Page: 39, 40

Strut





Page: 41, 42, 43

Clevis Hangers



Page: 44, 45



Clamps

Page: 46, 47, 48, 49



Flanges

Page: 50

Stud Protectors



Page: 51





Page: 52







Page: 53

Page: 54

Steel C-Clamp

Hardware

Nylon Nailin

Mechanical Anchors



Page: 55



Page: 56, 57, 58, 59, 60, 63



Page: 61

Plastic Coated Pipe Clips



Page: 62

Power Stud



Page: 64



The Sled

Page: 65



Page: 66

Pro-Pitch Hanger



Page: 67



Series 100 Copper Plated Tubing Clips

Size Range: 1/2" – 2"
Material: Carbon Steel
Finish: Copper Plating


Function: Used to clamp copper tubing flush to surface in both

vertical and horizontal applications.

Our Copper Plated Tubing Clips are designed to snap onto the

tubing for hands free nailing.





Part #	Size	Size Tubing	Packaged	Case Quantity
100-25	1/8"	3/16" O.D.	100	N/A
100-38	1/4"	3/8" O.D.	100	N/A
100-40	3/8"	1/2" O.D.	100	N/A
100-50	1/2"	5/8" O.D.	100	1000
100-75	3/4"	7/8" O.D.	100	1000
100-10	1"	1 1/8" O.D.	50	500
100-12	1 1/4"	1 3/8" O.D.	50	500
100-15	1 1/2"	1 5/8" O.D.	50	500
100-20	2"	2 1/8" O.D.	50	500

Manufactured At Our Rhode Island Facility



Series 150-160-170 Plastic Pipe Clips



Size Range: 1/2"- 2"

Finish: Black

Function: Secures copper, CPVC and PEX to both wood and metal framework.

Material: High Density Polyethylene

Part #	Size	Description	Packaged	Case Quantity
150-50	1/2"	Standard	100	1000
150-75	3/4"	Standard	100	1000
150-10	1"	Standard	100	1000
150-12	1 1/4"	Standard	100	1000
160-50	1/2"	Suspension	100	1000
160-75	3/4"	Suspension	100	1000
160-10	1"	Suspension	100	1000
160-12	1 1/4"	Suspension	100	1000
160-15	1 1/2"	Suspension	100	1000
160-20	2"	Suspension	100	1000

Series 170 Plastic J Clip with Nail

Size Range: 3/8" – 1"

Finish: Black

Function: Secures copper, CPVC and PEX tubing.

Material: High Density Polyethylene

Part #	Size	Description	Packaged	Case Quantity
170-38	3/8"	J Clip With Nail	100	1000
170-50	1/2"	J Clip With Nail	100	1000
170-75	3/4"	J Clip With Nail	100	1000
170-10	1"	J Clip With Nail	100	1000





Series 175 Plastic J Clip with Nail for FostaPex™

Size Range: 1/2" - 1"

Finish: Grey

Function: Secures FostaPex™.

Part #	Size	Description	Packaged	Case Quantity
175-50	1/2"	J Clip With Nail	100	1000
175-75	3/4"	J Clip With Nail	100	1000
175-10	1"	J Clip With Nail	100	1000

Series 176 Plastic Closed Clamp with Nail

Size Range: 1/2" - 3/4"

Finish: Black

Function: Secures copper, CPVC and PEX tubing.

Material: High Density Polyethylene

Part #	Size	Description	Packaged	Weight
176-50	1/2"	Plastic Closed Clamp with Nail	100	.04 Lbs
176-75	3/4"	Plastic Closed Clamp with Nail	100	.16 Lbs

Series 185 Bend Support



Size Range: 1/2" and 3/4"

Function: Plastic bend supports provide rigid 90 degree bends for pex tubing. The

bend supports are made of glass reinforced nylon.

Part #	Size	Description	Packaged	Weight
185-50	1/2"	Bend Supports	25	.04 Lbs
185-75	3/4"	Bend Supports	25	.16 Lbs



Series 190 Glide Lock Pipe Clip



Size Range: 1/2" - 1"

Function: The Glide Lock Pipe Clip allows the pipe to glide back and forth freely while pipe is mounted to easily achieve your installation needs. Then with a simple squeeze of the locking fingers your pipe is locked securely into place.

Part #	Size	Description	Packaged	Case Quantity
190-50	1/2"	Glide Lock Clip	100	1000
190-75	3/4"	Glide Lock Clip	100	1000
190-10	1"	Glide Lock Clip	100	1000

Tube Isolation Clip

Size Range: 1/2" – 1"

Function: The Tube Isolation Clip insulates tube in wood and Metal studs and reduces water line noise and vibration. The

Split design allows for use after piping runs.



Part #	Size	Description	Packaged	Case Quantity
186-50	1/2"	Tube Isolation Clip	100	1000
186-75	3/4"	Tube Isolation Clip	100	1000
186-10	1"	Tube Isolation Clip	100	1000



Series 180 Manifold Pipe Clip

Size Range: 3/8" - 1 1/4"

Function: Whether you have 2, 3 or 20 pipes running side by side, the Manifold Clip has the ability to connect to each other to form a manifold system that keeps your pipes neat and organized. The snap lock cross arm completes the installation, giving you a strong and professional way to hang your pipe.





Part #	Size	Description	Packaged	Case Quantity
180-38	3/8"	Manifold Pipe Clip	100	1000
180-50	1/2"	Manifold Pipe Clip	100	1000
180-75	3/4"	Manifold Pipe Clip	100	1000
180-10	1"	Manifold Pipe Clip	100	1000
180-12	1 1/4"	Manifold Pipe Clip	100	1000

Manifold Pipe Clip Screws

Part #	Size	Description	Packaged	Case Quantity
2155-C-100	1 1/4" X #6	Drywall Screw	100	1000

Manifold Pipe Clip Spacers

Part #	Size	Description	Packaged	Case Quantity
181-10	7/8" Wide	Spacers	100	1000



Series 5000 Gas Vent Sign

Size: 7" x 3" Yellow/Black Custom Sign

Description: Modifications to NFPA-54: A metal or plastic identification plate shall be permanently mounted to the exterior of the building at a minimum height of eight (8) feet above grade directly in line with the exhaust vent terminal for the horizontally vented gas fueled heating appliance or equipment. The sign shall read, in print no less than one-half (1/2) inch in size 'GAS VENT DIRECTLY BELOW. KEEP CLEAR OF ALL

OBSTRUCTIONS



AIR INTAKE

EXHAUST

Part #	Description	Size	Packaged
5000-1	Gas Vent Sign	7" X 3"	1
5500-1	Exhaust Label	3.25" X 17.75"	25
5500-2	Air Intake Label	3.25" X 17.75"	25




Series 130 Galvanized 2-Hole Pipe Clips

Size Range: 1/2" - 6" Material: Carbon Steel Finish: Galvanized Plating

Function: Used to clamp black iron pipe flush to the surface

in both vertical and horizontal applications.





Part #	Size	Gage	Packaged	Case Quantity
130-50	1/2"	18 Gage	100	500
130-75	3/4"	18 Gage	100	500
130-38	3/8"	18 Gage	100	500
130-10	1"	18 Gage	50	500
130-12	1 1/4"	18 Gage	50	N/A
130-15	1 1/2"	18 Gage	50	N/A
130-20	2"	18 Gage	50	N/A
130-25	2 1/2"	18 Gage	50	N/A
130-30	3" Heavy	16 Gage	25	N/A
130-40	4" Heavy	16 Gage	25	N/A
130-60	6" Heavy	12 Gage	25	N/A

Manufactured At Our Rhode Island Facility



Hanger Company


Series 300 Copper Plated Bell Hanger

Size Range: 1/2" - 2"
Material: Carbon Steel
Finish: Copper Plated

Function: Used to mount copper tubing.



Our Copper Plated Bell Hanger has a patented access hole through the top which allows the hanger to be mounted to most flat surfaces without disassembling the cap. We have added 4 additional mounting holes around the base of the bell for additional mounting flexibility. Our hanger is used as a standoff clamp in both vertical and horizontal applications and provides 3/4" standoff.



The Center Screw Has Been Pre-Installed

Part #	Size	Packaged	Case Quantity
300-2	1/2"	25	500
300-3	3/4"	25	500
300-4	1"	25	500
300-5	1 1/4"	25	N/A
300-6	1 1/2"	25	N/A
300-7	2"	25	N/A



Series 300 Corrosion Resistant Bell Hangers

Size Range: 1/2" - 2" Material: Carbon Steel Finish: Baked Enamel


Function: Used to mount tubing.

Our Corrosion Resistant Bell Hangers are excellent for outdoor applications. (outdoor showers, crawl spaces)

The mounting and clamp screws are stainless steel. The bell has a powder coated finish and provides 3/4" standoff.



Screws Are Included and Packaged In Bags



Part #	Size	Packaged
300-2-BP	1/2"	25
300-3-BP	3/4"	25
300-4-BP	1"	25
300-5-BP	1 1/4"	25
300-6-BP	1 1/2"	25
300-7-BP	2"	25

Manufactured At Our Rhode Island Facility



Series 300 Narrow Copper Plated Bell Hanger



Size Range: 1/2" - 2" Material: Carbon Steel Finish: Copper Plated

Function: Used to mount copper tubing.

The bell hanger is used as a standoff clamp in both vertical and horizontal applications and provides 3/4" standoff.

Part #	Size	Packaged	Case Quantity
300-2N	1/2"	25	500
300-3N	3/4"	25	500
300-4N	1"	25	500
300-5N	1 1/4"	25	N/A
300-6N	1 1/2"	25	N/A
300-7N	2"	25	N/A



Series 1500 Trap Covers

Material: Stainless Steel Finish: Polished Stainless



Part #	Description	Material	Weight	Packaged
1500-1	Raised	Stainless Steel	.130 Lbs	25
1500-2	Flat	Stainless Steel	.185 Lbs	25

Series 2113 Nailing Hooks

Material: Carbon Steel **Finish:** Copper Plating

Function: These Copper Nailing Hooks are designed to nail directly into Wooden joists. They provide quick installation of small diameter copper tubing.



Part #	Finish	Size	Packaged	Case Quantity
2113-C	Copper Plated	3/8"	100	1000
2113-D	Copper Plated	1/2"	100	1000



Series 200 Natick Type Hangers

Size Range: 1/2" - 2"
Material: Carbon Steel
Finish: Copper Plating

Function: Used to suspend copper tubing from floor joists, used in horizontal

applications.

Nails are Included and Packaged in Bags

		T
Part #	Size	Packaged
200-1	1/2" x 6"	25
200-2	3/4" x 6"	25
200-3	1" x 6"	25
200-4	1 1/4" x 6"	25
200-5	1 1/2" x 6"	25
200-6	2" x 6"	25
200-7	1/2" x 12"	25
200-8	3/4" x 12"	25
200-9	1" x 12"	25
200-10	1 1/4" x 12"	25
200-11	1 1/2" x 12"	25
200-12	2" x 12"	25

Manufactured At Our Rhode Island Facility




Series 200 Narrow Natick Type Hangers

Size Range: 1/2" - 2"
Material: Carbon Steel
Finish: Copper Plating

Function: Used to suspend copper tubing from floor joists, used

in horizontal applications.



Nails are Included and Packaged in Bags

Part #	Size	Packaged
200-1N	1/2" x 6"	25
200-2N	3/4" x 6"	25
200-3N	1" x 6"	25
200-4N	1 1/4" x 6"	25
200-5N	1 1/2" x 6"	25
200-6N	2" x 6"	25

Part #	Size	Packaged
200-7N	1/2" x 12"	25
200-8N	3/4" x 12"	25
200-9N	1" x 12"	25
200-10N	1 1/4" x 12"	25
200-11N	1 1/2" x 12"	25
200-12N	2" x 12"	25



Series 400 Milford Type Hangers

Size Range: 1/2" - 2"

Material: Carbon Steel

Finish: Copper Plating

Function: Used to suspend copper tubing from floor joists

and is used in horizontal applications.

Our Copper Plated Milford is the only milford hanger with the reinforced strap and patented keyholes, the keyhole allows for a faster and easier installation. The milford hanger is used to suspend copper tubing from floor joists and is used in horizontal applications.

Part #	Size	Packaged	Case Quantity
400-2	1/2" x 6"	25	500
400-3	3/4" x 6"	25	500
400-4	1" x 6"	25	500
400-5	1 1/4" x 6"	25	N/A
400-6	1 1/2" x 6"	25	N/A
400-7	2" x 6"	25	N/A

Part #	Size	Packaged	Case Quantity
400-8	1/2" x 12"	25	300
400-9	3/4" x 12"	25	300
400-10	1" x 12"	25	300
400-11	1 1/4" x 12"	25	N/A
400-12	1 1/2" x 12"	25	N/A
400-13	2" x 12"	25	N/A



Nails are Included and Packaged in Bags



Series 400 Narrow Milford Type Hangers

Size Range: 1/2" - 2" Material: Carbon Steel Finish: Copper Plating

Function: Used to suspend copper tubing from floor joists,

used in horizontal applications.



Nails are Included and Packaged in Bags

Part #	Size	Packaged	Case Quantity
400-2N	1/2" x 6"	25	500
400-3N	3/4" x 6"	25	500
400-4N	1" x 6"	25	500
400-5N	1 1/4" x 6"	25	N/A
400-6N	1 1/2" x 6"	25	N/A
400-7N	2" x 6"	25	N/A

Part #	Size	Packaged	Case Quantity
400-8N	1/2" x 12"	25	300
400-9N	3/4" x 12"	25	300
400-10N	1" x 12"	25	300
400-11N	1 1/4" x 12"	25	N/A
400-12N	1 1/2" x 12"	25	N/A
400-13N	2" x 12"	25	N/A



Series 550 Copper Plated Wire Hooks

Size Range: 1/2" – 1 1/2"

Material: Carbon Steel

Finish: Copper Plating

Function: Used to hang copper tubing from floor joist.

Our copper plated wire hooks are manufactured out of 10 gage material. The hook has nail points on each end to allow hook to be driven into the floor joist.





Part #	Copper Wire Hooks	Packaged
550-2	1/2" x 6"	50
550-3	1/2" x 8"	50
550-4	1/2" x 10"	50
550-7	3/4" x 6"	50
550-8	3/4" x 8"	50
550-9	3/4" x 10"	50
550-10	3/4" x 12"	50
550-12	1" x 6"	50
550-13	1" x 8"	50
550-14	1" x 10"	50
550-15	1" x 12"	50
550-16	1 1/4" x 6"	50
550-17	1 1/4" x 8"	50
550-18	1 1/4" x 10"	50
550-19	1 1/4" x 12""	50
550-20	1 1/2" x 6"	50

Manufactured At Our Rhode Island Facility




Series 575 Plastic Coated Copper Plated Wire Hooks

Size Range: 1/2" -1 1/4" Material: Carbon Steel

Finish: Copper Plated With Plastic Coating

Function: Used to hang copper tubing from floor joist.

Our Plastic Coated Copper Plated Wire Hooks are manufactured out of 10 gage material. The hook has nail points on each end to allow hook to be driven into the wooden rafter.




Part #	Copper Wire Hooks	Package
575-2	1/2" x 6"	50
575-3	1/2" x 8"	50
575-7	3/4" x 6"	50
575-8	3/4" x 8"	50
575-12	1" x 6"	50
575-13	1" x 8"	50
575-16	1 1/4" x 6"	50
575-17	1 1/4" x 8"	50

Manufactured At Our Rhode Island Facility




Hanger Company

Series 500 Plain Black Wire Hooks



Finish: Plain

Function: Used to suspend black iron pipe from floor joists.



Our plain wire pipe hooks are manufactured out of 10 gage material. These hooks are made to hang black iron pipe from wooden rafters. The hook has nail points on each end to allow hook to be driven into the wooden joists.

Part #	Black Wire Hooks	Package
500-2	1/2" x 6"	50
500-3	1/2" x 8"	50
500-4	1/2" x 10"	50
500-5	1/2" x 12"	50
500-7	3/4" x 6"	50
500-8	3/4" x 8"	50
500-9	3/4" x 10"	50
500-10	3/4" x 12"	50
500-12	1" x 6"	50
500-13	1" x 8"	50
500-14	1" x 10"	50
500-15	1" x 12"	50
500-16	1 1/4" x 6"	50
500-17	1 1/4" x 8"	50
500-18	1 1/4" x 10"	50

Manufactured At Our Rhode Island Facility




Series 525 Plastic Coated Black Wire Hooks

Size Range: 1/2" – 1 1/4" Material: Carbon Steel

Finish: Plain with Plastic Coating

Function: Used to hang black iron pipe from floor joist.

Our Plastic Coated Black Wire Hooks are manufactured out of 10 gage material. The hook has nail points on each end to allow hook to be driven into the floor joist.



Part #	Black Wire Hooks	Package
525-2	1/2" x 6"	50
525-3	1/2" x 8"	50
525-7	3/4" x 6"	50
525-8	3/4" x 8"	50
525-12	1" x 6"	50
525-13	1" x 8"	50
525-16	1 1/4" x 6"	50
525-17	1 1/4" x 8"	50

Manufactured At Our Rhode Island Facility



Series 800 Tube Support Bracket

Size Range: 1/2", 3/4" and 1"

Material: Carbon Steel Finish: Copper Plated

Function: Designed to position stub outs for all types of fixtures. Our keyhole slot adds

alignment flexibility.

Part #	Size	Accepts	Width	Gauge	Packaged
800-50	Tube Bracket Narrow	1/2" Tubing	1 1/4"	16	50
800-51	Tube Bracket Wide	1/2", 3/4" & 1" Tubing	1 1/2"	16	50



Standard packaging 50 PCs per box



Keyhole slot adds alignment flexibility

Series 850 Adjustable Slide Bracket

Size Range: 12" to 19"
Material: Carbon Steel
Finish: Galvanized

Function: Used to support pipe or ductwork

between joists.



Part #	Description	Gauge	Packaged
850-1	Adjustable Slide Bracket		25



Series 250 & 275 Black Iron Pipe Hangers

Size Range: 1/2" – 1 1/4" Material: Carbon Steel

Finish: Galvanized and Plastic Coated **Function:** Used to support black iron pipes.

Our Black Iron Pipe Hanger is similar to our Natick Hanger. It is a great substitute for black wire pipe hooks

and split ring hangers.



Nails are Included and Packaged in Bags

Part #	Size	Finish	Weight	Packaged
250-1	1/2" x 8"	Galvanized	.090 Lbs	25
250-2	3/4" x 8"	Galvanized	.105 Lbs	25
250-3	1" x 8"	Galvanized	.127 Lbs	25
250-4	1 1/4" x 8"	Galvanized	.180 Lbs	25
275-1	1/2" x 8"	Plastic Coated	.090 Lbs	25
275-2	3/4" x 8"	Plastic Coated	.105 Lbs	25
275-3	1" x 8"	Plastic Coated	.127 Lbs	25
275-4	1 1/4" x 8"	Plastic Coated	.180 Lbs	25

Manufactured At Our Rhode Island Facility



Series 3000-3100-3500-3700 Perforated Hanger Strapping

Size Range: 10', 50' and 100' Foot Coils

Material: 21 Gage Carbon Steel Finish: Plain, Copper, Galvanized

Function: Used to hang insulated flexible duct, round pipe or rectangular duct. This helps prevent the duct system from

sagging over long runs.



Fast Strap

Part #	Finish	Coil Size	Weight	Packaged
3000-10	Galvanized	10 Ft	.79 Lbs	20
3000-50	Galvanized	50 Ft	4.44 Lbs	1
3000-100	Galvanized	100 Ft	8.60 Lbs	1
3100-10	Copper Plated	10 Ft	.92 Lbs	20
3100-50	Copper Plated	50 Ft	4.90 Lbs	1
3100-100	Copper Plated	100 Ft	9.20 Lbs	1
3500-10	Plain Steel	10 Ft	.79 Lbs	20
3500-50	Plain Steel	50 Ft	4.44 Lbs	1
3500-100	Plain Steel	100 Ft	8.60 Lbs	1
<u>With</u>	Fast Strap		<u>With</u>	Fast Strap
	<u>Keyholes</u>			<u>Keyholes</u>
3000-10K	Galvanized	10 Ft	.79 Lbs	20
3000-50K	Galvanized	50 Ft	4.44 Lbs	1
3000-100K	Galvanized	100 Ft	8.60 Lbs	1
3100-10K	Copper Plated	10 Ft	.92 Lbs	20
3100-50K	Copper Plated	50 Ft	4.90 Lbs	1
3100-100K	Copper Plated	100 Ft	9.20 Lbs	1
3500-10K	Plain Steel	10 Ft	.79 Lbs	20
3500-50K	Plain Steel	50 Ft	4.44 Lbs	1
3500-100K	Plain Steel	100 Ft	8.60 Lbs	1
3700-10	Plastic	10 Ft	0.095 Lbs	1
3700-50	Plastic	50 Ft	0.63 Lbs	1
3700-100	Plastic	100 Ft	1.265 Lbs	1

Manufactured At Our Rhode Island Facility



Series 1000 Galvanized DWV Hangers

Size Range: 1 1/2" - 4" Available in 3 lengths: 12", 24" and 36"

Material: Carbon Steel Finish: Galvanized Plating

Function: Designed for rapid installation of both ABS and PVC plastic

DWV piping systems.

Our Galvanized DWV Hangers have patented keyholes that allow for faster and easier installation which makes for a labor saving, more profitable job. Simply pre screw or nail the floor joists where the length of pipe is to be installed, slip the hangers over the pipe, do not open the hanger. Lift the pipe by the hangers and slide the hanger over the screws that has been mounted into the floor joists.



Nails are Included and Packaged in Bags

Part #	Size	Finish	Weight	Packaged
1000-1	1 1/2" x 12"	Galvanized	.21 Lbs	25
1000-2	2" x 12"	Galvanized	.29 Lbs	25
1000-3	3" x 12"	Galvanized	.39 Lbs	25
1000-4	4" x 12"	Galvanized	.47 Lbs	25
1000-1-24	1 1/2" x 24"	Galvanized	.32 Lbs	25
1000-2-24	2" x 24"	Galvanized	.39 Lbs	25
1000-3-24	3" x 24"	Galvanized	.51 Lbs	25
1000-4-24	4" x 24"	Galvanized	.61 Lbs	25
1000-1-36	1 1/2" x 36"	Galvanized	.42 Lbs	25
1000-2-36	2" x 36"	Galvanized	.54 Lbs	25
1000-3-36	3" x 36"	Galvanized	.62 Lbs	25
1000-4-36	4" x 36"	Galvanized	.75 Lbs	25

Manufactured At Our Rhode Island Facility

Series 1300 Plastic Coated DWV Hangers

Size Range: 1 1/2" – 4" Available in 3 lengths 12", 24" and 36"

Material: Carbon Steel **Finish:** Galvanized Plating

Function: Designed for rapid installation of both ABS and PVC plastic

DWV piping systems.

Our Plastic Coated DWV Hangers have patented keyholes that allow for faster and easier installation which makes for a labor saving, more profitable job. Simply pre-screw or nail the floor joists where the length of pipe is to be installed, slip the hangers over the pipe, do not open the hanger. Lift the pipe by the hangers and slide the hanger over the screws that has been mounted into the floor joists.

Nails are Included and Packaged in Bags

Part #	Size	Finish	Weight	Packaged
1300-1	1 1/2" x 12"	Plastic Coated	.25 Lbs	25
1300-2	2" x 12"	Plastic Coated	.35 Lbs	25
1300-3	3" x 12"	Plastic Coated	.45 Lbs	25
1300-4	4" x 12"	Plastic Coated	.53 Lbs	25
1300-1-24	1 1/2" x 24"	Plastic Coated	.34 Lbs.	25
1300-2-24	2" x 24"	Plastic Coated	.41 Lbs	25
1300-3-24	3" x 24"	Plastic Coated	.53 Lbs.	25
1300-4-24	4" x 24"	Plastic Coated	.63 Lbs	25
1300-1-36	1 1/2" x 36"	Plastic Coated	.44 Lbs.	25
1300-2-36	2" x 36"	Plastic Coated	.56 Lbs	25
1300-3-36	3" x 36"	Plastic Coated	.64 Lbs.	25
1300-4-36	4" x 36"	Plastic Coated	.77 Lbs	25

Manufactured At Our Rhode Island Facility



Series 1100 Copper Plated DWV Hangers

Size Range: 1 1/2" – 4" Material: Carbon Steel Finish: Copper Plating

Function: Designed for rapid installation of both ABS and PVC plastic

DWV piping systems.

Our Copper Plated DWV Hangers have patented keyholes that allow for faster and easier installation which makes for a labor saving, more profitable job. Simply pre-screw or nail the floor joists where the length of pipe is to be installed, slip the hangers over the pipe, do not open the hanger. Lift the pipe by the hangers and slide the hanger over the screws that has been mounted into the floor joists.

Nails are Included and Packaged in Bags

Part #	Size	Finish	Weight	Packaged
1100-1	1 1/2" x 12"	Copper Plated	.25 Lbs	25
1100-2	2" x 12"	Copper Plated	.35 Lbs	25
1100-3	3" x 12"	Copper Plated	.47 Lbs	25
1100-4	4" x 12"	Copper Plated	.54 Lbs	25

Manufactured At Our Rhode Island Facility



Series 1050 Galvanized DWV Hangers Heavy Material Width 1"

Size Range: 1 1/2" – 4"

Material: Carbon Steel

Finish: Galvanized Plating

Function: Designed for rapid installation of both ABS and PVC plastic

DWV piping systems.

Part #	Size	Finish	Packaged
1050-1	1 1/2" x 12"	Galvanized	25
1050-2	2" x 12"	Galvanized	25
1050-3	3" x 12"	Galvanized	25
1050-4	4" x 12"	Galvanized	25
1050-6	6" X 12"	Galvanized	25

Series 1350 Plastic Coated DWV Hangers Material Width 1"

Size Range: 1 1/2" – 4

Material: Carbon Steel

Finish: Galvanized Plating

Function: Designed for rapid installation of both ABS and PVC plastic

DWV piping systems.

Part #	Size	Finish	Packaged
1350-1	1 1/2" x 12"	Plastic Coated	25
1350-2	2" x 12"	Plastic Coated	25
1350-3	3" x 12"	Plastic Coated	25
1350-4	4" x 12"	Plastic Coated	25
1350-6	6" X 12"	Plastic Coated	25

Manufactured At Our Rhode Island Facility





Series 1001 & 1002 Spiral Vent & Z-Vent Hanger

Size Range: 3"- 6" Available in 3 lengths 12", 24" and 36"

Material: Carbon Steel **Finish:** Galvanized

Function: Designed for rapid installation of both ABS and PVC plastic

Vent or Z Vent piping systems.

Our Spiral Vent and Z Vent Hangers have patented keyholes that allow for faster and easier installation which makes for a labor saving, more profitable job. Simply pre-screw or nail the floor joists where the length of pipe is to be installed, slip the hangers over the pipe, do not open the hanger. Lift the pipe by the hangers and slide the hanger over the screws that has been mounted into the floor joists.

Part #	Size	Finish	Weight	Packaged
1001-4	4" x 12" Spiral Vent	Galvanized	.49 Lbs	25
1001-5	5" x 12" Spiral Vent	Galvanized	.59 Lbs	25
1001-6	6" x 12" Spiral Vent	Galvanized	.73 Lbs	25
1002-3	3" x 12" Z Vent	Galvanized	.39 Lbs	25
1002-4	4" x 12" Z Vent	Galvanized	.285 Lbs	25

Manufactured At Our Rhode Island Facility




Series 1425 Glide Lock J Hook

Size Range: 1 1/2" – 4"

Function: The New Glide Lock J Hook allows pipe to glide back and forth to easily achieve your fit and gluing needs. Then simply apply pressure to the ratchet arm to lock pipe securely in place.





Part #	Size	Туре	Packaged
1425-1	1 1/2" x 7"	DWV	25
1425-2	2" x 7"	DWV	25
1425-3	3" x 7"	DWV	25
1425-4	4" x 7"	DWV	25

Hang It Faster!!!



See video demo @ www.WarwickHanger.com



Series 1400 Plastic J Hook for DWV and CTS

Size Range: 1/2" – 4"

Function: The J-Hook is an exceptional hanger that saves time and money. Hugs pipes snug and secure at easily determined grades. Snap in lock feature holds pipe securely, glue able with same adhesive used for pipe fittings. 3" hook fits both Sch30 and Sch40.

Part #	Size	Type	Packaged
1400-1	1 1/2" x 8"	DWV	25
1400-2	2" x 8"	DWV	25
1400-3	3" x 9"	DWV	25
1400-4	4" x 9"	DWV	25
1400-5	1/2" x 5"	CTS	25
1400-6	3/4" x 5"	CTS	25
1400-7	1" x 5"	CTS	25
1400-8	1 1/4" x 5"	CTS	25
1400-12	1/2" x 1/2" x 4"	CTS	25
1400-13	3/4" x 3/4" x 4"	CTS	25





Series 700 - - 725 - - 750 - - 900 - - 950 Nailing Plates

Gauge Range: 16 - 18

Material: Galvanized or plain hardened steel **Function:** Used to protect pipes from nail punctures

SN = Self Nailing Point H = Nailing Holes Only

Part #	Size	Gauge	SN/H	Packaged
700-3	1 1/2" x 3"	18	SN	100
700-5	1 1/2" x 5"	18	SN	100
700-6	1 1/2" x 6"	18	SN	100
700-9	1 1/2" x 9"	18	Н	25
700-18	1 1/2" X 18"	18	Н	25
700-20	2 3/4" X 8 3/4"	16	Н	25
700-22	1 1/2" X 22"	18	Н	25
700-23	3 1/2" X 5 3/4"	16	Н	25
700-28	1 1/2" X 28"	18	Η	25
715-3	1 1/2" X 3"	16	Η	100
715-5	1 1/2" X 5"	16	Τ	100
715-6	1 1/2" X 6"	16	Τ	100
725-3	1 1/2" X 3"	18	Τ	100
725-5	1 1/2" X 5"	18	Τ	100
725-6	1 1/2" X 6"	18	Н	100
730-8	5" x 8"	16	Τ	25
730-18	5" X 18"	16	Τ	25
750-3	1 1/2" X 3"	16	SN	100
750-5	1 1/2" X 5"	16	SN	100
750-6	1 1/2" X 6"	16	SN	100
920-9	3" X 9"	18	Н	25
920-18	3" X 18"	18	Н	25
935-5	3 1/2" X 5"	16	SN	25
935-6	3 1/2" X 6"	16	Н	25
955-8	5" X 8"	16	SN	25
955-16	5" X 16 5/16"	16	SN	25
955-18	5" X 18"	16	SN	25









Hang It Faster!!!

Manufactured At Our Rhode Island Facility



Hanger Company

Copper Plated Split Ring Hangers

Series 2100

Size Range: 3/8" – 4" Material: Malleable Iron Finish: Copper Plated

Function: For suspending non-insulated stationary pipe lines.

Our Copper Plated Split Ring Hangers are used to suspend copper tubing from joists, steel beams, wooden rafters or walls. They can be used in both

horizontal and vertical applications.







Hinged



Part #	Size	Rod Size	Weight	Packaged
2100-1	3/8"	3/8"	.07 Lbs	25
2100-2	1/2"	3/8"	.07 Lbs	25
2100-3	3/4"	3/8"	.09 Lbs	25
2100-4	1"	3/8"	.11 Lbs	25
2100-5	1 1/4"	3/8"	.12 Lbs	25
2100-6	1 1/2"	3/8"	.17 Lbs	25
2100-7	2"	3/8"	.22 Lbs	25
2100-8	2 1/2"	1/2"	.42 Lbs	25
2100-9	3"	1/2"	.48 Lbs	25
2100-10	4"	1/2"	.60 Lbs	25

For hinged add the letter "H" to the part number: Example: 2100-1 Copper Split Ring Hanger 2 Screw 2100-1-H Copper Split Ring Hanger Hinged

All Split Ring Hangers are available with an Epoxy coating. For Epoxy Finish add the letters "EPX" to the part number: **Example: 2100-1-EPX**



Hanger Company

Series 2000 Galvanized Split Ring Hangers

Size Range: 3/8"-4"
Material: Malleable Iron
Finish: Galvanized

Function: For suspending non-insulated stationary pipe lines.



2- Screw

Our Galvanized Split Ring Hangers are used to suspend black iron pipe from joist, steel beams, wooden rafters or walls. They can be used in both horizontal and vertical applications.



Hinged

Part #	Size	Rod Size	Weight	Packaged
2000-1	3/8"	3/8"	.12 Lbs	25
2000-2	1/2"	3/8"	.12 Lbs	25
2000-3	3/4"	3/8"	.13 Lbs	25
2000-4	1"	3/8"	.14 Lbs	25
2000-5	1 1/4"	3/8"	.19 Lbs	25
2000-6	1 1/2"	3/8"	.20 Lbs	25
2000-7	2"	3/8"	.30 Lbs	25
2000-8	2 1/2"	1/2"	.40 Lbs	25
2000-9	3"	1/2"	.57 Lbs	25
2000-10	4"	1/2"	.67 Lbs	25

For hinged add the letter "H" to the part number: Example: 2000-1 Galvanized Split Ring Hanger 2 Screw 2000-1-H Galvanized Split Ring Hanger Hinged



Series 2200 Black Split Ring Hangers

Size Range: 3/8"– 4"
Material: Malleable Iron

Finish: Plain

Function: For suspending non-insulated stationary pipe lines.



2- Screw

Our Black Split Ring Hangers are used to suspend black iron pipe from joists, steel beams, wooden rafters or walls. They can be used in both horizontal and

vertical applications.



Hinged

Part #	Size	Rod Size	Weight	Packaged
2200-1	3/8"	3/8"	.08 Lbs	25
2200-2	1/2"	3/8"	.10 Lbs	25
2200-3	3/4"	3/8"	.11 Lbs	25
2200-4	1"	3/8"	.19 Lbs	25
2200-5	1 1/4"	3/8"	.23 Lbs	25
2200-6	1 1/2"	3/8"	.25 Lbs	25
2200-7	2"	3/8"	.30 Lbs	25
2200-8	2 1/2"	1/2"	.45 Lbs	25
2200-9	3"	1/2"	.49 Lbs	25
2200-10	4"	1/2"	.61 Lbs	25

For hinged add the letter "H" to the part number: Example: 2200-1 Plain Split Ring Hanger 2 Screw 2200-1-H Plain Split Ring Hanger Hinged



Series 2600 Copper Plated Adjustable Band Hangers

Size Range: 1/2"-6"
Material: Carbon Steel
Finish: Copper Plating

Function: Used for the suspension of both non-insulated

and insulated piping.



Our Copper Plated A-Band Tubing Hangers are made out of 17 gage material. They are used to suspend copper tubing from joists, wooden rafters, and steel beams. Use in conjunction with threaded rod to achieve various heights.



Part #	Size	Rod Size	Finish	Weight	Packaged
2600-1	1/2"	3/8"	Copper Plated	.10 Lbs	25
2600-2	3/4"	3/8"	Copper Plated	.10 Lbs	25
2600-3	1"	3/8"	Copper Plated	.10 Lbs	25
2600-4	1 1/4"	3/8"	Copper Plated	.11 Lbs	25
2600-5	1 1/2"	3/8"	Copper Plated	.12 Lbs	25
2600-6	2"	3/8"	Copper Plated	.13 Lbs	25
2600-7	2 1/2"	1/2"	Copper Plated	.19 Lbs	25
2600-8	3"	1/2"	Copper Plated	.27 Lbs	25
2600-10	4"	5/8"	Copper Plated	.44 Lbs	25
2600-11	5"	5/8"	Copper Plated	.66 Lbs	25
2600-12	6"	3/4"	Copper Plated	.69 Lbs	25



Hanger Company

Series 2500 Plain Adjustable Band Hangers

Size Range: 1/2" – 6" Material: Carbon Steel


Finish: Plain

Function: Used for the suspension of both non-insulated

and insulated pipe.



Our Plain Steel A-Band Black Iron Pipe Hangers are made out of 17 gage material. They are used to suspend Black Iron Pipe from joists, wooden rafters, and steel beams. Use in conjunction with threaded rod to achieve various heights.



Part #	Size	Rod Size	Finish	Gauge	Weight	Packaged
2500-1	1/2"	3/8"	Plain	18	.09 Lbs	25
2500-2	3/4"	3/8"	Plain	18	.09 Lbs	25
2500-3	1"	3/8"	Plain	18	.11 Lbs	25
2500-4	1 1/4"	3/8"	Plain	18	.12 Lbs	25
2500-5	1 1/2"	3/8"	Plain	18	.13 Lbs	25
2500-6	2"	3/8"	Plain	18	.16 Lbs	25
2500-7	2 1/2	1/2"	Plain	16	.25 Lbs	25
2500-8	3"	1/2"	Plain	16	.33 Lbs	25
2500-9	3 1/2"	1/2"	Plain	16	.45 Lbs	25
2500-10	4"	5/8"	Plain	16	.58 Lbs	25
2500-11	5"	5/8"	Plain	11	1.00 Lbs	10
2500-12	6"	3/4"	Plain	11	1.25 Lbs	10

Manufactured At Our Rhode Island Facility




Series 2950 Copper Plated Swivel Hanger

Size Range: 1/2" – 4" Material: Carbon Steel Finish: Copper Plated

Function: Used for the suspension of non-insulated stationary

copper tubing.

Our Copper Plated Swivel Hanger is used for general piping purposes. Knurled swivel nut design permits hanger adjustment after installation. Spring tension on swivel nut holds it securely in hanger before installation. Swivel nut easily removed.



Part #	Size	Finish	Weight	Knurl Nut Size	Packaged
2950-1	1/2"	Copper Plated	.15 Lbs	3/8"	25
2950-2	3/4"	Copper Plated	.15 Lbs	3/8"	25
2950-3	1"	Copper Plated	.16 Lbs	3/8"	25
2950-4	1 1/4"	Copper Plated	.18 Lbs	3/8"	25
2950-5	1 1/2"	Copper Plated	.20 Lbs	3/8"	25
2950-6	2"	Copper Plated	.22 Lbs	3/8"	25
2950-7	2 1/2"	Copper Plated	.28 Lbs	3/8"	25
2950-8	3"	Copper Plated	.30 Lbs	3/8"	25
2950-10	4"	Copper Plated	.33 Lbs	5/8"	25

Manufactured At Our Rhode Island Facility



Series 2900 Galvanized Swivel Hangers

Size Range: 1/2"-8"
Material: Carbon Steel
Finish: Galvanized

Function: Used for the suspension of both non-insulated

and insulated piping.

Our Galvanized Swivel Hanger is used for general piping purposes. Knurled swivel nut design permits hanger adjustment after installation. Spring tension on swivel nut holds it securely in hanger before installation.

Swivel nut easily removed.

Part #	Size	Finish	Weight	Knurl Nut Size	Packaged
2900-1	1/2"	Galvanized	.15 Lbs	3/8"	25
2900-2	3/4"	Galvanized	.15 Lbs	3/8"	25
2900-3	1"	Galvanized	.16 Lbs	3/8"	25
2900-4	1 1/4"	Galvanized	.18 Lbs	3/8"	25
2900-5	1 1/2"	Galvanized	.20 Lbs	3/8"	25
2900-6	2"	Galvanized	.22 Lbs	3/8"	25
2900-7	2 1/2	Galvanized	.37 Lbs	3/8"	25
2900-8	3"	Galvanized	.44 Lbs	3/8"	25
2900-9	3 1/2"	Galvanized	.51 Lbs	3/8"	25
2900-10	4"	Galvanized	.56 Lbs	3/8"	25
2900-11	5"	Galvanized	.97 Lbs	1/2"	25
2900-12	6"	Galvanized	1.10 Lbs	1/2"	25
2900-13	8"	Galvanized	1.38 Lbs	1/2"	25

Manufactured At Our Rhode Island Facility



Series 650 Copper Plated Strut Clamps



Size Range: 1/2" – 4"
Material: Carbon Steel
Finish: Copper Plating

Function: The copper pipe clamps are designed for copper tubing and used at any

point along the slot side of the channel strut.



Part #	Size	Weight	Packaged
650-2	1/2"	.07 Lbs	25
650-3	3/4"	.09 Lbs	25
650-4	1"	.11 Lbs	25
650-5	1 1/4"	.12 Lbs	25
650-6	1 1/2"	.17 Lbs	25
650-7	2"	.22 Lbs	25
650-8	2 1/2"	.42 Lbs	25
650-9	3"	.48 Lbs	25
650-10	3 1/2"	.60 Lbs	25
650-11	4"	.72 Lbs	25



Series 600 Galvanized Strut Clamps

Size Range: 1/2"-8"
Material: Carbon Steel
Finish: Galvanized

Function: Used at any point along the slot side of the channel

strut and are inserted into the two channel returns.

The galvanized pipe clamps are designed for black iron pipe, PVC and ABS for

fastening of the piping for any industry.



Part #	Size	Weight	Packaged
600-2	1/2"	.12 Lbs	25
600-3	3/4"	.13 Lbs	25
600-4	1"	.14 Lbs	25
600-5	1 1/4"	.19 Lbs	25
600-6	1 1/2"	.20 Lbs	25
600-7	2"	.30 Lbs	25
600-8	2 1/2"	.40 Lbs	25
600-9	3"	.57 Lbs	25
600-10	3 1/2"	.67 Lbs	25
600-11	4"	.79 Lbs	25
600-12	5"	.94 Lbs	25
600-13	6"	1.24 Lbs	25
600-14	8"	1.41 Lbs	25




Series 675-690-691 Cushion Clamps

Size Range: 3/16" – 6" Material: Carbon Steel Finish: Galvanized

Function: Used to absorb shock and vibration. Reduces

unwanted noise and prevents galvanic corrosion.



Part #	Size	O.D. Size	Weight	Packaged
675-1	5/8"	3/4"	.13 Lbs	25
675-2	3/16"	1/4"	.10 Lbs	25
675-3	1/4"	3/8"	.10 Lbs	25
675-4	3/8"	1/2"	.13 Lbs	25
675-5	1/2"	5/8"	.14 Lbs	25
675-6	3/4"	7/8"	.15 Lbs	25
675-7	1"	1 1/8"	.15 Lbs	25
675-8	1 1/4"	1 3/8"	.17 Lbs	25
675-9	1 1/2"	1 5/8"	.18 Lbs	25
675-10	2"	2 1/8"	.20 Lbs	25
675-11	2 1/2"	2 5/8"	.33 Lbs	10
675-12	3"	3 1/8"	.60 Lbs	10
675-13	4"	4 1/8"	.90 Lbs	10
675-14	5"	5 1/8"	1.3 Lbs	10
675-15	6"	6 1/8"	1.4 Lbs	10



675-20	20' Roll	Cushion Strip	1

Strut

Part #	Description	Gauge	Packaged
691-10	Strut 1 5/8" X 13/16" X 10'	12	1
691-15	Strut 1 5/8" X 1 5/8" X 10'	12	1









Series 2755 Copper Painted Clevis Hangers

Size Range: 1/2" - 4"
Material: Carbon Steel
Finish: Copper Plating

Function: Used to suspend non-insulated stationary copper

tubing.





Part #	Size	Rod Size	Weight	Packaged
2755-1	1/2"	3/8"	.26 Lbs	25
2755-2	3/4"	3/8"	.28 Lbs	25
2755-3	1"	3/8"	.30 Lbs	25
2755-4	1 1/4"	3/8"	.33 Lbs	25
2755-5	1 1/2"	3/8"	.35 Lbs	25
2755-6	2"	3/8"	.41 Lbs	25
2755-7	2 1/2"	3/8"	.70 Lbs	10
2755-8	3"	3/8"	.91 Lbs	10
2755-10	4"	1/2"	1.05 Lbs	10



Series 2700 Carbon Steel Clevis Hangers

Size Range: 1/2" – 12" Material: Carbon steel

Finish: Plain

Function: Used to suspend non-insulated stationary black iron

pipe.

Our Clevis Hanger is used in conjunction with threaded rod to achieve various heights. It allows the pipe to feed through the U portion of the hanger. Used in horizontal pipe

runs.





Series 2850 Copper Painted Riser Clamps

Size Range: 1/2"-4"
Material: Carbon Steel
Finish: Copper Plating

Function: Used for supporting copper tubing through floors.

Our Riser Clamp is used for the support copper tubing lines where extreme load conditions exist. The Riser Clamp utilizes the structure to support the legs on each end of the clamp, normally rests on the floor through which the riser passes.





Part #	Size	Material	Weight	Packaged
2855-1	1/2"	Carbon Steel	1.44 Lbs	25
2855-2	3/4"	Carbon Steel	1.44 Lbs	25
2855-3	1"	Carbon Steel	1.47 Lbs	25
2855-4	1 1/4"	Carbon Steel	1.50 Lbs	25
2855-5	1 1/2"	Carbon Steel	1.55 Lbs	25
2855-6	2"	Carbon Steel	1.69 Lbs	10
2855-7	2 1/2"	Carbon Steel	2.20 Lbs	10
2855-8	3"	Carbon Steel	2.50 Lbs	10
2855-10	4"	Carbon Steel	3.49 Lbs	10



Series 2800 Riser Clamps

Size Range: 1/2"-12"
Material: Carbon Steel

Finish: Plain

Function: Used for supporting black iron piping through floors.

Our Riser Clamp is used for the support of steel or cast iron pipe lines where extreme load conditions exist. The Riser Clamp utilizes the structure to support the legs on each end of clamp, normally rests on the floor through which the riser passes.





Part #	Size	Material	Weight	Packaged
2800-1	1/2"	Carbon Steel	1.44 Lbs	25
2800-2	3/4"	Carbon Steel	1.44 Lbs	25
2800-3	1"	Carbon Steel	1.47 Lbs	25
2800-4	1 1/4"	Carbon Steel	1.50 Lbs	25
2800-5	1 1/2"	Carbon Steel	1.55 Lbs	25
2800-6	2"	Carbon Steel	1.69 Lbs	10
2800-7	2 1/2"	Carbon Steel	2.20 Lbs	10
2800-8	3"	Carbon Steel	2.50 Lbs	10
2800-9	3 1/2"	Carbon Steel	2.63 Lbs	10
2800-10	4"	Carbon Steel	3.49 Lbs	10
2800-11	5"	Carbon Steel	3.90 Lbs	5
2800-12	6"	Carbon Steel	5.55 Lbs	5
2800-13	8"	Carbon Steel	7.80 Lbs	5
2800-14	10"	Carbon Steel	9.72 Lbs	5
2800-15	12"	Carbon Steel	12.60 Lbs	5



Series 2825 & 2875 Short Arm Riser Clamps


Size Range: 11/2" – 4" Material: Carbon Steel

Finish: Plain and Plastic Coated

Function: Used for supporting black iron piping through floors.

Our Riser Clamp is used for the support of PVC or ABS pipe lines where extreme load conditions exist. The Riser Clamp utilizes the structure to support the legs on each end of clamp, normally rests on the floor through which the riser passes.





Part #	Size	Material	Weight	Packaged
2825-5	1 1/2" Black	Carbon Steel	.52 Lbs	25
2825-6	2" Black	Carbon Steel	.55 Lbs	10
2825-8	3" Black	Carbon Steel	.72 Lbs	10
2825-10	4" Black	Carbon Steel	.89 Lbs	10
2875-5	1 1/2" Plastic Coated	Carbon Steel	.58 Lbs	10
2875-6	2" Plastic Coated	Carbon Steel	.65 Lbs	10
2875-8	3" Plastic Coated	Carbon Steel	.85 Lbs	10
2875-10	4" Plastic Coated	Carbon Steel	1.01 Lbs	10



Series 2840 Double Bolt Clamps


Size Range: 3" – 6" Material: Carbon Steel

Finish: Plain

Function: Recommended for the suspension of heavy duty high temperature


pipe runs. This design allows flexibility of clamp installation.





Part #	Size	Material	Packaged
2840-8	3"	Carbon Steel	10
2840-10	4"	Carbon Steel	10
2840-12	6"	Carbon Steel	5





Closet Flange Extension Kit



Adjustable Closet Flange

Flanges



Street Compression Flange



Adjustable Street Closet Flange



Closet Flange Replacement

Part #	Size	Package
CF300A	1/4" Closet Flange Extension Kit (ABS)	12
CF300P	1/4" Closet Flange Extension Kit (PVC)	12
CF350P	1/4" Closet Flange Extension (PVC)	12
CF250P	Closet Flange Extension Kit Bulk (PVC)	10
GF340A	Adjustable 3" X 4" Closet Flange (ABS)	12
GF340P	Adjustable 3" X 4" Closet Flange (PVC)	12
GH950A	Street Compression 4" Closet Flange (ABS)	12
GH950P	Street Compression 4" Closet Flange (PVC)	12
IF333A	Adjustable 3" Street Closet Flange (ABS)	12
IF333P	Adjustable 3" Street Closet Flange (PVC)	12
MH350A	3" Closet Flange Replace. Comp. (ABS)	12
MH350P	3" Closet Flange Replace. Comp. (PVC)	12
MH450P	4"Closet Flange Replace. Comp. (PVC)	12



Series 700 Stud Protectors



Size Range: Single and Double Stud Protection.


Material: Carbon Steel **Finish:** White Enamel

Function: Stud shoes reinforce studs notched in construction.

Stud Shoes provide tension load capacity as well as increased compression loads. Flared flanges provide greater strength. Installs over pipe up to 2 3/8" outside diameter.

Part #	Size	Gauge	Weight	Packaged
700-50	Single Stud Protector	18	.45 Lbs	25
700-51	Double Stud Protector	18	.52 Lbs	25





Series 1550 Pipe Shields



Size Range: 1 1/2" – 10"

Material: Carbon Steel

Finish: Galvanized Plating

Function: To protect pipe insulation when used with hangers.

Designed for protection of foam, fiberglass or high density insulation when used with pipe hangers.

Part #	Size	Packaged
1550-1	1 1/2" x 10"	25
1550-2	2" x 10"	25
1550-3	2 1/2" x 10"	25
1550-4	3" x 10"	25
1550-10	3 1/2" X 12"	25
1550-5	4" x 10"	25
1550-6	5" x 10"	25
1550-7	6" x 10"	25
1550-8	8" x 10"	25
1550-9	10" x 10"	25

Part #	Size	Packaged
1552-1	1 1/2" x 12"	25
1552-2	2" x 12"	25
1552-3	2 1/2" x 12"	25
1552-4	3" x 12"	25
1552-10	3 1/2" X 12"	25
1552-5	4" x 12"	25
1552-6	5" x 12"	25
1552-7	6" x 12"	25
1552-8	8" x 12"	25
1552-9	10" x 12"	25



Series 2004-2104-2024 Top Beams

Size Range: 3/8" – 1/2" Material: Malleable Iron

Finish: Plain

Function: Used in conjunction with a wide variety of pipe hangers.

Our Top Beam Clamp is designed to clamp onto a steel I beam and is used in conjunction with threaded rod. The clamp has a threaded hole to accept a piece of threaded rod allowing various types of pipe hangers to be threaded on to the opposite end of the rod.



Part #	Junior Size	Rod Size	Weight	Packaged
2004-C-P	3/8"	3/8"	.30 Lbs	25
2004-D-P	1/2"	1/2"	.35 Lbs	25

Part #	Senior Size	Rod Size	Weight	Packaged
2104-C-P	3/8"	3/8"	.40 Lbs	25
2104-D-P	1/2"	1/2"	.49 Lbs	25

Beam Clamp/Retaining Strap

Size Range: 4" – 24" Material: Galvanized

Function: Used to secure top beam and c-clamps to a metal beam, girder or similar structure. Simply slide keyhole in retaining strap over bolt on clamp, then bend retaining strap around metal beam or girder.

Part #	Size	Weight	Packaged
2024-1	4"	.060	25
2024-2	6"	.090	25
2024-3	8"	.120	25
2024-4	10"	.155	25
2024-5	12"	.190	25
2024-6	14"	.210	25
2024-7	16"	.270	25
2024-8	20"	.330	25
2024-9	24"	.385	25



Series 2002-2003 Side Beam Connectors


Size Range: 3/8" – 1/2" Material: Malleable Iron

Finish: Plain

Function: Used to mount threaded rod.

Our Side Beam Connector is designed to mount onto a steel beam or joist and is used in conjunction with threaded rod. It has a threaded hole to accept threaded rod allowing various types of pipe hangers to be threaded on to the opposite end of the rod.

Part #	Size	Rod Size	Weight	Packaged
2003-C	3/8"	3/8"	.12 Lbs	25
2003-D	1/2"	1/2"	.17 Lbs	25



Ceiling Flange

Size Range: 3/8"-1/2" Threaded Rod

Material: Malleable Iron

Finish: Plain, Galvanized and Copper **Function:** Used to mount threaded rod.

Our Ceiling Flanges are used in conjunction with threaded rod. The flanges can be mounted to most surfaces. The center hole accepts a piece of 3/8 threaded rod allowing various types of pipe hangers to be threaded on to the opposite end of the rod.

Part #	Finish	Rod Size	Weight	Packaged
2002-A-P	Plain	1/4"	.14 Lbs	25
2002-C-P	Plain	3/8"	.14 Lbs	25
2002-D-P	Plain	1/2"	.14 Lbs	25
2002-A-G	Galvanized	1/4"	.16 Lbs	25
2002-C-G	Galvanized	3/8"	.16 Lbs	25
2002-D-G	Galvanized	1/2"	.16 Lbs	25
2002-A-C	Copper Plated	1/4"	.16 Lbs	25
2002-C-C	Copper Plated	3/8"	.16 Lbs	25
2002-D-C	Conner Plated	1/2"	16 l hc	25



Series 2005 Steel C-Clamp

Size Range: 3/8" - 5/8" Rod Material: Carbon Steel Finish: Plain and Galvanized

Function: Used to mount threaded rod.

Our Steel C-Clamp is designed to mount onto a steel beam or joist and is used in conjunction with threaded rod. It has a threaded hole to accept threaded rod allowing various types of pipe hangers to be threaded on to the opposite end of the rod.





Part #	Size	Rod Size	Weight	Packaged
2005-C-P	3/8"	3/8"	.41	25
2005-D-P	1/2"	1/2"	.65	25
2005-E-P	5/8"	5/8"	.90	25
2005-F-P	3/4"	3/4"	.98	25





Series 2110-2010-2111 Hardware

Part #	Description	Finish	Size	Packaged
2110-A-G	Rod Couplings	Plated	1/4 - 20	50
2110-B-G	Rod Couplings	Plated	5/16 -18	50
2110-C-G	Rod Couplings	Plated	3/8 - 16	50
2110-D-G	Rod Couplings	Plated	1/2 - 13	50
2110-E-G	Rod Couplings	Plated	5/8 - 11	50
2110-F-G	Rod Couplings	Plated	3/4- 10	50
2110-G-G	Rod Couplings	Plated	7/8 - 9	50
2110-H-G	Rod Couplings	Plated	1 - 8	50
2010-A-G	Coupling Reducers	Plated	1/4" to 3/8"	50
2010-D-G	Coupling Reducers	Plated	3/8" to 1/2"	50



Part #	Description	Finish	Size	Packaged
2111-A-P	Lag Screws	Plain	3/8" x 4"	25
2111-B-P	Lag Screws	Plain	3/8" x 6"	25
2111-C-P	Lag Screws	Plain	3/8" x 8"	25
2111-D-P	Lag Screws	Plain	3/8" x 12"	25
2111-A-G	Lag Screws	Plated	3/8" x 4"	25
2111-B-G	Lag Screws	Plated	3/8" x 6"	25
2111-C-G	Lag Screws	Plated	3/8" x 8"	25
2111-D-G	Lag Screws	Plated	3/8" X 12"	25





Series 2006-2009 Hardware

Part #	Description	Finish	6 Feet	Packaged
2006-A-P	Threaded Rod	Plain	1/4 - 20	50
2006-B-P	Threaded Rod	Plain	5/16-18	35
2006-C-P	Threaded Rod	Plain	3/8 - 16	25
2006-D-P	Threaded Rod	Plain	1/2 - 13	13
2006-E-P	Threaded Rod	Plain	5/8 - 11	8
2006-F-P	Threaded Rod	Plain	3/4 - 10	5
2006-G-P	Threaded Rod	Plain	7/8 – 9	4
2006-H-P	Threaded Rod	Plain	1 – 8	2
2006-A-G	Threaded Rod	Zinc Plated	1/4 - 20	50
2006-B-G	Threaded Rod	Zinc Plated	5/16-18	35
2006-C-G	Threaded Rod	Zinc Plated	3/8 - 16	25
2006-D-G	Threaded Rod	Zinc Plated	1/2 - 13	13
2006-E-G	Threaded Rod	Zinc Plated	5/8 - 11	8
2006-F-G	Threaded Rod	Zinc Plated	3/4 - 10	5
2006-G-G	Threaded Rod	Zinc Plated	7/8 – 9	4
2006-H-G	Threaded Rod	Zinc Plated	1 – 8	2



Part #	Description	Finish	Diam./Length	Packaged
2006-C-G-2 1/2"	Threaded Rod	Zinc Plated	3/8" X 2 1/2"	100
2006-C-P-1 1/2"	Threaded Rod	Plain	3/8" X 1 1/2"	100
2006-C-P-2"	Threaded Rod	Plain	3/8" X 2"	100
2006-C-P-2 1/2"	Threaded Rod	Plain	3/8" X 2 1/2"	100
2006-C-P-4"	Threaded Rod	Plain	3/8" X 4"	100
2006-C-P-6"	Threaded Rod	Plain	3/8" X 6"	100
2006-D-P-3/4"	Threaded Rod	Plain	1/2" X 3/4"	100
2006-D-P-2"	Threaded Rod	Plain	1/2" X 2"	100
2006-D-P-8"	Threaded Rod	Plain	1/2" X 8"	100





Series 2007 Hardware

Part #	Description	Finish	Size	Packaged
2009-A-P	Washer	Plain	1/4"	100
2009-B-P	Washer	Plain	5/16"	100
2009-C-P	Washer	Plain	3/8"	100
2009-D-P	Washer	Plain	1/2"	100
2009-E-P	Washer	Plain	5/8"	100
2009-F-P	Washer	Plain	3/4"	100
2009-G-P	Washer	Plain	7/8"	100
2009-H-P	Washer	Plain	1"	100
2009-A-G	Washer	Zinc Plated	1/4"	100
2009-B-G	Washer	Zinc Plated	5/16"	100
2009-C-G	Washer	Zinc Plated	3/8"	100
2009-D-G	Washer	Zinc Plated	1/2"	100
2009-E-G	Washer	Zinc Plated	5/8"	100
2009-F-G	Washer	Zinc Plated	3/4"	100
2009-G-G	Washer	Zinc Plated	7/8"	100
2009-H-G	Washer	Zinc Plated	1"	100



Part #	Description	Finish	Size	Packaged
2007-B-P	Heavy Hex Nut	Plain	5/16-18	100
2007-C-P	Heavy Hex Nut	Plain	3/8 - 16	100
2007-D-P	Heavy Hex Nut	Plain	1/2 - 13	100
2007-E-P	Heavy Hex Nut	Plain	5/8 - 11	100
2007-F-P	Heavy Hex Nut	Plain	3/4 - 10	100
2007-G-P	Heavy Hex Nut	Plain	7/8 - 9	100
2007-H-P	Heavy Hex Nut	Plain	1 - 8	100
2007-A-G	Heavy Hex Nut	Zinc Plated	1/4 - 20	100
2007-B-G	Heavy Hex Nut	Zinc Plated	5/16-18	100
2007-C-G	Heavy Hex Nut	Zinc Plated	3/8 - 16	100
2007-D-G	Heavy Hex Nut	Zinc Plated	1/2 - 13	100
2007-E-G	Heavy Hex Nut	Zinc Plated	5/8 - 11	100
2007-F-G	Heavy Hex Nut	Zinc Plated	3/4 - 10	100
2007-G-G	Heavy Hex Nut	Zinc Plated	7/8 - 9	100
2007-H-G	Heavy Hex Nut	Zinc Plated	1 - 8	100



Hang It Faster!!!



Series 2128-2115-2116-2014-2300 Hardware









			· - · · · · ·
Part #	Description	Finish	Packaged
2128-A-P	5/8" X 1" Heavy Hex Bolt	Plain	25
2128-B-P	5/8" X 1 1/4" Heavy Hex Bolt	Plain	25
2128-C-P	5/8" X 1 1/2" Heavy Hex Bolt	Plain	25
2128-D-P	5/8" X 2" Heavy Hex Bolt	Plain	25
2128-E-P	5/8" X 2 1/4" Heavy Hex Bolt	Plain	25
2128-F-P	5/8" X 2 1/2" Heavy Hex Bolt	Plain	25
2128-G-P	5/8" X 3" Heavy Hex Bolt	Plain	25
2128-A-G	5/8" X 1" Heavy Hex Bolt	Galvanized	25
2128-B-G	5/8" X 1 1/4" Heavy Hex Bolt	Galvanized	25
2128-C-G	5/8" X 1 1/2" Heavy Hex Bolt	Galvanized	25
2128-D-G	5/8" X 2" Heavy Hex Bolt	Galvanized	25
2128-E-G	5/8" X 2 1/4" Heavy Hex Bolt	Galvanized	25
2128-F-G	5/8" X 2 1/2" Heavy Hex Bolt	Galvanized	25
2128-G-G	5/8" X 3" Heavy Hex Bolt	Galvanized	25
2115-E	#12 X 1 1/2" Drive Screw	Plain	100
2115-F	#12 X 2" Drive Screw	Plain	100
2116-A	1/4" x 3/4" Mushroom Drive Pin	Zinc	100
2116-B	1/4" x 1" Mushroom Drive Pin	Zinc	100
2116-C	1/4" x 1 1/4" Mushroom Drive Pin	Zinc	100
2116-D	1/4" x 1 1/2" Mushroom Drive Pin	Zinc	100
2116-E	1/4" x 2" Mushroom Drive Pin	Zinc	100
2014-A	1/4" x 1 1/4 Fender Washers	Zinc	100
2014-B	5/16" x 1 1/4 Fender Washers	Zinc	100
2014-C	3/8" x 1 1/4 Fender Washers	Zinc	100
2300-C	3/8" Drop In Anchor (Uses 1/2" Drill)	Zinc	50
2300-D	1/2" Drop In Anchor	Zinc	50



Series 2012-2013-2400 Strut Hardware








Part #	Description	Finish	Packaged
2012-A	1/4" Spring Nut	Plated	50
2012-C	3/8" Spring Nut	Plated	50
2012-D	1/2" Spring Nut	Plated	50
2012-E	5/8" Spring Nut	Plated	50
2012-F	3/4" Spring Nut	Plated	50
2013-A	1/4" Spring Less Nut	Plated	50
2013-C	3/8" Spring Less Nut	Plated	50
2013-D	1/2" Spring Less Nut	Plated	50
2013-E	5/8" Spring Less Nut	Plated	50
2013-F	3/4" Spring Less Nut	Plated	50
2400-8	4" X 3" Angle Bracket	Plain	25
2400-9	4 1/2" X 3 1/2" Angle Bracket	Plain	25







Series 2117 Nylon Nailin



Size Range: 1" to 2"
Material: Carbon Steel
Finish: Carbon Steel

Function: The Nylon Nailin is a nail drive anchor with a body formed from engineered plastic and drive nails available in carbon and stainless steel. The anchor can be used in concrete, block, brick or stone. The anchor is pre-assembled with either a carbon steel or stainless steel nail. This anchor is not recommended for applications overhead. For overhead applications, please refer to the Zamac Hammer-Screw.

Part #	Size	Packaged	Case Quantity
2117-D	1/4" X 1"	25	1000
2117-F	1/4" X 1 1/2"	25	1000
2117-G	1/4" X 2"	25	1000

Series 2130 and 2131 Wall Dog

Size Range:

Material: Carbon Steel **Finish:** Galvanized

Function: The Wall Dog is an all steel, one piece, threaded fastener, which is used to

fasten various fixtures directly to drywall.

Part #	Size	Description	Packaged
2130-A	3/16" X 1 1/4"	Oval Head	100
2131-A	1/4" X 1 1/4"	Pan Head	100





Series 2112 Mechanical Anchors





Part #	Mount	Size	Rod Size	Weight	Packaged
2109-L	Vertical	1 1/4" Concrete Vertical Mount	1/4"		25
2109-B	Vertical	2" Wood Vertical Mount	1/4"		25
Part #	Mount	Size	Rod Size	Weight	Packaged
2112-F	Side	1" Wood Side Mount	3/8"	.060	25
2112-E	Vertical	1" Wood Vertical Mount	3/8"	.065	25
2112-A	Side	2" Wood Side Mount	3/8"	.07	25
2112-B	Vertical	2" Wood Vertical Mount	3/8"	.07	25
2112-P	Vertical	2 1/2" Wood Vertical Mount	3/8"	.085	25
2112-G	Vertical	3" Wood Vertical Mount	3/8"	.080	25
2112-H	Vertical	1" Steel Vertical Mount w/Nut	3/8"	.065	25
2112-M	Vertical	1 1/2" Steel Side Mount	3/8"	.065	25
2112-I	Vertical	2" Steel Vertical Mount	3/8"	.075	25
2112-D	Vertical	1 3/4" Concrete Vertical Mount	3/8"	.045	25
2112-C	Side	1 3/4" Concrete Side Mount w/Bit	3/8"	.07	25
2112-U	Vertical	1 1/2" Steel Vertical Mount	3/8"	.07	25
2112-K	Vertical	2 3/4" Concrete Vertical Mount	1/2"	.155	25
2112-R	3/8"	Nut Driver for Cement	3/8"	.055	1
2112-T	1/2"	Nut Driver for Cement	1/2"	.135	1
		(For item #'s 2112-C & 2112-K)			
2112-S		Universal Driver For Steel and Wood		.100	1



Hardware

Part #	Description	Finish	Size	Packaged
2001-A-P	Lag Ends	Plain	3/8" x 3 1/2"	25
2001-B-P	Lag Ends	Plain	3/8" x 4"	25
2001-C-P	Lag Ends	Plain	3/8" x 4 1/2"	25
2001-D-P	Lag Ends	Plain	3/8" x 6"	25
2001-E-P	Lag Ends	Plain	3/8" x 8"	25
2001-F-P	Lag Ends	Plain	3/8" x 12"	25
2011-A-P	Lag Ends	Plain	1/2" x 3 1/2"	25
2011-B-P	Lag Ends	Plain	1/2" x 4"	25
2011-C-P	Lag Ends	Plain	1/2" x 4 1/2"	25
2011-D-P	Lag Ends	Plain	1/2" X 6"	25
2011-E-P	Lag Ends	Plain	1/2" X 8"	25
2011-F-P	Lag Ends	Plain	1/2" x 12"	25
2001-A-G	Lag Ends	Plated	3/8" x 3 1/2"	25
2001-B-G	Lag Ends	Plated	3/8" x 4"	25
2001-C-G	Lag Ends	Plated	3/8" x 4 1/2"	25
2001-D-G	Lag Ends	Plated	3/8" x 6"	25
2001-E-G	Lag Ends	Plated	3/8" x 8"	25
2001-F-G	Lag Ends	Plated	3/8" x 12"	25
2011-A-G	Lag Ends	Plated	1/2" x 3 1/2"	25
2011-B-G	Lag Ends	Plated	1/2" X 4"	25
2011-C-G	Lag Ends	Plated	1/2" x 4 1/2"	25
2011-D-G	Lag Ends	Plated	1/2" X 6"	25
2011-E-G	Lag Ends	Plated	1/2" X 8"	25
2011-F-G	Lag Ends	Plated	1/2" x 12"	25
2001-H	Lag End Driver 3/8"	Plain	3/8"	1
2001-l	Lag End Driver 1/2"	Plain	1/2"	1





Lag End Driver



Hanger Company

Series 2122 Power Stud



Size Range: 2 1/4" and 3" Material: Carbon Steel

Function: The Power-Stud anchor, formerly known as the Rawl-Stud, is a fully threaded, torque controlled, wedge expansion anchor which is designed for consistent performance. It is available in threaded, rod hanger and tie-wire versions suitable for applications in solid concrete and grout-filled concrete masonry. The threaded version is produced in carbon steel and stainless steel to offer various levels of corrosion resistance depending on use. The drill bit diameter necessary for proper installation is the same as the anchor diameter.

Part #	Size	Packaged	Case Quantity
2122-H	3/8" X 2 1/4"	50	N/A
2122-J	3/8" X 3"	50	N/A

Series 2121 Power Bolt



Size Range: 2 1/4" and 3" Material: Carbon Steel

Function: The Power-Bolt anchor, formerly known as the Rawl-Stud, is a heavy duty sleeve style, self locking anchor which is vibration resistant and removable. It is available with a finished hex head or flat head with a hex key insert and can be used in concrete, block, brick or stone.

Part #	Description	Packaged	Weight
2121-H	3/8" X 2 1/4"	50	N/A
2121-J	3/8" X 3"	50	N/A



Hang It Faster!!!

Series 4000 The SLED

Function: The Sled is an easy to use, labor saving tool that eliminates alignment issues and the need for return panels. It is a router guide system that enables the operator to cut return bends directly into grooved radiant flooring panels.





See video demo @ www.WarwickHanger.com

(Shown With Optional Sled Handle)

Part #	Description	Packaged	Weight
4000-1	The Sled	1	15.2 Lbs

Series 4010 The SLED Accessories

Part #	Description	Packaged
4010-1	Sled Vacuum Kit	1
4010-2	Sled Handle	1
4010-3	Sled Wall Kit	1
4010-4	Sled Router Bit	1
4010-5	Sled Replacement Points	4



Series 130 Plastic Coated 2-Hole Pipe Clips

Size Range: 1/2" - 6"
Material: Carbon Steel
Finish: Galvanized Plating

Function: Used to clamp black iron pipe or plastic coated pipe flush to the surface

in both vertical and horizontal applications.



Part #	Size	Gage	Packaged	Case Quantity
130-50-PC	1/2"	18	100	500
130-75-PC	3/4"	18	100	500
130-10-PC	1"	18	50	500
130-12-PC	1 1/4"	18	50	N/A
130-15-PC	1 1/2"	18	50	N/A
130-20-PC	2"	18	50	N/A
130-30-PC	3"	16	25	N/A
130-40-PC	4"	16	25	N/A
130-60-PC	6"	12	25	N/A

Manufactured At Our Rhode Island Facility



Series 4200 Pro-Pitch Pipe Hanger

Size Range: Fits either 1 1/2" or 2" DWV Pipe

Finish: White

Function: Our patented Pro-Pitch Pipe Hanger has a simple and easy design. It's marked in 1/4" increments to allow easy adjustments. The strength and rigidity make it perfect for **Attic**

Vent Pipe or any DWV pipe installation.



Part #	Size	Description	Packaged
4200-1	1 1/2" - 2"	Pro-Pitch Pipe Hanger	25



Terms and Conditions of Sale:

2% 30 Days-Net 31

Please call for Prepaid Freight

Billing Address: 34 Canal Street, Westerly, RI 02891 Shipping Address: 34 Canal Street, Westerly, RI 02891

> Tel: 401-596-8062 Fax: 401-596-8063

Website: www.WarwickHanger.com

Revision: 1036.1



INDEX

ITEM	PAGE	
BAND HANGERS (ADJUSTABLE)		
COPPER PLATED	37	
PLAIN	38	
BELL (VAN) HANGERS		
COPPER PLATED	11	
CORROSION RESISTEN	12	
NARROW COPPER	13	
BEND SUPPORT	6	
CLAMPS		
BEAM RETAINING STRAP	53	
C-CLAMP (STEEL)	55	
CUSHION	43	
DOUBLE BOLT	49	
RISER CLAMPS	46-48	
TOP BEAM	53	
CLEVIS HANGERS	<u> </u>	
CARBON STEEL	45	
COPPER PAINTED	44	
DWV HANGERS		
COPPER PLATED	28	
GALVANIZED	26	
GALVANIZED 1" WIDTH	29	
PLASTIC COATED	27	
PLASTIC COATED 1" WIDTH	29	
SPIRAL VENT	30	
Z-VENT	30	
FLANGES	<u>50</u>	
CEILING	54	
GAS VENT SIGN	9	
HANGER STRAPPING (PERFORATED)		
COPPER	<u> 25</u>	
GALVANIZED	25	
PLAIN	25	
PLASTIC	25	



HARDWARE	
ANGLE BRACKETS	60
DRIVE SCREWS	59
DROP IN ANCHOR	59
HEAVY HEX BOLT	59
HEAVY HEX NUT	58
LAG ENDS	63
LAG SCREWS	56
MECHANICAL ANCHORS	62
MUSHROOM DRIVE PINS	59
NYLON NAILIN	61
POWER BOLT	64
POWER STUD	64
ROD COUPLINGS-COUPLING REDUCERS	56
SPRING NUTS	60
SPRINGLESS NUTS	60
THREADED RODS	57
WALL DOG	61
WASHERS	58
FENDER WASHERS	59
ISOLATION CLIP	7
J HOOKS	
DWV AND CTS	32
GLIDE LOCK	31
J CLIP WITH NAIL	5,6
MILFORD TYPE HANGERS	17
NARROW	18
NAILING HOOKS	14
NAILING PLATES	33
NATICK TYPE HANGERS	15
NARROW	16
PIPE CLIPS	
COPPER (2 HOLE)	4
GALVANIZED (2 HOLE)	10
GALVANIZED (PLASTIC COATED)	66
GLIDE LOCK	7
MANIFOLD	8
SCREWS	8
SPACERS	8
PLASTIC CLIPS	5,6,7,8
CLOSED CLAMP WITH NAIL	6



PIPE HANGERS (BLACK IRON)	24
PIPE SHIELDS	52
PRO-PITCH HANGER	67
RISER CLAMPS	
COPPER PAINTED	46
PLAIN	47
SHORT ARM	48
SIDE BEAM CONNECTOR	54
SLED	65
SLED ACCESSORIES	65
SPLIT RING HANGERS	
BLACK	36
COPPER PLATED	34
GALVANIZED	35
STRUT CLAMPS	
COPPER PLATED	41
GALVANIZED	42
CUSHION CLAMPS	43
STUD PROTECTORS	51
SWIVEL HANGERS	
COPPER PLATED	39
GALVANIZED	40
TRAP COVERS	14
TUBE SUPPORT BRACKET	23
WIRE HOOKS	
COPPER PLATED	19
PLAIN BLACK	21
PLASTIC COATED COPPER	20
PLASTIC COATED BLACK	22