# **ALPHA™ RESTRAINED JOINT** RESTRAINED FLANGED COUPLING

# SUBMITTAL INFORMATION



## USE

Provides a Restrained Joint for multi-purpose use from IPS PVC through Cast iron to flanged fittings. The ALPHA FC can accommodate up to 4 degrees of deflection. The XL may have limited deflection at the top of the range (2 degrees max.).

# **FLANGE**

Compatible with ANSI Class 125 and 150 bolt circles.

# **MATERIALS**

#### **CASTINGS**

All cast components (end rings, center ring, and bolt guides) are ductile iron, meeting or exceeding the requirements of ASTM A 536, grade 65-45-12.

## **GRIPPERS**

Ductile (nodular) iron, meeting or exceeding ASTM A 536, Grade 65-45-12. Machine sharpened and heat treated. Xylan 1424 coated for superior corrosion resistance.

#### **GASKETS**

SBR compounded for water and sewer service per ASTM D2000, classified by UL to meet NSF61 or NBR compounded for water and sewer service per ASTM D2000, NSF61 Certified. O-Ring style flange gasket is NBR in accordance with ASTM D2000, NSF61 Certified. Other compounds available upon request.

#### **DRAW HOOKS**

Uncoated 304 stainless steel.

#### RAMP RUNNERS

Nylon 66, Black, 14% Glass filled

### **BOLTS AND NUTS**

5/8-11 bolts with heavy hex nuts. E-coated nuts, 304 stainless steel. Fasteners provided with anti-galling protection. 316 stainless steel available by request.

#### **COATINGS**

Flanged coupling body is Romacote fusion bonded epoxy, NSF 61 Certified. End rings are Romabond polyester.

## **PRESSURE**

When properly installed, the Romac ALPHA coupling can be used at a working pressures equal to the rating of the installed pipe up to 350 psi.

# PIPE MATERIALS

The Romac ALPHA series couplings can be used on DI, Oversized Cast Iron, PVC (IPS, C900, C909), and HDPE (SDRs 9, 11, 13.5 and 17). Stiffener not required.

# **SIZES & RANGES**

See catalog.

This information is based on the best data available at the date printed above. Please check with Romac for any updates or changes.

