


## PV-LOK<sup>™</sup> MODEL PWP SERRATED BELL JOINT RESTRAINT FOR AWWA C900/905 PVC PIPE



## **PRODUCT SPECIFICATIONS**

MATERIAL:	Machine-serrated clamping ring is manufactured of high strength ductile iron in accordance with ASTM A536, Grade 65-45-12. Side clamping bolts and hex nuts are manufactured of high strength steel in accordance with ASTM A449 and zinc-plated to B663, Type III Sec.1 for corrosion resistance.
SIZE RANGE:	4" through 48"
DIMENSION:	Conform to ANSI/AWWA C900/905 standards
PRESSURE RATINGS:	Equal to the water working pressure rating of the pipe upon which it is installed with a minimum 2:1 factor of safety.
COATING:	Red Alkyd paint Electro-deposition "CORRSAFE™" available upon request. For further information, please refer to our CORRSAFE Product Information sheet at http://www.sigmaco. com/pipe-restraint-product coatings-linings/
APPROVALS:	Factory Mutual approved in sizes 4", 6", 8" & 10"
DEFLECTION:	Maintains the allowable nominal deflection within the PVC pipe manufacturer recommendation for AWWA C900/905 PVC pipe bells.
TRACEABILITY:	Machine-serrated clamping rings are individually cast with exact heat code information.
INSTALLATION:	In accordance with manufacturer's recommendation and applicable AWWA standards.