AMERISTAR DUCTLESS SYSTEMS 18 SEER LOW AMBIENT SINGLE ZONE

Ameristar^{*}

The Ameristar line of heating and cooling products offer you flexible and affordable options for HVAC equipment replacement. The Ameristar product line should complement the national brand you are selling and provide an opportunity to capture additional volume and market share with today's budget-conscious consumers.

The Ameristar Ductless family offers a cost-effective solution for heating and cooling in single-zone applications.



- Available for installations in all regions (18 SEER)
- 9000, 12000, 18000, and 24000 BTUH models available
- -Quiet operation (39-52 db)
- temperatures as low as -13° F. – Inverter driven (Variable Speed Compressor)

- Matched Ameristar ductless products

have cooling capabilities at outdoor ambient temperatures as low as 0° F and

heating capabilities at outdoor ambient

- Hand held remote controller included
- -Includes base pan heaters
- Blue Fin Coastal coating
- -AHRI Certified Systems

18 SEER HP Low Ambient Single Zone Ductless Systems

IO SELITIF LOW	Amplem Single /	Lone Du	Citess 2	ysieilis							
Outdoor	Indoor	SEER	HSPF	EER	Capacity (BTUH) Cooling	Capacity (BTUH) Heating	Voltage	Gas Line	Liquid Line	Max Overcurrent Protection	
M4TLS1809A11NA	M4MLW1809A1N0A	18.5	10.2	10.6	9200	10000	208-230/60/1	3/8"	1/4"	15	
M4TLS1812A11NA	M4MLW1812A1N0A	18.5	9.2	10.4	12100	12900	208-230/60/1	3/8"	1/4"	15	
M4TLS1818A11NA	M4MLW1818A1N0A	18.0	9.2	9.9	17800	20000	208-230/60/1	1/2"	1/4"	25	
M4TLS1824A11NA	M4MLW1824A1N0A	18.4	10.5	11.0	22800	25000	208-230/60/1	5/8"	1/4"	25	



Hand held remote includes many features including: I-Feel, X-Fan, and Sleep Mode.

AMERISTAR WARRANTIES

Registered Limited Warranty terms are applicable if the products are registered within 60 days of installation. Products can be registered online at ameristarac.com or by phone at 866-554-5611, otherwise Ameristar's Base Limited Warranty terms will apply. Base Limited Warranty terms can be found online at ameristarac.com. Warranties are for residential use only: some restrictions may apply. Warranties available include:

• 5-Year Base Limited Parts Warranty

• 10-Year Registered Parts Warranty

©2018 Ingersoll-Rand Company 92-1027-01

