


Zinc

Specification: ASME B18.21.1

Finish: Fe/Zn 3AN per ASTM F1941/F1941M



SKU	Nominal Size (ID X OD)	A			B			C		
		Inside Diameter (in)			Outside Diameter (in)			Thickness (in)		
		Basic	Max	Min	Basic	Max	Min	Basic	Max	Min
FNWFENWZ12112	1/2 x 1-1/2	0.535	0.525	0.545	1.500	1.492	1.529	0.065	0.047	0.080
FNWFENWZ122	1/2 x 2	0.535	0.525	0.545	2.000	1.992	2.029	0.065	0.047	0.080
FNWFENWZ141	1/4 x 1	0.285	0.275	0.295	1.000	0.992	1.029	0.065	0.047	0.080
FNWFENWZ14112	1/4 x 1-1/2	0.285	0.275	0.295	1.500	1.492	1.529	0.065	0.047	0.080
FNWFENWZ14114	1/4 x 1-1/4	0.285	0.275	0.295	1.250	1.242	1.279	0.065	0.047	0.080
FNWFENWZ3161	3/16 x 1	0.190	0.213	0.233	1.000	0.992	1.018	0.065	0.047	0.080
FNWFENWZ316114	3/16 x 1-1/4	0.190	0.213	0.233	1.250	1.242	1.279	0.065	0.047	0.080
FNWFENWZ342	3/4 x 2	0.823	0.804	0.841	2.000	1.992	2.029	0.065	0.047	0.080
FNWFENWZ38112	3/8 x 1-1/2	0.410	0.400	0.420	1.500	1.492	1.529	0.065	0.047	0.080
FNWFENWZ38114	3/8 x 1-1/4	0.410	0.400	0.420	1.250	1.242	1.279	0.065	0.047	0.080
FNWFENWZ382	3/8 x 2	0.410	0.400	0.420	2.000	1.992	2.029	0.065	0.047	0.080
FNWFENWZ516112	5/16 x 1-1/2	0.348	0.338	0.358	1.500	1.492	1.529	0.065	0.047	0.080
FNWFENWZ516114	5/16 x 1-1/4	0.348	0.338	0.358	1.250	1.242	1.279	0.065	0.047	0.080