





3C ProPolymer® HAZ-LO® Flashlight

FL 1 STANDARD	3C PROPOLYMER HAZ-LO
	150 LUMENS
	18h
	167m
	7,000cd



- Material/Lens** Impact and chemical resistant Engineering Polymer resin; o-ring sealed and vented. Available in high visibility yellow or orange. Unbreakable polycarbonate lens with scratch resistant coating
- Dims/Weight** Length: 9.30 in. (23.62 cm); Body diameter: 1.46 in. (3.71 cm); Face cap diameter: 2.08 in. (5.28 cm); 6.8 oz (193 grams) without batteries; 13.9 oz (394 grams) with batteries (batteries sold separately)
- Light Source** C4® LED technology, shock-proof with a 50,000 hour lifetime. Lightly textured parabolic reflector produces a smooth uniform beam with optimum peripheral illumination. Regulated run time provides consistent performance throughout battery life
- Switch** Push-button tail switch. Sealed switch design protects it from corrosion caused by battery leakage
- Battery** Three "C" alkaline batteries (sold separately)
- Features**
- High-performance, anti-static, thermoplastic material resistant to chemicals and solvents
 - "Captured locking" set screw will not back out - prevents FOD (Foreign Object Debris)
 - Safety measure: Set screw helps to avoid batteries being changed out, or the housing inadvertently being opened in a hazardous environment
 - Set screw goes into a metal tray that evenly distributes pressure to protect the body from over-tightening of the set screw
 - Re-inforced pocket clip clamps securely to belts and gear
 - IP67 rated for dust-tight and waterproof to 1 meter for 30 minutes; IPX4 for water spray
 - 3 meter impact resistance tested
 - Larger size makes the 3C ProPolymer HAZ-LO ideally suited for situations where gloves are typically worn
- Approvals** C-UL-US Classified Class I, Division 1, Groups A,B,C,D; Class II, Division 1, Groups E,F,G; Class III; Exia; Temperature Code T4
- Most models meet applicable European Community Directives
- MSHA** MSHA Permissible Flashlight. Approval No. 20-A130003-0 Tested for Intrinsic Safety in Methane-Air mixtures only.
- ATEX** FTZU 11 ATEX 0183X; II 1G Ex ia IIC T4 Ga; II 1D Ex ia IIIC T99C Da
- IECEX** IECEX FTZU 14.0011X; Ex ia IIC T4 Ga; Ex ia IIIC T99°C Da
- InMetro** UL-BR 12.0516X; Ex ia IIC T4 Ga; Ex ia IIIC T99°C
- Warranty** Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

Item	UPC	Part #
3C ProPolymer HAZ-LO - Yellow	080926-33820-3	33820
3C ProPolymer HAZ-LO - Orange	080926-33822-7	33822
3C ProPolymer HAZ-LO (InMetro) - Yellow	080926-33824-1	33824
3C ProPolymer HAZ-LO (InMetro) - Orange	080926-33825-8	33825
Lanyard with Push Button Slide*	080926-72024-4	72024
Holster	080926-25090-1	25090

*Image not available



STREAMLIGHT



30 Eagleview Road • Eagleview, PA 19403 • 610-631-0600/800-523-7488 Phone • 610-631-0712/800-220-7007 Fax
www.streamlight.com ©Streamlight, Inc. 3C ProPolymer HAZ-LO 2/15