ADS POTABLE WATER SERVICE TUBING (CTS) PIPE SPECIFICATIONS

Scope

This specification describes ADS Potable Water Service Tubing (CTS) pipe SDR 9 for use in potable water service applications.

Pipe Requirements

ADS potable water service tubing shall meet the requirements of ASTM D2737, AWWA C901 and NSF Standards 14 and 61. Pipe dimensions shall meet Copper Tubing Size (CTS) standards.

Material Properties

Tubing material shall be high-density polyethylene conforming to the minimum requirements of cell classification 445574E as defined and described in ASTM D3350. The resin shall have a material designation code of PE4710 by the Plastic Pipe Institute.

Disinfection/Maintenance

The active chlorine content of disinfecting solutions shall not exceed 12%. All disinfecting solution must be flushed from all lines within the system. Industry accepted procedures, like ANSI/AWWA C651 *Disinfecting Water Mains*, should be followed for both new and repaired potable water lines.

Installation

Installation is similar to other flexible tubing/pipe products. Methods including direct bury, plowing or pulling are applicable per local, state or federal guidelines for the application.

Tubing Properties

		3/4"	1"	1 1/4"	1 1/2"	2"
SDR 9	Outside Diameter.	0.875 ±0.004	1.125 ±0.005	1.375 ±0.005	1.625 ±0.006	2.125 ±0.006
	in (mm)	(22.2 ±0.10)	(28.6 ±0.13)	(34.9 ±0.13)	(41.3 ±0.15)	(54.0 ±0.51)
	Wall Thickness.	0.097 +0.010	0.125 +0.012	0.153 +0.015	0.181 +0.018	0.236 +0.024
	in (mm)	(2.5 +0.25)	(3.2 +0.30)	(3.9 +0.38)	(4.6 +0.46)	(6.0 +0.61)
	Pressure Rating @ 73°F,	250	250	250	250	250
	psi (kPa)	(1724)	(1724)	(1724)	(1724)	(1724)
	Weight, gm/ft (gm/m)	46 ±2	78 ±3	125 ±4	162 ±4	275 ±5
		(151 ±7)	(256 ±10)	(410 ±13)	(531 ±13)	(902 ±16)