

Nipples Product

PVC, CPVC & PE Nipples



- PVC/CPVC Nipples furnished may be produced from extruded stock, or from molding grade PVC/CPVC compounds. Both processes provide quality products meeting ASTM requirements.
- For half Size Nipples, go to the same as the next full size for MSRP.
For example: 7-1/2" is the same as 8".
- CONTACT YOUR LOCAL SPEARS® REPRESENTATIVE FOR MSRP AND AVAILABILITY OF SIZES, LENGTHS, AND/OR CONFIGURATIONS NOT SHOWN.

PVC Nipples

PVC Schedule 80 Nipples

Size	Threaded Both Ends	Threaded One End	Plain End	Std Pk	Mstr Pk	Prod Code
1/8" Diameter						
1/8XCLOSE	879-005 1.45	1879-005 1.45	879-005P 1.45	25	800	120
1/8X1-1/2	879-015 1.45	1879-015 1.45	879-015P 1.45	25	800	120
1/8X2	879-020 1.64	1879-020 1.64	879-020P 1.64	25	800	120
1/8X2-1/2	879-025 1.73	1879-025 1.73	879-025P 1.73	25	800	120
1/8X3	879-030 2.07	1879-030 2.07	879-030P 2.07	25	800	120
1/8X3-1/2	879-035 2.17	1879-035 2.17	879-035P 2.17	25	800	120
1/8X4	879-040 2.31	1879-040 2.31	879-040P 2.31	25	800	120
1/8X4-1/2	879-045 2.34	1879-045 2.34	879-045P 2.46	25	600	120
1/8X5	879-050 2.57	1879-050 2.57	879-050P 2.16	25	600	120
1/8X5-1/2	879-055 2.67	1879-055 2.67	879-055P 2.67	25	600	120
1/8X6	879-060 2.74	1879-060 2.74	879-060P 2.74	25	600	120
1/8X7	879-070 2.87	1879-070 2.87	879-070P 2.87	25	450	120
1/8X8	879-080 3.25	1879-080 3.25	879-080P 3.25	25	600	120
1/8X9	879-090 3.42	1879-090 3.42	879-090P 3.42	25	400	120
1/8X10	879-100 3.94	1879-100 3.94	879-100P 3.94	25	400	120
1/8X11	879-110 4.06	1879-110 4.06	879-110P 4.06	25	400	120
1/8X12	879-120 4.25	1879-120 4.25	879-120P 4.25	25	400	120
1/8X13	879-130 4.46	1879-130 4.46	879-130P 4.46	25	400	120
1/8X14	879-140 4.96	1879-140 4.96	879-140P 4.96	25	250	120
1/8X15	879-150 6.31	1879-150 6.31	879-150P 6.31	25	300	120
1/8X16	879-160 6.97	1879-160 6.97	879-160P 6.97	25	250	120
1/8X17	879-170 7.25	1879-170 7.25	879-170P 7.25	25	250	120
1/8X18	879-180 7.45	1879-180 7.45	879-180P 7.45	25	0	120
1/8X19	879-190 7.94	1879-190 7.94	879-190P 7.94	5	0	120

PVC Schedule 80 Nipples (continued)

Size	Threaded Both Ends	Threaded One End	Plain End	Std Pk	Mstr Pk	Prod Code
1/8" Diameter						
1/8X20	879-200 8.45	1879-200 8.45	879-200P 8.45	25	0	120
1/8X22	879-220 9.03	1879-220 9.03	879-220P 9.03	25	0	120
1/8X24	879-240 9.13	1879-240 9.13	879-240P 9.13	25	0	120
1/8X30	879-300 12.56	1879-300 12.56	879-300P 12.56	25	0	120
1/8X36	879-360 14.78	1879-360 14.78	879-360P 14.78	25	0	120
1/8X42	879-420 17.22	1879-420 17.22	879-420P 17.22	25	0	120
1/8X48	879-480 19.67	1879-480 19.67	879-480P 19.67	25	0	120

1/4" Diameter

1/4XCLOSE	880-005 1.51	1880-005 1.96	880-005P 1.96	25	1200	120
1/4X1-1/2	880-015 1.51	1880-015 2.13	880-015P 2.13	25	1200	120
1/4X2	880-020 1.85	1880-020 2.13	880-020P 2.13	25	500	120
1/4X2-1/2	880-025 2.27	1880-025 2.27	880-025P 2.27	25	500	120
1/4X3	880-030 2.47	1880-030 2.59	880-030P 2.59	25	550	120
1/4X3-1/2	880-035 2.74	1880-035 2.74	880-035P 2.74	25	500	120
1/4X4	880-040 2.87	1880-040 2.97	880-040P 2.97	25	300	120
1/4X4-1/2	880-045 3.09	1880-045 3.09	880-045P 3.09	25	250	120
1/4X5	880-050 3.12	1880-050 3.34	880-050P 3.34	25	250	120
1/4X5-1/2	880-055 3.54	1880-055 3.54	880-055P 3.54	25	250	120
1/4X6	880-060 3.58	1880-060 3.58	880-060P 3.58	25	250	120
1/4X7	880-070 3.82	1880-070 3.82	880-070P 3.82	25	250	120
1/4X8	880-080 4.04	1880-080 4.04	880-080P 4.04	25	250	120
1/4X9	880-090 4.16	1880-090 4.16	880-090P 4.16	25	250	120
1/4X10	880-100 4.23	1880-100 4.23	880-100P 4.23	25	250	120
1/4X11	880-110 4.43	1880-110 4.43	880-110P 4.43	25	250	120
1/4X12	880-120 4.63	1880-120 4.63	880-120P 4.63	25	250	120



Nipples Product PVC, CPVC & PE Nipples

PVC Nipples

PVC Schedule 80 Nipples (continued)

Size	Threaded Both Ends	Threaded One End	Plain End	Std Pk	Mstr Pk	Prod Code
1/4" Diameter						
1/4X13	880-130 6.40	1880-130 6.40	880-130P 6.40	25	250	120
1/4X14	880-140 6.46	1880-140 6.46	880-140P 6.46	25	250	120
1/4X15	880-150 6.85	1880-150 6.85	880-150P 6.85	25	500	120
1/4X16	880-160 7.29	1880-160 7.29	880-160P 7.29	25	250	120
1/4X17	880-170 7.53	1880-170 7.53	880-170P 7.53	25	300	120
1/4X18	880-180 7.78	1880-180 7.78	880-180P 7.78	25	300	120
1/4X19	880-190 8.05	1880-190 8.05	880-190P 8.05	25	300	120
1/4X20	880-200 8.65	1880-200 8.65	880-200P 8.65	25	200	120
1/4X22	880-220 9.15	1880-220 9.15	880-220P 9.15	25	300	120
1/4X24	880-240 9.52	1880-240 9.52	880-240P 9.52	25	200	120
1/4X30	880-300 12.68	1880-300 12.68	880-300P 12.68	25	0	120
1/4X36	880-360 15.57	1880-360 15.57	880-360P 15.57	25	0	120
1/4X42	880-420 18.05	1880-420 18.05	880-420P 18.05	25	0	120
1/4X48	880-480 20.37	1880-480 20.37	880-480P 20.37	25	0	120

3/8" Diameter

3/8XCLOSE	881-005 2.04	1881-005 2.04	881-005P 2.04	25	800	120
3/8X1-1/2	881-015 1.57	1881-015 2.25	881-015P 2.25	25	800	120
3/8X2	881-020 2.02	1881-020 2.41	881-020P 2.41	25	600	120
3/8X2-1/2	881-025 2.47	1881-025 2.47	881-025P 2.47	25	600	120
3/8X3	881-030 2.02	1881-030 2.68	881-030P 2.68	25	400	120
3/8X3-1/2	881-035 2.87	1881-035 2.87	881-035P 2.87	25	400	120
3/8X4	881-040 2.41	1881-040 3.06	881-040P 3.06	25	300	120
3/8X4-1/2	881-045 3.15	1881-045 3.15	881-045P 3.15	25	250	120
3/8X5	881-050 3.45	1881-050 3.45	881-050P 3.45	25	250	120
3/8X5-1/2	881-055 3.62	1881-055 3.62	881-055P 3.62	25	250	120
3/8X6	881-060 3.73	1881-060 3.73	881-060P 3.73	25	250	120
3/8X7	881-070 3.88	1881-070 3.88	881-070P 3.88	25	200	120
3/8X8	881-080 4.16	1881-080 4.16	881-080P 4.16	25	200	120
3/8X9	881-090 4.21	1881-090 4.21	881-090P 4.21	25	200	120

PVC Schedule 80 Nipples (continued)

Size	Threaded Both Ends	Threaded One End	Plain End	Std Pk	Mstr Pk	Prod Code
3/8" Diameter						
3/8X10	881-100 4.36	1881-100 4.36	881-100P 4.36	25	200	120
3/8X11	881-110 4.59	1881-110 4.59	881-110P 4.59	25	200	120
3/8X12	881-120 4.83	1881-120 4.83	881-120P 4.83	25	200	120
3/8X13	881-130 6.87	1881-130 6.87	881-130P 6.87	25	0	120
3/8X14	881-140 7.13	1881-140 7.13	881-140P 7.13	25	200	120
3/8X15	881-150 7.46	1881-150 7.46	881-150P 7.46	25	200	120
3/8X16	881-160 7.66	1881-160 7.66	881-160P 7.66	25	200	120
3/8X17	881-170 7.94	1881-170 7.94	881-170P 7.94	25	0	120
3/8X18	881-180 8.21	1881-180 8.21	881-180P 8.21	25	200	120
3/8X19	881-190 8.39	1881-190 8.39	881-190P 8.39	25	0	120
3/8X20	881-200 8.62	1881-200 8.62	881-200P 8.62	25	250	120
3/8X22	881-220 9.33	1881-220 9.33	881-220P 9.33	25	200	120
3/8X24	881-240 9.55	1881-240 9.55	881-240P 9.55	25	200	120
3/8X30	881-300 12.87	1881-300 12.87	881-300P 12.87	25	0	120
3/8X36	881-360 17.02	1881-360 17.02	881-360P 17.02	25	0	120
3/8X42	881-420 18.58	1881-420 18.58	881-420P 18.58	25	0	120
3/8X48	881-480 21.03	1881-480 21.03	881-480P 21.03	25	0	120

1/2" Diameter

1/2XCLOSE	882-005 1.36	1882-005 2.22	882-005P 2.22	25	675	120
1/2X1-1/2	882-015 1.36	1882-015 2.22	882-015P 2.22	25	600	120
1/2X2	882-020 1.45	1882-020 2.32	882-020P 2.32	50	300	120
1/2X2-1/2	882-025 1.45	1882-025 2.51	882-025P 2.51	50	600	120
1/2X3	882-030 1.64	1882-030 2.61	882-030P 2.61	50	600	120
1/2X3-1/2	882-035 1.64	1882-035 2.71	882-035P 2.71	25	300	120
1/2X4	882-040 1.92	1882-040 2.82	882-040P 2.82	25	300	120
1/2X4-1/2	882-045 1.92	1882-045 2.91	882-045P 2.91	25	300	120
1/2X5	882-050 2.14	1882-050 2.94	882-050P 2.94	25	300	120
1/2X5-1/2	882-055 3.02	1882-055 3.02	882-055P 3.02	25	300	120
1/2X6	882-060 2.24	1882-060 3.11	882-060P 3.11	25	300	120
1/2X7	882-070 2.60	1882-070 3.44	882-070P 3.44	25	200	120