## ABOVE-GRADE FLASHING DRAIN

833 series Finish Line™

#### **SPECIFICATION**

Sioux Chief 833 series Finish Line adjustable above-grade flashing drain shall be used where necessary in drainage systems. Flashing drain shall allow adjustment of 1.25" before the concrete pour, and 1.25" after the concrete pour. Flashing drain shall have an invertible flashing collar and a cast iron no-hub or push-joint connection. Strainer shall meet applicable load requirements for intended use. Trap primer port shall be threaded  $^{1}\!\!/_{2}$  FIP and plugged for optional connection. Designed in accordance with ASME A112.6.3-2001

#### **MATERIALS**

ring/strainer: nickel-bronze, 304 stainless steel, ductile iron head adapter, coring sleeve, flashing collar: ductile iron

coring plug: high-impact polymer

base adapter: cast iron

#### STRAINER LOAD RATING

nickel-bronze: 1,000 lbs. (light duty, pedestrian traffic - heel-proof) stainless steel: 2,000 lbs. (light duty, pedestrian traffic - heel-proof) ductile iron: 5,000 lbs. (heavy duty)

#### STRAINER FREE AREA

	large	standard
round nickel-bronze/stainless:	11.75 in <sup>2</sup>	7.5 in <sup>2</sup>
square nickel-bronze/stainless:	16.4 in <sup>2</sup>	12.75 in <sup>2</sup>
ductile iron:	13.25 in <sup>2</sup>	_

#### **DIMENSIONS**

A: connection 2", 3", or 4"

B: ring/strainer diameter

round 5½" or 64½" or 64½" or 7" C: flange diameter 84½"


D: pre-pour adjustment

no-hub 47/8"-75/16" push-joint 51/4"-711/16"


E: post-pour adjustment

round 0"-1½" square  $5\frac{1}{16}$ "-1½"

Trap primer port ½" FIP thread, plugged









**ACCESSORIES** 

Models 833-23DiR, 833-23DNR, and 833-23DNQ are UPC listed

### Create Item Number

Δ

CONNECTION TYPE

# 833-<u>ABCD</u>

e.g. 833-23DNRV = Finish Line flashing drain with 3" no-hub connection with vandal resistant nickel ring and strainer

RING & STRAINER

$\Delta$	CONNECTION THE	<u>U</u>	MING & STITAINEN		ACCESSORIES
□ 2	no-hub	□ iR	round ductile iron1		832-UM stainless steel debris screen 5
□ 6	push-joint	$\square$ NR	round nickel-bronze		832-S4 shim kit
		□ NQ	square nickel-bronze		832-EX4 ductile iron extension nipple 5,6
<u>B</u>	CONNECTION / TOP SIZE	□ SR	round stainless steel		832-W locating bristle kit
□ 2D	2" conn. / large top	□ SQ	square stainless steel		863-FN nickel-bronze funnel
□ 25D	2" conn. / standard top	1 Avai	ilable in large top only		863-FA aluminum funnel
□ 3D	3" conn. / large top				863-FNO oval nickel-bronze funnel
□ 35D	3" conn. / standard top	D	OPTIONS (FACTORY INSTALLED)	5	For use with large top only
□ 4D	4" conn. / large top	□ V	vandal-resistant strainer screws	6	Extends heads 2" (min) to 4" (max) above coring sleeve
		□Н	hinged strainer <sup>2</sup>		
		□Е	13/8" extended strainer rim 3		
		□В	complies with Buy American Act 4		
		2 Avai	ilable for large nickel-bronze or stainless steel only	,	
		3 Avai	ilable for large, round nickel-bronze strainers only		
		4 Avai	lable for round nickel-bronze strainers only		
	0114				