




**Schedule 80 PVC Technical  
Schedule 80 Unions**

**Union 2000 - Fipt/FKM**

Fipt x Fipt with FKM O-ring Seal  
 Dimensions Also Applicable to  
 8098-XXX EPDM O-Ring Seals




Pressure Rating  
 1/4" - 4" 235 psi @ 73°F  
 6" 150 PSI @ 73°F

Part Number	Size	L	M	N	NUT O.D.	Approx. Wt. (Lbs.)
858-002	1/4	1-15/16	15/16	11/16	1-21/32	.09
858-003	3/8	2- 5/32	1- 1/32	15/16	1-25/32	.12
8058-005	1/2	1-29/32	1- 3/16	17/32	1- 7/8	.12
8058-007	3/4	2- 1/16	1- 3/8	9/16	2- 9/32	.18
8058-010	1	2-17/32	1-11/16	25/32	2- 9/16	.28
8058-012	1-1/4	2-21/32	2- 1/32	3/4	3- 1/8	.40
8058-015	1-1/2	2-25/32	2- 3/8	29/32	3- 1/2	.54
8058-020	2	3- 1/8	3	1- 3/16	4- 7/32	.90
8058-025	2-1/2	4- 1/32	3- 9/16	1-15/32	6- 5/32	2.28
8058-030	3	4- 5/32	4- 9/32	1-13/32	6- 5/32	2.37
8058-040	4	4-21/32	5- 1/4	1-21/32	7- 3/4	3.88
8058-060	6	6- 1/8	7-21/32	2-13/16	11-19/32	12.22

**Union 2000 - Special Reinforced Fipt/FKM**

SR Fipt x SR Fipt w/FKM O-ring Seal - Stainless Steel Collar  
 Dimensions Also Applicable to  
 8098-XXXSR EPDM O-Ring Seals



Pressure Rating  
 1/2" - 4" 235 psi @ 73°F  
 6" 150 PSI @ 73°F

Part Number	Size	L	M	N	NUT O.D.	Approx. Wt. (Lbs.)
8058-005SR	1/2	2	1- 3/16	5/8	1- 7/8	.14
8058-007SR	3/4	2- 5/32	1- 3/8	21/32	2- 9/32	.21
8058-010SR	1	2- 9/16	1-11/16	13/16	2- 9/16	.31
8058-012SR	1-1/4	2-23/32	2- 1/32	13/16	3- 1/8	.44
8058-015SR	1-1/2	2-27/32	2-13/32	29/32	3-17/32	.60
8058-020SR	2	3- 7/32	3- 1/32	1- 3/16	4- 7/32	.97
8058-025SR	2-1/2	4- 3/32	3- 9/16	1-15/32	6- 5/32	2.37
8058-030SR	3	4- 3/16	4- 9/32	1- 3/8	6- 5/32	2.49
8058-040SR	4	4-23/32	5- 1/4	3/4	7-3/4	3.96
8058-060SR	6	6- 3/16	7-11/16	2-13/16	11- 5/8	12.05