

# Commercial Gas Water Heaters

#### **MASTER-FIT® BTR**

The Master-Fit® BTR series provides outstanding performance and maximum installation flexibility for both new construction and replacement applications. Multiple options for placement of water connections and low installation clearances are additional installer-friendly features.

#### FACTORY-INSTALLED DRAFT DIVERTER AND AUTOMATIC FLUE DAMPER (BTR-120-400 MODELS)

- Low-profile draft diverter helps for installation in tight spaces
- Automatic motorized flue damper helps minimize standby heat loss
- BTR-500 Model features induced draft design and no damper

### THREE WATER CONNECTION OPTIONS FOR ADDED FLEXIBILITY

- Hot and cold water connections can be made through front, top or back of unit
- Eliminator<sup>™</sup> system operates when cold water is connected through front

### PERMAGLAS® ULTRA COAT™ GLASS LINING

- Exclusive process provides superior protection against corrosion
- CoreGard<sup>™</sup> anode rods with stainless steel core provide additional corrosion protection

### INTERMITTENT ELECTRONIC IGNITION

- Eliminates standing pilot, saves energy
- Includes power ON/OFF switch
- Provides flame failure response in less than one second

## FACTORY- INSTALLED, CSA CERTIFIED AND ASME RATED T&P RELIEF VALVE

### MAXIMUM HYDROSTATIC WORKING PRESSURE: 160 PSI

#### **CODES AND STANDARDS**

- Design-certified by UL (Underwriters Laboratories), according to ANSI Z.21.10.3 - CSA 4.3 standards governing storage-type water heaters
- Meets the thermal efficiency and standby loss requirements of the U.
   Department of Energy and current edition of ASHRAE/IESNA 90.1
- Design-certified by Underwriters Laboratories Sanitation to NSF Standard 5 for 180°F (82°C) water
- Optional ASME tank construction available on select models

### THE ELIMINATOR™ SELF-CLEANING SYSTEM

- Designed to significantly reduce or eliminate sediment build-up inside the tank
- Reduced sediment build-up maintains rated thermal efficiency and reduces water heating costs
- Self-cleaning system maximizes tank life

### 3-YEAR LIMITED TANK / 1-YEAR LIMITED PARTS WARRANTY

 For complete warranty information, consult written warranty or go to hotwater.com.



BTR-120 THROUGH BTR-500(A)

#### THE ELIMINATOR™ SELF-CLEANING SYSTEM















### Commercial Gas Water Heaters

#### **OTHER MASTER-FIT® FEATURES**

#### **FULLY AUTOMATIC CONTROL SYSTEM**

- Manual-reset gas shut-off device prevents excessive water temperature
- Adjustable thermostat with 120°F 180°F range
- Gas pressure regulator and pilot filter

#### **HANDHOLE CLEANOUT**

Allows easy access to tank interior for cleaning

#### **PLUG KITS**

 Pipe nipples and caps included to plug unused water connections MASTER-FIT® OPTIONS:

#### MANIFOLD KITS FOR MULTIPLE HEATER INSTALLATIONS

- 2-unit kit, Part Number 100109228
- 3-unit kit, Part Number 100109229
- 4-unit kit, Part Number 100109230

#### **OPTIONAL LEG KIT TO MEET NSF STANDARD 5**

• For all BTR models, Part Number 100109227


#### MECHANICAL VENTING KITS


- For BTR-120 through BTR-200, Part Number 100110445
- For BTR-250 through BTR-400, Part Number 100109235
- For installation of approved power venter to operate in conjunction with water heater thermostat
- Field wiring should conform to latest version of the National Electric Code ANSI/NFPA No.70
- For more information, consult manual shipped with water heater or contact the A. O. Smith Technical Support Center at1-800-527-1953

Water Connections in Inches										
Model Number		Inlet		Outlet						
	Тор	Front	Back	Тор	Front	Back				
BTR-120	1-1/2	1-1/2	1-1/2	1-1/2	1-1/2	1-1/2				
BTR-154	1-1/2	1-1/2	1-1/2	1-1/2	1-1/2	1-1/2				
BTR-180	1-1/2	1-1/2	1-1/2	1-1/2	1-1/2	1-1/2				
BTR-197	1-1/2	1-1/2	1-1/2	1-1/2	1-1/2	1-1/2				
BTR-199	1-1/2	1-1/2	1-1/2	1-1/2	1-1/2	1-1/2				
BTR-200(A)	1-1/2	2	2	1-1/2	2	2				
BTR-250(A)	1-1/2	2	2	1-1/2	2	2				
BTR-251(A)	N/A	1-1/2	1-1/2	N/A	1-1/2	1-1/2				
BTR-275(A)	1-1/2	2	2	1-1/2	2	2				
BTR-305(A)	N/A	1-1/2	1-1/2	N/A	1-1/2	1-1/2				
BTR-365(A)	1-1/2	1-1/2	1-1/2	1-1/2	1-1/2	1-1/2				
BTR-400(A)	1-1/2	2	2	1-1/2	2	2				
BTR-500(A)	1-1/2	1-1/2	1-1/2	1-1/2	1-1/2	1-1/2				



### **Commercial Gas Water Heaters**





#### **Dimensions**

Model Number	Inches or CM	Dimensions									Approx. Shipping Weight		
		Α	В	С	D	E	F	G	Н	I	J	Standard	ASME
BTR-120*	Inches	69-3/4"	4-1/4"	59-1/2"	50-7/8"	19-11/16"	19"	1/2"	51-7/8"	6"	27-3/4"	400 lbs.	-
	CM	177	11	151	129	50	48	-	132	15	71	182 Kg	-
BTR-154	Inches	67-1/2"	4-1/2"	62"	53-1/2"	20-1/2"	21"	1/2"	54-5/8"	6"	27-3/4"	470 lbs.	-
B1K-134	CM	171	12	157	136	52	53	-	139	15	71	213 Kg	-
BTR-180	Inches	67-1/2"	4-1/2"	62"	53-1/2"	20-1/2"	21"	1/2"	54-5/8"	6"	27-3/4"	470 lbs.	-
DIN-10U	CM	171	12	157	136	52	53	-	139	15	71	213 Kg	-
BTR-197	Inches	75"	4-1/2"	70	61-1/2"	20-1/2"	21"	1/2"	62-5/8"	6"	27-3/4"	603 lbs.	-
DIN-197	CM	192	12	178	157	52	53	-	159	15	71	273 Kg	
DTD 400	Inches	67-1/2"	4-1/2"	62	53-1/2"	20-1/2"	21"	1/2"	54-1/8"	6"	27-3/4"	470 lbs.	-
BTR-199	CM	171	12	157	136	52	53	-	139	15	71	213 Kg	-
DTD 200(A)	Inches	72"	4-1/2"	65-1/8"	55-7/8"	19-3/4"	23"	1/2"	56-3/8"	6"	30-1/4"	630 lbs.	725 lbs.
BTR-200(A)	CM	183	12	165	142	50	58	-	143	20	77	286 Kg	329 Kg
BTR-250(A)**	Inches	72"	4-1/2"	65-1/8"	55-7/8"	19-3/4"	23"	1/2"	56-3/8"	8"	30-1/4"	630 lbs.	725 lbs.
B1K-23U(A)***	CM	183	12	165	142	50	58	-	143	20	77	286 Kg	329 Kg
BTR-251(A)**	Inches	75"	4-1/2"	65-3/4"	57-1/4"	20"	N/A	1/2"	58-3/4"	8"	27-3/4"	750 lbs.	862 lbs.
B1K-231(A)	CM	191	12	167	145	51	N/A	-	149	20	70	341 Kg	391 Kg
BTR-275(A)**	Inches	72"	4-1/2"	65-1/8"	55-7/8"	19-3/4"	23"	1/2"	56-3/8"	8"	30-1/4"	630 lbs.	725 lbs.
D1R-275(A)***	CM	183	12	165	142	50	58	-	143	20	77	286 Kg	329 Kg
BTR-305(A)	Inches	75"	4-1/2"	65 - 3/4"	57-1/4"	20"	N/A	1/2"	58-3/4"	8"	27.75	750 lbs.	862 lbs.
D1K-303(A)	CM	191	12	167	145	51	N/A	-	149	20	70	341 Kg	391 Kg
BTR-365(A)	Inches	79-1/2"	4-1/2"	70-1/4"	62-1/2"	22-1/2'	23"	3/4"	63"	8"	27-3/4"	725 lbs.	833 lbs.
D111-303(A)	CM	202	12	178	159	57	58	-	160	20	71	329 Kg	379 Kg
BTR-400(A)	Inches	75-1/2"	4-1/2"	67-1/2"	58-1/4"	26-3/4"	23"	3/4"	59"	8"	30-1/4"	760 lbs.	874 lbs.
D1N-400(A)	CM	192	12	171	148	68	58	-	150	20	77	345 Kg	396 Kg
BTR-500(A)†**	Inches	81-1/2"	17.5"	77-1/4"	67-1/2"	27-1/8"	21"	1"	67-1/2"	8"	27-3/4"	812 lbs.	857 lbs.
	CM	209	44	196	171	69	53	3	171	20	70	368 Kg	389 Kg

Specify when ordering propane (LP) gas.

\*Model BTR 120 is shipped with a 6" x 5" flue outlet adapter.

\*\*Models BTR 250, 251, 275 and 500 are shipped with a 8" x 6" flue outlet adapter.

Standard models certified for sea level to 2,000 ft. elevation. Order SMR S54 for elevations up to 8,000 ft.

 $<sup>\</sup>ensuremath{^{\dagger}}$  BTR-500 model features induced draft design and no damper.

Back side water connections, Inlet and outlet, are represented by "E" and "H" respectively for height dimensions.




## **Commercial Gas**

#### CAPACITY, INPUT AND OUTPUT

	Input BTU/HR			Litres	Recovery - Gallons or Litres Per Hour at Degree Rise			
Model Number		Gallons or Litres	Tank Size		40°F	100°F	140°F	
					22°C	56°C	78°C	
BTR-120*	120,000	U.S. Gallons	71	GPH	291	116	83	
		Litres	268	LPH	1102	439	314	
BTR-154	154,000	U.S. Gallons	81	GPH	373	149	107	
		Litres	307	LPH	1412	564	405	
BTR-180	180,000	U.S. Gallons	81	GPH	434	174	124	
		Litres	307	LPH	1643	659	469	
BTR-197	199,000	U.S. Gallons	100	GPH	482	193	132	
	199,000	Litres	307	LPH	1825	731	500	
BTR-199	199,000	U.S. Gallons	81	GPH	482	193	132	
		Litres	307	LPH	1825	731	500	
BTR-200(A)	199,000	U.S. Gallons	100	GPH	482	193	132	
		Litres	379	LPH	1825	731	500	
BTR-250(A)**	250,000	U.S. Gallons	100	GPH	606	242	173	
B1K-230(A)		Litres	379	LPH	2294	918	655	
BTR-251(A)**	251,000	U.S. Gallons	65	GPH	608	243	174	
		Litres	246	LPH	2303	921	658	
BTR-275(A)**	275,000	U.S. Gallons	100	GPH	667	267	190	
		Litres	379	LPH	2524	1009	721	
BTR-305(A)	305,000	U.S. Gallons	65	GPH	739	296	211	
		Litres	246	LPH	2799	1120	800	
BTR-365(A)	365,000	U.S. Gallons	85	GPH	885	354	253	
	303,000	Litres	322	LPH	3349	1340	957	
BTR-400(A)	390,000	U.S. Gallons	100	GPH	970	388	277	
		Litres	379	LPH	3671	1468	1049	
BTR-500(A)†**	500,000	U.S. Gallons	85	GPH	1212	485	346	
DIN-300(A)I		Litres	322	LPH	4588	1835	1311	

Recovery based on 80% efficiency.

#### **SPECIFICATION**



For technical information, call 800-527-1953. A. O. Smith Corporation reserves the right to make product changes or improvements without prior notice.

Specify when ordering propane (LP) gas.
\*Model BTR 120 is shipped with a 6" x 5" flue outlet adapter.

<sup>\*\*</sup>Models BTR 250, 251, 275 and 500 are shipped with a 8" x 6" flue outlet adapter.

Standard models certified for sea level to 2,000 ft. elevation. Order SMR S54 for elevations up to 8,000 ft.

<sup>†</sup> BTR-500 model features induced draft design and no damper.