

CAST IRON THREADED FITTINGS



Class 125 (Standard)

FIG. 3387

Cored Plug






FIGURE 3387 - CORED PLUG			
Nominal Size	Maximum Working Pressure▲	Dimension A	Approx. Wt. Each
In. (mm)	PSI (kPa)	In. (mm)	Lbs. (kg)
1/2*	300	0.94	0.10
15	2065	23.87	0.05
3/4	300	1.07	0.17
20	2065	27.17	0.08
1	300	1.25	0.28
25	2065	31.75	0.13
11/4	300	1.36	0.44
32	2065	34.54	0.20
1½	300	1.45	0.62
40	2065	36.83	0.28
2	300	1.56	0.91
50	2065	39.62	0.41

^{▲ –} Working Pressure Ratings are for reference only and based on Sch. 40 pipe. For the latest UL/ULC, and FM pressure ratings versus pipe schedule, please visit anvilintl.com or contact your local Anvil Representative.

MATERIAL SPECIFICATIONS

Dimensions: ASME B16.14 Material: ASTM A126

Finish: Black or Hot Dip Galvanized per ASTM

A153 Class A

Threads: NPT per ASME B1.20.1

Agency Approvals: All cast iron threaded fittings are

UL/ULC Listed and FM Approved.

 \blacktriangle Pressure - Temperature Ratings in accordance with ASME B16.4 Class 125

PROJECT INFORMATION	APPROVAL STAMP
Project:	☐ Approved
Address:	Approved as noted
Contractor:	☐ Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	

^{*} Part supplied as Solid Plug.